



Engineering Data

ED 19101

Group: **WSHP**

Part Number: ED 19101

Date: **November 2017**

Sound Power Ratings – Enfinity™ Console Model MHC-MHW Water Source Heat Pumps

Sound Power Data - dBA (Tested in Accordance with ARI 350-2000)

Size	Mode	Fan Speed	Voltage	Octave Band (Hz)								Sound Power dB "A" 1.0p ^u	
				125	250	500	1000	2000	4000	8000	RPM		
007	Fan Only	Low	208										
	Cooling			64	58	52	50	41	36	37	990	56	
	Heating			64	57	52	52	42	39	35	1050	56	
	Fan Only	High											
	Cooling			64	59	55	54	47	40	38	1236	58	
	Heating			64	58	55	55	47	41	36	1280	58	
009	Fan Only	Low	208	54	49	50	43	36	37	35	864	50	
	Cooling			66	61	57	54	41	39	38	866	59	
	Heating			70	59	60	52	45	40	37	911	60	
	Fan Only	High		59	55	55	50	44	40	37	1095	56	
	Cooling			66	61	58	55	46	42	39	1045	60	
	Heating			69	61	61	54	48	42	38	1125	61	
012	Fan Only	Low	208	59	53	49	46	41	45	45	1075	53	
	Cooling			66	59	52	50	41	40	45	1040	56	
	Heating			63	61	52	50	42	38	36	1125	56	
	Fan Only	High		63	58	54	53	47	43	41	1310	57	
	Cooling			65	60	55	55	47	40	35	1290	59	
	Heating			64	61	56	54	46	40	36	1340	59	
015	Fan Only	Low	208	59	55	55	51	44	36	33	1068	56	
	Cooling			65	59	56	52	45	36	34	1066	58	
	Heating			68	60	57	52	44	36	33	1100	59	
	Fan Only	High		66	62	62	66	54	46	38	1380	67	
	Cooling			69	62	61	66	54	47	45	1365	67	
	Heating			71	64	62	65	56	2	44	1390	67	
018	Fan Only	Low	208	62	57	57	53	47	39	37	1145	58	
	Cooling			68	59	58	53	48	41	39	1140	60	
	Heating			69	60	58	53	48	46	40	1150	60	
	Fan Only	High		65	60	60	60	52	47	39	1310	63	
	Cooling			69	61	61	60	52	47	40	1304	63	
	Heating			70	62	61	60	53	49	41	1310	64	



Daikin Applied Training and Development

Now that you have made an investment in modern, efficient Daikin equipment, its care should be a high priority. For training information on all Daikin HVAC products, please visit us at www.DaikinApplied.com and click on Training, or call 540-248-9646 and ask for the Training Department.

Warranty

All Daikin equipment is sold pursuant to its standard terms and conditions of sale, including Limited Product Warranty. Consult your local Daikin Applied representative for warranty details. Refer to Form 933-430285Y. To find your local Daikin Applied representative, go to www.DaikinApplied.com.

Aftermarket Services

To find your local parts office, visit www.DaikinApplied.com or call 800-37PARTS (800-377-2787). To find your local service office, visit www.DaikinApplied.com or call 800-432-1342.

This document contains the most current product information as of this printing. For the most up-to-date product information, please go to www.DaikinApplied.com.

Products manufactured in an ISO Certified Facility.