


Magnitude® Magnetic Bearing Centrifugal Chiller
WMC • 86 - 400 Tons
Heat Recovery options available




Magnitude® Magnetic Bearing Centrifugal Chiller
WMT • 350 - 600 Tons



Magnitude® Magnetic Bearing Centrifugal Chiller
WME • 400 - 1600 Tons



Single Centrifugal Chiller
WSC • 300 - 1200 Tons
Heat Recovery options available



Dual Centrifugal Chiller
WDC • 1700 - 2500 Tons
Dual Series Counterflow Centrifugal Chiller
WCC • 1700 - 2500 Tons



Navigator® Water-Cooled Screw Chiller
WWV • 150 - 300 Tons

Templifier® Heat Recovery Water Heaters

TWV (Screw Compressor)	150 - 300 tons cooling	1680 - 3600 MBH heating
TMC (Centrifugal Compressor)	86 - 400 tons cooling	1600-6800 MBH heating
TSC (Centrifugal Compressor)	300 - 1200 tons cooling	3000 - 18000 MBH heating



Trailblazer® Air-to Water Scroll Heat Pump
EWYQ • 25 RT

Trailblazer® Air-Cooled Scroll Compressor Chiller
AGZ-F • 30 - 245 RT
High-Efficiency options available



Pathfinder® Air-Cooled Screw Compressor Chiller
AWV VFD • 100 - 565 RT

*100% Configurable with Variable Volume Ratio (VVR) Technology
Remote Evaporator, Pump Package, and Integrated Water-side Economizer options available*

