

## Application 2151: Fan Coil Unit Cooling and Heating with Secure Mode

---

### Table of Contents

<b>Overview .....</b>	<b>2</b>
Hardware Inputs .....	3
Hardware Outputs .....	3
Ordering Notes .....	3
Point Database .....	3
Secure Mode Operation .....	3
Sequence of Operation .....	3
Control Temperature Setpoints .....	3
Room Temperature Offset.....	4
Day and Night Modes .....	4
Night Mode Override Switch.....	4
Heating/Cooling Switchover .....	4
Control Loops .....	5
Cooling Operation.....	5
Heating Operation .....	5
Fan Operation.....	5
Calibration .....	6
Fail-Safe Operation .....	6
Application Notes.....	6
Wiring Diagram .....	7

## Overview

In Application 2151, the controller modulates separate valves in the fan coil unit for cooling and heating. The fan coil unit also has a fan to circulate room air. In order for the fan coil unit to work properly, the central plant must provide chilled and hot water (Figure 2151-1 and Figure 2151-2).





Figure 2151-1. Application 2151 Control Drawing.



1. See Sequence of Operation, Control Temperature Setpoints.
2. See Sequence of Operation, Heating/Cooling Switchover.

Figure 2151-2. Application 2151 Control Schedule.

## Hardware Inputs

### Analog

- Room temperature sensor
- Room temperature setpoint dial (optional)

### Digital

- Night mode override (optional)
- Wall switch (optional)

## Hardware Outputs

### Analog

- None

### Digital

- Cooling valve actuator
- Fan (switched 24 Vac, pilot duty)
- Heating valve actuator

## Ordering Notes

Unit Conditioner Controller – Electronic Output with Secure Mode 540-110C

See *APOGEE Automation Configuration and Sizing Guidelines* on InfoLink for product numbers.

Cooling valve actuator

Heating valve actuator

Terminal Equipment Controller room temperature sensor

## Point Database

Table 2151-1 presents the point database information for Application 2151.

## Secure Mode Operation

Secure Mode prevents unauthorized users from making changes to the TEC through the MMI port or room sensor. This mode can only be enabled/disabled through an Insight command. When Secure Mode is enabled, any attempts to make point changes in the TEC will be rejected and result in an error message indicating that the priority is too low.

## Sequence of Operation

The following paragraphs present the sequence of operation for Application 2151, “Fan Coil Unit Cooling and Heating with Secure Mode”.

## Control Temperature Setpoints

Depending on the controller’s current operational mode (day or night), CTL STPT (Point 92) holds the value of one of the following setpoints:

**Day Mode** – CTL STPT holds the value of DAY CLG STPT (Point 6) or DAY HTG STPT (Point 7). If the room temperature sensor has a setpoint dial and STPT DIAL (Point 14) = YES, CTL STPT holds the value of RM STPT DIAL (Point 13).

If the setpoint dial is used and RM STPT DIAL < RM STPT MIN (Point 11), CTL STPT holds the value of RM STPT MIN. If RM STPT DIAL > RM STPT MAX (Point 12), CTL STPT holds the value of RM STPT MAX.

**Night Mode** – CTL STPT holds the value of NGT CLG STPT (Point 8) or NGT HTG STPT (Point 9).

## Room Temperature Offset

Room Temperature Offset, RMTMP OFFSET (Point 3), is a user-adjustable offset that will compensate for deviations between the value of ROOM TEMP (Point 4) and the actual room temperature. This corrected value is displayed in CTL TEMP (Point 78).

CTL TEMP (Point 78) = ROOM TEMP (Point 4) + RMTMP OFFSET (Point 3).

## Day and Night Modes

The day/night status of the space is determined by the status of DAY.NGT (Point 29). The control of this point differs depending on whether the controller is monitoring the status of a wall switch or if the controller is connected to a field panel.

When a wall switch is physically connected to the termination strip on the controller at DI 2 (Figure 2151-1 and Figure 2151-3), and WALL SWITCH (Point 18) = YES, the controller monitors the status of DI 2. When the status of DI 2 (Point 24) is ON (the switch is closed), DAY.NGT will be set to DAY indicating that the controller is in day mode. When the status of DI 2 is OFF (the switch is open), DAY.NGT will be set to NIGHT indicating that the controller is in night mode.

When WALL SWITCH = NO, the controller does not monitor the status of the wall switch, even if one is connected to it. In this case, the controller is operating stand-alone and stays in day mode all the time. If the controller is operating with centralized control, connected to a field panel, the field panel can send an operator or PPCL command to override the status of DAY.NGT. See *APOGEE Powers Process Control Language (PPCL) User's Manual* (125-1896) and [APOGEE Field Panel User's Manual](#) (125-3000) for more information.

## Night Mode Override Switch

If an override switch is present on the room temperature sensor, and a value (in hours) other than zero has been entered into OVRD TIME (Point 20), pressing the override switch will reset the controller to day mode for the amount of time set in OVRD TIME. The status of NGT OVRD (Point 21) changes to DAY. After the override time elapses, the controller returns to night mode and the status of NGT OVRD changes back to NIGHT.

The override switch on the room sensor will only affect the controller when in night mode.

## Heating/Cooling Switchover

The heating/cooling switchover determines whether the controller is in heating or cooling mode by monitoring the room temperature and the demand for heating and cooling (as determined by the temperature control loops).

If the following conditions are met for the length of time set in SWITCH TIME (Point 86), the controller switches from heating to cooling mode by setting HEAT.COOL (Point 5) to COOL:

- HTG LOOPOUT (Point 80) < SWITCH LIMIT (Point 85).

- CTL TEMP (Point 78) > CTL STPT (Point 92) by at least the value set in SWITCH DBAND (Point 90).
- CTL TEMP > the appropriate cooling setpoint minus SWITCH DBAND.

If the following conditions are met for the length of time set in SWITCH TIME, the controller switches from cooling to heating mode by setting HEAT.COOL to HEAT:

- CLG LOOPOUT (Point 79) < SWITCH LIMIT.
- CTL TEMP < CTL STPT by at least the value set in SWITCH DBAND.
- CTL TEMP < the appropriate heating setpoint plus SWITCH DBAND.

## Control Loops

The fan coil unit is controlled by two Proportional, Integral, and Derivative (PID) temperature loops.

**Temperature Loops** – The two temperature loops are a cooling loop and a heating loop. The active temperature loop maintains room temperature at the value in CTL STPT (Point 92). See *Sequence of Operation, Control Temperature Setpoints*.

## Cooling Operation

In cooling mode, the controller uses CTL STPT (Point 92) and CTL TEMP (Point 78) as inputs for the cooling loop. The output of the cooling loop is CLG LOOPOUT (Point 79), which modulates the cooling valve, VLV 1 COMD (Point 48). HTG LOOPOUT (Point 80) is set to 0%.

When in heating mode, the cooling valve is closed.

## Heating Operation

In heating mode, the controller uses CTL STPT (Point 92) and CTL TEMP (Point 78) as inputs for the heating loop. The output of the heating loop is HTG LOOPOUT (Point 80), which modulates the hot water valve, VLV 2 COMD (Point 52), in order to warm up the space. CLG LOOPOUT (Point 79) is set to 0%.

When in cooling mode, the heating valve is closed.

## Fan Operation

**Day Mode** – The fan may be set to stay ON at all times or to cycle to save energy. If CYCLE FAN (Point 60) = NO, the fan will be ON during the day. If CYCLE FAN = YES, the fan will cycle according to the following conditions:

1. If either valve points, VLV 1 POS (Point 49) or VLV 2 POS (Point 53), is open more than the value of STAGE FAN (Point 84) the fan will turn ON.
2. If both valves are closed below the value of SWITCH LIMIT (Point 85), the fan will turn OFF.
3. If neither of the above two conditions is met, the condition of the fan remains unchanged.

**Night Mode** – The fan cycles using the same three conditions described in the day mode section above, regardless of the setting of CYCLE FAN. If NGT OVRD (Point 21) = DAY (indicating that the night mode override button has been pressed), the fan is controlled as in day mode.

## Calibration

The controller will regularly calibrate the valves based on the value of CAL TIMER (Point 96). A value of 12 indicates that the controller will calibrate the valves once every 12 hours.

The calibration consists of driving the valves closed, and then resetting the values of VLV 1 POS (Point 49) and VLV 2 POS (Point 53) to 0. The actuators are then released to normal control.

## Fail-Safe Operation

If the room temperature sensor fails, the controller operates using the last known temperature value.

## Application Notes

1. If temperature variations in the room are excessive or there is trouble maintaining the setpoint, the cooling loop, the heating loop, or both need to be tuned. See *iKnow Troubleshooting Tool* for more information.
2. The Unit Conditioner Controller – Electronic Output, as shipped from the factory, keeps all associated equipment OFF. See the *Equipment Controllers* section in the *APOGEE Automation Start-up Procedures* on InfoLink for information on how to release the controller and its equipment to application control.
3. Spare DOs can be used as auxiliary points that are controlled by the field panel after being defined in the field panel's database. If a cooling valve is not being controlled by the application, DO 1 and DO 2 may be used as auxiliary motor points. If a heating valve is not being controlled by the application, DO 3 and DO 4 may be used as auxiliary motor points. If using a pair of spare DOs to control a motor, you must make sure that the motor setup, motor timing, and motor rotation angle are enabled correctly before you unbundle VLV 1 COMD (Point 48) for DO 1 and DO 2 and VLV 2 COMD (Point 52) for DO 3 and DO 4. See *APOGEE Automation Start-up Procedures* on InfoLink for more information.

## Wiring Diagram

The point wiring for Application 2151 is shown in Figure 2151-3.



### CAUTION:

The controller's DOs control 24 Vac loads only. The maximum rating is 12 VA for each DO. Use an interposing 220V 4-relay module for any of the following:

- VA requirements higher than the maximum
- 110 or 220 Vac requirements
- DC power requirements
- Separate transformers used to power the load




Figure 2151-3. Application 2151 Wiring Diagram.

Table 2151-1. Point Database for Application 2151.

Point Number	Descriptor	Factory Default (SI Units)	Eng. Units (SI Units)	Slope (SI Units)	Intercept (SI Units)	On Text	Off Text
01	CTLR ADDRESS	99	–	1	0	–	–
02	APPLICATION	2188	–	1	0	–	–
03	RMTMP OFFSET	0.0 (0.0)	DEG F (DEG C)	0.25 (0.14)	-31.75 (-17.78)	–	–
{04}	ROOM TEMP	74.0 (23.449)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
{05}	HEAT.COOL	COOL	–	–	–	HEAT	COOL
06	DAY CLG STPT	74.0 (23.449)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
07	DAY HTG STPT	70.0 (21.209)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
08	NGT CLG STPT	82.0 (27.929)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
09	NGT HTG STPT	65.0 (18.409)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
11	RM STPT MIN	55.0 (12.809)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
12	RM STPT MAX	90.0 (32.409)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
{13}	RM STPT DIAL	74.0 (23.449)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
14	STPT DIAL	NO	–	–	–	YES	NO
{15}	AUX TEMP	74.0 (23.496)	DEG F (DEG C)	0.5 (0.28)	37.5 (3.056)	–	–
18	WALL SWITCH	NO	–	–	–	YES	NO
{19}	DI OVRD SW	OFF	–	–	–	ON	OFF
20	OVRD TIME	0	HRS	1	0	–	–
{21}	NGT OVRD	NIGHT	–	–	–	NIGHT	DAY
{24}	DI 2	OFF	–	–	–	ON	OFF
{25}	DI 3	OFF	–	–	–	ON	OFF
{29}	DAY.NGT	DAY	–	–	–	NIGHT	DAY
{41}	DO 1	OFF	–	–	–	ON	OFF

1. Points not listed are not used in this application.
2. A single value in a column means that the value is the same in English units and in SI units.
3. Point numbers that appear in brackets { } may be unbundled at the field panel.

Continued on next page...



Table 2151-1. Point Database for Application 2151.

Point Number	Descriptor	Factory Default (SI Units)	Eng. Units (SI Units)	Slope (SI Units)	Intercept (SI Units)	On Text	Off Text
{42}	DO 2	OFF	–	–	–	ON	OFF
{43}	DO 3	OFF	–	–	–	ON	OFF
{44}	DO 4	OFF	–	–	–	ON	OFF
{45}	DO 5	OFF	–	–	–	ON	OFF
{46}	FAN	OFF	–	–	–	ON	OFF
{48}	VLV 1 COMD	0.0	PCT	0.4	0.0	–	–
{49}	VLV 1 POS	0.0	PCT	0.4	0.0	–	–
51	MTR 1 TIMING	130	SEC	1	0	–	–
{52}	VLV 2 COMD	0.0	PCT	0.4	0.0	–	–
{53}	VLV 2 POS	0.0	PCT	0.4	0.0	–	–
55	MTR 2 TIMING	130	SEC	1	0	–	–
56	MTR1 ROT ANG	90	–	1	0	–	–
57	MTR2 ROT ANG	90	–	1	0	–	–
58	MTR SETUP	0	–	1	0	–	–
59	DO DIR. REV	0	–	1	0	–	–
60	CYCLE FAN	NO	–	–	–	YES	NO
63	CLG P GAIN	20.0 (36.0)	–	0.25 (0.45)	0.0	–	–
64	CLG I GAIN	0.01 (0.018)	–	0.001 (0.0018)	0.0	–	–
65	CLG D GAIN	0 (0.0)	–	2 (3.6)	0	–	–
66	CLG BIAS	0.0	PCT	0.4	0.0	–	–
67	HTG P GAIN	10.0 (18.0)	–	0.25 (0.45)	0.0	–	–
68	HTG I GAIN	0.01 (0.018)	–	0.001 (0.0018)	0.0	–	–
69	HTG D GAIN	0 (0.0)	–	2 (3.6)	0	–	–
70	HTG BIAS	0.0	PCT	0.4	0.0	–	–
{78}	CTL TEMP	74.0 (23.449)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
{79}	CLG LOOPOUT	0.0	PCT	0.4	0.0	–	–

1. Points not listed are not used in this application.
2. A single value in a column means that the value is the same in English units and in SI units.
3. Point numbers that appear in brackets { } may be unbundled at the field panel.

Continued on next page...

**Table 2151-1. Point Database for Application 2151.**

Point Number	Descriptor	Factory Default (SI Units)	Eng. Units (SI Units)	Slope (SI Units)	Intercept (SI Units)	On Text	Off Text
{80}	HTG LOOPOUT	0.0	PCT	0.4	0.0	–	–
84	STAGE FAN	10.0	PCT	0.4	0.0	–	–
85	SWITCH LIMIT	5.2	PCT	0.4	0.0	–	–
86	SWITCH TIME	10	MIN	1	0	–	–
90	SWITCH DBAND	1.0 (0.56)	DEG F (DEG C)	0.25 (0.14)	0.0	–	–
{92}	CTL STPT	74.0 (23.449)	DEG F (DEG C)	0.25 (0.14)	48.0 (8.889)	–	–
96	CAL TIMER	12	HRS	1	0	–	–
98	LOOP TIME	5	SEC	1	0	–	–
{99}	ERROR STATUS	0	–	1	0	–	–

1. Points not listed are not used in this application.
2. A single value in a column means that the value is the same in English units and in SI units.
3. Point numbers that appear in brackets { } may be unbundled at the field panel.