

Group: Unit Vent


Type: Capacity Data

Date: October 2013

# Daikin Classroom Unit Ventilator -

## Cooling Capacity Data

Ceiling Models AHF, AHV, AHR, AHB (F Vintage)



### Contents

<b>Chilled Water Coil Selection Procedure .....</b>	<b>2-3</b>
<b>750 CFM - Standard Capacity</b>	
<b>2, 3, 4, 5-Row Chilled Water Cooling .....</b>	<b>4-11</b>
(61° EWB).....	4
(63° EWB).....	5
(65° EWB).....	6
(67° EWB).....	7
(69° EWB).....	8
(71° EWB).....	9
(73° EWB).....	10
(75° EWB).....	11
<b>1000 CFM - Standard Capacity</b>	
<b>2, 3, 4, 5-Row Chilled Water Cooling .....</b>	<b>12-19</b>
(61° EWB).....	12
(63° EWB).....	13
(65° EWB).....	14
(67° EWB).....	15
(69° EWB).....	16
(71° EWB).....	17
(73° EWB).....	18
(75° EWB).....	19
<b>1250 CFM - Standard Capacity</b>	
<b>2, 3, 4, 5-Row Chilled Water Cooling .....</b>	<b>20-27</b>
(61° EWB).....	20
(63° EWB).....	21
(65° EWB).....	22
(67° EWB).....	23
(69° EWB).....	24
(71° EWB).....	25
(73° EWB).....	26
(75° EWB).....	27
<b>1500 CFM - Standard Capacity</b>	
<b>2, 3, 4, 5-Row Chilled Water Cooling .....</b>	<b>28-35</b>
(61° EWB).....	28
(63° EWB).....	29
(65° EWB).....	30
(67° EWB).....	31
(69° EWB).....	32
(71° EWB).....	33
(73° EWB).....	34
(75° EWB).....	35
<b>2000 CFM - Standard Capacity</b>	
<b>2, 3, 4, 5-Row Chilled Water Cooling .....</b>	<b>36-43</b>
(61° EWB).....	36
(63° EWB).....	37
(65° EWB).....	38
(67° EWB).....	39
(69° EWB).....	40
(71° EWB).....	41
(73° EWB).....	42
(75° EWB).....	43

# Chilled Water Coil Selection

## STEP 1 Determine Design Conditions

Design indoor and outdoor air temperatures should be determined in accordance with established engineering practices as outlined in the ASHRAE Guide or other authoritative source. Indoor temperatures of 80°F dry bulb and 67°F wet bulb for summer, are usually acceptable for design or peak load conditions even though the expected operating conditions of the system may be somewhat different.

### Formula

#### Mixture Entering Dry Bulb °F (EDB) & Entering Wet Bulb °F (EWB) Temperature —

$$EDB = \text{Room DB} \times \frac{\% RA}{100} + \text{Outdoor DB} \times \frac{\% OA}{100}$$

$$EDB = 76(.8) + 96(.2) = 80^{\circ}\text{F}$$

EWB=Room Enthalpy x

$$\frac{\% RA}{100} + \text{Outdoor Enthalpy} \times \frac{\% OA}{100}$$

Refer to Table 3 for Enthalpy (H).

$$EWB = 30.06(.8) + 37.66(.2) = 31.58H = 67^{\circ}\text{F}$$

## STEP 2 Determine Desired Cooling Load

Unit cooling capacity should be selected to equal or slightly exceed the sum of computed room sensible and latent heat gains (Room Total Capacity). When operating on the mechanical cooling cycle, the control system introduces a constant amount of outdoor air for ventilation. The latent and sensible heat gain from this outdoor ventilation air must be added to the room total cooling load before choosing the proper capacity unit.

## STEP 3

Use tables to properly size the unit based on the calculated cooling capacities, entering air conditions, water flow rate, and water temperature.

For conditions of coil performance beyond the scope of the these selection procedures, AAF®-HermanNelson® offers computer selection programs for chilled water, hot water and steam coils. Consult your local AAF-HermanNelson representative for details.

## STEP 4 Calculate Leaving Air Conditions

Leaving air temperatures dry bulb °F (LDB) and wet bulb °F (LWB) may be calculated as follows:

$$LDB = EDB - \frac{SC (\text{BTUH})}{CFM \times 1.085} =$$

$$LWB = EWB - \frac{TC (\text{BTUH})}{CFM \times 4.5} =$$

NOTE: See table 3, page 3 to get LWB (°F)

## STEP 5 Freeze Protection

CONSTANT PUMP OPERATION IS REQUIRED WHENEVER THE OUTDOOR AIR TEMPERATURE IS BELOW 35°F. This will assist in providing protection against freeze up of the system water piping and coils. To avoid the possibility of water coil freeze up on valve controlled units, the valve must be selected properly to ensure water flow. One of the steps below should be followed:

### CHILLED WATER

1. Draining of the chilled water system during cold weather or;
2. Opening of the chilled water coil valves and operation of the chilled water circulating pump any time the outside air temperature is below 35°F.
3. Usage of an antifreeze in the system.

## STEP 6 Units with Antifreeze

If ethylene or propylene glycol is used, it is necessary to consider its effect upon heating and cooling capacities and water pressure drop through the coil and piping system.

1. Divide cooling loads determined from STEP 2 by the applicable glycol correction factor to arrive at the calculated unit capacity required to take care of the capacity reduction caused by the glycol solution.

**Table 1. Capacity Correction Factors For Ethylene and Propylene Glycol**

	%	20	30	40
Capacity	Ethylene	.92	.84	.75
	Propylene	.86	.73	.62

2. Determine the GPM required by entering the appropriate chilled water cooling capacity table or hot water capacity chart using the calculated unit capacity.

3. Determine the water pressure drop by multiplying the water pressure drop for the GPM determined above by the pressure drop factor for the % glycol used.

**Table 2. Pressure Drop Correction Factors for Ethylene and Propylene Glycol**

	%	20	30	40
Pressure Drop	Ethylene	1.15	1.22	1.34
	Propylene	1.35	1.27	1.24

**Table 3. Enthalpy (H) - at Saturation, but Per Pound of Dry Air**

Wet Bulb Temp. °F.	TENTHS OF A DEGREE									
	.0	.1	.2	.3	.4	.5	.6	.7	.8	.9
50	20.30	20.36	20.41	20.47	20.52	20.58	20.64	20.69	20.75	20.80
51	20.86	20.92	20.97	21.03	21.09	21.15	21.20	21.26	21.32	21.38
52	21.44	21.50	21.56	21.62	21.67	21.73	21.79	21.85	21.91	21.97
53	22.02	22.08	22.14	22.20	22.26	22.32	22.38	22.44	22.50	22.56
54	22.62	22.68	22.74	22.80	22.86	22.92	22.98	23.04	23.10	23.16
55	23.22	23.28	23.34	23.41	23.47	23.53	23.59	23.65	23.72	23.78
56	23.84	23.90	23.97	24.03	24.10	24.16	24.22	24.29	24.35	24.42
57	24.48	24.54	24.61	24.67	24.74	24.80	24.86	24.93	24.99	25.06
58	25.12	25.19	25.25	25.32	25.38	25.45	25.52	25.58	26.65	26.71
59	25.78	25.85	25.92	25.98	26.05	26.12	26.19	26.26	26.32	26.39
60	26.46	26.53	26.60	26.67	26.74	26.81	26.87	26.94	27.01	27.08
61	27.15	27.22	27.29	27.36	27.43	27.50	27.57	27.64	27.71	27.78
62	27.85	27.92	27.99	28.07	28.14	28.21	28.28	28.35	28.43	28.50
63	28.57	28.64	28.72	28.79	28.87	28.94	29.01	29.09	29.16	29.24
64	29.31	29.39	29.46	29.54	29.61	29.69	29.76	29.84	29.91	29.99
65	30.06	30.14	30.21	30.29	30.37	30.45	30.52	30.60	30.68	30.78
66	30.83	30.91	30.99	31.07	31.15	31.23	31.30	31.38	31.46	31.54
67	31.62	31.70	31.78	31.86	31.94	32.02	32.10	32.18	32.26	32.34
68	32.42	32.50	32.59	32.67	32.75	32.84	32.92	33.00	33.08	33.17
69	33.25	33.33	33.42	33.50	33.59	33.67	33.75	33.84	33.92	34.01
70	34.09	34.18	34.26	34.35	34.43	34.52	34.61	34.69	34.78	34.86
71	34.95	35.04	35.13	35.21	35.30	35.39	35.48	35.57	35.65	35.74
72	35.83	35.92	36.01	36.10	36.19	36.29	36.38	36.47	36.56	36.65
73	36.74	36.83	36.92	37.02	37.11	37.20	37.29	37.38	37.48	37.57
74	37.66	37.76	37.85	37.95	38.04	38.14	38.23	38.33	38.42	38.52
75	38.61	38.71	38.80	38.90	38.99	39.09	39.19	39.28	39.38	39.47
76	39.57	39.67	39.77	39.87	39.97	40.07	40.17	40.27	40.37	40.47
77	40.57	40.67	40.77	40.87	40.97	41.08	41.18	41.28	41.38	41.48
78	41.58	41.68	41.79	41.89	42.00	42.10	42.20	42.31	42.41	42.52
79	42.62	42.73	42.83	42.94	43.05	43.16	43.26	43.37	43.48	43.58
80	43.69	43.80	43.91	44.02	44.13	44.24	44.34	44.45	44.56	44.67
81	44.78	44.89	45.00	45.12	45.23	45.34	45.45	45.56	45.68	45.79
82	45.90	46.01	46.13	46.24	46.36	46.47	46.58	46.70	46.81	46.93
83	47.04	47.16	47.28	47.39	47.51	47.63	47.75	47.87	47.98	48.10
84	48.22	48.34	48.46	48.58	48.70	48.83	48.95	49.07	49.19	49.31
85	49.43	49.55	49.68	49.80	49.92	50.05	50.17	50.29	50.41	50.54

Interpolated to tenths of degrees from 1963 edition ASHRAE Guide & Data Book. Published by the American Society of Heating, Refrigerating and Air Conditioning Engineers, Inc.

#### Capacity Tables Legend

EDB = Entering Air Dry Bulb  
SC = Sensible Cooling Capacity

EWB = Entering Air Wet Bulb  
TC = Total Cooling Capacity

WPD = Water Pressure Drop (Ft. H<sub>2</sub>O)  
EWT = Entering Water Temperature

TR = Water Temperature Rise  
GPM = Gallons Per Minute

# 750 CFM - Standard Capacity (61° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	15.3	13.5	11.7	14.5	12.8	10.5	13.7	12.1	9.9	13.0	11.0	9.2
	SC	13.5	12.4	11.2	13.1	12.0	10.4	12.7	11.6	9.7	12.2	10.9	9.1
	gpm	3.9	2.7	2.0	3.7	2.6	1.8	3.5	2.5	1.7	3.3	2.2	1.5
	wpd	4.5	2.2	1.2	4.2	2.1	1.0	3.7	1.9	0.9	3.3	1.5	0.7
76	TC	16.1	14.5	12.5	15.4	13.9	11.9	14.7	13.0	11.3	14.1	12.4	10.7
	SC	14.9	13.8	12.4	14.5	13.4	11.8	14.1	12.8	11.2	13.6	12.2	10.5
	gpm	4.1	2.9	2.1	3.9	2.9	2.0	3.7	2.6	1.9	3.5	2.5	1.8
	wpd	5.1	2.6	1.3	4.5	2.5	1.2	4.2	2.1	1.1	3.8	1.9	1.0
78	TC	17.0	15.4	13.9	16.4	14.9	13.3	15.7	14.3	12.7	15.1	13.7	12.1
	SC	16.3	15.2	13.7	15.9	14.7	13.1	15.4	14.1	12.5	14.9	13.5	12.0
	gpm	4.3	3.2	2.3	4.2	3.0	2.2	3.9	2.9	2.2	3.9	2.8	2.1
	wpd	5.7	3.0	1.6	5.3	2.8	1.5	4.7	2.6	1.4	4.5	2.3	1.3
80	TC	18.0	16.7	15.2	17.4	16.1	14.7	16.9	15.6	14.1	16.3	15.0	13.5
	SC	17.7	16.5	15.0	17.2	15.9	14.5	16.7	15.4	13.9	16.1	14.8	13.3
	gpm	4.5	3.4	2.5	4.4	3.2	2.5	4.2	3.2	2.4	4.2	3.0	2.2
	wpd	6.3	3.5	2.0	5.9	3.2	1.9	5.5	3.0	1.7	5.3	2.8	1.5
82	TC	19.2	17.9	16.5	18.6	17.4	16.0	18.1	16.8	15.4	17.5	16.3	14.8
	SC	18.9	17.7	16.3	18.4	17.1	15.7	17.8	16.6	15.2	17.3	16.0	14.6
	gpm	4.9	3.6	2.8	4.7	3.5	2.7	4.5	3.4	2.6	4.4	3.3	2.5
	wpd	7.2	4.0	2.3	6.7	3.8	2.2	6.3	3.5	2.1	5.9	3.3	1.9
84	TC	20.4	19.2	17.8	19.8	18.6	17.2	19.2	18.0	16.7	18.7	17.5	16.1
	SC	20.1	18.9	17.6	19.5	18.4	17.0	19.0	17.8	16.5	18.4	17.3	15.9
	gpm	5.2	3.9	3.0	5.0	3.8	2.9	4.9	3.6	2.9	4.7	3.5	2.7
	wpd	8.1	4.5	2.8	7.6	4.3	2.6	7.2	4.0	2.5	6.7	3.8	2.2
86	TC	21.5	20.4	19.1	20.9	19.8	18.5	20.4	19.3	18.0	19.8	18.7	17.4
	SC	21.2	20.1	18.8	20.7	19.6	18.3	20.1	19.0	17.7	19.6	18.5	17.2
	gpm	5.5	4.2	3.2	5.3	4.0	3.2	5.2	3.9	3.0	5.0	3.8	2.9
	wpd	9.1	5.3	3.2	8.6	4.9	3.0	8.1	4.7	2.8	7.6	4.3	2.6
88	TC	22.6	21.6	20.3	22.1	21.1	19.8	21.5	20.5	19.2	21.0	19.9	18.7
	SC	22.3	21.3	20.1	21.8	20.8	19.5	21.2	20.2	19.0	20.7	19.7	18.4
	gpm	5.7	4.4	3.5	5.6	4.2	3.3	5.5	4.2	3.2	5.3	4.0	3.2
	wpd	9.9	5.9	3.7	9.6	5.5	3.3	9.1	5.3	3.2	8.6	4.9	3.0
90	TC	23.8	22.8	21.6	23.2	22.3	21.0	22.7	21.7	20.5	22.1	21.2	19.9
	SC	23.5	22.5	21.3	22.9	22.0	20.7	22.4	21.4	20.2	21.8	20.9	19.7
	gpm	6.0	4.6	3.6	5.9	4.5	3.5	5.7	4.4	3.5	5.6	4.3	3.4
	wpd	11.0	6.5	4.0	10.5	6.3	3.8	9.9	5.9	3.7	9.6	5.7	3.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	22.7	21.0	19.3	21.5	19.8	18.3	20.2	18.7	17.3	19.0	17.6	16.4
	SC	17.4	16.6	15.8	16.8	16.0	15.3	16.2	15.5	14.9	15.7	15.1	14.4
	gpm	5.7	4.2	3.3	5.4	4.0	3.1	5.1	3.8	2.9	4.8	3.6	2.7
	wpd	6.0	3.3	2.0	5.3	2.9	1.7	4.7	2.6	1.5	4.2	2.4	1.4
76	TC	23.2	21.7	20.3	22.0	20.6	19.4	20.8	19.6	18.5	19.8	18.6	17.7
	SC	18.8	18.1	17.5	18.3	17.6	17.0	17.8	17.2	16.6	17.3	16.7	16.2
	gpm	5.9	4.4	3.4	5.6	4.1	3.3	5.2	4.0	3.1	5.0	3.8	3.0
	wpd	6.3	3.5	2.2	5.6	3.1	2.0	5.0	2.9	1.8	4.6	2.6	1.6
78	TC	23.7	22.5	21.4	22.6	21.5	20.5	21.6	20.6	19.7	20.6	19.8	17.4
	SC	20.3	19.7	19.2	19.8	19.3	18.7	19.3	18.8	18.3	18.9	18.4	17.2
	gpm	6.0	4.5	3.6	5.7	4.4	3.4	5.5	4.1	3.4	5.2	4.0	3.0
	wpd	6.6	3.8	2.4	6.0	3.5	2.2	5.5	3.1	2.1	5.0	2.9	1.6
80	TC	24.3	23.4	22.5	23.3	22.5	21.7	22.4	21.7	19.6	21.6	20.1	18.9
	SC	21.9	21.4	20.9	21.4	20.9	20.5	21.0	20.5	19.4	20.5	19.9	18.7
	gpm	6.2	4.8	3.8	5.9	4.5	3.7	5.6	4.4	3.3	5.5	4.1	3.2
	wpd	7.0	4.2	2.7	6.3	3.8	2.5	5.8	3.5	2.0	5.5	3.0	1.9
82	TC	25.1	24.4	23.7	24.2	23.7	21.9	23.5	22.2	21.2	22.4	21.6	20.5
	SC	23.4	23.0	22.6	23.0	22.6	21.6	22.6	22.0	20.9	22.1	21.3	20.2
	gpm	6.3	4.9	4.0	6.1	4.8	3.7	6.0	4.5	3.6	5.6	4.4	3.4
	wpd	7.3	4.4	2.9	6.8	4.2	2.5	6.4	3.8	2.4	5.8	3.5	2.2
84	TC	26.1	25.0	24.0	25.1	24.3	23.3	24.4	23.7	22.7	23.8	23.0	22.0
	SC	25.1	24.7	23.7	24.8	24.0	23.0	24.1	23.4	22.4	25.0	24.0	22.7
	gpm	6.6	5.1	4.1	6.3	4.9	3.9	6.2	4.8	3.8	5.9	4.5	3.7
	wpd	7.9	4.7	3.0	7.3	4.4	2.8	7.0	4.2	2.7	6.6	4.0	2.5
86	TC	27.1	26.4	25.4	26.4	25.7	24.8	25.8	25.1	24.1	25.1	24.4	23.4
	SC	26.7	26.0	25.1	26.1	25.4	24.5	25.4	24.2	23.8	24.8	24.1	23.2
	gpm	6.9	5.3	4.3	6.7	5.2	4.1	6.5	5.1	4.1	6.7	5.2	4.2
	wpd	8.6	5.2	3.4	8.1	5.0	3.1	7.7	4.7	3.0	7.3	4.4	2.9
88	TC	28.4	27.7	26.9	27.7	27.1	26.2	27.1	26.4	25.5	26.5	25.8	24.9
	SC	28.0	27.4	26.5	27.4	26.7	25.9	26.7	26.1	25.2	26.1	25.5	24.9
	gpm	7.2	5.6	4.5	7.0	5.5	4.5	6.9	5.4	4.3	6.7	5.2	4.2
	wpd	9.5	5.8	3.8	9.0	5.5	3.6	8.6	5.3	3.4	8.3	5.0	3.3
90	TC	29.7	29.1	28.3	29.1	28.4	27.6	28.4	27.8	27.0	27.8	27.1	26.3
	SC	29.3	28.7	27.9	28.7	28.1	27.3	28.0	27.4	26.6	27.4	26.8	26.0
	gpm	7.5	5.9	4.8	7.4	5.7	4.7	7.2	5.6	4.5	7.0	5.5	4.5
	wpd	10.3	6.3	4.2	9.9	6.0	4.0	9.5	5.8	3.8	9.0	5.5	3.6

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	18.3	16.2	14.3	17.2	15.3	13.6	16.2	14.4	11.1	15.2	13.7	10.4
	SC	15.0	14.0	13.0	14.5	13.6	12.6	14.0	13.1	11.0	13.6	12.7	10.2
	gpm	4.6	3.2	2.4	4.4	3.1	2.3	4.1	2.9	1.9	3.8	2.8	1.7

# 750 CFM - Standard Capacity (63° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	17.3	14.8	12.3	16.3	13.8	11.5	15.2	12.8	10.7	14.2	12.0	10.0
	SC	12.9	11.8	10.7	12.5	11.4	10.2	12.0	10.9	9.8	11.6	10.5	9.3
	gpm	4.4	3.0	2.1	4.1	2.8	1.9	3.9	2.6	1.8	3.5	2.4	1.7
	wpd	5.9	2.8	1.3	5.1	2.3	1.1	4.5	2.1	1.0	3.8	1.7	0.9
76	TC	17.8	15.5	13.4	16.8	14.6	12.7	15.9	13.8	12.0	14.9	13.0	11.3
	SC	14.3	13.2	12.2	13.9	12.9	11.7	13.4	12.4	11.3	13.0	12.0	10.8
	gpm	4.5	3.2	2.2	4.2	2.9	2.2	4.0	2.8	2.0	3.8	2.6	1.9
	wpd	6.1	3.0	1.5	5.5	2.6	1.4	4.9	2.3	1.2	4.3	2.1	1.1
78	TC	18.4	16.3	14.6	17.4	15.6	13.9	16.5	14.8	13.3	15.7	14.1	12.1
	SC	15.6	14.7	13.6	15.2	14.3	13.2	14.8	13.9	12.7	14.4	13.4	12.0
	gpm	4.6	3.3	2.5	4.4	3.2	2.3	4.2	3.0	2.2	3.9	2.9	2.1
	wpd	6.5	3.3	1.9	5.9	3.0	1.6	5.3	2.8	1.5	4.7	2.5	1.3
80	TC	19.0	17.3	15.7	18.1	16.6	14.7	17.3	15.9	14.1	16.6	15.0	13.5
	SC	17.0	16.1	15.1	16.6	15.7	14.5	16.3	15.3	13.9	15.9	14.8	13.3
	gpm	4.8	3.5	2.6	4.6	3.4	2.5	4.4	3.2	2.4	4.2	3.0	2.3
	wpd	7.0	3.7	2.1	6.5	3.5	1.9	5.9	3.2	1.7	5.5	2.8	1.6
82	TC	19.7	18.3	16.6	18.9	17.6	16.0	18.3	16.8	15.4	17.7	16.3	14.9
	SC	18.4	17.5	16.3	18.0	17.1	15.8	17.6	16.6	15.2	17.2	16.1	14.7
	gpm	5.0	3.7	2.8	4.8	3.5	2.7	4.6	3.4	2.6	4.5	3.3	2.5
	wpd	7.6	4.2	2.3	7.0	3.8	2.2	6.5	3.5	2.1	6.1	3.3	2.0
84	TC	20.5	19.2	17.9	19.9	18.6	17.3	19.3	18.1	16.7	18.7	17.5	16.1
	SC	19.8	19.0	17.6	19.4	18.4	17.1	19.0	17.9	16.5	18.5	17.3	15.9
	gpm	5.2	3.9	3.0	5.0	3.8	2.9	4.9	3.6	2.9	4.7	3.5	2.7
	wpd	8.1	4.5	2.8	7.6	4.3	2.6	7.2	4.0	2.5	6.7	3.8	2.2
86	TC	21.5	20.4	19.1	21.0	19.9	18.6	20.4	19.3	18.0	19.9	18.8	17.4
	SC	21.3	20.2	18.9	20.7	19.6	18.3	20.2	19.1	17.8	19.6	18.5	17.2
	gpm	5.5	4.2	3.2	5.3	4.0	3.2	5.2	3.9	3.0	5.0	3.8	2.9
	wpd	9.1	5.3	3.2	8.6	4.9	3.0	8.1	4.7	2.8	7.6	4.3	2.6
88	TC	22.7	21.7	20.4	22.1	21.1	19.8	21.6	20.5	19.3	21.0	20.0	18.7
	SC	22.4	21.4	20.1	21.8	20.8	19.6	21.3	20.3	19.0	20.7	19.7	18.5
	gpm	5.8	4.4	3.5	5.6	4.2	3.3	5.5	4.2	3.2	5.3	4.1	3.2
	wpd	10.2	5.9	3.7	9.6	5.5	3.3	9.1	5.3	3.2	8.6	5.1	3.0
90	TC	23.8	22.9	21.6	23.3	22.3	21.0	22.7	21.8	20.5	22.1	21.2	20.0
	SC	23.5	22.6	21.3	23.0	22.0	20.8	22.4	21.5	20.2	21.9	20.9	19.7
	gpm	6.0	4.6	3.6	5.9	4.5	3.5	5.8	4.4	3.5	5.6	4.3	3.4
	wpd	11.0	6.5	4.0	10.5	6.3	3.8	10.2	5.9	3.7	9.6	5.7	3.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.0	23.8	21.7	24.6	22.5	20.3	23.2	21.1	19.0	21.8	19.8	17.8
	SC	17.2	16.2	15.3	16.6	15.6	14.7	15.9	15.0	14.1	15.3	14.4	13.6
	gpm	6.6	4.9	3.7	6.3	4.5	3.4	5.9	4.2	3.2	5.6	4.0	3.0
	wpd	7.9	4.3	2.5	7.1	3.8	2.2	6.3	3.3	1.9	5.6	2.9	1.6
76	TC	26.2	24.3	22.3	24.9	23.0	21.1	23.5	21.7	19.9	22.2	20.4	18.7
	SC	18.5	17.7	16.8	17.9	17.1	16.3	17.3	16.5	15.7	16.8	16.0	15.2
	gpm	6.7	4.9	3.8	6.3	4.6	3.6	6.0	4.4	3.4	5.6	4.2	3.1
	wpd	8.1	4.4	2.6	7.1	3.9	2.4	6.4	3.5	2.1	5.8	3.1	1.8
78	TC	26.5	24.8	23.0	25.2	23.5	21.9	24.0	22.3	20.8	22.7	21.2	19.8
	SC	19.9	19.2	18.4	19.4	18.6	17.9	18.8	18.1	17.4	18.2	17.5	16.9
	gpm	6.7	5.0	3.9	6.4	4.8	3.7	6.0	4.5	3.5	5.7	4.3	3.4
	wpd	8.3	4.6	2.8	7.5	4.2	2.5	6.6	3.8	2.3	6.0	3.4	2.1
80	TC	26.9	25.3	23.8	25.7	24.2	22.8	24.4	23.0	21.8	23.2	22.0	20.9
	SC	21.4	20.6	20.0	20.8	20.1	19.5	20.2	19.6	19.0	19.7	19.1	18.6
	gpm	6.8	5.2	4.0	6.5	4.9	3.8	6.2	4.6	3.7	5.9	4.5	3.5
	wpd	8.5	4.9	2.9	7.7	4.4	2.7	7.0	3.9	2.5	6.3	3.6	2.3
82	TC	27.3	25.9	24.7	26.1	24.9	23.7	25.0	23.9	22.8	23.9	22.9	22.0
	SC	22.8	22.2	21.6	22.2	21.7	21.1	21.7	21.2	20.7	21.2	20.8	20.3
	gpm	6.9	5.2	4.1	6.7	5.0	4.0	6.3	4.9	3.8	6.0	4.6	3.8
	wpd	8.6	5.0	3.1	8.1	4.6	2.9	7.3	4.3	2.7	6.6	3.9	2.6
84	TC	27.7	26.7	25.6	26.7	25.7	24.8	25.6	24.8	24.0	24.6	23.9	23.3
	SC	24.2	23.7	23.2	23.3	22.8	22.3	22.8	22.4	22.0	22.8	22.4	22.0
	gpm	7.0	5.4	4.3	6.7	5.2	4.2	6.5	5.0	4.1	6.3	4.9	3.9
	wpd	8.8	5.3	3.4	8.3	5.0	3.3	7.7	4.6	3.0	7.1	4.3	2.8
86	TC	28.3	27.5	26.7	27.3	26.6	25.9	26.4	25.8	25.2	25.6	25.1	24.5
	SC	25.8	25.3	24.9	25.3	24.9	24.5	24.8	24.5	24.1	24.4	24.1	23.2
	gpm	7.2	5.6	4.5	6.9	5.4	4.4	6.7	5.2	4.2	6.9	5.3	4.1
	wpd	9.5	5.6	3.8	8.6	5.3	3.5	8.1	5.0	3.3	7.7	5.2	3.6
88	TC	29.0	28.4	27.8	28.2	27.7	26.3	27.4	26.5	25.6	28.5	28.2	27.2
	SC	27.3	27.0	26.6	26.6	25.9	26.5	26.2	25.3	26.2	27.7	27.4	26.0
	gpm	7.4	5.8	4.7	7.1	5.6	4.5	6.3	5.4	4.2	7.9	5.9	3.9
	wpd	9.9	6.1	4.0	9.2	5.8	3.6	8.8	5.3	3.4	8.3	5.7	3.4
90	TC	30.0	29.1	28.3	29.1	28.5	27.7	28.5	27.8	27.0	29.6	28.2	27.2
	SC	28.9	28.8	28.0	28.7	28.1	27.3	28.2	27.4	27.0	29.1	28.8	27.8
	gpm	7.6	6.1	5.0	7.5	6.0	4.9	7.3	6.1	4.7	7.1	5.6	4.6
	wpd	10.5	6.3	4.2	9.9	6.1	4.0	9.5	5.8	3.8	9.0	5.5	3.6

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	20.8	18.1	15.5	19.6	17.0	14.5	18.4	15.9	13.4	17.2	14.8	12.5
	SC	14.6	13.4	12.3	14.1	12.9	11.8	13.5	12.4	11.3	13.0	12.0	10.9
	gpm	5.3	3.7	2.6	5.0	3.5	2.4	4.7	3.2	2.3	4.4	3.0	2.1

# 750 CFM - Standard Capacity (65° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	20.4	17.3	14.2	19.2	16.1	13.0	17.9	14.9	11.8	16.6	13.7	10.8
	SC	12.7	11.5	10.2	12.2	11.0	9.7	11.7	10.5	9.2	11.2	10.0	8.8
	gpm	5.2	3.5	2.4	4.9	3.2	2.2	4.5	3.0	2.0	4.2	2.8	1.9
	wpd	8.1	3.7	1.7	7.2	3.2	1.4	6.3	2.8	1.2	5.5	2.3	1.0
76	TC	20.4	17.6	14.8	19.2	16.5	13.8	18.0	15.4	12.8	16.9	14.4	11.9
	SC	13.9	12.7	11.6	13.4	12.3	11.1	12.9	11.8	10.7	12.5	11.4	10.3
	gpm	5.2	3.5	2.5	4.9	3.3	2.3	4.5	3.2	2.2	4.2	2.9	2.0
	wpd	8.1	3.8	1.9	7.2	3.3	1.6	6.3	3.0	1.4	5.5	2.6	1.2
78	TC	20.5	18.1	15.6	19.4	17.1	14.7	18.4	16.1	13.8	17.4	15.1	13.1
	SC	15.1	14.1	13.0	14.7	13.7	12.6	14.3	13.2	12.2	13.8	12.8	11.8
	gpm	5.2	3.7	2.6	4.9	3.5	2.5	4.6	3.2	2.3	4.4	3.1	2.2
	wpd	8.1	4.2	2.1	7.4	3.7	1.9	6.5	3.2	1.6	5.9	2.9	1.5
80	TC	20.8	18.7	16.5	19.8	17.7	15.7	18.9	16.8	14.9	18.0	15.9	14.2
	SC	16.4	15.5	14.4	16.0	15.0	14.1	15.6	14.6	13.6	15.2	14.3	13.2
	gpm	5.2	3.8	2.8	5.0	3.5	2.6	4.8	3.4	2.5	4.5	3.2	2.4
	wpd	8.4	4.3	2.3	7.6	3.8	2.1	7.0	3.5	2.0	6.3	3.2	1.7
82	TC	21.3	19.3	17.4	20.4	18.5	16.7	19.5	17.7	16.0	18.5	16.9	15.4
	SC	17.7	16.8	15.9	17.4	16.4	15.5	17.0	16.1	15.1	16.5	15.7	14.7
	gpm	5.4	3.9	2.9	5.2	3.8	2.9	4.9	3.5	2.7	4.7	3.4	2.6
	wpd	8.9	4.7	2.6	8.1	4.3	2.5	7.4	3.8	2.2	6.7	3.5	2.1
84	TC	21.8	20.1	18.4	20.9	19.3	17.8	20.0	18.6	17.2	19.2	17.9	16.2
	SC	19.1	18.3	17.3	18.7	17.9	16.9	18.3	17.5	16.5	17.9	17.1	16.0
	gpm	5.6	4.1	3.1	5.2	3.9	3.0	5.1	3.8	2.9	4.9	3.6	2.7
	wpd	9.4	5.1	2.9	8.4	4.7	2.8	7.9	4.3	2.6	7.2	4.0	2.2
86	TC	22.3	20.9	19.5	21.5	20.2	18.9	20.8	19.6	18.0	20.1	19.0	17.5
	SC	20.4	19.7	18.7	20.1	19.3	18.3	19.7	18.9	17.8	19.3	18.5	17.2
	gpm	5.6	4.2	3.3	5.5	4.1	3.2	5.2	3.9	3.1	5.1	3.9	2.9
	wpd	9.6	5.5	3.3	9.1	5.1	3.0	8.4	4.7	2.9	7.9	4.5	2.6
88	TC	23.0	21.9	20.4	22.3	21.3	19.9	21.7	20.6	19.3	21.0	20.0	18.8
	SC	21.8	21.1	20.2	21.5	20.7	19.6	21.1	20.3	19.1	20.8	19.8	18.5
	gpm	5.9	4.5	3.5	5.6	4.3	3.4	5.5	4.2	3.2	5.3	4.1	3.2
	wpd	10.5	6.1	3.7	9.6	5.7	3.5	9.1	5.3	3.2	8.6	5.1	3.0
90	TC	23.9	23.0	21.6	23.3	22.4	21.1	22.7	21.8	20.5	22.2	21.3	20.0
	SC	23.2	22.4	21.4	22.8	22.1	20.8	22.5	21.5	20.3	21.9	21.0	19.7
	gpm	6.1	4.6	3.6	5.9	4.5	3.5	5.8	4.4	3.5	5.6	4.3	3.4
	wpd	11.3	6.5	4.0	10.7	6.3	3.8	10.2	5.9	3.7	9.6	5.7	3.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	29.9	27.6	25.0	28.4	26.1	23.5	26.9	24.6	22.0	25.4	23.0	20.5
	SC	17.2	16.2	15.1	16.5	15.5	14.4	15.9	14.9	13.8	15.2	14.2	13.1
	gpm	7.6	5.6	4.2	7.2	5.2	4.0	6.8	5.0	3.7	6.4	4.7	3.4
	wpd	10.5	5.6	3.3	9.5	5.0	2.9	8.5	4.6	2.5	7.5	4.0	2.2
76	TC	29.9	27.7	25.3	28.5	26.3	23.9	27.0	24.8	22.5	25.6	23.4	21.1
	SC	18.5	17.5	16.5	17.8	16.9	15.8	17.2	16.2	15.2	16.6	15.6	14.7
	gpm	7.6	5.6	4.3	7.2	5.3	4.0	6.9	5.0	3.8	6.5	4.7	3.5
	wpd	10.5	5.8	3.4	9.5	5.2	2.9	8.6	4.6	2.6	7.7	4.0	2.3
78	TC	30.0	28.0	25.8	28.6	26.5	24.5	27.2	25.2	23.1	25.8	23.8	21.8
	SC	19.8	18.9	17.9	19.1	18.2	17.3	18.5	17.6	16.8	17.9	17.1	16.2
	gpm	7.6	5.6	4.4	7.2	5.4	4.1	6.9	5.1	3.9	6.5	4.9	3.7
	wpd	10.5	5.8	3.5	9.5	5.3	3.1	8.6	4.7	2.8	7.7	4.3	2.5
80	TC	30.2	28.3	26.3	28.8	27.0	25.1	27.5	25.7	23.8	26.1	24.4	22.5
	SC	21.1	20.3	19.4	20.5	19.7	18.8	19.9	19.1	18.3	19.3	18.5	17.8
	gpm	7.7	5.7	4.5	7.3	5.5	4.2	7.0	5.2	4.0	6.6	4.9	3.8
	wpd	10.7	6.0	3.6	9.7	5.5	3.3	8.8	4.9	2.9	7.9	4.4	2.7
82	TC	30.4	28.7	26.9	29.1	27.4	25.7	27.8	26.1	24.5	26.5	24.9	23.4
	SC	22.5	21.7	20.9	21.9	21.1	20.4	21.3	20.6	19.9	20.7	20.0	19.4
	gpm	7.7	5.8	4.5	7.4	5.6	4.3	7.0	5.2	4.1	6.7	5.1	3.9
	wpd	10.7	6.1	3.8	9.9	5.6	3.4	9.0	5.0	3.1	8.3	4.7	2.8
84	TC	30.7	29.1	27.5	29.4	27.9	26.4	28.2	26.7	25.3	26.9	25.5	24.3
	SC	23.8	23.1	22.4	23.3	22.6	21.9	22.7	22.1	21.4	22.2	21.5	20.0
	gpm	7.8	5.9	4.6	7.4	5.6	4.5	7.1	5.4	4.3	6.8	5.2	4.1
	wpd	10.9	6.3	3.9	10.1	5.8	3.6	9.2	5.3	3.4	8.5	4.9	3.0
86	TC	31.0	29.6	28.2	29.8	28.5	27.2	28.6	27.3	26.2	29.4	28.1	25.2
	SC	25.2	24.6	24.0	24.7	24.1	23.5	24.1	23.6	23.0	23.6	23.1	22.6
	gpm	7.8	6.0	4.8	7.5	5.8	4.6	7.2	5.6	4.4	7.0	5.3	4.2
	wpd	11.2	6.6	4.2	10.3	6.1	3.9	9.5	5.6	3.5	8.8	5.2	3.3
88	TC	31.3	30.2	29.0	30.2	29.1	28.0	29.0	28.1	27.1	28.0	27.1	26.3
	SC	26.6	26.1	25.6	26.1	25.6	25.1	25.6	25.1	24.7	25.1	24.7	24.3
	gpm	7.9	6.1	4.9	7.7	5.9	4.7	7.4	5.7	4.6	7.0	5.5	4.5
	wpd	11.4	6.8	4.4	10.7	6.3	4.0	9.9	6.0	3.9	9.0	5.5	3.6
90	TC	31.7	30.8	29.9	30.7	29.8	29.0	29.6	28.9	28.2	28.6	27.4	26.4
	SC	28.1	27.6	27.2	27.6	27.2	26.7	27.1	26.7	26.3	26.6	26.2	25.0
	gpm	8.1	6.3	5.0	7.8	6.0	4.9	7.5	5.9	4.8	7.3	5.6	4.6
	wpd	11.8	7.1	4.6	10.9	6.6	4.4	10.3	6.3	4.2	9.7	5.8	3.9

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	24.2	21.1	17.9	22.9	19.7	16.5	21.5	18.4	15.2	20.1	17.1	14.0
	SC	14.5	13.2	11.8	13.9	12.6	11.3	13.3	12.0	10.8	12.7	11.5	10.3
	gpm	6.1	4.3	3.0	5.8	4.0	2.8	5.4	3.7	2.6	5.1	3.5</	

# 750 CFM - Standard Capacity (67° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	23.5	20.9	17.4	22.3	19.6	15.9	21.1	18.2	14.5	19.9	16.8	13.1
	SC	12.4	11.4	10.0	12.0	10.9	9.5	11.5	10.4	9.0	11.0	9.9	8.4
	gpm	5.9	4.2	2.9	5.6	3.9	2.7	5.3	3.7	2.5	5.0	3.4	2.2
	wpd	10.7	5.5	2.6	9.6	4.7	2.2	8.6	4.2	1.9	7.6	3.5	1.5
76	TC	23.5	20.9	17.4	22.3	19.6	16.2	21.1	18.2	14.9	19.9	16.9	13.7
	SC	13.6	12.6	11.2	13.2	12.1	10.7	12.7	11.5	10.3	12.2	11.0	9.8
	gpm	5.9	4.2	2.9	5.6	3.9	2.7	5.3	3.7	2.5	5.0	3.4	2.3
	wpd	10.7	5.5	2.6	9.6	4.7	2.2	8.6	4.2	2.0	7.6	3.5	1.6
78	TC	23.5	20.8	17.8	22.3	19.6	16.6	21.1	18.3	15.5	19.8	17.2	14.4
	SC	14.8	13.7	12.5	14.3	13.2	12.1	13.8	12.8	11.6	13.4	12.3	11.2
	gpm	5.9	4.2	3.0	5.6	3.9	2.8	5.3	3.7	2.6	5.0	3.5	2.4
	wpd	10.7	5.5	2.8	9.6	4.7	2.3	8.6	4.2	2.1	7.6	3.7	1.7
80	TC	23.6	21.2	18.5	22.5	20.0	17.4	21.3	18.9	16.3	20.1	17.9	15.3
	SC	15.9	15.0	13.8	15.5	14.5	13.4	15.0	14.1	13.0	14.6	13.6	12.5
	gpm	5.9	4.3	3.1	5.7	4.1	2.9	5.4	3.9	2.8	5.1	3.6	2.5
	wpd	10.7	5.7	2.9	9.9	5.1	2.6	8.9	4.5	2.3	7.9	4.0	2.0
82	TC	23.5	21.4	18.9	22.4	20.3	17.9	21.4	19.4	17.0	20.3	18.3	16.1
	SC	17.2	16.3	15.2	16.7	15.9	14.8	16.3	15.5	14.4	15.9	15.0	14.1
	gpm	5.9	4.3	3.2	5.6	4.1	3.0	5.4	3.9	2.9	5.2	3.7	2.7
	wpd	10.7	5.7	3.0	9.6	5.1	2.8	8.9	4.7	2.5	8.1	4.2	2.2
84	TC	23.8	21.9	19.7	22.8	20.9	18.8	21.8	20.0	17.9	20.9	19.0	17.1
	SC	18.5	17.6	16.6	18.0	17.2	16.2	17.6	16.8	15.9	17.2	16.4	15.5
	gpm	6.0	4.4	3.3	5.8	4.2	3.2	5.6	4.0	3.0	5.3	3.9	2.9
	wpd	11.0	5.9	3.3	10.2	5.5	3.0	9.4	4.9	2.8	8.6	4.5	2.5
86	TC	24.2	22.5	20.4	23.3	21.6	19.6	22.4	20.6	18.9	21.4	19.8	18.1
	SC	19.8	19.0	18.1	19.4	18.6	17.7	19.0	18.2	17.3	18.6	17.8	16.9
	gpm	6.1	4.5	3.5	5.9	4.4	3.3	5.6	4.2	3.2	5.4	4.0	3.1
	wpd	11.3	6.3	3.7	10.7	5.9	3.3	9.6	5.3	3.0	8.9	4.9	2.9
88	TC	24.7	23.1	21.3	23.8	22.2	20.6	22.8	21.4	19.9	21.9	20.6	19.2
	SC	21.1	20.4	19.4	20.7	20.0	19.1	20.3	19.6	18.7	19.9	19.2	18.3
	gpm	6.2	4.7	3.6	6.0	4.5	3.5	5.8	4.3	3.4	5.6	4.2	3.2
	wpd	11.9	6.7	4.0	11.0	6.1	3.7	10.2	5.7	3.5	9.4	5.3	3.2
90	TC	25.2	23.8	22.2	24.3	23.0	21.5	23.4	22.3	20.9	22.6	21.6	20.3
	SC	22.4	21.8	20.9	22.0	21.4	20.5	21.6	21.0	20.1	21.3	20.6	19.7
	gpm	6.4	4.9	3.8	6.2	4.6	3.6	5.9	4.5	3.5	5.7	4.4	3.5
	wpd	12.5	7.2	4.3	11.6	6.5	4.0	10.7	6.3	3.8	9.9	5.9	3.7

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	33.8	31.8	29.2	32.4	30.3	27.6	31.0	28.7	26.0	29.5	27.1	24.3
	SC	17.1	16.3	15.1	16.5	15.6	14.4	15.9	14.9	13.8	15.2	14.2	13.1
	gpm	8.5	6.4	4.9	8.2	6.1	4.7	7.8	5.8	4.4	7.4	5.5	4.1
	wpd	13.3	7.5	4.4	12.3	6.8	4.0	11.2	6.1	3.5	10.1	5.5	3.0
76	TC	33.8	31.8	29.3	32.4	30.3	27.7	31.0	28.8	26.2	29.5	27.2	24.6
	SC	18.4	17.5	16.4	17.8	16.9	15.8	17.1	16.2	15.1	16.5	15.5	14.5
	gpm	8.5	6.4	4.9	8.2	6.1	4.7	7.8	5.9	4.4	7.4	5.5	4.1
	wpd	13.3	7.5	4.4	12.3	6.8	4.0	11.2	6.3	3.5	10.1	5.5	3.1
78	TC	33.8	31.8	29.5	32.4	30.4	27.9	30.9	28.9	26.4	29.5	27.4	24.9
	SC	19.7	18.8	17.8	19.0	18.1	17.1	18.4	17.5	16.5	17.8	16.9	15.8
	gpm	8.5	6.4	5.0	8.2	6.1	4.7	7.8	5.9	4.5	7.4	5.6	4.2
	wpd	13.3	7.5	4.6	12.3	6.8	4.0	11.2	6.3	3.6	10.1	5.6	3.3
80	TC	34.1	32.2	29.9	32.7	30.8	28.5	31.3	29.3	27.0	29.8	27.8	25.6
	SC	20.9	20.1	19.1	20.3	19.5	18.5	19.7	18.8	17.9	19.1	18.2	17.3
	gpm	8.6	6.5	5.1	8.3	6.3	4.8	7.9	6.0	4.5	7.5	5.6	4.3
	wpd	13.5	7.7	4.7	12.5	7.1	4.3	11.4	6.4	3.9	10.3	5.8	3.4
82	TC	33.9	32.2	30.0	32.5	30.8	28.6	31.2	29.4	27.3	29.8	27.9	25.9
	SC	22.2	21.5	20.5	21.6	20.8	19.9	21.0	20.2	19.4	20.4	19.6	18.8
	gpm	8.6	6.5	5.1	8.2	6.3	4.9	7.9	6.0	4.6	7.5	5.6	4.4
	wpd	13.5	7.7	4.7	12.3	7.1	4.3	11.4	6.4	3.9	10.3	5.8	3.4
84	TC	34.1	32.4	30.5	32.7	31.1	29.2	31.4	29.7	27.8	30.0	28.4	26.5
	SC	23.6	22.8	22.0	23.0	22.2	21.4	22.4	21.6	20.8	21.8	21.1	20.3
	gpm	8.6	6.6	5.2	8.3	6.3	4.9	8.0	6.0	4.7	7.6	5.8	4.5
	wpd	13.5	7.9	4.9	12.5	7.1	4.4	11.6	6.6	4.0	10.5	6.1	3.6
86	TC	34.3	32.7	31.0	32.9	31.4	29.7	31.6	30.1	28.4	30.3	28.8	27.2
	SC	24.9	24.2	23.4	24.3	23.6	22.9	23.7	23.1	22.3	23.2	22.5	21.8
	gpm	8.7	6.7	5.2	8.4	6.4	5.1	8.1	6.2	4.9	7.8	6.0	4.7
	wpd	13.8	8.1	5.0	12.8	7.3	4.6	11.6	6.8	4.2	10.7	6.3	3.9
88	TC	34.4	33.1	31.5	33.2	31.8	30.3	31.9	30.6	29.1	30.6	29.4	27.9
	SC	26.2	25.6	24.9	25.7	25.1	24.4	25.1	24.5	23.9	24.5	23.0	21.7
	gpm	8.7	6.7	5.3	8.4	6.4	5.1	8.1	6.2	4.9	7.8	6.0	4.7
	wpd	13.8	8.3	5.2	12.8	7.5	4.7	11.8	7.0	4.4	10.9	6.4	4.0
90	TC	34.7	33.5	32.0	33.5	32.3	30.9	32.3	31.1	29.8	31.0	29.9	28.7
	SC	27.6	27.1	26.4	27.0	26.5	25.9	26.5	26.0	25.4	26.0	25.5	24.9
	gpm	8.8	6.8	5.4	8.5	6.6	5.2	8.1	6.3	5.0	7.8	6.0	4.9
	wpd	14.0	8.5	5.3	13.0	7.9	4.9	12.1	7.1	4.6	11.2	6.6	4.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	28.1	25.0	21.5	26.8	23.6	19.9	25.4	22.1	18.4	23.9	20.6	16.9
	SC	14.5	13.2	11.7	13.9	12.6	11.1	13.3	12.0	10.6	12.7	11.4	10.0
	gpm	7.1	5.1	3.6	6.8	4.8	3.3	6.4	4.5	3.1	6.0	4.2	2.9

# 750 CFM - Standard Capacity (69° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.5	24.2	21.0	25.3	23.0	19.7	24.1	21.7	18.3	22.9	20.4	16.9
	SC	12.1	11.2	10.0	11.6	10.7	9.5	11.1	10.2	9.0	10.7	9.7	8.4
	gpm	6.7	4.9	3.5	6.4	4.6	3.3	6.1	4.4	3.1	5.8	4.1	2.9
	wpd	13.7	7.2	3.8	12.5	6.5	3.3	11.3	5.9	2.9	10.2	5.1	2.5
76	TC	26.6	24.3	21.1	25.4	23.2	19.8	24.2	21.9	18.4	23.0	20.5	16.9
	SC	13.3	12.4	11.2	12.8	12.0	10.7	12.4	11.5	10.1	11.9	11.0	9.6
	gpm	6.7	4.9	3.5	6.4	4.7	3.3	6.2	4.4	3.1	5.8	4.2	2.9
	wpd	13.7	7.4	3.8	12.5	6.7	3.3	11.6	5.9	2.9	10.2	5.3	2.5
78	TC	26.7	24.4	21.2	25.5	23.2	19.8	24.3	21.9	18.4	23.1	20.6	17.0
	SC	14.5	13.6	12.4	14.0	13.1	11.8	13.6	12.7	11.3	13.1	12.1	10.8
	gpm	6.7	4.9	3.5	6.5	4.7	3.3	6.2	4.5	3.1	5.9	4.2	2.9
	wpd	13.7	7.4	3.8	12.8	6.7	3.3	11.6	6.1	2.9	10.5	5.3	2.5
80	TC	26.7	24.4	21.2	25.5	23.2	19.9	24.3	21.9	18.6	23.1	20.6	17.4
	SC	15.7	14.8	13.5	15.2	14.3	13.1	14.8	13.8	12.6	14.3	13.3	12.1
	gpm	6.8	4.9	3.5	6.4	4.7	3.4	6.2	4.5	3.2	5.9	4.2	2.9
	wpd	14.0	7.4	3.8	12.5	6.7	3.5	11.6	6.1	3.0	10.5	5.3	2.6
82	TC	26.7	24.4	21.4	25.5	23.2	20.2	24.2	21.9	19.1	23.0	20.7	18.0
	SC	16.9	15.9	14.8	16.4	15.5	14.3	15.9	15.0	13.9	15.4	14.6	13.5
	gpm	6.8	4.9	3.6	6.4	4.7	3.4	6.1	4.5	3.2	5.8	4.2	3.0
	wpd	14.0	7.4	4.0	12.5	6.7	3.5	11.3	6.1	3.2	10.2	5.3	2.8
84	TC	26.6	24.4	21.8	25.4	23.3	20.7	24.2	22.2	19.7	23.0	21.1	18.6
	SC	18.0	17.2	16.1	17.5	16.7	15.7	17.1	16.3	15.3	16.6	15.9	14.8
	gpm	6.7	4.9	3.7	6.4	4.7	3.5	6.1	4.5	3.3	5.9	4.2	3.2
	wpd	13.7	7.4	4.2	12.5	6.7	3.7	11.3	6.1	3.3	10.5	5.5	3.0
86	TC	26.6	24.7	22.3	25.5	23.7	21.3	24.4	22.6	20.3	23.4	21.6	19.3
	SC	19.2	18.4	17.5	18.8	18.0	17.0	18.3	17.6	16.6	17.9	17.2	16.2
	gpm	6.8	5.0	3.8	6.5	4.8	3.6	6.2	4.5	3.4	5.9	4.4	3.2
	wpd	14.0	7.6	4.3	12.8	7.0	4.0	11.6	6.3	3.5	10.7	5.9	3.2
88	TC	26.8	25.1	23.0	25.8	24.1	22.0	24.8	23.1	21.0	23.8	22.2	20.1
	SC	20.5	19.7	18.8	20.0	19.3	18.4	19.6	18.9	18.0	19.2	18.6	17.7
	gpm	6.8	5.1	3.9	6.6	4.9	3.7	6.3	4.7	3.5	6.0	4.5	3.4
	wpd	14.0	7.9	4.5	13.1	7.2	4.2	12.2	6.7	3.8	11.0	6.1	3.5
90	TC	27.2	25.6	23.6	26.2	24.7	22.7	25.3	23.7	21.8	24.3	22.8	21.0
	SC	21.8	21.0	20.2	21.4	20.7	19.8	21.0	20.3	19.4	20.6	19.9	19.0
	gpm	6.9	5.2	4.0	6.6	5.0	3.9	6.4	4.8	3.7	6.2	4.6	3.5
	wpd	14.3	8.1	4.9	13.4	7.6	4.5	12.5	7.0	4.2	11.6	6.5	3.8

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	31.8	29.1	25.7	30.4	27.7	24.2	29.1	26.2	22.6	27.8	24.7	21.0
	SC	14.3	13.2	11.8	13.7	12.6	11.2	13.2	12.0	10.6	12.6	11.5	10.0
	gpm	8.0	5.9	4.4	7.7	5.6	4.1	7.3	5.3	3.8	7.0	5.0	3.5
	wpd	10.3	5.6	3.1	9.5	5.0	2.7	8.6	4.5	2.4	7.9	4.0	2.0
76	TC	31.8	29.1	25.7	30.5	27.7	24.2	29.2	26.3	22.7	27.8	24.7	21.1
	SC	15.5	14.4	13.1	15.0	13.9	12.5	14.4	13.3	11.9	13.9	12.7	11.3
	gpm	8.1	5.9	4.3	7.7	5.6	4.1	7.4	5.3	3.8	7.0	5.0	3.5
	wpd	10.5	5.6	3.0	9.5	5.0	2.7	8.8	4.5	2.4	8.1	4.0	2.0
78	TC	31.9	29.2	25.8	30.5	27.7	24.5	29.2	26.3	23.1	27.8	24.9	21.7
	SC	16.8	15.7	14.3	16.2	15.1	13.7	15.7	14.5	13.1	15.1	13.9	12.5
	gpm	8.1	5.9	4.4	7.7	5.6	4.1	7.4	5.3	3.8	7.1	5.0	3.5
	wpd	10.5	5.6	3.1	9.5	5.0	2.8	8.8	4.6	2.5	7.9	4.1	2.1
80	TC	31.9	29.1	25.8	30.5	27.7	24.5	29.2	26.3	23.1	27.8	24.9	21.7
	SC	18.0	16.8	15.5	17.4	16.3	15.0	18.1	17.0	15.8	17.5	16.4	15.3
	gpm	8.1	5.9	4.4	7.7	5.7	4.2	7.4	5.4	3.9	7.0	5.1	3.8
	wpd	10.5	5.6	3.1	9.5	5.2	2.8	8.8	4.6	2.5	7.9	4.1	2.3
82	TC	31.8	29.2	26.1	30.5	27.8	24.8	29.2	26.4	23.5	27.8	25.1	22.2
	SC	19.2	18.1	16.8	18.6	17.5	16.3	18.1	17.0	15.8	17.5	16.4	15.3
	gpm	8.1	5.9	4.4	7.7	5.7	4.2	7.4	5.4	3.9	7.0	5.1	3.8
	wpd	10.5	5.6	3.1	9.5	5.2	3.0	8.8	4.8	2.7	8.1	4.2	2.4
84	TC	31.8	29.3	26.6	30.5	28.0	25.3	29.2	26.8	24.0	27.9	25.5	22.8
	SC	20.4	19.3	18.2	19.8	18.8	17.7	19.3	18.3	17.2	18.8	17.8	16.7
	gpm	8.1	6.0	4.5	7.7	5.7	4.3	7.4	5.4	4.1	7.1	5.1	3.8
	wpd	10.5	5.7	3.2	9.5	5.2	3.0	8.8	4.8	2.7	8.1	4.2	2.4
86	TC	31.9	29.6	27.0	30.6	28.4	25.8	29.4	27.2	24.7	28.2	26.0	23.5
	SC	21.6	20.6	19.6	21.1	20.1	19.1	20.6	19.6	18.6	20.1	19.1	18.1
	gpm	8.1	6.0	4.5	7.7	5.7	4.2	7.5	5.5	4.2	7.2	5.3	4.0
	wpd	10.5	5.7	3.3	9.5	5.3	3.1	9.0	4.9	2.8	8.3	4.5	2.6
88	TC	32.1	30.0	27.6	30.9	28.8	26.4	29.7	27.6	25.3	28.5	26.4	24.3
	SC	22.9	22.0	21.0	22.4	21.5	20.5	21.9	21.0	20.1	21.4	20.5	19.6
	gpm	8.2	6.0	4.7	7.8	5.8	4.5	7.5	5.6	4.3	7.2	5.4	4.1
	wpd	10.7	5.9	3.5	9.9	5.4	3.2	9.2	5.0	3.0	8.5	4.6	2.7
90	TC	32.4	30.5	28.2	31.3	29.3	27.1	30.1	28.1	26.1	28.9	27.0	25.0
	SC	24.2	23.4	22.4	23.7	22.9	21.9	23.2	22.4	21.5	22.7	21.9	21.1
	gpm	8.2	6.2	4.8	7.9	5.9	4.6	7.6	5.7	4.4	7.3	5.4	4.2
	wpd	10.9	6.2	3.6	10.1	5.6	3.4	9.4	5.2	3.1	8.6	4.8	2.9

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	41.6	40.4	38.8	40.2	38.9	37.2	38.7	37.4	35.6	37.2	35.8	33.9
	SC	20.7	20.1	19.2	19.9	19.3	18.4	19.2	18.5	17.6	18.4	17.7	16.8
	gpm	10.6	8.1	6.6	10.2	7.9	6.3	9.8					

# 750 CFM - Standard Capacity (71° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	29.6	27.4	24.6	28.5	26.2	23.3	27.3	24.9	22.0	26.0	23.7	20.6
	SC	11.7	10.8	9.8	11.2	10.3	9.3	10.8	9.9	8.8	10.3	9.4	8.3
	gpm	7.5	5.6	4.2	7.2	5.3	3.9	6.9	5.0	3.7	6.6	4.8	3.5
	wpd	17.0	9.4	5.3	16.0	8.6	4.7	14.7	7.6	4.2	13.1	7.0	3.7
76	TC	29.7	27.5	24.8	28.5	26.2	23.5	27.3	25.0	22.1	26.1	23.8	20.8
	SC	12.9	12.0	11.0	12.4	11.6	10.5	12.0	11.1	10.0	11.5	10.6	9.6
	gpm	7.5	5.6	4.2	7.2	5.3	3.9	6.9	5.1	3.8	6.6	4.8	3.5
	wpd	17.0	9.4	5.3	15.7	8.6	4.7	14.7	7.9	4.3	13.4	7.0	3.7
78	TC	29.8	27.6	24.9	28.6	26.4	23.6	27.5	25.1	22.2	26.2	23.9	20.9
	SC	14.1	13.3	12.3	13.7	12.8	11.8	13.2	12.3	11.3	12.7	11.9	10.8
	gpm	7.6	5.6	4.2	7.2	5.3	4.0	6.9	5.1	3.8	6.6	4.9	3.5
	wpd	17.4	9.6	5.5	16.0	8.6	4.9	14.7	7.9	4.3	13.4	7.2	3.8
80	TC	30.0	27.7	25.0	28.8	26.5	23.7	27.5	25.2	22.3	26.4	24.0	20.9
	SC	15.4	14.5	13.4	14.9	14.0	13.0	14.4	13.5	12.5	14.0	13.1	11.9
	gpm	7.6	5.6	4.2	7.2	5.4	4.0	6.9	5.1	3.8	6.7	4.9	3.5
	wpd	17.4	9.6	5.5	16.0	8.9	4.9	14.7	7.9	4.3	13.7	7.2	3.8
82	TC	30.1	27.7	25.0	28.9	26.5	23.7	27.6	25.3	22.3	26.4	24.0	20.9
	SC	16.6	15.7	14.6	16.1	15.2	14.1	15.6	14.7	13.6	15.1	14.3	13.1
	gpm	7.6	5.6	4.2	7.3	5.3	4.0	6.9	5.1	3.8	6.6	4.9	3.5
	wpd	17.7	9.6	5.5	16.3	8.6	4.9	14.7	7.9	4.3	13.4	7.2	3.8
84	TC	30.1	27.7	25.0	28.9	26.5	23.7	27.6	25.2	22.4	26.3	23.9	21.1
	SC	17.8	16.8	15.8	17.3	16.4	15.3	16.8	15.9	14.9	16.3	15.4	14.4
	gpm	7.6	5.6	4.2	7.3	5.4	4.0	7.0	5.1	3.8	6.6	4.9	3.5
	wpd	17.7	9.6	5.5	16.3	8.9	4.9	15.0	7.9	4.3	13.4	7.2	3.8
86	TC	30.1	27.7	25.1	28.8	26.4	23.9	27.6	25.2	22.7	26.2	24.0	21.6
	SC	18.9	18.0	17.0	18.4	17.5	16.5	18.0	17.1	16.1	17.5	16.6	15.7
	gpm	7.6	5.6	4.2	7.3	5.3	4.0	6.9	5.1	3.9	6.6	4.9	3.6
	wpd	17.7	9.6	5.5	16.3	8.6	4.9	14.7	7.9	4.5	13.4	7.2	4.0
88	TC	30.0	27.7	25.4	28.7	26.5	24.3	27.5	25.4	23.2	26.3	24.3	22.1
	SC	20.1	19.2	18.3	19.6	18.8	17.9	19.1	18.3	17.5	18.7	17.9	17.0
	gpm	7.6	5.6	4.3	7.2	5.4	4.1	6.9	5.2	3.9	6.6	4.9	3.7
	wpd	17.4	9.6	5.7	16.0	8.9	5.1	14.7	8.1	4.7	13.4	7.4	4.2
90	TC	29.9	27.8	25.8	28.8	26.7	24.8	27.6	25.7	23.8	26.4	24.7	22.7
	SC	21.2	20.4	19.6	20.8	20.0	19.2	20.4	19.6	18.8	19.9	19.2	18.4
	gpm	7.6	5.6	4.4	7.3	5.4	4.2	7.0	5.2	4.0	6.7	5.0	3.9
	wpd	17.4	9.6	5.9	16.3	8.9	5.3	15.0	8.1	4.9	13.7	7.6	4.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	35.6	33.2	29.9	34.2	31.8	28.5	32.9	30.4	27.0	31.5	28.9	25.4
	SC	14.1	13.1	11.8	13.5	12.6	11.2	13.0	12.0	10.7	12.4	11.4	10.1
	gpm	9.0	6.7	5.1	8.7	6.4	4.8	8.3	6.2	4.5	7.9	5.9	4.3
	wpd	13.0	7.3	4.1	12.1	6.6	3.8	11.1	6.2	3.3	10.1	5.6	3.0
76	TC	35.6	33.2	30.0	34.3	31.8	28.6	32.9	30.5	27.0	31.5	29.0	25.5
	SC	15.3	14.4	13.1	14.8	13.8	12.5	14.2	13.2	11.9	13.7	12.7	11.4
	gpm	9.0	6.7	5.1	8.7	6.4	4.8	8.4	6.2	4.5	8.0	5.9	4.3
	wpd	13.0	7.3	4.1	12.1	6.6	3.8	11.1	6.2	3.4	10.3	5.6	3.0
78	TC	35.6	33.3	30.1	34.3	32.0	28.6	33.0	30.5	27.1	31.6	29.1	25.6
	SC	16.6	15.6	14.3	16.0	15.0	13.8	15.5	14.5	13.2	14.9	13.9	12.6
	gpm	9.1	6.7	5.1	8.7	6.4	4.8	8.3	6.2	4.6	8.0	5.9	4.3
	wpd	13.2	7.3	4.1	12.1	6.8	3.8	11.1	6.2	3.4	10.3	5.6	3.0
80	TC	35.7	33.4	30.1	34.4	32.0	28.6	33.0	30.5	27.1	31.6	29.1	25.6
	SC	17.8	16.8	15.5	17.2	16.3	15.0	16.7	15.7	14.4	16.1	15.1	13.8
	gpm	9.1	6.7	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.3
	wpd	13.2	7.3	4.1	12.1	6.8	3.8	11.3	6.2	3.4	10.3	5.6	3.1
82	TC	35.7	33.4	30.2	34.4	31.9	28.8	33.0	30.5	27.1	31.6	29.1	26.0
	SC	19.0	18.1	16.7	18.5	17.5	16.2	17.9	16.9	15.6	17.3	16.3	15.1
	gpm	9.1	6.8	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.4
	wpd	13.2	7.4	4.1	12.1	6.8	3.8	11.3	6.2	3.4	10.3	5.6	3.1
84	TC	35.7	33.3	30.4	34.3	32.0	29.1	33.0	30.6	27.7	31.6	29.2	26.4
	SC	20.2	19.3	18.0	19.7	18.7	17.4	19.1	18.1	16.9	18.5	17.5	16.4
	gpm	9.1	6.7	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.4
	wpd	13.2	7.4	4.1	12.1	6.8	3.8	11.3	6.2	3.4	10.3	5.6	3.1
86	TC	35.7	33.3	30.4	34.3	32.0	29.1	33.0	30.6	27.7	31.6	29.2	26.4
	SC	21.4	20.5	19.3	20.9	19.9	18.7	20.3	19.4	18.2	19.7	18.8	17.7
	gpm	9.1	6.8	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.5
	wpd	13.2	7.4	4.1	12.1	6.8	3.8	11.3	6.2	3.4	10.3	5.6	3.2
88	TC	35.7	33.6	31.1	34.4	32.4	29.9	33.1	31.1	28.6	31.8	29.9	27.4
	SC	23.8	23.0	21.9	23.3	22.5	21.4	22.8	22.0	21.0	22.3	21.5	20.5
	gpm	9.0	6.8	5.3	8.7	6.6	5.1	8.4	6.3	4.8	8.1	6.0	4.6
	wpd	13.0	7.4	4.5	12.1	6.9	4.1	11.3	6.5	3.8	10.5	5.9	3.4
90	TC	35.7	33.6	31.1	34.4	32.4	29.9	33.1	31.1	28.6	31.8	29.9	27.4
	SC	23.8	23.0	21.9	23.3	22.5	21.4	22.8	22.0	21.0	22.3	21.5	20.5
	gpm	9.0	6.8	5.3	8.7	6.6	5.1	8.4	6.3	4.8	8.1	6.0	4.6
	wpd	13.0	7.4	4.5	12.1	6.9	4.1	11.3	6.5	3.8	10.5	5.9	3.4

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	46.1	44.9	43.5	44.6	43.4	41.9	43.2	41.8	40.3	41.6	40.3	38.7
	SC	20.7	20.0	19.3	19.9	19.2	18.5	19.1	18.5	17.7	18.4	17.7	17.0
	gpm	11.7	9.1	7.4	11.4								

# 750 CFM - Standard Capacity (73° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	33.2	30.8	28.5	32.0	29.6	27.2	30.8	28.4	25.9	29.5	27.1	24.5
	SC	11.3	10.4	9.5	10.8	9.9	9.1	10.3	9.5	8.6	9.9	9.0	8.1
	gpm	8.4	6.2	4.8	8.1	6.0	4.5	7.8	5.8	4.4	7.5	5.5	4.2
	wpd	21.5	11.9	7.0	20.0	11.0	6.3	18.5	10.2	5.9	17.0	9.1	5.3
76	TC	33.1	30.8	28.4	31.9	29.6	27.2	30.7	28.3	25.9	29.5	27.1	24.5
	SC	12.5	11.6	10.8	12.0	11.2	10.3	11.6	10.7	9.9	11.1	10.3	9.4
	gpm	8.4	6.2	4.8	8.1	6.0	4.5	7.7	5.8	4.4	7.5	5.5	4.2
	wpd	21.5	11.9	7.0	20.0	11.0	6.3	18.1	10.2	5.9	17.0	9.1	5.3
78	TC	33.1	30.8	28.5	31.9	29.6	27.2	30.7	28.3	26.0	29.5	27.1	24.6
	SC	13.7	12.8	12.0	13.3	12.4	11.5	12.8	11.9	11.1	12.3	11.5	10.6
	gpm	8.4	6.2	4.8	8.1	6.0	4.6	7.8	5.7	4.4	7.4	5.5	4.2
	wpd	21.5	11.9	7.0	20.0	11.0	6.5	18.5	9.9	5.9	16.7	9.1	5.3
80	TC	33.2	30.9	28.6	32.0	29.7	27.4	30.8	28.5	26.1	29.6	27.3	24.8
	SC	15.0	14.1	13.2	14.5	13.6	12.8	14.0	13.1	12.3	13.6	12.7	11.8
	gpm	8.4	6.2	4.9	8.1	6.0	4.6	7.8	5.8	4.4	7.5	5.6	4.2
	wpd	21.5	11.9	7.2	20.0	11.0	6.5	18.5	10.2	5.9	17.0	9.4	5.3
82	TC	33.4	31.0	28.7	32.1	29.8	27.5	30.9	28.6	26.2	29.7	27.3	24.9
	SC	16.2	15.3	14.4	15.7	14.8	14.0	15.2	14.4	13.5	14.8	13.9	13.0
	gpm	8.4	6.3	4.9	8.1	6.0	4.6	7.8	5.8	4.4	7.5	5.6	4.2
	wpd	21.5	12.2	7.2	20.0	11.0	6.5	18.5	10.2	5.9	17.0	9.4	5.5
84	TC	33.5	31.2	28.8	32.3	29.9	27.6	31.0	28.7	26.3	29.8	27.4	24.9
	SC	17.4	16.5	15.6	16.9	16.0	15.2	16.5	15.6	14.7	16.0	15.1	14.2
	gpm	8.5	6.3	4.9	8.2	6.1	4.6	7.9	5.8	4.5	7.6	5.6	4.2
	wpd	21.9	12.2	7.2	20.3	11.3	6.5	18.8	10.2	6.1	17.4	9.4	5.3
86	TC	33.6	31.2	28.8	32.4	30.0	27.5	31.1	28.7	26.2	29.8	27.4	24.9
	SC	18.6	17.7	16.8	18.1	17.2	16.3	17.7	16.8	15.9	17.2	16.3	15.4
	gpm	8.5	6.3	4.9	8.2	6.1	4.6	7.9	5.8	4.4	7.6	5.6	4.2
	wpd	21.9	12.2	7.2	20.3	11.3	6.5	18.6	10.2	5.9	17.4	9.4	5.3
88	TC	33.6	31.2	28.8	32.4	29.9	27.5	31.1	28.6	26.2	29.8	27.3	24.9
	SC	19.8	18.9	18.0	19.3	18.4	17.5	18.8	17.9	17.0	18.4	17.5	16.6
	gpm	8.5	6.3	4.9	8.2	6.1	4.6	7.9	5.8	4.4	7.6	5.6	4.2
	wpd	21.9	12.2	7.2	20.3	11.3	6.5	18.8	10.2	5.9	17.4	9.4	5.5
90	TC	33.6	31.1	28.8	32.3	29.8	27.6	31.0	28.6	26.4	29.7	27.4	25.3
	SC	21.0	20.0	19.1	20.5	19.6	18.7	20.0	19.1	18.3	19.5	18.6	17.9
	gpm	8.5	6.3	4.9	8.2	6.0	4.6	7.9	5.8	4.5	7.6	5.6	4.2
	wpd	21.9	12.2	7.2	20.3	11.0	6.5	18.8	10.2	6.1	17.4	9.4	5.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	39.6	37.4	34.4	38.3	36.0	33.0	36.9	34.6	31.5	35.5	33.2	30.0
	SC	13.9	13.0	11.8	13.4	12.4	11.3	12.8	11.9	10.7	12.2	11.3	10.1
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.4	7.0	5.3	9.0	6.7	5.1
	wpd	16.2	9.2	5.4	15.0	8.6	5.0	14.1	7.9	4.5	13.0	7.3	4.1
76	TC	39.6	37.4	34.4	38.2	36.0	33.0	36.9	34.6	31.5	35.5	33.2	30.0
	SC	15.1	14.2	13.0	14.6	13.7	12.5	14.0	13.1	11.9	13.5	12.6	11.3
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.4	7.0	5.3	9.0	6.7	5.1
	wpd	16.2	9.2	5.4	15.0	8.6	5.0	14.1	7.9	4.5	13.0	7.3	4.1
78	TC	39.6	37.4	34.5	38.2	36.0	33.0	36.9	34.6	31.6	35.5	33.2	30.0
	SC	16.3	15.4	14.3	15.8	14.9	13.7	15.2	14.3	13.2	14.7	13.8	12.6
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.4	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.2	5.4	15.3	8.6	5.0	14.1	7.9	4.6	13.0	7.3	4.1
80	TC	39.6	37.4	34.6	38.3	36.1	33.1	36.9	34.7	31.7	35.6	33.3	30.1
	SC	17.6	16.7	15.5	17.0	16.1	15.0	16.5	15.6	14.4	15.9	15.0	13.8
	gpm	10.0	7.6	5.8	9.7	7.3	5.6	9.4	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.4	5.4	15.3	8.6	5.0	14.1	7.9	4.6	13.0	7.3	4.1
82	TC	39.7	37.5	34.6	38.4	36.1	33.1	37.0	34.7	31.6	35.6	33.3	30.1
	SC	18.8	17.9	16.8	18.3	17.4	16.2	17.7	16.8	15.6	17.2	16.3	15.1
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.4	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.2	5.4	15.3	8.6	5.0	14.1	7.9	4.6	13.2	7.3	4.1
84	TC	39.7	37.5	34.6	38.4	36.1	33.1	37.0	34.7	31.6	35.6	33.3	30.1
	SC	20.0	19.1	18.0	19.5	18.6	17.4	18.9	18.0	16.8	18.4	17.5	16.3
	gpm	10.0	7.6	5.8	9.7	7.3	5.6	9.4	7.0	5.4	9.1	6.7	5.1
	wpd	16.2	9.4	5.4	15.3	8.6	5.0	14.1	7.9	4.6	13.2	7.3	4.1
86	TC	39.7	37.5	34.6	38.4	36.1	33.1	37.0	34.7	31.7	35.6	33.3	30.2
	SC	21.2	20.3	19.2	20.7	19.8	18.6	20.1	19.2	18.1	19.6	18.7	17.5
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.4	7.0	5.4	9.1	6.7	5.1
	wpd	16.2	9.2	5.4	15.0	8.6	5.0	14.1	7.9	4.6	13.2	7.3	4.1
88	TC	39.7	37.5	34.6	38.3	36.1	33.4	36.9	34.7	32.0	35.5	33.4	30.7
	SC	22.4	21.5	20.4	21.9	21.0	19.8	21.3	20.4	19.3	20.8	19.9	18.8
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.4	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.2	5.4	15.0	8.6	5.0	14.1	7.9	4.6	13.0	7.3	4.2
90	TC	39.6	37.4	34.7	38.3	36.1	33.4	36.9	34.7	32.0	35.5	33.4	30.7
	SC	23.6	22.7	21.8	23.1	22.1	21.4	22.0	21.3	20.6	22.5	21.6	20.6
	gpm	10.0	7.6	5.8	9.8	7.9	7.2	12.1	9.4	7.6	11.7	9.1	7.4
	wpd	13.5	20.4	13.5	31.8	19.1	12.7	29.9	18.2	11.7	28.0	16.7	11.0

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	50.7	49.5	48.2	49.3	48.0	46.6	47.8	46.5	45.0	46.3	44.9	43.4
	SC	20.6	20.0	19.3	19.8	19.2	18.5	19.1	18.4	17.7	18.3	17.7	16.9
	gpm	12.8	10.0	8.1	12.5								

# 750 CFM - Standard Capacity (75° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	36.8	34.4	32.0	35.6	33.2	30.7	34.3	31.9	29.5	33.1	30.6	28.2
	SC	12.1	11.2	10.3	11.6	10.7	9.9	11.1	10.3	9.4	10.7	9.8	9.0
	gpm	9.3	6.9	5.4	9.0	6.7	5.2	8.7	6.5	5.0	8.3	6.2	4.8
	wpd	26.5	14.7	8.9	24.8	13.7	8.1	23.1	12.8	7.6	21.1	11.6	7.0
78	TC	36.8	34.4	32.0	35.6	33.1	30.7	34.3	31.9	29.5	33.1	30.6	28.2
	SC	13.3	12.4	11.6	12.9	12.0	11.1	12.4	11.5	10.7	11.9	11.1	10.2
	gpm	9.3	6.9	5.4	9.0	6.7	5.2	8.7	6.5	5.0	8.3	6.2	4.8
	wpd	26.5	14.7	8.9	24.8	13.7	8.1	23.1	12.8	7.6	21.1	11.6	7.0
80	TC	36.8	34.4	32.0	35.5	33.1	30.7	34.3	31.9	29.4	33.0	30.6	28.2
	SC	14.5	13.7	12.8	14.1	13.2	12.3	13.6	12.7	11.9	13.1	12.3	11.4
	gpm	9.3	6.9	5.4	9.0	6.7	5.2	8.6	6.5	4.9	8.3	6.2	4.8
	wpd	26.5	14.7	8.9	24.8	13.7	8.1	22.7	12.8	7.4	21.1	11.6	7.0
82	TC	36.8	34.5	32.1	35.6	33.2	30.8	34.4	32.0	29.6	33.1	30.7	28.3
	SC	15.8	14.9	14.0	15.3	14.4	13.6	14.8	14.0	13.1	14.4	13.5	12.7
	gpm	9.3	7.0	5.4	9.0	6.7	5.2	8.7	6.5	5.0	8.4	6.2	4.8
	wpd	26.5	15.0	9.0	24.8	13.7	8.4	23.1	12.8	7.6	21.5	11.9	7.0
84	TC	36.9	34.6	32.2	35.7	33.3	31.0	34.5	32.1	29.7	33.2	30.8	28.4
	SC	17.0	16.1	15.2	16.5	15.6	14.8	16.1	15.2	14.3	15.6	14.7	13.9
	gpm	9.3	7.0	5.5	9.0	6.8	5.2	8.7	6.5	5.0	8.4	6.2	4.8
	wpd	26.5	15.0	9.1	24.8	14.0	8.4	23.1	12.8	7.6	21.5	11.9	7.0
86	TC	37.0	34.7	32.3	35.8	33.4	31.0	34.6	32.2	29.8	33.3	30.9	28.4
	SC	18.2	17.3	16.5	17.7	16.9	16.0	17.3	16.4	15.5	16.8	15.9	15.1
	gpm	9.4	7.0	5.5	9.1	6.8	5.2	8.8	6.6	5.0	8.4	6.2	4.8
	wpd	26.9	15.0	9.1	25.2	14.0	8.4	23.5	13.1	7.6	21.5	11.9	7.0
88	TC	37.1	34.8	32.4	35.9	33.5	31.1	34.7	32.3	29.8	33.4	31.0	28.5
	SC	19.4	18.5	17.7	19.0	18.1	17.2	18.5	17.6	16.7	18.0	17.1	16.3
	gpm	9.4	7.0	5.5	9.1	6.8	5.2	8.8	6.6	5.0	8.5	6.2	4.8
	wpd	26.9	15.0	9.1	25.2	14.0	8.4	23.5	13.1	7.6	21.9	11.9	7.0
90	TC	37.2	34.8	32.4	36.0	33.6	31.1	34.7	32.3	29.8	33.4	31.0	28.4
	SC	20.6	19.7	18.8	20.2	19.3	18.4	19.7	18.8	17.9	19.2	18.3	17.4
	gpm	9.4	7.1	5.5	9.1	6.8	5.2	8.8	6.6	5.0	8.5	6.2	4.8
	wpd	26.9	15.3	9.1	25.2	14.0	8.4	23.5	13.1	7.6	21.9	11.9	7.0

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	51.6	49.9	48.0	50.1	48.4	46.5	48.7	46.9	44.9	47.2	45.3	43.4
	SC	18.1	17.4	16.6	17.5	16.7	15.9	16.8	16.1	15.3	16.2	15.4	14.6
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.4
	wpd	31.1	18.6	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.9
78	TC	51.5	49.8	48.0	50.1	48.3	46.4	48.6	46.8	44.9	47.1	45.3	43.3
	SC	19.4	18.6	17.9	18.7	18.0	17.2	17.4	16.6	15.6	17.5	16.7	15.9
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.4
	wpd	31.1	18.6	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.9
80	TC	51.5	49.7	47.9	50.0	48.3	46.4	48.6	46.8	44.9	47.1	45.2	43.3
	SC	20.6	19.9	19.1	20.0	19.3	18.5	19.4	18.6	17.8	18.7	18.0	17.2
	gpm	13.1	10.0	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.1	18.3	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.7
82	TC	51.5	49.7	48.0	50.0	48.3	46.4	48.6	46.8	44.9	47.1	45.3	43.3
	SC	21.9	21.2	20.4	21.3	20.5	19.8	20.6	19.9	19.1	20.0	19.3	18.5
	gpm	13.1	10.0	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.1	18.3	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.9
84	TC	51.5	49.7	48.0	50.0	48.3	46.4	48.6	46.8	44.9	47.1	45.3	43.3
	SC	23.2	22.4	21.7	22.5	21.8	21.0	21.9	21.2	20.4	21.3	20.5	19.7
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.1	18.6	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.7
86	TC	51.5	49.8	48.0	50.0	48.3	46.4	48.6	46.8	44.9	47.1	45.3	43.3
	SC	24.4	23.7	23.0	23.8	23.1	22.3	23.2	22.4	21.7	22.5	21.8	21.0
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.1	18.6	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.7
88	TC	51.4	49.7	47.9	50.0	48.3	46.4	48.5	46.7	44.8	47.0	45.1	43.3
	SC	25.7	25.0	24.2	25.1	24.3	23.6	24.4	23.7	22.9	23.8	23.0	22.3
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.1	18.6	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.7
90	TC	51.4	49.7	47.9	50.0	48.2	46.4	48.5	46.7	44.8	47.1	45.2	43.3
	SC	27.0	26.2	25.5	26.3	25.6	24.8	25.7	24.9	24.2	25.1	24.3	23.5
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.1	18.6	11.8	29.3	17.4	11.2	27.5	16.3	10.5	25.8	15.3	9.7

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	43.8	41.6	39.1	42.5	40.2	37.7	41.1	38.8	36.2	39.7	37.4	34.7
	SC	14.9	14.0	13.0	14.4	13.4	12.5	13.8	12.9	11.9	13.2	12.3	11.3
	gpm	11.1	8.4	6.6	10.8	8.2	6.3	10.4	7.8	6			

# 1000 CFM - Standard Capacity (61° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	20.3	17.8	15.5	19.2	16.9	14.6	18.1	16.0	12.9	17.1	15.1	12.0
	SC	17.6	16.3	14.6	17.1	15.7	14.1	16.5	15.1	12.7	16.0	14.6	11.8
	gpm	5.1	3.6	2.6	4.8	3.4	2.4	4.6	3.3	2.2	4.3	3.0	2.0
	wpd	5.6	2.8	1.4	5.0	2.5	1.3	4.5	2.3	1.0	4.0	2.0	0.9
76	TC	21.3	19.2	17.2	20.3	18.3	15.5	19.3	17.5	14.7	18.5	16.2	13.9
	SC	19.4	18.2	16.6	18.9	17.6	15.3	18.4	17.0	14.5	17.8	15.9	13.7
	gpm	5.3	3.9	2.9	5.1	3.7	2.6	4.9	3.6	2.5	4.7	3.3	2.4
	wpd	6.1	3.2	1.8	5.6	3.0	1.4	5.1	2.7	1.4	4.7	2.3	1.2
78	TC	22.4	20.7	18.1	21.6	19.9	17.3	20.8	18.6	16.6	19.6	17.8	15.8
	SC	21.3	20.1	17.9	20.8	19.4	17.1	20.3	18.3	16.3	19.3	17.6	15.6
	gpm	5.7	4.2	3.0	5.5	4.0	2.9	5.3	3.8	2.8	5.0	3.6	2.7
	wpd	7.0	3.7	2.0	6.5	3.4	1.8	6.0	3.1	1.7	5.3	2.8	1.5
80	TC	23.8	21.7	19.8	23.1	21.0	19.1	21.9	20.2	18.3	21.2	19.5	17.6
	SC	23.2	21.4	19.6	22.6	20.7	18.8	21.6	20.0	18.1	20.9	19.2	17.3
	gpm	6.0	4.4	3.3	5.9	4.2	3.2	5.6	4.1	3.1	5.3	3.9	3.0
	wpd	7.8	4.1	2.4	7.4	3.8	2.2	6.6	3.6	2.1	6.1	3.3	1.9
82	TC	24.8	23.3	21.5	24.1	22.6	20.8	23.4	21.8	20.0	22.7	21.1	19.3
	SC	24.5	23.0	21.2	23.8	22.3	20.5	23.1	21.5	19.8	22.3	20.8	19.1
	gpm	6.3	4.7	3.6	6.1	4.6	3.5	5.9	4.5	3.4	5.7	4.2	3.3
	wpd	8.5	4.8	2.8	7.9	4.5	2.6	7.6	4.3	2.5	7.0	3.8	2.3
84	TC	26.3	24.9	23.2	25.6	24.2	22.4	24.8	23.5	21.7	24.1	22.7	21.0
	SC	25.9	24.6	22.9	25.2	23.8	22.1	24.5	23.1	21.4	23.8	22.4	20.7
	gpm	6.7	5.0	3.9	6.5	4.9	3.8	6.3	4.7	3.6	6.1	4.6	3.6
	wpd	9.6	5.5	3.3	8.9	5.1	3.1	8.5	4.8	2.8	7.9	4.5	2.7
86	TC	27.7	26.5	24.8	27.0	25.8	24.1	26.3	25.0	23.4	25.6	24.3	22.7
	SC	27.4	26.1	24.5	26.7	25.4	23.8	26.0	24.7	23.1	25.2	24.0	22.3
	gpm	7.0	5.3	4.2	6.8	5.2	4.1	6.7	5.0	3.9	6.5	4.9	3.9
	wpd	10.7	6.1	3.7	10.0	5.8	3.6	9.6	5.5	3.3	8.9	5.1	3.2
88	TC	29.2	28.0	26.4	28.5	27.3	25.7	27.8	26.6	25.0	27.0	25.9	24.3
	SC	28.8	27.7	26.0	28.1	27.0	25.4	27.4	26.3	24.7	26.7	25.6	24.0
	gpm	7.4	5.7	4.5	7.2	5.6	4.4	7.0	5.4	4.2	6.8	5.3	4.1
	wpd	11.8	7.0	4.3	11.1	6.6	4.1	10.7	6.3	3.8	10.0	6.0	3.6
90	TC	30.7	29.5	28.0	29.9	28.8	27.3	29.2	28.1	26.6	28.5	27.4	25.9
	SC	30.2	29.1	27.6	29.5	28.4	26.9	28.8	27.7	26.2	28.1	27.0	25.5
	gpm	7.8	5.9	4.7	7.6	5.8	4.6	7.4	5.6	4.5	7.2	5.6	4.4
	wpd	13.0	7.6	4.8	12.3	7.2	4.5	11.8	6.8	4.3	11.1	6.6	4.1

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	27.5	24.9	22.5	25.9	23.5	21.3	24.4	22.1	20.1	23.0	20.9	19.1
	SC	21.8	20.6	19.4	21.1	20.0	18.9	20.5	19.3	18.2	19.8	18.7	17.6
	gpm	7.0	5.1	3.8	6.6	4.8	3.6	6.2	4.5	3.4	5.8	4.3	3.2
	wpd	8.7	4.6	2.6	7.7	4.0	2.3	6.8	3.6	2.1	6.0	3.3	1.9
76	TC	28.2	26.0	24.0	26.8	24.7	22.9	25.3	23.5	21.9	24.0	22.5	20.9
	SC	23.8	22.7	21.7	23.1	22.1	21.1	22.5	21.6	20.5	21.9	21.0	19.9
	gpm	7.1	5.2	4.0	6.8	5.0	3.9	6.4	4.8	3.7	6.1	4.5	3.6
	wpd	9.1	4.9	2.9	8.3	4.4	2.7	7.3	4.0	2.5	6.6	3.6	2.3
78	TC	29.0	27.2	25.6	27.7	26.1	24.7	26.5	25.1	23.7	25.4	24.2	21.2
	SC	25.8	24.9	23.9	25.2	24.3	23.3	24.6	23.8	22.7	24.0	23.2	21.0
	gpm	7.4	5.5	4.4	7.0	5.3	4.2	6.7	5.1	4.0	6.4	4.9	3.6
	wpd	9.7	5.5	3.4	8.9	5.0	3.1	8.1	4.6	2.9	7.3	4.3	2.3
80	TC	30.0	28.7	27.3	30.3	28.6	27.0	29.1	27.8	26.4	28.2	26.9	23.3
	SC	27.9	27.1	26.1	27.3	26.5	24.8	26.8	25.9	23.9	26.2	24.7	23.0
	gpm	7.6	5.8	4.6	7.4	5.6	4.3	7.0	5.5	4.1	6.8	5.1	4.0
	wpd	10.3	6.0	3.8	9.7	5.6	3.3	8.9	5.3	3.0	8.3	4.6	2.8
82	TC	31.3	30.2	27.9	30.3	28.6	27.0	29.7	28.1	26.5	28.1	26.7	24.3
	SC	30.0	29.2	27.6	30.5	28.3	26.7	29.5	28.3	26.5	28.6	27.5	25.3
	gpm	7.9	6.1	5.7	8.9	6.9	5.5	8.6	6.7	5.4	8.5	6.6	5.2
	wpd	11.8	8.9	5.8	14.0	8.5	5.5	13.3	8.1	5.2	12.8	7.7	4.9
84	TC	32.5	31.3	29.8	31.6	30.5	29.0	30.8	29.6	28.1	31.4	30.0	29.1
	SC	32.1	30.9	29.5	31.2	30.1	28.6	30.4	29.2	27.7	31.2	30.2	28.8
	gpm	8.2	6.3	5.1	8.4	6.6	5.2	8.2	6.3	5.1	8.0	6.2	4.9
	wpd	13.3	8.1	5.2	12.6	7.7	4.9	12.1	7.2	4.6	11.4	6.8	4.3
86	TC	35.9	34.9	33.6	35.0	34.1	32.7	34.2	33.2	31.9	33.3	32.4	31.0
	SC	35.4	34.5	33.2	34.6	33.6	32.3	33.8	32.8	31.5	32.9	32.0	30.6
	gpm	9.1	7.0	5.7	8.9	6.9	5.5	8.6	6.7	5.4	8.5	6.6	5.2
	wpd	14.8	8.9	5.8	14.0	8.5	5.5	13.3	8.1	5.2	12.8	7.7	4.9
88	TC	37.6	36.7	35.4	36.7	35.8	34.5	35.9	35.0	33.7	35.0	34.2	32.9
	SC	37.1	36.2	34.9	36.3	35.4	34.1	35.4	34.6	33.3	34.6	33.7	32.5
	gpm	9.5	7.4	5.9	9.3	7.3	5.9	9.1	7.1	5.7	8.9	6.9	5.5
	wpd	16.1	9.9	6.3	15.3	9.5	6.1	14.8	9.1	5.8	14.0	8.5	5.5
90	TC	38.8	38.6	38.1	38.0	37.8	37.3	37.2	37.0	36.5	36.4	36.1	35.7
	SC	43.4	43.1	42.6	42.5	42.2	41.7	41.6	41.3	40.8	40.7	40.4	39.9
	gpm	9.8	7.8	6.4	9.6	7.7	6.3	9.4	7.5	6.2	9.3	7.4	6.1
	wpd	8.2	5.1	3.5	7.8	4.9	3.3	7.5	4.8	3.2	7.2	4.6	3.1

# 1000 CFM - Standard Capacity (63° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	22.9	19.6	16.4	21.5	18.2	15.3	20.1	17.1	14.2	18.8	15.9	13.2
	SC	17.0	15.5	13.9	16.4	14.9	13.4	15.8	14.4	12.8	15.2	13.8	12.2
	gpm	5.8	3.9	2.7	5.4	3.7	2.6	5.0	3.5	2.4	4.7	3.2	2.2
	wpd	7.2	3.3	1.6	6.3	3.0	1.4	5.5	2.6	1.2	4.8	2.2	1.1
76	TC	23.4	20.6	17.8	22.2	19.4	16.8	20.9	18.3	15.8	19.7	17.3	15.0
	SC	18.7	17.3	15.9	18.1	16.8	15.3	17.6	16.3	14.8	17.0	15.7	14.2
	gpm	5.9	4.2	3.0	5.6	3.9	2.8	5.3	3.7	2.7	5.0	3.5	2.5
	wpd	7.6	3.7	1.9	6.8	3.3	1.7	6.0	3.0	1.5	5.3	2.6	1.4
78	TC	24.1	21.6	19.2	23.0	20.6	18.3	21.8	19.6	17.5	20.7	18.7	16.7
	SC	20.5	19.2	17.8	19.9	18.6	17.3	19.4	18.1	16.7	18.9	17.6	16.1
	gpm	6.1	4.4	3.3	5.8	4.2	3.1	5.5	3.9	3.0	5.3	3.8	2.8
	wpd	7.9	4.1	2.3	7.2	3.7	2.1	6.5	3.3	1.9	6.0	3.1	1.7
80	TC	24.9	22.8	20.7	23.8	21.9	19.9	22.8	21.0	19.1	21.9	20.2	17.6
	SC	22.3	21.1	19.7	21.7	20.5	19.1	21.2	20.0	18.6	20.7	19.4	17.4
	gpm	6.3	4.6	3.5	6.0	4.5	3.3	5.8	4.2	3.3	5.6	4.1	3.0
	wpd	8.5	4.5	2.6	7.8	4.3	2.4	7.2	3.8	2.3	6.6	3.6	1.9
82	TC	25.8	24.1	22.3	24.8	23.2	21.6	23.9	22.5	20.1	23.1	21.2	19.4
	SC	24.0	22.9	21.6	23.5	22.4	21.0	23.0	21.9	19.8	22.4	20.9	19.1
	gpm	6.5	4.9	3.8	6.3	4.7	3.6	6.1	4.5	3.4	5.9	4.3	3.3
	wpd	9.2	5.1	3.1	8.5	4.7	2.8	7.9	4.4	2.5	7.4	4.0	2.3
84	TC	26.8	25.5	23.2	26.0	24.8	22.5	25.3	23.5	21.8	24.2	22.8	21.0
	SC	25.8	24.8	22.9	25.3	24.2	22.2	24.8	23.2	21.5	23.8	22.5	20.7
	gpm	6.8	5.2	3.9	6.6	5.0	3.8	6.4	4.7	3.6	6.1	4.6	3.6
	wpd	10.0	5.8	3.3	9.4	5.5	3.1	8.7	4.8	2.8	7.9	4.5	2.7
86	TC	28.2	26.5	24.9	27.1	25.8	24.1	26.4	25.1	23.4	25.6	24.4	22.7
	SC	27.6	26.2	24.5	26.7	25.5	23.8	26.0	24.8	23.1	25.3	24.0	22.4
	gpm	7.1	5.3	4.2	6.8	5.2	4.1	6.7	5.1	3.9	6.5	5.0	3.9
	wpd	10.9	6.1	3.8	10.0	5.8	3.6	9.6	5.6	3.3	9.2	5.3	3.2
88	TC	29.3	28.1	26.5	28.5	27.4	25.8	27.8	26.7	25.1	27.1	26.0	24.3
	SC	28.9	27.7	26.1	28.2	27.0	25.4	27.4	26.3	24.7	26.7	25.6	24.0
	gpm	7.4	5.7	4.5	7.3	5.6	4.4	7.0	5.4	4.2	6.9	5.3	4.1
	wpd	11.8	7.0	4.3	11.4	6.6	4.1	10.7	6.3	3.8	10.2	6.0	3.6
90	TC	30.7	29.6	28.1	30.0	28.9	27.4	29.3	28.1	26.6	28.6	27.4	25.9
	SC	30.3	29.2	27.7	29.6	28.5	27.0	28.9	27.8	26.3	28.2	27.0	25.6
	gpm	7.8	6.0	4.7	7.6	5.9	4.6	7.4	5.7	4.5	7.3	5.6	4.4
	wpd	13.0	7.8	4.8	12.5	7.4	4.5	11.8	7.0	4.4	11.4	6.6	4.1

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	33.3	30.4	27.5	31.5	28.7	25.8	29.7	26.9	24.1	27.9	25.2	22.5
	SC	22.0	20.7	19.4	21.2	19.9	18.7	20.4	19.2	18.0	19.6	18.5	17.3
	gpm	8.4	6.2	4.7	8.0	5.8	4.4	7.5	5.5	4.1	7.1	5.1	3.8
	wpd	8.5	4.6	2.6	7.6	4.0	2.3	6.8	3.6	2.0	6.0	3.1	1.7
76	TC	33.6	31.0	28.4	31.8	29.3	26.8	30.1	27.7	25.3	28.5	26.1	23.8
	SC	23.7	22.6	21.4	23.0	21.8	20.7	22.2	21.1	20.0	21.5	20.4	19.4
	gpm	8.5	6.2	4.8	8.0	5.9	4.5	7.6	5.6	4.3	7.2	5.3	4.0
	wpd	8.7	4.7	2.8	7.8	4.2	2.5	6.9	3.7	2.2	6.3	3.3	1.9
78	TC	34.0	31.7	29.3	32.3	30.1	27.9	30.7	28.5	26.5	29.1	27.1	25.2
	SC	25.5	24.5	23.4	24.8	23.8	22.8	24.1	23.1	22.1	23.3	22.4	21.6
	gpm	8.6	6.4	5.0	8.2	6.1	4.7	7.7	5.8	4.4	7.4	5.5	4.2
	wpd	8.8	4.9	3.0	8.1	4.5	2.7	7.2	4.0	2.4	6.5	3.6	2.1
80	TC	34.4	32.4	30.4	32.9	30.9	29.1	31.3	29.5	27.8	29.8	28.1	26.7
	SC	27.4	26.4	25.5	26.6	25.7	24.9	25.9	25.1	24.3	25.3	24.5	23.8
	gpm	8.7	6.5	5.1	8.4	6.2	4.9	7.9	6.0	4.7	7.5	5.7	4.5
	wpd	9.2	5.2	3.1	8.4	4.7	2.9	7.5	4.4	2.6	6.8	3.9	2.5
82	TC	35.0	33.2	31.6	33.5	31.8	30.4	32.0	30.6	29.2	30.7	29.4	28.2
	SC	29.2	28.4	27.6	28.5	27.7	27.0	27.8	27.2	26.5	29.0	28.0	27.0
	gpm	8.9	6.7	5.3	8.5	6.5	4.5	7.6	5.6	4.3	7.8	5.8	4.6
	wpd	9.5	5.4	3.4	8.7	5.0	3.1	7.9	4.6	3.0	7.2	4.2	2.7
84	TC	35.6	34.2	32.8	34.2	32.9	31.8	32.9	31.8	30.7	31.6	30.7	28.2
	SC	31.1	30.4	29.7	30.4	29.8	29.2	29.8	29.3	28.7	30.0	29.8	28.7
	gpm	9.0	6.9	5.6	8.7	6.7	5.3	8.3	6.5	5.2	8.6	6.5	5.3
	wpd	9.8	5.8	3.7	9.0	5.4	3.4	8.2	5.0	3.2	7.6	4.7	3.2
86	TC	36.4	35.2	34.2	35.1	34.1	33.2	33.9	33.1	30.9	32.9	31.4	30.1
	SC	33.0	32.4	31.9	32.4	31.9	31.4	31.9	31.4	30.5	33.1	32.8	31.0
	gpm	9.2	7.1	5.8	8.6	6.5	5.2	8.0	6.2	4.7	8.4	6.5	5.3
	wpd	10.1	6.1	4.0	9.5	5.8	3.8	8.8	5.4	3.3	8.4	4.9	3.1
88	TC	37.3	36.5	34.5	36.2	35.5	33.6	35.2	34.0	32.8	37.3	35.7	34.0
	SC	35.0	34.6	34.0	34.5	34.1	33.2	34.0	33.5	32.4	37.0	35.7	34.0
	gpm	9.5	7.4	5.8	9.2	7.2	5.6	9.0	6.9	5.6	8.7	6.7	5.4
	wpd	10.8	6.5	4.0	10.1	6.3	3.8	9.6	5.8	3.7	9.0	5.4	3.5
90	TC	38.5	37.4	36.3	37.4	36.5	35.5	36.5	35.7	34.6	38.0	37.4	35.8
	SC	37.1	36.9	35.8	36.9	36.1	35.0	36.1	35.2	34.4	38.5	37.4	36.0
	gpm	9.8	7.5	6.2	9.5	7.4	6.0	9.3	7.2	5.9	9.0	7.1	5.7
	wpd	11.5	6.8	4.6	10.8	6.5	4.4	10.3	6.3	4.1	9.8	6.0	3.9

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	31.3	28.2	25.0	29.6	26.5	23.4	27.9	24.8	21.9	26.1	23.2	20.3
	SC	21.4	20.0	18.6	20.6	19.3	17.9	19.9	18.5	17.2	19.1	17.8	16.5
	gpm	7.9	5.7	4.2	7.5	5.4	4.0	7.0	5.1	3.7	6.6	4	

# 1000 CFM - Standard Capacity (65° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	26.7	23.0	18.8	25.2	21.4	17.2	23.6	19.8	15.7	22.0	18.2	14.3
	SC	16.6	15.1	13.4	16.0	14.5	12.7	15.4	13.8	12.1	14.7	13.2	11.5
	gpm	6.8	4.7	3.2	6.4	4.3	2.9	6.0	4.0	2.7	5.6	3.7	2.4
	wpd	9.8	4.7	2.2	8.7	4.0	1.8	7.8	3.4	1.5	6.6	3.0	1.2
76	TC	26.6	23.3	19.6	25.2	21.9	18.3	23.7	20.4	17.0	22.3	19.0	15.8
	SC	18.1	16.7	15.2	17.5	16.2	14.5	16.9	15.6	14.1	16.4	15.0	13.4
	gpm	6.8	4.7	3.3	6.4	4.5	3.1	6.0	4.2	2.9	5.6	3.9	2.7
	wpd	9.8	4.8	2.4	8.7	4.3	2.1	7.8	3.7	1.8	6.8	3.2	1.5
78	TC	26.8	23.9	20.7	25.4	22.5	19.5	24.0	21.2	18.4	22.8	20.0	17.3
	SC	19.7	18.5	17.0	19.2	17.9	16.5	18.6	17.3	15.9	18.1	16.8	15.4
	gpm	6.8	4.8	3.5	6.4	4.5	3.3	6.1	4.3	3.1	5.8	4.1	2.9
	wpd	9.8	5.0	2.6	8.7	4.4	2.3	7.9	4.0	2.1	7.2	3.6	1.8
80	TC	27.2	24.6	21.8	25.9	23.4	20.8	24.7	22.3	19.7	23.5	21.1	18.8
	SC	21.4	20.2	18.9	20.9	19.7	18.4	20.3	19.2	17.9	19.8	18.7	17.3
	gpm	6.9	5.0	3.7	6.5	4.7	3.5	6.2	4.5	3.3	5.9	4.3	3.2
	wpd	10.2	5.3	3.0	9.2	4.8	2.6	8.3	4.4	2.4	7.6	4.0	2.2
82	TC	27.8	25.6	23.1	26.6	24.5	22.1	25.4	23.3	21.2	24.3	22.3	20.3
	SC	23.2	22.0	20.8	22.6	21.6	20.3	22.1	21.0	19.7	21.6	20.6	19.2
	gpm	7.0	5.2	3.9	6.8	5.0	3.7	6.5	4.7	3.6	6.2	4.5	3.4
	wpd	10.7	5.8	3.3	9.8	5.3	3.0	8.9	4.8	2.7	8.1	4.4	2.5
84	TC	28.4	26.5	24.4	27.3	25.5	23.5	26.2	24.5	22.6	25.2	23.6	21.8
	SC	24.9	23.9	22.6	24.3	23.3	22.2	23.9	22.9	21.6	23.3	22.3	21.1
	gpm	7.2	5.3	4.1	6.9	5.1	3.9	6.6	5.0	3.8	6.4	4.7	3.1
	wpd	11.1	6.1	3.6	10.2	5.6	3.3	9.4	5.3	3.1	8.7	4.8	3.0
86	TC	29.3	27.6	25.7	28.2	26.7	24.9	27.2	25.8	24.1	26.3	25.0	23.4
	SC	26.7	25.7	24.5	26.1	25.2	23.9	25.7	24.7	23.5	25.1	24.1	22.8
	gpm	7.4	5.6	4.4	7.1	5.4	4.2	6.9	5.2	4.1	6.7	5.0	3.9
	wpd	11.8	6.6	4.1	10.9	6.3	3.8	10.2	5.8	3.6	9.6	5.5	3.3
88	TC	30.1	28.8	27.2	29.2	28.0	26.5	28.3	27.2	25.1	27.5	26.5	24.4
	SC	28.4	27.5	26.4	27.9	27.0	25.8	27.4	26.5	24.8	26.9	25.9	24.1
	gpm	7.6	5.9	4.6	7.4	5.7	4.5	7.2	5.5	4.2	7.0	5.3	4.2
	wpd	12.5	7.4	4.5	11.8	7.0	4.3	11.1	6.5	3.8	10.4	6.1	3.7
90	TC	31.2	30.1	28.7	30.4	29.4	27.4	29.7	28.2	26.7	28.6	27.5	26.0
	SC	30.2	29.3	28.1	29.7	28.8	27.0	29.1	27.8	26.3	28.2	27.1	25.6
	gpm	7.9	6.1	4.8	7.7	5.9	4.6	7.6	5.7	4.5	7.3	5.6	4.4
	wpd	13.5	7.9	5.0	12.8	7.6	4.5	12.3	7.0	4.4	11.4	6.6	4.1

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	38.3	35.2	31.8	36.4	33.3	29.8	34.5	31.3	27.8	32.6	29.4	25.9
	SC	22.0	20.6	19.2	21.2	19.8	18.3	20.3	19.0	17.5	19.5	18.1	16.7
	gpm	9.7	7.1	5.3	9.3	6.8	5.0	8.7	6.3	4.7	8.2	5.9	4.4
	wpd	11.3	6.1	3.4	10.3	5.5	3.1	9.2	4.8	2.6	8.1	4.2	2.3
76	TC	38.3	35.4	32.2	36.5	33.5	30.4	34.6	31.7	28.6	32.8	29.8	26.8
	SC	23.7	22.4	21.0	22.8	21.5	20.2	22.0	20.7	19.4	21.2	19.9	18.7
	gpm	9.7	7.2	5.4	9.3	6.8	5.1	8.8	6.4	4.8	8.3	6.0	4.5
	wpd	11.3	6.3	3.5	10.3	5.5	3.1	9.3	4.9	2.8	8.2	4.4	2.5
78	TC	38.4	35.7	32.9	36.7	33.9	31.2	34.9	32.2	29.4	33.1	30.4	27.7
	SC	25.3	24.1	22.9	24.5	23.3	22.1	23.7	22.6	21.4	23.0	21.8	20.7
	gpm	9.7	7.2	5.6	9.3	6.8	5.3	8.8	6.5	5.0	8.4	6.2	4.7
	wpd	11.3	6.3	3.7	10.3	5.6	3.3	9.3	5.0	3.0	8.5	4.6	2.6
80	TC	38.7	36.2	33.6	37.0	34.5	31.9	35.2	32.8	30.3	33.5	31.2	28.7
	SC	27.0	25.9	24.8	26.3	25.2	24.1	25.5	24.4	23.3	24.7	23.7	22.7
	gpm	9.8	7.4	5.6	9.3	7.0	5.4	8.9	6.6	5.1	8.5	6.3	4.8
	wpd	11.5	6.5	3.8	10.5	5.9	3.5	9.5	5.3	3.1	8.7	4.8	2.8
82	TC	39.0	36.7	34.3	37.3	35.1	32.8	35.7	33.5	31.3	34.0	31.9	29.9
	SC	28.8	27.8	26.7	28.0	27.1	26.0	27.3	26.3	25.4	26.6	25.6	24.8
	gpm	9.9	7.4	5.8	9.5	7.1	5.6	9.0	6.8	5.3	8.6	6.5	5.0
	wpd	11.7	6.7	4.0	10.8	6.1	3.7	9.8	5.5	3.3	8.8	5.0	3.1
84	TC	39.3	37.3	35.2	37.7	35.8	33.8	36.2	34.2	32.4	34.6	32.7	30.0
	SC	30.5	29.6	28.7	29.8	28.9	28.0	29.1	28.2	27.4	29.5	28.6	26.8
	gpm	10.0	7.5	5.9	9.6	7.2	5.7	9.2	6.9	5.5	8.7	6.5	4.8
	wpd	12.0	6.8	4.2	11.0	6.3	3.9	10.1	5.8	3.6	9.2	5.3	3.3
86	TC	39.7	37.9	36.2	38.2	36.5	34.8	36.7	35.1	33.5	35.2	33.7	31.3
	SC	32.3	31.5	30.7	31.6	30.8	30.1	30.9	30.2	29.5	30.3	29.6	28.9
	gpm	10.0	7.7	6.1	9.6	7.4	5.9	9.3	7.1	5.6	9.0	7.3	5.6
	wpd	12.0	7.1	4.5	11.2	6.5	4.1	10.5	6.0	3.8	9.6	5.6	3.5
88	TC	40.2	38.7	37.2	38.7	37.3	35.9	37.3	36.0	34.8	35.9	34.8	33.7
	SC	34.1	33.4	32.7	33.4	32.8	32.1	32.8	32.2	31.6	32.2	31.6	30.1
	gpm	10.2	7.8	6.2	9.8	7.6	6.1	9.4	7.3	5.9	9.1	7.1	5.6
	wpd	12.4	7.4	4.7	11.5	6.9	4.5	10.6	6.4	4.1	10.0	6.0	3.8
90	TC	40.7	39.5	38.3	39.4	38.3	37.1	38.0	37.0	36.1	38.6	37.9	35.2
	SC	36.0	35.4	34.8	35.3	34.8	34.2	34.7	34.3	33.7	35.0	34.9	33.2
	gpm	10.3	8.0	6.5	10.0	7.7	6.2	9.6	7.5	6.1	9.3	7.3	5.9
	wpd	12.8	7.8	5.0	12.0	7.2	4.7	11.2	6.8	4.5	10.5	6.4	4.2

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	35.9	32.9	29.1	34.1	31.0	27.2	32.2	29.0	25.2	30.3	27.1	23.3
	SC	21.1	19.8	18.2	20.3	19.0	17.4	19.5	18.2	16.6	18.7	17.4	15.8
	gpm	9.1	6.7	4.9	8.6	6.3	4.6	8.2	5.9	4.3	7.7	5.5	4.0

# 1000 CFM - Standard Capacity (67° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	30.7	27.7	23.2	29.2	26.0	21.3	27.6	24.3	19.4	26.0	22.5	17.6
	SC	16.2	15.0	13.3	15.6	14.4	12.6	15.0	13.7	11.8	14.4	13.0	11.2
	gpm	7.8	5.6	3.9	7.3	5.3	3.6	7.0	4.9	3.3	6.5	4.5	3.0
	wpd	13.0	6.8	3.3	11.6	6.0	2.7	10.4	5.1	2.3	9.2	4.4	1.9
76	TC	30.8	27.8	23.3	29.2	26.0	21.5	27.6	24.2	19.9	26.0	22.5	18.2
	SC	17.8	16.6	14.8	17.2	15.9	14.2	16.6	15.2	13.5	15.9	14.5	12.9
	gpm	7.8	5.6	3.9	7.4	5.3	3.6	7.0	4.9	3.3	6.6	4.5	3.0
	wpd	13.0	6.8	3.3	11.8	6.0	2.8	10.4	5.1	2.4	9.4	4.4	2.0
78	TC	30.8	27.6	23.6	29.2	26.0	22.1	27.6	24.4	20.5	26.0	22.8	19.1
	SC	19.3	18.1	16.5	18.7	17.4	15.9	18.1	16.8	15.2	17.4	16.2	14.7
	gpm	7.8	5.6	4.0	7.4	5.3	3.7	7.0	5.0	3.5	6.6	4.6	3.2
	wpd	13.0	6.6	3.4	11.8	6.0	3.0	10.4	5.3	2.6	9.4	4.5	2.2
80	TC	30.9	28.1	24.4	29.3	26.6	23.0	27.8	25.1	21.6	26.3	23.6	20.3
	SC	20.8	19.7	18.1	20.2	19.1	17.6	19.6	18.5	17.0	19.0	17.9	16.5
	gpm	7.8	5.7	4.2	7.4	5.3	3.9	7.0	5.0	3.6	6.7	4.7	3.4
	wpd	13.0	7.0	3.7	11.8	6.1	3.2	10.7	5.5	2.8	9.6	4.8	2.5
82	TC	30.7	28.2	25.0	29.3	26.8	23.7	27.9	25.5	22.6	26.6	24.2	21.4
	SC	22.4	21.4	19.9	21.8	20.8	19.4	21.3	20.2	18.9	20.7	19.7	18.4
	gpm	7.8	5.7	4.2	7.4	5.4	4.0	7.0	5.1	3.8	6.8	4.9	3.6
	wpd	13.0	7.0	3.8	11.8	6.3	3.4	10.7	5.6	3.1	9.8	5.1	2.8
84	TC	31.0	28.9	26.0	29.7	27.6	24.9	28.4	26.3	23.7	27.2	25.2	22.7
	SC	24.1	23.1	21.8	23.5	22.5	21.3	23.0	22.0	20.8	22.5	21.5	20.2
	gpm	7.9	5.9	4.4	7.5	5.6	4.2	7.2	5.3	4.0	6.9	5.1	3.9
	wpd	13.3	7.4	4.1	12.1	6.6	3.8	11.1	6.1	3.4	10.2	5.6	3.2
86	TC	31.5	29.5	27.1	30.3	28.4	26.0	29.1	27.2	24.9	27.9	26.2	24.0
	SC	25.8	24.8	23.7	25.3	24.3	23.1	24.7	23.9	22.6	24.2	23.3	22.1
	gpm	7.9	5.9	4.5	7.6	5.7	4.4	7.3	5.5	4.2	7.0	5.3	4.0
	wpd	13.5	7.6	4.4	12.5	7.0	4.1	11.6	6.5	3.8	10.7	6.1	3.4
88	TC	32.2	30.3	28.2	31.0	29.2	27.2	29.9	28.1	26.2	28.7	27.1	25.3
	SC	27.5	26.6	25.5	27.0	26.1	25.0	26.5	25.6	24.5	26.0	25.0	24.0
	gpm	8.2	6.2	4.7	7.9	5.9	4.6	7.6	5.7	4.5	7.3	5.5	4.3
	wpd	14.3	8.1	4.8	13.3	7.6	4.5	12.3	7.0	4.3	11.4	6.5	4.0
90	TC	32.9	31.2	29.3	31.8	30.2	28.4	30.7	29.1	27.5	29.6	28.2	26.8
	SC	29.2	28.4	27.3	28.8	27.8	26.8	28.2	27.4	26.3	27.7	26.8	25.8
	gpm	8.3	6.3	5.0	8.0	6.1	4.8	7.8	5.9	4.7	7.5	5.7	4.5
	wpd	14.8	8.5	5.3	13.8	7.9	5.0	13.0	7.4	4.7	12.1	7.0	4.4

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	43.4	40.7	37.2	41.6	38.8	35.1	39.7	36.7	33.0	37.8	34.7	30.9
	SC	22.0	20.8	19.3	21.1	19.9	18.4	20.3	19.1	17.5	19.5	18.2	16.7
	gpm	10.9	8.3	6.3	10.5	7.8	5.9	10.1	7.4	5.6	9.6	7.0	5.2
	wpd	14.3	8.2	4.8	13.3	7.4	4.2	12.2	6.7	3.7	11.0	5.9	3.2
76	TC	43.4	40.7	37.3	41.5	38.8	35.3	39.7	36.8	33.3	37.8	34.8	31.2
	SC	23.6	22.4	20.9	22.7	21.6	20.1	21.9	20.7	19.2	21.1	19.9	18.4
	gpm	11.0	8.3	6.3	10.5	7.8	5.9	10.1	7.4	5.6	9.6	7.1	5.3
	wpd	14.5	8.2	4.8	13.2	7.4	4.2	12.2	6.7	3.8	11.0	6.0	3.3
78	TC	43.3	40.7	37.5	41.5	38.8	35.6	39.6	37.0	33.7	37.8	35.0	31.7
	SC	25.2	24.0	22.6	24.4	23.2	21.8	23.5	22.4	21.0	22.7	21.6	20.2
	gpm	11.0	8.3	6.3	10.5	7.8	6.0	10.0	7.5	5.7	9.6	7.1	5.3
	wpd	14.5	8.2	4.8	13.2	7.4	4.4	12.0	6.8	3.9	11.0	6.0	3.4
80	TC	43.7	41.2	38.2	41.9	39.4	36.3	40.1	37.5	34.5	38.2	35.6	32.6
	SC	26.8	25.7	24.4	26.0	24.9	23.6	25.2	24.1	22.8	24.4	23.4	21.0
	gpm	11.1	8.4	6.5	10.6	8.0	6.2	10.2	7.6	5.8	9.6	7.2	5.7
	wpd	14.7	8.4	5.0	13.5	7.6	4.6	12.4	6.9	4.0	11.2	6.3	3.6
82	TC	43.5	41.2	38.4	41.7	39.4	36.6	40.0	37.6	34.8	38.2	35.8	33.1
	SC	28.5	27.5	26.2	27.7	26.7	25.5	26.9	25.9	24.7	26.1	25.0	22.0
	gpm	11.0	8.4	6.5	10.5	8.0	6.2	10.2	7.6	5.9	9.6	7.1	5.7
	wpd	14.5	8.4	5.0	13.3	7.6	4.6	12.4	6.9	4.1	11.3	6.3	3.7
84	TC	43.7	41.5	38.9	42.0	39.8	37.2	40.2	38.1	35.6	44.2	41.8	39.2
	SC	30.2	29.2	28.1	29.4	28.5	27.4	28.6	27.7	26.7	27.0	26.5	24.1
	gpm	11.1	8.4	6.5	10.6	8.0	6.3	10.2	7.7	6.0	10.6	7.9	6.1
	wpd	14.7	8.5	5.2	13.5	7.8	4.8	12.6	7.2	4.4	11.5	6.5	3.9
86	TC	43.9	41.9	39.6	42.2	40.3	38.0	40.6	38.6	36.4	38.9	37.0	34.8
	SC	31.9	31.0	30.0	31.1	30.3	29.3	30.4	29.5	28.6	29.7	28.8	27.9
	gpm	11.1	8.5	6.7	10.7	8.1	6.4	10.3	7.8	6.2	9.9	7.4	5.9
	wpd	14.9	8.7	5.4	13.7	7.9	4.9	12.8	7.4	4.6	11.7	6.7	4.1
88	TC	44.2	42.4	40.3	42.5	40.8	38.7	40.9	39.2	37.2	44.6	42.9	41.0
	SC	33.6	32.8	31.9	32.1	31.2	32.2	31.4	30.5	31.4	39.7	41.2	39.5
	gpm	11.1	8.6	6.8	10.8	8.3	6.5	10.3	8.0	6.3	39.5	41.2	39.6
	wpd	14.9	8.8	5.5	13.9	8.2	5.2	12.8	7.6	4.8	11.9	6.9	4.4
90	TC	44.5	43.0	41.0	42.9	41.4	39.5	41.4	39.8	38.1	44.9	43.4	41.8
	SC	35.4	34.7	33.8	34.6	34.0	33.1	33.9	33.3	32.6	41.3	40.5	39.6
	gpm	11.3	8.7	6.9	10.8	8.4	6.7	10.5	8.0	6.4	41.6	40.2	38.9
	wpd	15.3	9.2	5.8	14.1	8.5	5.4	13.2	7.8	4.9	12.2	7.2	4.6

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	40.9	38.2	34.5	39.0	36.3	32.4	37.2	34.4	30.2	35.3	32.3	28.5
	SC	20.9	19.8	18.3	20.1	19.0	17.4	19.4	18.2	16.5	18.6	17.4	15.7
	gpm	10.4	7.8	5.9	9.9	7.4	5.5</						

# 1000 CFM - Standard Capacity (69° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	34.5	31.7	28.0	33.0	30.1	26.2	31.4	28.6	24.4	29.9	27.0	22.6
	SC	15.8	14.6	13.2	15.1	14.0	12.5	14.5	13.4	11.9	13.9	12.8	11.2
	gpm	8.8	6.4	4.7	8.4	6.1	4.5	7.9	5.8	4.2	7.6	5.5	3.8
	wpd	16.5	8.7	4.8	15.1	7.9	4.3	13.5	7.2	3.7	12.3	6.5	3.1
76	TC	34.7	31.9	28.2	33.2	30.3	26.4	31.6	28.7	24.6	30.1	27.1	22.7
	SC	17.4	16.2	14.8	16.7	15.6	14.1	16.1	15.0	13.5	15.5	14.4	12.7
	gpm	8.8	6.5	4.7	8.4	6.2	4.5	8.0	5.8	4.2	7.6	5.5	3.9
	wpd	16.7	8.9	4.8	15.1	8.1	4.3	13.8	7.2	3.7	12.5	6.5	3.2
78	TC	34.9	32.0	28.2	33.4	30.4	26.5	31.8	28.8	24.6	30.2	27.2	22.8
	SC	18.9	17.8	16.3	18.3	17.2	15.7	17.7	16.6	15.0	17.1	16.0	14.3
	gpm	8.8	6.5	4.7	8.5	6.2	4.5	8.1	5.8	4.2	7.6	5.5	3.9
	wpd	16.7	8.9	4.8	15.4	8.1	4.3	14.0	7.2	3.7	12.5	6.5	3.2
80	TC	34.9	32.0	28.2	33.4	30.4	26.5	31.8	28.8	24.9	30.2	27.1	23.2
	SC	20.5	19.3	17.9	19.9	18.7	17.2	19.3	18.1	16.6	18.6	17.5	15.9
	gpm	8.8	6.5	4.7	8.4	6.2	4.5	8.1	5.9	4.2	7.6	5.5	3.9
	wpd	16.7	9.2	4.8	15.1	8.1	4.3	14.0	7.4	3.8	12.5	6.5	3.3
82	TC	34.9	31.9	28.4	33.3	30.3	26.9	31.7	28.8	25.3	30.0	27.3	23.8
	SC	22.0	20.8	19.5	21.4	20.2	18.8	20.8	19.6	18.3	20.1	19.1	17.7
	gpm	8.8	6.5	4.8	8.4	6.2	4.5	8.0	5.8	4.3	7.6	5.6	4.0
	wpd	16.7	8.9	5.0	15.1	8.1	4.4	13.8	7.2	4.0	12.3	6.6	3.4
84	TC	34.8	32.0	28.9	33.2	30.5	27.5	31.6	29.1	26.0	30.2	27.7	24.7
	SC	23.5	22.4	21.1	22.9	21.8	20.6	22.3	21.3	20.0	21.7	20.7	19.4
	gpm	8.8	6.5	4.9	8.4	6.2	4.7	8.0	5.9	4.4	7.6	5.6	4.2
	wpd	16.7	8.9	5.1	15.1	8.1	4.7	13.8	7.4	4.1	12.5	6.8	3.7
86	TC	34.8	32.2	29.5	33.3	30.9	28.2	31.9	29.6	26.8	30.5	28.3	25.6
	SC	25.0	24.0	22.9	24.5	23.5	22.3	23.9	23.0	21.8	23.4	22.4	21.3
	gpm	8.8	6.5	5.0	8.5	6.3	4.7	8.1	6.0	4.5	7.7	5.7	4.3
	wpd	16.7	9.2	5.3	15.4	8.5	4.8	14.0	7.8	4.4	12.8	7.0	4.0
88	TC	35.1	32.7	30.3	33.6	31.5	29.0	32.3	30.2	27.9	31.0	29.0	26.7
	SC	26.7	25.7	24.6	26.1	25.2	24.1	25.6	24.6	23.6	25.1	24.2	23.2
	gpm	8.9	6.6	5.1	8.5	6.4	4.9	8.2	6.1	4.7	7.8	5.9	4.5
	wpd	17.0	9.4	5.6	15.4	8.7	5.1	14.3	7.9	4.7	13.0	7.4	4.4
90	TC	35.4	33.4	31.2	34.2	32.3	30.1	32.9	31.0	28.9	31.7	29.8	27.8
	SC	28.4	27.4	26.4	27.8	26.9	26.0	27.3	26.4	25.5	26.8	25.9	24.9
	gpm	9.0	6.8	5.3	8.6	6.5	5.0	8.3	6.3	4.9	8.0	6.0	4.7
	wpd	17.3	9.8	6.0	15.9	9.2	5.5	14.8	8.5	5.1	13.8	7.8	4.7

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	48.6	46.4	43.2	46.8	44.5	41.1	44.9	42.6	39.0	43.1	40.5	36.8
	SC	21.8	20.9	19.5	21.0	20.1	18.6	20.2	19.2	17.7	19.4	18.4	16.8
	gpm	12.3	9.4	7.3	11.8	9.0	6.9	11.4	8.7	6.6	10.9	8.2	6.2
	wpd	18.1	10.6	6.4	16.8	9.8	5.8	15.5	9.0	5.3	14.3	8.1	4.7
76	TC	48.6	46.4	43.1	46.8	44.6	41.1	44.9	42.6	39.0	43.1	40.5	36.9
	SC	23.5	22.5	21.1	22.7	21.7	20.3	21.9	20.8	19.4	21.0	20.0	18.5
	gpm	12.3	9.4	7.3	11.8	9.0	6.9	11.4	8.7	6.6	10.9	8.2	6.2
	wpd	18.3	10.6	6.4	16.8	9.8	5.8	15.5	9.0	5.3	14.3	8.1	4.7
78	TC	48.7	46.4	43.1	46.8	44.5	41.1	45.0	42.6	39.1	43.0	40.5	37.0
	SC	25.1	24.2	22.7	24.3	23.3	21.9	23.5	22.5	21.0	22.7	21.6	20.2
	gpm	12.3	9.4	7.3	11.8	9.0	6.9	11.4	8.7	6.6	10.8	8.2	6.2
	wpd	18.3	10.6	6.4	16.8	9.8	5.8	15.5	9.0	5.3	14.1	8.1	4.7
80	TC	48.6	46.4	43.2	46.8	44.5	41.2	44.9	42.5	39.3	43.0	40.5	37.2
	SC	26.7	25.8	24.4	25.9	24.9	23.6	25.1	24.1	22.7	24.3	23.2	21.9
	gpm	12.3	9.4	7.3	11.8	9.0	7.0	11.4	8.6	6.6	10.9	8.2	6.2
	wpd	18.3	10.6	6.4	16.8	9.8	5.9	15.5	8.8	5.3	14.3	8.1	4.7
82	TC	48.6	46.5	43.4	46.8	44.6	41.5	44.9	42.7	39.6	43.0	40.7	37.6
	SC	28.3	27.4	26.1	27.5	26.6	25.3	26.7	25.8	24.5	27.0	25.9	23.6
	gpm	12.3	9.4	7.3	11.8	9.0	7.0	11.4	8.7	6.7	10.9	8.3	6.3
	wpd	18.3	10.6	6.4	16.8	9.8	5.9	15.5	9.0	5.4	14.3	8.2	4.8
84	TC	48.6	46.6	43.7	46.8	44.7	41.8	45.0	42.9	40.0	43.1	41.0	38.1
	SC	30.0	29.1	27.8	29.1	28.3	27.0	28.4	27.5	26.2	27.6	26.7	25.5
	gpm	12.3	9.5	7.4	11.9	9.1	7.1	11.4	8.7	6.8	10.9	8.3	6.4
	wpd	18.3	10.8	6.5	17.0	10.0	6.0	15.5	9.2	5.5	14.3	8.2	4.9
86	TC	48.7	46.8	44.0	46.9	45.0	42.2	45.1	43.2	40.4	43.4	41.3	38.7
	SC	31.6	30.8	29.6	30.8	30.0	28.8	30.0	29.2	28.0	29.3	28.4	27.3
	gpm	12.3	9.5	7.4	11.9	9.1	7.1	11.4	8.7	6.8	11.0	8.4	6.5
	wpd	18.3	10.8	6.7	17.0	10.0	6.1	15.7	9.2	5.6	14.5	8.4	5.2
88	TC	48.8	47.0	44.5	47.1	45.3	42.7	45.4	43.5	41.0	43.6	41.1	39.3
	SC	33.3	32.5	31.4	32.5	31.7	30.6	31.7	30.9	29.9	31.0	30.2	29.2
	gpm	12.4	9.4	7.5	12.0	9.2	7.2	11.5	8.8	6.9	11.1	8.4	6.6
	wpd	18.5	10.8	6.8	17.2	10.1	6.3	15.9	9.3	5.8	14.7	8.5	5.3
90	TC	49.0	47.3	45.0	47.3	45.6	43.3	45.6	43.9	41.7	43.9	42.3	40.1
	SC	35.0	34.2	33.2	34.2	33.5	32.5	33.5	32.7	31.8	32.7	32.0	31.1
	gpm	12.3	9.6	7.6	12.0	9.3	7.3	11.5	8.9	7.1	11.1	8.6	6.8
	wpd	18.3	11.0	6.9	17.2	10.3	6.4	15.9	9.5	6.0	14.7	8.8	5.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	45.9	43.3	40.2	44.1	41.4	38.2	42.2	39.5	36.1	40.3	37.5	33.9
	SC	20.7	19.5	18.3	19.9	18.8	17.5	19.1	18.0	16.6	18.3	17.2	15.8
	gpm	11.6	8.8	6.8	11.2	8.4	6.5</						

# 1000 CFM - Standard Capacity (71° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	38.7	35.8	32.7	37.2	34.2	30.9	35.6	32.6	29.2	34.0	30.9	27.4
	SC	15.2	14.1	13.0	14.7	13.5	12.3	14.0	12.9	11.7	13.4	12.3	11.0
	gpm	9.8	7.3	5.5	9.4	6.9	5.2	9.1	6.6	4.9	8.6	6.2	4.6
	wdp	20.6	11.4	6.5	19.1	10.2	5.8	17.6	9.4	5.1	15.9	8.3	4.5
76	TC	38.7	35.9	32.9	37.2	34.3	31.2	35.7	32.7	29.4	34.1	31.1	27.6
	SC	16.8	15.7	14.6	16.2	15.1	13.9	15.6	14.5	13.3	15.0	13.9	12.7
	gpm	9.8	7.3	5.6	9.4	7.0	5.3	9.1	6.6	5.0	8.6	6.3	4.7
	wdp	20.6	11.4	6.6	18.8	10.4	6.0	17.6	9.4	5.3	15.9	8.5	4.7
78	TC	38.9	36.0	33.1	37.4	34.5	31.4	35.8	32.9	29.6	34.3	31.3	27.9
	SC	18.4	17.3	16.2	17.8	16.7	15.5	17.2	16.1	14.9	16.6	15.5	14.3
	gpm	9.9	7.3	5.6	9.4	7.0	5.3	9.1	6.7	5.0	8.7	6.3	4.7
	wdp	20.9	11.4	6.6	19.1	10.4	6.0	17.6	9.6	5.3	16.2	8.5	4.7
80	TC	39.1	36.2	33.2	37.6	34.6	31.5	36.0	33.1	29.8	34.4	31.4	27.9
	SC	20.0	18.9	17.8	19.4	18.3	17.1	18.8	17.7	16.5	18.2	17.1	15.8
	gpm	9.9	7.3	5.6	9.5	7.0	5.3	9.1	6.7	5.0	8.8	6.4	4.7
	wdp	20.9	11.6	6.6	19.4	10.4	6.1	17.6	9.6	5.5	16.5	8.7	4.7
82	TC	39.3	36.3	33.3	37.7	34.7	31.5	36.1	33.1	29.8	34.5	31.5	27.9
	SC	21.6	20.5	19.3	21.0	19.8	18.6	20.4	19.2	18.0	19.8	18.6	17.3
	gpm	9.9	7.3	5.6	9.5	7.0	5.3	9.1	6.7	5.0	8.7	6.4	4.7
	wdp	21.2	11.6	6.8	19.4	10.7	6.1	17.9	9.6	5.5	16.2	8.7	4.8
84	TC	39.3	36.3	33.3	37.7	34.7	31.5	36.1	33.0	29.8	34.5	31.3	28.2
	SC	23.2	22.0	20.8	22.5	21.4	20.2	21.9	20.8	19.5	21.3	20.1	18.9
	gpm	9.9	7.3	5.6	9.6	7.0	5.3	9.1	6.7	5.0	8.7	6.3	4.7
	wdp	21.2	11.6	6.8	19.7	10.7	6.1	17.9	9.6	5.5	16.2	8.5	4.8
86	TC	39.3	36.3	33.3	37.7	34.6	31.7	36.0	33.0	30.2	34.4	31.4	28.6
	SC	24.7	23.5	22.3	24.1	22.9	21.8	23.4	22.3	21.2	22.8	21.7	20.6
	gpm	9.9	7.3	5.6	9.5	7.0	5.3	9.1	6.7	5.1	8.7	6.4	4.8
	wdp	21.2	11.6	6.8	19.4	10.4	6.1	17.9	9.6	5.6	16.2	8.7	5.0
88	TC	39.2	36.2	33.6	37.6	34.7	32.1	35.9	33.2	30.7	34.4	31.7	29.2
	SC	26.2	25.0	24.0	25.6	24.5	23.5	25.0	23.9	22.9	24.3	23.4	22.3
	gpm	9.9	7.3	5.6	9.5	7.0	5.4	9.1	6.8	5.2	8.7	6.4	4.9
	wdp	21.2	11.6	6.8	19.4	10.4	6.3	17.9	9.8	5.8	16.2	8.7	5.1
90	TC	39.1	36.4	34.0	37.6	35.0	32.6	36.0	33.6	31.4	34.6	32.2	30.0
	SC	27.7	26.6	25.7	27.1	26.1	25.1	26.5	25.6	24.6	26.0	25.0	24.1
	gpm	9.9	7.3	5.7	9.5	7.0	5.5	9.1	6.8	5.3	8.8	6.5	5.0
	wdp	21.2	11.6	7.0	19.4	10.7	6.5	17.6	10.0	6.0	16.5	9.2	5.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	54.1	51.9	49.2	52.3	50.1	47.2	50.4	48.1	45.2	48.5	46.2	43.0
	SC	12.8	20.8	19.6	20.9	20.0	18.7	20.1	19.1	17.9	19.3	18.3	17.0
	gpm	13.7	10.5	8.3	13.2	10.2	8.0	12.7	9.8	7.6	12.3	9.3	7.3
	wdp	22.5	13.3	8.2	21.1	12.4	7.6	19.4	11.5	6.9	18.1	10.5	6.4
76	TC	54.1	52.0	49.2	52.3	50.1	47.2	50.4	48.2	45.2	48.5	46.2	43.1
	SC	23.4	22.4	21.3	22.6	21.6	20.4	21.7	20.8	19.6	20.9	20.0	18.7
	gpm	13.7	10.5	8.3	13.2	10.2	8.0	12.7	9.8	7.7	12.3	9.3	7.3
	wdp	22.5	13.3	8.2	21.1	12.4	7.6	19.4	11.5	7.1	18.1	10.5	6.4
78	TC	54.1	52.0	49.2	52.3	50.1	47.2	50.5	48.2	45.2	48.6	46.2	43.1
	SC	25.0	24.1	22.9	24.2	23.3	22.1	23.4	22.4	21.2	22.6	21.6	20.3
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.6	12.3	9.3	7.3
	wdp	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	6.9	18.1	10.5	6.4
80	TC	54.2	52.0	49.3	52.3	50.1	47.2	50.5	48.2	45.2	48.6	46.2	43.1
	SC	26.7	25.7	24.5	25.8	24.9	23.7	25.0	24.1	22.8	24.2	23.2	22.0
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.6	12.3	9.3	7.3
	wdp	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	6.9	18.1	10.5	6.4
82	TC	54.2	52.0	49.2	52.3	50.1	47.3	50.5	48.2	45.2	48.5	46.2	43.2
	SC	28.3	27.3	26.2	27.5	26.5	25.3	26.6	25.7	24.5	28.0	26.9	23.6
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.7	12.3	9.3	7.3
	wdp	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	7.1	18.1	10.5	6.4
84	TC	54.1	51.9	49.3	52.3	50.1	47.3	50.4	48.1	45.4	48.5	46.2	43.4
	SC	29.9	28.9	27.8	28.1	27.0	26.2	28.9	27.3	26.4	29.1	28.0	24.9
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.7	13.4	10.4	7.7
	wdp	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	7.1	18.1	10.6	6.4
86	TC	54.1	51.9	49.4	52.2	50.1	47.5	50.4	48.2	45.6	48.5	46.3	43.6
	SC	31.5	30.5	29.5	30.7	29.7	28.6	29.8	28.9	27.9	29.0	28.2	27.1
	gpm	13.7	10.5	8.4	13.2	10.1	8.0	12.8	9.8	7.7	12.3	9.4	7.4
	wdp	22.5	13.3	8.4	21.1	12.2	7.6	19.7	11.5	7.1	18.1	10.6	6.5
88	TC	54.1	52.0	49.6	52.2	50.2	47.7	50.4	48.3	45.8	48.6	46.5	43.9
	SC	33.1	32.2	31.2	32.3	31.4	30.4	31.5	30.6	29.6	30.7	29.8	28.8
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.7	12.3	9.4	7.4
	wdp	22.5	13.3	8.4	21.1	12.4	7.8	19.7	11.5	7.2	18.3	10.6	6.7
90	TC	54.1	52.2	49.9	52.3	50.4	48.1	50.5	48.6	46.2	48.7	46.4	43.7
	SC	34.7	33.9	32.9	33.9	33.1	32.1	33.1	32.3	31.3	34.0	33.1	30.6
	gpm	13.7	10.5	8.4	13.2	10.2	8.1	12.8	9.9	7.8	13.4	10.4	7.9
	wdp	22.5	13.3	8.5	21.1	12.6	7.9	19.7	11.7	7.4	18.3	10.8	6.8

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	51.3	48.6	45.8	49.4	46.7	43.8	47.5	44.7	41.8	45.6	42.8	39.8
	SC	20.4	19.3	18.1	19.6	18.5	17.3	18.8	17.7	16.5	18.0		

# 1000 CFM - Standard Capacity (73° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	43.3	40.3	37.3	41.7	38.6	35.6	40.1	37.1	34.0	38.5	35.4	32.3
	SC	14.7	13.6	12.5	14.1	13.0	11.9	13.5	12.4	11.3	12.9	11.8	10.7
	gpm	10.9	8.2	6.3	10.5	7.8	6.0	10.2	7.5	5.7	9.8	7.2	5.5
	wpd	25.5	14.3	8.5	23.8	13.0	7.8	22.2	12.1	7.0	20.6	11.1	6.5
76	TC	43.2	40.2	37.2	41.6	38.6	35.6	40.0	37.0	33.9	38.5	35.4	32.3
	SC	16.3	15.2	14.1	15.7	14.6	13.5	15.1	14.0	12.9	14.5	13.4	12.3
	gpm	10.9	8.2	6.3	10.5	7.8	6.0	10.1	7.5	5.7	9.7	7.2	5.5
	wpd	25.5	14.3	8.5	23.8	13.0	7.8	21.9	12.1	7.0	20.3	11.1	6.5
78	TC	43.2	40.2	37.2	41.6	38.6	35.7	40.0	37.1	34.0	38.4	35.4	32.4
	SC	17.9	16.8	15.6	17.3	16.2	15.1	16.7	15.6	14.5	16.1	15.0	13.9
	gpm	10.9	8.2	6.3	10.5	7.8	6.0	10.1	7.5	5.7	9.7	7.2	5.5
	wpd	25.5	14.3	8.5	23.8	13.0	7.8	21.9	12.1	7.0	20.3	11.1	6.5
80	TC	43.4	40.4	37.4	41.8	38.8	35.8	40.2	37.2	34.2	38.6	35.6	32.6
	SC	19.5	18.4	17.3	18.9	17.8	16.7	18.3	17.2	16.1	17.7	16.6	15.5
	gpm	11.0	8.2	6.3	10.5	7.9	6.1	10.2	7.5	5.8	9.7	7.2	5.5
	wpd	25.9	14.3	8.5	23.8	13.3	7.9	22.2	12.1	7.2	20.3	11.1	6.5
82	TC	43.5	40.6	37.6	41.9	39.0	36.0	40.4	37.4	34.4	38.7	35.7	32.7
	SC	21.1	20.0	18.8	20.5	19.4	18.2	19.9	18.8	17.7	19.3	18.2	17.1
	gpm	11.0	8.2	6.3	10.6	7.9	6.1	10.2	7.6	5.8	9.8	7.2	5.5
	wpd	25.9	14.6	8.5	24.2	13.3	7.9	22.5	12.3	7.2	20.6	11.1	6.5
84	TC	43.7	40.7	37.7	42.1	39.1	36.1	40.5	37.5	34.5	38.9	35.8	32.8
	SC	22.7	21.6	20.4	22.1	20.9	19.8	21.5	20.3	19.2	20.9	19.7	18.6
	gpm	11.1	8.2	6.4	10.7	7.9	6.1	10.2	7.6	5.8	9.9	7.3	5.6
	wpd	26.2	14.6	8.7	24.5	13.5	7.9	22.5	12.3	7.2	20.9	11.4	6.6
86	TC	43.8	40.8	37.8	42.2	39.2	36.1	40.6	37.5	34.4	39.0	35.9	32.7
	SC	24.3	23.1	22.0	23.7	22.5	21.4	23.0	21.9	20.7	22.4	21.3	20.1
	gpm	11.1	8.3	6.4	10.7	7.9	6.1	10.3	7.6	5.8	9.9	7.3	5.5
	wpd	26.6	14.8	8.7	24.5	13.5	7.9	22.8	12.3	7.2	20.9	11.4	6.5
88	TC	43.9	40.8	37.7	42.3	39.2	36.0	40.6	37.5	34.4	39.0	35.8	32.8
	SC	25.8	24.7	23.5	25.2	24.0	22.9	24.6	23.4	22.3	24.0	22.8	21.7
	gpm	11.1	8.3	6.4	10.7	7.9	6.1	10.3	7.6	5.8	9.9	7.3	5.6
	wpd	26.6	14.8	8.7	24.5	13.5	7.9	22.8	12.3	7.2	20.9	11.4	6.6
90	TC	43.8	40.8	37.7	42.2	39.1	36.1	40.6	37.4	34.6	38.9	35.7	33.1
	SC	27.3	26.2	25.0	26.7	25.5	24.4	26.1	24.9	23.9	25.5	24.3	23.3
	gpm	11.1	8.2	6.4	10.7	7.9	6.1	10.2	7.6	5.9	9.9	7.2	5.6
	wpd	26.6	14.6	8.7	24.5	13.5	7.9	22.5	12.3	7.4	20.9	11.1	6.6

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	57.0	54.2	51.4	55.1	52.3	49.4	53.2	50.4	47.5	51.3	48.4	45.5
	SC	20.1	19.0	17.8	19.3	18.2	17.0	18.6	17.4	16.3	17.8	16.6	15.5
	gpm	14.3	11.0	8.7	14.0	10.6	8.3	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	36.6	21.6	13.5	35.0	20.1	12.3	32.3	18.6	11.4	30.1	17.2	10.5
76	TC	56.9	54.2	51.4	55.1	52.3	49.4	53.2	50.3	47.4	51.3	48.4	45.4
	SC	21.8	20.7	19.5	21.1	19.9	18.7	20.3	19.1	18.0	19.5	18.3	17.2
	gpm	14.3	11.0	8.7	13.9	10.6	8.3	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	36.6	21.6	13.5	34.6	20.1	12.3	32.3	18.3	11.4	30.1	17.2	10.5
78	TC	56.9	54.2	51.4	55.1	52.3	49.4	53.2	50.3	47.5	51.2	48.4	45.5
	SC	23.5	22.4	21.3	22.7	21.6	20.5	22.0	20.8	19.7	21.2	20.1	18.9
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5
80	TC	56.9	54.3	51.5	55.1	52.3	49.5	53.2	50.4	47.5	51.3	48.4	45.5
	SC	25.2	24.1	23.0	24.5	23.3	22.2	23.7	22.6	21.4	22.9	21.8	20.7
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5
82	TC	57.0	54.3	51.5	55.1	52.4	49.6	53.2	50.5	47.6	51.3	48.5	45.5
	SC	27.0	25.9	24.7	26.2	25.1	23.9	25.4	24.3	23.2	24.6	23.5	22.4
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5
84	TC	57.1	54.4	51.6	55.2	52.5	49.6	53.3	50.5	47.6	51.4	48.5	45.5
	SC	28.7	27.6	26.4	27.9	26.8	25.6	27.1	26.0	24.9	26.3	25.2	24.1
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	37.4	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5
86	TC	57.1	54.4	51.5	55.2	52.5	49.6	53.3	50.5	47.6	51.3	48.5	45.5
	SC	30.4	29.3	28.1	29.6	28.5	27.3	28.8	27.7	26.5	28.0	26.9	25.8
	gpm	14.5	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7
	wpd	37.4	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5
88	TC	57.0	54.3	51.5	55.1	52.4	49.6	53.2	50.4	47.7	51.2	48.5	45.9
	SC	33.7	32.6	31.5	32.9	31.8	30.7	32.2	31.0	30.0	31.4	30.3	29.2
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.1	13.0	9.8	7.8
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5
90	TC	57.0	54.3	51.5	55.1	52.4	49.6	53.2	50.4	47.7	51.2	48.5	45.9
	SC	33.7	32.6	31.5	32.9	31.8	30.7	32.2	31.0	30.0	31.4	30.3	29.2
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.5	10.2	8.1	13.0	9.8	7.8
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	62.3	60.5	58.1	60.4	58.7	56.1	58.6	56.7	54.0	56.7	54.7	51.9
	SC	2											

# 1000 CFM - Standard Capacity (75° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	48.0	44.9	41.9	46.4	43.3	40.2	44.8	41.7	38.6	43.1	40.0	36.9
	SC	15.8	14.6	13.5	15.2	14.0	12.9	14.6	13.4	12.3	13.9	12.8	11.8
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.4	8.5	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	9.8	27.7	15.4	9.2	25.5	14.0	8.3
78	TC	48.0	44.9	41.8	46.4	43.3	40.2	44.8	41.6	38.5	43.1	40.0	36.9
	SC	17.4	16.2	15.1	16.8	15.6	14.5	16.2	15.0	14.0	15.6	14.4	13.4
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.3	8.4	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	9.8	27.3	15.1	9.2	25.5	14.0	8.3
80	TC	47.9	44.9	41.8	46.3	43.3	40.2	44.7	41.6	38.5	43.1	40.0	36.9
	SC	19.0	17.8	16.7	18.4	17.2	16.1	17.8	16.6	15.5	17.2	16.0	15.0
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.3	8.4	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	9.8	27.3	15.1	9.2	25.5	14.0	8.3
82	TC	48.0	45.0	41.9	46.4	43.4	40.3	44.8	41.7	38.7	43.2	40.1	37.0
	SC	20.5	19.4	18.3	19.9	18.8	17.7	19.3	18.2	17.1	18.7	17.6	16.5
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.4	8.5	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	10.0	27.7	15.4	9.2	25.5	14.0	8.3
84	TC	48.1	45.1	42.1	46.6	43.5	40.5	45.0	41.9	38.8	43.3	40.3	37.2
	SC	22.1	21.0	19.9	21.5	20.4	19.3	20.9	19.8	18.7	20.3	19.2	18.1
	gpm	12.2	9.1	7.1	11.8	8.8	6.8	11.4	8.5	6.5	11.0	8.2	6.2
	wpd	31.8	17.9	10.9	29.9	16.7	10.0	27.7	15.4	9.2	25.9	14.3	8.3
86	TC	48.3	45.3	42.3	46.7	43.7	40.6	45.1	42.0	39.0	43.5	40.4	37.3
	SC	23.7	22.6	21.5	23.1	22.0	20.9	22.5	21.4	20.3	21.9	20.8	19.7
	gpm	12.2	9.2	7.1	11.8	8.8	6.8	11.4	8.5	6.6	11.0	8.2	6.3
	wpd	32.2	18.2	10.9	29.9	16.7	10.0	28.0	15.6	9.4	25.9	14.3	8.5
88	TC	48.5	45.4	42.4	46.9	43.8	40.7	45.2	42.2	39.0	43.6	40.5	37.3
	SC	25.3	24.2	23.1	24.7	23.6	22.5	24.1	23.0	21.9	23.5	22.4	21.3
	gpm	12.2	9.2	7.2	11.9	8.9	6.9	11.4	8.5	6.6	11.1	8.2	6.3
	wpd	32.2	18.2	11.1	30.3	17.0	10.2	28.0	15.6	9.4	26.2	14.6	8.5
90	TC	48.6	45.5	42.4	47.0	43.9	40.7	45.3	42.2	39.0	43.7	40.5	37.3
	SC	26.9	25.7	24.6	26.3	25.1	24.0	25.7	24.5	23.4	25.1	23.9	22.8
	gpm	12.3	9.2	7.1	11.9	8.9	6.9	11.5	8.5	6.6	11.1	8.2	6.3
	wpd	32.6	18.2	10.9	30.3	17.0	10.2	28.4	15.6	9.4	26.2	14.6	8.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	66.0	63.9	61.5	64.2	62.0	59.6	62.3	60.0	57.6	60.4	58.1	55.5
	SC	23.2	22.3	21.2	22.4	21.4	20.4	21.6	20.6	19.6	20.7	19.8	18.7
	gpm	16.7	12.9	10.4	16.2	12.6	10.1	15.8	12.2	9.7	15.3	11.8	9.4
	wpd	33.5	20.1	13.0	31.8	19.0	12.2	30.0	17.9	11.3	28.0	16.8	10.6
78	TC	66.0	63.8	61.4	64.1	61.9	59.5	62.3	60.0	57.5	60.4	58.0	55.5
	SC	24.8	23.9	22.9	24.0	23.0	22.0	23.2	22.2	21.2	22.4	21.4	20.4
	gpm	16.7	12.9	10.4	16.2	12.6	10.0	15.8	12.2	9.7	15.3	11.7	9.4
	wpd	33.5	20.1	13.0	31.8	19.0	12.0	30.0	17.9	11.3	28.0	16.6	10.6
80	TC	65.9	63.7	61.4	64.1	61.9	59.4	62.2	59.9	57.5	60.3	58.0	55.5
	SC	26.4	25.5	24.5	25.6	24.7	23.7	24.8	23.8	22.8	24.0	23.0	22.0
	gpm	16.7	12.9	10.4	16.2	12.6	10.0	15.8	12.2	9.7	15.3	11.7	9.4
	wpd	33.5	19.9	13.0	31.8	19.0	12.0	30.0	17.9	11.3	28.0	16.6	10.6
82	TC	65.9	63.7	61.4	64.1	61.9	59.5	62.2	59.9	57.5	60.3	58.0	55.5
	SC	28.1	27.1	26.1	27.2	26.3	25.3	26.4	25.5	24.5	25.6	24.7	23.7
	gpm	16.7	12.9	10.4	16.2	12.6	10.0	15.8	12.2	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	19.0	12.0	30.0	17.9	11.3	28.0	16.6	10.5
84	TC	65.9	63.7	61.4	64.1	61.8	59.5	62.2	59.9	57.5	60.3	58.0	55.5
	SC	29.7	28.7	27.8	28.9	27.9	26.9	28.1	27.1	26.1	27.2	26.3	25.3
	gpm	16.7	12.9	10.4	16.2	12.5	10.0	15.8	12.2	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.0	30.0	17.9	11.3	28.0	16.6	10.5
86	TC	65.9	63.7	61.4	64.1	61.8	59.5	62.2	59.9	57.5	60.3	58.0	55.5
	SC	31.3	30.4	29.4	30.5	29.5	28.6	29.7	28.7	27.7	29.8	28.8	27.8
	gpm	16.7	12.9	10.4	16.2	12.5	10.1	15.8	12.1	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.2	30.0	17.6	11.3	28.0	16.6	10.5
88	TC	65.9	63.7	61.4	64.1	61.8	59.4	62.2	59.9	57.4	60.3	58.0	55.5
	SC	32.9	32.0	31.0	32.1	31.2	30.2	31.3	30.3	29.4	30.5	29.5	28.5
	gpm	16.7	12.9	10.4	16.2	12.5	10.0	15.8	12.1	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.0	30.0	17.6	11.3	28.0	16.6	10.5
90	TC	65.9	63.7	61.4	64.1	61.8	59.4	62.2	59.8	57.4	60.2	57.8	55.4
	SC	34.5	33.6	32.6	33.7	32.8	31.8	32.9	31.9	31.0	32.1	31.1	30.2
	gpm	16.7	12.9	10.4	16.2	12.5	10.0	15.8	12.1	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.0	30.0	17.6	11.3	28.0	16.6	10.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	62.9	60.2	57.3	61.0	58.2	55.3	59.1	56.3	53.3	57.2	54.3	51.3
	SC	21.5	20.4	19.3	20.8	19.6	18.5	20.0	18.8	17.7	20.5	19.4	

# 1250 CFM - Standard Capacity (61° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.9	23.6	20.6	25.4	22.4	19.4	24.0	21.2	17.2	22.7	20.1	16.1
	SC	23.2	21.5	19.4	22.5	20.8	18.7	21.9	20.0	17.0	21.2	19.3	15.9
	gpm	6.8	4.8	3.5	6.5	4.5	3.2	6.1	4.3	2.9	5.8	4.0	2.7
	wpd	6.6	3.3	1.7	6.0	2.9	1.5	5.3	2.6	1.2	4.8	2.3	1.0
76	TC	28.1	25.4	22.8	26.8	24.3	20.9	25.6	23.3	19.8	24.5	21.7	18.7
	SC	25.6	24.0	22.1	25.0	23.2	20.6	24.3	22.6	19.5	23.6	21.4	18.5
	gpm	7.1	5.1	3.9	6.8	4.9	3.6	6.5	4.7	3.3	6.2	4.4	3.2
	wpd	7.2	3.8	2.1	6.6	3.4	1.8	6.0	3.2	1.6	5.6	2.8	1.4
78	TC	29.7	27.4	24.3	28.5	26.4	23.3	27.5	24.9	22.3	26.2	23.9	21.2
	SC	28.2	26.6	24.0	27.4	25.7	23.0	26.8	24.6	22.0	25.9	23.6	20.9
	gpm	7.5	5.5	4.1	7.3	5.4	3.9	6.9	5.0	3.8	6.6	4.8	3.6
	wpd	8.1	4.4	2.4	7.6	4.1	2.2	6.9	3.7	2.1	6.3	3.3	1.8
80	TC	31.3	29.0	26.6	30.4	28.1	25.6	29.2	27.1	24.6	28.3	26.2	23.6
	SC	30.6	28.7	26.3	29.8	27.8	25.3	28.9	26.8	24.3	27.9	25.8	23.3
	gpm	7.9	5.8	4.5	7.7	5.7	4.3	7.4	5.5	4.2	7.1	5.3	3.9
	wpd	8.9	4.9	2.9	8.4	4.6	2.7	7.9	4.4	2.5	7.2	4.0	2.2
82	TC	33.1	31.2	28.8	32.2	30.2	27.9	31.2	29.3	26.9	30.2	28.3	25.9
	SC	32.7	30.8	28.5	31.7	29.9	27.6	30.8	28.9	26.6	30.8	27.9	25.6
	gpm	8.4	6.3	4.9	8.1	6.2	4.7	7.9	5.9	4.6	7.7	5.7	4.4
	wpd	10.1	5.7	3.4	9.5	5.4	3.2	8.9	5.0	3.0	8.4	4.6	2.8
84	TC	35.1	33.3	31.1	34.1	32.4	30.1	33.1	31.4	29.1	32.2	30.5	28.2
	SC	34.6	32.9	30.7	33.7	32.0	29.7	32.7	31.0	28.8	31.8	30.1	27.8
	gpm	8.9	6.8	5.2	8.6	6.5	5.0	8.4	6.4	4.9	8.1	6.2	4.7
	wpd	11.4	6.6	3.9	10.6	6.2	3.7	10.1	5.9	3.4	9.5	5.4	3.2
86	TC	37.0	35.4	33.3	36.0	34.5	32.3	35.1	33.5	31.4	34.1	32.6	30.4
	SC	36.5	35.0	32.8	35.6	34.1	31.9	34.6	33.1	31.0	33.7	32.2	30.0
	gpm	9.4	7.2	5.6	9.2	7.0	5.4	8.9	6.8	5.3	8.7	6.6	5.1
	wpd	12.7	7.4	4.5	12.0	7.1	4.3	11.4	6.6	4.0	10.8	6.3	3.8
88	TC	38.9	37.4	35.4	38.0	36.5	34.5	37.0	35.6	33.5	36.1	34.6	32.6
	SC	38.5	37.0	34.9	37.5	36.0	34.0	36.6	35.1	33.1	35.6	34.2	32.2
	gpm	9.9	7.6	6.0	9.6	7.4	5.8	9.4	7.2	5.7	9.2	7.0	5.5
	wpd	14.0	8.2	5.2	13.3	7.9	4.9	12.7	7.4	4.6	12.0	7.1	4.4
90	TC	40.9	39.4	37.5	39.9	38.4	36.6	39.0	37.5	35.6	38.0	36.5	34.7
	SC	40.4	38.9	37.0	39.4	37.9	36.1	38.5	37.0	35.2	37.5	36.1	34.3
	gpm	10.3	8.0	6.3	10.1	7.8	6.2	9.9	7.6	6.0	9.6	7.4	5.8
	wpd	15.4	9.1	5.7	14.7	8.8	5.4	14.0	8.2	5.2	13.3	7.9	4.9

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	34.2	30.4	26.8	32.3	28.6	25.4	30.4	27.1	20.6	28.6	25.6	19.2
	SC	30.5	28.8	24.1	26.9	25.2	23.3	26.1	24.4	20.3	25.2	23.7	19.0
	gpm	8.6	6.1	4.6	8.1	5.8	4.2	7.6	5.5	3.5	7.2	5.2	3.2
	wpd	5.9	3.0	1.7	5.3	2.7	1.4	4.6	2.4	1.0	4.1	2.1	0.8
76	TC	35.5	32.1	29.3	33.7	30.7	25.1	31.9	29.3	23.8	30.4	26.1	22.5
	SC	33.2	28.8	27.2	30.7	28.1	24.8	30.9	27.4	23.5	28.1	25.8	22.2
	gpm	9.0	6.5	5.0	8.6	6.2	4.2	8.1	5.9	4.0	7.7	5.3	3.8
	wpd	6.4	3.3	2.0	5.8	3.1	1.4	5.2	2.8	1.3	4.7	2.2	1.2
78	TC	36.7	34.2	32.9	35.1	32.8	28.1	33.8	30.1	26.8	32.5	28.9	25.5
	SC	33.2	31.8	30.9	32.5	31.1	27.7	31.8	29.7	26.5	31.0	28.5	25.2
	gpm	9.3	6.9	5.0	8.9	6.6	4.7	8.6	6.1	4.5	8.2	5.8	4.3
	wpd	6.9	3.8	2.0	6.3	3.5	1.8	5.8	2.9	1.6	5.4	2.7	1.5
80	TC	38.4	36.3	32.1	37.1	33.8	30.9	35.8	32.7	29.7	33.9	31.5	28.5
	SC	36.1	34.7	31.7	35.4	33.4	30.5	34.6	32.3	29.3	33.5	31.1	28.1
	gpm	10.7	7.6	5.9	9.7	7.4	5.6	9.5	7.1	5.5	9.2	6.9	5.2
	wpd	8.3	4.5	2.8	7.5	4.3	2.5	7.1	4.1	2.4	6.8	3.8	2.2
82	TC	42.0	40.0	37.4	40.9	38.6	33.6	39.8	37.7	35.1	38.7	36.6	34.0
	SC	41.5	39.5	37.0	40.4	38.4	35.9	39.3	37.3	34.7	38.2	36.2	33.6
	gpm	10.6	8.1	6.3	10.4	7.9	6.1	10.1	7.6	5.9	9.8	7.4	5.7
	wpd	9.0	5.3	3.2	8.6	4.9	3.0	8.0	4.6	2.8	7.6	4.3	2.6
84	TC	44.4	42.4	40.0	43.3	41.3	38.9	42.2	40.2	37.7	41.1	39.1	36.6
	SC	43.8	41.9	39.5	42.8	40.8	38.4	41.7	39.7	37.3	40.6	38.6	36.2
	gpm	11.2	8.6	6.7	11.0	8.4	6.6	10.7	8.1	6.4	10.4	7.9	6.1
	wpd	10.0	5.8	3.6	9.6	5.6	3.4	9.1	5.3	3.3	8.6	4.9	3.0
86	TC	46.7	44.8	42.5	45.6	43.7	41.4	44.5	42.6	40.3	43.4	41.5	39.2
	SC	46.1	44.2	42.0	45.1	43.2	40.9	44.0	42.1	39.8	42.9	41.0	38.7
	gpm	11.9	9.1	7.1	11.5	8.8	7.0	11.3	8.6	6.8	11.0	8.4	6.6
	wpd	11.2	6.5	4.1	10.6	6.2	3.9	10.1	5.9	3.7	9.6	5.6	3.4
88	TC	48.9	47.2	45.0	47.8	46.1	43.9	46.7	45.0	42.8	45.6	43.9	41.7
	SC	48.3	46.6	44.5	47.2	45.5	43.4	46.2	44.5	42.3	45.1	43.4	41.2
	gpm	12.4	9.6	7.6	12.0	9.3	7.4	11.8	9.1	7.2	11.5	8.9	7.1
	wpd	12.2	7.2	4.6	11.5	6.9	4.3	11.1	6.6	4.1	10.6	6.3	4.0
90	TC	49.4	49.3	49.0	48.4	48.3	47.9	47.4	47.3	46.9	46.4	46.2	45.9
	SC	54.7	54.6	54.2	53.6	53.4	53.0	52.4	52.3	51.9	51.3	51.2	50.7
	gpm	12.5	10.0	8.3	12.3	9.7	8.1	12.0	9.6	8.0	11.8	9.4	7.7
	wpd	13.8	8.7	6.0	13.3	8.3	5.8	12.7	8.1	5.6	12.2	7.7	5.3

# 1250 CFM - Standard Capacity (63° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	30.5	26.2	21.8	28.6	24.4	20.2	26.8	22.7	18.9	25.1	21.2	17.5
	SC	22.4	20.5	18.4	21.6	19.7	17.7	20.9	18.9	17.0	20.1	18.4	16.1
	gpm	7.7	5.3	3.7	7.3	5.0	3.4	6.8	4.6	3.2	6.3	4.3	2.9
	wdp	8.6	4.0	2.0	7.6	3.6	1.7	6.6	3.0	1.4	5.7	2.6	1.2
76	TC	31.1	27.3	23.6	29.5	25.8	22.3	27.9	24.3	21.0	26.2	23.0	19.9
	SC	24.6	22.9	21.0	23.9	22.1	20.4	23.2	21.6	19.6	22.5	20.8	18.8
	gpm	7.9	5.5	4.0	7.5	5.2	3.8	7.0	4.9	3.6	6.6	4.7	3.4
	wdp	8.9	4.4	2.3	8.1	3.9	2.1	7.1	3.4	1.8	6.3	3.1	1.7
78	TC	32.0	28.7	25.5	30.4	27.2	24.4	28.9	26.0	23.3	27.5	24.8	22.1
	SC	26.9	25.3	23.6	26.2	24.7	22.9	25.6	24.0	22.2	25.0	23.3	21.4
	gpm	8.1	5.8	4.3	7.7	5.5	4.1	7.3	5.3	3.9	6.9	5.0	3.7
	wdp	9.5	4.8	2.7	8.4	4.4	2.4	7.7	4.0	2.2	6.9	3.7	2.0
80	TC	32.9	30.2	27.6	31.4	29.0	26.5	30.1	27.8	25.4	28.9	26.7	23.6
	SC	29.3	27.8	26.1	28.5	27.2	25.5	28.0	26.5	24.6	27.4	25.8	23.3
	gpm	8.4	6.2	4.7	8.0	5.8	4.5	7.7	5.7	4.3	7.3	5.4	4.0
	wdp	10.1	5.4	3.1	9.1	4.9	2.9	8.4	4.6	2.6	7.7	4.3	2.3
82	TC	33.9	31.8	29.5	32.7	30.8	28.6	31.6	29.7	27.0	30.5	28.8	26.0
	SC	31.6	30.3	28.6	30.9	29.6	27.8	30.3	28.9	26.6	29.7	28.2	25.7
	gpm	8.6	6.5	5.0	8.3	6.2	4.8	8.0	6.0	4.6	7.7	5.8	4.4
	wdp	10.6	6.0	3.6	9.9	5.6	3.3	9.1	5.2	3.0	8.6	4.9	2.8
84	TC	35.4	33.7	31.7	34.3	32.8	30.2	33.3	31.5	29.2	32.3	30.5	28.2
	SC	34.0	32.8	31.0	33.3	32.0	29.8	32.6	31.1	28.8	31.8	30.1	27.9
	gpm	9.0	6.9	5.4	8.7	6.6	5.1	8.4	6.4	4.9	8.1	6.2	4.7
	wdp	11.6	6.8	4.1	10.8	6.3	3.8	10.2	5.9	3.4	9.5	5.4	3.2
86	TC	37.1	35.5	33.3	36.1	34.6	32.4	35.2	33.6	31.4	34.2	32.7	30.5
	SC	36.4	35.1	32.9	35.7	34.1	32.0	34.7	33.2	31.0	33.8	32.2	30.1
	gpm	9.4	7.2	5.6	9.2	7.0	5.4	8.9	6.8	5.3	8.7	6.6	5.1
	wdp	12.7	7.4	4.5	12.0	7.1	4.3	11.4	6.6	4.0	10.8	6.3	3.8
88	TC	39.0	37.5	35.5	38.1	36.6	34.6	37.1	35.6	33.6	36.1	34.7	32.6
	SC	38.5	37.0	35.0	37.6	36.1	34.1	36.6	35.2	33.2	35.7	34.2	32.2
	gpm	9.9	7.6	6.0	9.6	7.4	5.8	9.4	7.3	5.7	9.2	7.0	5.5
	wdp	14.0	8.2	5.2	13.3	7.9	4.9	12.7	7.6	4.6	12.0	7.1	4.4
90	TC	41.0	39.5	37.6	40.0	38.5	36.7	39.0	37.5	35.7	38.1	36.6	34.8
	SC	40.4	39.0	37.1	39.5	38.0	36.2	38.6	37.1	35.3	37.6	36.1	34.3
	gpm	10.4	8.0	6.3	10.2	7.8	6.2	9.9	7.6	6.0	9.6	7.4	5.8
	wdp	15.6	9.1	5.7	14.9	8.8	5.4	14.2	8.2	5.2	13.3	7.9	4.9

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	40.6	36.9	33.2	38.4	34.8	31.0	36.2	32.7	29.1	34.0	30.5	27.0
	SC	26.7	25.1	23.5	25.7	24.2	22.5	24.8	23.2	21.7	23.8	22.3	20.8
	gpm	10.3	7.5	5.6	9.7	7.1	5.3	9.1	6.6	4.9	8.6	6.2	4.5
	wdp	9.2	4.9	2.7	8.2	4.3	2.4	7.2	3.8	2.1	6.5	3.3	1.8
76	TC	41.0	37.7	34.4	38.9	35.6	32.4	36.8	33.7	30.5	34.8	31.7	28.8
	SC	28.9	27.4	25.9	27.9	26.5	25.1	27.0	25.6	24.2	26.1	24.8	23.5
	gpm	10.4	7.6	5.8	9.9	7.2	5.5	9.4	6.8	5.2	8.8	6.4	4.9
	wdp	9.3	5.0	2.9	8.4	4.5	2.6	7.6	4.1	2.3	6.7	3.6	2.1
78	TC	41.5	38.5	35.6	39.5	36.7	33.9	37.5	34.8	32.2	35.5	33.0	30.7
	SC	31.0	29.7	28.4	30.1	28.9	27.6	29.2	28.0	26.9	28.4	27.2	26.2
	gpm	10.5	7.8	6.0	10.0	7.4	5.7	9.5	7.1	5.5	9.0	6.7	5.2
	wdp	9.6	5.2	3.2	8.7	4.8	2.8	7.8	4.3	2.6	7.0	3.9	2.3
80	TC	42.1	39.5	36.9	40.2	37.8	35.4	38.3	36.0	34.0	36.5	34.4	32.5
	SC	33.3	32.1	30.9	32.4	31.3	30.2	31.5	30.5	29.5	30.7	29.8	28.8
	gpm	10.7	8.0	6.3	10.2	7.6	6.0	9.7	7.3	5.8	9.2	7.0	5.5
	wdp	9.8	5.5	3.4	8.9	5.0	3.1	8.2	4.6	2.9	7.4	4.2	2.6
82	TC	42.8	40.5	38.6	41.0	38.9	37.1	39.3	37.4	35.7	37.6	36.0	34.4
	SC	35.5	34.5	33.5	34.7	33.7	32.8	33.9	33.1	32.1	33.1	32.4	31.5
	gpm	10.9	8.2	6.6	10.4	7.8	6.3	9.9	7.6	6.0	9.5	7.3	5.8
	wdp	10.2	5.8	3.7	9.3	5.3	3.4	8.6	5.0	3.2	7.8	4.6	2.9
84	TC	43.7	41.8	40.2	42.0	40.4	38.8	40.4	39.0	37.6	38.9	37.7	36.4
	SC	37.8	37.0	36.1	37.0	36.3	35.4	36.3	35.6	34.8	35.7	35.0	34.2
	gpm	11.1	8.5	6.8	10.7	8.2	6.6	10.2	7.9	6.3	9.8	7.6	6.1
	wdp	10.7	6.3	4.0	9.8	5.8	3.7	9.1	5.4	3.5	8.3	5.0	3.2
86	TC	44.6	43.2	41.9	43.1	41.9	40.7	41.7	40.7	39.6	40.4	39.5	35.9
	SC	40.2	39.5	38.8	39.5	38.9	38.1	38.8	38.2	37.5	38.2	37.6	34.2
	gpm	11.3	8.8	7.1	10.9	8.5	6.8	10.6	8.3	6.7	10.2	8.0	6.0
	wdp	11.1	6.7	4.3	10.4	6.3	4.1	9.7	5.9	3.9	9.1	5.5	3.2
88	TC	45.9	44.8	43.8	44.5	43.7	40.2	43.3	40.7	39.2	40.8	39.7	38.2
	SC	42.7	42.1	41.4	42.0	41.5	39.7	41.4	40.1	38.6	40.2	39.6	38.8
	gpm	11.6	9.1	7.4	11.3	8.9	6.8	10.9	8.3	6.6	10.2	8.8	7.4
	wdp	11.6	7.1	4.8	11.1	6.8	4.0	10.4	5.9	3.8	9.2	5.6	3.6
90	TC	47.3	44.7	43.4	44.8	43.8	42.4	43.8	42.8	41.4	42.8	41.8	40.4
	SC	45.3	44.1	42.8	44.1	43.2	41.2	42.2	40.8	39.2	42.2	41.6	40.0
	gpm	12.0	9.1	7.3	11.4	8.9	7.1	11.1	8.7	7.0	10.9	8.5	6.8
	wdp	12.5	7.1	4.7	11.2	6.8	4.4	10.7	6.6	4.2	10.2	6.3	4.1

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	39.2	34.2	29.2	36.9	32.0	27.1	34.6	29.8	25.3	32.3	27.8	23.4
	SC	27.2	25.0	22.8	26.2	24.1	21.9	25.2	23.2	21.0	24.2	22.3	20.2
	gpm	9.9	6.9	4.9	9.3	6.5	4.6</td						

# 1250 CFM - Standard Capacity (65° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	35.4	30.7	25.1	33.3	28.6	23.0	31.2	26.5	21.1	29.2	24.4	18.8
	SC	21.9	20.0	17.7	21.1	19.1	16.8	20.2	18.3	16.0	19.4	17.4	15.1
	gpm	8.9	6.2	4.3	8.4	5.8	3.9	7.9	5.4	3.6	7.4	5.0	3.2
	wpd	11.4	5.6	2.6	10.2	4.8	2.1	8.9	4.1	1.8	7.9	3.6	1.4
76	TC	35.3	31.1	26.3	33.3	29.2	24.3	31.4	27.3	22.6	29.5	25.4	21.1
	SC	23.9	22.1	20.0	23.1	21.3	19.2	22.3	20.6	18.5	21.5	19.8	17.8
	gpm	8.9	6.3	4.4	8.4	5.9	4.1	8.0	5.5	3.8	7.5	5.1	3.6
	wpd	11.4	5.7	2.8	10.2	5.0	2.4	9.1	4.4	2.1	8.1	3.8	1.8
78	TC	35.4	31.9	27.5	33.6	30.1	25.9	31.9	28.3	24.4	30.2	26.6	23.0
	SC	26.0	24.4	22.4	25.2	23.6	21.7	24.5	22.9	21.2	23.8	22.2	20.4
	gpm	8.9	6.5	4.7	8.5	6.1	4.3	8.0	5.8	4.1	7.7	5.4	3.9
	wpd	11.4	6.0	3.1	10.4	5.3	2.7	9.3	4.8	2.4	8.4	4.1	2.1
80	TC	36.0	32.8	29.0	34.3	31.2	27.6	32.7	29.5	26.2	31.1	28.0	25.0
	SC	28.2	26.7	24.9	27.4	26.0	24.3	26.8	25.2	23.6	26.1	24.6	23.0
	gpm	9.1	6.6	4.9	8.7	6.3	4.7	8.3	6.0	4.4	7.9	5.7	4.2
	wpd	11.8	6.3	3.4	10.8	5.7	3.1	9.9	5.2	2.8	8.9	4.6	2.5
82	TC	36.8	34.0	30.6	35.2	32.4	29.4	33.6	31.0	28.1	32.0	29.6	27.0
	SC	30.5	29.1	27.5	29.7	28.4	26.8	29.1	27.8	26.2	28.4	27.1	25.4
	gpm	9.3	6.9	5.2	8.9	6.5	5.0	8.5	6.3	4.7	8.1	6.0	4.6
	wpd	12.5	6.8	3.9	11.4	6.2	3.6	10.4	5.7	3.2	9.5	5.2	3.0
84	TC	37.6	35.1	32.3	36.1	33.7	31.1	34.6	32.5	30.0	33.2	31.2	28.9
	SC	32.8	31.4	29.9	32.0	30.9	29.3	31.3	30.2	28.5	30.8	29.6	27.9
	gpm	9.5	7.1	5.4	9.1	6.8	5.3	8.8	6.5	5.0	8.4	6.3	4.9
	wpd	12.9	7.2	4.3	11.8	6.6	4.0	11.0	6.2	3.7	10.1	5.7	3.4
86	TC	38.5	36.5	34.1	37.1	35.3	33.1	35.8	34.2	32.0	34.6	33.1	31.1
	SC	35.0	33.9	32.4	34.3	33.2	31.7	33.7	32.6	31.1	33.1	32.1	30.3
	gpm	9.8	7.4	5.8	9.4	7.2	5.6	9.1	6.9	5.4	8.8	6.7	5.2
	wpd	13.8	7.9	4.8	12.7	7.4	4.5	11.8	6.9	4.3	11.0	6.5	3.9
88	TC	39.7	38.0	36.0	38.4	36.9	35.1	37.3	35.9	33.7	36.3	35.0	32.7
	SC	37.4	36.3	34.9	36.8	35.6	34.2	36.1	35.0	33.3	35.5	34.2	32.3
	gpm	10.0	7.7	6.1	9.7	7.5	5.9	9.5	7.3	5.7	9.2	7.1	5.5
	wpd	14.4	8.4	5.3	13.5	8.1	5.0	12.9	7.6	4.6	12.2	7.2	4.4
90	TC	41.1	39.7	38.0	40.1	38.7	36.7	39.1	37.6	35.8	38.2	36.7	34.8
	SC	39.8	38.7	37.2	39.2	37.9	36.3	38.4	37.1	35.3	37.7	36.2	34.4
	gpm	10.4	8.0	6.5	10.2	7.8	6.2	9.9	7.6	6.1	9.7	7.4	5.8
	wpd	15.6	9.3	6.0	14.9	8.8	5.6	14.2	8.2	5.3	13.5	7.9	4.9

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	46.7	42.8	38.4	44.4	40.4	35.9	42.1	38.0	33.6	39.7	35.5	31.2
	SC	26.8	25.0	23.1	25.8	24.0	22.1	24.7	23.0	21.1	23.7	21.9	20.1
	gpm	11.8	8.6	6.5	11.2	8.2	6.0	10.7	7.7	5.7	10.0	7.2	5.3
	wpd	12.1	6.5	3.6	10.9	5.8	3.2	9.8	5.1	2.8	8.7	4.5	2.4
76	TC	46.8	43.1	39.0	44.6	40.7	36.7	42.3	38.5	34.5	40.0	36.2	32.3
	SC	28.8	27.1	25.4	27.8	26.1	24.4	26.8	25.1	23.5	25.7	24.1	22.6
	gpm	11.9	8.7	6.6	11.3	8.2	6.2	10.7	7.8	5.8	10.2	7.3	5.5
	wpd	12.2	6.6	3.8	11.1	6.0	3.3	10.0	5.2	2.9	8.9	4.7	2.6
78	TC	46.9	43.5	39.8	44.8	41.3	37.8	42.6	39.2	35.6	40.4	37.0	33.6
	SC	30.8	29.2	27.7	29.8	28.3	26.8	28.8	27.4	25.8	27.9	26.4	25.0
	gpm	11.9	8.8	6.7	11.4	8.4	6.3	10.8	7.9	6.0	10.2	7.5	5.7
	wpd	12.2	6.7	3.9	11.2	6.0	3.5	10.1	5.4	3.1	9.1	4.9	2.8
80	TC	47.2	44.1	40.8	45.1	42.1	38.8	43.1	40.0	36.9	41.0	37.9	34.9
	SC	32.9	31.5	30.0	31.9	30.6	29.2	31.0	29.7	28.3	30.1	28.7	27.5
	gpm	12.0	8.9	6.9	11.4	8.5	6.6	10.9	8.1	6.2	10.4	7.6	5.9
	wpd	12.4	6.9	4.1	11.2	6.3	3.7	10.2	5.6	3.3	9.3	5.0	3.0
82	TC	47.6	44.8	41.9	45.6	42.8	40.0	43.6	40.9	38.1	41.6	39.0	36.3
	SC	35.0	33.7	32.4	34.1	32.8	31.6	33.2	32.0	30.8	32.3	31.2	30.0
	gpm	12.1	9.1	7.1	11.6	8.7	6.8	11.0	8.3	6.4	10.5	7.9	6.1
	wpd	12.7	7.1	4.3	11.6	6.6	4.0	10.5	5.9	3.6	9.6	5.4	3.2
84	TC	48.1	45.5	42.9	46.1	43.7	41.1	44.2	41.9	39.5	42.3	40.1	37.9
	SC	37.1	36.0	34.8	36.2	35.2	34.0	35.4	34.4	33.3	34.5	33.6	32.6
	gpm	12.2	9.2	7.3	11.7	8.9	6.9	11.2	8.5	6.7	10.7	8.1	6.4
	wpd	12.8	7.4	4.6	11.9	6.8	4.1	10.9	6.3	3.9	10.0	5.7	3.6
86	TC	48.6	46.4	44.1	46.7	44.7	42.5	44.9	42.9	41.0	43.1	41.3	39.6
	SC	39.3	38.3	37.3	38.4	37.5	36.6	37.6	35.7	33.9	36.8	35.0	35.2
	gpm	12.2	9.4	7.5	11.8	9.0	7.2	11.4	8.7	6.9	10.9	8.4	6.7
	wpd	13.0	7.6	4.9	12.1	7.0	4.5	11.2	6.6	4.1	10.4	6.0	3.9
88	TC	49.2	47.4	45.4	47.4	45.7	44.0	45.7	44.2	42.6	44.0	42.7	41.3
	SC	41.5	40.7	39.8	40.7	39.9	39.1	39.9	39.2	38.4	39.2	38.1	40.4
	gpm	12.5	9.6	7.6	12.0	9.3	7.4	11.5	8.9	7.2	11.2	8.6	7.0
	wpd	13.4	7.9	5.0	12.5	7.5	4.8	11.5	6.9	4.5	10.8	6.5	4.2
90	TC	49.9	48.5	46.9	48.3	47.0	45.6	46.7	45.5	44.3	45.2	44.2	43.1
	SC	43.8	43.1	42.4	43.0	42.4	41.7	42.3	41.8	41.1	41.6	41.1	40.4
	gpm	12.7	9.9	7.9	12.2	9.5	7.7	11.8	9.2	7.5	11.4	8.9	7.3
	wpd	13.9	8.4	5.4	13.0	7.8	5.1	12.1	7.4	4.9	11.4	6.9	4.6

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	45.6	39.8	33.8	43.1	37.4	31.2	40.5	34.8	28.5	37.9	32.4	26.4
	SC	27.1	24.6	22.1	26.0	23.6	21.0	24.9	22.5	20.0	23.8	21.5	19.1
	gpm	11.5	8.1	5.7	10.9	7.6	5.2						

# 1250 CFM - Standard Capacity (67° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	40.6	36.9	31.1	38.6	34.7	28.5	36.5	32.5	25.9	34.4	30.1	23.6
	SC	21.4	19.9	17.6	20.6	19.0	16.6	19.8	18.2	15.6	19.0	17.3	14.7
	gpm	10.3	7.5	5.2	9.8	7.0	4.8	9.2	6.5	4.3	8.7	6.1	3.9
	wpd	15.1	8.1	3.9	13.8	7.1	3.3	12.2	6.2	2.7	10.8	5.3	2.2
76	TC	40.7	37.0	31.1	38.7	34.7	28.8	36.6	32.4	26.6	34.5	30.1	24.5
	SC	23.5	21.9	19.6	22.6	21.1	18.7	21.8	20.1	17.9	21.0	19.2	17.0
	gpm	10.3	7.5	5.3	9.8	7.0	4.9	9.2	6.5	4.5	8.7	6.1	4.1
	wpd	15.4	8.1	4.0	13.8	7.1	3.4	12.2	6.2	2.9	10.8	5.3	2.4
78	TC	40.6	36.8	31.6	38.6	34.8	29.6	36.5	32.6	27.5	34.4	30.5	25.6
	SC	25.4	23.9	21.8	24.6	23.1	21.0	23.8	22.2	20.2	23.0	21.4	19.4
	gpm	10.3	7.4	5.4	9.8	7.0	5.0	9.2	6.6	4.7	8.7	6.2	4.3
	wpd	15.1	7.9	4.1	13.8	7.1	3.6	12.2	6.3	3.1	10.8	5.4	2.7
80	TC	40.9	37.4	32.6	38.8	35.4	30.8	36.8	33.5	29.0	34.8	31.5	27.0
	SC	27.4	25.9	24.0	26.5	25.2	23.3	25.8	24.4	22.5	25.0	23.6	21.7
	gpm	10.3	7.6	5.5	9.8	7.2	5.2	9.3	6.8	4.9	8.8	6.4	4.6
	wpd	15.4	8.2	4.4	13.8	7.4	3.9	12.5	6.6	3.4	11.2	5.9	3.0
82	TC	40.6	37.5	33.5	38.7	35.8	31.8	36.9	34.1	30.1	35.2	32.2	28.5
	SC	29.4	28.1	26.4	28.7	27.4	25.7	28.0	26.7	24.9	27.3	26.0	24.2
	gpm	10.3	7.6	5.7	9.8	7.3	5.4	9.3	6.9	5.0	8.9	6.5	4.8
	wpd	15.1	8.2	4.6	13.8	7.6	4.1	12.5	6.9	3.7	11.4	6.2	3.3
84	TC	41.0	38.3	34.7	39.3	36.6	33.0	37.6	35.0	31.5	36.0	33.4	30.1
	SC	31.6	30.4	28.7	30.9	29.7	28.0	30.2	29.0	27.4	29.6	28.3	26.8
	gpm	10.4	7.7	5.8	9.9	7.4	5.6	9.5	7.1	5.4	9.2	6.8	5.0
	wpd	15.6	8.6	4.9	14.2	7.9	4.5	13.1	7.2	4.1	12.0	6.6	3.7
86	TC	41.7	39.2	35.9	40.1	37.6	34.4	38.5	36.0	33.1	36.9	34.5	31.8
	SC	33.8	32.7	31.2	33.2	32.0	30.5	32.5	31.3	29.9	31.9	30.7	29.2
	gpm	10.6	7.9	6.1	10.1	7.6	5.8	9.7	7.3	5.6	9.3	7.0	5.4
	wpd	16.1	8.9	5.3	14.7	8.2	4.9	13.5	7.6	4.5	12.5	7.1	4.1
88	TC	42.6	40.1	37.3	41.0	38.5	36.0	39.4	37.2	34.8	37.8	35.8	33.6
	SC	36.2	35.0	33.7	35.5	34.3	33.0	34.8	33.6	32.3	34.1	33.1	31.7
	gpm	10.8	8.1	6.3	10.3	7.8	6.1	9.9	7.5	5.8	9.5	7.3	5.7
	wpd	16.8	9.5	5.7	15.4	8.8	5.3	14.2	8.1	4.9	13.1	7.6	4.6
90	TC	43.5	41.1	38.8	41.9	39.7	37.6	40.4	38.4	36.5	39.0	37.2	35.4
	SC	38.5	37.2	36.0	37.7	36.7	35.5	37.0	36.0	34.8	36.5	35.4	34.0
	gpm	11.0	8.4	6.5	10.6	8.0	6.3	10.3	7.8	6.2	9.9	7.5	6.0
	wpd	17.3	10.1	6.2	16.1	9.3	5.7	15.1	8.8	5.4	14.0	8.1	5.2

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	52.3	47.3	40.7	49.9	44.7	37.9	47.5	41.9	35.0	45.0	39.0	32.0
	SC	26.9	24.8	22.1	25.9	23.7	21.0	24.9	22.6	19.8	23.8	21.4	18.7
	gpm	13.2	9.6	6.9	12.6	9.1	6.4	12.0	8.5	5.9	11.4	7.9	5.4
	wpd	13.9	7.2	3.8	12.7	6.5	3.3	11.5	5.7	2.8	10.3	4.9	2.3
76	TC	52.4	47.3	41.0	49.9	44.6	38.4	47.5	42.0	35.6	45.0	39.2	33.0
	SC	29.1	27.0	24.4	28.1	25.9	23.4	27.1	24.8	22.3	26.0	23.7	21.2
	gpm	13.2	9.6	6.9	12.6	9.1	6.5	12.0	8.5	6.0	11.4	7.9	5.6
	wpd	13.9	7.2	3.8	12.7	6.5	3.3	11.5	5.7	2.8	10.3	4.9	2.5
78	TC	52.3	47.4	41.6	49.9	44.9	39.2	47.4	42.4	36.7	45.0	39.8	34.0
	SC	31.3	29.3	26.9	30.3	28.2	25.9	29.3	27.2	24.9	28.3	26.2	23.8
	gpm	13.2	9.6	7.0	12.6	9.1	6.6	12.0	8.6	6.1	11.4	8.1	5.7
	wpd	13.9	7.4	3.9	12.7	6.6	3.5	11.4	5.8	3.0	10.3	5.2	2.6
80	TC	52.7	48.2	42.9	50.4	45.7	40.4	48.0	43.4	38.2	45.7	41.1	36.0
	SC	33.5	31.6	29.4	32.5	30.6	28.4	31.5	29.6	27.5	30.6	28.7	26.6
	gpm	13.4	9.7	7.2	12.7	9.2	6.8	12.1	8.8	6.5	11.5	8.3	6.1
	wpd	14.2	7.5	4.1	12.8	6.8	3.7	11.7	6.2	3.3	10.6	5.5	2.9
82	TC	52.6	48.5	43.6	50.3	46.1	41.5	48.1	43.9	39.3	45.9	41.6	37.3
	SC	35.9	34.1	32.0	34.9	33.1	31.1	34.0	32.2	30.3	33.0	31.2	29.4
	gpm	13.3	9.8	7.4	12.7	9.3	7.0	12.2	8.9	6.6	11.6	8.4	6.3
	wpd	14.0	7.6	4.3	12.8	6.9	3.9	11.8	6.3	3.5	10.7	5.6	3.2
84	TC	53.0	49.2	44.8	50.8	47.1	42.7	48.6	44.9	40.8	46.6	42.8	38.8
	SC	38.2	36.6	34.7	37.3	35.7	33.8	36.4	34.8	33.0	35.5	33.9	32.2
	gpm	13.4	10.0	7.6	13.0	9.3	7.5	12.5	9.3	7.1	11.8	8.6	6.6
	wpd	14.2	7.9	4.5	13.0	7.2	4.1	12.0	6.5	3.8	11.1	5.9	3.4
86	TC	53.6	50.0	46.1	51.5	48.0	44.2	49.3	45.9	42.3	47.2	44.0	40.4
	SC	40.7	39.1	37.4	39.8	38.2	36.5	38.8	37.4	35.7	37.9	36.5	34.9
	gpm	13.5	10.1	7.8	13.0	9.3	7.5	12.5	9.3	7.1	12.0	8.9	6.8
	wpd	14.9	8.4	5.1	13.9	7.9	4.7	12.8	7.2	4.3	11.7	6.6	4.1
88	TC	54.2	51.0	47.4	52.1	49.0	45.6	50.1	47.2	43.8	48.1	45.2	42.2
	SC	43.1	41.7	40.1	42.2	40.8	39.3	41.3	40.0	38.5	40.5	39.2	37.7
	gpm	13.7	10.3	8.0	13.2	10.0	7.7	12.7	9.6	7.4	12.1	9.1	7.1
	wpd	14.9	8.4	5.1	13.9	7.9	4.7	12.8	7.2	4.3	11.7	6.6	4.1
90	TC	54.8	51.5	48.8	52.9	50.2	47.0	50.9	48.4	45.5	49.1	46.6	44.1
	SC	45.6	44.3	42.8	44.7	43.5	42.0	43.9	42.7	41.2	43.1	41.9	40.6
	gpm	13.9	10.6	8.2	13.4	10.2	8.0	12.9	9.8	7.6	12.5	9.5	7.5
	wpd	15.3	8.8	5.4	14.2	8.3	5.1	13.2	7.6	4.6	12.3	7.1	4.4

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	58.6	55.6	53.5	56.3	54.2	50.9	54.0	51.7	48.3	51.6	49.2	45.6
	SC	33.3	32.3	30.6	32.1	31.0	29.3	30.9	29.7	28.0	29.6	28.4</	

# 1250 CFM - Standard Capacity (69° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	45.7	41.9	37.3	43.7	39.9	35.0	41.6	37.9	32.7	39.5	35.8	30.2
	SC	20.8	19.3	17.5	20.0	18.5	16.7	19.2	17.7	15.8	18.4	16.9	14.9
	gpm	11.6	8.5	6.3	11.0	8.0	5.9	10.6	7.7	5.5	10.0	7.3	5.1
	wpd	19.3	10.4	5.7	17.5	9.3	5.0	16.1	8.4	4.4	14.4	7.6	3.8
76	TC	45.8	42.2	37.7	43.9	40.1	35.3	41.8	38.0	33.0	39.8	36.0	30.4
	SC	22.9	21.4	19.6	22.1	20.6	18.7	21.3	19.8	17.9	20.5	19.0	16.9
	gpm	11.6	8.5	6.4	11.1	8.1	6.0	10.6	7.7	5.6	10.1	7.3	5.1
	wpd	19.3	10.4	5.9	17.8	9.5	5.2	16.1	8.6	4.5	14.7	7.6	3.8
78	TC	46.1	42.4	37.7	44.0	40.3	35.4	42.0	38.2	33.0	40.0	36.0	30.6
	SC	24.9	23.5	21.6	24.1	22.6	20.8	23.3	21.8	19.8	22.5	21.0	18.9
	gpm	11.7	8.6	6.4	11.1	8.1	6.0	10.7	7.7	5.5	10.1	7.3	5.1
	wpd	19.6	10.6	5.9	17.8	9.5	5.2	16.3	8.6	4.4	14.7	7.6	3.8
80	TC	46.2	42.4	37.7	44.1	40.3	35.5	42.0	38.2	33.2	39.9	36.0	31.1
	SC	27.0	25.5	23.6	26.2	24.6	22.8	25.3	23.8	21.9	24.5	23.0	21.1
	gpm	11.7	8.6	6.4	11.1	8.2	6.0	10.6	7.7	5.6	10.1	7.3	5.2
	wpd	19.6	10.6	5.9	17.8	9.7	5.2	16.1	8.6	4.5	14.7	7.6	3.9
82	TC	46.1	42.3	38.0	44.0	40.2	35.9	41.9	38.2	33.9	39.8	36.1	31.9
	SC	29.0	27.4	25.7	28.1	26.6	24.9	27.3	25.8	24.1	26.5	25.1	23.4
	gpm	11.7	8.5	6.4	11.1	8.1	6.1	10.6	7.7	5.7	10.0	7.3	5.4
	wpd	19.6	10.4	5.9	17.8	9.5	5.3	16.1	8.6	4.6	14.4	7.7	4.1
84	TC	46.0	42.4	38.6	43.9	40.4	36.6	41.9	38.6	34.9	39.9	36.7	33.0
	SC	30.9	29.4	27.9	30.1	28.7	27.2	29.3	28.0	26.5	28.5	27.2	25.7
	gpm	11.7	8.6	6.5	11.1	8.2	6.2	10.6	7.8	5.9	10.1	7.4	5.6
	wpd	19.6	10.6	6.0	17.8	9.7	5.4	16.1	8.8	5.0	14.7	7.9	4.5
86	TC	46.0	42.7	39.4	44.1	40.9	37.7	42.2	39.2	35.8	40.3	37.6	34.2
	SC	32.9	31.6	30.2	32.2	30.9	29.5	31.5	30.2	28.8	30.7	29.5	28.1
	gpm	11.7	8.7	6.6	11.2	8.3	6.4	10.7	8.0	6.1	10.3	7.7	5.8
	wpd	19.6	10.8	6.3	18.0	9.9	5.9	16.5	9.1	5.3	15.1	8.4	4.8
88	TC	46.3	43.4	40.3	44.5	41.7	38.8	42.8	40.0	37.1	41.0	38.4	35.4
	SC	35.1	33.8	32.5	34.3	33.1	31.8	33.7	32.5	31.1	32.9	31.8	30.5
	gpm	11.7	8.8	6.8	11.2	8.4	6.5	10.8	8.1	6.3	10.3	7.8	6.0
	wpd	19.6	11.0	6.6	18.0	10.2	6.2	16.8	9.5	5.7	15.4	8.8	5.2
90	TC	46.9	44.2	41.5	45.2	42.6	39.9	43.6	41.0	38.3	42.0	39.4	36.9
	SC	37.3	36.1	34.8	36.6	35.4	34.1	35.9	34.7	33.5	35.2	34.1	33.0
	gpm	11.8	9.0	7.0	11.4	8.7	6.7	11.0	8.3	6.5	10.7	8.0	6.2
	wpd	20.1	11.6	7.1	18.8	10.8	6.5	17.5	9.9	6.0	16.3	9.1	5.6

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	58.9	54.8	48.7	56.4	52.2	45.9	54.0	49.5	43.1	51.6	46.9	40.1
	SC	26.5	24.8	22.3	25.5	23.7	21.2	24.5	22.7	20.1	23.5	21.6	19.0
	gpm	14.9	11.1	8.2	14.3	10.6	7.7	13.6	10.1	7.3	13.0	9.5	6.7
	wpd	17.6	9.8	5.4	16.2	8.8	4.7	14.7	8.0	4.2	13.5	7.1	3.6
76	TC	59.0	54.9	48.8	56.6	52.3	46.1	54.1	49.7	43.1	51.6	46.9	40.2
	SC	28.8	27.1	24.6	27.8	26.0	23.5	26.8	24.9	22.4	25.7	23.8	21.2
	gpm	15.0	11.1	8.2	14.3	10.6	7.8	13.7	10.1	7.3	13.0	9.5	6.8
	wpd	17.8	9.8	5.4	16.2	9.0	4.8	14.9	8.0	4.2	13.5	7.1	3.7
78	TC	59.1	55.0	48.8	56.7	52.4	46.1	54.2	49.7	43.4	51.7	46.9	40.5
	SC	31.1	29.4	26.8	30.0	28.3	25.7	29.0	27.2	24.7	28.0	26.1	23.6
	gpm	15.0	11.1	8.2	14.4	10.6	7.8	13.7	10.1	7.3	13.0	9.5	6.8
	wpd	17.8	9.8	5.4	16.4	9.0	4.8	14.9	8.0	4.2	13.5	7.1	3.7
80	TC	59.2	54.9	49.1	56.7	52.4	46.4	54.2	49.7	43.8	51.7	47.1	41.1
	SC	33.3	31.5	29.1	32.3	30.5	28.1	31.2	29.4	27.1	30.2	28.3	26.0
	gpm	15.0	11.1	8.3	14.4	10.6	7.8	13.7	10.1	7.4	13.0	9.6	6.9
	wpd	17.8	9.8	5.5	16.4	9.0	4.9	14.9	8.0	4.3	13.5	7.2	3.8
82	TC	59.1	55.0	49.5	56.6	52.4	46.9	54.1	49.9	44.5	51.7	47.4	42.1
	SC	35.5	33.8	31.5	34.4	32.7	30.5	33.4	31.7	29.5	32.4	30.7	28.6
	gpm	15.0	11.1	8.3	14.4	10.6	7.9	13.7	10.1	7.5	13.1	9.6	7.1
	wpd	17.8	9.8	5.5	16.4	9.1	5.2	15.1	8.4	4.6	13.7	7.5	4.2
84	TC	59.0	55.3	50.2	56.7	52.9	47.9	54.3	50.5	45.4	51.9	48.1	43.1
	SC	37.7	36.1	34.0	36.7	35.1	33.0	35.7	34.1	32.0	34.7	33.2	31.1
	gpm	14.9	11.2	8.5	14.4	10.7	8.1	13.8	10.2	7.6	13.1	9.7	7.3
	wpd	17.6	10.0	5.7	16.4	9.1	5.2	15.1	8.6	4.9	13.9	7.8	4.4
86	TC	59.1	55.7	50.9	56.9	53.5	48.8	54.6	51.2	46.5	52.3	48.9	44.4
	SC	39.9	38.5	36.5	39.0	37.5	35.6	38.0	36.6	34.7	37.1	35.7	33.8
	gpm	15.0	11.2	8.6	14.4	10.9	8.2	13.8	10.4	7.9	13.2	9.9	7.5
	wpd	17.8	10.0	5.9	16.4	9.4	5.2	15.1	8.6	4.9	13.9	7.8	4.4
88	TC	59.5	56.3	52.0	57.3	54.1	49.8	55.1	51.9	47.7	53.0	49.7	45.6
	SC	42.3	40.9	39.0	41.4	40.0	38.2	40.4	39.1	37.3	39.5	38.1	36.5
	gpm	15.0	11.4	8.7	14.5	11.0	8.4	14.0	10.5	8.1	13.4	10.1	7.7
	wpd	18.0	10.3	6.0	16.8	9.6	5.6	15.5	8.7	5.2	14.2	8.0	4.7
90	TC	60.1	57.1	53.0	57.9	55.0	51.0	55.8	52.8	49.0	53.6	50.7	47.1
	SC	44.7	43.4	41.6	46.8	42.6	40.3	48.9	46.0	43.0	42.0	40.7	39.2
	gpm	15.2	11.5	9.0	14.7	11.1	8.6	14.1	10.7	8.3	13.5	10.3	8.0
	wpd	18.4	10.6	6.4	17.2	9.8	5.9	15.8	9.1	5.5	14.6	8.4	5.1

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	65.4	63.5	60.9	63.1	61.1	58.4	60.8	58.7	55.8	58.4	56.2	53.1
	SC	33.3	32.3	30.9	32.1	30.9	26.3	30.8	29.8	28.3	29		

# 1250 CFM - Standard Capacity (71° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	51.1	47.4	43.5	49.2	45.3	41.4	47.1	43.2	39.1	45.0	41.0	36.7
	SC	20.2	18.7	17.2	19.4	17.9	16.4	18.6	17.1	15.6	17.8	16.3	14.7
	gpm	12.9	9.6	7.3	12.5	9.2	6.9	11.9	8.8	6.6	11.4	8.3	6.2
	wpd	24.1	13.3	7.7	22.3	12.0	6.9	20.4	11.0	6.3	18.6	9.9	5.4
76	TC	51.2	47.5	43.6	49.2	45.4	41.6	47.2	43.4	39.4	45.1	41.2	37.0
	SC	22.2	20.8	19.3	21.4	20.0	18.5	20.6	19.2	17.7	19.8	18.4	16.8
	gpm	12.9	9.6	7.3	12.4	9.2	7.0	12.0	8.8	6.6	11.4	8.4	6.2
	wpd	24.1	13.3	7.7	22.1	12.2	7.1	20.7	11.0	6.3	18.8	10.1	5.6
78	TC	51.4	47.7	43.9	49.4	45.6	41.8	47.3	43.6	39.6	45.3	41.4	37.3
	SC	24.3	22.8	21.4	23.5	22.1	20.6	22.7	21.3	19.8	21.9	20.5	18.9
	gpm	13.0	9.6	7.4	12.5	9.2	7.1	11.9	8.8	6.7	11.5	8.4	6.3
	wpd	24.4	13.3	7.9	22.3	12.2	7.2	20.4	11.2	6.5	19.1	10.1	5.7
80	TC	51.7	47.9	44.1	49.6	45.8	42.0	47.6	43.8	39.8	45.5	41.6	37.3
	SC	26.4	24.9	23.4	25.6	24.1	22.6	24.8	23.3	21.8	24.0	22.5	20.9
	gpm	13.1	9.7	7.4	12.5	9.2	7.1	12.0	8.8	6.7	11.4	8.4	6.3
	wpd	24.7	13.5	7.9	22.6	12.2	7.2	20.7	11.2	6.5	18.8	10.2	5.7
82	TC	51.9	48.1	44.2	49.8	45.9	42.0	47.7	43.8	39.8	45.6	41.7	37.4
	SC	28.5	27.0	25.5	27.7	26.1	24.6	26.8	25.3	23.8	26.0	24.5	22.9
	gpm	13.1	9.7	7.5	12.6	9.3	7.1	12.1	8.8	6.7	11.5	8.4	6.3
	wpd	24.7	13.5	8.1	22.9	12.5	7.2	20.9	11.2	6.5	19.1	10.2	5.7
84	TC	52.0	48.1	44.1	49.9	45.9	42.0	47.7	43.8	39.9	45.6	41.5	37.6
	SC	30.5	29.0	27.4	29.7	28.1	26.6	28.9	27.3	25.8	28.0	26.5	25.1
	gpm	13.2	9.7	7.4	12.6	9.3	7.1	12.1	8.8	6.7	11.5	8.4	6.3
	wpd	25.0	13.5	7.9	22.9	12.5	7.2	20.9	11.2	6.5	19.1	10.2	5.7
86	TC	51.9	48.0	44.2	49.8	45.8	42.1	47.6	43.7	40.2	45.5	41.7	38.3
	SC	32.5	30.9	29.4	31.7	30.1	28.7	30.8	29.3	28.0	30.0	28.5	27.2
	gpm	13.2	9.7	7.5	12.6	9.3	7.1	12.1	8.8	6.8	11.5	8.4	6.5
	wpd	25.0	13.5	8.1	22.9	12.5	7.2	20.9	11.2	6.6	19.1	10.2	6.0
88	TC	51.8	47.9	44.5	49.7	45.9	42.7	47.5	43.9	40.8	45.5	42.1	39.1
	SC	34.5	32.9	31.6	33.6	32.1	30.9	32.8	31.4	30.2	32.0	30.7	29.5
	gpm	13.1	9.7	7.5	12.5	9.3	7.3	12.1	8.9	6.9	11.5	8.5	6.6
	wpd	24.7	13.5	8.1	22.6	12.5	7.6	20.9	11.4	6.8	19.1	10.4	6.3
90	TC	51.6	48.2	45.1	49.7	46.3	43.4	47.7	44.4	41.7	45.7	42.7	39.9
	SC	36.4	35.0	33.8	35.6	34.3	33.1	34.9	33.6	32.4	34.1	32.9	31.8
	gpm	13.0	9.8	7.6	12.6	9.4	7.3	12.1	9.0	7.0	11.5	8.7	6.7
	wpd	24.4	13.8	8.2	22.9	12.7	7.7	20.9	11.6	7.1	19.1	10.8	6.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	65.9	62.0	56.7	63.4	59.5	53.9	60.9	57.0	51.2	58.4	54.4	48.3
	SC	26.2	24.6	22.4	25.1	23.5	21.3	24.1	22.5	20.3	23.1	21.5	19.2
	gpm	16.7	12.5	9.6	16.0	12.0	9.1	15.4	11.5	8.6	14.8	11.1	8.1
	wpd	22.1	12.5	7.2	20.4	11.5	6.5	18.8	10.6	5.9	17.4	9.7	5.3
76	TC	65.9	62.1	56.8	63.5	59.6	54.1	61.0	57.0	51.4	58.5	54.5	48.5
	SC	28.4	26.8	24.7	27.4	25.8	23.6	26.4	24.8	22.6	25.4	23.8	21.5
	gpm	16.7	12.5	9.6	16.0	12.0	9.1	15.5	11.5	8.7	14.8	11.1	8.2
	wpd	22.1	12.5	7.2	20.4	11.5	6.6	19.0	10.6	6.0	17.4	9.7	5.4
78	TC	66.0	62.2	57.0	63.6	59.7	54.3	61.1	57.2	51.5	58.6	54.7	48.7
	SC	30.7	29.1	27.0	29.7	28.1	25.9	28.6	27.1	24.8	27.6	26.1	23.8
	gpm	16.7	12.6	9.6	16.1	12.1	9.1	15.5	11.5	8.6	14.8	11.1	8.2
	wpd	22.1	12.7	7.4	20.6	11.7	6.6	19.2	10.6	6.0	17.6	9.7	5.4
80	TC	66.1	62.3	57.1	63.7	59.8	54.4	61.2	57.3	51.5	58.7	54.7	48.6
	SC	33.0	31.4	29.3	31.9	30.4	28.2	30.9	29.3	27.1	29.9	28.3	26.0
	gpm	16.8	12.6	9.6	16.1	12.1	9.1	15.5	11.5	8.7	14.9	11.1	8.2
	wpd	22.4	12.7	7.4	20.6	11.7	6.6	19.2	10.6	6.0	17.6	9.7	5.4
82	TC	66.2	62.3	57.0	63.8	59.8	54.3	61.3	57.3	51.7	58.7	54.6	48.9
	SC	35.2	33.6	31.5	34.2	32.6	30.4	33.2	31.5	29.3	32.1	30.5	28.3
	gpm	16.8	12.6	9.6	16.1	12.1	9.1	15.5	11.6	8.7	14.9	11.1	8.2
	wpd	22.4	12.7	7.4	20.6	11.7	6.6	19.2	10.7	6.0	17.6	9.7	5.4
84	TC	66.2	62.3	57.2	63.7	59.8	54.5	61.2	57.2	51.9	58.7	54.7	49.3
	SC	37.4	35.8	33.7	36.4	34.8	32.7	35.4	33.8	31.7	34.3	32.7	30.6
	gpm	16.8	12.6	9.6	16.1	12.0	9.3	15.4	11.6	8.7	14.9	11.1	8.3
	wpd	22.4	12.7	7.4	20.6	11.7	6.8	19.2	10.7	6.0	17.6	9.7	5.5
86	TC	66.1	62.2	57.4	63.7	59.8	55.0	61.0	57.3	52.4	58.6	54.9	50.0
	SC	39.6	38.0	36.0	38.6	37.0	35.0	37.5	36.0	34.1	36.5	35.1	33.1
	gpm	16.7	12.6	9.7	16.1	12.0	9.3	15.4	11.5	8.9	14.9	11.1	8.5
	wpd	22.1	12.7	7.5	20.6	11.5	6.9	18.8	10.6	6.3	17.6	9.8	5.7
88	TC	66.0	62.4	57.8	63.6	59.0	55.5	61.1	57.7	53.2	58.7	55.3	50.8
	SC	41.8	40.3	38.4	40.8	39.3	37.5	39.7	38.3	36.6	38.8	37.4	35.6
	gpm	16.7	12.6	9.7	16.0	12.1	9.4	15.5	11.7	9.0	14.9	11.2	8.6
	wpd	22.1	12.7	7.5	20.4	11.7	7.0	19.0	10.9	6.4	17.6	10.0	5.8
90	TC	66.1	62.7	58.6	63.7	60.4	56.2	61.4	58.2	54.0	59.1	56.0	51.8
	SC	44.0	42.6	40.9	43.0	41.7	39.9	42.1	40.7	39.0	41.1	39.8	38.1
	gpm	16.7	12.7	9.9	16.1	12.2	9.5	15.5	11.8	9.1	15.0	11.3	8.7
	wpd	22.1	12.8	7.8	20.6	11.8	7.1	19.2	11.1	6.6	17.8	10.1	6.0

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	72.3	70.4	68.3	70.1	68.1	65.9	67.7	65.7	63.4	65.4	63.2	60.8
	SC	33.2	32.2	31.1									

# 1250 CFM - Standard Capacity (73° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	57.2	53.3	49.4	55.1	51.2	47.3	53.0	49.1	45.1	50.9	46.9	42.9
	SC	19.4	18.0	16.5	18.6	17.2	15.7	17.8	16.4	15.0	17.1	15.6	14.2
	gpm	14.4	10.8	8.4	13.9	10.3	8.0	13.3	9.9	7.6	12.9	9.5	7.3
	wpd	30.0	16.8	10.1	27.7	15.4	9.1	25.6	14.2	8.2	24.1	13.1	7.6
76	TC	57.1	53.2	49.4	55.1	51.1	47.2	53.0	49.1	45.0	50.9	46.9	42.9
	SC	21.6	20.1	18.7	20.8	19.3	17.9	20.0	18.6	17.1	19.2	17.8	16.3
	gpm	14.4	10.8	8.4	13.9	10.3	8.0	13.3	9.9	7.6	12.9	9.5	7.3
	wpd	30.0	16.8	10.1	27.7	15.4	9.1	25.6	14.2	8.2	24.1	12.9	7.6
78	TC	57.1	53.2	49.4	55.0	51.1	47.3	52.9	49.0	45.1	50.8	47.0	43.0
	SC	23.6	22.2	20.7	22.8	21.4	19.9	22.0	20.6	19.2	21.2	19.8	18.4
	gpm	14.4	10.8	8.3	13.9	10.3	8.0	13.4	9.9	7.7	12.9	9.5	7.3
	wpd	30.0	16.8	9.9	27.7	15.4	9.1	25.9	14.2	8.4	23.8	13.1	7.6
80	TC	57.3	53.5	49.6	55.2	51.4	47.5	53.2	49.3	45.4	51.0	47.2	43.2
	SC	25.7	24.3	22.8	24.9	23.5	22.0	24.1	22.7	21.3	23.3	21.9	20.5
	gpm	14.5	10.8	8.4	14.0	10.4	8.0	13.4	9.9	7.7	12.9	9.5	7.3
	wpd	30.3	16.8	10.1	28.0	15.6	9.3	25.9	14.2	8.4	23.8	13.1	7.6
82	TC	57.5	53.7	49.8	55.4	51.6	47.7	53.3	49.4	45.6	51.2	47.3	43.4
	SC	27.8	26.3	24.9	27.0	25.5	24.1	26.2	24.7	23.3	25.4	24.0	22.5
	gpm	14.5	10.9	8.4	14.0	10.4	8.0	13.5	10.0	7.7	12.9	9.5	7.3
	wpd	30.3	17.0	10.1	28.3	15.6	9.3	26.2	14.4	8.6	24.1	13.1	7.7
84	TC	57.7	53.9	50.0	55.6	51.8	47.8	53.5	49.6	45.6	51.4	47.5	43.5
	SC	29.9	28.4	26.9	29.1	27.6	26.1	28.3	26.8	25.3	27.5	26.0	24.5
	gpm	14.6	10.9	8.4	14.1	10.5	8.0	13.6	10.0	7.7	13.0	9.6	7.3
	wpd	30.6	17.0	10.2	28.7	15.8	9.3	26.5	14.4	8.4	24.4	13.3	7.7
86	TC	57.9	54.0	50.0	55.8	51.9	47.9	53.7	49.7	45.6	51.5	47.5	43.4
	SC	32.0	30.4	28.9	31.1	29.6	28.1	30.3	28.8	27.3	29.5	28.0	26.5
	gpm	14.7	11.0	8.4	14.1	10.5	8.0	13.6	10.1	7.7	13.0	9.6	7.3
	wpd	31.0	17.3	10.2	28.7	15.8	9.3	26.5	14.7	8.6	24.4	13.3	7.7
88	TC	57.9	54.0	50.0	55.8	51.8	47.8	53.7	49.7	45.6	51.5	47.4	43.6
	SC	34.0	32.4	30.9	33.2	31.6	30.1	32.3	30.8	29.3	31.5	30.0	28.6
	gpm	14.7	11.0	8.4	14.1	10.5	8.0	13.6	10.1	7.7	13.0	9.6	7.3
	wpd	31.0	17.3	10.2	28.7	15.8	9.3	26.5	14.7	8.6	24.4	13.3	7.7
90	TC	57.9	53.8	49.9	55.7	51.7	47.9	53.6	49.4	45.8	51.4	47.4	43.9
	SC	36.0	34.4	32.9	35.1	33.6	32.1	34.3	32.8	31.4	33.5	32.0	30.7
	gpm	14.7	10.9	8.4	14.1	10.5	8.0	13.6	10.0	7.7	13.0	9.5	7.4
	wpd	31.0	17.0	10.2	28.7	15.8	9.3	26.5	14.4	8.6	24.4	13.1	7.9

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	73.4	69.5	65.1	70.9	66.9	62.5	68.4	64.4	59.8	65.9	61.8	56.9
	SC	25.8	24.2	22.4	24.8	23.2	21.4	23.8	22.1	20.3	22.7	21.1	19.3
	gpm	18.6	14.0	11.0	17.9	13.5	10.6	17.3	13.0	10.1	16.7	12.5	9.6
	wpd	27.5	15.7	9.6	25.6	14.6	8.8	23.7	13.5	8.0	22.1	12.3	7.2
76	TC	73.3	69.4	65.0	70.8	66.9	62.4	68.3	64.3	59.7	65.8	61.7	56.9
	SC	28.1	26.4	24.7	27.0	23.7	20.9	28.2	26.6	22.6	25.0	23.4	21.5
	gpm	18.6	14.0	11.0	17.9	13.5	10.6	17.3	13.0	10.1	16.6	12.5	9.6
	wpd	27.5	15.7	9.6	25.6	14.6	8.8	23.7	13.5	8.2	22.1	12.3	7.2
78	TC	73.2	69.4	65.1	70.9	66.9	62.4	68.3	64.3	59.8	65.8	61.7	57.0
	SC	30.3	28.7	27.0	29.3	27.7	25.9	28.2	26.7	24.9	27.2	25.6	23.8
	gpm	18.5	14.0	11.0	17.9	13.5	10.6	17.3	13.0	10.1	16.7	12.5	9.6
	wpd	27.3	15.7	9.6	25.6	14.6	8.8	23.7	13.5	8.2	22.1	12.5	7.4
80	TC	73.3	69.5	65.2	70.9	67.0	62.6	68.4	64.5	60.0	65.9	61.9	57.2
	SC	32.6	31.0	29.3	31.5	30.0	28.2	30.5	28.9	27.2	29.5	27.9	26.1
	gpm	18.6	14.1	11.1	18.0	13.6	10.6	17.4	13.0	10.1	16.7	12.5	9.6
	wpd	27.5	15.8	9.7	25.8	14.7	8.8	23.9	13.5	8.2	22.1	12.5	7.4
82	TC	73.4	69.5	65.3	71.0	67.1	62.7	68.5	64.5	59.9	66.0	61.9	57.2
	SC	34.8	33.2	31.5	33.8	32.2	30.5	32.8	31.2	29.4	31.8	30.2	28.4
	gpm	18.6	14.0	11.1	18.0	13.6	10.6	17.4	13.0	10.1	16.7	12.5	9.6
	wpd	27.3	15.7	9.7	25.8	14.6	8.8	23.9	13.5	8.2	22.1	12.5	7.4
84	TC	73.4	69.6	65.4	71.1	67.1	62.7	68.6	64.6	60.0	66.1	62.0	57.1
	SC	37.1	35.5	33.8	36.1	34.4	32.7	35.0	33.5	31.7	34.0	32.4	30.6
	gpm	18.5	14.0	11.1	18.0	13.5	10.6	17.4	13.1	10.1	16.7	12.5	9.6
	wpd	27.3	15.7	9.7	25.8	14.6	8.8	23.9	13.5	8.2	22.1	12.5	7.4
86	TC	73.5	69.6	65.4	71.0	67.0	62.8	68.5	64.4	60.1	66.0	61.9	57.6
	SC	39.3	37.7	36.0	38.3	36.7	34.9	37.3	35.6	33.9	36.2	34.6	32.8
	gpm	18.5	14.1	11.1	18.0	13.6	10.6	17.4	13.0	10.1	16.8	12.5	9.6
	wpd	27.3	15.8	9.7	25.6	14.6	8.9	23.7	13.5	8.2	22.1	12.5	7.5
88	TC	73.5	69.6	65.5	70.9	67.1	63.0	68.4	64.6	60.5	65.8	62.0	57.9
	SC	41.5	39.9	38.2	40.5	38.9	37.2	39.4	37.8	36.2	38.4	36.8	35.2
	gpm	18.6	14.1	11.1	17.9	13.5	10.6	17.3	13.0	10.1	16.7	12.5	9.7
	wpd	27.5	15.8	9.7	25.6	14.6	8.9	23.7	13.5	8.2	22.1	12.5	7.5
90	TC	73.4	69.5	65.5	70.9	67.1	63.0	68.4	64.6	60.5	65.8	62.0	57.9
	SC	43.7	42.1	40.5	42.7	41.1	39.5	41.6	40.1	38.5	40.6	39.1	37.5
	gpm	18.5	14.1	11.1	17.9	13.6	10.6	17.3	13.0	10.2	16.6	12.5	9.8
	wpd	27.3	15.8	9.7	25.6	14.7	8.9	23.7	13.5	8.3	21.9	12.5	7.6

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	79.6	77.7	75.6	77.4	75.							

# 1250 CFM - Standard Capacity (75° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	63.4	59.5	55.5	61.3	57.3	53.3	59.2	55.2	51.2	57.1	53.0	48.9
	SC	20.8	19.3	17.9	20.0	18.5	17.1	19.2	17.8	16.4	18.4	17.0	15.6
	gpm	16.1	12.1	9.4	15.5	11.6	9.0	15.0	11.1	8.7	14.4	10.7	8.3
	wpd	37.2	20.9	12.7	34.7	19.3	11.6	32.3	17.8	10.8	30.0	16.5	9.9
78	TC	63.4	59.4	55.4	61.3	57.3	53.3	59.2	55.1	51.1	57.0	52.9	48.9
	SC	22.9	21.5	20.0	22.2	20.7	19.3	21.4	19.9	18.5	20.6	19.1	17.7
	gpm	16.0	12.1	9.4	15.5	11.6	9.0	15.0	11.1	8.6	14.4	10.7	8.3
	wpd	36.9	20.9	12.7	34.7	19.3	11.6	32.3	17.8	10.6	30.0	16.5	9.9
80	TC	63.3	59.4	55.4	61.2	57.3	53.2	59.1	55.1	51.1	57.0	52.9	48.9
	SC	25.1	23.6	22.1	24.3	22.8	21.3	23.5	22.0	20.5	22.7	21.2	19.8
	gpm	16.0	12.1	9.4	15.5	11.6	9.0	15.0	11.1	8.6	14.4	10.7	8.3
	wpd	36.9	20.9	12.7	34.4	19.3	11.6	32.3	17.8	10.6	30.0	16.5	9.9
82	TC	63.4	59.5	55.6	61.3	57.4	53.4	59.2	55.3	51.3	57.1	53.1	49.1
	SC	27.1	25.6	24.2	26.3	24.9	23.4	25.5	24.1	22.6	24.7	23.3	21.9
	gpm	16.1	12.1	9.4	15.5	11.6	9.0	15.0	11.2	8.7	14.4	10.7	8.3
	wpd	37.2	20.9	12.7	34.7	19.3	11.6	32.3	18.0	10.8	30.0	16.5	9.9
84	TC	63.6	59.7	55.8	61.5	57.6	53.7	59.4	55.5	51.5	57.3	53.3	49.3
	SC	29.2	27.7	26.3	28.4	26.9	25.5	27.6	26.2	24.7	26.8	25.4	23.9
	gpm	16.1	12.1	9.5	15.6	11.7	9.1	15.1	11.2	8.7	14.5	10.8	8.3
	wpd	37.2	20.9	12.9	35.1	19.6	11.8	32.6	18.0	10.8	30.3	16.8	9.9
86	TC	63.8	59.9	56.0	61.7	57.8	53.8	59.6	55.6	51.6	57.4	53.5	49.4
	SC	31.3	29.8	28.3	30.5	29.0	27.6	29.7	28.2	26.8	28.9	27.4	26.0
	gpm	16.2	12.1	9.5	15.6	11.7	9.1	15.1	11.3	8.8	14.5	10.8	8.4
	wpd	37.6	21.2	12.9	35.1	19.6	11.8	32.6	18.3	11.0	30.3	16.8	10.1
88	TC	64.0	60.1	56.0	61.9	57.9	53.9	59.8	55.8	51.7	57.6	53.6	49.5
	SC	33.3	31.9	30.4	32.6	31.1	29.6	31.8	30.3	28.8	31.0	29.5	28.0
	gpm	16.2	12.1	9.5	15.7	11.8	9.2	15.1	11.3	8.8	14.6	10.9	8.4
	wpd	37.6	21.2	12.9	35.4	19.9	12.0	33.0	18.3	11.0	30.6	17.0	10.1
90	TC	64.1	60.1	56.1	62.0	58.0	53.9	59.9	55.8	51.7	57.7	53.6	49.4
	SC	35.4	33.9	32.4	34.6	33.1	31.6	33.8	32.3	30.8	33.0	31.5	30.0
	gpm	16.3	12.1	9.5	15.7	11.8	9.1	15.1	11.4	8.8	14.6	10.9	8.4
	wpd	38.0	21.2	12.9	35.4	19.9	11.8	33.0	18.6	11.0	30.6	17.0	10.1

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	80.6	77.8	74.8	78.4	75.5	72.5	76.1	73.1	70.0	73.7	70.7	67.5
	SC	28.4	27.2	25.9	27.4	26.2	24.9	26.4	25.1	23.9	25.4	24.1	22.8
	gpm	20.4	15.8	12.6	19.9	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.2	21.5	13.8	34.2	20.4	13.0	32.0	19.1	12.1	30.1	17.8	11.2
78	TC	80.6	77.8	74.8	78.3	75.4	72.4	76.0	73.1	70.0	73.6	70.6	67.5
	SC	30.4	29.2	27.9	29.4	28.1	26.9	28.3	27.1	25.8	27.3	26.1	24.8
	gpm	20.4	15.8	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.2	21.5	13.8	34.0	20.4	13.0	32.0	19.1	12.1	30.1	17.8	11.2
80	TC	80.5	77.7	74.7	78.2	75.4	72.3	75.9	73.0	69.9	73.6	70.6	67.4
	SC	32.3	31.1	29.8	31.3	30.1	28.8	30.3	29.1	27.8	29.3	28.1	26.8
	gpm	20.4	15.8	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.0	21.5	13.8	34.0	20.2	12.8	32.0	19.1	12.1	30.1	17.8	11.2
82	TC	80.5	77.7	74.7	78.2	75.4	72.3	75.9	73.0	69.9	73.6	70.6	67.5
	SC	34.3	33.1	31.8	33.3	32.1	30.8	32.3	31.1	29.8	31.3	30.0	28.8
	gpm	20.4	15.8	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.0	21.5	13.8	34.0	20.2	12.8	32.0	19.1	12.1	30.1	17.8	11.2
84	TC	80.5	77.7	74.7	78.2	75.4	72.4	75.9	73.1	69.9	73.6	70.6	67.5
	SC	36.3	35.1	33.8	35.3	34.1	32.8	34.3	33.0	31.7	33.2	30.7	28.7
	gpm	20.4	15.7	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.0	21.3	13.8	34.0	20.4	13.0	32.0	19.1	12.1	30.1	17.8	11.2
86	TC	80.5	77.7	74.7	78.3	75.4	72.4	75.9	73.1	69.9	73.6	70.6	67.4
	SC	38.3	37.0	35.8	37.2	36.0	34.7	36.2	35.0	33.7	35.2	33.0	32.7
	gpm	20.4	15.7	12.6	19.9	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.2	21.3	13.8	34.2	20.2	13.0	32.0	18.9	12.1	30.1	17.8	11.2
88	TC	80.5	77.7	74.7	78.3	75.4	72.4	75.9	73.0	69.9	73.6	70.6	67.4
	SC	40.2	39.0	37.7	39.2	37.9	36.7	38.2	36.9	35.6	37.2	35.0	34.0
	gpm	20.4	15.7	12.6	19.9	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.2	21.3	13.8	34.2	20.2	13.0	32.0	18.9	12.1	30.1	17.8	11.2
90	TC	80.5	77.7	74.7	78.2	75.3	72.3	75.9	72.9	69.9	73.5	70.5	67.4
	SC	42.1	40.9	39.6	41.1	39.9	38.6	40.1	38.8	37.6	39.1	37.8	36.6
	gpm	20.4	15.7	12.6	19.9	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.2	21.3	13.8	34.2	20.2	13.0	32.0	18.9	12.1	30.1	17.8	11.2

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	81.1	77.1	73.1	78.6	74.6	70.5	76.1	72.1	67.9	73.6	69.4	65.2
	SC	27.7	26.3	24.7	28.9								

# 1500 CFM - Standard Capacity (61° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	33.0	29.7	26.4	31.2	28.1	25.1	29.5	26.6	23.7	27.9	25.2	22.4
	SC	28.0	26.4	24.4	27.1	25.5	23.4	26.3	24.7	22.6	25.6	23.8	21.6
	gpm	8.4	6.0	4.5	7.9	5.7	4.3	7.4	5.4	4.0	7.1	5.1	3.8
	wpd	11.5	5.8	3.3	10.2	5.2	3.0	9.1	4.7	2.7	8.1	4.3	2.4
76	TC	34.2	31.6	28.8	32.5	30.2	27.5	31.1	28.9	26.3	29.8	27.6	24.1
	SC	30.7	29.2	27.3	30.0	28.5	26.5	29.1	27.6	25.5	28.4	26.8	23.8
	gpm	8.7	6.4	4.9	8.2	6.1	4.7	7.8	5.9	4.4	7.5	5.6	4.0
	wpd	12.3	6.8	3.9	11.1	6.1	3.5	10.0	5.7	3.2	9.3	5.1	2.7
78	TC	35.7	33.7	31.3	34.3	32.4	30.1	33.0	31.3	28.1	31.8	29.6	26.9
	SC	33.5	32.2	30.3	32.8	31.4	29.3	32.1	30.5	27.7	31.1	29.2	26.5
	gpm	9.0	6.8	5.3	8.7	6.6	5.1	8.4	6.4	4.7	8.1	6.0	4.5
	wpd	13.2	7.6	4.5	12.3	7.1	4.3	11.5	6.6	3.7	10.6	5.8	3.3
80	TC	37.5	36.0	33.1	36.4	34.4	31.9	35.0	33.3	30.8	33.9	32.1	29.6
	SC	36.3	35.1	32.7	35.5	34.0	31.5	34.6	32.8	30.4	33.4	31.7	29.2
	gpm	9.5	7.3	5.6	9.2	7.0	5.4	8.8	6.7	5.2	8.6	6.5	5.0
	wpd	14.9	8.7	5.1	13.9	8.0	4.7	12.8	7.4	4.4	12.1	6.9	4.2
82	TC	39.6	37.9	35.7	38.5	36.8	34.6	37.3	35.6	33.4	36.2	34.5	32.2
	SC	39.1	37.4	35.2	38.0	36.3	34.1	36.8	35.2	33.0	35.7	34.1	31.8
	gpm	10.0	7.7	6.0	9.8	7.4	5.8	9.5	7.2	5.7	9.1	7.0	5.4
	wpd	16.4	9.6	6.0	15.6	9.1	5.5	14.6	8.5	5.2	13.7	8.0	4.8
84	TC	41.9	40.2	38.3	40.8	39.1	37.1	39.6	38.0	36.0	38.5	36.8	34.8
	SC	41.4	39.7	37.8	40.2	38.6	36.6	39.1	37.5	35.5	38.0	36.3	34.4
	gpm	10.6	8.1	6.4	10.3	7.9	6.3	10.1	7.7	6.0	9.8	7.4	5.9
	wpd	18.5	10.8	6.8	17.4	10.2	6.5	16.6	9.6	6.0	15.6	9.1	5.7
86	TC	44.2	42.5	40.7	43.0	41.4	39.6	41.9	40.2	38.5	40.8	39.1	37.4
	SC	43.6	42.0	40.2	42.5	40.8	39.1	41.4	39.7	38.0	40.3	38.6	36.9
	gpm	11.2	8.6	6.9	10.9	8.4	6.7	10.6	8.1	6.5	10.3	7.9	6.3
	wpd	20.4	12.1	7.8	19.6	11.5	7.3	18.5	10.8	6.9	17.4	10.2	6.5
88	TC	46.5	44.8	43.1	45.3	43.7	42.0	44.2	42.5	40.9	43.1	41.4	39.7
	SC	45.9	44.2	42.6	44.8	43.1	41.5	43.6	42.0	40.3	42.5	40.9	39.2
	gpm	11.8	9.1	7.3	11.5	8.8	7.1	11.2	8.6	6.9	10.9	8.4	6.7
	wpd	22.7	13.5	8.7	21.6	12.8	8.3	20.7	12.1	7.8	19.6	11.5	7.4
90	TC	48.7	47.1	45.5	47.6	46.0	44.3	46.5	44.8	43.2	45.4	43.7	42.1
	SC	48.1	46.5	44.9	47.0	45.4	43.7	45.9	44.3	42.6	44.8	43.1	41.5
	gpm	12.3	9.5	7.7	12.0	9.3	7.5	11.8	9.1	7.3	11.5	8.8	7.1
	wpd	24.9	14.9	9.6	23.6	14.2	9.3	22.7	13.5	8.7	21.6	12.8	8.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	42.3	38.2	34.2	39.9	35.9	32.2	37.6	33.9	30.7	35.3	32.0	25.5
	SC	33.6	31.7	29.7	32.5	30.6	28.7	31.5	29.7	27.9	30.5	28.8	25.2
	gpm	10.7	7.7	5.8	10.1	7.2	5.5	9.5	6.8	5.2	9.0	6.5	4.3
	wpd	10.4	5.5	3.1	9.3	4.8	2.7	8.3	4.3	2.5	7.4	3.9	1.7
76	TC	43.5	39.9	36.6	41.3	38.0	35.1	39.1	36.2	30.5	37.1	34.6	29.0
	SC	36.7	34.9	33.2	35.7	34.0	32.3	34.7	33.1	30.2	33.7	32.3	28.7
	gpm	11.0	8.1	6.2	10.4	7.7	5.9	9.9	7.3	5.1	9.4	7.0	4.9
	wpd	11.1	6.0	3.5	10.0	5.5	3.2	9.0	4.9	2.4	8.2	4.5	2.2
78	TC	44.8	41.9	39.3	42.7	40.3	35.3	40.9	38.7	33.9	39.3	36.5	32.4
	SC	39.8	38.3	36.8	38.8	37.4	34.9	38.0	36.6	33.5	37.1	35.1	32.0
	gpm	11.3	8.5	6.6	10.8	8.1	5.9	10.3	7.8	5.7	9.9	7.2	5.5
	wpd	11.7	6.6	4.0	10.8	6.1	3.2	9.8	5.6	3.0	9.0	4.7	2.7
80	TC	46.4	44.2	39.9	44.7	42.7	38.5	43.1	40.0	37.1	40.9	38.6	35.7
	SC	43.0	41.8	39.4	42.2	40.9	38.0	41.4	39.5	36.6	40.4	38.1	35.2
	gpm	11.7	9.0	6.8	11.3	8.6	6.5	10.9	8.1	6.3	10.3	7.8	6.0
	wpd	12.6	7.4	4.2	11.7	6.8	3.9	10.9	6.0	3.6	9.8	5.6	3.3
82	TC	48.4	45.5	43.0	46.9	44.2	41.6	45.0	42.9	40.2	43.7	41.6	38.8
	SC	46.4	44.9	42.4	45.5	43.7	41.1	44.4	42.4	39.7	43.1	41.0	38.4
	gpm	12.3	9.2	7.2	11.9	9.0	7.0	11.4	8.7	6.8	11.1	8.4	6.6
	wpd	13.9	7.8	4.8	13.0	7.4	4.5	11.9	7.0	4.2	11.2	6.5	4.0
84	TC	50.2	48.4	45.9	48.9	47.0	44.6	47.6	45.7	43.2	46.3	44.4	41.9
	SC	49.6	47.8	45.4	48.3	46.5	44.1	47.0	45.2	42.7	45.7	43.9	41.4
	gpm	12.7	9.8	7.7	12.4	9.5	7.5	12.0	9.3	7.3	11.7	9.0	7.1
	wpd	14.8	8.8	5.5	14.0	8.3	5.1	13.1	7.9	4.9	12.6	7.4	4.6
86	TC	52.8	51.2	48.9	51.5	49.9	47.6	50.2	48.6	46.3	48.9	47.3	44.9
	SC	52.2	50.5	48.3	50.9	49.3	47.0	49.6	48.0	45.7	48.3	46.7	44.4
	gpm	13.4	10.3	8.2	13.0	10.1	8.1	12.7	9.9	7.8	12.4	9.5	7.6
	wpd	16.4	9.8	6.2	15.6	9.3	6.0	14.8	8.9	5.6	14.0	8.3	5.3
88	TC	55.4	54.0	51.8	54.5	52.7	50.5	52.8	51.4	49.2	51.5	50.1	47.9
	SC	54.8	53.3	51.2	53.5	52.0	49.9	52.2	50.7	48.6	50.9	49.5	47.3
	gpm	14.0	10.9	8.8	13.7	10.7	8.6	13.4	10.4	8.3	13.0	10.2	8.1
	wpd	18.0	10.9	7.1	17.2	10.4	6.7	16.4	10.0	6.3	15.6	9.5	6.0
90	TC	58.0	56.7	54.7	56.8	55.4	53.4	56.5	55.5	54.1	52.1	54.2	52.8
	SC	57.3	56.0	54.0	56.1	54.7	52.7	54.8	53.4	51.4	53.5	52.2	50.2
	gpm	14.7	11.5	9.3	14.3	11.2	9.0	14.0	11.0	8.8	13.7	10.7	8.6
	wpd	19.9	12.1	7.9	18.8	11.6	7.5	18.0	11.1	7.1	17.2	10.6	6.7

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	52.7	50.4	47.9	50.1	47.8	45.3	47.4	45.2	42.9	44.7	42.6	40.5
	SC	42.3	41.1	39.7	40.9	37.9	34.8	39.5	38.3	37.2	38.		

# 1500 CFM - Standard Capacity (63° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	36.9	33.3	28.4	34.9	31.2	26.6	32.8	29.0	24.9	30.8	27.0	23.2
	SC	26.9	25.2	23.0	25.9	24.3	22.1	25.1	23.4	21.3	24.2	22.4	20.5
	gpm	9.3	6.7	4.8	8.8	6.3	4.5	8.3	5.9	4.2	7.8	5.4	4.0
	wpd	14.2	7.4	3.8	12.8	6.5	3.3	11.3	5.7	2.9	10.0	4.8	2.6
76	TC	37.6	34.3	30.4	35.7	32.5	28.6	33.7	30.6	27.1	31.9	28.8	25.6
	SC	29.5	28.0	25.9	28.6	27.1	25.3	27.8	26.2	24.4	26.9	25.5	23.6
	gpm	9.5	7.0	5.1	9.0	6.6	4.8	8.5	6.2	4.6	8.1	5.8	4.3
	wpd	14.9	8.0	4.3	13.2	7.1	3.8	11.9	6.3	3.4	10.6	5.5	3.1
78	TC	38.6	35.7	32.3	36.7	34.0	30.9	34.8	32.3	29.4	33.1	30.8	28.1
	SC	32.2	30.7	29.0	31.3	30.0	28.1	30.5	29.2	27.4	29.7	28.4	26.5
	gpm	9.8	7.2	5.4	9.3	6.9	5.2	8.8	6.5	5.0	8.4	6.3	4.7
	wpd	15.6	8.5	4.8	14.2	7.8	4.4	12.8	6.9	4.0	11.5	6.5	3.7
80	TC	39.6	37.2	34.4	37.8	35.7	33.0	36.2	34.2	31.7	34.7	32.9	30.5
	SC	34.9	33.7	32.0	34.0	32.8	31.1	33.3	32.2	30.4	32.5	31.3	29.5
	gpm	10.0	7.5	5.8	9.5	7.2	5.6	9.1	6.9	5.4	8.8	6.7	5.1
	wpd	16.4	9.3	5.5	14.9	8.5	5.1	13.7	7.8	4.7	12.6	7.3	4.3
82	TC	40.8	38.8	36.6	39.3	37.4	35.3	37.8	36.2	34.2	36.5	35.0	32.3
	SC	37.6	36.4	34.8	36.9	35.7	34.1	36.2	34.8	33.2	35.3	34.0	31.9
	gpm	10.3	7.9	6.2	9.9	7.6	6.0	9.6	7.4	5.7	9.2	7.1	5.4
	wpd	17.4	10.2	6.3	16.1	9.5	5.8	15.1	8.9	5.4	13.9	8.1	4.8
84	TC	42.4	40.7	38.9	41.1	39.4	37.8	39.8	38.4	36.1	38.6	36.9	34.9
	SC	40.5	39.2	37.8	39.7	38.4	36.8	38.9	37.5	35.6	38.1	36.4	34.5
	gpm	10.7	8.2	6.6	10.4	8.0	6.4	10.1	7.8	6.1	9.8	7.5	5.9
	wpd	18.7	11.1	7.1	17.7	10.4	6.6	16.6	9.8	6.1	15.6	9.3	5.7
86	TC	44.3	42.8	40.8	43.2	41.5	39.7	42.0	40.3	38.6	40.9	39.2	37.5
	SC	43.3	41.9	40.3	42.4	40.9	39.2	41.5	39.8	38.1	40.3	38.7	37.0
	gpm	11.2	8.7	6.9	10.9	8.4	6.7	10.6	8.1	6.5	10.4	7.9	6.4
	wpd	20.7	12.3	7.8	19.6	11.5	7.3	18.5	10.8	6.9	17.7	10.2	6.6
88	TC	46.6	44.9	43.2	45.4	43.8	42.1	44.3	42.6	41.0	43.2	41.5	39.8
	SC	46.0	44.3	42.7	44.8	43.2	41.6	43.7	42.1	40.4	42.6	41.0	39.3
	gpm	11.8	9.1	7.3	11.6	8.8	7.1	11.2	8.6	6.9	10.9	8.4	6.7
	wpd	22.7	13.5	8.7	21.8	12.8	8.3	20.7	12.1	7.8	19.6	11.5	7.4
90	TC	48.8	47.2	45.5	47.7	46.1	44.4	46.6	44.9	43.3	45.4	43.8	42.1
	SC	48.2	46.6	45.0	47.1	45.5	43.8	46.0	44.4	42.7	44.9	43.2	41.6
	gpm	12.3	9.5	7.7	12.0	9.3	7.5	11.8	9.1	7.3	11.6	8.8	7.1
	wpd	24.9	14.9	9.6	23.6	14.2	9.3	22.7	13.5	8.7	21.8	12.8	8.3

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	53.0	48.0	42.9	50.2	45.4	40.3	47.2	42.5	37.5	44.4	39.8	35.2
	SC	35.1	32.9	30.6	33.8	31.7	29.5	32.5	30.4	28.3	31.3	29.3	27.3
	gpm	13.4	9.7	7.2	12.7	9.2	6.8	11.9	8.6	6.3	11.2	8.0	5.9
	wpd	11.8	6.2	3.4	10.5	5.6	3.0	9.4	4.8	2.6	8.3	4.2	2.3
76	TC	53.5	49.1	44.5	50.8	46.5	42.1	48.1	43.9	39.6	45.3	41.3	37.4
	SC	37.9	35.9	33.9	36.7	34.7	32.8	35.5	33.6	31.7	34.3	32.5	30.7
	gpm	13.5	9.9	7.5	12.9	9.4	7.1	12.2	8.9	6.7	11.5	8.3	6.3
	wpd	12.0	6.5	3.7	10.9	5.8	3.3	9.7	5.2	2.9	8.6	4.6	2.6
78	TC	54.2	50.3	46.3	51.5	47.7	44.0	49.0	45.3	41.9	46.4	42.9	39.8
	SC	40.8	39.0	37.2	39.6	37.8	36.2	38.4	36.8	35.2	37.3	35.7	34.3
	gpm	13.7	10.2	7.9	13.0	9.6	7.5	12.4	9.1	7.1	11.8	8.7	6.7
	wpd	12.3	6.8	4.0	11.1	6.1	3.6	10.1	5.5	3.3	9.1	4.9	3.0
80	TC	55.0	51.5	48.0	52.4	49.2	46.0	50.0	46.9	44.1	47.6	44.8	42.3
	SC	43.7	42.1	40.5	42.6	41.1	39.6	41.4	40.0	38.7	40.4	39.1	37.9
	gpm	14.0	10.4	8.1	13.2	9.9	7.8	12.7	9.5	7.5	12.0	9.1	7.1
	wpd	12.8	7.1	4.3	11.5	6.5	4.0	10.5	6.0	3.6	9.5	5.4	3.3
82	TC	55.9	52.8	50.1	53.5	50.8	48.2	51.2	48.7	46.5	50.0	47.4	44.9
	SC	46.7	45.3	44.0	45.6	44.3	43.0	44.5	43.4	42.2	43.6	42.5	41.5
	gpm	14.1	10.7	8.5	13.5	10.3	8.1	13.0	9.9	7.9	12.4	9.5	7.6
	wpd	13.1	7.5	4.7	12.0	6.9	4.3	11.1	6.4	4.0	10.1	5.9	3.8
84	TC	56.9	54.5	52.3	54.7	52.5	50.5	52.6	50.7	49.0	50.6	49.1	44.8
	SC	49.7	48.6	47.5	48.7	47.6	46.6	47.7	46.8	45.8	49.5	47.4	44.2
	gpm	14.4	11.1	8.8	13.8	10.7	8.6	13.3	10.3	8.3	13.7	11.0	9.1
	wpd	13.7	8.0	5.1	12.5	7.5	4.8	11.6	6.9	4.5	10.8	6.5	3.7
86	TC	58.2	56.3	54.5	56.1	54.5	53.1	54.3	53.0	49.3	52.6	50.1	47.9
	SC	52.8	51.9	50.9	51.9	50.1	50.1	50.3	48.7	45.2	50.2	48.6	45.5
	gpm	14.7	11.4	9.2	14.2	11.1	9.0	13.7	10.7	8.3	14.7	11.7	9.5
	wpd	14.1	8.5	5.6	13.2	8.0	5.3	12.3	7.6	4.6	11.6	6.8	4.3
88	TC	59.6	58.4	57.1	57.9	56.9	53.7	56.4	54.4	52.4	54.5	53.0	51.0
	SC	56.0	55.3	54.5	55.2	54.5	53.0	54.4	53.7	51.7	53.8	52.4	50.4
	gpm	15.2	11.9	9.6	14.7	11.5	9.1	14.3	11.1	8.8	13.8	11.0	9.1
	wpd	15.1	9.2	6.1	14.1	8.7	5.4	13.4	8.0	5.1	12.5	7.6	4.9
90	TC	61.6	59.8	58.0	59.9	58.5	56.7	58.5	57.2	55.3	59.6	57.9	55.6
	SC	59.4	59.0	57.3	59.0	57.8	56.0	57.8	56.5	54.6	59.5	57.9	55.9
	gpm	15.6	12.1	9.8	15.2	11.9	9.5	14.8	11.6	9.3	14.5	11.3	9.1
	wpd	16.0	9.6	6.3	15.1	9.2	6.0	14.4	8.9	5.7	13.8	8.4	5.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	48.2	43.3	38.0	45.6	40.5	35.4	42.9	38.0	33.1	40.2	35.5	30.5
	SC	32.9	30.7	28.4	31.8	29.5	27.3	30.6	28.4				

# 1500 CFM - Standard Capacity (65° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	43.0	38.8	33.3	40.6	36.4	31.0	38.1	34.1	28.4	35.6	31.6	26.1
	SC	26.3	24.6	22.3	25.3	23.6	21.4	24.3	22.7	20.4	23.3	21.7	19.4
	gpm	10.9	7.8	5.6	10.2	7.4	5.2	9.6	6.9	4.8	9.0	6.4	4.4
	wpd	19.3	10.0	5.1	17.1	8.9	4.4	15.1	7.8	3.8	13.2	6.6	3.2
76	TC	42.8	39.0	34.2	40.4	36.8	32.1	38.1	34.6	29.8	35.8	32.4	27.4
	SC	28.6	27.0	25.0	27.6	26.1	24.1	26.7	25.2	23.1	25.8	24.4	22.2
	gpm	10.8	7.9	5.7	10.2	7.4	5.4	9.6	7.0	5.0	9.1	6.6	4.7
	wpd	19.0	10.2	5.4	17.1	9.1	4.8	15.1	8.0	4.2	13.5	7.1	3.5
78	TC	42.9	39.5	35.5	40.7	37.5	33.3	38.6	35.5	31.3	36.6	33.4	29.6
	SC	31.0	29.5	27.7	30.2	28.7	26.9	29.3	27.8	25.9	28.4	27.0	25.3
	gpm	10.9	8.0	6.0	10.3	7.6	5.6	9.8	7.2	5.3	9.2	6.7	5.0
	wpd	19.3	10.4	5.8	17.4	9.5	5.1	15.6	8.5	4.5	13.9	7.4	4.0
80	TC	43.4	40.4	36.8	41.5	38.4	34.9	39.5	36.6	33.2	37.6	34.6	31.6
	SC	33.6	32.2	30.5	32.8	31.4	29.7	31.9	30.6	29.1	31.1	29.7	28.2
	gpm	11.0	8.2	6.2	10.5	7.8	5.9	10.0	7.4	5.6	9.5	7.0	5.4
	wpd	19.8	11.1	6.3	18.2	10.0	5.7	16.4	9.1	5.1	14.9	8.0	4.7
82	TC	44.3	41.4	38.3	42.4	39.6	36.7	40.5	37.8	35.2	38.6	36.2	33.7
	SC	36.2	34.9	33.4	35.5	34.1	32.8	34.6	33.3	31.9	33.8	32.7	31.2
	gpm	11.2	8.4	6.4	10.7	8.0	6.2	10.2	7.7	6.0	9.8	7.3	5.7
	wpd	20.4	11.5	6.8	18.7	10.4	6.3	17.1	9.6	5.8	15.6	8.7	5.2
84	TC	45.3	42.5	40.1	43.4	40.9	38.7	41.5	39.3	37.2	39.9	37.9	35.9
	SC	39.0	37.7	36.4	38.2	36.8	35.6	37.3	36.2	34.9	36.5	35.3	34.0
	gpm	11.5	8.6	6.7	11.0	8.3	6.5	10.5	8.0	6.3	10.1	7.7	6.0
	wpd	21.6	12.1	7.4	19.8	11.3	6.9	18.2	10.4	6.5	16.6	9.6	6.0
86	TC	46.3	43.9	42.0	44.6	42.4	40.6	42.9	41.0	39.3	41.4	39.7	38.1
	SC	41.7	40.5	39.4	40.8	39.7	38.5	40.2	39.0	37.6	39.3	38.1	36.9
	gpm	11.7	8.8	7.1	11.3	8.6	6.8	10.9	8.3	6.7	10.5	8.1	6.4
	wpd	22.4	12.8	8.1	21.0	12.1	7.6	19.3	11.3	7.3	17.9	10.6	6.8
88	TC	47.5	45.6	43.9	46.0	44.3	42.6	44.6	43.0	41.5	43.3	41.8	39.9
	SC	44.5	43.4	42.0	43.7	42.5	41.3	43.0	41.8	40.4	42.2	40.8	39.4
	gpm	12.0	9.2	7.4	11.6	9.0	7.2	11.3	8.7	7.0	11.0	8.5	6.7
	wpd	23.6	13.9	9.1	22.1	13.2	8.5	21.0	12.3	8.0	19.8	11.7	7.4
90	TC	49.1	47.5	45.9	47.8	46.3	44.8	46.6	45.0	43.4	45.5	43.9	42.2
	SC	47.3	46.0	44.8	46.4	45.2	43.9	45.7	44.5	42.8	45.0	43.3	41.7
	gpm	12.4	9.6	7.8	12.1	9.4	7.6	11.8	9.1	7.4	11.6	8.9	7.1
	wpd	25.2	15.1	9.8	23.9	14.4	9.5	22.7	13.7	8.9	21.8	13.0	8.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	55.3	50.5	44.2	52.4	47.4	41.1	49.5	44.4	38.2	46.7	41.5	35.1
	SC	32.5	30.5	27.8	31.3	29.2	26.5	30.1	27.9	25.3	28.9	26.7	24.1
	gpm	14.0	10.3	7.5	13.3	9.6	6.9	12.5	9.0	6.4	11.8	8.4	5.9
	wpd	18.0	9.7	5.1	16.2	8.5	4.4	14.4	7.4	3.8	12.8	6.5	3.2
76	TC	55.3	50.8	45.2	52.5	47.9	42.3	49.8	45.2	39.4	47.0	42.3	36.9
	SC	35.1	33.2	30.8	33.9	32.0	29.6	32.8	30.8	28.4	31.6	29.6	27.4
	gpm	14.0	10.3	7.7	13.3	9.7	7.2	12.6	9.2	6.7	11.9	8.6	6.3
	wpd	18.0	9.7	5.4	16.2	8.6	4.7	14.6	7.8	4.1	13.0	6.7	3.6
78	TC	55.5	51.5	46.2	52.8	48.8	43.8	50.3	46.0	41.2	47.7	43.4	38.8
	SC	37.8	36.1	33.8	36.7	34.9	32.7	35.6	33.7	31.7	34.5	32.6	30.6
	gpm	14.1	10.4	7.8	13.4	9.9	7.4	12.7	9.3	6.9	12.1	8.8	6.5
	wpd	18.2	10.0	5.6	16.4	8.9	5.0	14.8	7.9	4.4	13.3	7.1	3.9
80	TC	56.0	52.3	47.8	53.4	49.8	45.2	50.9	47.3	43.1	48.5	44.8	40.7
	SC	40.6	39.0	37.0	39.5	37.9	35.9	38.4	36.8	34.9	37.4	35.8	33.9
	gpm	14.2	10.6	8.1	13.5	10.1	7.7	12.9	9.6	7.2	12.3	9.1	6.8
	wpd	18.4	10.3	6.0	16.8	9.3	5.4	15.2	8.5	4.8	13.9	7.6	4.3
82	TC	56.7	53.3	49.3	54.2	50.9	47.0	51.7	48.6	44.7	49.4	46.3	42.8
	SC	43.5	42.0	40.1	42.4	40.9	39.2	41.3	39.9	38.1	40.3	38.9	37.2
	gpm	14.3	10.8	8.3	13.7	10.3	7.9	13.1	9.9	7.6	12.5	9.4	7.2
	wpd	18.8	10.8	6.3	17.2	9.7	5.7	15.8	8.9	5.3	14.2	8.0	4.8
84	TC	57.4	54.5	50.9	55.0	52.3	48.7	52.7	50.0	46.8	50.5	47.9	44.9
	SC	46.4	45.1	43.3	45.3	44.0	42.3	44.3	43.1	41.5	43.3	42.1	40.6
	gpm	14.5	11.1	8.6	13.9	10.6	8.2	13.4	10.2	7.9	12.8	9.7	7.6
	wpd	19.3	11.2	6.8	17.8	10.3	6.2	16.4	9.5	5.7	15.0	8.6	5.3
86	TC	58.3	55.9	52.5	56.1	53.7	50.7	53.9	51.5	48.9	51.8	49.6	47.4
	SC	49.3	48.1	46.5	48.3	47.2	45.6	47.3	46.2	44.8	46.4	45.3	44.0
	gpm	14.7	11.3	8.9	14.2	10.9	8.6	13.7	10.4	8.2	13.1	10.0	8.0
	wpd	19.9	11.7	7.2	18.4	10.9	6.7	17.2	10.0	6.2	15.8	9.2	5.8
88	TC	59.3	57.2	54.5	57.2	55.2	52.9	55.1	53.4	51.3	53.2	51.7	49.8
	SC	52.3	51.2	49.9	51.3	50.3	49.0	50.4	49.5	48.3	49.5	48.7	47.4
	gpm	15.1	11.6	9.2	14.5	11.2	9.0	13.9	10.8	8.6	13.4	10.5	8.4
	wpd	20.8	12.3	7.8	19.3	11.4	7.4	17.8	10.8	6.8	16.6	10.1	6.5
90	TC	60.5	58.7	56.7	58.5	57.0	55.2	56.7	55.4	53.8	55.1	53.9	51.0
	SC	55.3	54.4	53.3	54.4	53.6	52.5	53.6	52.8	51.6	52.7	51.9	50.4
	gpm	15.3	11.9	9.6	14.8	11.6	9.4	14.3	11.2	9.1	13.9	10.9	8.6
	wpd	21.5	13.0	8.5	20.1	12.3	8.0	18.8	11.6	7.6	17.8	10.9	6.8

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	67.6	65.4	62.2	64.7	62.4	59.1	61.8	59.4	55.9	58.8	56.3	52.6
	SC	41.9	40.8	39.1									

# 1500 CFM - Standard Capacity (67° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	49.0	45.0	40.5	46.7	42.6	37.8	44.3	40.1	34.9	41.9	37.6	31.9
	SC	25.7	24.1	22.3	24.8	23.1	21.2	23.8	22.1	20.1	22.9	21.2	19.0
	gpm	12.4	9.1	6.8	11.9	8.6	6.4	11.2	8.1	5.9	10.6	7.6	5.4
	wpd	25.2	13.7	7.6	23.0	12.1	6.6	20.7	10.8	5.7	18.5	9.5	4.7
76	TC	49.2	45.1	40.6	46.8	42.6	37.8	44.4	40.1	35.3	41.9	37.6	32.4
	SC	28.2	26.5	24.6	27.2	25.5	23.6	26.2	24.5	22.5	25.2	23.5	21.5
	gpm	12.4	9.1	6.8	11.8	8.6	6.4	11.2	8.1	6.0	10.6	7.6	5.4
	wpd	25.2	13.7	7.6	22.7	12.1	6.6	20.7	10.8	5.8	18.5	9.5	4.8
78	TC	49.2	45.0	40.8	46.8	42.5	38.3	44.3	40.2	36.0	41.8	37.7	33.5
	SC	30.5	28.8	27.0	29.5	27.8	26.1	28.5	26.8	25.1	27.5	26.0	24.2
	gpm	12.4	9.1	6.9	11.8	8.6	6.4	11.2	8.1	6.0	10.5	7.6	5.7
	wpd	25.2	13.5	7.8	22.7	12.1	6.8	20.4	10.8	6.0	18.2	9.5	5.2
80	TC	49.5	45.5	41.8	47.0	43.1	39.5	44.6	40.9	37.2	42.3	38.8	35.0
	SC	32.8	31.1	29.6	31.8	30.2	28.7	30.9	29.3	27.8	29.9	28.4	26.8
	gpm	12.6	9.2	7.1	11.9	8.8	6.7	11.3	8.3	6.3	10.7	7.8	5.9
	wpd	25.8	13.9	8.1	23.0	12.6	7.3	21.0	11.3	6.5	18.7	10.0	5.7
82	TC	49.1	45.5	42.3	46.8	43.4	40.3	44.7	41.4	38.1	42.5	39.4	36.0
	SC	35.2	33.7	32.3	34.3	32.9	31.4	33.4	32.0	30.6	32.6	31.2	29.7
	gpm	12.5	9.2	7.1	11.9	8.8	6.6	11.3	8.4	6.4	10.8	8.0	6.0
	wpd	25.5	13.9	8.3	23.0	12.6	7.6	21.0	11.5	6.8	19.0	10.4	6.0
84	TC	49.4	46.3	43.2	47.3	44.3	41.3	45.4	42.3	39.4	43.3	40.5	37.7
	SC	37.7	36.3	35.0	36.9	35.5	34.1	36.0	34.7	33.3	35.2	33.9	32.5
	gpm	12.5	9.4	7.3	11.9	9.0	7.0	11.5	8.6	6.7	10.9	8.2	6.4
	wpd	25.5	14.4	8.7	23.3	13.2	8.0	21.6	12.1	7.3	19.6	11.1	6.6
86	TC	50.2	47.3	44.4	48.3	45.4	42.6	46.4	43.5	41.0	44.5	41.6	39.3
	SC	40.4	39.0	37.6	39.5	38.2	36.8	38.7	37.3	36.1	37.9	36.6	35.4
	gpm	12.7	9.6	7.5	12.2	9.2	7.2	11.7	8.8	6.9	11.2	8.5	6.6
	wpd	26.5	15.1	9.3	24.3	13.9	8.5	22.4	12.8	7.8	20.7	11.7	7.1
88	TC	51.2	48.4	45.7	49.3	46.5	44.1	47.4	44.7	42.5	45.5	43.0	41.1
	SC	43.1	41.7	40.4	42.2	40.9	39.8	41.5	40.1	38.9	40.6	39.4	38.3
	gpm	12.9	9.8	7.7	12.5	9.5	7.4	12.0	9.1	7.2	11.5	8.7	7.0
	wpd	27.4	15.9	9.6	25.5	14.6	9.1	23.6	13.5	8.5	21.6	12.3	8.0
90	TC	52.2	49.4	47.2	50.3	47.8	45.7	48.4	46.2	44.3	46.7	44.7	43.0
	SC	45.8	44.4	43.3	44.9	43.6	42.4	44.1	42.9	41.8	43.2	42.1	40.9
	gpm	13.2	10.0	8.0	12.7	9.7	7.8	12.3	9.4	7.5	11.9	9.1	7.3
	wpd	28.4	16.4	10.4	26.5	15.4	9.8	24.6	14.4	9.3	23.0	13.5	8.7

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	69.2	64.7	58.6	66.3	61.6	55.4	63.3	58.3	51.9	60.3	55.0	48.4
	SC	35.1	33.1	30.4	33.8	31.7	29.1	32.4	30.3	27.6	31.1	28.9	26.2
	gpm	17.6	13.1	9.9	16.8	12.4	9.4	16.0	11.8	8.7	15.2	11.1	8.2
	wpd	20.2	11.3	6.4	18.6	10.1	5.8	16.9	9.1	5.0	15.2	8.1	4.4
76	TC	69.2	64.7	58.8	66.3	61.6	55.7	63.3	58.4	52.4	60.2	55.2	48.9
	SC	37.6	35.7	33.1	36.4	34.3	31.8	35.0	32.9	30.4	33.7	31.6	29.0
	gpm	17.5	13.1	9.9	16.8	12.5	9.4	16.0	11.8	8.8	15.2	11.1	8.3
	wpd	20.0	11.3	6.5	18.6	10.3	5.8	16.9	9.1	5.1	15.2	8.1	4.5
78	TC	69.1	64.8	59.3	66.2	61.8	56.3	63.3	58.8	53.1	60.3	55.6	49.9
	SC	40.2	38.3	35.9	38.9	37.0	34.7	37.6	35.7	33.3	36.3	34.3	32.0
	gpm	17.5	13.1	10.0	16.8	12.5	9.5	16.0	11.9	9.0	15.3	11.2	8.4
	wpd	20.0	11.3	6.6	18.4	10.3	6.0	16.9	9.2	5.3	15.4	8.3	4.6
80	TC	69.7	65.6	60.5	66.8	62.6	57.4	63.9	59.7	54.3	61.0	56.7	51.6
	SC	42.8	41.0	38.8	41.5	39.7	37.5	40.3	38.4	36.2	39.0	37.2	35.0
	gpm	17.6	13.3	10.2	16.9	12.7	9.7	16.2	12.0	9.1	15.4	11.5	8.7
	wpd	20.4	11.6	6.8	18.8	10.5	6.2	17.2	9.5	5.5	15.5	8.6	4.9
82	TC	69.4	65.6	60.8	66.6	62.7	58.1	63.8	59.9	55.2	60.9	57.0	52.5
	SC	45.5	43.8	41.7	44.3	42.5	40.6	43.0	41.3	39.4	41.8	40.1	38.2
	gpm	17.6	13.3	10.3	16.8	12.7	9.8	16.2	12.1	9.3	15.4	11.5	8.9
	wpd	20.2	11.6	6.9	18.6	10.5	6.3	17.2	9.6	5.7	15.5	8.7	5.2
84	TC	69.7	66.2	61.8	67.0	63.4	59.1	64.3	60.8	56.6	61.5	57.9	53.9
	SC	48.2	46.7	44.7	47.0	45.4	43.6	45.8	44.3	42.5	44.6	43.1	41.9
	gpm	17.6	13.4	10.4	17.0	12.8	10.0	16.3	12.3	9.5	15.6	11.7	9.1
	wpd	20.4	11.8	7.1	18.9	10.8	6.6	17.4	10.0	6.0	15.9	9.0	5.4
86	TC	70.2	66.9	63.0	67.5	64.2	60.4	64.8	61.6	57.7	62.1	59.1	55.4
	SC	51.0	49.5	47.8	49.8	48.3	46.7	48.6	47.2	45.5	47.4	46.1	44.5
	gpm	17.8	13.5	10.6	17.1	13.0	10.2	16.4	12.4	9.7	15.8	11.9	9.4
	wpd	20.8	12.0	7.3	19.1	11.1	6.8	17.7	10.1	6.2	16.4	9.4	5.8
88	TC	70.6	67.7	64.1	68.0	65.2	61.6	65.4	62.6	59.3	62.8	60.1	56.9
	SC	53.7	52.4	50.8	52.6	51.3	49.8	51.4	50.2	48.7	50.3	49.1	47.7
	gpm	17.8	13.7	10.8	17.2	13.2	10.4	16.5	12.7	10.0	15.9	12.1	9.6
	wpd	20.8	12.3	7.7	19.3	11.5	7.1	17.9	10.5	6.6	16.5	9.6	6.1
90	TC	71.2	68.6	65.3	68.6	66.1	63.0	66.1	63.7	60.8	63.6	61.3	58.7
	SC	56.6	55.4	53.9	55.4	54.3	52.9	54.3	53.2	51.9	53.2	52.2	51.0
	gpm	18.0	13.9	11.1	17.3	13.4	10.7	16.8	12.9	10.3	16.0	12.4	9.9
	wpd	21.2	12.6	8.0	19.7	11.8	7.5	18.4	10.9	6.9	16.9	10.1	6.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	62.9	58.7	52.6	60.1	55.9	49.4	57.2	52.8	46.0	54.2	49.6	42.6
	SC	32.2	30.5	27.9									

# 1500 CFM - Standard Capacity (69° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	55.1	50.9	46.8	52.7	48.6	44.3	50.4	46.1	41.9	47.9	43.7	39.4
	SC	25.0	23.4	21.7	24.1	22.4	20.8	23.1	21.5	19.9	22.2	20.5	18.9
	gpm	14.0	10.3	7.9	13.3	9.8	7.4	12.8	9.4	7.1	12.2	8.8	6.7
	wpd	31.9	17.4	10.2	29.1	15.9	9.1	26.8	14.4	8.1	24.3	12.8	7.3
76	TC	55.4	51.2	47.1	53.0	48.8	44.6	50.6	46.4	42.1	48.2	43.9	39.5
	SC	27.5	25.8	24.2	26.5	24.9	23.2	25.6	23.9	22.3	24.6	23.0	21.3
	gpm	14.0	10.4	8.0	13.4	9.8	7.5	12.8	9.4	7.1	12.3	8.9	6.7
	wpd	32.2	17.7	10.4	29.4	15.9	9.3	26.8	14.4	8.3	24.6	13.0	7.3
78	TC	55.7	51.5	47.3	53.3	49.0	44.7	50.8	46.5	42.2	48.3	44.0	39.6
	SC	29.9	28.3	26.6	29.0	27.3	25.6	28.0	26.3	24.6	27.0	25.4	23.7
	gpm	14.1	10.4	8.0	13.5	9.9	7.5	12.9	9.4	7.1	12.2	8.9	6.7
	wpd	32.6	17.7	10.4	29.8	16.1	9.3	27.1	14.4	8.3	24.3	13.0	7.3
80	TC	55.8	51.6	47.2	53.4	49.1	44.7	50.9	46.5	42.3	48.4	43.9	39.8
	SC	32.3	30.6	28.9	31.4	29.6	27.9	30.4	28.7	27.0	29.4	27.7	26.1
	gpm	14.1	10.5	8.0	13.5	9.9	7.5	12.9	9.4	7.1	12.3	8.9	6.7
	wpd	32.6	17.9	10.4	29.8	16.1	9.3	27.1	14.4	8.3	24.6	13.0	7.4
82	TC	55.8	51.5	47.4	53.3	49.0	44.9	50.8	46.5	42.7	48.2	44.1	40.5
	SC	34.7	33.0	31.3	33.7	32.0	30.4	32.7	31.0	29.5	31.7	30.1	28.6
	gpm	14.1	10.5	8.0	13.5	9.9	7.6	12.9	9.5	7.2	12.2	8.9	6.8
	wpd	32.6	17.9	10.4	29.8	16.1	9.5	27.1	14.6	8.5	24.3	13.0	7.6
84	TC	55.6	51.4	47.7	53.2	49.1	45.5	50.7	46.8	43.3	48.3	44.6	41.3
	SC	37.0	35.3	33.8	36.0	34.4	32.9	35.1	33.5	32.1	34.1	32.6	31.3
	gpm	14.1	10.4	8.1	13.5	9.9	7.7	12.9	9.5	7.3	12.3	9.0	7.0
	wpd	32.6	17.7	10.6	29.8	16.1	9.6	27.1	14.6	8.7	24.6	13.2	8.0
86	TC	55.5	51.8	48.4	53.2	49.6	46.4	50.8	47.4	44.4	48.7	45.4	42.2
	SC	39.4	37.8	36.4	38.4	36.9	35.6	37.5	36.1	34.7	36.6	35.3	33.9
	gpm	14.1	10.5	8.0	13.5	10.1	7.8	12.8	9.6	7.5	12.3	9.2	7.1
	wpd	32.6	17.9	10.8	29.8	16.6	10.0	26.8	15.8	9.3	24.6	13.9	8.3
88	TC	55.7	52.4	49.4	53.5	50.4	47.3	51.4	48.4	45.4	49.4	46.4	43.5
	SC	41.8	40.4	39.0	40.9	39.6	38.2	40.1	38.7	37.4	39.3	38.0	36.6
	gpm	14.1	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7	12.5	9.4	7.4
	wpd	32.6	18.5	11.5	29.8	17.1	10.4	27.8	15.9	9.6	25.5	14.4	8.9
90	TC	56.3	53.3	50.4	54.3	51.4	48.5	52.4	49.5	46.6	50.4	47.6	44.8
	SC	44.4	43.0	41.7	43.6	42.3	40.9	42.7	41.4	40.0	42.0	40.6	39.4
	gpm	14.3	10.8	8.5	13.7	10.4	8.1	13.3	10.0	7.8	12.8	9.6	7.6
	wpd	33.3	19.0	11.9	30.8	17.7	10.8	28.8	16.4	10.0	26.8	15.1	9.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	70.6	66.5	61.7	67.8	63.6	58.5	64.9	60.6	55.2	62.0	57.6	51.9
	SC	31.8	30.1	28.1	30.6	28.8	26.8	29.4	27.6	25.5	28.2	26.4	24.2
	gpm	17.9	13.4	10.4	17.2	12.9	9.9	16.5	12.2	9.3	15.7	11.6	8.8
	wpd	29.4	16.6	10.0	27.1	15.2	8.9	24.8	13.7	7.9	22.6	12.4	7.1
76	TC	70.8	66.7	61.8	68.0	63.7	58.7	65.1	60.8	55.4	62.1	57.8	52.1
	SC	34.5	32.7	30.7	33.3	31.5	29.4	32.0	30.3	28.1	30.8	29.1	26.8
	gpm	17.9	13.5	10.4	17.2	12.9	9.9	16.5	12.3	9.4	15.7	11.6	8.8
	wpd	29.4	16.8	10.0	27.1	15.4	9.0	25.1	13.9	8.0	22.6	12.4	7.1
78	TC	70.9	66.8	61.8	68.1	63.8	58.7	65.2	60.8	55.6	62.2	57.9	52.7
	SC	37.1	35.4	33.3	35.9	34.2	32.1	34.7	32.9	30.8	33.5	31.7	29.5
	gpm	18.0	13.5	10.4	17.3	12.9	9.9	16.5	12.3	9.4	15.7	11.7	8.8
	wpd	29.7	16.8	10.0	27.3	15.4	9.0	25.1	13.9	8.0	22.6	12.6	7.1
80	TC	71.0	66.7	61.9	68.1	63.8	58.9	65.2	60.8	55.6	62.2	57.9	52.7
	SC	39.8	37.9	36.0	38.5	36.7	34.7	37.3	35.5	33.4	36.1	34.3	32.3
	gpm	18.0	13.4	10.4	17.3	12.9	10.0	16.5	12.3	9.4	15.7	11.7	8.9
	wpd	29.7	16.6	10.0	27.3	15.4	9.0	25.1	13.9	8.0	22.6	12.6	7.2
82	TC	70.8	66.7	62.2	67.9	63.8	59.3	65.1	60.9	56.3	62.2	58.1	53.3
	SC	42.3	40.5	38.7	41.1	39.3	37.5	39.9	38.2	36.3	38.7	37.0	35.1
	gpm	17.9	13.5	10.5	17.1	12.9	10.0	16.5	12.3	9.5	15.8	11.7	9.0
	wpd	29.4	16.8	10.1	26.8	15.4	9.2	25.1	13.9	8.3	22.9	12.6	7.5
84	TC	70.8	66.9	62.7	68.0	64.1	59.9	65.1	61.4	57.1	62.3	58.6	54.3
	SC	44.9	43.2	41.5	43.7	42.1	40.3	42.5	40.9	39.2	41.3	39.8	38.0
	gpm	17.9	13.5	10.6	17.2	13.0	10.1	16.5	12.5	9.6	15.7	11.9	9.2
	wpd	29.4	16.8	10.3	27.1	15.6	9.3	24.8	14.2	8.5	22.6	13.0	7.8
86	TC	70.9	67.3	63.5	68.2	64.6	60.8	65.5	62.0	57.9	62.8	59.3	55.3
	SC	47.5	46.0	44.4	46.4	44.9	43.2	45.2	43.8	42.1	44.1	42.7	41.0
	gpm	17.9	13.6	10.7	17.3	13.1	10.3	16.5	12.5	9.8	15.9	12.1	9.4
	wpd	29.4	17.0	10.6	27.3	15.8	9.7	25.1	14.4	8.8	23.1	13.3	8.0
88	TC	71.2	67.9	64.3	68.6	65.2	61.8	66.0	62.7	59.2	63.4	60.2	56.7
	SC	50.2	48.8	47.3	49.1	47.7	46.2	48.0	46.6	45.1	46.9	45.6	44.1
	gpm	18.1	13.8	10.8	17.3	13.3	10.4	16.7	12.7	10.0	16.0	12.2	9.6
	wpd	30.0	17.4	10.8	27.6	16.2	10.0	25.6	14.8	9.2	23.6	13.7	8.5
90	TC	71.8	68.5	65.3	69.2	66.0	62.8	66.7	63.6	60.4	64.2	61.0	58.0
	SC	53.0	51.6	50.2	52.0	50.6	49.2	50.9	49.5	48.2	49.8	48.5	47.2
	gpm	18.2	13.8	11.0	17.5	13.4	10.6	16.9	12.9	10.2	16.3	12.3	9.8
	wpd	30.2	17.6	11.1	28.1	16.4	10.3	26.3	15.2	9.5	24.3	13.9	8.8

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	84.6	82.4	79.9	81.7	79.4	76.8	78.7	76.3	73.6	75.7	7	

# 1500 CFM - Standard Capacity (71° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	61.7	57.5	53.2	59.3	55.0	50.7	56.8	52.6	48.1	54.4	50.0	45.5
	SC	24.3	22.7	21.0	23.4	21.7	20.1	22.4	20.8	19.1	21.5	19.8	18.2
	gpm	15.6	11.6	9.0	15.0	11.1	8.5	14.3	10.6	8.1	13.8	10.2	7.7
	wdp	39.8	22.1	13.2	36.7	20.1	11.9	33.7	18.5	10.8	31.2	16.9	9.6
76	TC	61.8	57.6	53.3	59.4	55.1	50.9	56.9	52.7	48.4	54.5	50.2	45.8
	SC	26.7	25.1	23.4	24.1	22.5	24.8	23.2	21.6	23.9	22.3	20.6	
	gpm	15.7	11.6	9.0	15.0	11.2	8.6	14.4	10.6	8.1	13.7	10.2	7.8
	wdp	40.2	22.1	13.2	37.0	20.4	12.1	34.0	18.5	10.8	30.8	16.9	9.8
78	TC	62.0	57.8	53.6	59.6	55.4	51.1	57.2	52.9	48.6	54.7	50.4	46.0
	SC	29.2	27.6	25.9	28.3	26.6	25.0	27.3	25.7	24.0	26.3	24.7	23.1
	gpm	15.7	11.7	9.1	15.1	11.2	8.6	14.4	10.7	8.2	13.8	10.2	7.8
	wdp	40.2	22.4	13.5	37.4	20.7	12.1	34.0	18.7	11.1	31.2	16.9	9.8
80	TC	62.3	58.1	53.8	59.9	55.7	51.3	57.4	53.2	48.8	55.0	50.6	46.2
	SC	31.7	30.0	28.3	30.7	29.0	27.4	29.7	28.1	26.4	28.8	27.1	25.5
	gpm	15.7	11.8	9.1	15.1	11.2	8.7	14.5	10.8	8.2	13.9	10.2	7.8
	wdp	40.5	22.7	13.5	37.4	20.7	12.3	34.4	19.0	11.1	31.5	17.1	10.0
82	TC	62.5	58.3	54.0	60.1	55.8	51.4	57.6	53.3	48.8	55.1	50.7	46.2
	SC	34.1	32.4	30.7	33.1	31.5	29.8	32.2	30.5	28.8	31.2	29.5	27.8
	gpm	15.8	11.8	9.1	15.2	11.3	8.7	14.6	10.8	8.2	14.0	10.2	7.8
	wdp	40.9	22.7	13.7	37.8	21.0	12.3	34.8	19.0	11.1	31.9	17.1	9.8
84	TC	62.6	58.3	53.9	60.2	55.8	51.4	57.7	53.3	48.8	55.1	50.7	46.4
	SC	36.5	34.8	33.1	35.5	33.8	32.1	34.5	32.8	31.1	33.6	31.9	30.2
	gpm	15.9	11.9	9.1	15.3	11.3	8.7	14.6	10.8	8.2	14.0	10.2	7.8
	wdp	41.4	23.0	13.7	38.2	21.0	12.3	34.8	19.0	11.1	31.9	17.1	10.0
86	TC	62.6	58.2	53.9	60.1	55.7	51.5	57.6	53.1	49.0	55.0	50.7	46.8
	SC	38.8	37.1	35.4	37.9	36.1	34.5	36.9	35.1	33.6	35.9	34.2	32.7
	gpm	15.9	11.8	9.1	15.2	11.3	8.7	14.6	10.7	8.3	14.0	10.3	7.9
	wdp	41.4	22.7	13.5	37.8	21.0	12.3	34.8	18.7	11.3	31.9	17.4	10.2
88	TC	62.5	58.1	54.1	60.0	55.7	52.0	57.4	53.3	49.8	54.9	51.0	47.5
	SC	41.2	39.4	37.9	40.2	38.5	37.0	39.2	37.5	36.1	38.2	36.7	35.4
	gpm	15.8	11.8	9.1	15.2	11.2	8.8	14.5	10.8	8.4	13.9	10.3	8.0
	wdp	40.9	22.7	13.7	37.8	20.7	12.6	34.4	19.0	11.5	31.5	17.4	10.4
90	TC	62.1	58.3	54.8	59.8	56.1	52.5	57.4	53.9	50.6	55.1	51.6	48.5
	SC	43.4	41.8	40.4	42.5	41.0	39.6	41.5	40.1	38.8	40.7	39.3	37.9
	gpm	15.7	11.8	9.2	15.1	11.3	8.8	14.5	10.9	8.5	14.0	10.5	8.2
	wdp	40.5	22.7	13.9	37.4	21.0	12.8	34.4	19.6	11.9	31.9	17.9	11.1

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	78.9	74.7	70.3	76.1	71.8	67.3	73.2	68.8	64.2	70.2	65.8	61.2
	SC	31.4	29.6	27.8	30.2	28.4	26.6	29.0	27.2	25.4	27.7	26.0	24.2
	gpm	20.0	15.1	11.9	19.3	14.6	11.4	18.6	13.9	10.8	17.8	13.4	10.3
	wdp	36.8	21.0	13.0	34.2	19.5	11.9	31.6	17.8	10.8	28.9	16.4	9.8
76	TC	78.9	74.8	70.4	76.1	71.8	67.4	73.2	68.9	64.4	70.3	65.9	61.4
	SC	34.0	32.3	30.5	32.8	31.1	29.3	31.6	29.9	28.1	30.4	28.7	26.9
	gpm	20.0	15.1	11.9	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.3
	wdp	36.8	21.0	13.0	34.2	19.5	11.9	31.6	18.0	10.9	29.2	16.4	9.8
78	TC	79.0	74.8	70.6	76.2	72.0	67.7	73.4	69.1	64.6	70.5	66.0	61.5
	SC	36.7	34.9	33.2	35.5	33.7	32.0	34.3	32.5	30.8	33.1	31.3	29.6
	gpm	20.0	15.1	11.9	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.4
	wdp	36.8	21.0	13.0	34.4	19.5	11.9	31.9	18.0	10.9	29.2	16.6	9.8
80	TC	79.1	75.0	70.6	76.3	72.0	67.6	73.5	69.1	64.6	70.5	66.1	61.5
	SC	39.3	37.6	35.8	38.2	36.4	34.6	36.9	35.2	33.4	35.7	34.0	32.2
	gpm	20.0	15.2	11.9	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.3
	wdp	36.5	21.0	13.0	34.4	19.5	11.9	31.9	18.0	10.9	29.2	16.6	9.8
82	TC	79.2	75.0	70.7	76.3	72.1	67.6	73.5	69.1	64.6	70.5	66.1	61.6
	SC	42.0	40.2	38.4	40.8	39.0	37.2	39.6	37.8	36.0	38.4	36.6	34.8
	gpm	20.0	15.2	11.9	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.4
	wdp	36.8	21.3	13.1	34.2	19.5	11.9	31.9	18.0	10.9	29.9	16.4	10.0
84	TC	79.2	74.9	70.8	76.3	72.1	68.0	73.3	69.1	65.2	70.3	66.2	62.2
	SC	44.6	42.8	41.0	43.4	41.6	39.9	42.1	40.4	38.7	40.9	39.2	37.5
	gpm	20.0	15.2	11.9	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.4
	wdp	36.8	21.3	13.1	34.2	19.5	11.9	31.9	18.0	10.9	29.8	16.6	10.1
86	TC	79.2	75.1	71.7	76.3	72.6	69.1	73.6	69.9	66.4	70.8	67.3	63.6
	SC	47.2	48.0	46.4	48.5	46.9	45.3	47.3	45.7	44.2	46.1	44.6	43.1
	gpm	20.0	15.2	12.0	19.3	14.7	11.5	18.6	14.1	11.1	17.8	13.5	10.7
	wdp	36.8	21.3	13.1	34.2	19.7	12.1	31.6	18.2	11.2	29.2	16.8	10.4
88	TC	79.1	75.4	71.7	76.3	72.6	69.1	73.6	69.9	66.4	70.8	67.3	63.6
	SC	52.3	50.8	49.2	51.2	49.6	48.1	50.0	48.5	47.0	48.9	47.4	45.9
	gpm	20.0	15.3	12.1	19.3	14.7	11.6	18.6	14.2	11.2	17.9	13.7	10.7
	wdp	36.8	21.5	13.5	34.2	19.9	12.4	31.9	18.4	11.6	29.4	17.2	10.6
90	TC	79.1	75.1	71.7	76.3	72.6	69.1	73.6	69.9	66.4	70.8	67.3	63.6
	SC	52.3	50.8	49.2	51.2	49.6	48.1	50.0	48.5	47.0	48.9	47.4	45.9
	gpm	20.0	15.3	12.1	19.3	14.7	11.6	18.6	14.2	11.2	17.9	13.7	10.7
	wdp	36.8	21.5	13.5	34.2	19.9	12.4	31.9	18.4	11.6	29.4	17.2	10.6

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10

# 1500 CFM - Standard Capacity (73° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	68.9	64.6	60.2	66.4	62.1	57.6	63.9	59.5	55.1	61.4	57.0	52.5
	SC	23.5	21.8	20.2	22.5	20.9	19.3	21.6	19.9	18.4	20.6	19.0	17.4
	gpm	17.4	13.1	10.2	16.8	12.6	9.7	16.1	12.0	9.3	15.5	11.5	8.8
76	wpd	49.8	28.1	16.9	46.3	25.8	15.4	42.6	23.6	14.2	39.4	21.6	12.8
	TC	68.8	64.5	60.1	66.4	62.0	57.6	63.9	59.5	55.1	61.4	56.9	52.5
	SC	26.0	24.3	22.7	25.0	23.4	21.8	24.1	22.5	20.9	23.2	21.5	19.9
78	gpm	17.4	13.1	10.2	16.8	12.6	9.7	16.1	12.0	9.3	15.5	11.5	8.8
	wpd	49.8	28.1	16.9	46.3	25.8	15.4	42.6	23.6	14.2	39.4	21.6	12.8
	TC	68.8	64.5	60.2	66.3	62.0	57.6	63.9	59.5	55.1	61.4	57.0	52.6
80	SC	28.4	26.8	25.1	27.5	25.8	24.2	26.5	24.9	23.3	25.6	23.9	22.4
	gpm	17.4	13.1	10.2	16.8	12.6	9.7	16.1	12.0	9.3	15.5	11.6	8.9
	wpd	49.8	28.1	16.9	46.3	25.8	15.4	42.6	23.6	14.2	39.4	21.8	13.0
82	TC	69.0	64.7	60.4	66.5	62.3	57.9	64.1	59.8	55.4	61.6	57.2	52.8
	SC	30.9	29.2	27.6	29.9	28.3	26.7	29.0	27.4	25.7	28.0	26.4	24.8
	gpm	17.4	13.1	10.2	16.8	12.6	9.8	16.2	12.1	9.4	15.6	11.6	8.9
84	wpd	49.8	28.1	17.1	46.3	26.1	15.6	43.0	23.9	14.4	39.8	21.8	13.0
	TC	69.2	64.9	60.7	66.8	62.5	58.1	64.3	60.0	55.6	61.8	57.4	53.0
	SC	33.3	31.7	30.0	32.4	30.7	29.1	31.4	29.8	28.2	30.5	28.9	27.2
86	gpm	17.5	13.2	10.2	16.9	12.6	9.8	16.2	12.3	9.4	15.7	11.6	8.9
	wpd	50.3	28.4	17.1	46.8	26.1	15.9	43.4	24.3	14.4	40.2	22.1	13.0
	TC	69.4	65.2	60.8	67.0	62.7	58.3	64.5	60.2	55.8	62.0	57.6	53.1
88	SC	35.8	34.1	32.4	34.8	33.2	31.5	33.9	32.2	30.6	32.9	31.3	29.6
	gpm	17.6	13.3	10.2	17.0	12.7	9.8	16.4	12.2	9.4	15.7	11.7	9.0
	wpd	50.7	28.8	17.1	47.2	26.5	15.9	43.8	24.3	14.4	40.5	22.4	13.2
90	TC	69.7	65.3	60.9	67.2	62.9	58.3	64.7	60.3	55.8	62.2	57.7	53.1
	SC	38.2	36.5	34.8	37.3	35.6	33.9	36.3	34.6	32.9	35.3	33.7	32.0
	gpm	17.7	13.2	10.3	17.1	12.7	9.8	16.4	12.3	9.5	15.7	11.7	9.0
90	wpd	51.2	28.4	17.4	47.6	26.5	15.9	44.2	24.3	14.4	40.5	22.4	13.2
	TC	69.8	65.3	60.9	67.3	62.8	58.3	64.7	60.2	55.6	62.1	57.6	53.1
	SC	40.6	38.9	37.2	39.6	37.9	36.2	38.7	36.9	35.2	37.7	36.0	34.3
90	gpm	17.7	13.2	10.3	17.1	12.7	9.8	16.4	12.2	9.4	15.7	11.7	9.0
	wpd	51.2	28.4	17.4	47.6	26.5	15.9	44.2	24.3	14.4	40.5	22.4	13.2
	TC	69.6	65.2	60.7	67.2	62.7	58.3	64.6	60.1	55.9	62.0	57.5	53.4
90	SC	42.9	41.2	39.5	42.0	40.2	38.6	41.0	39.3	37.7	40.0	38.3	36.8
	gpm	17.6	13.2	10.2	17.1	12.7	9.8	16.4	12.2	9.5	15.7	11.6	9.0
	wpd	50.7	28.4	17.1	47.6	26.5	15.9	43.8	24.3	14.6	40.5	22.1	13.2

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	87.8	83.4	79.0	84.9	80.6	76.1	82.0	77.6	73.0	79.0	74.5	69.9
	SC	31.0	29.2	27.4	29.8	28.0	26.2	28.6	26.8	25.0	27.3	25.6	23.8
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.3	20.0	15.1	11.8
76	wpd	45.3	26.1	16.4	42.4	24.6	15.2	39.5	22.6	13.9	36.8	20.8	12.8
	TC	87.6	83.4	79.0	84.8	80.4	76.0	81.9	77.5	72.9	78.9	74.4	69.8
	SC	33.6	31.8	30.0	32.4	30.6	28.8	31.2	29.4	27.6	30.0	28.2	26.4
78	gpm	22.1	16.9	13.4	21.5	16.3	12.9	20.8	15.6	12.3	20.0	15.1	11.8
	wpd	44.7	26.1	16.4	42.4	24.3	15.2	39.5	22.4	13.9	36.5	20.8	12.8
	TC	87.5	83.3	78.9	84.8	80.4	76.0	81.8	77.4	73.0	78.9	74.4	69.9
80	SC	36.2	34.5	32.7	35.0	33.3	31.5	33.8	32.0	30.3	32.6	30.9	29.1
	gpm	22.1	16.9	13.4	21.5	16.3	12.9	20.8	15.6	12.3	20.0	15.1	11.8
	wpd	45.0	26.3	16.4	42.1	24.3	15.2	39.5	22.6	13.9	36.8	21.0	12.8
82	TC	87.6	83.6	79.2	84.9	80.6	76.2	81.9	77.6	73.1	79.1	74.6	70.1
	SC	41.5	39.8	38.0	40.3	38.6	36.8	39.1	37.4	35.6	37.9	36.2	34.4
	gpm	22.2	16.9	13.4	21.4	16.3	12.9	20.8	15.7	12.3	20.0	15.1	11.8
84	wpd	45.0	26.3	16.4	42.1	24.3	15.2	39.5	22.6	13.9	36.5	20.8	12.8
	TC	87.9	83.7	79.3	85.0	80.7	76.3	82.1	77.7	73.2	79.1	74.7	70.0
	SC	44.2	42.5	40.7	43.0	41.2	39.5	41.8	40.0	38.2	40.6	38.8	37.0
86	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.4	20.0	15.1	11.8
	wpd	45.3	26.3	16.6	42.4	24.6	15.2	39.5	22.6	13.9	36.5	21.0	12.8
	TC	87.9	83.7	79.3	85.0	80.7	76.3	82.1	77.6	73.3	79.0	74.6	70.2
88	SC	46.8	45.1	43.3	45.6	43.9	42.1	44.4	42.6	40.8	43.2	41.4	39.7
	gpm	22.2	16.9	13.4	21.5	16.3	12.9	20.8	15.7	12.4	20.0	15.1	11.9
	wpd	45.3	26.3	16.6	42.4	24.6	15.2	39.5	22.6	13.9	36.5	21.0	13.0
90	TC	87.9	83.6	79.3	84.9	80.6	76.3	82.0	77.7	73.5	78.9	74.7	70.7
	SC	52.0	50.2	48.5	50.8	49.0	47.3	49.5	47.8	46.2	48.3	46.6	45.1
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.4	20.0	15.1	12.0
90	wpd	45.3	26.3	16.4	42.4	24.6	15.2	39.5	22.6	13.9	36.5	21.0	13.1

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	TR	8	10	12	TR	8	10	12
74	TC	102.9	100.8	98.3	100.0	97.7	95.2	97.1	94.7	92.0	94.0	91.5	88.7
	SC	41.7	40.6	39.3	40.2	39.0	37.7	38.7	37.5	36.2	37.2	35.9	34.6
	gpm	26.0	20.4	16.6	25.4	19.8	16.1	24.7	19.1	15.5	23.9	18.5	15.0
76	wpd	61.8	38.1	25.3	58.9	35.8	23.6	55.6	33.5	22.0	52.1	31.4	20.5
	TC	102.9	100.8	98.4	100.0	97.8	95.3	97.1	94.8	92.1	94.1	91.6	88.9
	SC	44.6	43.5	42.3	43.1	42.0	40.7	41.6	40.4	39.1	40.1	38.8	37.5
78	gpm	26.0	20.5	16.6	25.3	19.8	16.1	24.7	19.2	15.6	23.9	18.6	15.0
	wpd	61.8	38.4	25.3	58.5	36.1	23.9	54.9					

# 1500 CFM - Standard Capacity (75° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	76.3	71.9	67.5	73.8	69.4	64.9	71.3	66.8	62.3	68.8	64.3	59.7
	SC	25.1	23.4	21.8	24.2	22.5	20.9	23.2	21.6	20.0	22.3	20.7	19.1
	gpm	19.3	14.6	11.4	18.7	14.0	10.9	18.1	13.6	10.5	17.4	13.0	10.1
	wpd	61.0	34.8	21.3	57.2	32.2	19.6	53.4	30.1	18.2	49.4	27.8	16.6
78	TC	76.2	71.9	67.4	73.8	69.3	64.9	71.2	66.7	62.2	68.6	64.2	59.6
	SC	27.6	26.0	24.4	26.7	25.0	23.4	25.7	24.1	22.5	24.8	23.2	21.6
	gpm	19.3	14.6	11.4	18.7	14.0	10.9	18.1	13.6	10.5	17.4	13.0	10.1
	wpd	61.0	34.8	21.3	57.2	32.2	19.6	53.4	30.1	18.2	49.4	27.8	16.6
80	TC	76.2	71.8	67.4	73.7	69.3	64.8	71.2	66.7	62.2	68.6	64.2	59.6
	SC	30.1	28.5	26.8	29.2	27.5	25.9	28.2	26.6	24.9	27.3	25.6	24.0
	gpm	19.3	14.6	11.4	18.7	14.0	10.9	18.1	13.6	10.5	17.4	13.0	10.1
	wpd	61.0	34.8	21.3	57.2	32.2	19.6	53.4	29.8	18.2	49.4	27.8	16.6
82	TC	76.2	71.8	67.5	73.8	69.4	65.0	71.3	66.9	62.5	68.8	64.3	59.9
	SC	32.5	30.8	29.2	31.6	29.9	28.3	30.6	29.0	27.4	29.7	28.1	26.5
	gpm	19.3	14.5	11.4	18.7	14.1	11.0	18.1	13.6	10.5	17.4	13.0	10.1
	wpd	61.0	34.4	21.3	57.2	32.6	19.8	53.4	30.1	18.2	49.8	27.8	16.6
84	TC	76.4	72.1	67.7	74.0	69.6	65.2	71.5	67.1	62.7	69.0	64.6	60.1
	SC	35.0	33.3	31.7	34.0	32.4	30.8	33.1	31.5	29.8	32.2	30.5	28.9
	gpm	19.4	14.6	11.4	18.8	14.0	11.0	18.1	13.6	10.6	17.4	13.1	10.2
	wpd	61.5	34.8	21.3	57.6	32.2	19.8	53.9	30.5	18.5	49.8	28.1	16.9
86	TC	76.6	72.3	67.9	74.2	69.8	65.4	71.7	67.2	62.8	69.2	64.7	60.2
	SC	37.4	35.8	34.1	36.5	34.8	33.2	35.5	33.9	32.2	34.6	33.0	31.3
	gpm	19.5	14.7	11.5	18.8	14.1	11.0	18.1	13.6	10.6	17.5	13.1	10.2
	wpd	62.0	35.1	21.6	57.6	32.6	19.8	53.9	30.1	18.5	50.3	28.1	16.9
88	TC	76.8	72.5	68.1	74.4	70.0	65.5	71.9	67.4	62.9	69.4	64.9	60.3
	SC	39.8	38.2	36.5	38.9	37.2	35.6	38.0	36.3	34.6	37.0	35.4	33.7
	gpm	19.4	14.7	11.5	18.8	14.2	11.1	18.2	13.6	10.6	17.6	13.2	10.2
	wpd	61.5	35.1	21.6	58.1	33.0	20.1	54.3	30.5	18.5	50.7	28.4	16.9
90	TC	77.0	72.7	68.2	74.6	70.1	65.6	72.1	67.5	63.0	69.5	64.9	60.3
	SC	42.3	40.6	38.9	41.3	39.6	38.0	40.4	38.7	37.0	39.4	37.7	36.1
	gpm	19.5	14.7	11.6	18.9	14.2	11.1	18.3	13.6	10.6	17.6	13.1	10.2
	wpd	62.0	35.5	21.8	58.6	33.0	20.1	54.8	30.5	18.5	50.7	28.1	16.9

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	96.8	92.6	88.1	93.9	89.6	85.1	91.1	86.6	82.0	88.1	83.6	78.9
	SC	33.2	31.4	29.6	31.9	30.2	28.4	30.8	28.9	27.2	29.5	27.8	26.0
	gpm	24.4	18.7	14.9	23.7	18.2	14.3	23.1	17.5	13.8	22.3	16.9	13.4
	wpd	54.7	32.2	20.4	51.5	30.2	18.8	49.0	28.1	17.6	45.6	26.3	16.4
78	TC	96.8	92.5	88.0	93.9	89.5	85.0	90.8	86.4	81.9	88.0	83.4	78.7
	SC	35.8	34.0	32.2	34.6	32.8	31.0	33.4	31.6	29.8	32.2	30.4	28.6
	gpm	24.4	18.7	14.9	23.7	18.2	14.3	23.0	17.5	13.8	22.3	16.9	13.3
	wpd	54.7	32.2	20.4	51.5	30.0	18.8	48.4	28.1	17.6	45.6	26.1	16.2
80	TC	96.7	92.4	88.0	93.8	89.4	85.0	90.8	86.4	81.9	87.9	83.5	78.9
	SC	34.8	36.7	34.9	37.2	35.5	33.7	36.0	34.2	32.5	34.8	33.0	31.3
	gpm	24.4	18.7	14.9	23.7	18.1	14.3	23.0	17.5	13.8	22.2	16.9	13.3
	wpd	54.7	32.2	20.4	51.5	30.0	18.8	48.4	28.1	17.6	45.6	26.1	16.2
82	TC	96.7	92.5	88.1	93.8	89.5	85.1	90.9	86.5	82.0	87.9	83.5	79.8
	SC	41.1	39.3	37.6	39.8	38.1	36.4	38.6	36.9	35.2	37.4	35.7	34.0
	gpm	24.4	18.7	14.9	23.7	18.2	14.3	23.0	17.5	13.8	22.2	16.9	13.3
	wpd	54.7	32.2	20.4	51.5	30.0	18.8	48.4	28.1	17.6	45.6	26.1	16.2
84	TC	96.8	92.6	88.2	93.9	89.6	85.2	91.0	86.6	82.1	88.0	83.6	79.0
	SC	43.7	42.0	40.2	42.5	40.8	39.0	41.3	39.6	37.8	40.1	38.6	36.6
	gpm	24.5	18.7	14.9	23.8	18.2	14.4	23.0	17.5	13.8	22.2	16.9	13.4
	wpd	55.1	32.2	20.4	51.8	30.2	19.0	48.7	28.4	17.6	45.3	26.3	16.4
86	TC	96.9	92.7	88.3	94.1	89.7	85.2	91.0	86.7	82.2	88.1	83.6	79.0
	SC	46.4	44.6	42.9	45.2	43.4	41.7	43.9	42.2	40.5	42.7	41.0	39.3
	gpm	24.5	18.8	14.9	23.8	18.2	14.4	23.0	17.6	13.8	22.2	16.9	13.4
	wpd	55.1	32.4	20.4	51.8	30.2	19.0	48.7	28.4	17.8	45.6	26.3	16.4
88	TC	97.0	92.7	88.3	94.1	89.8	85.3	91.1	86.7	82.2	88.1	83.7	79.0
	SC	49.0	47.3	45.5	47.8	46.1	44.3	46.6	44.9	43.1	45.4	43.6	41.9
	gpm	24.5	18.8	14.9	23.8	18.2	14.4	23.0	17.6	13.9	22.3	16.9	13.4
	wpd	55.1	32.4	20.4	51.8	30.2	19.0	48.7	28.4	17.8	45.6	26.3	16.4
90	TC	97.0	92.8	88.3	94.1	89.8	85.2	91.2	86.7	82.1	88.1	83.6	79.0
	SC	51.6	49.9	48.1	50.4	48.7	46.9	49.2	47.5	45.7	48.0	46.2	44.5
	gpm	24.6	18.8	14.9	23.9	18.2	14.3	23.0	17.6	13.8	22.3	16.9	13.4
	wpd	55.5	32.4	20.4	52.2	30.5	18.8	48.7	28.4	17.6	45.6	26.3	16.4

## 5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	112.7	110.6	108.2	109.8	107.6	105.1	106.8	104.6	101.9	103.9	101.4	98.7

# 2000 CFM - Standard Capacity (61° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	39.3	36.3	32.6	37.3	34.5	31.0	35.4	32.8	29.3	33.6	31.2	27.8
	SC	34.4	32.9	30.4	33.5	31.8	29.2	32.6	30.8	28.2	31.7	29.9	26.9
	gpm	9.9	7.4	5.5	9.5	7.0	5.2	9.0	6.7	5.0	8.5	6.3	4.7
	wpd	16.1	8.9	5.0	14.6	8.0	4.4	13.2	7.3	4.0	11.9	6.5	3.5
76	TC	41.0	38.5	35.6	39.3	37.0	34.1	37.6	35.5	31.5	36.1	34.1	30.1
	SC	38.1	36.4	34.2	37.2	35.3	33.0	36.1	34.4	31.1	35.1	33.2	29.7
	gpm	10.4	7.8	6.0	9.9	7.4	5.7	9.5	7.2	5.4	9.1	6.9	5.0
	wpd	17.7	10.0	6.0	16.1	9.1	5.4	14.9	8.5	4.7	13.5	7.8	4.2
78	TC	43.3	41.1	38.7	41.7	39.7	36.4	40.3	37.7	34.9	38.6	36.3	33.5
	SC	41.6	39.9	37.7	40.6	38.7	36.0	39.5	37.3	34.5	38.1	35.9	33.0
	gpm	10.9	8.3	6.5	10.5	8.1	6.1	10.2	7.7	5.9	9.8	7.4	5.7
	wpd	19.6	11.3	6.9	18.2	10.6	6.1	16.9	9.6	5.7	15.6	8.9	5.2
80	TC	45.9	43.5	41.1	44.3	42.1	39.7	42.9	40.6	38.2	41.5	39.2	36.8
	SC	45.0	42.9	40.6	43.7	41.5	39.3	42.3	40.1	37.7	40.9	38.7	36.3
	gpm	11.6	8.8	7.0	11.2	8.5	6.7	10.9	8.2	6.4	10.5	8.0	6.2
	wpd	22.1	12.8	8.0	20.7	11.9	7.3	19.3	11.1	6.8	17.9	10.4	6.3
82	TC	48.6	46.3	44.0	47.1	44.9	42.7	45.7	43.5	41.3	44.3	42.1	39.8
	SC	47.9	45.7	43.5	46.5	44.4	42.1	45.1	43.0	40.7	43.8	41.6	39.3
	gpm	12.3	9.4	7.4	11.9	9.1	7.2	11.6	8.8	7.0	11.2	8.5	6.7
	wpd	24.9	14.4	9.1	23.3	13.7	8.5	21.8	12.8	8.0	20.7	11.9	7.4
84	TC	51.4	49.2	46.9	50.0	47.8	45.5	48.6	46.4	44.1	47.2	45.0	42.7
	SC	50.8	48.5	46.3	49.4	47.1	44.9	48.0	45.8	43.6	46.6	44.4	42.2
	gpm	13.0	9.9	7.9	12.6	9.7	7.7	12.3	9.4	7.4	11.9	9.1	7.2
	wpd	27.8	16.1	10.2	26.1	15.4	9.6	24.9	14.4	9.1	23.3	13.7	8.5
86	TC	54.3	52.0	49.8	52.9	50.6	48.4	51.5	49.2	47.0	50.0	47.8	45.6
	SC	53.6	51.4	49.2	52.2	50.0	47.8	50.8	48.6	46.4	49.4	47.2	45.0
	gpm	13.7	10.5	8.5	13.4	10.2	8.1	13.0	9.9	7.9	12.7	9.7	7.7
	wpd	30.8	18.2	11.7	29.4	17.1	10.8	27.8	16.1	10.2	26.5	15.4	9.6
88	TC	57.1	54.9	52.7	55.7	53.5	51.3	54.3	52.1	49.9	52.9	50.7	48.5
	SC	56.4	54.2	52.0	55.0	52.8	50.6	53.6	51.4	49.2	52.2	50.0	47.9
	gpm	14.5	11.1	8.9	14.1	10.9	8.7	13.8	10.5	8.5	13.4	10.2	8.2
	wpd	34.4	20.1	13.0	32.6	19.3	12.3	31.2	18.2	11.7	29.4	17.1	11.1
90	TC	60.0	57.8	55.6	58.6	56.4	54.2	57.1	55.0	52.8	55.7	53.5	51.4
	SC	59.2	57.0	54.8	57.8	55.6	53.4	56.4	54.2	52.0	55.0	52.9	50.7
	gpm	15.2	11.7	9.4	14.9	11.4	9.1	14.5	11.2	8.9	14.1	10.9	8.7
	wpd	37.8	22.4	14.4	36.3	21.3	13.7	34.4	20.4	13.0	32.6	19.3	12.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	52.3	47.9	43.2	49.6	45.2	40.9	46.8	42.8	38.9	44.2	40.5	32.9
	SC	42.6	40.5	38.1	41.4	39.2	36.8	40.2	38.1	35.7	38.9	36.8	32.5
	gpm	13.3	9.7	7.3	12.5	9.1	6.9	11.9	8.6	6.6	11.2	8.2	5.5
	wpd	16.2	8.6	4.9	14.4	7.6	4.4	13.0	6.8	4.0	11.6	6.2	2.8
76	TC	53.8	50.3	46.5	51.2	47.8	44.4	48.7	45.8	39.1	46.5	43.8	37.2
	SC	46.6	44.7	42.5	45.4	43.6	41.4	44.2	42.4	38.6	43.1	41.3	36.8
	gpm	13.6	10.2	7.8	12.9	9.7	7.5	12.3	9.3	6.6	11.7	8.9	6.3
	wpd	17.0	9.5	5.6	15.4	8.6	5.1	13.9	7.9	4.0	12.6	7.2	3.6
78	TC	55.6	53.0	49.8	53.4	51.0	45.0	51.3	49.1	43.3	49.3	45.3	41.5
	SC	50.7	49.1	47.1	49.6	48.1	44.5	48.5	46.9	42.8	47.4	44.7	40.9
	gpm	14.1	10.7	8.4	13.5	10.3	7.6	13.0	9.9	7.3	12.5	9.1	7.0
	wpd	18.2	10.6	6.5	16.8	9.8	5.3	15.6	9.0	4.9	14.2	7.6	4.5
80	TC	58.0	56.0	50.8	56.0	52.5	49.0	53.2	50.8	47.3	51.5	49.1	45.5
	SC	55.0	53.5	50.2	53.9	51.9	48.4	52.6	50.2	46.7	50.9	48.5	44.9
	gpm	14.7	11.3	8.6	14.2	10.7	8.3	13.5	10.3	8.0	13.0	9.9	7.7
	wpd	19.9	11.7	6.7	18.4	10.4	6.3	16.8	9.7	5.8	15.6	9.0	5.4
82	TC	60.0	57.8	54.7	58.3	56.1	52.9	56.6	54.5	51.2	54.9	52.8	49.5
	SC	59.2	57.1	54.0	57.6	55.4	52.3	55.9	53.8	50.6	54.3	52.1	48.9
	gpm	15.2	11.7	9.2	14.8	11.3	9.0	14.3	11.1	8.6	13.9	10.7	8.4
	wpd	21.3	12.6	7.8	20.1	11.7	7.4	18.8	11.2	6.8	17.8	10.4	6.5
84	TC	63.3	61.2	58.4	61.6	59.6	56.7	60.0	57.9	55.0	58.3	56.2	53.4
	SC	62.5	60.5	57.7	60.9	58.8	56.0	59.3	57.2	54.3	57.6	55.5	52.7
	gpm	16.0	12.4	9.9	15.6	12.1	9.6	15.2	11.7	9.3	14.8	11.4	9.0
	wpd	23.4	14.0	8.9	22.2	13.3	8.5	21.3	12.6	7.9	20.1	11.9	7.5
86	TC	66.7	64.6	62.2	65.0	63.0	60.5	63.3	61.3	58.8	61.7	59.6	57.1
	SC	65.9	63.9	61.4	64.2	62.2	59.8	62.6	60.5	58.1	60.9	58.9	56.4
	gpm	16.9	13.1	10.5	16.5	12.8	10.2	16.0	12.5	9.9	15.6	12.1	9.6
	wpd	26.1	15.8	10.1	24.8	15.0	9.5	23.4	14.2	9.0	22.2	13.3	8.5
88	TC	70.1	68.0	65.9	68.4	66.4	64.2	66.7	64.7	62.5	65.0	63.0	60.8
	SC	69.2	67.2	65.1	67.6	65.6	63.4	65.9	63.9	61.8	64.2	62.2	60.1
	gpm	17.8	13.8	11.2	17.3	13.4	10.8	16.9	13.1	10.6	16.5	12.8	10.3
	wpd	28.9	17.4	11.4	27.3	16.6	10.8	26.1	15.8	10.3	24.8	15.0	9.7
90	TC	73.4	71.4	69.3	71.8	69.8	67.6	70.1	68.1	65.9	68.4	66.4	64.3
	SC	72.5	70.6	68.4	70.9	68.6	66.8	69.2	67.3	65.1	67.6	65.6	63.5
	gpm	18.6	14.5	11.6	18.2	14.2	11.4	17.8	13.8	11.1	17.3	14.8	9.9
	wpd	31.6	19.3	12.4	30.2	18.4	11.9	28.9	17.6	11.2	27.3	16.6	10.8

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	46.3	42.3	38.4	43.8	39.9	36.3	41.2	37.5	34.5	38.8	35.5	3

# 2000 CFM - Standard Capacity (63° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	43.9	39.8	34.7	41.3	37.5	32.7	38.9	35.0	30.5	36.5	33.0	28.6
	SC	32.9	31.1	28.7	31.8	30.0	27.8	30.8	29.0	26.6	29.8	28.0	25.8
	gpm	11.1	8.1	5.9	10.5	7.6	5.5	9.8	7.1	5.1	9.2	6.7	4.8
	wpd	20.1	10.6	5.7	17.9	9.5	5.0	15.9	8.3	4.3	13.9	7.3	3.8
76	TC	44.8	41.1	37.1	42.4	38.9	35.2	40.2	36.9	33.4	37.9	35.0	31.6
	SC	36.3	34.5	32.5	35.3	33.4	31.5	34.3	32.7	30.6	33.2	31.7	29.4
	gpm	11.3	8.3	6.3	10.8	7.9	6.0	10.2	7.4	5.7	9.6	7.1	5.4
	wpd	21.0	11.3	6.5	19.0	10.2	5.8	16.9	9.1	5.2	15.1	8.3	4.7
78	TC	46.0	42.7	39.7	43.7	40.8	37.9	41.7	39.0	36.3	39.8	37.3	34.6
	SC	39.7	38.0	36.2	38.7	37.1	35.3	37.7	36.1	34.1	36.8	35.1	33.2
	gpm	11.6	8.6	6.7	11.0	8.2	6.4	10.5	7.9	6.1	10.0	7.5	5.8
	wpd	22.1	12.1	7.4	19.8	11.1	6.8	18.2	10.2	6.1	16.4	9.3	5.5
80	TC	47.4	44.7	42.3	45.5	43.0	40.7	43.7	41.4	39.1	42.0	39.8	37.7
	SC	43.1	41.5	39.9	42.3	40.6	38.8	41.2	39.5	37.8	40.3	38.6	36.7
	gpm	12.0	9.1	7.1	11.5	8.7	6.9	11.1	8.4	6.6	10.6	8.1	6.4
	wpd	23.6	13.5	8.3	21.6	12.3	7.8	20.1	11.5	7.1	18.5	10.6	6.6
82	TC	49.3	47.0	44.8	47.6	45.5	43.4	46.1	44.0	41.3	44.6	42.2	39.9
	SC	46.7	45.0	43.4	45.8	44.1	42.2	44.9	43.0	40.8	43.7	41.6	39.4
	gpm	12.5	9.5	7.5	12.1	9.2	7.4	11.6	8.9	7.0	11.3	8.5	6.7
	wpd	25.5	14.9	9.3	23.9	13.9	8.9	22.1	13.0	8.0	21.0	11.9	7.4
84	TC	51.6	49.6	47.6	50.2	47.8	45.6	48.7	46.5	44.2	47.3	45.1	42.8
	SC	50.2	48.4	46.5	49.2	47.2	45.0	48.1	45.9	43.6	46.7	44.5	42.2
	gpm	13.1	10.0	8.1	12.7	9.7	7.7	12.3	9.5	7.4	11.9	9.1	7.2
	wpd	28.1	16.4	10.6	26.5	15.4	9.6	24.9	14.6	9.1	23.3	13.7	8.5
86	TC	54.4	52.1	49.9	53.0	50.7	48.5	51.5	49.3	47.1	50.1	47.9	45.7
	SC	53.7	51.5	49.3	52.3	50.1	47.9	50.9	48.7	46.5	49.5	47.3	45.1
	gpm	13.8	10.5	8.5	13.4	10.2	8.2	13.1	10.0	8.0	12.7	9.7	7.7
	wpd	31.2	18.2	11.7	29.4	17.1	11.1	28.1	16.4	10.4	26.5	15.4	9.6
88	TC	57.2	55.0	52.8	55.8	53.6	51.4	54.4	52.2	50.0	53.0	50.8	48.6
	SC	56.5	54.3	52.1	55.1	52.9	50.7	53.7	51.5	49.3	52.3	50.1	48.0
	gpm	14.5	11.2	8.9	14.2	10.9	8.7	13.8	10.5	8.5	13.4	10.3	8.2
	wpd	34.4	20.4	13.0	33.0	19.3	12.3	31.2	18.2	11.7	29.4	17.4	11.1
90	TC	60.1	57.9	55.7	58.7	56.5	54.3	57.3	55.1	52.9	55.8	53.6	51.5
	SC	59.3	57.1	54.9	57.9	55.7	53.6	56.5	54.3	52.2	55.1	53.0	50.8
	gpm	15.2	11.7	9.4	14.9	11.5	9.1	14.5	11.2	8.9	14.2	10.9	8.7
	wpd	37.8	22.4	14.4	36.3	21.6	13.7	34.4	20.4	13.0	33.0	19.3	12.3

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	67.0	61.3	55.4	63.5	57.9	51.8	59.9	54.3	48.5	56.5	50.9	45.3
	SC	45.0	42.5	39.8	43.5	41.0	38.3	41.9	39.4	36.8	40.4	38.0	35.5
	gpm	17.0	12.4	9.4	16.1	11.7	8.7	15.2	11.0	8.2	14.3	10.3	7.6
	wpd	18.9	10.1	5.8	17.0	9.0	5.0	15.1	7.9	4.4	13.4	6.9	3.8
76	TC	67.6	49.1	44.5	64.2	59.5	54.1	60.9	56.1	51.0	57.7	52.9	48.1
	SC	48.7	35.9	33.9	47.2	45.1	42.6	45.7	43.6	41.3	44.3	42.2	40.0
	gpm	17.1	9.9	7.5	16.2	12.0	9.1	15.4	11.4	8.6	14.6	10.7	8.1
	wpd	19.1	6.5	3.7	17.2	9.5	5.5	15.5	8.5	4.8	14.0	7.6	4.3
78	TC	68.4	64.2	59.5	65.3	61.0	56.5	62.1	58.0	53.8	58.9	55.0	51.3
	SC	52.5	50.6	48.4	51.1	49.1	47.0	49.6	47.8	45.8	48.3	46.5	44.7
	gpm	17.3	13.0	10.0	16.5	12.3	9.5	15.7	11.7	9.1	14.9	11.1	8.7
	wpd	19.7	11.1	6.6	17.9	10.0	6.0	16.2	9.0	5.4	14.6	8.1	4.9
80	TC	69.6	51.5	48.0	66.5	63.0	59.2	63.4	60.2	56.8	60.6	57.5	54.5
	SC	56.4	42.1	40.5	55.0	53.4	51.5	53.6	52.1	50.4	52.4	50.9	49.3
	gpm	17.6	10.4	8.1	16.8	12.7	10.0	16.0	12.2	9.6	15.3	11.6	9.2
	wpd	20.4	7.1	4.3	18.6	10.7	6.6	16.9	9.7	6.1	15.4	8.9	5.6
82	TC	70.8	67.8	64.4	67.9	65.1	62.1	65.2	62.6	60.0	62.5	60.3	57.9
	SC	60.3	58.9	57.2	59.0	57.6	55.1	58.7	56.5	54.0	59.5	57.4	55.0
	gpm	18.0	13.7	10.9	17.2	13.1	10.5	16.5	12.7	10.1	15.9	12.2	9.8
	wpd	21.2	12.3	7.8	19.5	11.3	7.2	17.9	10.5	6.7	16.5	9.7	6.3
84	TC	72.3	70.0	67.3	69.7	67.6	65.2	67.1	65.4	63.2	64.8	63.3	44.8
	SC	64.4	63.2	61.8	63.1	62.1	60.7	61.9	61.0	59.6	60.9	59.9	44.2
	gpm	18.3	14.2	11.4	17.6	13.7	11.0	17.0	13.2	10.7	16.4	12.8	7.5
	wpd	21.9	13.2	8.5	20.4	12.3	7.9	18.9	11.5	7.5	17.5	10.8	3.7
86	TC	74.1	72.5	70.4	71.7	70.4	68.6	68.5	63.7	67.7	64.7	61.9	51.9
	SC	68.6	66.4	67.4	66.6	65.4	66.3	65.5	62.9	65.3	63.9	61.1	51.1
	gpm	18.8	14.7	11.9	18.8	14.6	11.7	18.2	14.3	11.5	17.7	13.9	11.1
	wpd	23.1	14.1	9.2	21.7	13.4	8.9	20.4	12.6	7.6	19.3	11.3	7.1
88	TC	76.4	75.4	71.0	74.4	71.9	69.3	71.7	70.2	67.6	70.0	68.5	65.8
	SC	72.9	72.2	70.1	71.9	71.0	68.5	70.8	69.3	66.7	69.1	67.6	65.0
	gpm	19.4	15.3	11.9	18.8	14.6	11.7	18.2	14.3	11.5	17.7	13.9	11.1
	wpd	24.7	15.4	9.4	23.3	14.0	9.0	21.7	13.4	8.6	20.6	12.6	8.1
90	TC	78.6	77.2	74.9	76.9	75.5	73.1	75.2	73.7	71.4	73.5	72.0	69.6
	SC	77.7	76.2	73.9	76.0	74.5	72.2	74.3	72.8	70.5	72.5	71.1	68.8
	gpm	20.0	15.6	12.7	19.5	15.3	12.3	19.1	15.0	12.0	18.6	14.6	11.7
	wpd	26.1	16.0	10.5	24.9	15.4	10.0	23.9	14.7	9.5	22.7	14.0	9.0

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	58.9	54.1	47.7	55.7								

# 2000 CFM - Standard Capacity (65° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	50.8	45.6	40.5	47.9	42.8	37.7	44.9	40.0	34.7	42.0	37.4	31.8
	SC	32.0	29.8	27.7	30.8	28.7	26.5	29.6	27.6	25.4	28.5	26.5	24.1
	gpm	12.9	9.2	6.8	12.1	8.7	6.4	11.4	8.1	5.9	10.6	7.5	5.4
	wpd	27.1	13.9	7.6	23.9	12.3	6.6	21.3	10.6	5.7	18.5	9.3	4.7
76	TC	50.6	45.9	41.6	47.8	43.4	38.9	45.0	40.8	36.3	42.5	38.3	33.6
	SC	34.9	33.0	31.1	33.8	31.9	29.9	32.8	30.9	28.8	31.7	29.8	27.7
	gpm	12.8	9.3	7.0	12.1	8.8	6.6	11.4	8.2	6.1	10.7	7.8	5.7
	wpd	26.8	14.2	8.0	23.9	12.6	7.1	21.3	11.1	6.1	18.7	9.8	5.2
78	TC	51.0	46.8	42.9	48.4	44.4	40.4	45.9	41.9	38.3	43.5	39.6	36.1
	SC	38.2	36.3	34.4	37.1	35.3	33.4	36.1	34.3	32.4	35.0	33.2	31.5
	gpm	12.9	9.5	7.2	12.3	9.0	6.8	11.6	8.5	6.4	11.0	8.1	6.1
	wpd	27.1	14.6	8.5	24.6	13.2	7.6	22.1	11.9	6.8	19.8	10.6	6.1
80	TC	51.8	47.9	44.4	49.4	45.6	42.4	47.1	43.4	40.4	44.8	41.4	38.7
	SC	41.5	39.7	37.8	40.4	38.6	37.1	39.5	37.6	36.1	38.4	36.9	35.1
	gpm	13.1	9.7	7.5	12.5	9.2	7.1	11.9	8.8	6.8	11.3	8.4	6.5
	wpd	28.1	15.4	9.3	25.5	13.9	8.3	23.3	12.6	7.6	21.0	11.5	6.9
82	TC	52.9	49.3	46.3	50.6	47.3	44.5	48.3	45.3	42.7	46.2	43.5	41.0
	SC	44.9	43.0	41.6	43.8	42.2	40.6	42.9	41.3	39.7	41.9	40.3	38.6
	gpm	13.3	10.0	7.8	12.8	9.6	7.5	12.2	9.1	7.2	11.7	8.8	6.9
	wpd	29.1	16.4	10.0	26.8	15.1	9.3	24.3	13.7	8.5	22.4	12.8	7.8
84	TC	54.2	51.0	48.4	52.0	49.2	46.7	49.9	47.4	45.1	48.1	45.8	43.6
	SC	48.3	46.7	44.9	47.3	45.7	44.1	46.4	44.8	43.0	45.4	43.7	42.1
	gpm	13.7	10.3	8.1	13.2	10.0	7.9	12.6	9.6	7.6	12.2	9.3	7.4
	wpd	30.8	17.4	10.8	28.4	16.4	10.2	26.1	15.1	9.5	24.3	14.2	8.9
86	TC	55.6	53.0	50.8	53.8	51.4	49.2	52.0	49.8	47.7	50.5	48.3	46.4
	SC	51.7	50.3	48.4	50.8	49.2	47.6	49.9	48.3	46.4	48.8	47.2	45.3
	gpm	14.1	10.7	8.6	13.6	10.4	8.3	13.2	10.1	8.1	12.8	9.8	7.8
	wpd	32.6	18.7	12.1	30.5	17.7	11.3	28.4	16.6	10.6	26.8	15.6	10.0
88	TC	57.6	55.4	53.3	56.1	53.9	51.9	54.5	52.5	50.1	53.1	50.9	48.7
	SC	55.4	53.5	51.9	54.3	52.6	50.8	53.4	51.5	49.4	52.4	50.2	48.0
	gpm	14.6	11.2	9.0	14.2	10.9	8.8	13.8	10.6	8.5	13.5	10.3	8.2
	wpd	34.8	20.7	13.2	33.0	19.6	12.6	31.2	18.5	11.7	29.8	17.4	11.1
90	TC	60.1	58.1	55.8	58.7	56.6	54.4	57.4	55.2	53.0	56.0	53.8	51.6
	SC	58.8	57.0	55.1	57.7	55.8	53.7	56.6	54.5	52.3	55.2	53.1	50.9
	gpm	15.1	11.8	9.5	14.9	11.5	9.2	14.6	11.2	8.9	14.2	10.9	8.7
	wpd	37.4	22.7	14.6	36.3	21.6	13.9	34.8	20.4	13.0	33.0	19.3	12.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	67.4	62.1	55.4	63.8	58.5	51.6	60.3	55.2	48.0	56.7	51.7	44.1
	SC	40.5	38.2	35.3	39.0	36.7	33.8	37.5	35.3	32.3	36.0	33.9	30.7
	gpm	17.0	12.5	9.4	16.1	11.8	8.7	15.2	11.2	8.1	14.3	10.4	7.4
	wpd	26.6	14.4	8.0	23.8	12.8	7.0	21.3	11.4	6.0	18.8	10.0	5.0
76	TC	67.5	62.6	56.5	64.0	59.2	53.0	60.7	55.9	49.5	57.3	52.7	46.4
	SC	43.9	41.8	39.2	42.5	40.4	37.7	41.0	39.0	36.2	39.6	37.6	34.9
	gpm	17.1	12.7	9.5	16.2	12.0	9.0	15.4	11.3	8.4	14.5	10.7	7.8
	wpd	26.8	14.8	8.3	24.1	13.1	7.4	21.7	11.7	6.5	19.3	10.4	5.6
78	TC	67.9	63.4	57.8	64.7	60.2	54.8	61.4	57.0	51.7	58.2	54.0	48.8
	SC	47.5	45.5	43.0	46.1	44.1	41.7	44.7	42.8	40.4	43.4	41.5	39.2
	gpm	17.2	12.9	9.8	16.4	12.2	9.3	15.6	11.6	8.7	14.7	11.0	8.2
	wpd	27.1	15.2	8.8	24.6	13.7	7.9	22.2	12.3	7.0	19.9	11.1	6.2
80	TC	68.6	64.4	59.7	65.5	61.4	56.8	62.4	58.4	54.0	59.2	55.6	51.0
	SC	51.2	49.3	47.1	49.8	48.0	45.9	48.5	46.8	44.7	47.2	45.5	43.3
	gpm	17.3	13.0	10.1	16.5	12.5	9.6	15.7	11.8	9.1	15.0	11.2	8.6
	wpd	27.6	15.6	9.3	25.1	14.2	8.5	22.6	12.8	7.6	20.6	11.6	6.8
82	TC	69.6	65.7	61.8	66.5	62.9	58.9	63.6	60.2	56.2	60.7	57.4	53.9
	SC	55.0	53.2	51.3	53.6	52.0	50.0	52.4	50.7	48.8	51.1	49.5	47.8
	gpm	17.6	13.4	10.4	16.9	12.8	9.9	16.1	12.2	9.5	15.4	11.6	9.1
	wpd	28.4	16.4	10.0	26.1	15.0	9.0	23.8	13.7	8.3	21.7	12.4	7.6
84	TC	70.7	67.3	63.7	67.8	64.5	61.3	65.1	61.9	58.9	62.3	59.4	56.7
	SC	58.8	57.2	55.4	57.5	55.9	54.2	56.3	54.7	53.2	55.1	53.6	52.0
	gpm	17.9	13.7	10.7	17.2	13.0	10.3	16.5	12.5	9.9	15.8	12.1	9.5
	wpd	29.4	17.2	10.6	27.1	15.6	9.8	24.8	14.4	9.0	22.9	13.3	8.3
86	TC	72.1	68.9	66.1	69.3	66.3	63.9	66.7	64.1	61.9	64.2	61.9	59.9
	SC	62.7	61.1	59.6	61.5	60.0	58.6	60.3	58.9	57.5	59.1	57.8	56.5
	gpm	18.2	13.9	11.2	17.6	13.4	10.7	16.9	12.9	10.4	16.3	12.5	10.1
	wpd	30.5	17.8	11.4	28.4	16.6	10.6	26.3	15.4	10.0	24.3	14.4	9.3
88	TC	73.6	70.9	68.7	71.0	68.7	66.7	68.7	66.7	64.8	66.6	64.7	61.1
	SC	66.7	65.2	63.9	65.5	64.2	63.0	64.3	63.1	61.8	63.3	62.0	60.3
	gpm	18.6	14.4	11.6	17.9	13.9	11.3	17.3	13.5	10.9	16.9	13.1	10.3
	wpd	31.9	19.0	12.4	29.4	17.8	11.7	27.6	16.8	10.9	26.1	15.8	9.8
90	TC	75.5	73.4	71.4	73.3	71.4	69.6	71.2	69.5	66.2	69.4	66.7	64.6
	SC	70.7	69.5	68.2	69.7	68.4	67.0	68.6	67.2	65.4	67.5	65.9	63.8
	gpm	19.1	14.9	12.1	18.6	14.5	11.8	18.0	14.1	11.2	17.6	13.5	10.9
	wpd	33.3	20.4	13.3	31.6	19.3	12.8	29.7	18.2	11.4	28.4	16.8	10.9

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	91.1	87.6	84.0	87.0	83.5							

# 2000 CFM - Standard Capacity (67° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	58.1	53.0	47.7	55.3	50.1	44.8	52.4	47.1	41.7	49.4	44.0	38.6
	SC	31.0	29.0	26.9	29.9	27.8	25.7	28.8	26.7	24.6	27.6	25.5	23.4
	gpm	14.7	10.8	8.1	14.0	10.2	7.6	13.3	9.5	7.1	12.5	8.9	6.5
	wpd	35.1	19.0	10.6	32.2	16.9	9.5	28.8	14.9	8.1	25.5	13.0	6.9
76	TC	58.3	53.1	47.8	55.4	50.1	44.9	52.5	47.1	42.0	49.4	44.1	39.3
	SC	34.1	32.0	29.9	33.0	30.9	28.8	31.8	29.7	27.6	30.7	28.5	26.6
	gpm	14.7	10.7	8.1	14.0	10.2	7.6	13.3	9.5	7.1	12.5	8.9	6.7
	wpd	35.5	18.7	10.6	31.9	16.9	9.5	28.4	14.9	8.1	25.5	13.0	7.3
78	TC	58.3	53.0	48.1	55.3	50.1	45.4	52.3	47.3	42.9	49.2	44.5	40.2
	SC	37.2	35.0	33.0	36.0	33.9	32.0	34.8	32.7	30.9	33.6	31.7	29.9
	gpm	14.7	10.7	8.1	14.0	10.2	7.7	13.2	9.5	7.2	12.4	9.0	6.8
	wpd	35.5	18.7	10.8	31.9	16.9	9.6	28.4	14.9	8.5	25.2	13.2	7.6
80	TC	58.6	53.7	49.3	55.6	51.0	46.7	52.8	48.4	44.2	50.0	45.8	41.8
	SC	40.1	38.0	36.2	38.9	37.0	35.2	37.8	36.0	34.1	36.8	35.0	33.1
	gpm	14.8	10.9	8.3	14.1	10.3	7.9	13.3	9.8	7.4	12.6	9.3	7.1
	wpd	35.9	19.3	11.3	32.6	17.4	10.2	29.1	15.6	9.1	26.1	14.2	8.1
82	TC	58.3	53.9	50.0	55.7	51.5	47.5	53.1	49.0	45.2	50.6	46.6	43.1
	SC	43.2	41.5	39.6	42.2	40.4	38.7	41.2	39.4	37.6	40.2	38.4	36.6
	gpm	14.7	10.9	8.5	14.1	10.4	8.0	13.4	9.9	7.6	12.8	9.4	7.3
	wpd	35.5	19.6	11.7	32.6	17.7	10.4	29.4	16.1	9.5	26.8	14.4	8.7
84	TC	58.9	55.1	51.3	56.5	52.7	49.1	54.0	50.4	47.0	51.7	48.1	45.0
	SC	46.6	44.8	43.0	45.6	43.8	42.0	44.6	42.8	41.0	43.6	41.8	40.3
	gpm	14.9	11.2	8.7	14.3	10.7	8.3	13.6	10.2	8.0	13.0	9.8	7.6
	wpd	36.3	20.4	12.3	33.3	18.7	11.3	30.5	17.1	10.4	27.8	15.6	9.5
86	TC	60.0	56.4	52.9	57.7	54.0	50.9	55.4	51.9	49.0	53.0	49.9	47.2
	SC	50.0	48.2	46.5	49.0	47.3	45.7	47.9	46.3	44.7	47.0	45.5	43.9
	gpm	15.2	11.4	8.9	14.6	10.9	8.6	14.0	10.5	8.3	13.4	10.1	8.0
	wpd	37.8	21.3	13.0	34.8	19.6	12.1	32.2	18.2	11.3	29.4	16.6	10.4
88	TC	61.3	57.7	54.7	59.0	55.7	53.0	56.7	53.7	51.2	54.6	51.9	49.6
	SC	53.5	51.6	50.1	52.4	50.6	49.1	51.4	49.8	48.2	50.3	49.0	47.2
	gpm	15.5	11.6	9.2	14.9	11.2	8.9	14.3	10.9	8.7	13.8	10.5	8.4
	wpd	39.4	22.1	13.9	36.3	20.7	13.0	33.7	19.3	12.3	31.2	17.9	11.5
90	TC	62.4	59.4	56.9	60.4	57.6	55.2	58.4	55.8	53.7	56.5	54.3	52.1
	SC	56.8	55.2	53.7	55.7	54.1	52.6	54.9	53.3	51.5	53.8	52.2	50.6
	gpm	15.8	12.0	9.6	15.3	11.6	9.3	14.8	11.3	9.1	14.3	11.0	8.8
	wpd	40.9	23.6	15.1	38.2	22.1	14.2	35.9	21.0	13.5	33.7	19.8	12.8

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	86.4	81.5	74.8	82.6	77.6	70.7	78.8	73.7	66.4	74.9	69.7	62.0
	SC	44.1	42.0	39.1	42.4	40.3	37.4	40.8	38.6	35.6	39.1	37.0	33.8
	gpm	21.9	16.5	12.6	20.9	15.7	11.9	20.0	14.9	11.2	18.9	14.1	10.4
	wpd	31.4	17.9	10.4	28.7	16.2	9.4	26.1	14.6	8.3	23.5	13.1	7.1
76	TC	86.3	64.7	58.8	82.6	77.7	71.1	78.8	73.8	67.0	74.9	69.9	62.8
	SC	47.5	35.7	33.1	45.9	43.8	41.0	44.2	42.1	39.3	42.6	40.5	37.6
	gpm	21.8	13.1	9.9	20.9	15.8	12.0	20.0	15.0	11.3	19.0	14.2	10.6
	wpd	31.2	11.3	6.5	28.7	16.4	9.5	26.1	14.7	8.4	23.7	13.2	7.3
78	TC	86.3	81.6	75.7	82.6	77.9	71.7	78.8	74.1	67.8	75.0	70.4	63.8
	SC	50.9	48.9	46.3	49.3	47.3	44.7	47.7	45.7	43.1	46.0	44.1	41.4
	gpm	21.8	16.5	12.7	20.8	15.8	12.1	19.9	15.0	11.5	18.9	14.3	10.7
	wpd	31.2	17.9	10.7	28.5	16.4	9.6	25.9	14.7	8.6	23.5	13.4	7.6
80	TC	87.0	65.6	60.5	83.4	79.0	73.2	79.7	75.3	69.4	76.0	71.6	65.8
	SC	54.4	41.0	38.8	52.8	50.9	48.4	51.2	49.3	46.8	49.6	47.8	45.4
	gpm	22.0	13.3	10.2	21.1	16.0	12.3	20.1	15.2	11.7	19.2	14.5	11.1
	wpd	31.9	11.6	6.8	29.2	16.9	10.0	26.6	15.2	9.0	24.3	13.8	8.0
82	TC	86.8	82.7	77.6	83.3	79.0	74.0	79.7	75.5	70.5	76.1	72.2	67.1
	SC	58.0	56.2	54.0	56.4	54.6	52.5	54.9	53.1	51.0	53.4	51.7	49.5
	gpm	22.0	16.8	13.1	21.1	16.0	12.5	20.2	15.3	11.9	19.2	14.6	11.3
	wpd	31.6	18.4	11.2	29.2	16.9	10.3	26.8	15.4	9.2	24.3	14.0	8.4
84	TC	87.3	83.3	78.8	83.9	80.0	75.5	80.4	76.5	72.2	76.9	73.3	53.9
	SC	61.6	59.9	57.9	60.1	58.4	56.5	58.6	57.0	55.1	57.1	55.6	41.3
	gpm	22.1	16.8	13.3	21.2	16.2	12.7	20.4	15.5	12.2	19.5	14.8	9.1
	wpd	32.1	18.6	11.6	29.6	17.2	10.7	27.2	15.7	9.7	24.9	14.4	5.4
86	TC	88.0	84.3	80.3	84.6	81.1	77.0	81.3	77.8	73.8	77.9	74.5	70.8
	SC	65.4	63.7	61.9	63.8	62.3	60.5	62.4	60.9	59.1	60.9	59.5	57.8
	gpm	22.3	17.1	13.5	21.5	16.4	13.0	20.6	15.7	12.4	19.7	15.1	11.9
	wpd	32.6	19.1	12.0	30.3	17.7	11.1	27.8	16.2	10.1	25.5	14.9	9.4
88	TC	88.7	85.5	81.8	85.4	82.2	78.8	82.2	79.1	75.8	79.0	76.0	72.8
	SC	69.1	67.6	65.9	67.6	66.2	64.6	66.2	64.8	63.3	64.8	63.5	62.0
	gpm	22.4	17.3	13.8	21.6	16.7	13.3	20.8	16.0	12.8	20.0	15.4	12.3
	wpd	32.8	19.7	12.5	30.5	18.2	11.6	28.3	16.9	10.8	26.3	15.5	10.0
90	TC	89.6	86.6	83.5	86.4	83.6	80.7	83.3	80.6	77.9	80.2	77.7	75.2
	SC	72.9	71.5	70.1	71.4	70.1	68.8	70.0	68.8	67.6	68.7	66.4	64.4
	gpm	22.7	17.6	14.1	21.9	16.9	13.6	21.0	16.4	13.1	20.3	15.8	12.7
	wpd	33.8	20.2	13.1	31.4	18.8	12.2	28.9	17.5	11.3	27.0	16.4	10.5

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10</th

# 2000 CFM - Standard Capacity (69° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	65.2	60.0	54.8	62.3	57.1	51.8	59.4	54.2	48.9	56.5	51.2	45.9
	SC	29.9	27.9	25.9	28.8	26.8	24.8	27.7	25.7	23.7	26.5	24.5	22.5
	gpm	16.4	12.1	9.2	15.7	11.6	8.8	15.0	11.0	8.3	14.3	10.4	7.8
	wpd	44.2	23.9	13.9	40.5	21.8	12.6	37.0	19.8	11.3	33.7	17.7	9.8
76	TC	65.6	60.5	55.3	62.7	57.5	52.3	59.8	54.6	49.2	56.9	51.6	46.2
	SC	33.1	31.0	29.0	31.9	29.9	27.9	30.8	28.8	26.7	29.7	27.7	25.6
	gpm	16.6	12.3	9.3	15.8	11.6	8.8	15.1	11.1	8.3	14.4	10.5	7.8
	wpd	45.1	24.6	14.2	40.9	22.1	12.8	37.4	20.1	11.3	34.0	17.9	10.0
78	TC	66.0	60.8	55.4	63.1	57.8	52.4	60.1	54.7	49.3	57.1	51.7	46.2
	SC	36.2	34.1	32.0	35.1	33.0	30.9	33.9	31.8	29.8	32.8	30.7	28.6
	gpm	16.7	12.3	9.3	16.0	11.7	8.8	15.2	11.1	8.3	14.4	10.5	7.8
	wpd	45.5	24.9	14.2	41.8	22.4	12.8	37.8	20.1	11.3	34.0	17.9	10.0
80	TC	66.1	60.8	55.4	63.2	57.8	52.4	60.1	54.7	49.6	57.1	51.6	46.6
	SC	39.3	37.2	35.0	38.1	36.0	33.9	37.0	34.8	32.8	35.8	33.7	31.8
	gpm	16.7	12.3	9.4	16.0	11.7	8.8	15.2	11.1	8.4	14.4	10.5	7.9
	wpd	45.9	24.9	14.4	41.8	22.4	12.8	37.8	20.1	11.5	34.0	17.9	10.2
82	TC	66.0	60.7	55.7	63.0	57.7	52.9	60.0	54.8	50.3	56.8	52.0	47.6
	SC	42.3	40.2	38.1	41.1	39.0	37.1	40.0	37.9	36.1	38.8	36.9	35.1
	gpm	16.7	12.3	9.4	16.0	11.7	8.9	15.2	11.1	8.5	14.4	10.5	8.1
	wpd	45.9	24.9	14.4	41.8	22.4	13.0	37.8	20.1	11.9	34.0	18.2	10.6
84	TC	65.9	60.8	56.3	62.9	58.0	53.7	60.0	55.4	51.2	57.1	52.7	48.7
	SC	45.3	43.2	41.4	44.1	42.2	40.4	43.0	41.1	39.4	42.0	40.2	38.3
	gpm	16.7	12.3	9.5	15.9	11.7	9.1	15.2	11.2	8.6	14.5	10.6	8.2
	wpd	45.5	24.6	14.9	41.4	22.4	13.5	37.8	20.4	12.1	34.4	18.5	11.1
86	TC	65.7	61.4	57.3	63.1	58.8	54.9	60.5	56.4	52.4	57.8	53.9	50.0
	SC	48.3	46.5	44.7	47.3	45.5	43.7	46.3	44.5	42.8	45.3	43.5	41.8
	gpm	16.6	12.4	9.7	15.9	11.9	9.3	15.4	11.4	8.8	14.6	10.9	8.5
	wpd	45.1	25.2	15.4	41.4	23.3	14.2	38.6	21.3	12.8	34.8	19.6	11.7
88	TC	66.3	62.4	58.4	63.9	59.9	56.1	61.3	57.6	53.8	58.9	55.2	51.7
	SC	51.6	49.9	48.1	50.7	48.8	47.1	49.6	47.9	46.1	48.7	46.9	45.3
	gpm	16.7	12.6	9.8	16.1	12.2	9.5	15.5	11.6	9.1	14.9	11.2	8.8
	wpd	45.9	26.1	15.9	42.6	24.3	14.6	39.4	22.1	13.5	36.3	20.4	12.6
90	TC	67.3	63.6	59.9	65.0	61.3	57.7	62.7	58.9	55.6	60.3	56.6	53.6
	SC	55.0	53.3	51.4	54.1	52.3	50.6	53.0	51.4	49.6	52.0	50.3	48.8
	gpm	17.1	12.9	10.1	16.4	12.4	9.8	15.8	11.9	9.4	15.3	11.4	9.1
	wpd	47.6	27.1	16.6	44.2	25.2	15.6	40.9	23.3	14.4	38.2	21.3	13.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	96.8	91.9	86.8	93.1	88.1	82.7	89.3	84.2	78.5	85.4	80.2	74.1
	SC	43.6	41.5	39.3	41.9	39.8	37.6	40.3	38.2	35.9	38.7	36.5	34.1
	gpm	24.5	18.6	14.7	23.6	17.9	14.0	22.6	17.1	13.2	21.6	16.3	12.5
	wpd	39.2	22.7	14.1	36.4	21.0	12.8	33.5	19.1	11.5	30.7	17.4	10.3
76	TC	96.9	74.1	68.4	93.1	88.1	82.8	89.4	84.3	78.5	85.5	80.3	74.2
	SC	47.1	36.0	33.5	45.4	43.3	41.1	43.8	41.7	39.3	42.2	40.1	37.6
	gpm	24.5	15.0	11.5	23.5	17.8	14.0	22.7	17.1	13.2	21.6	16.3	12.5
	wpd	39.2	25.2	14.7	36.2	20.8	12.8	33.8	19.1	11.5	30.7	17.4	10.3
78	TC	97.0	92.1	87.0	93.2	88.2	82.9	89.3	84.2	78.7	85.5	80.2	74.4
	SC	50.6	48.5	46.3	48.9	46.8	44.6	47.2	45.1	42.9	45.6	43.5	41.1
	gpm	24.5	18.7	14.7	23.6	17.9	14.0	22.5	17.0	13.3	21.6	16.2	12.6
	wpd	39.5	22.9	14.1	36.4	21.0	12.9	33.3	18.9	11.6	30.7	17.2	10.4
80	TC	97.0	74.0	68.5	93.2	88.2	83.1	89.3	84.4	79.2	85.4	80.4	75.0
	SC	54.0	41.1	38.8	52.3	50.3	48.1	50.7	48.6	46.5	49.0	47.0	44.8
	gpm	24.5	15.0	11.5	23.6	17.9	14.0	22.5	17.1	13.4	21.6	16.3	12.7
	wpd	39.5	14.7	8.7	36.4	21.0	13.1	33.5	19.3	11.9	30.7	17.5	10.5
82	TC	96.9	92.2	87.6	93.2	88.5	83.7	89.4	84.7	79.8	85.5	80.8	75.8
	SC	57.4	55.4	53.4	55.8	53.8	51.8	54.1	52.2	50.2	52.5	50.6	48.5
	gpm	24.5	18.7	14.8	23.6	18.0	14.1	22.6	17.2	13.5	21.6	16.4	12.7
	wpd	39.5	22.9	14.4	36.4	21.2	13.1	33.5	19.3	11.9	30.7	17.5	10.7
84	TC	97.0	92.0	88.2	93.4	88.9	84.5	89.7	85.2	80.6	85.9	81.5	60.4
	SC	60.9	59.0	57.1	59.3	57.4	55.5	57.7	55.8	53.9	56.1	54.3	40.5
	gpm	24.5	18.8	14.9	23.7	18.0	14.3	22.7	17.3	13.6	21.7	16.5	10.2
	wpd	39.5	23.1	14.6	36.7	21.3	13.4	33.8	19.7	12.2	31.0	17.9	6.8
86	TC	97.3	93.1	88.8	93.7	89.4	85.3	90.1	85.8	81.8	86.4	82.2	78.3
	SC	64.4	62.6	60.7	62.9	61.0	59.3	61.3	59.5	57.8	59.8	58.0	56.4
	gpm	24.7	18.8	15.0	23.7	18.0	14.4	22.8	17.3	13.8	21.9	16.6	13.2
	wpd	40.0	23.3	14.7	36.9	21.3	13.5	34.2	19.7	12.5	31.4	18.1	11.5
88	TC	97.8	93.7	89.9	94.3	90.2	86.5	90.8	86.8	83.0	87.2	83.3	79.8
	SC	68.1	66.3	64.6	66.5	64.8	63.2	65.0	63.3	61.7	63.5	61.9	60.4
	gpm	24.8	19.0	15.2	23.9	18.3	14.6	23.0	17.6	14.0	22.1	16.8	13.5
	wpd	40.3	23.7	15.1	37.4	21.9	14.0	34.7	20.2	12.9	32.1	18.6	11.9
90	TC	98.4	94.6	90.9	95.0	91.2	87.7	91.4	87.8	84.4	88.0	84.5	81.1
	SC	71.7	70.0	68.4	70.2	68.6	67.1	68.7	67.1	65.7	67.2	65.7	64.3
	gpm	24.9	19.2	15.4	24.1	18.4	14.8	23.2	17.8	14.3	22.3	17.2	13.7
	wpd	40.8	24.1	15.5	37.9	22.3	14.4	35.2	20.8	13.4	32.6	19.3	12.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8							

# 2000 CFM - Standard Capacity (71° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	72.9	67.6	62.3	70.0	64.6	59.3	67.0	61.7	56.2	64.1	58.6	53.1
	SC	28.8	26.7	24.8	27.6	25.6	23.6	26.5	24.5	22.5	25.4	23.4	21.4
	gpm	18.5	13.6	10.5	17.7	13.0	10.0	16.9	12.5	9.5	16.2	11.9	8.9
	wpd	55.7	30.5	18.2	51.2	27.8	16.4	46.8	25.5	14.6	43.0	23.0	13.0
76	TC	73.1	67.8	62.5	70.2	64.8	59.6	67.2	61.9	56.6	64.2	58.9	53.5
	SC	31.9	29.9	27.9	30.8	28.7	26.8	29.6	27.6	25.7	28.5	26.5	24.6
	gpm	18.5	13.7	10.5	17.8	13.1	10.1	17.0	12.5	9.5	16.2	11.9	9.0
	wpd	55.7	30.8	18.2	51.6	28.1	16.6	47.2	25.5	14.9	43.0	23.3	13.2
78	TC	73.4	68.2	62.9	70.5	65.2	59.9	67.5	62.2	56.9	64.5	59.2	53.9
	SC	35.1	33.0	31.0	33.9	31.9	29.9	32.8	30.8	28.8	31.7	29.7	27.7
	gpm	18.6	13.8	10.6	17.8	13.2	10.1	17.1	12.6	9.6	16.3	11.9	9.1
	wpd	56.7	31.2	18.5	52.1	28.4	16.6	47.6	25.8	15.1	43.4	23.3	13.5
80	TC	73.8	68.6	63.3	70.9	65.6	60.2	67.9	62.6	57.1	64.9	59.5	54.1
	SC	38.2	36.2	34.1	37.1	35.0	33.0	36.0	33.9	31.9	34.8	32.8	30.7
	gpm	18.7	13.9	10.7	17.9	13.3	10.2	17.2	12.6	9.6	16.4	12.0	9.1
	wpd	57.2	31.5	18.7	52.5	28.8	16.9	48.5	26.1	15.1	44.2	23.6	13.7
82	TC	74.2	68.8	63.4	71.2	65.8	60.2	68.2	62.7	57.2	65.1	59.6	54.0
	SC	41.3	39.3	37.2	40.2	38.1	36.0	39.1	37.0	34.9	37.9	35.8	33.7
	gpm	18.8	14.0	10.7	18.0	13.3	10.2	17.2	12.7	9.6	16.4	12.1	9.1
	wpd	57.6	31.9	18.7	53.0	29.1	16.9	48.5	26.5	15.1	44.2	23.9	13.7
84	TC	74.3	68.8	63.4	71.2	65.8	60.2	68.2	62.7	57.4	65.1	59.5	54.4
	SC	44.4	42.3	40.2	43.3	41.1	39.0	42.1	40.0	37.9	40.9	38.8	36.9
	gpm	18.8	14.0	10.7	18.1	13.3	10.2	17.3	12.7	9.7	16.4	12.0	9.1
	wpd	58.1	31.9	18.7	53.4	29.1	16.9	48.9	26.5	15.1	44.2	23.6	13.7
86	TC	74.2	68.6	63.5	71.1	65.5	60.5	68.0	62.6	57.8	64.9	59.8	55.1
	SC	47.4	45.3	43.2	46.3	44.1	42.2	45.1	43.0	41.2	43.9	41.9	40.1
	gpm	18.8	13.9	10.7	18.0	13.3	10.2	17.2	12.6	9.8	16.4	12.1	9.3
	wpd	57.6	31.5	18.7	53.0	28.8	17.1	48.5	26.1	15.6	44.2	23.9	14.2
88	TC	74.0	68.7	64.0	70.8	65.7	61.4	67.9	63.1	58.7	64.8	60.4	56.2
	SC	50.4	48.3	46.5	49.2	47.2	45.4	48.1	46.2	44.5	46.9	45.2	43.5
	gpm	18.8	13.9	10.8	17.9	13.3	10.4	17.2	12.8	9.9	16.4	12.3	9.5
	wpd	57.6	31.5	19.0	52.5	29.1	17.7	48.5	26.8	16.1	43.8	24.6	14.6
90	TC	73.8	69.1	64.8	70.9	66.5	62.3	68.2	63.9	59.9	65.4	61.4	57.3
	SC	53.4	51.6	49.8	52.3	50.5	48.7	51.3	49.6	47.7	50.2	48.5	46.8
	gpm	18.6	14.0	10.9	17.9	13.5	10.5	17.2	12.9	10.2	16.5	12.4	9.7
	wpd	56.7	32.2	19.6	52.5	29.8	17.9	48.5	27.4	16.9	44.6	25.2	15.4

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	96.4	90.7	85.0	92.8	87.0	81.2	89.1	83.3	77.4	85.4	79.5	73.6
	SC	38.1	35.8	33.6	36.7	34.4	32.1	35.2	32.9	30.7	33.7	31.4	29.2
	gpm	24.4	18.4	14.3	23.5	17.7	13.7	22.6	16.9	13.1	21.6	16.1	12.5
	wpd	54.7	31.1	18.8	50.8	28.6	17.2	46.7	26.1	15.8	42.7	23.8	14.2
76	TC	96.5	90.9	85.2	92.9	87.2	81.4	89.2	83.5	77.6	85.5	79.7	73.8
	SC	41.7	39.4	37.1	40.2	37.9	35.7	38.7	36.4	34.2	37.2	35.0	32.7
	gpm	24.4	18.4	14.4	23.6	17.7	13.8	22.6	16.9	13.1	21.7	16.1	12.5
	wpd	54.7	31.1	19.0	50.8	28.6	17.4	46.7	26.3	15.8	43.0	23.8	14.2
78	TC	96.6	91.0	85.4	93.0	87.4	81.7	89.4	83.7	77.9	85.7	79.9	74.0
	SC	45.2	42.9	40.6	43.7	41.4	39.2	42.2	40.0	37.7	40.7	38.5	36.2
	gpm	24.5	18.4	14.4	23.6	17.7	13.8	22.6	16.9	13.1	21.7	16.2	12.5
	wpd	55.1	31.3	19.0	51.1	28.9	17.4	47.0	26.3	15.8	43.3	24.1	14.2
80	TC	96.9	91.2	85.5	93.3	87.5	81.8	89.6	83.9	78.0	85.9	80.1	74.1
	SC	48.7	46.4	44.1	47.2	44.9	42.7	45.7	43.5	41.2	44.3	42.0	39.7
	gpm	24.6	18.5	14.4	23.6	17.7	13.8	22.7	17.0	13.2	21.7	16.2	12.5
	wpd	55.5	31.3	19.0	51.8	28.9	17.6	47.3	26.6	16.0	43.3	24.1	14.4
82	TC	97.0	91.3	85.7	93.3	87.6	82.0	89.7	83.8	78.2	85.9	80.1	74.7
	SC	55.6	53.3	51.0	54.1	51.8	49.5	52.6	50.3	48.1	51.1	48.8	46.7
	gpm	24.5	18.5	14.5	23.5	17.8	13.8	22.7	16.9	13.2	21.7	16.2	12.6
	wpd	55.1	31.3	19.3	50.8	28.9	17.6	47.3	26.3	16.0	43.3	24.1	14.6
84	TC	97.0	91.3	86.0	93.2	87.7	82.5	89.4	84.0	79.0	85.8	80.5	75.4
	SC	55.6	53.3	51.0	54.1	51.8	49.5	52.6	50.3	48.1	51.1	48.8	46.7
	gpm	24.5	18.5	14.5	23.5	17.8	13.8	22.7	17.0	13.4	21.7	16.2	12.6
	wpd	55.1	31.3	19.3	50.8	28.9	17.6	47.3	26.6	16.4	43.0	24.3	14.8
86	TC	96.9	91.3	86.0	93.2	87.7	82.5	89.4	84.0	79.0	85.8	80.5	75.4
	SC	59.0	56.7	54.5	57.5	55.2	53.1	59.4	57.3	55.1	57.1	54.2	50.4
	gpm	24.5	18.5	14.5	23.5	17.8	13.9	22.6	17.0	13.4	21.7	16.3	12.7
	wpd	55.1	31.3	19.3	50.8	28.9	17.8	46.7	26.6	16.4	43.0	24.3	14.8
88	TC	96.8	91.6	86.5	93.3	88.1	83.1	89.6	84.6	79.8	86.1	81.2	76.4
	SC	62.4	60.2	58.1	60.9	58.8	56.8	59.4	57.4	55.4	58.0	56.0	54.1
	gpm	24.5	18.6	14.6	23.6	17.8	14.0	22.6	17.2	13.4	21.7	16.5	12.9
	wpd	55.1	31.6	19.5	51.1	29.2	18.0	47.0	27.1	16.6	43.3	24.8	15.4
90	TC	97.0	92.0	87.4	93.6	88.8	84.1	90.1	85.5	80.7	86.7	82.0	77.4
	SC	65.9	63.8	61.8	64.4	62.5	60.5	63.0	61.1	59.2	61.7	59.8	57.9
	gpm	24.6	18.6	14.7	23.7	18.0	14.2	22.8	17.3	13.6	22.0	16.6	13.0
	wpd	55.5	31.6	19.9	51.5	29.7	18.4	47.7	27.6	17.0	44.3	25.3	15.6

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10			

# 2000 CFM - Standard Capacity (73° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	81.4	76.0	70.5	78.4	73.0	67.4	75.4	69.9	64.4	72.3	66.9	61.3
	SC	27.3	25.3	23.4	26.2	24.3	22.3	25.1	23.2	21.3	24.0	22.1	20.2
	gpm	20.6	15.4	11.9	19.9	14.7	11.4	19.1	14.1	10.9	18.3	13.6	10.3
	wpd	69.6	38.6	23.0	64.5	35.5	21.3	59.5	32.6	19.3	54.8	30.1	17.4
76	TC	81.4	75.9	70.5	78.4	72.9	67.4	75.3	69.8	64.3	72.3	66.7	61.2
	SC	30.7	28.7	26.7	29.6	27.6	25.6	28.5	26.5	24.5	27.3	25.4	23.4
	gpm	20.6	15.4	11.9	19.9	14.7	11.4	19.1	14.2	10.9	18.3	13.5	10.3
	wpd	69.6	38.6	23.0	64.5	35.5	21.3	59.5	32.6	19.3	54.8	29.8	17.4
78	TC	81.3	75.9	70.6	78.4	72.9	67.5	75.4	69.9	64.5	72.3	66.9	61.3
	SC	33.8	31.8	29.8	32.7	30.7	28.7	31.6	29.6	27.6	30.4	28.5	26.5
	gpm	20.6	15.4	11.9	19.9	14.8	11.4	19.1	14.2	10.9	18.3	13.5	10.3
	wpd	69.6	38.6	23.3	64.5	35.9	21.3	59.5	33.0	19.3	54.8	29.8	17.4
80	TC	81.6	76.3	70.9	78.7	73.3	67.9	75.7	70.3	64.8	72.7	67.2	61.7
	SC	37.0	35.0	33.0	35.9	33.8	31.9	34.7	32.7	30.8	33.6	31.6	29.7
	gpm	20.7	15.4	12.0	19.9	14.9	11.5	19.2	14.3	10.9	18.4	13.6	10.4
	wpd	70.1	39.0	23.6	65.0	36.3	21.6	60.0	33.3	19.6	55.3	30.1	17.7
82	TC	82.0	76.6	71.3	79.0	73.6	68.3	76.0	70.6	65.2	73.0	67.6	62.1
	SC	40.1	38.1	36.1	39.0	37.0	35.0	37.9	35.9	33.9	36.8	34.8	32.8
	gpm	20.8	15.5	12.0	20.0	15.0	11.6	19.2	14.3	11.0	18.5	13.6	10.5
	wpd	70.7	39.4	23.6	65.5	36.7	21.8	60.5	33.7	19.8	55.7	30.5	17.9
84	TC	82.4	77.0	71.5	79.4	74.0	68.5	76.4	70.9	65.4	73.3	67.8	62.2
	SC	43.3	41.2	39.2	42.2	40.1	38.1	41.0	39.0	37.0	39.9	37.9	35.8
	gpm	20.9	15.6	12.0	20.1	15.0	11.6	19.3	14.3	11.0	18.5	13.7	10.5
	wpd	71.2	39.8	23.6	66.0	37.0	21.8	61.0	33.7	19.8	56.2	30.8	17.9
86	TC	82.6	77.1	71.6	79.6	74.1	68.5	76.6	71.0	65.4	73.5	67.9	62.2
	SC	46.4	44.3	42.2	45.3	43.2	41.1	44.1	42.1	40.0	43.0	40.9	38.8
	gpm	20.9	15.6	12.1	20.2	15.0	11.6	19.4	14.4	11.1	18.6	13.7	10.5
	wpd	71.7	39.8	23.9	66.5	37.0	21.8	61.5	34.0	20.1	56.7	30.8	18.2
88	TC	82.7	77.1	71.6	79.6	74.0	68.4	76.5	70.8	65.3	73.4	67.7	62.4
	SC	49.5	47.3	45.2	48.3	46.2	44.1	47.2	45.0	43.0	46.0	43.9	41.9
	gpm	20.9	15.6	12.1	20.2	15.0	11.6	19.4	14.3	11.0	18.6	13.7	10.5
	wpd	71.7	39.8	23.9	66.5	36.7	21.8	61.5	33.7	19.8	56.7	30.8	18.2
90	TC	82.6	77.0	71.6	79.5	73.8	68.7	76.4	70.7	65.7	73.2	67.8	63.0
	SC	52.5	50.3	48.3	51.3	49.2	47.2	50.2	48.0	46.2	49.0	47.0	45.2
	gpm	20.9	15.6	12.1	20.2	15.0	11.6	19.4	14.3	11.1	18.5	13.7	10.6
	wpd	71.7	39.8	23.9	66.5	36.7	22.1	61.5	33.7	20.1	56.2	30.8	18.5

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	119.7	114.7	109.5	115.9	110.7	105.4	112.0	106.7	101.3	108.1	102.7	97.2
	SC	42.6	40.5	38.3	41.0	38.8	36.7	39.3	37.2	35.0	37.7	35.5	33.3
	gpm	30.3	23.3	18.5	29.3	22.4	17.8	28.3	21.6	17.1	27.4	20.8	16.4
	wpd	60.2	35.5	22.5	56.2	33.1	20.8	52.5	30.5	19.1	48.7	28.3	17.5
76	TC	119.6	92.1	88.3	115.8	110.6	105.3	111.9	106.6	101.2	107.9	102.6	97.1
	SC	46.1	35.6	34.0	44.4	42.3	40.1	42.8	40.6	38.5	41.1	39.0	36.8
	gpm	30.2	18.7	14.9	29.3	22.4	17.8	28.3	21.6	17.1	27.3	20.8	16.4
	wpd	59.9	22.9	14.6	56.2	33.1	20.8	52.5	30.5	19.1	48.7	28.3	17.5
78	TC	119.5	114.5	109.4	115.7	110.6	105.4	111.8	106.7	101.3	107.9	102.6	97.2
	SC	49.6	47.4	45.3	47.9	45.8	43.7	46.3	44.2	42.0	44.6	42.5	40.4
	gpm	30.2	23.3	18.5	29.3	22.4	17.8	28.3	21.6	17.1	27.3	20.8	16.4
	wpd	59.9	35.5	22.5	56.2	33.1	20.8	52.5	30.5	19.1	48.7	28.3	17.7
80	TC	119.6	92.1	88.4	115.8	110.7	105.5	111.9	106.8	101.4	108.0	102.7	97.3
	SC	53.1	40.9	39.3	51.4	49.3	47.2	49.8	47.7	45.5	48.1	46.0	43.9
	gpm	30.3	18.7	14.9	29.3	22.4	17.8	28.3	21.6	17.2	27.3	20.8	16.4
	wpd	60.2	22.9	14.6	56.5	33.1	20.8	52.5	30.7	19.3	48.7	28.5	17.7
82	TC	119.7	114.7	109.6	115.9	110.8	105.6	112.0	106.8	101.5	108.1	102.8	97.3
	SC	55.6	54.5	52.3	54.9	52.8	50.7	53.3	51.2	49.0	51.6	49.5	47.4
	gpm	30.3	23.3	18.5	29.3	22.4	17.9	28.3	21.6	17.2	27.3	20.8	16.4
	wpd	60.2	35.5	22.5	56.5	33.1	20.8	52.8	30.7	19.3	49.0	28.5	17.7
84	TC	119.8	114.8	109.5	115.9	110.8	105.5	112.1	106.9	101.5	108.1	102.8	97.4
	SC	60.0	57.9	55.8	58.4	56.3	54.1	56.7	54.6	52.5	55.1	53.0	40.5
	gpm	30.3	23.3	18.4	29.3	22.4	17.8	28.4	21.6	17.2	27.3	20.8	13.3
	wpd	60.2	35.5	22.3	56.5	33.1	20.8	52.8	30.7	19.3	49.0	28.5	11.6
86	TC	119.8	114.8	109.5	115.9	110.8	105.5	112.0	106.8	101.5	108.0	102.7	97.4
	SC	63.5	61.4	59.2	61.8	59.7	57.5	60.2	58.1	55.9	58.5	56.4	54.3
	gpm	30.4	23.3	18.4	29.3	22.4	17.8	28.4	21.6	17.2	27.3	20.8	16.4
	wpd	60.6	35.5	22.3	56.5	33.1	20.8	52.8	30.7	19.3	49.0	28.5	17.7
88	TC	119.7	114.6	109.6	115.9	110.7	105.6	111.9	106.8	101.7	107.9	102.8	97.8
	SC	66.9	64.7	62.7	65.2	63.1	61.0	63.6	61.5	59.5	61.9	59.9	57.9
	gpm	30.3	23.2	18.5	29.3	22.4	17.8	28.4	21.6	17.2	27.3	20.8	16.5
	wpd	60.2	35.2	22.5	56.5	33.2	20.8	52.8	30.7	19.3	49.0	28.5	17.9
90	TC	119.6	114.7	109.9	115.7	110.7	106.1	111.9	106.9	102.1	108.0	103.1	98.3
	SC	70.3	68.2	66.2	68.6	66.6	64.6	67.0	65.0	63.0	65.4	63.4	61.5
	gpm	30.3	23.2	18.6	29.3	22.4	18.0	28.4	21.6	17.2	27.3	20.8	16.6
	wpd	60.2	35.2	22.7	56.5	33.1	21.2	52.8	30.7	19.5	49.0	28.5	18.1

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44	
-----	-----	----	--	--	----	--	--	----	--

# 2000 CFM - Standard Capacity (75° EWB)

## 2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	90.2	84.7	79.1	87.2	81.6	76.0	84.1	78.5	72.8	81.0	75.3	69.7
	SC	29.1	27.2	25.2	28.0	26.1	24.2	27.0	25.0	23.1	25.9	23.9	22.0
	gpm	22.9	17.1	13.3	22.1	16.5	12.9	21.2	15.9	12.3	20.5	15.3	11.8
	wpd	85.6	48.1	29.1	79.9	44.6	27.1	73.9	41.4	24.9	68.6	38.2	22.7
78	TC	90.1	84.6	79.0	87.1	81.5	75.9	84.0	78.4	72.8	80.9	75.3	69.6
	SC	32.5	30.5	28.6	31.4	29.5	27.5	30.3	28.4	26.4	29.3	27.3	25.4
	gpm	22.8	17.1	13.3	22.0	16.5	12.8	21.2	15.9	12.3	20.5	15.3	11.7
	wpd	85.1	48.1	29.1	79.4	44.6	26.8	73.9	41.4	24.6	68.6	38.2	22.4
80	TC	90.0	84.5	79.0	87.0	81.5	75.9	84.0	78.4	72.8	80.9	75.3	69.7
	SC	35.7	33.7	31.7	34.6	32.6	30.6	33.5	31.5	29.5	32.4	30.4	28.4
	gpm	22.8	17.1	13.3	22.0	16.5	12.8	21.2	15.9	12.3	20.5	15.3	11.8
	wpd	85.1	48.1	29.1	79.4	44.6	26.8	73.9	41.4	24.9	68.6	38.2	22.7
82	TC	90.2	84.7	79.2	87.2	81.7	76.2	84.2	78.7	73.1	81.1	75.6	70.0
	SC	38.8	36.8	34.8	37.7	35.7	33.8	36.6	34.6	32.7	35.5	33.5	31.6
	gpm	22.9	17.2	13.3	22.1	16.6	12.9	21.3	16.0	12.3	20.5	15.4	11.8
	wpd	85.6	48.5	29.1	79.9	45.1	27.1	74.4	41.8	24.9	69.1	38.6	22.7
84	TC	90.5	85.0	79.5	87.5	82.0	76.5	84.5	79.0	73.4	81.4	75.9	70.3
	SC	42.0	40.0	38.0	40.9	38.9	36.9	39.8	37.8	35.8	38.7	36.7	34.7
	gpm	23.0	17.2	13.4	22.2	16.7	12.9	21.4	16.1	12.4	20.6	15.4	11.9
	wpd	86.2	48.5	29.4	80.5	45.5	27.1	75.0	42.2	25.2	69.6	38.6	23.0
86	TC	90.8	85.3	79.9	87.8	82.3	76.8	84.8	79.3	73.7	81.7	76.2	70.6
	SC	45.2	43.1	41.1	44.0	42.0	40.0	42.9	40.9	38.9	41.8	39.8	37.8
	gpm	23.0	17.3	13.5	22.3	16.6	12.9	21.5	16.1	12.4	20.7	15.4	11.9
	wpd	86.8	48.9	29.8	81.0	45.1	27.4	75.5	42.2	25.2	70.1	39.0	23.3
88	TC	91.2	85.7	80.2	88.2	82.6	77.0	85.1	79.5	73.8	82.0	76.4	70.6
	SC	48.3	46.2	44.2	47.2	45.1	43.1	46.1	44.0	42.0	45.0	42.9	40.9
	gpm	23.1	17.4	13.6	22.3	16.7	13.0	21.6	16.1	12.5	20.8	15.5	11.9
	wpd	87.4	49.4	30.1	81.6	45.5	27.8	76.0	42.2	25.5	70.7	39.4	23.3
90	TC	91.4	85.8	80.2	88.4	82.7	77.1	85.3	79.5	73.9	82.1	76.3	70.6
	SC	51.4	49.3	47.3	50.3	48.2	46.1	49.2	47.1	45.0	48.0	45.9	43.9
	gpm	23.2	17.4	13.6	22.4	16.7	13.0	21.6	16.1	12.5	20.8	15.4	11.9
	wpd	88.0	49.4	30.1	82.2	45.9	27.8	76.6	42.2	25.5	70.7	39.0	23.3

## 4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC												
	SC												
	gpm												
	wpd												
76	TC	132.0	101.9	98.0	128.1	122.9	117.5	124.2	118.9	113.4	120.2	114.8	109.2
	SC	45.6	35.5	33.9	44.0	41.8	39.6	42.3	40.1	38.0	40.7	38.5	36.3
	gpm	33.4	20.7	16.5	32.4	24.9	19.9	31.4	24.1	19.2	30.4	23.3	18.4
	wpd	73.3	28.1	17.9	68.8	40.8	25.9	64.8	37.9	24.1	60.6	35.5	22.3
78	TC	131.9	126.8	121.5	128.0	122.8	117.4	124.1	118.8	113.3	120.1	114.7	109.1
	SC	49.1	46.9	44.7	47.4	45.3	43.1	45.8	43.6	41.4	44.1	42.0	39.8
	gpm	33.4	25.7	20.5	32.4	24.9	19.9	31.3	24.1	19.2	30.4	23.3	18.4
	wpd	73.0	43.4	27.6	68.8	40.8	25.9	64.4	37.9	24.1	60.6	35.5	22.3
80	TC	131.7	101.7	97.9	127.9	122.7	117.4	124.0	118.7	113.3	120.0	114.6	109.1
	SC	52.5	40.7	39.1	50.9	48.7	46.6	49.2	47.1	44.9	47.6	45.5	43.3
	gpm	33.4	20.6	16.5	32.4	24.9	19.9	31.3	24.1	19.2	30.4	23.3	18.4
	wpd	73.0	27.8	17.9	68.8	40.5	25.9	64.4	37.9	24.1	60.6	35.5	22.3
82	TC	131.8	126.7	121.4	127.9	122.8	117.4	124.0	118.8	113.4	120.0	114.7	109.2
	SC	56.0	53.9	51.7	54.4	52.3	50.1	52.7	50.6	48.5	51.1	49.0	46.8
	gpm	33.4	25.7	20.4	32.4	24.9	19.8	31.4	24.1	19.2	30.4	23.3	18.4
	wpd	73.0	43.4	27.4	68.8	40.8	25.7	64.8	37.9	24.1	60.6	35.5	22.3
84	TC	131.8	126.8	121.5	128.0	122.9	117.5	124.1	118.9	113.4	120.1	114.8	108.5
	SC	59.5	57.4	55.2	57.8	55.8	53.6	56.2	54.1	51.9	54.6	52.5	40.4
	gpm	33.4	25.7	20.5	32.4	24.9	19.8	31.4	24.1	19.1	30.4	23.3	15.0
	wpd	73.3	43.4	27.6	68.8	40.8	25.7	64.8	38.2	23.9	60.6	35.5	14.7
86	TC	131.9	126.8	121.6	128.0	122.9	117.5	124.1	118.9	113.4	120.2	114.8	109.2
	SC	63.0	60.8	58.7	61.3	59.2	57.1	59.7	57.6	55.4	58.1	55.9	53.8
	gpm	33.4	25.7	20.5	32.5	24.9	19.8	31.4	24.1	19.2	30.4	23.3	18.4
	wpd	73.3	43.2	27.6	69.1	40.8	25.7	64.8	38.2	24.1	60.6	35.7	22.3
88	TC	131.9	126.8	121.6	128.1	122.8	117.5	124.2	118.9	113.4	120.2	114.8	109.2
	SC	66.4	64.3	62.2	64.8	62.6	60.5	63.2	61.0	58.9	61.5	59.4	57.2
	gpm	33.4	25.7	20.5	32.5	24.9	19.8	31.4	24.1	19.2	30.5	23.3	18.4
	wpd	73.3	43.2	27.6	69.1	40.5	25.7	64.8	38.2	24.1	60.6	35.7	22.3
90	TC	131.9	126.8	121.5	128.0	122.8	117.5	124.1	118.7	113.5	120.1	114.6	109.3
	SC	69.9	67.7	65.6	68.2	66.1	63.9	66.6	64.4	62.3	64.9	62.8	60.7
	gpm	33.4	25.7	20.5	32.5	24.9	19.9	31.4	24.0	19.2	30.4	23.2	18.4
	wpd	73.3	43.2	27.6	69.1	40.5	25.9	64.8	37.7	24.1	60.6	35.2	22.3

## 3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	118.4	112.6	106.7	114.8	108.8	102.8	111.1	105.1	98.9	107.3	101.2	95.1
	SC	39.8	37.5	35.2	38.3	36.0	33.7	36.9	34.6	32.3	35.4	33.1	30.8
	gpm	29.9	22.8	18.0	29.1	22.0</td							

### ***Daikin Training and Development***

Now that you have made an investment in modern, efficient Daikin equipment, its care should be a high priority. For training information on all Daikin HVAC products, please visit us at [www.DaikinAP.com](http://www.DaikinAP.com) and click on training, or call 540-248-9646 and ask for the Training Department.

### ***Warranty***

All Daikin equipment is sold pursuant to its standard terms and conditions of sale, including Limited Product Warranty. Consult your local Daikin Representative for warranty details. Refer to Form 933-430285Y. To find your local Daikin Representative, go to [www.DaikinAP.com](http://www.DaikinAP.com).

### ***Aftermarket Services***

To find your local parts office, visit [www.DaikinAP.com](http://www.DaikinAP.com) or call 800-37PARTS (800-377-2787). To find your local service office, visit [www.DaikinAPcom](http://www.DaikinAPcom) or call 800-432-1342.

This document contains the most current product information as of this printing. For the most up-to-date product information, please go to [www.DaikinAP.com](http://www.DaikinAP.com).

Products manufactured in an ISO Certified Facility.

