

Engineering Data

ED 18507-1

Group: Unit Ventilator

Date: November 2019

Daikin Classroom Unit Ventilator - Cooling Capacity Data

Models AVS, AVB, AVV and AVR Floor Units ("J" Vintage)



Chilled Water Coil Selection

STEP 1 – Determine Design Conditions

Design indoor and outdoor air temperatures should be determined in accordance with established engineering practices as outlined in the ASHRAE Guide or other authoritative source. Indoor temperatures of 80°F dry bulb and 67°F wet bulb for summer, are usually acceptable for design or peak load conditions even though the expected operating conditions of the system may be somewhat different.

Formula

Mixture Entering Dry Bulb °F (EDB) & Entering Wet Bulb °F (EWB) Temperature —

$$\text{EDB} = \text{Room DB} \times \frac{\% \text{ RA}}{100} + \text{Outdoor DB} \times \frac{\% \text{ OA}}{100}$$

$$\text{EDB} = 76(.8) + 96(.2) = 80^\circ\text{F}$$

$$\text{EWB} = \text{Room Enthalpy} \times$$

$$\frac{\% \text{ RA}}{100} + \text{Outdoor Enthalpy} \times \frac{\% \text{ OA}}{100}$$

Refer to Table 3 for Enthalpy (H).

$$\text{EWB} = 30.06(.8) + 37.66(.2) = 31.58\text{H} = 67^\circ\text{F}$$

STEP 2 – Determine Desired Cooling Load

Unit cooling capacity should be selected to equal or slightly exceed the sum of computed room sensible and latent heat gains (Room Total Capacity). When operating on the mechanical cooling cycle, the control system introduces a constant amount of outdoor air for ventilation. The latent and sensible heat gain from this outdoor ventilation air must be added to the room total cooling load before choosing the proper capacity unit.

STEP 3

Use tables to properly size the unit based on the calculated cooling capacities, entering air conditions, water flow rate, and water temperature.

For conditions of coil performance beyond the scope of these selection procedures, Daikin Applied offers computer selection programs for chilled water, hot water and steam coils. Consult your local Daikin representative for details.

STEP 4 – Calculate Leaving Air Conditions

Leaving air temperatures dry bulb °F (LDB) and wet bulb °F (LWB) may be calculated as follows:

$$\text{LDB} = \text{EDB} - \frac{\text{SC (BTUH)}}{\text{CFM} \times 1.085} =$$

$$\text{LWBH} = \text{EWB} - \frac{\text{TC (BTUH)}}{\text{CFM} \times 4.5} =$$

NOTE: See table 3, page 3 to get LWB (°F)

STEP 5 – Freeze Protection

CONSTANT PUMP OPERATION IS REQUIRED WHENEVER THE OUTDOOR AIR TEMPERATURE IS BELOW 35°F. This will assist in providing protection against freeze up of the system water piping and coils. To avoid the possibility of water coil freeze up on valve controlled units, the valve must be selected properly to ensure water flow. One of the steps below should be followed:

Chilled Water

1. Draining of the chilled water system during cold weather or;
2. Opening of the chilled water coil valves and operation of the chilled water circulating pump any time the outside air temperature is below 35°F.
3. Usage of an antifreeze in the system.

STEP 6 – Units with Antifreeze

If ethylene or propylene glycol is used, it is necessary to consider its effect upon heating and cooling capacities and water pressure drop through the coil and piping system.

1. Divide cooling loads determined from STEP 2 by the applicable glycol correction factor to arrive at the calculated unit capacity required to take care of the capacity reduction caused by the glycol solution.

Table 1: Capacity Correction Factors For Ethylene and Propylene Glycol

	%	20	30	40
Capacity	Ethylene	.92	.84	.75
	Propylene	.86	.73	.62

2. Determine the GPM required by entering the appropriate chilled water cooling capacity table or hot water capacity chart using the calculated unit capacity.
3. Determine the water pressure drop by multiplying the water pressure drop for the GPM determined above by the pressure drop factor for the % glycol used.

Pressure Drop Correction Factors for Ethylene and Propylene Glycol

	%	20	30	40
Pressure Drop	Ethylene	1.15	1.22	1.34
	Propylene	1.35	1.27	1.24

Table 3. Enthalpy (H) - at Saturation, but Per Pound of Dry Air

Wet Bulb Temp. °F.	Tenths of a Degree									
	.0	.1	.2	.3	.4	.5	.6	.7	.8	.9
50	20.30	20.36	20.41	20.47	20.52	20.58	20.64	20.69	20.75	20.80
51	20.86	20.92	20.97	21.03	21.09	21.15	21.20	21.26	21.32	21.38
52	21.44	21.50	21.56	21.62	21.67	21.73	21.79	21.85	21.91	21.97
53	22.02	22.08	22.14	22.20	22.26	22.32	22.38	22.44	22.50	22.56
54	22.62	22.68	22.74	22.80	22.86	22.92	22.98	23.04	23.10	23.16
55	23.22	23.28	23.34	23.41	23.47	23.53	23.59	23.65	23.72	23.78
56	23.84	23.90	23.97	24.03	24.10	24.16	24.22	24.29	24.35	24.42
57	24.48	24.54	24.61	24.67	24.74	24.80	24.86	24.93	24.99	25.06
58	25.12	25.19	25.25	25.32	25.38	25.45	25.52	25.58	26.65	25.71
59	25.78	25.85	25.92	25.98	26.05	26.12	26.19	26.26	26.32	26.39
60	26.46	26.53	26.60	26.67	26.74	26.81	26.87	26.94	27.01	27.08
61	27.15	27.22	27.29	27.36	27.43	27.50	27.57	27.64	27.71	27.78
62	27.85	27.92	27.99	28.07	28.14	28.21	28.28	28.35	28.43	28.50
63	28.57	28.64	28.72	28.79	28.87	28.94	29.01	29.09	29.16	29.24
64	29.31	29.39	29.46	29.54	29.61	29.69	29.76	29.84	29.91	29.99
65	30.06	30.14	30.21	30.29	30.37	30.45	30.52	30.60	30.68	30.78
66	30.83	30.91	30.99	31.07	31.15	31.23	31.30	31.38	31.46	31.54
67	31.62	31.70	31.78	31.86	31.94	32.02	32.10	32.18	32.26	32.34
68	32.42	32.50	32.59	32.67	32.75	32.84	32.92	33.00	33.08	33.17
69	33.25	33.33	33.42	33.50	33.59	33.67	33.75	33.84	33.92	34.01
70	34.09	34.18	34.26	34.35	34.43	34.52	34.61	34.69	34.78	34.86
71	34.95	35.04	35.13	35.21	35.30	35.39	35.48	35.57	35.65	35.74
72	35.83	35.92	36.01	36.10	36.19	36.29	36.38	36.47	36.56	36.65
73	36.74	36.83	36.92	37.02	37.11	37.20	37.29	37.38	37.48	37.57
74	37.66	37.76	37.85	37.95	38.04	38.14	38.23	38.33	38.42	38.52
75	38.61	38.71	38.80	38.90	38.99	39.09	39.19	39.28	39.38	39.47
76	39.57	39.67	39.77	39.87	39.97	40.07	40.17	40.27	40.37	40.47
77	40.57	40.67	40.77	40.87	40.97	41.08	41.18	41.28	41.38	41.48
78	41.58	41.68	41.79	41.89	42.00	42.10	42.20	42.31	42.41	42.52
79	42.62	42.73	42.83	42.94	43.05	43.16	43.26	43.37	43.48	43.58
80	43.69	43.80	43.91	44.02	44.13	44.24	44.34	44.45	44.56	44.67
81	44.78	44.89	45.00	45.12	45.23	45.34	45.45	45.56	45.68	45.79
82	45.90	46.01	46.13	46.24	46.36	46.47	46.58	46.70	46.81	46.93
83	47.04	47.16	47.28	47.39	47.51	47.63	47.75	47.87	47.98	48.10
84	48.22	48.34	48.46	48.58	48.70	48.83	48.95	49.07	49.19	49.31
85	49.43	49.55	49.68	49.80	49.92	50.05	50.17	50.29	50.41	50.54

Note: Interpolated to tenths of degrees from 1963 edition ASHRAE Guide & Data Book. Published by the American Society of Heating, Refrigerating and Air Conditioning Engineers, Inc.

Capacity Tables Legend

EDB = Entering Air Dry Bulb
SC = Sensible Cooling Capacity

EWB = Entering Air Wet Bulb
TC = Total Cooling Capacity

WPD = Water Pressure Drop (Ft. H₂O)
EWT = Entering Water Temperature

TR = Water Temperature Rise
GPM = Gallons Per Minute

2-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12
74	TC		13.5	11.8	10.3	12.7	11.2	9.2	12.0	10.6	8.7	11.4	9.7	8.1			
	SC		11.2	10.4	9.4	10.9	10.0	8.7	10.6	9.7	8.1	10.2	9.1	7.6			
	gpm		3.9	2.7	2.0	3.7	2.6	1.8	3.5	2.5	1.7	3.3	2.2	1.5			
	wpd		4.6	2.2	1.2	4.2	2.1	1.0	3.7	1.9	0.9	3.4	1.5	0.7			
76	TC		14.2	12.8	11.0	13.5	12.2	10.5	12.9	11.4	9.9	12.4	10.9	9.4			
	SC		12.4	11.6	10.3	12.1	11.2	9.8	11.8	10.7	9.3	11.4	10.2	8.8			
	gpm		4.1	2.9	2.1	3.9	2.9	2.0	3.7	2.6	1.9	3.6	2.5	1.8			
	wpd		5.1	2.6	1.3	4.6	2.5	1.2	4.2	2.1	1.1	3.9	1.9	1.0			
78	TC		15.0	13.6	12.2	14.4	13.1	11.7	13.8	12.6	11.2	13.3	12.0	10.7			
	SC		13.6	12.7	11.5	13.3	12.3	11.0	12.9	11.8	10.5	12.4	11.3	10.0			
	gpm		4.3	3.2	2.3	4.2	3.0	2.2	3.9	2.9	2.2	3.9	2.8	2.1			
	wpd		5.7	3.1	1.6	5.3	2.8	1.5	4.7	2.6	1.4	4.6	2.4	1.3			
80	TC		15.8	14.7	13.4	15.3	14.2	12.9	14.8	13.7	12.4	14.3	13.2	11.8			
	SC		14.8	13.8	12.6	14.4	13.3	12.1	13.9	12.8	11.6	13.5	12.4	11.1			
	gpm		4.6	3.4	2.6	4.4	3.2	2.5	4.3	3.2	2.4	4.2	3.0	2.2			
	wpd		6.3	3.5	2.0	5.9	3.2	1.9	5.5	3.1	1.7	5.3	2.8	1.5			
82	TC		16.9	15.8	14.5	16.4	15.3	14.0	15.9	14.8	13.5	15.4	14.3	13.0			
	SC		15.8	14.8	13.6	15.4	14.3	13.2	14.9	13.9	12.7	14.5	13.4	12.2			
	gpm		4.9	3.6	2.8	4.7	3.6	2.7	4.6	3.4	2.6	4.4	3.3	2.5			
	wpd		7.2	4.0	2.4	6.8	3.9	2.2	6.3	3.5	2.1	5.9	3.4	1.9			
84	TC		17.9	16.9	15.7	17.4	16.4	15.2	16.9	15.9	14.7	16.4	15.4	14.2			
	SC		16.8	15.8	14.7	16.3	15.4	14.2	15.9	14.9	13.8	15.4	14.4	13.3			
	gpm		5.2	3.9	3.0	5.0	3.8	2.9	4.9	3.6	2.9	4.7	3.6	2.7			
	wpd		8.2	4.6	2.8	7.7	4.4	2.6	7.2	4.0	2.5	6.8	3.9	2.2			
86	TC		18.9	17.9	16.8	18.4	17.4	16.3	17.9	17.0	15.8	17.4	16.5	15.3			
	SC		17.7	16.8	15.7	17.3	16.4	15.3	16.8	15.9	14.8	16.4	15.5	14.4			
	gpm		5.5	4.2	3.2	5.3	4.0	3.2	5.2	3.9	3.0	5.0	3.8	2.9			
	wpd		9.2	5.3	3.2	8.7	4.9	3.1	8.2	4.7	2.8	7.7	4.4	2.6			
88	TC		19.9	19.0	17.9	19.4	18.5	17.4	18.9	18.0	16.9	18.4	17.5	16.4			
	SC		18.7	17.8	16.8	18.2	17.4	16.3	17.8	16.9	15.9	17.3	16.5	15.4			
	gpm		5.7	4.4	3.5	5.6	4.3	3.3	5.5	4.2	3.2	5.3	4.0	3.2			
	wpd		10.0	5.9	3.7	9.7	5.5	3.4	9.2	5.3	3.2	8.7	4.9	3.1			
90	TC		20.9	20.1	19.0	20.4	19.6	18.5	19.9	19.1	18.0	19.4	18.6	17.5			
	SC		19.6	18.8	17.8	19.2	18.4	17.3	18.7	17.9	16.9	18.2	17.5	16.4			
	gpm		6.0	4.6	3.6	5.9	4.6	3.6	5.7	4.4	3.5	5.6	4.3	3.4			
	wpd		11.1	6.6	4.0	10.5	6.3	3.9	10.0	5.9	3.7	9.7	5.7	3.5			

3-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12
74	TC		16.0	14.2	12.6	15.1	13.4	11.9	14.2	12.7	9.8	13.4	12.0	9.1			
	SC		12.6	11.7	10.9	12.2	11.4	10.6	11.8	11.0	9.2	11.4	10.7	8.6			
	gpm		4.6	3.2	2.4	4.4	3.1	2.3	4.1	2.9	1.9	3.8	2.8	1.7			
	wpd		3.4	1.7	0.9	3.1	1.5	0.8	2.7	1.4	0.6	2.4	1.3	0.5			
76	TC		16.6	15.0	13.7	15.7	14.4	13.1	15.0	13.7	11.2	14.3	13.1	10.6			
	SC		13.8	13.1	12.3	13.4	12.7	11.9	13.1	12.4	10.6	12.8	12.0	10.0			
	gpm		4.8	3.5	2.6	4.5	3.3	2.5	4.3	3.2	2.2	4.1	3.0	2.0			
	wpd		3.7	1.9	1.1	3.3	1.8	1.0	3.0	1.6	0.8	2.8	1.5	0.7			
78	TC		17.2	16.0	14.9	16.5	15.4	13.2	15.9	14.8	12.6	15.3	13.5	12.0			
	SC		15.1	14.4	13.6	14.7	14.1	12.5	14.4	13.7	11.9	14.1	12.8	11.3			
	gpm		5.0	3.7	2.9	4.7	3.5	2.6	4.6	3.4	2.4	4.4	3.1	2.3			
	wpd		4.0	2.2	1.3	3.6	2.0	1.1	3.4	1.9	0.9	3.1	1.5	0.9			
80	TC		18.1	17.0	15.0	17.4	15.9	14.5	16.9	15.3	13.9	15.9	14.8	13.3			
	SC		16.4	15.7	14.2	16.0	15.0	13.7	15.7	14.5	13.2	15.1	14.0	12.6			
	gpm		5.2	3.9	2.9	5.1	3.7	2.8	4.9	3.5	2.6	4.6	3.4	2.6			
	wpd		4.4	2.5	1.3	4.1	2.2	1.3	3.9	2.0	1.1	3.4	1.9	1.1			
82	TC		19.0	17.6	16.3	18.2	17.1	15.8	17.6	16.5	15.2	17.1	16.0	14.6			
	SC		17.7	16.7	15.5	17.2	16.2	14.9	16.7	15.7	14.4	16.2	15.1	13.9			
	gpm		5.5	4.1	3.2	5.2	3.9	3.0	5.1	3.8	2.9	4.9	3.7	2.8			
	wpd		4.9	2.7	1.6	4.4	2.5	1.5	4.1	2.4	1.4	3.9	2.2	1.3			
84	TC		19.8	18.8	17.5	19.3	18.2	17.0	18.8	17.7	16.5	18.2	17.2	15.9			
	SC		18.8	17.8	16.6	18.3	17.3	16.1	17.8	16.8	15.6	17.3	16.3	15.1			
	gpm		5.7	4.4	3.4	5.6	4.2	3.2	5.4	4.1	3.2	5.3	3.9	3.1			
	wpd		5.3	3.1	1.9	5.0	2.9	1.7	4.7	2.7	1.6	4.5	2.5	1.5			
86	TC		20.9	19.9	18.8	20.4	19.4	18.2	19.9	18.9	17.7	19.4	18.4	17.1			
	SC		19.8	18.9	17.8	19.3	18.4	17.3	18.8	17.9	16.8	18.3	17.4	16.2			
	gpm		6.0	4.6	3.6	5.9	4.5	3.5	5.7	4.4	3.4	5.6	4.2	3.3			
	wpd		5.9	3.4	2.1	5.6	3.3	2.0	5.3	3.1	1.9	5.0	2.9	1.8			
88	TC		22.0	21.1	20.0	21.5	20.5	19.4	21.0	20.0	18.9	20.5	19.5	18.4			
	SC		20.9	20.0	18.9	20.4	19.5	18.4	19.9	19.0	17.9	19.4	18.5	17.4			
	gpm		6.3	4.8	3.8	6.2	4.7	3.8	6.0	4.6	3.6	5.9	4.5	3.5			
	wpd		6.5	3.7	2.4	6.2	3.6	2.3	5.9	3.4	2.1	5.6	3.3	2.0			
90	TC		23.1	22.2	21.2	22.6	21.7	20.6	22.1	21.2	20.1	21.6	20.6	19.6			
	SC		21.9	21.0	20.0	21.4	20.5	19.5	20.9	20.0	19.0	20.4	19.6	18.5			
	gpm		6.6	5.1	4.1	6.6	5.0	4.0	6.4	4.9	3.8	6.3	4.7	3.8			
	wpd		7.1	4.2	2.7	6.9	4.0	2.6	6.6	3.9	2.4	6.3	3.6	2.3			

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	20.0	18.5	17.0	18.9	17.4	16.1	17.8	16.4	15.2	16.7	15.5	14.4
	SC	14.6	13.9	13.3	14.1	13.5	12.9	13.6	13.0	12.5	13.2	12.6	12.1
	gpm	5.7	4.2	3.3	5.4	4.0	3.1	5.1	3.8	2.9	4.8	3.6	2.7
	wpd	6.0	3.3	2.0	5.3	2.9	1.7	4.7	2.6	1.5	4.2	2.4	1.4
76	TC	20.4	19.1	17.8	19.3	18.1	17.0	18.3	17.2	16.3	17.4	16.4	15.6
	SC	15.8	15.2	14.7	15.4	14.8	14.3	14.9	14.4	13.9	14.5	14.1	13.6
	gpm	5.9	4.4	3.5	5.6	4.2	3.3	5.3	4.0	3.1	5.0	3.8	3.0
	wpd	6.3	3.5	2.2	5.6	3.1	2.0	5.0	2.9	1.8	4.6	2.6	1.6
78	TC	20.8	19.8	18.8	19.9	18.9	18.1	19.0	18.1	17.4	18.1	17.4	15.3
	SC	17.1	16.6	16.1	16.6	16.2	15.7	16.2	15.8	15.4	15.9	15.5	14.4
	gpm	6.0	4.5	3.6	5.7	4.4	3.5	5.5	4.2	3.4	5.3	4.0	3.0
	wpd	6.6	3.8	2.4	6.0	3.5	2.2	5.5	3.1	2.1	5.0	2.9	1.6
80	TC	21.4	20.6	19.8	20.5	19.8	19.1	19.7	19.1	17.3	19.0	17.7	16.7
	SC	18.4	18.0	17.5	18.0	17.6	17.2	17.6	17.2	16.3	17.2	16.7	15.7
	gpm	6.2	4.8	3.8	5.9	4.5	3.7	5.6	4.4	3.3	5.5	4.1	3.2
	wpd	7.0	4.2	2.7	6.3	3.8	2.5	5.8	3.5	2.0	5.5	3.0	1.9
82	TC	22.1	21.5	20.9	21.3	20.8	19.2	20.7	19.6	18.6	19.7	19.0	18.0
	SC	19.7	19.4	19.0	19.3	19.0	18.1	19.0	18.4	17.6	18.6	17.9	17.0
	gpm	6.4	4.9	4.0	6.1	4.8	3.7	6.0	4.5	3.6	5.6	4.4	3.5
	wpd	7.3	4.4	2.9	6.8	4.2	2.5	6.5	3.8	2.4	5.8	3.5	2.2
84	TC	22.9	22.0	21.1	22.1	21.4	20.5	21.5	20.8	19.9	20.9	20.2	19.3
	SC	21.1	20.7	19.9	20.8	20.2	19.3	20.2	19.6	18.8	19.7	19.1	18.2
	gpm	6.6	5.1	4.1	6.4	4.9	3.9	6.2	4.8	3.8	6.0	4.7	3.7
	wpd	7.9	4.7	3.0	7.3	4.4	2.8	7.0	4.2	2.7	6.6	4.0	2.5
86	TC	23.8	23.2	22.4	23.2	22.6	21.8	22.7	22.1	21.2	22.1	21.5	20.6
	SC	22.4	21.9	21.1	21.9	21.3	20.5	21.4	20.8	20.0	20.8	20.2	19.4
	gpm	6.9	5.3	4.3	6.7	5.3	4.2	6.5	5.1	4.1	6.4	4.9	4.0
	wpd	8.7	5.2	3.4	8.1	5.0	3.1	7.7	4.7	3.0	7.3	4.4	2.9
88	TC	25.0	24.4	23.7	24.4	23.8	23.1	23.8	23.3	22.5	23.3	22.7	21.9
	SC	23.5	23.0	22.3	23.0	22.4	21.7	22.5	21.9	21.2	21.9	21.4	20.6
	gpm	7.2	5.6	4.5	7.1	5.5	4.5	6.9	5.4	4.3	6.7	5.3	4.2
	wpd	9.5	5.8	3.8	9.1	5.5	3.6	8.7	5.3	3.4	8.3	5.0	3.3
90	TC	26.1	25.6	24.9	25.6	25.0	24.3	25.0	24.4	23.7	24.4	23.9	23.2
	SC	24.6	24.1	23.4	24.1	23.6	22.9	23.6	23.0	22.4	23.0	22.5	21.8
	gpm	7.5	5.9	4.8	7.4	5.7	4.7	7.2	5.6	4.5	7.1	5.5	4.5
	wpd	10.3	6.3	4.2	9.9	6.0	4.0	9.5	5.8	3.8	9.1	5.5	3.6

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	24.8	23.5	22.2	23.5	22.2	21.0	22.2	21.0	19.9	20.9	19.8	18.8												
	SC	19.1	18.5	17.9	18.5	17.9	17.3	17.8	17.3	16.7	17.2	16.7	16.2												
	gpm	6.3	4.8	3.8	6.0	4.5	3.6	5.6	4.2	3.3	5.3	4.0	3.2												
	wpd	6.2	3.6	2.3	5.6	3.1	2.0	5.0	2.8	1.8	4.4	2.5	1.6												
76	TC	25.0	24.0	22.9	23.8	22.8	21.8	22.6	21.6	20.8	21.4	20.6	19.8												
	SC	20.6	20.0	19.5	19.9	19.4	18.9	19.3	18.9	18.4	18.8	18.4	18.0												
	gpm	6.4	4.8	3.9	6.0	4.6	3.7	5.7	4.4	3.5	5.4	4.2	3.3												
	wpd	6.4	3.7	2.4	5.6	3.4	2.2	5.1	3.0	1.9	4.6	2.7	1.8												
78	TC	25.4	24.5	23.7	24.2	23.5	22.7	23.1	22.4	21.8	22.0	21.4	21.0												
	SC	22.1	21.6	21.2	21.5	21.1	20.7	20.9	20.5	20.2	20.4	20.1	19.8												
	gpm	6.4	5.0	4.0	6.1	4.8	3.9	5.8	4.5	3.7	5.6	4.3	3.6												
	wpd	6.5	3.9	2.5	5.9	3.6	2.4	5.4	3.3	2.2	5.0	2.9	2.0												
80	TC	25.8	25.2	24.6	24.8	24.2	23.7	23.7	23.3	22.9	22.8	22.5	22.2												
	SC	23.6	23.2	22.9	23.0	22.7	22.5	22.5	22.3	22.0	22.0	21.8	21.6												
	gpm	6.6	5.1	4.2	6.3	4.9	4.0	6.1	4.7	3.9	5.8	4.5	3.8												
	wpd	6.8	4.1	2.7	6.2	3.8	2.5	5.8	3.5	2.4	5.2	3.3	2.3												
82	TC	26.4	26.0	25.6	25.4	25.1	24.8	24.5	24.4	23.4	23.4	23.1	22.7												
	SC	25.2	24.9	24.7	24.7	24.5	24.3	24.2	24.1	23.3	23.3	23.2	23.0												
	gpm	6.7	5.3	4.3	6.4	5.1	4.2	6.2	4.9	3.9	5.9	4.7	3.9												
	wpd	7.0	4.4	2.9	6.5	4.1	2.7	6.1	3.8	2.4	5.5	3.5	2.4												
84	TC	27.1	27.0	26.0	25.9	25.7	25.4	25.3	25.1	24.7	24.6	24.4	24.1												
	SC	26.8	26.7	25.9	25.8	25.7	25.6	25.5	25.4	25.2	25.2	25.1	24.8												
	gpm	6.9	5.4	4.4	6.6	5.2	4.3	6.4	5.1	4.2	6.2	5.0	4.1												
	wpd	7.5	4.7	3.0	6.8	4.3	2.9	6.5	4.1	2.7	6.1	3.9	2.6												
86	TC	27.8	27.6	27.4	27.2	27.0	26.7	26.6	26.4	26.1	25.9	25.7	25.4												
	SC	28.1	28.0	27.8	27.8	27.7	27.5	27.3	27.1	26.8	26.7	26.5	26.2												
	gpm	7.0	5.6	4.6	6.9	5.4	4.5	6.7	5.4	4.4	6.6	5.2	4.3												
	wpd	7.8	5.0	3.4	7.5	4.7	3.3	7.2	4.6	3.0	6.8	4.3	2.9												
88	TC	29.1	28.9	28.7	28.4	28.3	28.0	27.8	27.7	27.4	27.2	27.0	26.8												
	SC	29.9	29.8	29.5	29.3	29.1	28.9	28.6	28.5	28.2	28.0	27.8	27.5												
	gpm	7.3	5.9	4.8	7.2	5.8	4.8	7.0	5.6	4.6	6.9	5.5	4.5												
	wpd	8.5	5.5	3.7	8.2	5.2	3.6	7.8	5.0	3.4	7.5	4.8	3.3												
90	TC	30.3	30.2	30.0	29.7	29.6	29.3	29.1	28.9	28.7	28.4	28.3	28.1												
	SC	31.2	31.1	30.8	30.5	30.4	30.2	29.9	29.8	29.5	29.2	29.1	28.9												
	gpm	7.7	6.1	5.1	7.6	6.0	5.0	7.3	5.8	4.8	7.2	5.8	4.8												
	wpd	9.4	5.9	4.1	9.0	5.6	3.9	8.5	5.4	3.7	8.2	5.2	3.6												

2-Row Chilled Water Cooling

EDB	EWT	42				43			44				45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	15.2	13.0	10.9	14.3	12.1	10.1	13.4	11.3	9.4	12.5	10.5	8.8		
	SC	10.8	9.9	8.9	10.4	9.5	8.6	10.1	9.1	8.2	9.7	8.8	7.8		
	gpm	4.4	3.0	2.1	4.1	2.8	1.9	3.9	2.6	1.8	3.6	2.4	1.7		
	wpd	5.9	2.8	1.3	5.1	2.4	1.1	4.6	2.1	1.0	3.9	1.7	0.9		
76	TC	15.7	13.6	11.8	14.8	12.9	11.2	13.9	12.1	10.5	13.1	11.5	10.0		
	SC	11.9	11.1	10.2	11.6	10.7	9.8	11.2	10.4	9.4	10.9	10.0	9.0		
	gpm	4.5	3.2	2.2	4.3	2.9	2.2	4.0	2.8	2.0	3.8	2.6	1.9		
	wpd	6.1	3.1	1.5	5.5	2.6	1.4	4.9	2.4	1.2	4.4	2.1	1.1		
78	TC	16.1	14.4	12.8	15.3	13.7	12.2	14.5	13.0	11.7	13.8	12.4	10.7		
	SC	13.1	12.3	11.4	12.7	11.9	11.0	12.4	11.6	10.6	12.1	11.2	10.0		
	gpm	4.6	3.3	2.5	4.4	3.2	2.3	4.2	3.0	2.2	3.9	2.9	2.1		
	wpd	6.6	3.4	1.9	5.9	3.1	1.6	5.3	2.8	1.5	4.7	2.5	1.3		
80	TC	16.7	15.2	13.8	15.9	14.6	12.9	15.3	14.0	12.4	14.6	13.2	11.9		
	SC	14.2	13.5	12.6	13.9	13.1	12.1	13.6	12.8	11.6	13.3	12.4	11.1		
	gpm	4.8	3.5	2.6	4.6	3.4	2.5	4.4	3.2	2.4	4.3	3.0	2.3		
	wpd	7.0	3.7	2.1	6.6	3.5	1.9	5.9	3.2	1.7	5.5	2.8	1.6		
82	TC	17.3	16.1	14.6	16.7	15.5	14.1	16.1	14.8	13.6	15.5	14.3	13.1		
	SC	15.4	14.6	13.7	15.1	14.3	13.2	14.7	13.9	12.7	14.4	13.4	12.3		
	gpm	5.0	3.7	2.8	4.8	3.6	2.7	4.6	3.4	2.6	4.5	3.3	2.6		
	wpd	7.7	4.2	2.4	7.0	3.9	2.2	6.6	3.5	2.1	6.1	3.4	2.0		
84	TC	18.0	16.9	15.7	17.5	16.4	15.2	17.0	15.9	14.7	16.5	15.4	14.2		
	SC	16.6	15.9	14.7	16.2	15.4	14.3	15.9	14.9	13.8	15.4	14.5	13.3		
	gpm	5.2	3.9	3.0	5.0	3.8	2.9	4.9	3.6	2.9	4.7	3.6	2.7		
	wpd	8.2	4.6	2.8	7.7	4.4	2.6	7.2	4.0	2.5	6.8	3.9	2.2		
86	TC	19.0	18.0	16.8	18.5	17.5	16.3	18.0	17.0	15.8	17.5	16.5	15.3		
	SC	17.8	16.9	15.8	17.3	16.4	15.3	16.9	15.9	14.9	16.4	15.5	14.4		
	gpm	5.5	4.2	3.2	5.3	4.0	3.2	5.2	3.9	3.0	5.0	3.8	2.9		
	wpd	9.2	5.3	3.2	8.7	4.9	3.1	8.2	4.7	2.8	7.7	4.4	2.6		
88	TC	20.0	19.0	17.9	19.5	18.6	17.4	19.0	18.1	16.9	18.5	17.6	16.5		
	SC	18.7	17.9	16.8	18.3	17.4	16.4	17.8	17.0	15.9	17.3	16.5	15.4		
	gpm	5.8	4.4	3.5	5.6	4.3	3.3	5.5	4.2	3.2	5.3	4.1	3.2		
	wpd	10.2	5.9	3.7	9.7	5.5	3.4	9.2	5.3	3.2	8.7	5.1	3.1		
90	TC	21.0	20.1	19.0	20.5	19.6	18.5	20.0	19.1	18.0	19.5	18.7	17.6		
	SC	19.7	18.9	17.8	19.2	18.4	17.4	18.7	18.0	16.9	18.3	17.5	16.5		
	gpm	6.0	4.6	3.6	5.9	4.6	3.6	5.8	4.4	3.5	5.6	4.3	3.4		
	wpd	11.1	6.6	4.0	10.5	6.3	3.9	10.2	5.9	3.7	9.7	5.7	3.5		

3-Row Chilled Water Cooling

EDB	EWT	43						44						45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	18.3	15.9	13.6	17.2	14.9	12.7	16.1	13.9	11.8	15.0	12.9	11.0			
	SC	12.3	11.3	10.3	11.8	10.9	9.9	11.4	10.5	9.5	11.0	10.1	9.2			
	gpm	5.3	3.7	2.6	5.0	3.5	2.4	4.7	3.2	2.3	4.4	3.0	2.1			
	wpd	4.5	2.2	1.1	4.0	1.9	0.9	3.5	1.7	0.8	3.1	1.5	0.7			
76	TC	18.6	16.5	14.4	17.6	15.5	13.6	16.5	14.6	12.9	15.6	13.7	12.2			
	SC	13.4	12.5	11.6	13.0	12.1	11.3	12.6	11.7	10.9	12.2	11.4	10.5			
	gpm	5.4	3.8	2.8	5.1	3.6	2.6	4.7	3.4	2.5	4.4	3.2	2.3			
	wpd	4.6	2.3	1.3	4.1	2.1	1.1	3.6	1.9	1.0	3.2	1.6	0.9			
78	TC	19.0	17.1	15.4	18.0	16.3	14.6	17.1	15.4	14.0	16.2	14.7	13.3			
	SC	14.6	13.8	12.9	14.2	13.4	12.6	13.8	13.0	12.3	13.4	12.7	11.9			
	gpm	5.5	4.0	2.9	5.2	3.8	2.8	4.9	3.5	2.7	4.7	3.4	2.6			
	wpd	4.9	2.6	1.4	4.4	2.3	1.3	3.9	2.0	1.2	3.5	1.9	1.1			
80	TC	19.5	17.8	16.4	18.6	17.0	15.7	17.7	16.3	15.1	16.9	15.6	14.5			
	SC	15.8	15.0	14.3	15.4	14.7	13.9	15.0	14.3	13.6	14.6	14.0	13.2			
	gpm	5.7	4.1	3.2	5.4	3.9	3.0	5.1	3.8	2.9	4.8	3.6	2.8			
	wpd	5.1	2.7	1.6	4.6	2.5	1.5	4.2	2.3	1.4	3.7	2.1	1.3			
82	TC	20.0	18.6	17.4	19.2	17.9	16.8	18.4	17.3	16.2	17.7	16.7	14.7			
	SC	17.0	16.3	15.6	16.6	16.0	15.3	16.3	15.7	14.9	15.9	15.3	13.9			
	gpm	5.7	4.3	3.3	5.5	4.1	3.2	5.3	4.0	3.1	5.1	3.8	2.8			
	wpd	5.3	3.0	1.8	4.9	2.8	1.7	4.5	2.6	1.5	4.2	2.4	1.3			
84	TC	20.6	19.5	18.5	19.9	18.9	17.1	19.2	18.3	16.5	18.6	17.2	15.9			
	SC	18.2	17.6	17.0	17.9	17.3	16.2	17.6	16.9	15.6	17.2	16.3	15.1			
	gpm	6.0	4.5	3.5	5.7	4.4	3.3	5.6	4.2	3.2	5.4	4.0	3.1			
	wpd	5.7	3.3	2.0	5.3	3.1	1.8	5.0	2.9	1.6	4.6	2.6	1.5			
86	TC	21.4	20.5	18.8	20.8	19.9	18.3	20.2	18.9	17.7	19.4	18.4	17.2			
	SC	19.5	18.9	17.8	19.2	18.6	17.3	18.8	17.9	16.8	18.4	17.4	16.3			
	gpm	6.2	4.7	3.6	6.0	4.6	3.5	5.8	4.4	3.4	5.6	4.2	3.3			
	wpd	6.2	3.6	2.1	5.9	3.4	2.0	5.4	3.1	1.9	5.0	2.9	1.8			
88	TC	22.3	21.1	20.0	21.6	20.6	19.5	21.0	20.1	19.0	20.5	19.5	18.4			
	SC	20.8	20.0	19.0	20.4	19.5	18.5	19.9	19.0	17.9	19.4	18.5	17.4			
	gpm	6.4	4.9	3.8	6.3	4.7	3.8	6.1	4.6	3.6	6.0	4.5	3.5			
	wpd	6.6	3.9	2.4	6.3	3.6	2.3	6.0	3.4	2.1	5.7	3.3	2.0			
90	TC	23.2	22.3	21.2	22.7	21.7	20.7	22.1	21.2	20.2	21.6	20.7	19.6			
	SC	21.9	21.1	20.1	21.5	20.6	19.6	21.0	20.1	19.1	20.5	19.6	18.6			
	gpm	6.6	5.1	4.1	6.6	5.1	4.0	6.4	4.9	3.9	6.3	4.7	3.8			
	wpd	7.1	4.2	2.7	6.9	4.1	2.6	6.6	3.9	2.5	6.3	3.6	2.3			

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	22.9	21.0	19.1	21.7	19.8	17.9	20.4	18.6	16.7	19.2	17.4	15.6	
	SC	14.4	13.6	12.8	13.9	13.1	12.3	13.4	12.6	11.9	12.9	12.1	11.4	
	gpm	6.6	4.9	3.7	6.3	4.5	3.5	5.9	4.2	3.2	5.6	4.0	3.0	
	wpd	7.9	4.3	2.5	7.2	3.8	2.2	6.3	3.3	1.9	5.6	2.9	1.6	
76	TC	23.1	21.4	19.7	21.9	20.2	18.6	20.7	19.1	17.5	19.5	18.0	16.5	
	SC	15.6	14.8	14.1	15.1	14.4	13.7	14.6	13.9	13.2	14.1	13.4	12.8	
	gpm	6.7	4.9	3.8	6.3	4.6	3.6	6.0	4.4	3.4	5.6	4.2	3.1	
	wpd	8.1	4.4	2.6	7.2	3.9	2.4	6.5	3.5	2.1	5.8	3.1	1.8	
78	TC	23.3	21.8	20.3	22.2	20.7	19.3	21.1	19.6	18.3	20.0	18.6	17.4	
	SC	16.7	16.1	15.4	16.3	15.6	15.0	15.8	15.2	14.6	15.3	14.7	14.2	
	gpm	6.7	5.0	3.9	6.4	4.8	3.7	6.0	4.5	3.5	5.7	4.3	3.4	
	wpd	8.3	4.6	2.8	7.5	4.2	2.5	6.6	3.8	2.3	6.0	3.4	2.1	
80	TC	23.7	22.3	21.0	22.6	21.3	20.0	21.5	20.3	19.2	20.5	19.3	18.4	
	SC	17.9	17.3	16.8	17.5	16.9	16.4	17.0	16.5	16.0	16.6	16.1	15.6	
	gpm	6.8	5.2	4.0	6.5	4.9	3.8	6.2	4.6	3.7	5.9	4.5	3.5	
	wpd	8.5	4.9	2.9	7.7	4.4	2.7	7.0	3.9	2.5	6.3	3.6	2.3	
82	TC	24.0	22.8	21.7	23.0	21.9	20.9	22.0	21.0	20.1	21.0	20.2	19.4	
	SC	19.1	18.6	18.1	18.7	18.2	17.7	18.3	17.8	17.4	17.8	17.4	17.0	
	gpm	6.9	5.3	4.2	6.7	5.0	4.0	6.4	4.9	3.8	6.0	4.6	3.8	
	wpd	8.7	5.0	3.1	8.1	4.6	2.9	7.3	4.3	2.7	6.6	3.9	2.6	
84	TC	24.4	23.5	22.6	23.5	22.6	21.8	22.6	21.8	21.1	21.7	21.1	20.5	
	SC	20.4	19.9	19.5	19.9	19.5	19.1	19.5	19.2	18.8	19.2	18.8	18.5	
	gpm	7.0	5.4	4.3	6.7	5.3	4.2	6.5	5.0	4.1	6.3	4.9	3.9	
	wpd	8.9	5.3	3.4	8.3	5.0	3.3	7.7	4.6	3.0	7.2	4.3	2.8	
86	TC	24.9	24.2	23.5	24.1	23.4	22.8	23.2	22.7	22.2	22.5	22.1	20.7	
	SC	21.6	21.3	20.9	21.2	20.9	20.6	20.9	20.6	20.2	20.5	20.2	19.5	
	gpm	7.2	5.6	4.5	6.9	5.4	4.4	6.7	5.3	4.2	6.5	5.1	4.0	
	wpd	9.5	5.6	3.8	8.7	5.3	3.5	8.1	5.0	3.3	7.7	4.7	2.9	
88	TC	25.5	25.0	24.5	24.8	24.4	23.1	24.1	23.3	22.5	23.3	22.7	21.9	
	SC	22.9	22.6	22.3	22.6	22.3	21.8	22.2	22.0	21.2	22.0	21.4	20.7	
	gpm	7.4	5.8	4.7	7.1	5.6	4.5	7.0	5.4	4.3	6.7	5.3	4.2	
	wpd	9.9	6.1	4.0	9.3	5.8	3.6	8.9	5.3	3.4	8.3	5.0	3.3	
90	TC	26.4	25.6	24.9	25.6	25.1	24.4	25.1	24.5	23.8	24.5	23.9	23.2	
	SC	24.3	24.2	23.5	24.1	23.6	23.0	23.6	23.1	22.4	23.1	22.5	21.9	
	gpm	7.6	5.9	4.8	7.4	5.8	4.7	7.2	5.6	4.5	7.1	5.5	4.5	
	wpd	10.5	6.3	4.2	9.9	6.1	4.0	9.5	5.8	3.8	9.1	5.5	3.6	

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	28.3	26.8	25.1	26.9	25.3	23.7	25.5	23.9	22.3	24.0	22.5	20.9
	SC	19.1	18.3	17.5	18.4	17.6	16.8	17.7	16.9	16.2	17.0	16.3	15.5
	gpm	7.2	5.4	4.2	6.8	5.1	4.0	6.4	4.8	3.8	6.1	4.5	3.6
	wpd	8.2	4.7	2.8	7.3	4.2	2.5	6.5	3.7	2.3	5.8	3.3	2.0
76	TC	28.4	27.0	25.5	27.0	25.7	24.2	25.7	24.3	22.9	24.3	23.0	21.6
	SC	20.4	19.7	19.0	19.7	19.1	18.4	19.1	18.4	17.7	18.4	17.8	17.1
	gpm	7.2	5.4	4.3	6.9	5.2	4.1	6.5	4.9	3.9	6.1	4.6	3.6
	wpd	8.2	4.7	2.9	7.5	4.3	2.6	6.7	3.8	2.4	5.9	3.4	2.1
78	TC	28.5	27.3	26.0	27.2	26.0	24.8	25.9	24.7	23.6	24.6	23.5	22.4
	SC	21.8	21.2	20.5	21.2	20.6	19.9	20.5	19.9	19.4	19.9	19.3	18.8
	gpm	7.2	5.5	4.4	6.9	5.3	4.2	6.6	5.0	4.0	6.3	4.8	3.8
	wpd	8.2	4.8	3.0	7.5	4.4	2.7	6.8	3.9	2.5	6.2	3.6	2.3
80	TC	28.8	27.7	26.6	27.5	26.5	25.4	26.2	25.3	24.3	25.0	24.1	23.2
	SC	23.2	22.7	22.1	22.6	22.1	21.5	22.0	21.5	21.0	21.3	20.9	20.5
	gpm	7.3	5.6	4.5	7.0	5.4	4.3	6.7	5.1	4.1	6.4	4.9	3.9
	wpd	8.3	5.0	3.1	7.7	4.6	2.9	7.0	4.2	2.6	6.4	3.8	2.4
82	TC	29.0	28.1	27.2	27.8	26.9	26.1	26.6	25.8	25.1	25.4	24.7	24.1
	SC	24.7	24.2	23.7	24.0	23.6	23.2	23.4	23.0	22.7	22.9	22.5	22.2
	gpm	7.3	5.7	4.6	7.0	5.4	4.4	6.7	5.2	4.2	6.4	5.0	4.1
	wpd	8.5	5.1	3.4	7.8	4.7	3.0	7.2	4.3	2.8	6.5	3.9	2.6
84	TC	29.3	28.6	27.9	28.2	27.5	26.9	27.1	26.5	26.0	26.0	25.5	25.1
	SC	26.1	25.7	25.4	25.5	25.2	24.9	25.0	24.7	24.4	24.4	24.2	24.0
	gpm	7.4	5.8	4.7	7.1	5.6	4.5	6.9	5.4	4.4	6.6	5.1	4.2
	wpd	8.7	5.4	3.5	8.0	5.0	3.3	7.5	4.6	3.0	6.8	4.2	2.8
86	TC	29.7	29.2	28.7	28.6	28.2	27.8	27.6	27.3	27.0	26.7	26.5	26.2
	SC	27.6	27.3	27.1	27.1	26.8	26.6	26.5	26.4	26.2	26.1	25.9	25.8
	gpm	7.6	5.9	4.8	7.3	5.8	4.7	7.0	5.5	4.5	6.7	5.4	4.5
	wpd	9.0	5.5	3.7	8.3	5.2	3.5	7.8	4.8	3.3	7.2	4.6	3.1
88	TC	30.2	29.9	29.6	29.2	29.1	28.9	28.4	28.3	27.5	27.2	27.1	26.8
	SC	29.2	29.0	28.8	28.7	28.6	28.4	28.2	28.1	27.4	27.2	27.2	27.0
	gpm	7.6	6.1	5.0	7.4	5.9	4.8	7.2	5.8	4.6	6.9	5.5	4.5
	wpd	9.2	5.8	3.9	8.7	5.5	3.7	8.2	5.2	3.4	7.5	4.8	3.3
90	TC	30.9	30.9	30.1	29.7	29.6	29.4	29.1	29.0	28.8	28.5	28.4	28.1
	SC	30.8	30.8	29.9	29.8	29.7	29.6	29.5	29.4	29.3	29.1	29.1	28.9
	gpm	7.9	6.3	5.1	7.6	6.0	5.0	7.4	5.9	4.8	7.3	5.8	4.8
	wpd	9.8	6.2	4.1	9.0	5.6	3.9	8.7	5.5	3.7	8.3	5.2	3.6

2-Row Chilled Water Cooling

EDB	EWT	43						44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	18.0	15.2	12.4	16.9	14.1	11.4	15.8	13.1	10.4	14.6	12.0	9.5
	SC	10.6	9.6	8.5	10.2	9.2	8.1	9.8	8.8	7.7	9.4	8.4	7.3
	gpm	5.2	3.5	2.4	4.9	3.2	2.2	4.6	3.0	2.0	4.3	2.8	1.9
	wpd	8.2	3.7	1.7	7.2	3.2	1.4	6.3	2.8	1.2	5.5	2.4	1.0
76	TC	17.9	15.5	13.0	16.9	14.5	12.1	15.9	13.6	11.3	14.8	12.6	10.5
	SC	11.6	10.7	9.7	11.2	10.3	9.3	10.8	9.9	8.9	10.4	9.5	8.6
	gpm	5.2	3.6	2.5	4.9	3.3	2.3	4.6	3.2	2.2	4.3	2.9	2.0
	wpd	8.2	3.9	1.9	7.2	3.4	1.6	6.3	3.1	1.4	5.5	2.6	1.2
78	TC	18.0	15.9	13.7	17.1	15.0	12.9	16.2	14.1	12.2	15.3	13.3	11.5
	SC	12.6	11.8	10.8	12.3	11.4	10.5	11.9	11.1	10.2	11.6	10.7	9.8
	gpm	5.2	3.7	2.6	4.9	3.5	2.5	4.6	3.2	2.3	4.4	3.1	2.2
	wpd	8.2	4.2	2.1	7.5	3.7	1.9	6.6	3.2	1.6	5.9	2.9	1.5
80	TC	18.3	16.4	14.5	17.5	15.6	13.8	16.6	14.8	13.1	15.8	14.0	12.5
	SC	13.7	12.9	12.1	13.4	12.6	11.8	13.0	12.2	11.4	12.7	11.9	11.1
	gpm	5.3	3.8	2.8	5.0	3.6	2.6	4.8	3.4	2.6	4.6	3.2	2.4
	wpd	8.4	4.4	2.4	7.7	3.9	2.1	7.0	3.5	2.0	6.3	3.2	1.7
82	TC	18.7	17.0	15.3	17.9	16.2	14.7	17.1	15.5	14.1	16.3	14.9	13.5
	SC	14.8	14.1	13.3	14.5	13.7	12.9	14.2	13.4	12.6	13.8	13.1	12.3
	gpm	5.4	3.9	2.9	5.2	3.8	2.9	4.9	3.6	2.7	4.7	3.4	2.6
	wpd	8.9	4.7	2.6	8.2	4.4	2.5	7.5	3.9	2.2	6.8	3.5	2.1
84	TC	19.2	17.7	16.2	18.4	17.0	15.6	17.6	16.3	15.1	16.9	15.7	14.2
	SC	16.0	15.3	14.5	15.6	15.0	14.1	15.3	14.6	13.8	15.0	14.3	13.4
	gpm	5.6	4.1	3.1	5.3	3.9	3.0	5.1	3.8	2.9	4.9	3.6	2.7
	wpd	9.4	5.1	2.9	8.4	4.7	2.8	7.9	4.4	2.6	7.2	4.0	2.2
86	TC	19.6	18.4	17.2	18.9	17.8	16.6	18.3	17.2	15.9	17.7	16.7	15.4
	SC	17.1	16.4	15.7	16.8	16.1	15.3	16.5	15.8	14.9	16.1	15.4	14.4
	gpm	5.6	4.3	3.3	5.5	4.1	3.2	5.3	3.9	3.1	5.1	3.9	2.9
	wpd	9.7	5.5	3.4	9.2	5.1	3.1	8.4	4.7	2.9	7.9	4.6	2.6
88	TC	20.3	19.3	18.0	19.6	18.7	17.5	19.1	18.1	17.0	18.5	17.6	16.5
	SC	18.3	17.6	16.9	17.9	17.3	16.4	17.6	17.0	15.9	17.4	16.5	15.5
	gpm	5.9	4.5	3.5	5.6	4.3	3.4	5.5	4.2	3.2	5.3	4.1	3.2
	wpd	10.5	6.1	3.7	9.7	5.7	3.5	9.2	5.3	3.2	8.7	5.1	3.1
90	TC	21.0	20.2	19.0	20.5	19.7	18.6	20.0	19.2	18.1	19.5	18.7	17.6
	SC	19.4	18.8	17.9	19.0	18.5	17.4	18.8	18.0	17.0	18.3	17.5	16.5
	gpm	6.1	4.6	3.6	6.0	4.6	3.6	5.8	4.4	3.5	5.6	4.3	3.4
	wpd	11.4	6.6	4.0	10.8	6.3	3.9	10.2	5.9	3.7	9.7	5.7	3.5

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	21.2	18.5	15.7	20.0	17.3	14.5	18.8	16.1	13.4	17.6	14.9	12.3
	SC	12.2	11.1	9.9	11.7	10.6	9.5	11.2	10.1	9.0	10.7	9.7	8.6
	gpm	6.1	4.3	3.0	5.8	4.0	2.8	5.4	3.7	2.6	5.1	3.5	2.3
	wpd	6.0	3.0	1.5	5.4	2.6	1.3	4.7	2.2	1.1	4.1	1.9	0.9
76	TC	21.3	18.8	16.2	20.1	17.7	15.2	19.0	16.6	14.2	17.9	15.5	13.2
	SC	13.2	12.2	11.2	12.7	11.7	10.7	12.3	11.3	10.3	11.8	10.9	9.9
	gpm	6.2	4.4	3.1	5.8	4.1	2.9	5.5	3.8	2.7	5.1	3.5	2.6
	wpd	6.2	3.1	1.5	5.4	2.7	1.4	4.9	2.4	1.2	4.2	2.0	1.1
78	TC	21.4	19.2	16.9	20.4	18.1	15.9	19.3	17.1	15.0	18.2	16.1	14.1
	SC	14.3	13.3	12.4	13.8	12.9	12.0	13.4	12.5	11.6	13.0	12.1	11.2
	gpm	6.2	4.4	3.2	5.9	4.1	3.1	5.6	3.9	2.9	5.3	3.7	2.7
	wpd	6.2	3.2	1.7	5.6	2.8	1.5	5.0	2.5	1.3	4.5	2.2	1.2
80	TC	21.8	19.7	17.6	20.7	18.7	16.7	19.7	17.7	15.8	18.6	16.8	15.0
	SC	15.4	14.5	13.7	15.0	14.1	13.3	14.6	13.7	12.9	14.1	13.4	12.6
	gpm	6.3	4.5	3.4	6.0	4.3	3.2	5.7	4.1	3.0	5.4	3.8	2.9
	wpd	6.3	3.3	1.9	5.7	3.0	1.7	5.1	2.7	1.5	4.6	2.4	1.3
82	TC	22.1	20.2	18.3	21.1	19.3	17.5	20.1	18.4	16.7	19.2	17.5	16.0
	SC	16.6	15.7	14.9	16.1	15.3	14.6	15.7	15.0	14.2	15.3	14.6	13.9
	gpm	6.4	4.7	3.5	6.1	4.4	3.4	5.8	4.2	3.2	5.5	4.0	3.1
	wpd	6.6	3.5	2.0	6.0	3.2	1.9	5.4	2.9	1.7	4.9	2.6	1.5
84	TC	22.5	20.8	19.1	21.5	19.9	18.4	20.6	19.0	17.7	19.7	18.3	17.1
	SC	17.7	17.0	16.2	17.3	16.6	15.9	16.9	16.2	15.6	16.5	15.9	15.2
	gpm	6.5	4.8	3.7	6.2	4.6	3.5	6.0	4.4	3.4	5.7	4.2	3.3
	wpd	6.8	3.7	2.2	6.2	3.4	2.0	5.7	3.1	1.9	5.1	2.9	1.8
86	TC	22.9	21.4	20.0	22.0	20.6	19.3	21.2	19.8	18.7	20.3	19.2	18.1
	SC	18.9	18.2	17.5	18.5	17.8	17.2	18.1	17.5	16.9	17.8	17.2	16.5
	gpm	6.6	5.0	3.8	6.3	4.7	3.7	6.1	4.6	3.6	5.9	4.4	3.5
	wpd	7.1	4.0	2.4	6.5	3.6	2.2	6.0	3.4	2.1	5.6	3.2	1.9
88	TC	23.4	22.1	20.9	22.6	21.4	20.3	21.8	20.7	19.7	21.1	20.1	18.5
	SC	20.1	19.4	18.8	19.7	19.1	18.5	19.4	18.8	18.2	19.0	18.5	17.5
	gpm	6.8	5.1	4.1	6.6	4.9	3.9	6.3	4.7	3.8	6.1	4.6	3.5
	wpd	7.4	4.2	2.7	6.9	3.9	2.5	6.3	3.6	2.3	6.0	3.4	2.0
90	TC	24.0	22.9	21.9	23.2	22.3	21.4	22.6	21.7	20.2	21.9	20.7	19.7
	SC	21.3	20.8	20.1	21.0	20.4	19.8	20.6	20.1	19.1	20.3	19.6	18.6
	gpm	6.9	5.3	4.2	6.7	5.1	4.1	6.6	5.0	3.9	6.3	4.7	3.8
	wpd	7.7	4.5	2.9	7.2	4.2	2.8	6.9	4.0	2.5	6.5	3.6	2.3

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.3	24.3	22.0	25.0	22.9	20.7	23.7	21.6	19.3	22.4	20.3	18.0
	SC	14.4	13.6	12.7	13.9	13.0	12.1	13.3	12.5	11.6	12.8	11.9	11.0
	gpm	7.6	5.6	4.2	7.2	5.3	4.0	6.8	5.0	3.7	6.4	4.7	3.5
	wpd	10.5	5.6	3.3	9.5	5.0	2.9	8.5	4.6	2.5	7.5	4.0	2.2
76	TC	26.3	24.4	22.3	25.1	23.1	21.0	23.8	21.8	19.8	22.5	20.6	18.6
	SC	15.5	14.7	13.8	15.0	14.1	13.3	14.4	13.6	12.8	13.9	13.1	12.3
	gpm	7.6	5.6	4.3	7.2	5.3	4.0	6.9	5.0	3.8	6.5	4.7	3.5
	wpd	10.5	5.8	3.4	9.5	5.2	2.9	8.7	4.6	2.6	7.7	4.0	2.3
78	TC	26.4	24.6	22.7	25.2	23.4	21.5	23.9	22.1	20.3	22.7	20.9	19.2
	SC	16.6	15.8	15.0	16.1	15.3	14.6	15.6	14.8	14.1	15.0	14.3	13.6
	gpm	7.6	5.6	4.4	7.2	5.4	4.2	6.9	5.1	3.9	6.5	4.9	3.7
	wpd	10.5	5.8	3.5	9.5	5.3	3.1	8.7	4.7	2.8	7.7	4.3	2.5
80	TC	26.6	24.9	23.2	25.4	23.7	22.0	24.2	22.6	20.9	23.0	21.4	19.8
	SC	17.7	17.0	16.3	17.2	16.5	15.8	16.7	16.0	15.4	16.2	15.6	14.9
	gpm	7.7	5.7	4.5	7.3	5.5	4.2	7.0	5.2	4.0	6.6	4.9	3.8
	wpd	10.8	6.0	3.6	9.7	5.5	3.3	8.9	4.9	2.9	7.9	4.4	2.7
82	TC	26.8	25.2	23.7	25.6	24.1	22.6	24.5	23.0	21.6	23.3	21.9	20.6
	SC	18.9	18.2	17.6	18.4	17.7	17.1	17.9	17.3	16.7	17.4	16.8	16.3
	gpm	7.7	5.8	4.5	7.4	5.6	4.3	7.1	5.3	4.2	6.7	5.1	3.9
	wpd	10.8	6.1	3.8	9.9	5.6	3.4	9.1	5.0	3.1	8.3	4.7	2.8
84	TC	27.0	25.6	24.2	25.9	24.6	23.2	24.8	23.5	22.3	23.7	22.5	21.3
	SC	20.0	19.4	18.8	19.5	19.0	18.4	19.1	18.5	18.0	18.6	18.1	17.6
	gpm	7.8	5.9	4.6	7.4	5.6	4.5	7.1	5.4	4.3	6.8	5.2	4.1
	wpd	11.0	6.3	3.9	10.1	5.8	3.6	9.3	5.3	3.4	8.5	4.9	3.0
86	TC	27.3	26.1	24.9	26.2	25.0	23.9	25.1	24.1	23.0	24.1	23.1	22.2
	SC	21.2	20.7	20.1	20.7	20.2	19.7	20.3	19.8	19.3	19.8	19.4	19.0
	gpm	7.8	6.0	4.8	7.5	5.8	4.6	7.2	5.6	4.4	7.0	5.3	4.2
	wpd	11.2	6.6	4.2	10.3	6.1	3.9	9.5	5.6	3.5	8.9	5.2	3.3
88	TC	27.6	26.5	25.5	26.5	25.6	24.7	25.6	24.7	23.9	24.6	23.8	23.1
	SC	22.4	21.9	21.5	21.9	21.5	21.1	21.5	21.1	20.7	21.1	20.7	20.4
	gpm	7.9	6.1	4.9	7.7	5.9	4.7	7.4	5.7	4.6	7.1	5.5	4.5
	wpd	11.4	6.8	4.4	10.8	6.3	4.0	9.9	6.0	3.9	9.1	5.5	3.6
90	TC	27.9	27.1	26.3	27.0	26.2	25.5	26.1	25.4	24.8	25.2	24.6	24.1
	SC	23.6	23.2	22.8	23.2	22.8	22.5	22.8	22.4	22.1	22.4	22.1	21.8
	gpm	8.1	6.3	5.0	7.8	6.0	4.9	7.5	5.9	4.8	7.3	5.6	4.6
	wpd	11.9	7.2	4.6	11.0	6.6	4.4	10.3	6.3	4.2	9.7	5.8	3.9

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	32.1	30.6	28.8	30.7	29.1	27.3	29.2	27.6	25.7	27.8	26.1	24.2
	SC	19.0	18.3	17.5	18.3	17.6	16.7	17.7	16.9	16.0	17.0	16.2	15.3
	gpm	8.1	6.2	4.8	7.8	5.9	4.6	7.4	5.6	4.3	7.0	5.3	4.1
	wpd	10.4	6.1	3.7	9.6	5.5	3.4	8.7	5.0	2.9	7.8	4.4	2.6
76	TC	32.1	30.7	29.0	30.7	29.3	27.5	29.3	27.8	26.0	27.9	26.3	24.5
	SC	20.4	19.7	18.8	19.7	19.0	18.1	19.0	18.3	17.4	18.3	17.6	16.8
	gpm	8.1	6.2	4.9	7.8	5.9	4.6	7.4	5.6	4.4	7.0	5.3	4.2
	wpd	10.4	6.1	3.8	9.6	5.5	3.4	8.7	5.0	3.0	7.8	4.4	2.7
78	TC	32.1	30.8	29.2	30.8	29.4	27.8	29.4	28.0	26.4	28.0	26.6	25.0
	SC	21.7	21.0	20.3	21.0	20.4	19.6	20.3	19.7	18.9	19.7	19.0	18.3
	gpm	8.2	6.2	4.9	7.8	6.0	4.7	7.4	5.7	4.5	7.1	5.4	4.2
	wpd	10.6	6.1	3.8	9.6	5.6	3.5	8.7	5.1	3.1	8.0	4.6	2.8
80	TC	32.2	31.0	29.6	30.8	29.7	28.3	29.5	28.3	26.9	28.1	26.9	25.6
	SC	23.0	22.4	21.8	22.4	21.8	21.1	21.7	21.1	20.5	21.0	20.5	19.8
	gpm	8.1	6.3	5.0	7.8	6.0	4.8	7.4	5.8	4.5	7.1	5.4	4.3
	wpd	10.4	6.2	3.9	9.6	5.6	3.6	8.7	5.2	3.3	8.0	4.7	2.9
82	TC	32.3	31.3	30.0	31.0	30.0	28.7	29.7	28.6	27.4	28.4	27.3	26.1
	SC	24.4	23.9	23.2	23.7	23.2	22.6	23.1	22.6	22.0	22.5	22.0	21.4
	gpm	8.2	6.4	5.1	7.9	6.1	4.8	7.5	5.8	4.6	7.2	5.5	4.4
	wpd	10.6	6.4	4.1	9.8	5.8	3.7	8.9	5.4	3.4	8.2	4.8	3.0
84	TC	32.5	31.6	30.4	31.2	30.3	29.2	30.0	29.0	28.0	28.7	27.8	26.8
	SC	25.8	25.3	24.8	25.2	24.7	24.2	24.5	24.1	23.6	23.9	23.5	23.0
	gpm	8.2	6.4	5.1	7.9	6.1	4.9	7.6	5.9	4.7	7.3	5.7	4.5
	wpd	10.7	6.5	4.2	10.0	5.9	3.8	9.0	5.5	3.5	8.3	5.1	3.3
86	TC	32.7	31.9	30.9	31.5	30.6	29.7	30.2	29.4	28.6	29.0	28.3	27.5
	SC	27.2	26.8	26.3	26.6	26.2	25.7	26.0	25.6	25.2	25.4	25.0	24.6
	gpm	8.3	6.4	5.2	7.9	6.2	5.0	7.6	6.0	4.8	7.3	5.8	4.7
	wpd	10.9	6.5	4.3	10.0	6.1	3.9	9.2	5.6	3.7	8.5	5.2	3.5
88	TC	32.9	32.2	31.4	31.7	31.1	30.3	30.5	30.0	29.3	29.4	28.9	28.3
	SC	28.6	28.3	27.9	28.0	27.7	27.3	27.4	27.1	26.8	26.8	26.6	26.3
	gpm	8.3	6.5	5.3	8.0	6.3	5.1	7.7	6.1	4.9	7.5	5.8	4.8
	wpd	10.9	6.7	4.4	10.2	6.2	4.2	9.4	5.8	3.8	8.9	5.4	3.6
90	TC	33.2	32.7	32.1	32.1	31.6	31.1	30.9	30.6	30.1	29.9	29.5	29.2
	SC	30.1	29.8	29.5	29.5	29.3	29.0	28.9	28.7	28.5	28.4	28.2	28.0
	gpm	8.4	6.7	5.4	8.1	6.4	5.2	7.8	6.2	5.1	7.6	6.0	4.9
	wpd	11.1	7.0	4.7	10.4	6.5	4.3	9.6	6.1	4.1	9.0	5.6	3.8

2-Row Chilled Water Cooling

EDB	EWT	42				43			44				45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	20.6	18.4	15.3	19.6	17.2	14.0	18.5	16.1	12.7	17.5	14.8	11.5		
	SC	10.4	9.5	8.4	10.0	9.1	7.9	9.6	8.7	7.5	9.2	8.2	7.1		
	gpm	6.0	4.3	2.9	5.6	3.9	2.7	5.3	3.7	2.5	5.0	3.4	2.2		
	wpd	10.8	5.5	2.6	9.7	4.7	2.2	8.7	4.2	1.9	7.7	3.5	1.5		
76	TC	20.7	18.4	15.3	19.7	17.2	14.2	18.6	16.0	13.1	17.5	14.8	12.0		
	SC	11.4	10.5	9.4	11.0	10.1	9.0	10.6	9.7	8.6	10.2	9.2	8.2		
	gpm	6.0	4.3	2.9	5.6	3.9	2.7	5.3	3.7	2.6	5.0	3.4	2.3		
	wpd	10.8	5.5	2.6	9.7	4.7	2.2	8.7	4.2	2.0	7.7	3.5	1.6		
78	TC	20.7	18.3	15.6	19.6	17.2	14.6	18.5	16.1	13.6	17.5	15.1	12.6		
	SC	12.4	11.5	10.5	12.0	11.1	10.1	11.6	10.7	9.7	11.2	10.3	9.3		
	gpm	6.0	4.3	3.0	5.6	3.9	2.8	5.3	3.7	2.6	5.0	3.5	2.4		
	wpd	10.8	5.5	2.8	9.7	4.7	2.4	8.7	4.2	2.1	7.7	3.7	1.7		
80	TC	20.7	18.6	16.2	19.7	17.6	15.3	18.7	16.7	14.4	17.7	15.7	13.4		
	SC	13.3	12.5	11.6	12.9	12.1	11.2	12.6	11.8	10.8	12.2	11.4	10.5		
	gpm	6.0	4.3	3.1	5.7	4.1	2.9	5.4	3.9	2.8	5.1	3.6	2.6		
	wpd	10.8	5.7	2.9	10.0	5.1	2.6	8.9	4.6	2.4	7.9	4.0	2.0		
82	TC	20.6	18.8	16.6	19.7	17.9	15.8	18.8	17.0	15.0	17.9	16.1	14.2		
	SC	14.4	13.6	12.7	14.0	13.3	12.4	13.6	12.9	12.0	13.3	12.6	11.8		
	gpm	6.0	4.3	3.2	5.6	4.1	3.0	5.4	3.9	2.9	5.2	3.7	2.7		
	wpd	10.8	5.7	3.1	9.7	5.1	2.8	8.9	4.7	2.5	8.2	4.2	2.2		
84	TC	20.9	19.3	17.3	20.0	18.4	16.5	19.2	17.6	15.8	18.3	16.7	15.0		
	SC	15.4	14.8	13.9	15.1	14.4	13.6	14.7	14.1	13.3	14.4	13.7	13.0		
	gpm	6.0	4.4	3.3	5.8	4.3	3.2	5.6	4.0	3.0	5.3	3.9	2.9		
	wpd	11.1	5.9	3.4	10.2	5.5	3.1	9.4	4.9	2.8	8.7	4.6	2.5		
86	TC	21.3	19.8	18.0	20.5	19.0	17.3	19.7	18.2	16.6	18.8	17.4	15.9		
	SC	16.5	15.9	15.1	16.2	15.5	14.8	15.9	15.2	14.5	15.5	14.9	14.2		
	gpm	6.1	4.6	3.5	6.0	4.4	3.3	5.6	4.2	3.2	5.4	4.0	3.1		
	wpd	11.4	6.3	3.7	10.8	5.9	3.4	9.7	5.3	3.1	8.9	4.9	2.9		
88	TC	21.7	20.3	18.7	20.9	19.5	18.1	20.1	18.8	17.5	19.3	18.1	16.9		
	SC	17.7	17.0	16.3	17.3	16.7	16.0	17.0	16.4	15.7	16.6	16.1	15.3		
	gpm	6.3	4.7	3.6	6.0	4.5	3.5	5.8	4.3	3.4	5.6	4.2	3.2		
	wpd	11.9	6.8	4.0	11.1	6.1	3.7	10.2	5.7	3.5	9.4	5.3	3.2		
90	TC	22.2	20.9	19.6	21.4	20.2	18.9	20.6	19.6	18.4	19.9	19.0	17.9		
	SC	18.8	18.2	17.5	18.4	17.9	17.1	18.1	17.6	16.8	17.8	17.3	16.5		
	gpm	6.4	4.9	3.8	6.2	4.6	3.6	6.0	4.6	3.6	5.7	4.4	3.5		
	wpd	12.5	7.2	4.4	11.7	6.6	4.0	10.8	6.3	3.9	10.0	5.9	3.7		

3-Row Chilled Water Cooling

EDB	EWT	43						44				45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	24.7	21.9	18.8	23.5	20.6	17.4	22.2	19.4	16.1	21.0	18.0	14.8	
	SC	12.2	11.1	9.9	11.7	10.6	9.4	11.2	10.1	8.9	10.7	9.6	8.4	
	gpm	7.1	5.1	3.6	6.8	4.7	3.3	6.4	4.4	3.1	6.0	4.1	2.9	
	wpd	8.1	4.1	2.1	7.4	3.6	1.8	6.6	3.2	1.5	5.9	2.8	1.3	
76	TC	24.7	21.9	18.9	23.5	20.7	17.7	22.2	19.4	16.5	21.0	18.1	15.2	
	SC	13.2	12.1	10.9	12.7	11.6	10.5	12.2	11.1	10.0	11.7	10.6	9.5	
	gpm	7.1	5.1	3.6	6.8	4.7	3.4	6.4	4.4	3.2	6.0	4.1	2.9	
	wpd	8.1	4.1	2.1	7.4	3.6	1.9	6.6	3.2	1.6	5.9	2.8	1.4	
78	TC	24.6	22.0	19.3	23.4	20.8	18.1	22.2	19.6	16.9	21.0	18.5	15.8	
	SC	14.2	13.1	12.1	13.7	12.7	11.6	13.2	12.2	11.2	12.8	11.8	10.8	
	gpm	7.1	5.1	3.7	6.8	4.8	3.5	6.4	4.5	3.2	6.0	4.3	3.0	
	wpd	8.1	4.1	2.2	7.4	3.7	1.9	6.6	3.3	1.7	5.9	3.0	1.5	
80	TC	24.8	22.4	19.9	23.6	21.3	18.8	22.5	20.1	17.7	21.4	19.0	16.6	
	SC	15.2	14.2	13.2	14.7	13.8	12.8	14.3	13.3	12.4	13.8	12.9	12.0	
	gpm	7.2	5.2	3.8	6.8	4.9	3.6	6.5	4.7	3.4	6.2	4.4	3.2	
	wpd	8.3	4.4	2.4	7.4	3.9	2.1	6.8	3.5	1.9	6.2	3.1	1.6	
82	TC	24.7	22.5	20.3	23.7	21.5	19.2	22.6	20.4	18.3	21.5	19.4	17.3	
	SC	16.3	15.4	14.4	15.8	14.9	14.0	15.4	14.5	13.7	15.0	14.1	13.3	
	gpm	7.2	5.2	3.9	6.9	5.0	3.7	6.5	4.7	3.5	6.2	4.4	3.3	
	wpd	8.3	4.4	2.5	7.6	4.0	2.2	6.8	3.6	2.0	6.2	3.2	1.8	
84	TC	25.0	22.9	20.8	24.0	21.9	19.9	22.9	20.9	19.0	21.9	19.9	18.0	
	SC	17.4	16.5	15.7	17.0	16.1	15.3	16.5	15.7	14.9	16.1	15.3	14.5	
	gpm	7.2	5.3	4.0	6.9	5.1	3.8	6.6	4.8	3.6	6.3	4.6	3.5	
	wpd	8.4	4.5	2.6	7.7	4.1	2.4	7.1	3.7	2.1	6.5	3.4	1.9	
86	TC	25.3	23.3	21.5	24.3	22.4	20.6	23.2	21.4	19.7	22.3	20.5	18.8	
	SC	18.5	17.7	16.9	18.1	17.3	16.5	17.7	16.9	16.2	17.3	16.5	15.8	
	gpm	7.3	5.4	4.1	7.0	5.1	4.0	6.7	5.0	3.8	6.4	4.7	3.6	
	wpd	8.6	4.6	2.8	7.9	4.2	2.6	7.2	4.0	2.3	6.6	3.6	2.1	
88	TC	25.6	23.8	22.1	24.6	22.9	21.3	23.6	22.0	20.5	22.7	21.2	19.7	
	SC	19.6	18.9	18.1	19.2	18.5	17.8	18.8	18.1	17.4	18.4	17.8	17.1	
	gpm	7.4	5.5	4.2	7.1	5.3	4.1	6.8	5.1	3.9	6.6	4.9	3.8	
	wpd	8.8	4.9	2.9	8.1	4.5	2.7	7.4	4.1	2.5	6.9	3.9	2.3	
90	TC	25.9	24.4	22.8	25.0	23.5	22.0	24.1	22.6	21.3	23.2	21.8	20.7	
	SC	20.8	20.1	19.4	20.4	19.7	19.0	20.0	19.3	18.7	19.6	19.0	18.4	
	gpm	7.5	5.7	4.4	7.2	5.4	4.2	6.9	5.2	4.1	6.7	5.1	4.0	
	wpd	9.0	5.1	3.1	8.4	4.7	2.9	7.7	4.4	2.8	7.2	4.1	2.6	

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	29.8	28.0	25.7	28.6	26.7	24.3	27.3	25.3	22.9	26.0	23.9	21.4
	SC	14.4	13.7	12.7	13.9	13.1	12.1	13.3	12.5	11.6	12.8	12.0	11.0
	gpm	8.5	6.4	4.9	8.2	6.1	4.7	7.8	5.8	4.4	7.4	5.5	4.1
	wpd	13.3	7.5	4.4	12.3	6.8	4.0	11.2	6.1	3.5	10.1	5.5	3.0
76	TC	29.8	28.0	25.8	28.5	26.7	24.4	27.3	25.3	23.0	26.0	23.9	21.6
	SC	15.5	14.7	13.8	14.9	14.2	13.2	14.4	13.6	12.7	13.8	13.0	12.1
	gpm	8.5	6.4	4.9	8.2	6.1	4.7	7.8	5.9	4.4	7.4	5.5	4.2
	wpd	13.3	7.5	4.4	12.3	6.8	4.0	11.2	6.3	3.5	10.1	5.5	3.1
78	TC	29.8	28.0	25.9	28.5	26.7	24.6	27.2	25.4	23.2	25.9	24.1	21.9
	SC	16.5	15.8	14.9	16.0	15.2	14.4	15.4	14.7	13.8	14.9	14.2	13.3
	gpm	8.5	6.4	5.0	8.2	6.1	4.7	7.8	5.9	4.5	7.4	5.6	4.2
	wpd	13.3	7.5	4.6	12.3	6.8	4.0	11.2	6.3	3.6	10.1	5.6	3.3
80	TC	30.0	28.3	26.4	28.7	27.1	25.1	27.5	25.8	23.8	26.3	24.5	22.5
	SC	17.6	16.9	16.1	17.0	16.4	15.5	16.5	15.8	15.0	16.0	15.3	14.5
	gpm	8.6	6.5	5.1	8.3	6.3	4.8	7.9	6.0	4.5	7.5	5.6	4.3
	wpd	13.6	7.7	4.7	12.6	7.2	4.2	11.4	6.5	3.8	10.3	5.8	3.4
82	TC	29.8	28.3	26.4	28.6	27.1	25.2	27.4	25.8	24.0	26.2	24.6	22.8
	SC	18.7	18.0	17.2	18.2	17.5	16.7	17.6	17.0	16.3	17.1	16.5	15.8
	gpm	8.6	6.5	5.1	8.2	6.3	4.9	7.9	6.0	4.6	7.5	5.6	4.4
	wpd	13.6	7.7	4.7	12.3	7.2	4.3	11.4	6.5	3.9	10.3	5.8	3.5
84	TC	30.0	28.5	26.8	28.8	27.3	25.7	27.6	26.2	24.5	26.4	25.0	23.4
	SC	19.8	19.2	18.5	19.3	18.7	18.0	18.8	18.2	17.5	18.3	17.7	17.0
	gpm	8.6	6.6	5.2	8.3	6.3	4.9	8.0	6.0	4.7	7.6	5.8	4.5
	wpd	13.6	7.9	4.9	12.6	7.2	4.4	11.7	6.6	4.0	10.5	6.1	3.6
86	TC	30.1	28.8	27.2	29.0	27.6	26.1	27.8	26.5	25.0	26.7	25.4	23.9
	SC	20.9	20.3	19.7	20.4	19.8	19.2	19.9	19.4	18.8	19.4	18.9	18.3
	gpm	8.7	6.7	5.3	8.4	6.4	5.0	8.0	6.1	4.8	7.7	5.9	4.6
	wpd	13.8	8.1	5.0	12.8	7.3	4.6	11.7	6.8	4.2	10.8	6.3	3.9
88	TC	30.3	29.1	27.7	29.2	28.0	26.6	28.1	26.9	25.6	27.0	25.8	24.6
	SC	22.0	21.5	20.9	21.5	21.1	20.5	21.1	20.6	20.0	20.6	20.1	19.6
	gpm	8.7	6.7	5.3	8.4	6.4	5.1	8.1	6.2	4.9	7.8	6.0	4.7
	wpd	13.8	8.3	5.2	12.8	7.5	4.7	11.9	7.0	4.4	11.0	6.5	4.0
90	TC	30.5	29.5	28.2	29.5	28.4	27.2	28.4	27.3	26.2	27.3	26.3	25.2
	SC	23.2	22.7	22.2	22.7	22.3	21.7	22.2	21.8	21.3	21.8	21.4	20.9
	gpm	8.8	6.8	5.4	8.5	6.6	5.2	8.2	6.3	5.0	7.8	6.0	4.9
	wpd	14.0	8.5	5.3	13.1	7.9	4.9	12.1	7.2	4.6	11.2	6.6	4.3

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	36.1	34.8	33.0	34.7	33.4	31.5	33.2	31.8	29.9	31.8	30.3	28.2
	SC	19.1	18.5	17.6	18.4	17.7	16.8	17.7	17.0	16.1	17.0	16.3	15.3
	gpm	9.2	7.0	5.6	8.8	6.7	5.3	8.4	6.4	5.1	8.0	6.1	4.8
	wpd	13.2	7.8	5.0	12.2	7.2	4.4	11.1	6.5	4.1	10.2	5.9	3.6
76	TC	36.1	34.8	33.1	34.6	33.4	31.5	33.2	31.9	30.0	31.8	30.3	28.4
	SC	20.4	19.8	18.9	19.7	19.0	18.1	19.0	18.3	17.4	18.3	17.6	16.7
	gpm	9.2	7.0	5.6	8.8	6.7	5.3	8.4	6.4	5.1	8.0	6.1	4.8
	wpd	13.2	7.8	5.0	12.2	7.2	4.4	11.1	6.5	4.1	10.2	5.9	3.6
78	TC	36.0	34.8	33.2	34.6	33.4	31.7	33.2	31.9	30.1	31.8	30.4	28.6
	SC	21.7	21.1	20.2	21.0	20.4	19.5	20.3	19.7	18.8	19.6	18.9	18.1
	gpm	9.2	7.0	5.6	8.8	6.7	5.4	8.4	6.5	5.1	8.0	6.2	4.8
	wpd	13.2	7.8	5.0	12.2	7.2	4.6	11.1	6.7	4.1	10.2	6.1	3.7
80	TC	36.3	35.2	33.6	34.9	33.7	32.1	33.5	32.3	30.6	32.1	30.8	29.1
	SC	23.0	22.4	21.6	22.3	21.7	20.9	21.6	21.0	20.2	20.9	20.3	19.5
	gpm	9.2	7.1	5.7	8.9	6.8	5.4	8.5	6.5	5.1	8.2	6.2	4.9
	wpd	13.2	8.0	5.1	12.4	7.3	4.7	11.3	6.7	4.2	10.6	6.1	3.8
82	TC	36.1	35.0	33.5	34.7	33.6	32.1	33.3	32.2	30.7	31.9	30.8	29.3
	SC	24.3	23.8	23.0	23.6	23.1	22.3	22.9	22.4	21.7	22.3	21.7	21.0
	gpm	9.1	7.1	5.7	8.8	6.8	5.4	8.4	6.5	5.2	8.0	6.2	4.9
	wpd	13.0	8.0	5.1	12.2	7.3	4.7	11.1	6.7	4.3	10.2	6.1	3.8
84	TC	36.1	35.2	33.8	34.8	33.8	32.4	33.4	32.4	31.0	32.1	31.0	29.7
	SC	25.6	25.1	24.5	25.0	24.5	23.8	24.3	23.8	23.1	23.6	23.1	22.5
	gpm	9.2	7.1	5.7	8.8	6.9	5.4	8.5	6.6	5.2	8.1	6.3	5.0
	wpd	13.2	8.0	5.1	12.2	7.5	4.7	11.3	6.8	4.3	10.4	6.2	3.9
86	TC	36.2	35.3	34.1	34.9	34.0	32.8	33.6	32.7	31.4	32.3	31.4	30.1
	SC	27.0	26.5	25.9	26.3	25.9	25.3	25.7	25.2	24.6	25.0	24.6	24.0
	gpm	9.2	7.2	5.8	8.9	6.9	5.5	8.5	6.7	5.3	8.2	6.4	5.1
	wpd	13.2	8.2	5.2	12.4	7.5	4.8	11.3	7.0	4.4	10.6	6.4	4.1
88	TC	36.4	35.5	34.4	35.1	34.3	33.2	33.8	33.0	31.9	32.5	31.7	30.6
	SC	28.4	27.9	27.4	27.7	27.3	26.8	27.1	26.7	26.2	26.4	26.0	25.6
	gpm	9.2	7.2	5.8	8.9	7.0	5.6	8.5	6.7	5.4	8.2	6.4	5.1
	wpd	13.5	8.2	5.4	12.4	7.7	5.0	11.6	7.0	4.6	10.7	6.5	4.2
90	TC	36.5	35.8	34.8	35.3	34.5	33.6	34.0	33.3	32.4	32.7	32.1	31.2
	SC	29.7	29.4	28.9	29.1	28.8	28.3	28.5	28.1	27.7	27.9	27.5	27.1
	gpm	9.2	7.3	5.9	8.9	7.0	5.7	8.6	6.7	5.4	8.3	6.5	5.3
	wpd	13.5	8.3	5.5	12.6	7.7	5.1	11.8	7.2	4.7	10.9	6.7	4.4

2-Row Chilled Water Cooling

EDB	EWT	42				43			44				45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	23.3	21.3	18.5	22.2	20.2	17.3	21.2	19.1	16.1	20.1	17.9	14.8		
	SC	10.1	9.4	8.3	9.7	9.0	7.9	9.3	8.6	7.5	8.9	8.1	7.1		
	gpm	6.7	4.9	3.6	6.4	4.6	3.3	6.1	4.4	3.1	5.8	4.1	2.9		
	wpd	13.8	7.2	3.9	12.5	6.6	3.4	11.4	5.9	2.9	10.2	5.1	2.5		
76	TC	23.4	21.4	18.6	22.4	20.4	17.4	21.3	19.2	16.2	20.2	18.1	14.9		
	SC	11.1	10.4	9.3	10.7	10.0	8.9	10.3	9.6	8.5	9.9	9.2	8.0		
	gpm	6.7	4.9	3.6	6.4	4.7	3.3	6.2	4.4	3.1	5.8	4.2	2.9		
	wpd	13.8	7.5	3.9	12.5	6.8	3.4	11.7	5.9	2.9	10.2	5.3	2.5		
78	TC	23.5	21.5	18.6	22.5	20.4	17.4	21.4	19.3	16.2	20.3	18.1	15.0		
	SC	12.1	11.4	10.3	11.7	11.0	9.9	11.4	10.6	9.5	11.0	10.2	9.1		
	gpm	6.7	4.9	3.6	6.5	4.7	3.3	6.2	4.5	3.1	5.9	4.2	2.9		
	wpd	13.8	7.5	3.9	12.8	6.8	3.4	11.7	6.1	2.9	10.5	5.3	2.5		
80	TC	23.5	21.5	18.7	22.4	20.4	17.5	21.4	19.3	16.4	20.3	18.1	15.3		
	SC	13.1	12.4	11.3	12.7	12.0	10.9	12.3	11.6	10.5	11.9	11.1	10.1		
	gpm	6.8	4.9	3.6	6.4	4.7	3.4	6.2	4.5	3.2	5.9	4.2	2.9		
	wpd	14.1	7.5	3.9	12.5	6.8	3.5	11.7	6.1	3.1	10.5	5.3	2.6		
82	TC	23.5	21.4	18.8	22.4	20.4	17.8	21.3	19.3	16.8	20.2	18.2	15.8		
	SC	14.1	13.3	12.4	13.7	12.9	12.0	13.3	12.6	11.6	12.9	12.2	11.3		
	gpm	6.8	4.9	3.6	6.4	4.7	3.4	6.1	4.5	3.2	5.8	4.2	3.0		
	wpd	14.1	7.5	4.0	12.5	6.8	3.5	11.4	6.1	3.2	10.2	5.3	2.8		
84	TC	23.4	21.5	19.2	22.3	20.5	18.2	21.3	19.6	17.3	20.3	18.5	16.4		
	SC	15.1	14.4	13.4	14.7	14.0	13.1	14.3	13.6	12.8	13.9	13.3	12.4		
	gpm	6.7	4.9	3.7	6.4	4.7	3.5	6.1	4.5	3.3	5.9	4.3	3.2		
	wpd	13.8	7.5	4.2	12.5	6.8	3.7	11.4	6.1	3.4	10.5	5.5	3.1		
86	TC	23.4	21.7	19.6	22.4	20.8	18.8	21.4	19.9	17.9	20.6	19.0	17.0		
	SC	16.1	15.4	14.6	15.7	15.1	14.2	15.3	14.7	13.9	15.0	14.4	13.6		
	gpm	6.8	5.0	3.8	6.5	4.8	3.6	6.2	4.6	3.4	6.0	4.4	3.2		
	wpd	14.1	7.7	4.4	12.8	7.0	4.0	11.7	6.3	3.5	10.8	5.9	3.2		
88	TC	23.6	22.0	20.2	22.7	21.2	19.4	21.8	20.3	18.5	20.9	19.5	17.7		
	SC	17.1	16.5	15.7	16.8	16.2	15.4	16.4	15.8	15.0	16.1	15.5	14.8		
	gpm	6.8	5.1	3.9	6.6	4.9	3.7	6.3	4.7	3.6	6.0	4.5	3.4		
	wpd	14.1	7.9	4.6	13.2	7.2	4.2	12.2	6.8	3.9	11.1	6.1	3.5		
90	TC	23.9	22.5	20.8	23.1	21.7	20.0	22.2	20.9	19.2	21.4	20.0	18.5		
	SC	18.2	17.6	16.9	17.9	17.3	16.5	17.6	16.9	16.3	17.2	16.6	15.9		
	gpm	6.9	5.2	4.0	6.6	5.0	3.9	6.4	4.8	3.7	6.2	4.6	3.6		
	wpd	14.4	8.2	4.9	13.5	7.7	4.6	12.5	7.0	4.2	11.7	6.6	3.9		

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	27.8	25.5	22.5	26.7	24.2	21.2	25.5	22.9	19.8	24.3	21.7	18.4
	SC	12.0	11.1	10.0	11.6	10.6	9.5	11.1	10.1	8.9	10.6	9.6	8.4
	gpm	8.0	5.9	4.4	7.7	5.6	4.1	7.3	5.3	3.8	7.0	5.0	3.5
	wpd	10.3	5.6	3.1	9.5	5.0	2.7	8.6	4.5	2.4	7.9	4.0	2.0
76	TC	27.9	25.5	22.5	26.7	24.3	21.2	25.6	23.0	19.9	24.4	21.7	18.4
	SC	13.1	12.1	11.0	12.6	11.6	10.5	12.1	11.2	10.0	11.7	10.7	9.5
	gpm	8.1	5.9	4.3	7.7	5.6	4.1	7.4	5.3	3.8	7.0	5.0	3.5
	wpd	10.5	5.6	3.0	9.5	5.0	2.7	8.8	4.5	2.4	7.9	4.0	2.0
78	TC	27.9	25.6	22.6	26.8	24.3	21.3	25.6	23.0	19.9	24.4	21.7	18.6
	SC	14.1	13.2	12.0	13.6	12.7	11.5	13.2	12.2	11.0	12.7	11.7	10.5
	gpm	8.1	5.9	4.4	7.7	5.6	4.1	7.4	5.3	3.8	7.1	5.0	3.5
	wpd	10.5	5.6	3.1	9.5	5.0	2.7	8.8	4.5	2.4	8.1	4.0	2.0
80	TC	27.9	25.5	22.6	26.8	24.3	21.4	25.6	23.0	20.2	24.3	21.8	19.0
	SC	15.1	14.2	13.0	14.6	13.7	12.6	14.2	13.2	12.1	13.7	12.7	11.7
	gpm	8.1	5.9	4.4	7.7	5.6	4.1	7.4	5.4	3.9	7.0	5.1	3.6
	wpd	10.5	5.6	3.1	9.5	5.0	2.8	8.8	4.6	2.5	7.9	4.1	2.1
82	TC	27.9	25.5	22.9	26.7	24.3	21.7	25.5	23.2	20.6	24.4	22.0	19.4
	SC	16.1	15.2	14.2	15.6	14.7	13.7	15.2	14.3	13.3	14.7	13.8	12.8
	gpm	8.1	5.9	4.4	7.7	5.7	4.1	7.4	5.4	3.9	7.0	5.1	3.8
	wpd	10.5	5.6	3.1	9.5	5.1	2.8	8.8	4.6	2.5	7.9	4.1	2.3
84	TC	27.9	25.7	23.3	26.7	24.6	22.2	25.6	23.5	21.0	24.5	22.3	20.0
	SC	17.1	16.3	15.3	16.7	15.8	14.9	16.2	15.4	14.4	15.8	14.9	14.0
	gpm	8.1	6.0	4.4	7.7	5.7	4.3	7.4	5.4	4.1	7.1	5.1	3.8
	wpd	10.5	5.7	3.2	9.5	5.1	3.0	8.8	4.7	2.7	8.1	4.2	2.4
86	TC	27.9	25.9	23.7	26.8	24.9	22.6	25.8	23.8	21.6	24.7	22.7	20.6
	SC	18.2	17.4	16.5	17.7	16.9	16.0	17.3	16.5	15.6	16.9	16.1	15.3
	gpm	8.1	6.0	4.5	7.7	5.7	4.4	7.5	5.5	4.1	7.2	5.3	4.0
	wpd	10.5	5.7	3.3	9.5	5.3	3.1	9.0	4.9	2.8	8.3	4.5	2.6
88	TC	28.1	26.3	24.2	27.1	25.2	23.2	26.0	24.2	22.2	25.0	23.1	21.2
	SC	19.2	18.5	17.6	18.8	18.1	17.2	18.4	17.7	16.9	18.0	17.3	16.5
	gpm	8.1	6.0	4.7	7.8	5.8	4.4	7.5	5.6	4.3	7.2	5.4	4.1
	wpd	10.7	5.9	3.5	9.9	5.4	3.2	9.1	5.0	3.0	8.4	4.6	2.7
90	TC	28.4	26.7	24.7	27.4	25.6	23.8	26.4	24.6	22.8	25.3	23.7	21.9
	SC	20.4	19.6	18.8	19.9	19.2	18.5	19.5	18.8	18.1	19.1	18.4	17.7
	gpm	8.2	6.2	4.7	7.9	5.9	4.6	7.6	5.7	4.4	7.3	5.4	4.2
	wpd	10.9	6.2	3.6	10.1	5.6	3.4	9.3	5.1	3.1	8.6	4.7	2.9

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	33.4	31.9	29.7	32.1	30.6	28.4	30.9	29.2	26.9	29.6	27.9	25.4												
	SC	14.3	13.7	12.8	13.8	13.1	12.3	13.3	12.6	11.7	12.7	12.0	11.1												
	gpm	9.6	7.4	5.7	9.3	7.1	5.5	8.9	6.7	5.2	8.5	6.4	4.9												
	wpd	16.9	9.9	6.0	15.6	9.1	5.5	14.3	8.3	4.9	13.3	7.5	4.3												
76	TC	33.4	31.9	29.7	32.2	30.6	28.3	30.9	29.2	26.9	29.6	27.9	25.5												
	SC	15.4	14.8	13.9	14.9	14.2	13.3	14.3	13.7	12.8	13.8	13.1	12.2												
	gpm	9.6	7.4	5.7	9.3	7.1	5.4	8.9	6.7	5.2	8.5	6.4	4.9												
	wpd	16.9	9.9	6.0	15.6	9.1	5.3	14.3	8.3	4.9	13.1	7.5	4.4												
78	TC	33.4	31.9	29.8	32.1	30.6	28.4	30.9	29.2	27.1	29.5	27.9	25.7												
	SC	16.5	15.8	14.9	15.9	15.3	14.4	15.4	14.7	13.8	14.9	14.2	13.3												
	gpm	9.6	7.4	5.7	9.3	7.1	5.4	8.9	6.7	5.2	8.5	6.4	4.9												
	wpd	16.9	9.9	6.0	15.6	9.1	5.3	14.3	8.3	4.9	13.1	7.5	4.4												
80	TC	33.4	31.9	29.9	32.1	30.6	28.6	30.8	29.3	27.2	29.6	28.0	25.9												
	SC	17.5	16.9	16.0	17.0	16.3	15.5	16.5	15.8	14.9	15.9	15.2	14.4												
	gpm	9.6	7.4	5.7	9.3	7.1	5.5	8.9	6.7	5.2	8.5	6.4	4.9												
	wpd	16.9	9.9	6.0	15.6	9.1	5.5	14.3	8.3	4.9	13.1	7.5	4.4												
82	TC	33.4	31.9	29.9	32.1	30.6	28.6	30.8	29.3	27.2	29.6	28.0	25.9												
	SC	18.6	18.0	17.1	18.0	17.4	16.6	17.5	16.9	16.1	17.0	16.4	15.5												
	gpm	9.6	7.4	5.7	9.3	7.1	5.5	8.9	6.7	5.3	8.5	6.4	4.9												
	wpd	16.9	9.9	6.0	15.6	9.1	5.5	14.3	8.3	5.0	13.3	7.5	4.4												
84	TC	33.4	32.0	30.0	32.1	30.7	28.8	30.9	29.4	27.5	29.6	28.2	26.2												
	SC	19.6	19.1	18.3	19.1	18.5	17.7	18.6	18.0	17.2	18.1	17.5	16.7												
	gpm	9.6	7.4	5.8	9.3	7.1	5.5	8.9	6.8	5.3	8.5	6.5	5.0												
	wpd	16.9	9.9	6.1	15.6	9.1	5.5	14.6	8.5	5.0	13.3	7.7	4.6												
86	TC	33.4	32.1	30.3	32.2	30.9	29.0	31.0	29.6	27.8	29.8	28.4	26.6												
	SC	20.7	20.2	19.4	20.2	19.7	18.9	19.7	19.1	18.4	19.2	18.6	17.9												
	gpm	9.6	7.4	5.8	9.3	7.1	5.6	8.9	6.8	5.3	8.5	6.6	5.1												
	wpd	16.9	9.9	6.1	15.9	9.3	5.6	14.6	8.5	5.2	13.3	7.9	4.7												
88	TC	33.5	32.3	30.6	32.3	31.1	29.4	31.2	29.9	28.2	29.9	28.6	27.0												
	SC	21.8	21.3	20.6	21.3	20.8	20.1	20.8	20.3	19.6	20.3	19.8	19.2												
	gpm	9.6	7.4	5.9	9.3	7.1	5.6	9.0	6.9	5.4	8.6	6.6	5.2												
	wpd	16.9	10.1	6.3	15.9	9.3	5.8	14.8	8.7	5.3	13.6	7.9	4.9												
90	TC	33.6	32.5	30.9	32.5	31.3	29.8	31.3	30.1	28.7	30.1	29.0	27.5												
	SC	22.9	22.4	21.8	22.4	21.9	21.3	21.9	21.5	20.9	21.4	21.0	20.4												
	gpm	9.6	7.5	6.0	9.3	7.2	5.7	9.0	7.0	5.5	8.6	6.7	5.3												
	wpd	16.9	10.3	6.5	15.9	9.5	6.0	14.8	8.9	5.5	13.6	8.1	5.2												

5-Row Chilled Water Cooling

EDB	EWT		42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	40.2	39.0	37.5	38.8	37.6	36.0	37.4	36.1	34.4	35.9	34.6	32.8	
	SC	19.0	18.5	17.7	18.3	17.7	17.0	17.6	17.0	16.2	16.9	16.3	15.5	
	gpm	10.2	7.9	6.4	9.8	7.6	6.1	9.5	7.3	5.8	9.1	7.0	5.5	
	wpd	16.5	9.8	6.4	15.3	9.2	5.8	14.1	8.5	5.4	13.0	7.8	4.8	
76	TC	40.2	39.0	37.5	38.8	37.6	36.0	37.4	36.1	34.4	35.9	34.6	32.8	
	SC	20.4	19.8	19.0	19.7	19.1	18.3	19.0	18.4	17.5	18.3	17.6	16.8	
	gpm	10.2	7.9	6.4	9.8	7.6	6.1	9.5	7.3	5.8	9.1	7.0	5.5	
	wpd	16.5	9.8	6.4	15.3	9.0	5.8	14.1	8.5	5.4	13.0	7.8	4.8	
78	TC	40.2	39.0	37.6	38.8	37.6	36.1	37.4	36.1	34.5	35.9	34.6	33.0	
	SC	21.7	21.1	20.3	21.0	20.4	19.6	20.3	19.6	18.9	19.6	18.9	18.1	
	gpm	10.2	7.9	6.4	9.8	7.6	6.1	9.5	7.3	5.8	9.1	7.0	5.5	
	wpd	16.5	9.8	6.4	15.3	9.2	5.8	14.1	8.3	5.4	13.0	7.8	4.8	
80	TC	40.2	39.0	37.6	38.8	37.6	36.1	37.4	36.1	34.5	35.9	34.6	33.0	
	SC	23.0	22.4	21.7	22.3	21.7	20.9	21.6	21.0	20.2	20.9	20.3	19.5	
	gpm	10.1	7.9	6.4	9.8	7.6	6.1	9.5	7.3	5.8	9.1	7.0	5.5	
	wpd	16.2	10.0	6.4	15.3	9.2	5.8	14.1	8.5	5.4	13.0	7.8	4.8	
82	TC	40.2	39.1	37.7	38.8	37.6	36.2	37.4	36.2	34.7	35.9	34.7	33.1	
	SC	24.3	23.7	23.0	23.6	23.0	22.3	22.9	22.3	21.6	22.2	21.6	20.9	
	gpm	10.1	7.9	6.4	9.8	7.6	6.1	9.5	7.3	5.8	9.1	7.0	5.6	
	wpd	16.2	10.0	6.4	15.1	9.2	5.9	14.1	8.5	5.4	13.0	7.8	5.0	
84	TC	40.2	39.1	37.8	38.8	37.7	36.3	37.4	36.3	34.8	36.0	34.8	33.3	
	SC	25.6	25.0	24.4	24.9	24.3	23.7	24.2	23.6	23.0	23.5	23.0	22.3	
	gpm	10.1	7.9	6.4	9.8	7.6	6.1	9.5	7.3	5.9	9.1	7.0	5.6	
	wpd	16.2	10.0	6.4	15.3	9.2	5.9	14.1	8.5	5.5	13.0	7.8	5.0	
86	TC	40.2	39.2	37.9	38.8	37.8	36.5	37.4	36.4	35.0	36.0	35.0	33.6	
	SC	26.9	26.4	25.7	26.2	25.7	25.1	25.5	25.0	24.4	24.8	24.3	23.7	
	gpm	10.1	7.9	6.4	9.8	7.6	6.1	9.5	7.4	5.9	9.1	7.1	5.7	
	wpd	16.2	10.0	6.4	15.3	9.2	5.9	14.1	8.7	5.5	13.0	8.0	5.1	
88	TC	40.2	39.3	38.1	38.9	37.9	36.7	37.5	36.5	35.3	36.1	35.1	33.9	
	SC	28.2	27.7	27.1	27.5	27.1	26.5	26.9	26.4	25.8	26.2	25.7	25.2	
	gpm	10.2	7.9	6.4	9.8	7.7	6.2	9.5	7.4	6.0	9.2	7.1	5.8	
	wpd	16.5	10.0	6.5	15.3	9.4	6.1	14.4	8.7	5.6	13.2	8.0	5.2	
90	TC	40.3	39.4	38.3	39.0	38.1	37.0	37.6	36.7	35.7	36.3	35.4	34.3	
	SC	29.6	29.1	28.6	28.9	28.4	27.9	28.2	27.8	27.3	27.6	27.1	26.6	
	gpm	10.2	7.9	6.5	9.9	7.7	6.3	9.5	7.4	6.1	9.2	7.2	5.8	
	wpd	16.5	10.0	6.7	15.5	9.4	6.2	14.4	8.7	5.8	13.5	8.2	5.4	

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.1	24.1	21.7	25.1	23.0	20.5	24.0	21.9	19.3	22.9	20.8	18.1
	SC	9.8	9.0	8.2	9.4	8.7	7.8	9.0	8.3	7.4	8.6	7.9	6.9
	gpm	7.5	5.6	4.2	7.3	5.3	3.9	7.0	5.0	3.7	6.6	4.8	3.5
	wpd	17.1	9.4	5.3	16.1	8.7	4.7	14.7	7.7	4.2	13.2	7.0	3.7
76	TC	26.1	24.1	21.8	25.1	23.1	20.6	24.0	22.0	19.5	23.0	20.9	18.3
	SC	10.8	10.1	9.2	10.4	9.7	8.8	10.0	9.3	8.4	9.6	8.9	8.0
	gpm	7.5	5.6	4.2	7.2	5.3	3.9	7.0	5.1	3.8	6.6	4.8	3.5
	wpd	17.1	9.4	5.3	15.7	8.7	4.7	14.7	7.9	4.4	13.5	7.0	3.7
78	TC	26.2	24.3	21.9	25.2	23.2	20.8	24.2	22.1	19.6	23.1	21.0	18.4
	SC	11.8	11.1	10.2	11.4	10.7	9.8	11.0	10.3	9.4	10.7	9.9	9.0
	gpm	7.6	5.6	4.3	7.3	5.3	4.0	7.0	5.1	3.8	6.6	4.9	3.6
	wpd	17.5	9.7	5.5	16.1	8.7	4.9	14.7	7.9	4.4	13.5	7.2	3.9
80	TC	26.3	24.3	22.0	25.3	23.3	20.8	24.2	22.2	19.6	23.2	21.1	18.4
	SC	12.8	12.1	11.2	12.4	11.7	10.8	12.1	11.3	10.4	11.7	10.9	10.0
	gpm	7.6	5.6	4.3	7.3	5.4	4.0	7.0	5.1	3.8	6.7	4.9	3.6
	wpd	17.5	9.7	5.5	16.1	8.9	4.9	14.7	7.9	4.4	13.8	7.2	3.9
82	TC	26.4	24.4	22.0	25.4	23.3	20.8	24.3	22.2	19.6	23.2	21.1	18.4
	SC	13.9	13.1	12.2	13.5	12.7	11.8	13.1	12.3	11.4	12.7	11.9	11.0
	gpm	7.7	5.6	4.3	7.3	5.3	4.0	7.0	5.1	3.8	6.6	4.9	3.6
	wpd	17.8	9.7	5.5	16.4	8.7	4.9	14.7	7.9	4.4	13.5	7.2	3.9
84	TC	26.5	24.4	22.0	25.4	23.3	20.9	24.3	22.2	19.7	23.2	21.0	18.6
	SC	14.8	14.1	13.2	14.4	13.7	12.8	14.0	13.3	12.4	13.6	12.9	12.0
	gpm	7.7	5.6	4.3	7.3	5.4	4.0	7.0	5.1	3.8	6.6	4.9	3.6
	wpd	17.8	9.7	5.5	16.4	8.9	4.9	15.1	7.9	4.4	13.5	7.2	3.9
86	TC	26.4	24.3	22.0	25.3	23.2	21.0	24.2	22.2	20.0	23.1	21.1	19.0
	SC	15.8	15.1	14.2	15.4	14.7	13.8	15.0	14.3	13.5	14.6	13.9	13.1
	gpm	7.7	5.6	4.3	7.3	5.3	4.0	7.0	5.1	3.9	6.6	4.9	3.6
	wpd	17.8	9.7	5.5	16.4	8.7	4.9	14.7	7.9	4.6	13.5	7.2	4.0
88	TC	26.4	24.4	22.3	25.2	23.3	21.3	24.2	22.3	20.4	23.1	21.3	19.5
	SC	16.8	16.0	15.3	16.4	15.7	14.9	16.0	15.3	14.6	15.6	15.0	14.2
	gpm	7.6	5.6	4.3	7.3	5.4	4.1	7.0	5.2	3.9	6.6	4.9	3.7
	wpd	17.5	9.7	5.7	16.1	8.9	5.1	14.7	8.2	4.7	13.5	7.5	4.2
90	TC	26.3	24.5	22.7	25.3	23.5	21.8	24.3	22.6	20.9	23.3	21.7	20.0
	SC	17.8	17.1	16.4	17.4	16.7	16.0	17.0	16.4	15.7	16.7	16.0	15.4
	gpm	7.6	5.6	4.4	7.3	5.4	4.2	7.0	5.2	4.0	6.7	5.0	3.9
	wpd	17.5	9.7	5.9	16.4	8.9	5.3	15.1	8.2	4.9	13.8	7.7	4.6

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12					
74	TC	31.1	29.1	26.2	30.0	27.9	24.9	28.8	26.6	23.6	27.6	25.3	22.3												
	SC	11.9	11.0	9.9	11.4	10.6	9.5	10.9	10.1	9.0	10.4	9.6	8.5												
	gpm	9.0	6.7	5.1	8.7	6.4	4.8	8.3	6.2	4.5	7.9	5.9	4.3												
	wpd	13.0	7.2	4.1	12.1	6.6	3.7	11.1	6.2	3.3	10.1	5.6	3.0												
76	TC	31.2	29.1	26.3	30.0	27.9	25.0	28.8	26.7	23.7	27.6	25.4	22.4												
	SC	12.9	12.1	11.0	12.4	11.6	10.5	12.0	11.1	10.0	11.5	10.7	9.5												
	gpm	9.0	6.7	5.1	8.7	6.4	4.8	8.4	6.2	4.5	8.0	5.9	4.3												
	wpd	13.0	7.2	4.1	12.1	6.6	3.7	11.3	6.2	3.3	10.3	5.6	3.0												
78	TC	31.2	29.2	26.4	30.1	28.0	25.1	28.9	26.7	23.7	27.7	25.5	22.4												
	SC	13.9	13.1	12.1	13.5	12.6	11.6	13.0	12.2	11.1	12.5	11.7	10.6												
	gpm	9.0	6.7	5.1	8.7	6.4	4.8	8.3	6.2	4.6	8.0	5.9	4.3												
	wpd	13.2	7.2	4.1	12.1	6.6	3.7	11.1	6.2	3.4	10.3	5.6	3.0												
80	TC	31.3	29.2	26.4	30.1	28.0	25.1	28.9	26.7	23.8	27.7	25.5	22.4												
	SC	15.0	14.2	13.1	14.5	13.7	12.6	14.0	13.2	12.1	13.6	12.7	11.6												
	gpm	9.0	6.7	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.3												
	wpd	13.2	7.2	4.1	12.1	6.8	3.7	11.3	6.2	3.4	10.3	5.6	3.0												
82	TC	31.3	29.2	26.4	30.1	28.0	25.1	28.9	26.7	23.8	27.7	25.4	22.5												
	SC	16.0	15.2	14.1	15.5	14.7	13.6	15.1	14.2	13.1	14.6	13.7	12.7												
	gpm	9.0	6.8	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.4												
	wpd	13.2	7.4	4.1	12.1	6.8	3.7	11.3	6.2	3.4	10.3	5.6	3.1												
84	TC	31.3	29.2	26.4	30.1	28.0	25.2	28.9	26.7	24.0	27.7	25.5	22.7												
	SC	17.0	16.2	15.1	16.5	15.7	14.7	16.1	15.2	14.2	15.6	14.8	13.8												
	gpm	9.0	6.7	5.1	8.7	6.5	4.8	8.4	6.2	4.6	8.0	5.9	4.4												
	wpd	13.2	7.2	4.2	12.1	6.8	3.7	11.3	6.2	3.4	10.3	5.6	3.1												
86	TC	31.3	29.2	26.6	30.1	28.0	25.5	28.9	26.8	24.3	27.7	25.6	23.1												
	SC	18.0	17.2	16.2	17.5	16.7	15.8	17.1	16.3	15.3	16.6	15.8	14.9												
	gpm	9.0	6.8	5.1	8.7	6.5	4.9	8.4	6.2	4.7	8.0	5.9	4.4												
	wpd	13.2	7.4	4.2	12.1	6.8	3.9	11.3	6.2	3.5	10.3	5.6	3.2												
88	TC	31.2	29.3	26.9	30.0	28.2	25.8	28.9	27.0	24.6	27.7	25.9	23.5												
	SC	19.0	18.2	17.3	18.5	17.8	16.9	18.1	17.4	16.5	17.6	16.9	16.0												
	gpm	9.0	6.7	5.2	8.7	6.5	5.0	8.3	6.3	4.7	8.0	6.0	4.5												
	wpd	13.0	7.2	4.4	12.1	6.8	4.0	11.1	6.3	3.6	10.3	5.7	3.3												
90	TC	31.2	29.5	27.2	30.1	28.4	26.2	29.0	27.3	25.1	27.9	26.2	24.0												
	SC	20.0	19.3	18.4	19.6	18.9	18.0	19.1	18.5	17.6	18.7	18.0	17.2												
	gpm	9.0	6.8	5.3	8.7	6.6	5.1	8.4	6.3	4.8	8.1	6.0	4.6												
	wpd	13.0	7.4	4.5	12.1	6.9	4.1	11.3	6.5	3.7	10.5	5.9	3.4												

4-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	37.2	35.7	33.8	35.9	34.4	32.4	34.6	33.1	31.1	33.3	31.7	29.6				
	SC	14.3	13.6	12.9	13.7	13.1	12.3	13.2	12.6	11.8	12.6	12.0	11.2				
	gpm	10.7	8.2	6.5	10.4	7.9	6.2	10.0	7.6	6.0	9.6	7.3	5.7				
	wpd	21.0	12.3	7.7	19.5	11.4	7.0	18.1	10.5	6.5	16.7	9.7	6.0				
76	TC	37.2	35.7	33.9	35.9	34.4	32.5	34.6	33.1	31.1	33.3	31.7	29.7				
	SC	15.3	14.7	14.0	14.8	14.2	13.4	14.3	13.6	12.8	13.7	13.1	12.3				
	gpm	10.7	8.2	6.5	10.4	7.9	6.3	10.0	7.6	6.0	9.6	7.3	5.7				
	wpd	21.0	12.3	7.7	19.5	11.4	7.2	18.1	10.5	6.5	16.7	9.7	6.0				
78	TC	37.2	35.7	33.9	36.0	34.4	32.5	34.7	33.1	31.1	33.4	31.7	29.6				
	SC	16.4	15.8	15.0	15.9	15.3	14.5	15.3	14.7	13.9	14.8	14.2	13.3				
	gpm	10.7	8.2	6.5	10.4	7.9	6.3	10.0	7.6	6.0	9.6	7.3	5.7				
	wpd	21.0	12.3	7.7	19.5	11.4	7.2	18.1	10.5	6.5	16.7	9.7	6.0				
80	TC	37.2	35.7	33.9	36.0	34.4	32.5	34.7	33.1	31.1	33.4	31.7	29.6				
	SC	17.5	16.9	16.1	16.9	16.3	15.5	16.4	15.8	15.0	15.9	15.2	14.4				
	gpm	10.7	8.2	6.5	10.4	7.9	6.3	10.0	7.6	6.0	9.6	7.3	5.7				
	wpd	21.0	12.3	7.7	19.5	11.4	7.2	18.1	10.5	6.5	16.7	9.7	6.0				
82	TC	37.2	35.7	33.9	35.9	34.4	32.5	34.7	33.1	31.1	33.3	31.7	29.7				
	SC	18.5	17.9	17.2	18.0	17.4	16.6	17.5	16.8	16.1	16.9	16.3	15.5				
	gpm	10.7	8.2	6.5	10.4	7.9	6.3	10.0	7.6	6.0	9.6	7.3	5.7				
	wpd	21.0	12.3	7.7	19.5	11.4	7.2	18.1	10.5	6.5	16.7	9.7	6.0				
84	TC	37.2	35.7	33.8	35.9	34.4	32.5	34.6	33.1	31.2	33.3	31.7	29.8				
	SC	19.6	19.0	18.2	19.1	18.4	17.7	18.5	17.9	17.2	18.0	17.4	16.6				
	gpm	10.7	8.2	6.5	10.4	7.9	6.3	10.0	7.6	6.0	9.6	7.3	5.7				
	wpd	21.0	12.3	7.7	19.5	11.4	7.2	18.1	10.5	6.5	16.7	9.7	6.0				
86	TC	37.1	35.7	33.9	35.9	34.4	32.6	34.6	33.1	31.3	33.3	31.8	30.0				
	SC	20.6	20.0	19.3	20.1	19.5	18.8	19.6	19.0	18.3	19.0	18.5	17.8				
	gpm	10.7	8.2	6.5	10.4	7.9	6.3	10.0	7.7	6.0	9.6	7.4	5.8				
	wpd	21.0	12.3	7.7	19.5	11.4	7.2	18.1	10.8	6.6	16.7	9.9	6.1				
88	TC	37.1	35.7	34.1	35.9	34.5	32.8	34.6	33.2	31.5	33.3	31.9	30.2				
	SC	21.7	21.1	20.4	21.2	20.6	19.9	20.6	20.1	19.4	20.1	19.6	18.9				
	gpm	10.7	8.2	6.6	10.4	7.9	6.3	10.0	7.6	6.0	9.6	7.4	5.8				
	wpd	21.0	12.3	7.9	19.5	11.4	7.2	18.1	10.5	6.6	16.9	9.9	6.1				
90	TC	37.2	35.8	34.3	35.9	34.6	33.0	34.7	33.4	31.8	33.5	32.1	30.5				
	SC	22.8	22.2	21.6	22.2	21.7	21.1	21.7	21.2	20.6	21.2	20.7	20.1				
	gpm	10.7	8.2	6.6	10.4	8.0	6.4	10.0	7.7	6.1	9.6	7.4	5.9				
	wpd	21.0	12.3	7.9	19.5	11.7	7.3	18.4	10.8	6.8	16.9	9.9	6.3				

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	44.5	43.3	42.0	43.1	41.9	40.5	41.7	40.4	39.0	40.2	38.9	37.4
	SC	19.0	18.4	17.8	18.3	17.7	17.1	17.6	17.0	16.3	16.9	16.3	15.6
	gpm	11.3	8.8	7.1	11.0	8.5	6.8	10.6	8.2	6.6	10.2	7.9	6.4
	wpd	20.1	12.2	8.0	19.0	11.3	7.3	17.7	10.6	6.8	16.5	9.8	6.4
76	TC	44.5	43.4	42.1	43.1	41.9	40.6	41.7	40.4	39.0	40.3	39.0	37.5
	SC	20.3	19.8	19.1	19.6	19.0	18.4	18.9	18.3	17.7	18.2	17.6	16.9
	gpm	11.3	8.8	7.1	11.0	8.5	6.9	10.6	8.2	6.6	10.2	7.9	6.4
	wpd	20.1	12.2	8.0	19.0	11.3	7.5	17.7	10.6	6.8	16.5	9.8	6.4
78	TC	44.5	43.4	42.1	43.2	42.0	40.6	41.7	40.5	39.1	40.3	39.0	37.5
	SC	21.6	21.1	20.4	20.9	20.4	19.7	20.3	19.6	19.0	19.6	18.9	18.2
	gpm	11.2	8.8	7.1	11.0	8.5	6.9	10.6	8.2	6.6	10.2	7.9	6.3
	wpd	19.8	12.2	8.0	19.0	11.3	7.5	17.7	10.6	6.8	16.5	9.8	6.2
80	TC	44.5	43.4	42.1	43.2	42.0	40.6	41.7	40.5	39.1	40.3	39.0	37.5
	SC	22.9	22.4	21.8	22.3	21.7	21.0	21.6	21.0	20.3	20.9	20.2	19.6
	gpm	11.3	8.8	7.1	11.0	8.5	6.9	10.6	8.2	6.6	10.2	7.9	6.4
	wpd	20.1	12.2	8.0	19.0	11.3	7.5	17.7	10.6	6.8	16.5	9.8	6.4
82	TC	44.5	43.4	42.1	43.1	41.9	40.6	41.7	40.5	39.1	40.3	39.0	37.6
	SC	24.2	23.7	23.1	23.6	23.0	22.3	22.9	22.3	21.6	22.2	21.5	20.9
	gpm	11.3	8.8	7.1	10.9	8.5	6.9	10.6	8.2	6.6	10.2	7.9	6.4
	wpd	20.1	12.2	8.0	18.8	11.3	7.5	17.7	10.6	6.8	16.5	9.8	6.4
84	TC	44.5	43.4	42.1	43.1	41.9	40.7	41.7	40.5	39.2	40.2	39.0	37.6
	SC	25.5	25.0	24.4	24.8	24.3	23.7	24.1	23.6	23.0	23.4	22.9	22.2
	gpm	11.3	8.8	7.1	10.9	8.5	6.9	10.5	8.2	6.7	10.1	7.9	6.4
	wpd	20.1	12.2	8.0	18.8	11.3	7.5	17.5	10.6	7.0	16.2	9.8	6.4
86	TC	44.5	43.4	42.2	43.1	42.0	40.7	41.7	40.5	39.3	40.2	39.0	37.8
	SC	26.8	26.3	25.7	26.1	25.6	25.0	25.5	24.9	24.3	24.8	24.2	23.6
	gpm	11.3	8.8	7.1	10.9	8.5	6.9	10.5	8.2	6.7	10.1	7.9	6.4
	wpd	20.1	12.2	8.0	18.8	11.3	7.5	17.5	10.7	7.0	16.2	10.0	6.4
88	TC	44.5	43.4	42.3	43.1	42.0	40.8	41.7	40.6	39.4	40.2	39.1	37.9
	SC	28.1	27.6	27.1	27.5	26.9	26.4	26.8	26.2	25.7	26.1	25.6	25.0
	gpm	11.3	8.8	7.1	10.9	8.5	6.9	10.5	8.2	6.7	10.2	7.9	6.4
	wpd	20.1	12.2	8.0	18.8	11.6	7.5	17.5	10.7	7.0	16.5	10.0	6.4
90	TC	44.5	43.5	42.4	43.1	42.1	41.0	41.7	40.7	39.5	40.3	39.2	38.1
	SC	29.5	29.0	28.4	28.8	28.3	27.7	28.1	27.6	27.0	27.4	26.9	26.4
	gpm	11.3	8.9	7.2	10.9	8.5	6.9	10.6	8.2	6.7	10.2	7.9	6.4
	wpd	20.1	12.4	8.2	18.8	11.6	7.5	17.7	10.7	7.0	16.5	10.0	6.5

2-Row Chilled Water Cooling

EDB	EWT			43						44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12		
74	TC	29.2	27.1	25.0	28.1	26.1	23.9	27.1	25.0	22.8	26.0	23.8	21.6		
	SC	9.4	8.7	8.0	9.0	8.3	7.6	8.7	7.9	7.2	8.3	7.5	6.8		
	gpm	8.4	6.3	4.8	8.1	6.0	4.6	7.8	5.8	4.4	7.5	5.5	4.2		
	wpd	21.6	11.9	7.0	20.1	11.1	6.3	18.6	10.2	5.9	17.1	9.2	5.3		
76	TC	29.2	27.1	25.0	28.1	26.0	23.9	27.0	24.9	22.8	25.9	23.8	21.6		
	SC	10.5	9.7	9.0	10.1	9.3	8.6	9.7	9.0	8.2	9.3	8.6	7.8		
	gpm	8.4	6.3	4.8	8.1	6.0	4.6	7.7	5.8	4.4	7.5	5.5	4.2		
	wpd	21.6	11.9	7.0	20.1	11.1	6.3	18.2	10.2	5.9	17.1	9.2	5.3		
78	TC	29.1	27.1	25.1	28.1	26.0	24.0	27.0	24.9	22.9	25.9	23.9	21.7		
	SC	11.5	10.7	10.0	11.1	10.4	9.6	10.7	10.0	9.3	10.3	9.6	8.9		
	gpm	8.4	6.3	4.8	8.1	6.0	4.6	7.8	5.7	4.4	7.4	5.5	4.2		
	wpd	21.6	11.9	7.0	20.1	11.1	6.6	18.6	10.0	5.9	16.8	9.2	5.3		
80	TC	29.2	27.2	25.2	28.2	26.1	24.1	27.1	25.0	23.0	26.0	24.0	21.8		
	SC	12.5	11.8	11.0	12.1	11.4	10.7	11.7	11.0	10.3	11.3	10.6	9.9		
	gpm	8.4	6.3	4.9	8.1	6.0	4.6	7.8	5.8	4.4	7.5	5.6	4.2		
	wpd	21.6	11.9	7.2	20.1	11.1	6.6	18.6	10.2	5.9	17.1	9.4	5.3		
82	TC	29.3	27.3	25.2	28.3	26.2	24.2	27.2	25.1	23.1	26.1	24.0	21.9		
	SC	13.5	12.8	12.1	13.1	12.4	11.7	12.8	12.0	11.3	12.4	11.6	10.9		
	gpm	8.4	6.3	4.9	8.1	6.0	4.6	7.8	5.8	4.4	7.5	5.6	4.3		
	wpd	21.6	12.2	7.2	20.1	11.1	6.6	18.6	10.2	5.9	17.1	9.4	5.5		
84	TC	29.4	27.4	25.3	28.4	26.3	24.2	27.3	25.2	23.1	26.2	24.1	21.9		
	SC	14.5	13.8	13.1	14.2	13.4	12.7	13.8	13.0	12.3	13.4	12.6	11.9		
	gpm	8.5	6.3	4.9	8.2	6.1	4.6	7.9	5.8	4.5	7.6	5.6	4.2		
	wpd	22.0	12.2	7.2	20.5	11.4	6.6	18.9	10.2	6.1	17.5	9.4	5.3		
86	TC	29.5	27.5	25.3	28.5	26.4	24.2	27.4	25.2	23.1	26.2	24.1	21.9		
	SC	15.6	14.8	14.1	15.2	14.4	13.7	14.8	14.0	13.3	14.4	13.6	12.9		
	gpm	8.5	6.3	4.9	8.2	6.1	4.6	7.9	5.8	4.4	7.6	5.6	4.2		
	wpd	22.0	12.2	7.2	20.5	11.4	6.6	18.9	10.2	5.9	17.5	9.4	5.3		
88	TC	29.6	27.4	25.3	28.5	26.3	24.2	27.3	25.2	23.1	26.2	24.0	21.9		
	SC	16.6	15.8	15.0	16.2	15.4	14.6	15.8	15.0	14.3	15.4	14.6	13.9		
	gpm	8.5	6.3	4.9	8.2	6.1	4.6	7.9	5.8	4.4	7.6	5.6	4.3		
	wpd	22.0	12.2	7.2	20.5	11.4	6.6	18.9	10.2	5.9	17.5	9.4	5.5		
90	TC	29.5	27.4	25.3	28.4	26.2	24.3	27.3	25.2	23.2	26.2	24.1	22.2		
	SC	17.5	16.8	16.0	17.1	16.4	15.7	16.7	16.0	15.3	16.3	15.6	15.0		
	gpm	8.5	6.3	4.9	8.2	6.0	4.6	7.9	5.8	4.5	7.6	5.6	4.3		
	wpd	22.0	12.2	7.2	20.5	11.1	6.6	18.9	10.2	6.1	17.5	9.4	5.5		

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	34.7	32.8	30.2	33.5	31.6	28.9	32.3	30.3	27.6	31.1	29.1	26.3
	SC	11.7	10.9	9.9	11.2	10.5	9.5	10.8	10.0	9.0	10.3	9.5	8.5
	gpm	10.0	7.5	5.8	9.6	7.3	5.6	9.3	7.0	5.3	9.0	6.7	5.1
	wpd	16.2	9.1	5.4	15.0	8.6	5.0	14.1	7.9	4.5	13.0	7.2	4.1
76	TC	34.7	32.7	30.2	33.5	31.5	28.9	32.3	30.3	27.6	31.1	29.1	26.2
	SC	12.7	12.0	11.0	12.3	11.5	10.5	11.8	11.0	10.0	11.3	10.6	9.5
	gpm	10.0	7.5	5.8	9.6	7.3	5.6	9.3	7.0	5.3	9.0	6.7	5.1
	wpd	16.2	9.1	5.4	15.0	8.6	5.0	14.1	7.9	4.5	13.0	7.2	4.1
78	TC	34.7	32.7	30.2	33.5	31.5	28.9	32.3	30.3	27.7	31.1	29.1	26.3
	SC	13.7	13.0	12.0	13.3	12.5	11.5	12.8	12.1	11.1	12.3	11.6	10.6
	gpm	10.0	7.5	5.8	9.6	7.3	5.6	9.3	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.1	5.4	15.0	8.6	5.0	14.1	7.9	4.6	13.0	7.2	4.1
80	TC	34.7	32.8	30.3	33.5	31.6	29.0	32.4	30.4	27.7	31.2	29.2	26.4
	SC	14.8	14.0	13.1	14.3	13.6	12.6	13.9	13.1	12.1	13.4	12.6	11.6
	gpm	10.0	7.6	5.8	9.7	7.3	5.6	9.3	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.3	5.4	15.2	8.6	5.0	14.1	7.9	4.6	13.0	7.2	4.1
82	TC	34.7	32.8	30.3	33.6	31.6	29.0	32.4	30.4	27.7	31.2	29.2	26.4
	SC	15.8	15.1	14.1	15.4	14.6	13.6	14.9	14.1	13.1	14.4	13.7	12.7
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.3	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.1	5.4	15.2	8.6	5.0	14.1	7.9	4.6	13.0	7.2	4.1
84	TC	34.8	32.9	30.3	33.6	31.7	29.0	32.4	30.4	27.7	31.2	29.2	26.3
	SC	16.9	16.1	15.1	16.4	15.6	14.6	15.9	15.2	14.2	15.5	14.7	13.7
	gpm	10.0	7.6	5.8	9.7	7.3	5.6	9.3	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.3	5.4	15.2	8.6	5.0	14.1	7.9	4.6	13.2	7.2	4.1
86	TC	34.8	32.8	30.3	33.6	31.7	29.0	32.4	30.4	27.7	31.2	29.2	26.4
	SC	17.9	17.1	16.1	17.4	16.6	15.7	16.9	16.2	15.2	16.5	15.7	14.7
	gpm	10.0	7.5	5.8	9.7	7.3	5.6	9.3	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.1	5.4	15.2	8.6	5.0	14.1	7.9	4.6	13.2	7.2	4.1
88	TC	34.8	32.8	30.3	33.6	31.6	29.0	32.4	30.4	27.8	31.2	29.2	26.6
	SC	18.9	18.1	17.1	18.4	17.6	16.7	17.9	17.2	16.2	17.5	16.7	15.8
	gpm	10.0	7.5	5.8	9.6	7.3	5.6	9.3	7.0	5.4	9.0	6.7	5.1
	wpd	16.2	9.1	5.4	15.0	8.6	5.0	14.1	7.9	4.6	13.0	7.2	4.2
90	TC	34.7	32.8	30.4	33.5	31.6	29.2	32.3	30.4	28.0	31.1	29.2	26.9
	SC	19.9	19.1	18.2	19.4	18.7	17.8	18.9	18.2	17.3	18.5	17.8	16.9
	gpm	10.0	7.5	5.9	9.6	7.3	5.7	9.3	7.0	5.4	9.0	6.7	5.2
	wpd	16.2	9.1	5.6	15.0	8.6	5.1	13.8	7.9	4.7	13.0	7.2	4.4

4-Row Chilled Water Cooling

EDB	EWT	43						44				45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	41.2	39.7	38.1	39.9	38.4	36.8	38.7	37.1	35.4	37.3	35.7	34.0	
	SC	14.2	13.6	12.9	13.7	13.1	12.4	13.1	12.5	11.8	12.6	12.0	11.3	
	gpm	11.8	9.2	7.3	11.5	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.3	9.7	24.2	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
76	TC	41.2	39.7	38.1	39.9	38.4	36.7	38.6	37.0	35.4	37.3	35.7	33.9	
	SC	15.3	14.7	14.0	14.7	14.1	13.5	14.2	13.6	12.9	13.7	13.0	12.3	
	gpm	11.8	9.2	7.3	11.5	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.3	9.7	24.2	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
78	TC	41.1	39.7	38.0	39.9	38.4	36.7	38.6	37.0	35.4	37.3	35.7	34.0	
	SC	16.3	15.7	15.1	15.8	15.2	14.5	15.3	14.6	14.0	14.7	14.1	13.4	
	gpm	11.8	9.2	7.3	11.5	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.3	9.7	24.2	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
80	TC	41.2	39.7	38.1	39.9	38.4	36.8	38.6	37.1	35.4	37.3	35.7	34.0	
	SC	17.4	16.8	16.1	16.9	16.3	15.6	16.3	15.7	15.1	15.8	15.2	14.5	
	gpm	11.8	9.2	7.3	11.5	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.3	9.7	24.2	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
82	TC	41.2	39.6	38.1	39.9	38.4	36.8	38.6	37.1	35.4	37.3	35.7	34.0	
	SC	18.5	17.9	17.2	17.9	17.3	16.7	17.4	16.8	16.1	16.9	16.2	15.6	
	gpm	11.8	9.1	7.3	11.5	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.1	9.7	24.2	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
84	TC	41.2	39.6	38.1	39.9	38.4	36.7	38.6	37.0	35.4	37.3	35.7	34.0	
	SC	19.5	18.9	18.3	19.0	18.4	17.7	18.5	17.8	17.2	17.9	17.3	16.6	
	gpm	11.8	9.1	7.3	11.5	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.1	9.7	24.2	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
86	TC	41.2	39.6	38.0	39.9	38.3	36.7	38.6	37.0	35.3	37.3	35.7	34.0	
	SC	20.6	20.0	19.3	20.1	19.4	18.8	19.5	18.9	18.2	19.0	18.4	17.7	
	gpm	11.8	9.1	7.3	11.5	8.8	7.1	11.1	8.5	6.7	10.7	8.2	6.5	
	wpd	25.5	15.1	9.7	24.2	14.0	9.1	22.6	13.3	8.3	21.0	12.3	7.7	
88	TC	41.1	39.6	38.0	39.9	38.3	36.7	38.6	37.0	35.4	37.2	35.6	34.0	
	SC	21.7	21.0	20.4	21.1	20.5	19.9	20.6	19.9	19.3	20.0	19.4	18.8	
	gpm	11.8	9.1	7.3	11.5	8.8	7.1	11.1	8.5	6.8	10.7	8.2	6.5	
	wpd	25.5	15.1	9.7	24.2	14.0	9.1	22.6	13.3	8.5	21.0	12.3	7.7	
90	TC	41.1	39.6	38.1	39.8	38.3	36.8	38.5	37.0	35.5	37.2	35.7	34.2	
	SC	22.7	22.1	21.5	22.2	21.5	21.0	21.6	21.0	20.4	21.1	20.5	19.9	
	gpm	11.8	9.1	7.3	11.4	8.9	7.1	11.1	8.5	6.8	10.7	8.2	6.6	
	wpd	25.5	15.1	9.7	23.9	14.3	9.1	22.6	13.3	8.5	21.0	12.3	7.9	

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	49.0	47.8	46.5	47.6	46.4	45.0	46.2	44.9	43.5	44.7	43.4	41.9
	SC	19.0	18.4	17.7	18.3	17.7	17.0	17.6	16.9	16.3	16.9	16.2	15.5
	gpm	12.4	9.7	7.9	12.1	9.4	7.6	11.7	9.1	7.3	11.3	8.8	7.0
	wpd	24.3	14.8	9.8	23.2	13.9	9.2	21.7	13.0	8.5	20.4	12.2	7.8
76	TC	49.0	47.9	46.6	47.6	46.4	45.1	46.2	45.0	43.6	44.8	43.4	42.0
	SC	20.3	19.7	19.1	19.6	19.0	18.4	18.9	18.3	17.6	18.2	17.6	16.9
	gpm	12.3	9.7	7.9	12.1	9.4	7.6	11.7	9.1	7.3	11.3	8.8	7.1
	wpd	24.0	14.8	9.8	23.2	13.9	9.2	21.7	13.0	8.5	20.4	12.2	8.0
78	TC	49.0	47.9	46.6	47.7	46.5	45.1	46.2	45.0	43.6	44.8	43.5	42.0
	SC	21.6	21.0	20.4	20.9	20.3	19.7	20.2	19.6	19.0	19.5	18.9	18.2
	gpm	12.4	9.7	7.9	12.1	9.4	7.6	11.7	9.1	7.3	11.3	8.8	7.1
	wpd	24.3	14.8	9.8	23.2	13.9	9.2	21.7	13.0	8.5	20.4	12.2	8.0
80	TC	49.0	47.9	46.7	47.7	46.5	45.2	46.3	45.0	43.6	44.8	43.5	42.1
	SC	22.9	22.4	21.7	22.2	21.7	21.0	21.5	20.9	20.3	20.8	20.2	19.6
	gpm	12.4	9.7	7.9	12.0	9.5	7.6	11.7	9.2	7.3	11.3	8.8	7.1
	wpd	24.3	14.8	9.8	22.9	14.1	9.2	21.7	13.2	8.5	20.4	12.2	8.0
82	TC	49.1	48.0	46.7	47.7	46.5	45.2	46.2	45.0	43.7	44.8	43.5	42.1
	SC	24.2	23.7	23.1	23.5	23.0	22.3	22.8	22.3	21.6	22.1	21.5	20.9
	gpm	12.4	9.8	7.9	12.0	9.5	7.6	11.7	9.2	7.4	11.3	8.9	7.1
	wpd	24.3	15.1	9.8	22.9	14.1	9.2	21.5	13.2	8.7	20.4	12.4	8.0
84	TC	49.0	48.0	46.7	47.7	46.5	45.2	46.2	45.0	43.7	44.8	43.5	42.1
	SC	25.5	25.0	24.4	24.8	24.3	23.6	24.1	23.6	22.9	23.4	22.8	22.2
	gpm	12.4	9.8	7.9	12.0	9.5	7.6	11.7	9.2	7.4	11.3	8.9	7.1
	wpd	24.3	15.1	9.8	22.9	14.1	9.2	21.5	13.2	8.7	20.1	12.4	8.0
86	TC	49.0	47.9	46.7	47.6	46.5	45.2	46.2	45.0	43.6	44.8	43.5	42.1
	SC	26.8	26.3	25.7	26.1	25.6	24.9	25.4	24.9	24.2	24.7	24.2	23.5
	gpm	12.4	9.8	7.9	12.0	9.5	7.6	11.7	9.2	7.3	11.3	8.9	7.1
	wpd	24.3	15.1	9.8	22.9	14.1	9.2	21.5	13.2	8.5	20.1	12.4	8.0
88	TC	49.0	47.9	46.7	47.6	46.5	45.2	46.2	45.0	43.7	44.7	43.5	42.2
	SC	28.1	27.6	27.0	27.4	26.9	26.3	26.7	26.2	25.6	26.0	25.5	24.8
	gpm	12.4	9.7	7.9	12.0	9.5	7.6	11.7	9.2	7.3	11.3	8.9	7.1
	wpd	24.3	14.8	9.8	22.9	14.1	9.2	21.5	13.2	8.5	20.1	12.4	8.0
90	TC	49.0	47.9	46.7	47.6	46.5	45.3	46.2	45.0	43.8	44.7	43.6	42.3
	SC	29.4	28.9	28.3	28.7	28.2	27.6	28.0	27.5	26.9	27.3	26.8	26.2
	gpm	12.4	9.7	7.9	12.0	9.5	7.6	11.7	9.2	7.4	11.3	8.9	7.1
	wpd	24.3	14.8	9.8	22.9	14.1	9.2	21.5	13.2	8.7	20.1	12.4	8.0

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	32.4	30.3	28.2	31.3	29.2	27.0	30.2	28.1	25.9	29.1	26.9	24.8
	SC	10.1	9.3	8.6	9.7	9.0	8.2	9.3	8.6	7.9	8.9	8.2	7.5
	gpm	9.4	7.0	5.4	9.0	6.7	5.2	8.7	6.5	5.0	8.3	6.2	4.8
	wpd	26.7	14.7	8.9	24.9	13.8	8.2	23.2	12.8	7.7	21.2	11.7	7.0
76	TC	32.4	30.3	28.2	31.3	29.2	27.0	30.2	28.1	25.9	29.1	26.9	24.8
	SC	10.1	9.3	8.6	9.7	9.0	8.2	9.3	8.6	7.9	8.9	8.2	7.5
	gpm	9.4	7.0	5.4	9.0	6.7	5.2	8.7	6.5	5.0	8.3	6.2	4.8
	wpd	26.7	14.7	8.9	24.9	13.8	8.2	23.2	12.8	7.7	21.2	11.7	7.0
78	TC	32.4	30.3	28.1	31.3	29.2	27.0	30.2	28.0	25.9	29.1	26.9	24.8
	SC	11.1	10.4	9.7	10.7	10.0	9.3	10.4	9.6	8.9	10.0	9.3	8.6
	gpm	9.4	7.0	5.4	9.0	6.7	5.2	8.7	6.5	5.0	8.3	6.2	4.8
	wpd	26.7	14.7	8.9	24.9	13.8	8.2	23.2	12.8	7.7	21.2	11.7	7.0
80	TC	32.3	30.2	28.1	31.3	29.1	27.0	30.2	28.0	25.9	29.0	26.9	24.8
	SC	12.2	11.4	10.7	11.8	11.0	10.3	11.4	10.6	9.9	11.0	10.3	9.6
	gpm	9.4	7.0	5.4	9.0	6.7	5.2	8.7	6.5	4.9	8.3	6.2	4.8
	wpd	26.7	14.7	8.9	24.9	13.8	8.2	22.8	12.8	7.5	21.2	11.7	7.0
82	TC	32.4	30.3	28.2	31.3	29.2	27.1	30.2	28.1	26.0	29.1	27.0	24.9
	SC	13.2	12.4	11.7	12.8	12.1	11.3	12.4	11.7	11.0	12.0	11.3	10.6
	gpm	9.4	7.0	5.4	9.0	6.7	5.3	8.7	6.5	5.0	8.4	6.3	4.8
	wpd	26.7	15.1	8.9	24.9	13.8	8.4	23.2	12.8	7.7	21.6	11.9	7.0
84	TC	32.5	30.4	28.3	31.4	29.3	27.2	30.3	28.2	26.1	29.2	27.1	25.0
	SC	14.2	13.5	12.7	13.8	13.1	12.4	13.4	12.7	12.0	13.0	12.3	11.6
	gpm	9.4	7.0	5.5	9.0	6.8	5.3	8.7	6.5	5.0	8.4	6.3	4.8
	wpd	26.7	15.1	9.2	24.9	14.1	8.4	23.2	12.8	7.7	21.6	11.9	7.0
86	TC	32.6	30.5	28.4	31.5	29.4	27.3	30.4	28.3	26.2	29.3	27.2	25.0
	SC	15.2	14.5	13.8	14.8	14.1	13.4	14.5	13.7	13.0	14.1	13.3	12.6
	gpm	9.4	7.0	5.5	9.1	6.8	5.3	8.8	6.6	5.0	8.4	6.3	4.8
	wpd	27.1	15.1	9.2	25.3	14.1	8.4	23.7	13.2	7.7	21.6	11.9	7.0
88	TC	32.7	30.6	28.5	31.6	29.5	27.3	30.5	28.4	26.2	29.4	27.2	25.0
	SC	16.2	15.5	14.8	15.9	15.1	14.4	15.5	14.7	14.0	15.1	14.3	13.6
	gpm	9.4	7.0	5.5	9.1	6.8	5.3	8.8	6.6	5.0	8.5	6.3	4.8
	wpd	27.1	15.1	9.2	25.3	14.1	8.4	23.7	13.2	7.7	22.0	11.9	7.0
90	TC	32.7	30.6	28.5	31.7	29.5	27.3	30.5	28.4	26.2	29.4	27.2	25.0
	SC	17.3	16.5	15.7	16.9	16.1	15.4	16.5	15.7	15.0	16.1	15.3	14.6
	gpm	9.4	7.1	5.5	9.1	6.8	5.3	8.8	6.6	5.0	8.5	6.3	4.8
	wpd	27.1	15.4	9.2	25.3	14.1	8.4	23.7	13.2	7.7	22.0	11.9	7.0

3-Row Chilled Water Cooling

EDB	EWT	42						43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12		
74	TC	38.4	36.4	34.3	37.2	35.2	33.0	36.0	34.0	31.7	34.8	32.8	30.4			
	SC	12.5	11.8	10.9	12.1	11.3	10.5	11.6	10.8	10.0	11.1	10.4	9.5			
	gpm	11.1	8.4	6.6	10.8	8.1	6.3	10.4	7.8	6.1	10.0	7.5	5.9			
	wpd	19.8	11.3	7.1	18.7	10.7	6.5	17.4	9.9	6.0	16.2	9.1	5.6			
76	TC	38.4	36.4	34.3	37.2	35.2	33.0	36.0	34.0	31.7	34.8	32.7	30.4			
	SC	12.5	11.8	10.9	12.1	11.3	10.5	11.6	10.8	10.0	11.1	10.4	9.5			
	gpm	11.1	8.4	6.6	10.8	8.1	6.3	10.4	7.8	6.1	10.0	7.5	5.9			
	wpd	19.8	11.3	7.1	18.7	10.7	6.5	17.4	9.9	6.0	16.2	9.1	5.6			
78	TC	38.4	36.4	34.2	37.2	35.1	33.0	36.0	34.0	31.7	34.7	32.7	30.4			
	SC	13.6	12.8	12.0	13.1	12.3	11.5	12.6	11.9	11.0	12.2	11.4	10.6			
	gpm	11.1	8.4	6.6	10.8	8.1	6.3	10.4	7.8	6.1	10.0	7.5	5.9			
	wpd	19.8	11.3	6.9	18.7	10.7	6.5	17.4	9.9	6.0	16.2	9.1	5.6			
80	TC	38.3	36.4	34.2	37.2	35.1	33.0	36.0	34.0	31.7	34.7	32.7	30.4			
	SC	14.6	13.8	13.0	14.1	13.4	12.5	13.7	12.9	12.1	13.2	12.4	11.6			
	gpm	11.1	8.4	6.6	10.7	8.1	6.3	10.4	7.8	6.1	10.0	7.5	5.8			
	wpd	19.8	11.3	6.9	18.4	10.5	6.5	17.4	9.9	6.0	16.2	9.1	5.4			
82	TC	38.4	36.4	34.3	37.2	35.2	33.0	36.0	34.0	31.8	34.8	32.8	30.4			
	SC	15.6	14.9	14.1	15.2	14.4	13.6	14.7	13.9	13.1	14.2	13.5	12.7			
	gpm	11.1	8.4	6.6	10.8	8.1	6.3	10.4	7.8	6.1	10.0	7.5	5.9			
	wpd	19.8	11.5	7.1	18.7	10.7	6.5	17.4	9.9	6.0	16.2	9.1	5.6			
84	TC	38.4	36.4	34.4	37.2	35.2	33.1	36.0	34.0	31.8	34.8	32.8	30.5			
	SC	16.6	15.9	15.1	16.2	15.4	14.6	15.7	15.0	14.2	15.3	14.5	13.7			
	gpm	11.0	8.4	6.6	10.8	8.1	6.4	10.4	7.8	6.1	10.0	7.6	5.9			
	wpd	19.5	11.5	7.1	18.7	10.7	6.6	17.4	9.9	6.0	16.2	9.3	5.6			
86	TC	38.4	36.5	34.4	37.2	35.3	33.1	36.1	34.0	31.8	34.8	32.8	30.5			
	SC	17.7	16.9	16.1	17.2	16.5	15.7	16.8	16.0	15.2	16.3	15.6	14.7			
	gpm	11.1	8.4	6.6	10.7	8.1	6.4	10.4	7.8	6.1	10.1	7.6	5.9			
	wpd	19.8	11.5	7.1	18.4	10.7	6.6	17.4	9.9	6.0	16.4	9.3	5.6			
88	TC	38.4	36.5	34.3	37.2	35.3	33.1	36.0	34.0	31.8	34.9	32.8	30.5			
	SC	18.7	18.0	17.1	18.2	17.5	16.7	17.8	17.0	16.2	17.3	16.6	15.7			
	gpm	11.1	8.4	6.6	10.7	8.1	6.4	10.4	7.8	6.1	10.1	7.5	5.9			
	wpd	19.8	11.5	7.1	18.4	10.7	6.6	17.4	9.9	6.0	16.4	9.1	5.6			
90	TC	38.4	36.5	34.3	37.3	35.3	33.1	36.0	34.0	31.8	34.8	32.8	30.5			
	SC	19.7	19.0	18.2	19.3	18.5	17.7	18.8	18.0	17.2	18.3	17.6	16.8			
	gpm	11.1	8.4	6.6	10.7	8.1	6.4	10.4	7.8	6.1	10.0	7.5	5.9			
	wpd	19.8	11.5	7.1	18.4	10.7	6.6	17.4	9.9	6.0	16.2	9.1	5.6			

4-Row Chilled Water Cooling

EDB	EWT	43						44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	45.4	43.9	42.2	44.1	42.6	40.9	42.8	41.2	39.6	41.5	39.9	38.2
	SC	15.2	14.6	13.9	14.7	14.1	13.4	14.1	13.5	12.8	13.6	13.0	12.3
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.4
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.9
76	TC	45.4	43.9	42.2	44.1	42.6	40.9	42.8	41.2	39.6	41.5	39.9	38.2
	SC	15.2	14.6	13.9	14.7	14.1	13.4	14.1	13.5	12.8	13.6	13.0	12.3
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.4
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.9
78	TC	45.3	43.8	42.2	44.0	42.5	40.8	42.7	41.2	39.5	41.4	39.8	38.1
	SC	16.3	15.7	15.0	15.7	15.1	14.4	15.2	14.6	13.9	14.7	14.0	13.4
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.4
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.9
80	TC	45.3	43.8	42.2	44.0	42.5	40.8	42.7	41.2	39.5	41.4	39.8	38.1
	SC	17.3	16.7	16.1	16.8	16.2	15.5	16.3	15.6	15.0	15.7	15.1	14.4
	gpm	13.1	10.0	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.2	18.4	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.7
82	TC	45.3	43.8	42.2	44.0	42.5	40.9	42.7	41.2	39.5	41.4	39.8	38.1
	SC	18.4	17.8	17.1	17.9	17.2	16.6	17.3	16.7	16.1	16.8	16.2	15.5
	gpm	13.1	10.0	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.4
	wpd	31.2	18.4	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.9
84	TC	45.3	43.8	42.2	44.0	42.5	40.9	42.7	41.2	39.5	41.4	39.8	38.1
	SC	19.5	18.8	18.2	18.9	18.3	17.7	18.4	17.8	17.1	17.9	17.2	16.6
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.7
86	TC	45.3	43.8	42.2	44.0	42.5	40.9	42.7	41.2	39.5	41.4	39.8	38.1
	SC	20.5	19.9	19.3	20.0	19.4	18.7	19.5	18.8	18.2	18.9	18.3	17.6
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.7
88	TC	45.3	43.8	42.2	44.0	42.5	40.8	42.7	41.1	39.5	41.4	39.8	38.1
	SC	21.6	21.0	20.3	21.1	20.4	19.8	20.5	19.9	19.2	20.0	19.4	18.7
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.7
90	TC	45.3	43.8	42.2	44.0	42.4	40.8	42.7	41.1	39.4	41.4	39.7	38.1
	SC	22.6	22.0	21.4	22.1	21.5	20.9	21.6	20.9	20.3	21.0	20.4	19.8
	gpm	13.1	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.6	11.9	9.2	7.3
	wpd	31.2	18.6	11.9	29.4	17.5	11.2	27.6	16.4	10.5	25.9	15.3	9.7

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	53.7	52.6	51.3	52.3	51.1	49.8	50.9	49.6	48.2	49.4	48.1	46.7
	SC	20.2	19.7	19.0	19.5	18.9	18.3	18.8	18.2	17.6	18.1	17.5	16.8
	gpm	13.5	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.6	9.8	7.9
	wpd	29.0	18.0	12.0	27.7	17.0	11.1	26.5	16.0	10.6	24.9	15.1	9.8
76	TC	53.7	52.6	51.3	52.3	51.1	49.8	50.9	49.6	48.2	49.4	48.1	46.7
	SC	20.2	19.7	19.0	19.5	18.9	18.3	18.8	18.2	17.6	18.1	17.5	16.8
	gpm	13.5	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.6	9.8	7.9
	wpd	29.0	18.0	12.0	27.7	17.0	11.1	26.5	16.0	10.6	24.9	15.1	9.8
78	TC	53.7	52.6	51.4	52.3	51.2	49.8	50.9	49.7	48.3	49.5	48.2	46.7
	SC	21.5	21.0	20.4	20.8	20.3	19.6	20.2	19.6	18.9	19.5	18.8	18.2
	gpm	13.5	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.6	9.8	7.9
	wpd	29.0	18.0	12.0	27.7	17.0	11.1	26.5	16.0	10.6	24.9	15.1	9.8
80	TC	53.8	52.7	51.4	52.4	51.2	49.9	50.9	49.7	48.4	49.5	48.2	46.8
	SC	22.9	22.3	21.7	22.2	21.6	21.0	21.5	20.9	20.2	20.8	20.2	19.5
	gpm	13.6	10.7	8.6	13.2	10.4	8.5	12.9	10.1	8.2	12.6	9.8	7.9
	wpd	29.3	18.0	11.8	27.7	17.0	11.3	26.1	16.0	10.6	24.9	15.1	10.0
82	TC	53.8	52.7	51.4	52.4	51.2	49.9	50.9	49.8	48.4	49.5	48.3	46.8
	SC	24.2	23.6	23.0	23.5	22.9	22.3	22.8	22.2	21.6	22.1	21.5	20.8
	gpm	13.6	10.7	8.7	13.2	10.4	8.5	12.9	10.1	8.2	12.6	9.8	7.9
	wpd	29.3	18.0	12.0	27.7	17.0	11.3	26.1	16.0	10.6	24.9	15.1	10.0
84	TC	53.8	52.7	51.4	52.4	51.2	49.9	51.0	49.8	48.4	49.5	48.3	46.9
	SC	25.5	25.0	24.3	24.8	24.2	23.6	24.1	23.5	22.9	23.4	22.8	22.2
	gpm	13.6	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.5	9.8	7.9
	wpd	29.3	18.0	12.0	27.7	17.0	11.1	26.1	16.0	10.6	24.6	15.1	10.0
86	TC	53.8	52.7	51.4	52.4	51.2	49.9	51.0	49.8	48.4	49.5	48.3	46.9
	SC	26.8	26.3	25.7	26.1	25.6	24.9	25.4	24.9	24.2	24.7	24.1	23.5
	gpm	13.6	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.5	9.8	7.9
	wpd	29.3	18.0	12.0	27.7	17.0	11.1	26.1	16.0	10.6	24.6	15.1	10.0
88	TC	53.8	52.7	51.4	52.4	51.2	49.9	50.9	49.8	48.4	49.5	48.3	46.8
	SC	28.1	27.6	27.0	27.4	26.9	26.2	26.7	26.2	25.5	26.0	25.4	24.8
	gpm	13.6	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.5	9.8	7.9
	wpd	29.3	18.0	12.0	27.7	17.0	11.1	26.1	16.0	10.6	24.6	15.1	9.8
90	TC	53.7	52.7	51.4	52.3	51.2	49.9	50.9	49.7	48.4	49.5	48.2	46.8
	SC	29.4	28.9	28.3	28.7	28.2	27.5	28.0	27.5	26.8	27.3	26.7	26.1
	gpm	13.6	10.7	8.7	13.2	10.4	8.4	12.9	10.1	8.2	12.5	9.8	7.9
	wpd	29.3	18.0	12.0	27.7	17.0	11.1	26.1	16.0	10.6	24.6	15.1	9.8

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	20.3	17.8	15.5	19.2	16.9	14.6	18.1	16.0	12.9	17.1	15.1	12.0
	SC	17.5	16.2	14.6	17.1	15.6	14.0	16.5	15.1	12.6	16.0	14.5	11.8
	gpm	5.1	3.6	2.6	4.8	3.4	2.4	4.6	3.3	2.2	4.3	3.0	2.0
	wpd	5.6	2.8	1.4	5.0	2.5	1.3	4.5	2.3	1.0	4.0	2.0	0.9
76	TC	21.3	19.2	17.2	20.3	18.3	15.5	19.3	17.5	14.7	18.5	16.2	13.9
	SC	19.4	18.1	16.6	18.9	17.5	15.3	18.4	17.0	14.5	17.8	15.9	13.7
	gpm	5.3	3.9	2.9	5.1	3.7	2.6	4.9	3.6	2.5	4.7	3.3	2.4
	wpd	6.1	3.2	1.8	5.6	3.0	1.4	5.1	2.7	1.4	4.7	2.3	1.2
78	TC	22.4	20.7	18.1	21.6	19.9	17.3	20.8	18.6	16.6	19.6	17.8	15.8
	SC	21.2	20.0	17.8	20.7	19.4	17.1	20.2	18.3	16.3	19.3	17.5	15.5
	gpm	5.7	4.2	3.0	5.5	4.0	2.9	5.3	3.8	2.8	5.0	3.6	2.7
	wpd	7.0	3.7	2.0	6.5	3.4	1.8	6.0	3.1	1.7	5.3	2.8	1.5
80	TC	23.8	21.7	19.8	23.1	21.0	19.1	21.9	20.2	18.3	21.2	19.5	17.6
	SC	23.1	21.3	19.5	22.5	20.6	18.8	21.5	19.9	18.0	20.8	19.2	17.3
	gpm	6.0	4.4	3.3	5.9	4.2	3.2	5.6	4.1	3.1	5.3	3.9	3.0
	wpd	7.8	4.1	2.4	7.4	3.8	2.2	6.6	3.6	2.1	6.1	3.3	1.9
82	TC	24.8	23.3	21.5	24.1	22.6	20.8	23.4	21.8	20.0	22.7	21.1	19.3
	SC	24.4	22.9	21.2	23.7	22.2	20.4	23.0	21.5	19.7	22.3	20.8	19.0
	gpm	6.3	4.7	3.6	6.1	4.6	3.5	5.9	4.5	3.4	5.7	4.2	3.3
	wpd	8.5	4.8	2.8	7.9	4.5	2.6	7.6	4.3	2.5	7.0	3.8	2.3
84	TC	26.3	24.9	23.2	25.6	24.2	22.4	24.8	23.5	21.7	24.1	22.7	21.0
	SC	25.9	24.5	22.8	25.1	23.8	22.1	24.4	23.1	21.4	23.7	22.4	20.6
	gpm	6.7	5.0	3.9	6.5	4.9	3.8	6.3	4.7	3.6	6.1	4.6	3.6
	wpd	9.6	5.5	3.3	8.9	5.1	3.1	8.5	4.8	2.8	7.9	4.5	2.7
86	TC	27.7	26.5	24.8	27.0	25.8	24.1	26.3	25.0	23.4	25.6	24.3	22.7
	SC	27.3	26.0	24.4	26.6	25.3	23.7	25.9	24.6	23.0	25.2	23.9	22.3
	gpm	7.0	5.3	4.2	6.8	5.2	4.1	6.7	5.0	3.9	6.5	4.9	3.9
	wpd	10.7	6.1	3.7	10.0	5.8	3.6	9.6	5.5	3.3	8.9	5.1	3.2
88	TC	29.2	28.0	26.4	28.5	27.3	25.7	27.8	26.6	25.0	27.0	25.9	24.3
	SC	28.7	27.6	26.0	28.0	26.9	25.3	27.3	26.2	24.6	26.6	25.5	23.9
	gpm	7.4	5.7	4.5	7.2	5.6	4.4	7.0	5.4	4.2	6.8	5.3	4.1
	wpd	11.8	7.0	4.3	11.1	6.6	4.1	10.7	6.3	3.8	10.0	6.0	3.6
90	TC	30.7	29.5	28.0	29.9	28.8	27.3	29.2	28.1	26.6	28.5	27.4	25.9
	SC	30.2	29.0	27.5	29.5	28.3	26.9	28.7	27.6	26.2	28.0	26.9	25.5
	gpm	7.8	5.9	4.7	7.6	5.8	4.6	7.4	5.6	4.5	7.2	5.6	4.4
	wpd	13.0	7.6	4.8	12.3	7.2	4.5	11.8	6.8	4.3	11.1	6.6	4.1

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	27.4	24.9	22.4	25.9	23.4	21.2	24.4	22.1	20.1	22.9	20.9	19.0
	SC	21.8	20.6	19.4	21.1	19.9	18.8	20.4	19.3	18.2	19.7	18.7	17.6
	gpm	7.0	5.1	3.8	6.6	4.7	3.6	6.2	4.5	3.4	5.8	4.3	3.2
	wpd	8.6	4.6	2.6	7.7	4.0	2.3	6.8	3.6	2.1	6.0	3.3	1.9
76	TC	28.1	25.9	23.9	26.7	24.7	22.9	25.3	23.5	21.9	24.0	22.4	20.9
	SC	23.8	22.7	21.6	23.1	22.1	21.0	22.4	21.5	20.5	21.8	20.9	19.8
	gpm	7.1	5.2	4.0	6.8	5.0	3.9	6.4	4.7	3.7	6.1	4.5	3.6
	wpd	9.0	4.9	2.9	8.3	4.4	2.7	7.3	4.0	2.5	6.6	3.6	2.3
78	TC	29.0	27.2	25.6	27.6	26.1	24.6	26.4	25.1	23.7	25.4	24.1	21.2
	SC	25.8	24.8	23.9	25.1	24.3	23.3	24.6	23.7	22.7	24.0	23.1	20.9
	gpm	7.3	5.5	4.3	7.0	5.3	4.2	6.7	5.1	4.0	6.4	4.9	3.6
	wpd	9.7	5.5	3.4	8.8	5.0	3.1	8.1	4.6	2.9	7.3	4.3	2.3
80	TC	30.0	28.6	27.3	28.9	27.6	25.0	27.8	26.7	24.1	26.9	25.0	23.2
	SC	27.8	27.0	26.1	27.3	26.4	24.7	26.7	25.8	23.8	26.1	24.7	22.9
	gpm	7.6	5.8	4.6	7.3	5.6	4.3	7.0	5.5	4.1	6.8	5.1	4.0
	wpd	10.3	6.0	3.8	9.7	5.6	3.3	8.8	5.3	3.0	8.3	4.6	2.8
82	TC	31.2	30.2	27.9	30.3	28.6	27.0	29.0	27.7	26.1	28.2	26.9	25.2
	SC	30.0	29.2	27.5	29.4	28.2	26.6	28.7	27.4	25.8	27.8	26.5	24.9
	gpm	7.9	6.1	4.7	7.7	5.8	4.6	7.3	5.6	4.4	7.1	5.5	4.3
	wpd	11.2	6.6	3.9	10.5	6.0	3.8	9.7	5.6	3.5	9.0	5.3	3.3
84	TC	32.4	31.2	29.8	31.6	30.4	28.9	30.7	29.5	28.0	29.9	28.7	27.2
	SC	32.0	30.8	29.4	31.2	30.0	28.5	30.3	29.2	27.7	29.5	28.3	26.8
	gpm	8.2	6.3	5.1	8.0	6.2	4.9	7.7	6.0	4.7	7.5	5.8	4.6
	wpd	12.1	7.1	4.6	11.4	6.8	4.3	10.7	6.5	4.0	10.1	6.0	3.8
86	TC	34.1	33.0	31.7	33.3	32.2	30.8	32.4	31.4	29.9	31.6	30.5	29.1
	SC	33.7	32.6	31.3	32.8	31.8	30.4	32.0	31.0	29.6	31.2	30.1	28.7
	gpm	8.6	6.7	5.4	8.4	6.6	5.2	8.2	6.3	5.1	8.0	6.2	4.9
	wpd	13.3	8.1	5.2	12.5	7.7	4.9	12.1	7.1	4.6	11.4	6.8	4.3
88	TC	35.8	34.8	33.5	35.0	34.0	32.7	34.1	33.2	31.8	33.3	32.3	31.0
	SC	35.3	34.4	33.1	34.5	33.6	32.2	33.7	32.7	31.4	32.8	31.9	30.6
	gpm	9.1	7.0	5.7	8.8	6.9	5.5	8.6	6.7	5.4	8.5	6.6	5.2
	wpd	14.8	8.8	5.8	14.0	8.5	5.5	13.3	8.1	5.2	12.8	7.7	4.9
90	TC	37.5	36.6	35.3	36.6	35.8	34.5	35.8	34.9	33.7	35.0	34.1	32.8
	SC	37.0	36.1	34.9	36.2	35.3	34.0	35.4	34.5	33.2	34.5	33.6	32.4
	gpm	9.5	7.4	5.9	9.2	7.3	5.8	9.1	7.1	5.7	8.8	6.9	5.5
	wpd	16.1	9.9	6.3	15.3	9.5	6.1	14.8	9.0	5.8	14.0	8.5	5.5

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	29.1	26.7	24.5	27.5	25.2	23.2	25.9	23.8	21.9	24.4	22.5	20.8												
	SC	22.2	21.2	20.1	21.5	20.5	19.5	20.8	19.8	18.9	20.1	19.2	18.4												
	gpm	7.4	5.4	4.1	6.9	5.1	3.9	6.5	4.8	3.7	6.2	4.5	3.5												
	wpd	6.5	3.5	2.1	5.8	3.1	1.8	5.2	2.8	1.6	4.6	2.5	1.5												
76	TC	29.7	27.7	25.8	28.1	26.3	24.7	26.7	25.0	23.5	25.3	23.9	22.5												
	SC	24.1	23.2	22.3	23.4	22.5	21.7	22.7	22.0	21.2	22.1	21.4	20.6												
	gpm	7.5	5.6	4.4	7.1	5.3	4.1	6.8	5.1	4.0	6.4	4.8	3.8												
	wpd	6.8	3.8	2.3	6.1	3.4	2.1	5.5	3.1	1.9	4.9	2.8	1.8												
78	TC	30.4	28.7	27.3	29.0	27.5	26.2	27.7	26.4	25.2	26.4	25.4	22.1												
	SC	26.0	25.2	24.5	25.4	24.7	24.0	24.8	24.1	23.4	24.2	23.6	21.8												
	gpm	7.7	5.8	4.6	7.4	5.6	4.4	7.0	5.3	4.3	6.7	5.1	3.8												
	wpd	7.1	4.0	2.5	6.5	3.7	2.4	5.9	3.4	2.2	5.4	3.1	1.7												
80	TC	31.2	29.9	28.8	29.9	28.9	25.9	28.8	27.9	25.0	27.8	25.7	24.1												
	SC	28.0	27.4	26.7	27.4	26.8	25.6	26.8	26.3	24.7	26.3	25.4	23.8												
	gpm	7.9	6.1	4.9	7.5	5.9	4.4	7.3	5.6	4.2	7.1	5.2	4.1												
	wpd	7.5	4.5	2.9	6.8	4.1	2.3	6.4	3.8	2.1	6.0	3.2	2.0												
82	TC	32.2	31.3	28.8	31.1	29.4	27.9	29.6	28.5	27.0	28.8	27.6	26.1												
	SC	30.1	29.5	28.4	29.5	28.9	27.5	29.0	28.1	26.7	28.4	27.3	25.8												
	gpm	8.1	6.3	4.9	7.8	5.9	4.7	7.4	5.8	4.6	7.3	5.6	4.4												
	wpd	7.9	4.8	2.9	7.4	4.2	2.7	6.7	4.0	2.5	6.4	3.7	2.4												
84	TC	33.5	32.0	30.7	32.2	31.2	29.8	31.3	30.3	29.0	30.5	29.5	28.1												
	SC	32.2	31.6	30.3	31.8	30.8	29.4	30.9	29.9	28.6	30.1	29.1	27.7												
	gpm	8.5	6.5	5.2	8.1	6.3	5.0	7.9	6.2	4.9	7.7	5.9	4.7												
	wpd	8.7	5.0	3.2	7.9	4.8	3.1	7.5	4.6	2.9	7.2	4.2	2.7												
86	TC	34.7	33.8	32.6	33.9	33.0	31.7	33.1	32.1	30.9	32.2	31.3	30.0												
	SC	34.3	33.4	32.1	33.4	32.5	31.3	32.6	31.7	30.5	31.8	30.9	29.6												
	gpm	8.8	6.8	5.5	8.6	6.7	5.3	8.4	6.5	5.2	8.2	6.3	5.0												
	wpd	9.3	5.6	3.6	8.8	5.4	3.4	8.4	5.2	3.2	8.1	4.8	3.1												
88	TC	36.4	35.6	34.4	35.6	34.7	33.6	34.8	33.9	32.7	34.0	33.1	31.9												
	SC	35.9	35.1	34.0	35.1	34.3	33.1	34.3	33.5	32.3	33.5	32.6	31.4												
	gpm	9.3	7.2	5.8	9.0	7.1	5.6	8.8	6.8	5.5	8.6	6.7	5.3												
	wpd	10.3	6.3	4.0	9.8	6.0	3.8	9.3	5.6	3.6	8.8	5.4	3.4												
90	TC	38.1	37.3	36.2	37.3	36.5	35.4	36.5	35.6	34.6	35.6	34.8	33.7												
	SC	37.6	36.8	35.8	36.8	36.0	34.9	36.0	35.2	34.1	35.2	34.4	33.3												
	gpm	9.6	7.5	6.1	9.5	7.4	5.9	9.3	7.2	5.9	9.0	7.1	5.7												
	wpd	11.2	6.8	4.5	10.8	6.5	4.2	10.3	6.3	4.1	9.8	6.0	3.9												

5-Row Chilled Water Cooling

EDB	EWT	42						43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12		
74	TC	29.1	27.1	25.2	27.5	25.6	23.9	26.0	24.2	22.6	24.5	22.8	21.4			
	SC	22.4	21.5	20.5	21.7	20.8	19.9	20.9	20.1	19.3	20.2	19.4	18.8			
	gpm	7.4	5.5	4.3	7.0	5.2	4.0	6.6	4.9	3.8	6.2	4.6	3.6			
	wpd	6.9	3.8	2.3	6.1	3.4	2.0	5.4	3.0	1.8	4.9	2.7	1.6			
76	TC	29.6	27.9	26.4	28.1	26.6	25.1	26.6	25.3	24.0	25.3	24.1	23.0			
	SC	24.2	23.4	22.6	23.5	22.7	22.0	22.8	22.1	21.5	22.1	21.5	21.0			
	gpm	7.5	5.7	4.5	7.1	5.4	4.2	6.8	5.1	4.1	6.4	4.9	3.9			
	wpd	7.1	4.0	2.5	6.4	3.7	2.2	5.8	3.3	2.1	5.2	3.0	1.9			
78	TC	30.1	28.8	27.6	28.7	27.6	26.5	27.4	26.4	25.5	26.2	25.4	24.6			
	SC	26.0	25.4	24.8	25.4	24.8	24.2	24.7	24.2	23.7	24.1	23.7	23.2			
	gpm	7.6	5.9	4.7	7.2	5.6	4.5	7.0	5.4	4.3	6.6	5.2	4.1			
	wpd	7.3	4.3	2.8	6.6	3.9	2.5	6.1	3.7	2.3	5.5	3.4	2.2			
80	TC	30.8	29.8	28.9	29.6	28.7	28.0	28.4	27.7	27.1	27.3	26.8	25.4			
	SC	28.0	27.4	27.0	27.3	26.9	26.5	26.7	26.4	26.0	26.2	25.9	25.0			
	gpm	7.8	6.0	4.9	7.5	5.8	4.8	7.2	5.6	4.6	6.9	5.5	4.3			
	wpd	7.7	4.5	3.0	7.1	4.2	2.9	6.5	3.9	2.6	6.0	3.7	2.3			
82	TC	31.6	31.0	30.4	30.6	30.1	28.7	29.6	28.6	27.9	28.2	27.8	27.2			
	SC	29.9	29.6	29.2	29.4	29.1	28.1	28.9	28.0	27.7	27.8	27.6	27.3			
	gpm	8.0	6.3	5.2	7.7	6.1	4.8	7.5	5.8	4.8	7.2	5.7	4.6			
	wpd	8.1	5.0	3.4	7.5	4.6	2.9	7.1	4.2	2.9	6.5	4.0	2.7			
84	TC	32.7	31.7	31.2	31.4	31.0	30.4	30.6	30.2	29.6	29.8	29.4	28.8			
	SC	32.0	31.1	30.8	30.9	30.7	30.4	30.5	30.3	30.0	30.1	29.8	29.2			
	gpm	8.3	6.4	5.2	7.9	6.3	5.1	7.8	6.1	5.0	7.6	5.9	4.8			
	wpd	8.6	5.2	3.5	7.9	5.0	3.3	7.7	4.8	3.1	7.3	4.4	2.9			
86	TC	33.7	33.3	32.8	32.9	32.6	32.0	32.2	31.8	31.3	31.4	31.0	30.5			
	SC	33.6	33.4	33.2	33.2	33.0	32.5	32.6	32.3	31.7	31.8	31.5	30.9			
	gpm	8.5	6.8	5.5	8.3	6.6	5.4	8.1	6.5	5.2	7.9	6.3	5.2			
	wpd	9.1	5.8	3.8	8.8	5.5	3.7	8.4	5.3	3.5	7.9	5.0	3.4			
88	TC	35.2	34.9	34.5	34.5	34.2	33.7	33.7	33.4	32.9	32.9	32.6	32.1			
	SC	35.7	35.4	35.0	35.0	34.7	34.2	34.2	33.9	33.4	33.4	33.1	32.6			
	gpm	8.9	7.1	5.8	8.7	6.9	5.7	8.6	6.8	5.6	8.3	6.6	5.5			
	wpd	10.0	6.4	4.2	9.5	6.0	4.0	9.2	5.8	3.9	8.8	5.5	3.7			
90	TC	36.8	36.5	36.1	36.0	35.7	35.3	35.3	35.0	34.5	34.5	34.2	33.8			
	SC	37.3	37.0	36.6	36.5	36.3	35.8	35.8	35.5	35.0	35.0	34.7	34.3			
	gpm	9.3	7.4	6.1	9.1	7.2	5.9	8.9	7.1	5.9	8.8	7.0	5.7			
	wpd	10.9	6.9	4.6	10.5	6.6	4.4	10.0	6.4	4.3	9.7	6.1	4.1			

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	22.9	19.6	16.4	21.5	18.2	15.3	20.1	17.1	14.2	18.8	15.9	13.2
	SC	16.9	15.5	13.9	16.3	14.9	13.3	15.7	14.4	12.8	15.2	13.8	12.2
	gpm	5.8	3.9	2.7	5.4	3.7	2.6	5.0	3.5	2.4	4.7	3.2	2.2
	wpd	7.2	3.3	1.6	6.3	3.0	1.4	5.5	2.6	1.2	4.8	2.2	1.1
76	TC	23.4	20.6	17.8	22.2	19.4	16.8	20.9	18.3	15.8	19.7	17.3	15.0
	SC	18.7	17.3	15.9	18.1	16.8	15.3	17.5	16.2	14.7	17.0	15.7	14.1
	gpm	5.9	4.2	3.0	5.6	3.9	2.8	5.3	3.7	2.7	5.0	3.5	2.5
	wpd	7.6	3.7	1.9	6.8	3.3	1.7	6.0	3.0	1.5	5.3	2.6	1.4
78	TC	24.1	21.6	19.2	23.0	20.6	18.3	21.8	19.6	17.5	20.7	18.7	16.7
	SC	20.4	19.2	17.7	19.9	18.6	17.2	19.4	18.1	16.6	18.8	17.6	16.1
	gpm	6.1	4.4	3.3	5.8	4.2	3.1	5.5	3.9	3.0	5.3	3.8	2.8
	wpd	7.9	4.1	2.3	7.2	3.7	2.1	6.5	3.3	1.9	6.0	3.1	1.7
80	TC	24.9	22.8	20.7	23.8	21.9	19.9	22.8	21.0	19.1	21.9	20.2	17.6
	SC	22.2	21.0	19.7	21.7	20.5	19.1	21.1	20.0	18.5	20.6	19.4	17.3
	gpm	6.3	4.6	3.5	6.0	4.5	3.3	5.8	4.2	3.3	5.6	4.1	3.0
	wpd	8.5	4.5	2.6	7.8	4.3	2.4	7.2	3.8	2.3	6.6	3.6	1.9
82	TC	25.8	24.1	22.3	24.8	23.2	21.6	23.9	22.5	20.1	23.1	21.2	19.4
	SC	23.9	22.9	21.5	23.4	22.3	20.9	23.0	21.8	19.8	22.4	20.8	19.0
	gpm	6.5	4.9	3.8	6.3	4.7	3.6	6.1	4.5	3.4	5.9	4.3	3.3
	wpd	9.2	5.1	3.1	8.5	4.7	2.8	7.9	4.4	2.5	7.4	4.0	2.3
84	TC	26.8	25.5	23.2	26.0	24.8	22.5	25.3	23.5	21.8	24.2	22.8	21.0
	SC	25.7	24.7	22.8	25.2	24.1	22.1	24.7	23.1	21.4	23.8	22.4	20.7
	gpm	6.8	5.2	3.9	6.6	5.0	3.8	6.4	4.7	3.6	6.1	4.6	3.6
	wpd	10.0	5.8	3.3	9.4	5.5	3.1	8.7	4.8	2.8	7.9	4.5	2.7
86	TC	28.2	26.5	24.9	27.1	25.8	24.1	26.4	25.1	23.4	25.6	24.4	22.7
	SC	27.5	26.1	24.5	26.6	25.4	23.8	25.9	24.7	23.0	25.2	24.0	22.3
	gpm	7.1	5.3	4.2	6.8	5.2	4.1	6.7	5.1	3.9	6.5	5.0	3.9
	wpd	10.9	6.1	3.8	10.0	5.8	3.6	9.6	5.6	3.3	9.2	5.3	3.2
88	TC	29.3	28.1	26.5	28.5	27.4	25.8	27.8	26.7	25.1	27.1	26.0	24.3
	SC	28.8	27.6	26.0	28.1	26.9	25.4	27.4	26.2	24.7	26.7	25.5	23.9
	gpm	7.4	5.7	4.5	7.3	5.6	4.4	7.0	5.4	4.2	6.9	5.3	4.1
	wpd	11.8	7.0	4.3	11.4	6.6	4.1	10.7	6.3	3.8	10.2	6.0	3.6
90	TC	30.7	29.6	28.1	30.0	28.9	27.4	29.3	28.1	26.6	28.6	27.4	25.9
	SC	30.2	29.1	27.6	29.5	28.4	26.9	28.8	27.7	26.2	28.1	27.0	25.5
	gpm	7.8	6.0	4.7	7.6	5.9	4.6	7.4	5.7	4.5	7.3	5.6	4.4
	wpd	13.0	7.8	4.8	12.5	7.4	4.5	11.8	7.0	4.4	11.4	6.6	4.1

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	31.3	28.2	24.9	29.6	26.4	23.4	27.8	24.8	21.8	26.1	23.1	20.2
	SC	21.3	20.0	18.6	20.6	19.2	17.9	19.8	18.5	17.2	19.1	17.8	16.5
	gpm	7.9	5.7	4.2	7.5	5.4	4.0	7.0	5.1	3.7	6.6	4.7	3.4
	wpd	11.2	5.8	3.1	10.1	5.2	2.8	8.9	4.6	2.5	7.7	3.9	2.1
76	TC	31.6	28.8	26.0	30.0	27.2	24.6	28.4	25.7	23.1	26.7	24.2	21.7
	SC	23.2	21.9	20.7	22.4	21.2	20.0	21.7	20.5	19.3	21.0	19.9	18.7
	gpm	8.0	5.8	4.4	7.6	5.5	4.1	7.2	5.2	3.9	6.8	4.9	3.7
	wpd	11.4	6.1	3.5	10.3	5.5	3.0	9.3	4.9	2.7	8.3	4.3	2.5
78	TC	32.0	29.6	27.1	30.5	28.1	25.8	29.0	26.7	24.5	27.5	25.3	23.3
	SC	25.0	23.9	22.7	24.3	23.2	22.1	23.7	22.6	21.5	23.0	21.9	21.0
	gpm	8.1	6.0	4.6	7.7	5.7	4.3	7.3	5.4	4.1	7.0	5.1	4.0
	wpd	11.6	6.5	3.8	10.5	5.8	3.4	9.7	5.2	3.0	8.7	4.7	2.8
80	TC	32.6	30.5	28.3	31.1	29.1	27.1	29.7	27.8	26.0	28.3	26.6	25.0
	SC	26.9	25.9	24.9	26.3	25.3	24.3	25.6	24.7	23.7	25.0	24.1	23.2
	gpm	8.2	6.2	4.8	7.9	5.9	4.6	7.5	5.6	4.4	7.2	5.4	4.2
	wpd	12.1	6.8	4.2	11.2	6.3	3.8	10.1	5.6	3.5	9.3	5.2	3.1
82	TC	33.3	31.5	29.7	31.9	30.2	28.6	30.5	29.0	27.6	29.3	28.0	26.7
	SC	28.9	28.0	27.0	28.2	27.4	26.5	27.6	26.8	25.9	27.0	26.3	25.4
	gpm	8.5	6.4	5.0	8.1	6.1	4.8	7.7	5.8	4.7	7.4	5.7	4.5
	wpd	12.8	7.3	4.4	11.6	6.6	4.2	10.7	6.1	3.9	9.9	5.8	3.6
84	TC	34.0	32.6	31.2	32.8	31.5	30.2	31.6	30.5	29.2	30.5	29.5	27.2
	SC	30.8	30.1	29.2	30.2	29.5	28.7	29.7	29.0	28.1	29.1	28.4	26.9
	gpm	8.6	6.6	5.3	8.3	6.4	5.1	8.0	6.2	4.9	7.7	6.0	4.6
	wpd	13.3	7.9	5.0	12.3	7.3	4.7	11.4	6.8	4.3	10.7	6.5	3.8
86	TC	35.0	33.9	32.7	33.9	33.0	31.8	32.9	32.0	30.0	32.0	30.6	29.1
	SC	32.9	32.2	31.4	32.3	31.7	30.8	31.7	31.1	29.6	31.2	30.2	28.8
	gpm	8.8	6.9	5.5	8.6	6.7	5.4	8.3	6.5	5.1	8.1	6.2	4.9
	wpd	14.0	8.5	5.5	13.3	8.1	5.2	12.3	7.5	4.6	11.9	6.8	4.3
88	TC	36.2	35.4	33.6	35.3	34.1	32.7	34.2	33.2	31.9	33.3	32.4	31.0
	SC	35.0	34.4	33.2	34.4	33.6	32.3	33.8	32.8	31.5	32.9	32.0	30.6
	gpm	9.2	7.2	5.7	8.9	6.9	5.5	8.6	6.7	5.4	8.5	6.6	5.2
	wpd	15.0	9.3	5.8	14.3	8.5	5.5	13.3	8.1	5.2	12.8	7.7	4.9
90	TC	37.6	36.7	35.4	36.7	35.8	34.5	35.9	35.0	33.7	35.0	34.1	32.9
	SC	37.1	36.2	34.9	36.3	35.4	34.1	35.4	34.6	33.3	34.6	33.7	32.5
	gpm	9.5	7.4	6.0	9.3	7.3	5.8	9.1	7.1	5.7	8.8	7.0	5.5
	wpd	16.1	9.9	6.5	15.6	9.5	6.1	14.8	9.1	5.8	14.0	8.7	5.5

4-Row Chilled Water Cooling

EDB	EWT	42				43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	33.3	30.4	27.5	31.5	28.7	25.8	29.7	26.9	24.1	27.9	25.2	22.5	
	SC	22.0	20.7	19.4	21.2	19.9	18.7	20.4	19.2	18.0	19.6	18.5	17.3	
	gpm	8.4	6.2	4.7	8.0	5.8	4.4	7.5	5.5	4.1	7.1	5.1	3.8	
	wpd	8.5	4.6	2.6	7.6	4.0	2.3	6.8	3.6	2.0	6.0	3.1	1.7	
76	TC	33.6	31.0	28.4	31.8	29.3	26.8	30.1	27.7	25.3	28.5	26.1	23.8	
	SC	23.7	22.6	21.4	23.0	21.8	20.7	22.2	21.1	20.0	21.5	20.4	19.4	
	gpm	8.5	6.2	4.8	8.0	5.9	4.5	7.6	5.6	4.3	7.2	5.3	4.0	
	wpd	8.7	4.7	2.8	7.8	4.2	2.5	6.9	3.7	2.2	6.3	3.3	1.9	
78	TC	34.0	31.7	29.3	32.3	30.1	27.9	30.7	28.5	26.5	29.1	27.1	25.2	
	SC	25.5	24.5	23.4	24.8	23.8	22.8	24.1	23.1	22.1	23.3	22.4	21.6	
	gpm	8.6	6.4	5.0	8.2	6.1	4.7	7.7	5.8	4.4	7.4	5.5	4.2	
	wpd	8.8	4.9	3.0	8.1	4.5	2.7	7.2	4.0	2.4	6.5	3.6	2.1	
80	TC	34.4	32.4	30.4	32.9	30.9	29.1	31.3	29.5	27.8	29.8	28.1	26.7	
	SC	27.4	26.4	25.5	26.6	25.7	24.9	25.9	25.1	24.3	25.3	24.5	23.8	
	gpm	8.7	6.5	5.1	8.4	6.2	4.9	7.9	6.0	4.7	7.5	5.7	4.5	
	wpd	9.2	5.2	3.1	8.4	4.7	2.9	7.5	4.4	2.6	6.8	3.9	2.5	
82	TC	35.0	33.2	31.6	33.5	31.8	30.4	32.0	30.6	29.2	30.7	29.4	28.2	
	SC	29.2	28.4	27.6	28.5	27.7	27.0	27.8	27.2	26.5	27.2	26.6	26.0	
	gpm	8.9	6.7	5.3	8.5	6.5	5.1	8.1	6.2	5.0	7.7	5.9	4.7	
	wpd	9.5	5.4	3.4	8.7	5.0	3.1	7.9	4.6	3.0	7.2	4.2	2.7	
84	TC	35.6	34.2	32.8	34.2	32.9	31.8	32.9	31.8	30.7	31.6	30.7	28.2	
	SC	31.1	30.4	29.7	30.4	29.8	29.2	29.8	29.3	28.7	29.2	28.7	27.8	
	gpm	9.0	6.9	5.6	8.7	6.7	5.3	8.3	6.5	5.2	8.0	6.2	4.7	
	wpd	9.8	5.8	3.7	9.0	5.4	3.4	8.2	5.0	3.2	7.6	4.7	2.7	
86	TC	36.4	35.2	34.2	35.1	34.1	33.2	33.9	33.1	30.9	32.9	31.4	30.1	
	SC	33.0	32.4	31.9	32.4	31.9	31.4	31.9	31.4	30.5	31.3	30.9	29.7	
	gpm	9.2	7.1	5.8	8.9	6.9	5.6	8.6	6.7	5.3	8.4	6.4	5.1	
	wpd	10.1	6.1	4.0	9.5	5.8	3.8	8.8	5.4	3.3	8.4	4.9	3.1	
88	TC	37.3	36.5	34.5	36.2	35.5	33.6	35.2	34.0	32.8	34.0	33.2	31.9	
	SC	35.0	34.6	34.0	34.5	34.1	33.2	34.0	33.5	32.4	33.6	32.7	31.5	
	gpm	9.5	7.4	5.8	9.2	7.2	5.6	9.0	6.9	5.6	8.7	6.7	5.4	
	wpd	10.8	6.5	4.0	10.1	6.3	3.8	9.6	5.8	3.7	9.0	5.4	3.5	
90	TC	38.5	37.4	36.3	37.4	36.5	35.5	36.5	35.7	34.6	35.7	34.9	33.8	
	SC	37.1	36.9	35.8	36.9	36.1	35.0	36.1	35.2	34.2	35.2	34.4	33.3	
	gpm	9.8	7.5	6.2	9.5	7.4	6.0	9.3	7.2	5.9	9.0	7.1	5.7	
	wpd	11.5	6.8	4.6	10.8	6.5	4.4	10.3	6.3	4.1	9.8	6.0	3.9	

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	33.2	30.8	28.3	31.5	29.1	26.6	29.8	27.4	25.0	28.1	25.7	23.4
	SC	22.3	21.1	19.9	21.4	20.3	19.1	20.6	19.5	18.4	19.8	18.7	17.7
	gpm	8.4	6.2	4.8	7.9	5.9	4.5	7.5	5.5	4.2	7.1	5.2	3.9
	wpd	8.9	4.9	2.9	7.9	4.3	2.5	7.1	3.8	2.2	6.4	3.4	2.0
76	TC	33.5	31.3	29.0	31.8	29.7	27.5	30.2	28.1	26.0	28.5	26.5	24.5
	SC	24.0	22.9	21.8	23.2	22.1	21.1	22.4	21.4	20.4	21.6	20.6	19.7
	gpm	8.5	6.3	4.9	8.1	6.0	4.6	7.7	5.7	4.3	7.2	5.4	4.1
	wpd	9.1	5.1	3.0	8.2	4.5	2.7	7.4	4.1	2.4	6.6	3.7	2.2
78	TC	33.8	31.8	29.9	32.2	30.3	28.4	30.6	28.8	27.1	29.0	27.3	25.8
	SC	25.7	24.7	23.8	24.9	24.0	23.1	24.1	23.3	22.5	23.4	22.6	21.9
	gpm	8.6	6.4	5.0	8.1	6.1	4.8	7.7	5.8	4.6	7.4	5.5	4.3
	wpd	9.2	5.2	3.2	8.4	4.8	2.9	7.5	4.2	2.6	6.9	3.8	2.4
80	TC	34.1	32.5	30.8	32.6	31.0	29.4	31.1	29.6	28.2	29.6	28.3	27.0
	SC	27.4	26.6	25.8	26.7	25.9	25.1	25.9	25.2	24.5	25.2	24.6	24.0
	gpm	8.6	6.6	5.2	8.3	6.3	5.0	7.9	6.0	4.8	7.5	5.7	4.6
	wpd	9.4	5.4	3.4	8.6	5.0	3.1	7.8	4.5	2.9	7.1	4.1	2.6
82	TC	34.5	33.2	31.8	33.1	31.8	30.6	31.7	30.5	29.4	30.3	29.3	28.4
	SC	29.2	28.5	27.8	28.5	27.8	27.2	27.8	27.2	26.7	27.1	26.6	26.1
	gpm	8.7	6.7	5.4	8.3	6.5	5.2	8.0	6.2	5.0	7.7	5.9	4.8
	wpd	9.5	5.6	3.7	8.8	5.3	3.4	8.1	4.9	3.1	7.4	4.4	2.9
84	TC	35.0	33.9	32.9	33.7	32.7	31.8	32.4	31.5	30.8	31.1	30.4	29.8
	SC	31.0	30.4	29.9	30.3	29.8	29.4	29.7	29.2	28.8	29.1	28.7	28.4
	gpm	8.9	6.8	5.6	8.6	6.6	5.4	8.2	6.3	5.2	7.9	6.1	5.0
	wpd	10.0	5.9	3.9	9.2	5.5	3.7	8.5	5.1	3.4	7.8	4.8	3.2
86	TC	35.7	34.8	34.1	34.4	33.7	33.1	33.2	32.7	32.2	32.2	31.8	30.6
	SC	32.9	32.4	32.0	32.2	31.9	31.5	31.6	31.4	31.1	31.1	30.9	29.9
	gpm	9.0	7.0	5.7	8.8	6.8	5.6	8.4	6.6	5.5	8.1	6.4	5.2
	wpd	10.3	6.2	4.1	9.7	5.9	3.9	8.9	5.5	3.7	8.4	5.2	3.4
88	TC	36.4	35.9	35.4	35.3	35.0	33.8	34.4	33.5	33.0	33.0	32.7	32.2
	SC	34.8	34.5	34.2	34.2	34.0	33.0	33.7	32.8	32.6	32.6	32.5	32.2
	gpm	9.2	7.3	6.0	8.9	7.1	5.7	8.7	6.8	5.6	8.3	6.6	5.5
	wpd	10.8	6.7	4.5	10.0	6.4	4.1	9.5	5.8	3.9	8.8	5.5	3.7
90	TC	37.5	36.6	36.2	36.1	35.8	35.4	35.3	35.1	34.6	34.6	34.3	33.9
	SC	36.9	35.9	35.7	35.7	35.5	35.3	35.3	35.2	34.9	34.9	34.8	34.3
	gpm	9.5	7.5	6.1	9.1	7.2	6.0	9.0	7.1	5.9	8.8	7.0	5.7
	wpd	11.4	7.0	4.8	10.5	6.6	4.5	10.1	6.4	4.3	9.7	6.1	4.1

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.7	23.0	18.8	25.2	21.4	17.2	23.6	19.8	15.7	22.0	18.2	14.3
	SC	16.6	15.1	13.3	15.9	14.4	12.7	15.3	13.8	12.1	14.7	13.2	11.5
	gpm	6.8	4.7	3.2	6.4	4.3	2.9	6.0	4.0	2.7	5.6	3.7	2.4
	wpd	9.8	4.7	2.2	8.7	4.0	1.8	7.8	3.4	1.5	6.6	3.0	1.2
76	TC	26.6	23.3	19.6	25.2	21.9	18.3	23.7	20.4	17.0	22.3	19.0	15.8
	SC	18.1	16.7	15.1	17.5	16.1	14.5	16.9	15.5	14.0	16.3	14.9	13.4
	gpm	6.8	4.7	3.3	6.4	4.5	3.1	6.0	4.2	2.9	5.6	3.9	2.7
	wpd	9.8	4.8	2.4	8.7	4.3	2.1	7.8	3.7	1.8	6.8	3.2	1.5
78	TC	26.8	23.9	20.7	25.4	22.5	19.5	24.0	21.2	18.4	22.8	20.0	17.3
	SC	19.7	18.4	17.0	19.1	17.8	16.4	18.5	17.3	15.9	18.0	16.7	15.4
	gpm	6.8	4.8	3.5	6.4	4.5	3.3	6.1	4.3	3.1	5.8	4.1	2.9
	wpd	9.8	5.0	2.6	8.7	4.4	2.3	7.9	4.0	2.1	7.2	3.6	1.8
80	TC	27.2	24.6	21.8	25.9	23.4	20.8	24.7	22.3	19.7	23.5	21.1	18.8
	SC	21.3	20.2	18.9	20.8	19.6	18.3	20.3	19.1	17.8	19.7	18.6	17.2
	gpm	6.9	5.0	3.7	6.5	4.7	3.5	6.2	4.5	3.3	5.9	4.3	3.2
	wpd	10.2	5.3	3.0	9.2	4.8	2.6	8.3	4.4	2.4	7.6	4.0	2.2
82	TC	27.8	25.6	23.1	26.6	24.5	22.1	25.4	23.3	21.2	24.3	22.3	20.3
	SC	23.1	22.0	20.7	22.5	21.5	20.2	22.0	21.0	19.6	21.6	20.5	19.1
	gpm	7.0	5.2	3.9	6.8	5.0	3.7	6.5	4.7	3.6	6.2	4.5	3.4
	wpd	10.7	5.8	3.3	9.8	5.3	3.0	8.9	4.8	2.7	8.1	4.4	2.5
84	TC	28.4	26.5	24.4	27.3	25.5	23.5	26.2	24.5	22.6	25.2	23.6	21.8
	SC	24.8	23.8	22.6	24.3	23.3	22.1	23.8	22.8	21.5	23.2	22.2	21.0
	gpm	7.2	5.3	4.1	6.9	5.1	3.9	6.6	5.0	3.8	6.4	4.7	3.7
	wpd	11.1	6.1	3.6	10.2	5.6	3.3	9.4	5.3	3.1	8.7	4.8	3.0
86	TC	29.3	27.6	25.7	28.2	26.7	24.9	27.2	25.8	24.1	26.3	25.0	23.4
	SC	26.6	25.6	24.5	26.0	25.1	23.9	25.6	24.7	23.4	25.0	24.1	22.8
	gpm	7.4	5.6	4.4	7.1	5.4	4.2	6.9	5.2	4.1	6.7	5.0	3.9
	wpd	11.8	6.6	4.1	10.9	6.3	3.8	10.2	5.8	3.6	9.6	5.5	3.3
88	TC	30.1	28.8	27.2	29.2	28.0	26.5	28.3	27.2	25.1	27.5	26.5	24.4
	SC	28.3	27.4	26.3	27.8	26.9	25.7	27.3	26.5	24.7	26.8	25.8	24.0
	gpm	7.6	5.9	4.6	7.4	5.7	4.5	7.2	5.5	4.2	7.0	5.3	4.2
	wpd	12.5	7.4	4.5	11.8	7.0	4.3	11.1	6.5	3.8	10.4	6.1	3.7
90	TC	31.2	30.1	28.7	30.4	29.4	27.4	29.7	28.2	26.7	28.6	27.5	26.0
	SC	30.2	29.3	28.0	29.6	28.7	27.0	29.1	27.7	26.3	28.2	27.0	25.6
	gpm	7.9	6.1	4.8	7.7	5.9	4.6	7.6	5.7	4.5	7.3	5.6	4.4
	wpd	13.5	7.9	5.0	12.8	7.6	4.5	12.3	7.0	4.4	11.4	6.6	4.1

3-Row Chilled Water Cooling

EDB	EWT	42						43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	35.8	32.8	29.1	34.0	30.9	27.1	32.1	28.9	25.2	30.2	27.0	23.2			
	SC	21.1	19.8	18.2	20.3	19.0	17.4	19.5	18.1	16.6	18.7	17.4	15.8			
	gpm	9.1	6.6	4.9	8.6	6.2	4.6	8.1	5.8	4.3	7.7	5.5	4.0			
	wpd	14.8	7.9	4.3	13.3	7.0	3.8	11.9	6.1	3.3	10.5	5.3	2.8			
76	TC	35.8	33.0	29.6	34.0	31.2	27.7	32.2	29.4	25.9	30.5	27.5	24.2			
	SC	22.8	21.6	20.1	22.0	20.8	19.3	21.2	20.0	18.6	20.5	19.2	17.9			
	gpm	9.1	6.7	5.0	8.6	6.3	4.7	8.1	5.9	4.3	7.7	5.5	4.1			
	wpd	14.8	8.1	4.4	13.3	7.2	3.9	11.9	6.3	3.4	10.7	5.5	3.0			
78	TC	35.9	33.4	30.2	34.3	31.7	28.6	32.6	29.9	27.0	30.9	28.2	25.4			
	SC	24.5	23.4	22.0	23.8	22.6	21.3	23.0	21.9	20.6	22.3	21.2	20.0			
	gpm	9.1	6.8	5.1	8.7	6.4	4.8	8.2	6.1	4.6	7.8	5.7	4.3			
	wpd	14.8	8.3	4.6	13.5	7.3	4.2	12.1	6.6	3.8	11.0	5.8	3.3			
80	TC	36.2	33.9	31.1	34.6	32.2	29.5	33.0	30.7	28.0	31.3	29.1	26.5			
	SC	26.3	25.3	24.0	25.6	24.5	23.3	24.9	23.9	22.7	24.2	23.2	22.0			
	gpm	9.2	6.9	5.2	8.8	6.6	5.0	8.3	6.2	4.7	7.9	5.9	4.5			
	wpd	15.0	8.5	4.9	13.8	7.7	4.4	12.3	7.0	4.0	11.2	6.3	3.6			
82	TC	36.7	34.6	32.0	35.1	33.0	30.6	33.5	31.5	29.1	31.9	30.0	27.8			
	SC	28.1	27.2	26.1	27.4	26.5	25.4	26.8	25.9	24.8	26.1	25.2	24.2			
	gpm	9.3	7.0	5.4	8.8	6.7	5.1	8.5	6.4	4.9	8.1	6.1	4.7			
	wpd	15.6	8.9	5.2	14.0	8.1	4.7	12.8	7.3	4.3	11.6	6.6	3.9			
84	TC	37.1	35.3	33.0	35.6	33.8	31.6	34.1	32.4	30.3	32.7	31.0	29.1			
	SC	30.0	29.2	28.1	29.3	28.5	27.5	28.7	27.9	26.9	28.0	27.2	26.3			
	gpm	9.4	7.2	5.5	9.0	6.9	5.4	8.6	6.6	5.1	8.3	6.3	4.9			
	wpd	15.8	9.3	5.5	14.5	8.5	5.2	13.3	7.7	4.7	12.3	7.2	4.3			
86	TC	37.7	36.1	34.0	36.2	34.7	32.8	34.8	33.3	31.7	33.4	32.1	30.6			
	SC	31.9	31.1	30.2	31.3	30.5	29.6	30.6	29.9	29.0	30.0	29.3	28.5			
	gpm	9.6	7.3	5.8	9.2	7.0	5.5	8.8	6.7	5.4	8.5	6.5	5.1			
	wpd	16.4	9.7	6.0	15.0	8.9	5.5	14.0	8.1	5.2	12.8	7.5	4.7			
88	TC	38.4	36.9	35.3	37.0	35.7	34.1	35.6	34.5	33.2	34.3	33.4	32.2			
	SC	33.8	33.1	32.3	33.2	32.5	31.7	32.6	32.0	31.2	32.0	31.4	30.6			
	gpm	9.7	7.5	5.9	9.4	7.2	5.8	9.0	7.0	5.6	8.7	6.8	5.5			
	wpd	16.9	10.1	6.3	15.8	9.3	6.0	14.5	8.7	5.6	13.5	8.3	5.3			
90	TC	39.1	37.9	36.6	37.8	36.8	35.6	36.6	35.8	34.7	35.6	34.8	33.8			
	SC	35.8	35.2	34.4	35.2	34.6	33.9	34.6	34.1	33.3	34.1	33.5	32.7			
	gpm	9.9	7.7	6.2	9.6	7.5	6.0	9.2	7.3	5.8	9.0	7.0	5.7			
	wpd	17.5	10.5	6.8	16.4	10.1	6.5	15.3	9.5	6.1	14.5	8.9	5.8			

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	38.3	35.2	31.8	36.4	33.3	29.8	34.5	31.3	27.8	32.6	29.4	25.9												
	SC	22.0	20.6	19.2	21.2	19.8	18.3	20.3	19.0	17.5	19.5	18.1	16.7												
	gpm	9.7	7.1	5.3	9.3	6.8	5.0	8.7	6.3	4.7	8.2	5.9	4.4												
	wpd	11.3	6.1	3.4	10.3	5.5	3.1	9.2	4.8	2.6	8.1	4.2	2.3												
76	TC	38.3	35.4	32.2	36.5	33.5	30.4	34.6	31.7	28.6	32.8	29.8	26.8												
	SC	23.7	22.4	21.0	22.8	21.5	20.2	22.0	20.7	19.4	21.2	19.9	18.7												
	gpm	9.7	7.2	5.4	9.3	6.8	5.1	8.8	6.4	4.8	8.3	6.0	4.5												
	wpd	11.3	6.3	3.5	10.3	5.5	3.1	9.3	4.9	2.8	8.2	4.4	2.5												
78	TC	38.4	35.7	32.9	36.7	33.9	31.2	34.9	32.2	29.4	33.1	30.4	27.7												
	SC	25.3	24.1	22.9	24.5	23.3	22.1	23.7	22.6	21.4	23.0	21.8	20.7												
	gpm	9.7	7.2	5.6	9.3	6.8	5.3	8.8	6.5	5.0	8.4	6.2	4.7												
	wpd	11.3	6.3	3.7	10.3	5.6	3.3	9.3	5.0	3.0	8.5	4.6	2.6												
80	TC	38.7	36.2	33.6	37.0	34.5	31.9	35.2	32.8	30.3	33.5	31.2	28.7												
	SC	27.0	25.9	24.8	26.3	25.2	24.1	25.5	24.4	23.3	24.7	23.7	22.7												
	gpm	9.8	7.4	5.6	9.3	7.0	5.4	8.9	6.6	5.1	8.5	6.3	4.8												
	wpd	11.5	6.5	3.8	10.5	5.9	3.5	9.5	5.3	3.1	8.7	4.8	2.8												
82	TC	39.0	36.7	34.3	37.3	35.1	32.8	35.7	33.5	31.3	34.0	31.9	29.9												
	SC	28.8	27.8	26.7	28.0	27.1	26.0	27.3	26.3	25.4	26.6	25.6	24.8												
	gpm	9.9	7.4	5.8	9.5	7.1	5.6	9.0	6.8	5.3	8.6	6.5	5.0												
	wpd	11.7	6.7	4.0	10.8	6.1	3.7	9.8	5.5	3.3	8.8	5.0	3.1												
84	TC	39.3	37.3	35.2	37.7	35.8	33.8	36.2	34.2	32.4	34.6	32.7	31.0												
	SC	30.5	29.6	28.7	29.8	28.9	28.0	29.1	28.2	27.4	28.4	27.6	26.8												
	gpm	10.0	7.5	5.9	9.6	7.2	5.7	9.2	6.9	5.5	8.7	6.6	5.3												
	wpd	12.0	6.8	4.2	11.0	6.3	3.9	10.1	5.8	3.6	9.2	5.3	3.3												
86	TC	39.7	37.9	36.2	38.2	36.5	34.8	36.7	35.1	33.5	35.2	33.7	32.3												
	SC	32.3	31.5	30.7	31.6	30.8	30.1	30.9	30.2	29.5	30.3	29.6	28.9												
	gpm	10.0	7.7	6.1	9.6	7.4	5.9	9.3	7.1	5.6	9.0	6.8	5.4												
	wpd	12.0	7.1	4.5	11.2	6.5	4.1	10.5	6.0	3.8	9.6	5.6	3.5												
88	TC	40.2	38.7	37.2	38.7	37.3	35.9	37.3	36.0	34.8	35.9	34.8	33.7												
	SC	34.1	33.4	32.7	33.4	32.8	32.1	32.8	32.2	31.6	32.2	31.6	31.1												
	gpm	10.2	7.8	6.2	9.8	7.6	6.1	9.4	7.3	5.9	9.1	7.1	5.6												
	wpd	12.4	7.4	4.7	11.5	6.9	4.5	10.6	6.4	4.1	10.0	6.0	3.8												
90	TC	40.7	39.5	38.3	39.4	38.3	37.1	38.0	37.0	36.1	36.8	36.0	35.2												
	SC	36.0	35.4	34.8	35.3	34.8	34.2	34.7	34.3	33.7	34.1	33.7	33.2												
	gpm	10.3	8.0	6.5	10.0	7.7	6.2	9.6	7.5	6.1	9.3	7.3	5.9												
	wpd	12.8	7.8	5.0	12.0	7.2	4.7	11.2	6.8	4.5	10.5	6.4	4.2												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	38.0	35.5	32.5	36.3	33.6	30.6	34.5	31.8	28.7	32.7	29.9	26.9												
	SC	22.3	21.1	19.8	21.5	20.3	18.9	20.7	19.4	18.0	19.8	18.5	17.2												
	gpm	9.6	7.2	5.5	9.2	6.8	5.2	8.8	6.4	4.8	8.3	6.1	4.6												
	wpd	11.6	6.5	3.8	10.6	5.8	3.4	9.7	5.2	2.9	8.6	4.6	2.6												
76	TC	38.1	35.7	33.0	36.3	33.9	31.2	34.6	32.1	29.4	32.8	30.3	27.7												
	SC	23.9	22.8	21.5	23.1	21.9	20.7	22.3	21.1	19.9	21.4	20.3	19.1												
	gpm	9.6	7.2	5.6	9.2	6.8	5.2	8.8	6.5	5.0	8.3	6.1	4.7												
	wpd	11.6	6.6	3.9	10.6	5.9	3.5	9.7	5.3	3.1	8.8	4.8	2.8												
78	TC	38.2	35.9	33.5	36.5	34.2	31.8	34.8	32.6	30.1	33.1	30.8	28.4												
	SC	25.6	24.5	23.3	24.8	23.7	22.5	23.9	22.9	21.8	23.1	22.1	21.0												
	gpm	9.7	7.3	5.7	9.2	7.0	5.4	8.8	6.6	5.0	8.3	6.3	4.8												
	wpd	11.8	6.7	4.0	10.8	6.1	3.7	9.7	5.5	3.2	8.8	5.0	2.9												
80	TC	38.4	36.3	34.1	36.7	34.7	32.5	35.1	33.1	30.9	33.4	31.4	29.4												
	SC	27.2	26.2	25.2	26.4	25.4	24.4	25.6	24.7	23.7	24.8	23.9	23.0												
	gpm	9.7	7.4	5.7	9.3	7.0	5.5	8.9	6.7	5.2	8.5	6.3	5.0												
	wpd	11.9	6.9	4.1	10.9	6.2	3.8	10.0	5.6	3.5	9.1	5.1	3.1												
82	TC	38.6	36.7	34.8	37.0	35.1	33.2	35.4	33.6	31.8	33.8	32.0	30.3												
	SC	28.9	28.0	27.0	28.1	27.2	26.3	27.3	26.5	25.6	26.6	25.7	25.0												
	gpm	9.8	7.5	5.9	9.4	7.1	5.6	9.0	6.8	5.4	8.6	6.5	5.1												
	wpd	12.1	7.0	4.3	11.1	6.4	3.9	10.1	5.9	3.7	9.2	5.3	3.3												
84	TC	38.8	37.2	35.5	37.3	35.7	34.0	35.7	34.2	32.6	34.2	32.7	31.3												
	SC	30.6	29.8	28.9	29.8	29.1	28.2	29.1	28.3	27.6	28.3	27.6	27.0												
	gpm	9.8	7.5	6.0	9.4	7.2	5.7	9.0	6.9	5.5	8.6	6.6	5.3												
	wpd	12.1	7.1	4.5	11.1	6.6	4.1	10.3	6.0	3.8	9.4	5.5	3.6												
86	TC	39.2	37.7	36.3	37.7	36.3	34.9	36.2	34.9	33.6	34.7	33.5	32.4												
	SC	32.3	31.6	30.9	31.6	30.9	30.2	30.9	30.2	29.6	30.1	29.6	29.0												
	gpm	9.9	7.7	6.1	9.5	7.4	5.9	9.2	7.1	5.7	8.8	6.8	5.5												
	wpd	12.4	7.4	4.8	11.4	6.9	4.4	10.6	6.4	4.0	9.7	5.9	3.7												
88	TC	39.5	38.3	37.1	38.1	37.0	35.9	36.7	35.7	34.7	35.3	34.4	33.6												
	SC	34.1	33.5	32.9	33.4	32.8	32.3	32.7	32.2	31.7	32.0	31.6	31.1												
	gpm	10.0	7.7	6.3	9.7	7.5	6.1	9.3	7.2	5.9	9.0	7.0	5.7												
	wpd	12.6	7.5	5.0	11.8	7.0	4.6	10.9	6.6	4.3	10.1	6.1	4.0												
90	TC	40.0	39.0	38.1	38.6	37.8	36.9	37.3	36.6	35.9	36.0	35.4	34.9												
	SC	35.9	35.4	34.9	35.2	34.7	34.3	34.5	34.1	33.8	33.9	33.6	33.3												
	gpm	10.1	7.9	6.4	9.8	7.7	6.2	9.5	7.4	6.1	9.2	7.2	5.9												
	wpd	13.0	7.9	5.2	12.1	7.4	4.9	11.3	6.9	4.6	10.6	6.5	4.3												

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	30.7	27.7	23.2	29.2	26.0	21.3	27.6	24.3	19.4	26.0	22.5	17.6
	SC	16.2	15.0	13.2	15.6	14.3	12.5	15.0	13.7	11.8	14.3	13.0	11.1
	gpm	7.8	5.6	3.9	7.3	5.3	3.6	7.0	4.9	3.3	6.5	4.5	3.0
	wpd	13.0	6.8	3.3	11.6	6.0	2.7	10.4	5.1	2.3	9.2	4.4	1.9
76	TC	30.8	27.8	23.3	29.2	26.0	21.5	27.6	24.2	19.9	26.0	22.5	18.2
	SC	17.8	16.5	14.8	17.1	15.9	14.1	16.5	15.2	13.5	15.9	14.5	12.8
	gpm	7.8	5.6	3.9	7.4	5.3	3.6	7.0	4.9	3.3	6.6	4.5	3.0
	wpd	13.0	6.8	3.3	11.8	6.0	2.8	10.4	5.1	2.4	9.4	4.4	2.0
78	TC	30.8	27.6	23.6	29.2	26.0	22.1	27.6	24.4	20.5	26.0	22.8	19.1
	SC	19.3	18.0	16.4	18.7	17.4	15.8	18.0	16.8	15.2	17.4	16.2	14.6
	gpm	7.8	5.6	4.0	7.4	5.3	3.7	7.0	5.0	3.5	6.6	4.6	3.2
	wpd	13.0	6.6	3.4	11.8	6.0	3.0	10.4	5.3	2.6	9.4	4.5	2.2
80	TC	30.9	28.1	24.4	29.3	26.6	23.0	27.8	25.1	21.6	26.3	23.6	20.3
	SC	20.7	19.6	18.1	20.1	19.0	17.5	19.5	18.4	16.9	19.0	17.8	16.4
	gpm	7.8	5.7	4.2	7.4	5.3	3.9	7.0	5.0	3.6	6.7	4.7	3.4
	wpd	13.0	7.0	3.7	11.8	6.1	3.2	10.7	5.5	2.8	9.6	4.8	2.5
82	TC	30.7	28.2	25.0	29.3	26.8	23.7	27.9	25.5	22.6	26.6	24.2	21.4
	SC	22.3	21.3	19.9	21.8	20.7	19.4	21.2	20.2	18.9	20.7	19.6	18.3
	gpm	7.8	5.7	4.2	7.4	5.4	4.0	7.0	5.1	3.8	6.8	4.9	3.6
	wpd	13.0	7.0	3.8	11.8	6.3	3.4	10.7	5.6	3.1	9.8	5.1	2.8
84	TC	31.0	28.9	26.0	29.7	27.6	24.9	28.4	26.3	23.7	27.2	25.2	22.7
	SC	24.0	23.0	21.7	23.4	22.5	21.2	22.9	22.0	20.7	22.4	21.4	20.2
	gpm	7.9	5.9	4.4	7.5	5.6	4.2	7.2	5.3	4.0	6.9	5.1	3.9
	wpd	13.3	7.4	4.1	12.1	6.6	3.8	11.1	6.1	3.4	10.2	5.6	3.2
86	TC	31.5	29.5	27.1	30.3	28.4	26.0	29.1	27.2	24.9	27.9	26.2	24.0
	SC	25.7	24.8	23.6	25.2	24.2	23.1	24.6	23.8	22.5	24.1	23.3	22.0
	gpm	7.9	5.9	4.5	7.6	5.7	4.4	7.3	5.5	4.2	7.0	5.3	4.0
	wpd	13.5	7.6	4.4	12.5	7.0	4.1	11.6	6.5	3.8	10.7	6.1	3.4
88	TC	32.2	30.3	28.2	31.0	29.2	27.2	29.9	28.1	26.2	28.7	27.1	25.3
	SC	27.4	26.5	25.4	26.9	26.1	24.9	26.4	25.5	24.4	25.9	25.0	23.9
	gpm	8.2	6.2	4.7	7.9	5.9	4.6	7.6	5.7	4.5	7.3	5.5	4.3
	wpd	14.3	8.1	4.8	13.3	7.6	4.5	12.3	7.0	4.3	11.4	6.5	4.0
90	TC	32.9	31.2	29.3	31.8	30.2	28.4	30.7	29.1	27.5	29.6	28.2	26.8
	SC	29.2	28.3	27.2	28.7	27.7	26.7	28.1	27.3	26.2	27.6	26.7	25.7
	gpm	8.3	6.3	5.0	8.0	6.1	4.8	7.8	5.9	4.7	7.5	5.7	4.5
	wpd	14.8	8.5	5.3	13.8	7.9	5.0	13.0	7.4	4.7	12.1	7.0	4.4

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	40.8	38.1	34.4	39.0	36.2	32.3	37.1	34.3	30.2	35.2	32.2	28.0												
	SC	20.9	19.8	18.2	20.1	19.0	17.4	19.3	18.2	16.5	18.5	17.3	15.7												
	gpm	10.3	7.7	5.8	9.9	7.3	5.5	9.4	7.0	5.1	8.9	6.6	4.7												
	wpd	19.2	10.7	6.1	17.5	9.7	5.3	15.8	8.7	4.6	14.3	7.7	4.0												
76	TC	40.8	38.1	34.4	39.0	36.2	32.5	37.1	34.3	30.4	35.2	32.3	28.4												
	SC	22.6	21.4	19.9	21.8	20.6	19.1	21.0	19.9	18.3	20.2	19.0	17.5												
	gpm	10.3	7.7	5.8	9.9	7.3	5.5	9.4	7.0	5.1	8.9	6.6	4.8												
	wpd	19.2	10.7	6.0	17.5	9.7	5.3	15.8	8.7	4.7	14.3	7.7	4.2												
78	TC	40.8	38.1	34.7	38.9	36.3	32.8	37.1	34.4	30.9	35.2	32.5	28.9												
	SC	24.3	23.1	21.7	23.5	22.4	20.9	22.7	21.6	20.1	21.9	20.8	19.3												
	gpm	10.3	7.7	5.8	9.9	7.3	5.5	9.4	7.0	5.2	8.9	6.6	4.9												
	wpd	19.2	10.7	6.1	17.5	9.7	5.5	15.8	8.7	4.9	14.3	7.7	4.3												
80	TC	41.0	38.5	35.4	39.3	36.7	33.6	37.4	35.0	31.7	35.6	33.2	29.9												
	SC	25.9	24.8	23.5	25.1	24.1	22.8	24.4	23.4	22.0	23.6	22.6	21.3												
	gpm	10.3	7.8	6.0	10.0	7.4	5.7	9.5	7.1	5.4	9.0	6.7	5.1												
	wpd	19.2	11.0	6.5	17.8	9.9	5.8	16.1	9.1	5.2	14.5	8.1	4.6												
82	TC	40.8	38.6	35.6	39.1	36.9	33.9	37.4	35.1	32.2	35.6	33.4	30.5												
	SC	27.6	26.7	25.4	26.9	25.9	24.7	26.2	25.2	24.0	25.4	24.5	23.3												
	gpm	10.3	7.8	6.0	9.9	7.4	5.7	9.5	7.1	5.5	9.0	6.8	5.1												
	wpd	19.2	11.0	6.5	17.5	9.9	5.8	16.1	9.1	5.3	14.5	8.3	4.7												
84	TC	41.1	39.0	36.3	39.4	37.3	34.7	37.8	35.7	33.1	36.1	34.1	31.5												
	SC	29.4	28.5	27.3	28.7	27.8	26.6	28.0	27.1	26.0	27.3	26.4	25.3												
	gpm	10.4	7.9	6.2	10.0	7.6	5.8	9.6	7.2	5.6	9.2	6.9	5.3												
	wpd	19.5	11.2	6.8	17.8	10.3	6.1	16.4	9.3	5.6	15.0	8.5	5.0												
86	TC	41.5	39.5	37.0	39.9	37.9	35.6	38.2	36.3	34.0	36.6	34.8	32.5												
	SC	31.2	30.4	29.3	30.5	29.7	28.7	29.9	29.0	28.0	29.2	28.4	27.4												
	gpm	10.5	8.0	6.2	10.1	7.7	6.0	9.7	7.3	5.8	9.2	7.0	5.5												
	wpd	19.8	11.4	7.0	18.3	10.5	6.5	16.9	9.7	6.0	15.3	8.9	5.3												
88	TC	41.9	40.0	37.9	40.3	38.5	36.5	38.7	37.0	35.0	37.2	35.5	33.6												
	SC	33.1	32.2	31.3	32.4	31.6	30.7	31.7	30.9	30.0	31.1	30.3	29.4												
	gpm	10.7	8.1	6.4	10.2	7.7	6.2	9.8	7.5	5.9	9.4	7.2	5.7												
	wpd	20.4	11.6	7.3	18.6	10.7	6.8	17.2	10.1	6.3	15.8	9.3	5.8												
90	TC	42.4	40.6	38.8	40.8	39.2	37.4	39.3	37.8	36.1	37.9	36.4	34.8												
	SC	34.9	34.2	33.3	34.2	33.5	32.7	33.6	32.9	32.1	33.0	32.3	31.5												
	gpm	10.7	8.2	6.6	10.3	8.0	6.3	10.0	7.7	6.1	9.6	7.3	5.9												
	wpd	20.7	12.1	7.7	18.9	11.4	7.2	17.8	10.5	6.6	16.6	9.7	6.3												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	43.4	40.7	37.2	41.6	38.8	35.1	39.7	36.7	33.0	37.8	34.7	30.9												
	SC	22.0	20.8	19.3	21.1	19.9	18.4	20.3	19.1	17.5	19.5	18.2	16.7												
	gpm	10.9	8.3	6.3	10.5	7.8	5.9	10.1	7.4	5.6	9.6	7.0	5.2												
	wpd	14.3	8.2	4.8	13.3	7.4	4.2	12.2	6.7	3.7	11.0	5.9	3.2												
76	TC	43.4	40.7	37.3	41.5	38.8	35.3	39.7	36.8	33.3	37.8	34.8	31.2												
	SC	23.6	22.4	20.9	22.7	21.6	20.1	21.9	20.7	19.2	21.1	19.9	18.4												
	gpm	11.0	8.3	6.3	10.5	7.8	5.9	10.1	7.4	5.6	9.6	7.1	5.3												
	wpd	14.5	8.2	4.8	13.2	7.4	4.2	12.2	6.7	3.8	11.0	6.0	3.3												
78	TC	43.3	40.7	37.5	41.5	38.8	35.6	39.6	37.0	33.7	37.8	35.0	31.7												
	SC	25.2	24.0	22.6	24.4	23.2	21.8	23.5	22.4	21.0	22.7	21.6	20.2												
	gpm	11.0	8.3	6.3	10.5	7.8	6.0	10.0	7.5	5.7	9.6	7.1	5.3												
	wpd	14.5	8.2	4.8	13.2	7.4	4.4	12.0	6.8	3.9	11.0	6.0	3.4												
80	TC	43.7	41.2	38.2	41.9	39.4	36.3	40.1	37.5	34.5	38.2	35.6	32.6												
	SC	26.8	25.7	24.4	26.0	24.9	23.6	25.2	24.1	22.8	24.4	23.3	22.1												
	gpm	11.1	8.4	6.5	10.6	8.0	6.2	10.2	7.6	5.8	9.6	7.2	5.5												
	wpd	14.7	8.4	5.0	13.5	7.6	4.6	12.4	6.9	4.0	11.2	6.3	3.6												
82	TC	43.5	41.2	38.4	41.7	39.4	36.6	40.0	37.6	34.8	38.2	35.8	33.1												
	SC	28.5	27.5	26.2	27.7	26.7	25.5	26.9	25.9	24.7	26.1	25.1	24.0												
	gpm	11.0	8.4	6.5	10.5	8.0	6.2	10.2	7.6	5.9	9.7	7.2	5.6												
	wpd	14.5	8.4	5.0	13.3	7.6	4.6	12.4	6.9	4.1	11.3	6.3	3.7												
84	TC	43.7	41.5	38.9	42.0	39.8	37.2	40.2	38.1	35.6	38.5	36.4	33.9												
	SC	30.2	29.2	28.1	29.4	28.5	27.4	28.6	27.7	26.7	27.9	27.0	26.0												
	gpm	11.1	8.4	6.5	10.6	8.0	6.3	10.2	7.7	6.0	9.8	7.4	5.7												
	wpd	14.7	8.5	5.2	13.5	7.8	4.8	12.6	7.2	4.4	11.5	6.5	3.9												
86	TC	43.9	41.9	39.6	42.2	40.3	38.0	40.6	38.6	36.4	38.9	37.0	34.8												
	SC	31.9	31.0	30.0	31.1	30.3	29.3	30.4	29.5	28.6	29.7	28.8	27.9												
	gpm	11.1	8.5	6.7	10.7	8.1	6.4	10.3	7.8	6.2	9.9	7.4	5.9												
	wpd	14.9	8.7	5.4	13.7	7.9	4.9	12.8	7.4	4.6	11.7	6.7	4.1												
88	TC	44.2	42.4	40.3	42.5	40.8	38.7	40.9	39.2	37.2	39.3	37.6	35.8												
	SC	33.6	32.8	31.9	32.9	32.1	31.2	32.2	31.4	30.5	31.4	30.7	29.9												
	gpm	11.1	8.6	6.8	10.8	8.3	6.5	10.3	8.0	6.3	9.9	7.6	6.0												
	wpd	14.9	8.8	5.5	13.9	8.2	5.2	12.8	7.6	4.8	11.9	6.9	4.4												
90	TC	44.5	43.0	41.0	42.9	41.4	39.5	41.4	39.8	38.1	39.8	38.4	36.8												
	SC	35.4	34.7	33.8	34.6	34.0	33.1	33.9	33.3	32.5	33.3	32.6	31.9												
	gpm	11.3	8.7	6.9	10.8	8.4	6.7	10.5	8.0	6.4	10.1	7.7	6.2												
	wpd	15.3	9.2	5.8	14.1	8.5	5.4	13.2	7.8	4.9	12.2	7.2	4.6												

5-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	43.2	40.7	37.7	41.4	38.8	35.7	39.7	37.0	33.8	37.8	35.0	31.7				
	SC	22.5	21.3	19.9	21.6	20.4	19.0	20.8	19.6	18.1	19.9	18.7	17.2				
	gpm	10.9	8.2	6.3	10.4	7.9	6.0	10.1	7.5	5.7	9.6	7.1	5.4				
	wpd	15.0	8.5	5.1	13.7	7.8	4.5	12.8	7.1	4.1	11.6	6.4	3.7				
76	TC	43.2	40.7	37.9	41.4	38.9	36.0	39.6	37.0	34.0	37.8	35.1	32.1				
	SC	24.1	22.9	21.5	23.2	22.0	20.7	22.4	21.1	19.8	21.5	20.3	18.9				
	gpm	10.9	8.3	6.4	10.5	7.9	6.1	10.0	7.5	5.7	9.6	7.1	5.5				
	wpd	15.0	8.6	5.2	13.9	7.8	4.6	12.6	7.0	4.1	11.6	6.4	3.7				
78	TC	43.1	40.8	38.1	41.4	39.0	36.2	39.6	37.2	34.4	37.9	35.3	32.5				
	SC	25.6	24.5	23.2	24.8	23.7	22.4	23.9	22.8	21.5	23.1	21.9	20.7				
	gpm	10.9	8.3	6.4	10.5	7.9	6.1	10.0	7.5	5.8	9.6	7.2	5.5				
	wpd	15.0	8.6	5.2	13.9	7.9	4.8	12.6	7.1	4.2	11.6	6.5	3.7				
80	TC	43.5	41.3	38.7	41.8	39.5	36.9	40.0	37.7	35.1	38.3	35.9	33.4				
	SC	27.2	26.2	24.9	26.4	25.3	24.1	25.6	24.5	23.3	24.7	23.6	22.5				
	gpm	11.0	8.3	6.6	10.6	8.0	6.2	10.1	7.7	5.9	9.7	7.2	5.7				
	wpd	15.4	8.8	5.4	14.1	8.1	4.9	13.0	7.4	4.4	11.8	6.6	4.0				
82	TC	43.3	41.2	38.8	41.6	39.4	37.1	39.9	37.7	35.4	38.2	36.0	33.7				
	SC	28.8	27.8	26.7	28.0	27.0	25.9	27.2	26.2	25.1	26.4	25.4	24.3				
	gpm	11.0	8.3	6.6	10.6	8.0	6.3	10.1	7.7	6.0	9.7	7.3	5.7				
	wpd	15.2	8.8	5.4	14.1	8.1	5.0	12.8	7.4	4.5	11.8	6.7	4.0				
84	TC	43.4	41.4	39.3	41.8	39.8	37.7	40.1	38.1	36.0	38.4	36.5	34.4				
	SC	30.5	29.5	28.5	29.6	28.7	27.7	28.8	27.9	26.9	28.1	27.1	26.2				
	gpm	11.0	8.4	6.6	10.6	8.1	6.3	10.1	7.7	6.1	9.7	7.4	5.8				
	wpd	15.2	8.9	5.5	14.1	8.2	5.1	13.0	7.5	4.6	11.9	6.9	4.2				
86	TC	43.6	41.8	39.8	42.0	40.2	38.2	40.3	38.6	36.6	38.7	37.0	35.1				
	SC	32.1	31.2	30.3	31.3	30.5	29.5	30.5	29.7	28.8	29.8	28.9	28.1				
	gpm	11.0	8.5	6.8	10.6	8.1	6.5	10.2	7.8	6.1	9.8	7.5	5.9				
	wpd	15.4	9.1	5.8	14.2	8.4	5.3	13.1	7.7	4.8	12.1	7.1	4.4				
88	TC	43.7	42.2	40.4	42.2	40.6	38.8	40.6	39.0	37.4	39.0	37.5	35.9				
	SC	33.8	33.0	32.1	33.0	32.2	31.4	32.2	31.5	30.7	31.5	30.7	30.0				
	gpm	11.0	8.6	6.8	10.6	8.2	6.6	10.3	7.9	6.3	9.9	7.6	6.1				
	wpd	15.4	9.2	5.9	14.2	8.5	5.4	13.3	7.9	5.0	12.3	7.3	4.6				
90	TC	44.0	42.6	41.0	42.5	41.0	39.6	40.9	39.6	38.2	39.4	38.1	36.8				
	SC	35.5	34.7	34.0	34.7	34.0	33.3	33.9	33.3	32.6	33.2	32.6	32.0				
	gpm	11.1	8.6	6.9	10.8	8.3	6.7	10.4	8.0	6.4	9.9	7.7	6.2				
	wpd	15.6	9.4	6.0	14.6	8.8	5.6	13.5	8.1	5.2	12.4	7.5	4.9				

2-Row Chilled Water Cooling

EDB	EWT	43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	34.5	31.7	28.0	33.0	30.1	26.2	31.4	28.6	24.4	29.9	27.0	22.6						
	SC	15.7	14.6	13.2	15.1	14.0	12.5	14.5	13.4	11.8	13.9	12.8	11.2						
	gpm	8.8	6.4	4.7	8.4	6.1	4.5	7.9	5.8	4.2	7.6	5.5	3.8						
	wpd	16.5	8.7	4.8	15.1	7.9	4.3	13.5	7.2	3.7	12.3	6.5	3.1						
76	TC	34.7	31.9	28.2	33.2	30.3	26.4	31.6	28.7	24.6	30.1	27.1	22.7						
	SC	17.3	16.2	14.8	16.7	15.6	14.1	16.1	15.0	13.4	15.5	14.4	12.7						
	gpm	8.8	6.5	4.7	8.4	6.2	4.5	8.0	5.8	4.2	7.6	5.5	3.9						
	wpd	16.7	8.9	4.8	15.1	8.1	4.3	13.8	7.2	3.7	12.5	6.5	3.2						
78	TC	34.9	32.0	28.2	33.4	30.4	26.5	31.8	28.8	24.6	30.2	27.2	22.8						
	SC	18.9	17.7	16.3	18.3	17.1	15.6	17.7	16.5	14.9	17.1	15.9	14.2						
	gpm	8.8	6.5	4.7	8.5	6.2	4.5	8.1	5.8	4.2	7.6	5.5	3.9						
	wpd	16.7	8.9	4.8	15.4	8.1	4.3	14.0	7.2	3.7	12.5	6.5	3.2						
80	TC	34.9	32.0	28.2	33.4	30.4	26.5	31.8	28.8	24.9	30.2	27.1	23.2						
	SC	20.4	19.3	17.8	19.8	18.7	17.1	19.2	18.0	16.5	18.6	17.4	15.9						
	gpm	8.8	6.5	4.7	8.4	6.2	4.5	8.1	5.9	4.2	7.6	5.5	3.9						
	wpd	16.7	9.2	4.8	15.1	8.1	4.3	14.0	7.4	3.8	12.5	6.5	3.3						
82	TC	34.9	31.9	28.4	33.3	30.3	26.9	31.7	28.8	25.3	30.0	27.3	23.8						
	SC	22.0	20.8	19.4	21.3	20.1	18.8	20.7	19.5	18.2	20.1	19.0	17.6						
	gpm	8.8	6.5	4.8	8.4	6.2	4.5	8.0	5.8	4.3	7.6	5.6	4.0						
	wpd	16.7	8.9	5.0	15.1	8.1	4.4	13.8	7.2	4.0	12.3	6.6	3.4						
84	TC	34.8	32.0	28.9	33.2	30.5	27.5	31.6	29.1	26.0	30.2	27.7	24.7						
	SC	23.5	22.3	21.1	22.8	21.8	20.5	22.2	21.2	20.0	21.7	20.7	19.4						
	gpm	8.8	6.5	4.9	8.4	6.2	4.7	8.0	5.9	4.4	7.6	5.6	4.2						
	wpd	16.7	8.9	5.1	15.1	8.1	4.7	13.8	7.4	4.1	12.5	6.8	3.7						
86	TC	34.8	32.2	29.5	33.3	30.9	28.2	31.9	29.6	26.8	30.5	28.3	25.6						
	SC	25.0	24.0	22.8	24.4	23.4	22.2	23.9	22.9	21.7	23.3	22.4	21.2						
	gpm	8.8	6.5	5.0	8.5	6.3	4.7	8.1	6.0	4.5	7.7	5.7	4.3						
	wpd	16.7	9.2	5.3	15.4	8.5	4.8	14.0	7.8	4.4	12.8	7.0	4.0						
88	TC	35.1	32.7	30.3	33.6	31.5	29.0	32.3	30.2	27.9	31.0	29.0	26.7						
	SC	26.6	25.7	24.5	26.1	25.1	24.0	25.5	24.6	23.5	25.0	24.1	23.1						
	gpm	8.9	6.6	5.1	8.5	6.4	4.9	8.2	6.1	4.7	7.8	5.9	4.5						
	wpd	17.0	9.4	5.6	15.4	8.7	5.1	14.3	7.9	4.7	13.0	7.4	4.4						
90	TC	35.4	33.4	31.2	34.2	32.2	30.1	32.9	31.0	28.9	31.7	29.8	27.8						
	SC	28.3	27.3	26.3	27.8	26.8	25.9	27.3	26.3	25.4	26.7	25.8	24.8						
	gpm	9.0	6.8	5.3	8.6	6.5	5.0	8.3	6.3	4.9	8.0	6.0	4.7						
	wpd	17.3	9.8	6.0	15.9	9.2	5.5	14.8	8.5	5.1	13.8	7.8	4.7						

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	45.8	43.2	40.1	44.0	41.3	38.1	42.1	39.4	36.0	40.2	37.4	33.9
	SC	20.6	19.5	18.2	19.8	18.7	17.4	19.0	17.9	16.6	18.3	17.1	15.7
	gpm	11.6	8.8	6.8	11.1	8.4	6.5	10.7	8.0	6.1	10.2	7.6	5.7
	wpd	24.2	13.8	8.3	22.2	12.6	7.5	20.4	11.4	6.6	18.6	10.3	5.8
76	TC	45.9	43.2	40.2	44.1	41.4	38.1	42.2	39.4	36.1	40.3	37.5	33.9
	SC	22.3	21.2	20.0	21.6	20.4	19.1	20.8	19.6	18.3	20.0	18.9	17.5
	gpm	11.6	8.8	6.8	11.1	8.4	6.4	10.7	8.0	6.1	10.2	7.6	5.7
	wpd	24.2	13.8	8.3	22.2	12.6	7.3	20.4	11.4	6.6	18.6	10.3	5.8
78	TC	46.0	43.3	40.2	44.1	41.4	38.2	42.3	39.5	36.1	40.3	37.5	34.0
	SC	24.1	22.9	21.7	23.3	22.1	20.8	22.5	21.3	20.0	21.7	20.6	19.2
	gpm	11.7	8.8	6.8	11.2	8.4	6.4	10.7	8.0	6.1	10.2	7.6	5.8
	wpd	24.5	13.8	8.3	22.5	12.6	7.3	20.7	11.4	6.6	18.6	10.3	6.0
80	TC	45.9	43.3	40.3	44.1	41.3	38.3	42.2	39.5	36.3	40.3	37.5	34.2
	SC	25.7	24.6	23.4	25.0	23.8	22.6	24.2	23.0	21.7	23.4	22.2	21.0
	gpm	11.6	8.8	6.8	11.2	8.4	6.5	10.7	8.0	6.1	10.2	7.6	5.8
	wpd	24.2	13.8	8.3	22.5	12.6	7.5	20.7	11.4	6.6	18.6	10.3	6.0
82	TC	45.9	43.2	40.4	44.0	41.4	38.5	42.1	39.5	36.6	40.2	37.6	34.7
	SC	27.4	26.3	25.1	26.6	25.5	24.3	25.8	24.7	23.6	25.0	24.0	22.8
	gpm	11.6	8.8	6.8	11.1	8.4	6.5	10.7	8.0	6.2	10.1	7.6	5.8
	wpd	24.2	13.8	8.3	22.2	12.6	7.5	20.4	11.4	6.8	18.3	10.3	6.1
84	TC	45.9	43.3	40.7	44.0	41.5	38.9	42.2	39.7	37.1	40.3	38.0	35.2
	SC	29.1	28.0	26.9	28.3	27.3	26.2	27.5	26.5	25.4	26.8	25.8	24.7
	gpm	11.6	8.8	6.9	11.1	8.5	6.6	10.7	8.1	6.2	10.2	7.7	5.9
	wpd	24.2	13.8	8.5	22.2	12.8	7.7	20.4	11.6	7.0	18.6	10.5	6.3
86	TC	45.9	43.6	41.2	44.1	41.9	39.4	42.4	40.1	37.6	40.6	38.4	35.9
	SC	30.8	29.8	28.7	30.0	29.0	28.0	29.3	28.3	27.3	28.6	27.6	26.6
	gpm	11.6	8.8	7.0	11.1	8.5	6.6	10.7	8.1	6.3	10.3	7.8	6.1
	wpd	24.2	14.0	8.7	22.2	12.8	7.9	20.7	11.9	7.2	18.9	11.0	6.6
88	TC	46.1	44.0	41.7	44.4	42.3	39.9	42.7	40.6	38.3	41.0	38.9	36.7
	SC	32.5	31.6	30.6	31.8	30.9	29.9	31.1	30.2	29.2	30.4	29.5	28.6
	gpm	11.7	8.9	7.0	11.2	8.6	6.7	10.8	8.2	6.5	10.4	7.9	6.2
	wpd	24.5	14.3	8.9	22.5	13.3	8.1	21.0	12.1	7.5	19.5	11.2	7.0
90	TC	46.5	44.4	42.3	44.8	42.7	40.7	43.2	41.1	39.1	41.5	39.5	37.6
	SC	34.3	33.4	32.5	33.6	32.7	31.8	32.9	32.0	31.2	32.2	31.4	30.6
	gpm	11.8	9.0	7.1	11.4	8.6	6.9	10.9	8.3	6.6	10.5	8.0	6.3
	wpd	24.8	14.5	9.1	23.2	13.3	8.5	21.3	12.3	7.9	19.8	11.4	7.2

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	48.6	46.4	43.2	46.8	44.5	41.1	44.9	42.6	39.0	43.1	40.5	36.8												
	SC	21.8	20.9	19.5	21.0	20.1	18.6	20.2	19.2	17.7	19.4	18.4	16.8												
	gpm	12.3	9.4	7.3	11.8	9.0	6.9	11.4	8.7	6.6	10.9	8.2	6.2												
	wpd	18.1	10.6	6.4	16.8	9.8	5.8	15.5	9.0	5.3	14.3	8.1	4.7												
76	TC	48.6	46.4	43.1	46.8	44.6	41.1	44.9	42.6	39.0	43.1	40.5	36.9												
	SC	23.5	22.5	21.1	22.7	21.7	20.3	21.9	20.8	19.4	21.0	20.0	18.5												
	gpm	12.3	9.4	7.3	11.8	9.0	6.9	11.4	8.7	6.6	10.9	8.2	6.2												
	wpd	18.3	10.6	6.4	16.8	9.8	5.8	15.5	9.0	5.3	14.3	8.1	4.7												
78	TC	48.7	46.4	43.1	46.8	44.5	41.1	45.0	42.6	39.1	43.0	40.5	37.0												
	SC	25.1	24.2	22.7	24.3	23.3	21.9	23.5	22.5	21.0	22.7	21.6	20.2												
	gpm	12.3	9.4	7.3	11.8	9.0	6.9	11.4	8.7	6.6	10.8	8.2	6.2												
	wpd	18.3	10.6	6.4	16.8	9.8	5.8	15.5	9.0	5.3	14.1	8.1	4.7												
80	TC	48.6	46.4	43.2	46.8	44.5	41.2	44.9	42.5	39.3	43.0	40.5	37.2												
	SC	26.7	25.8	24.4	25.9	24.9	23.6	25.1	24.1	22.7	24.3	23.2	21.9												
	gpm	12.3	9.4	7.3	11.8	9.0	7.0	11.4	8.6	6.6	10.9	8.2	6.2												
	wpd	18.3	10.6	6.4	16.8	9.8	5.9	15.5	8.8	5.3	14.3	8.1	4.7												
82	TC	48.6	46.5	43.4	46.8	44.6	41.5	44.9	42.7	39.6	43.0	40.7	37.6												
	SC	28.3	27.4	26.1	27.5	26.6	25.3	26.7	25.8	24.5	25.9	24.9	23.6												
	gpm	12.3	9.4	7.3	11.8	9.0	7.0	11.4	8.7	6.7	10.9	8.3	6.3												
	wpd	18.3	10.6	6.4	16.8	9.8	5.9	15.5	9.0	5.4	14.3	8.2	4.8												
84	TC	48.6	46.6	43.7	46.8	44.7	41.8	45.0	42.9	40.0	43.1	41.0	38.1												
	SC	30.0	29.1	27.8	29.1	28.3	27.0	28.4	27.5	26.2	27.6	26.7	25.5												
	gpm	12.3	9.5	7.4	11.9	9.1	7.1	11.4	8.7	6.8	10.9	8.3	6.4												
	wpd	18.3	10.8	6.5	17.0	10.0	6.0	15.5	9.2	5.5	14.3	8.2	4.9												
86	TC	48.7	46.8	44.0	46.9	45.0	42.2	45.1	43.2	40.4	43.4	41.3	38.7												
	SC	31.6	30.8	29.6	30.8	30.0	28.8	30.0	29.2	28.0	29.3	28.4	27.3												
	gpm	12.3	9.5	7.4	11.9	9.1	7.1	11.4	8.7	6.8	11.0	8.4	6.5												
	wpd	18.3	10.8	6.7	17.0	10.0	6.1	15.7	9.2	5.6	14.5	8.4	5.2												
88	TC	48.8	47.0	44.5	47.1	45.3	42.7	45.4	43.5	41.0	43.6	41.7	39.3												
	SC	33.3	32.5	31.4	32.5	31.7	30.6	31.7	30.9	29.9	31.0	30.2	29.2												
	gpm	12.4	9.5	7.5	12.0	9.2	7.2	11.5	8.8	6.9	11.1	8.4	6.6												
	wpd	18.5	10.8	6.8	17.2	10.1	6.3	15.9	9.3	5.8	14.7	8.5	5.3												
90	TC	49.0	47.3	45.0	47.3	45.6	43.3	45.6	43.9	41.7	43.9	42.3	40.1												
	SC	35.0	34.2	33.2	34.2	33.5	32.5	33.5	32.7	31.8	32.7	32.0	31.1												
	gpm	12.3	9.6	7.6	12.0	9.3	7.3	11.5	8.9	7.1	11.1	8.6	6.8												
	wpd	18.3	11.0	6.9	17.2	10.3	6.4	15.9	9.5	6.0	14.7	8.8	5.5												

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	48.3	46.2	43.3	46.5	44.3	41.4	44.8	42.5	39.4	43.0	40.6	37.3
	SC	22.5	21.5	20.2	21.7	20.6	19.3	20.8	19.7	18.4	20.0	18.9	17.4
	gpm	12.2	9.4	7.3	11.8	9.0	7.0	11.3	8.6	6.7	10.8	8.2	6.3
	wpd	18.8	11.1	6.7	17.6	10.1	6.1	16.1	9.2	5.6	14.8	8.5	5.0
76	TC	48.3	46.2	43.4	46.6	44.4	41.4	44.8	42.5	39.4	43.0	40.6	37.4
	SC	24.1	23.1	21.8	23.3	22.2	20.8	22.4	21.3	19.9	21.6	20.4	19.0
	gpm	12.2	9.4	7.3	11.8	9.0	7.0	11.3	8.6	6.6	10.9	8.2	6.3
	wpd	18.8	11.1	6.7	17.6	10.1	6.1	16.1	9.4	5.5	15.0	8.5	5.1
78	TC	48.3	46.2	43.4	46.6	44.4	41.5	44.8	42.5	39.6	43.0	40.6	37.6
	SC	25.7	24.7	23.3	24.8	23.8	22.5	24.0	22.9	21.6	23.1	22.0	20.7
	gpm	12.2	9.4	7.3	11.8	9.0	7.0	11.3	8.6	6.7	10.9	8.2	6.3
	wpd	18.8	11.1	6.7	17.6	10.1	6.2	16.1	9.4	5.6	15.0	8.5	5.1
80	TC	48.3	46.2	43.6	46.5	44.4	41.7	44.8	42.6	39.8	43.0	40.7	37.9
	SC	27.2	26.2	25.0	26.4	25.4	24.1	25.5	24.5	23.2	24.7	23.7	22.4
	gpm	12.2	9.4	7.4	11.8	9.0	7.0	11.3	8.6	6.7	10.9	8.3	6.4
	wpd	18.8	11.1	6.9	17.6	10.3	6.2	16.1	9.4	5.6	15.0	8.6	5.2
82	TC	48.3	46.3	43.7	46.5	44.5	41.9	44.8	42.7	40.0	43.1	40.9	38.2
	SC	28.8	27.8	26.6	28.0	27.0	25.8	27.1	26.1	24.9	26.3	25.3	24.1
	gpm	12.2	9.4	7.4	11.8	9.0	7.0	11.4	8.6	6.8	10.9	8.3	6.5
	wpd	18.8	11.1	6.9	17.6	10.3	6.2	16.3	9.4	5.8	15.0	8.6	5.3
84	TC	48.3	46.4	44.0	46.6	44.7	42.2	44.9	42.9	40.4	43.1	41.1	38.6
	SC	30.4	29.4	28.3	29.5	28.6	27.5	28.7	27.8	26.6	27.9	27.0	25.8
	gpm	12.2	9.4	7.5	11.8	9.0	7.1	11.4	8.7	6.8	11.0	8.3	6.5
	wpd	18.8	11.1	7.0	17.6	10.3	6.4	16.3	9.5	5.9	15.2	8.8	5.3
86	TC	48.3	46.5	44.3	46.7	44.8	42.6	45.0	43.1	40.9	43.3	41.3	39.1
	SC	31.9	31.1	30.0	31.1	30.3	29.2	30.3	29.4	28.4	29.5	28.6	27.6
	gpm	12.2	9.4	7.5	11.9	9.0	7.2	11.4	8.7	6.9	11.0	8.3	6.6
	wpd	18.8	11.1	7.0	17.8	10.3	6.5	16.3	9.5	6.0	15.2	8.8	5.5
88	TC	48.4	46.7	44.7	46.8	45.1	43.0	45.1	43.4	41.3	43.4	41.7	39.7
	SC	33.6	32.7	31.8	32.8	31.9	31.0	32.0	31.2	30.2	31.2	30.4	29.4
	gpm	12.2	9.5	7.5	11.8	9.1	7.2	11.4	8.8	7.0	11.0	8.4	6.7
	wpd	18.8	11.3	7.1	17.6	10.5	6.6	16.3	9.7	6.1	15.2	8.9	5.6
90	TC	48.5	47.0	45.0	46.9	45.4	43.5	45.3	43.7	41.8	43.6	42.1	40.2
	SC	35.2	34.4	33.5	34.4	33.7	32.7	33.6	32.9	32.0	32.8	32.1	31.2
	gpm	12.3	9.5	7.6	11.9	9.2	7.3	11.5	8.8	7.0	11.0	8.6	6.8
	wpd	19.0	11.4	7.3	17.8	10.6	6.7	16.5	9.8	6.2	15.4	9.2	5.8

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	38.7	35.8	32.7	37.2	34.2	30.9	35.6	32.6	29.2	34.0	30.9	27.4												
	SC	15.2	14.1	12.9	14.6	13.5	12.3	14.0	12.9	11.7	13.4	12.3	11.0												
	gpm	9.8	7.3	5.5	9.4	6.9	5.2	9.1	6.6	4.9	8.6	6.2	4.6												
	wpd	20.6	11.4	6.5	19.1	10.2	5.8	17.6	9.4	5.1	15.9	8.3	4.5												
76	TC	38.7	35.9	32.9	37.2	34.3	31.2	35.7	32.7	29.4	34.1	31.1	27.6												
	SC	16.8	15.7	14.5	16.2	15.1	13.9	15.6	14.5	13.3	15.0	13.9	12.6												
	gpm	9.8	7.3	5.6	9.4	7.0	5.3	9.1	6.6	5.0	8.6	6.3	4.7												
	wpd	20.6	11.4	6.6	18.8	10.4	6.0	17.6	9.4	5.3	15.9	8.5	4.7												
78	TC	38.9	36.0	33.1	37.4	34.5	31.4	35.8	32.9	29.6	34.3	31.3	27.9												
	SC	18.4	17.2	16.1	17.8	16.7	15.5	17.2	16.1	14.9	16.6	15.5	14.2												
	gpm	9.9	7.3	5.6	9.4	7.0	5.3	9.1	6.7	5.0	8.7	6.3	4.7												
	wpd	20.9	11.4	6.6	19.1	10.4	6.0	17.6	9.6	5.3	16.2	8.5	4.7												
80	TC	39.1	36.2	33.2	37.6	34.6	31.5	36.0	33.1	29.8	34.4	31.4	27.9												
	SC	20.0	18.8	17.7	19.4	18.2	17.1	18.8	17.6	16.4	18.2	17.0	15.7												
	gpm	9.9	7.3	5.6	9.5	7.0	5.3	9.1	6.7	5.0	8.8	6.4	4.7												
	wpd	20.9	11.6	6.6	19.4	10.4	6.1	17.6	9.6	5.5	16.5	8.7	4.7												
82	TC	39.3	36.3	33.3	37.7	34.7	31.5	36.1	33.1	29.8	34.5	31.5	27.9												
	SC	21.6	20.4	19.3	20.9	19.8	18.6	20.3	19.2	17.9	19.7	18.6	17.3												
	gpm	9.9	7.3	5.6	9.5	7.0	5.3	9.1	6.7	5.0	8.7	6.4	4.7												
	wpd	21.2	11.6	6.8	19.4	10.7	6.1	17.9	9.6	5.5	16.2	8.7	4.8												
84	TC	39.3	36.3	33.3	37.7	34.7	31.5	36.1	33.0	29.8	34.5	31.3	28.2												
	SC	23.1	21.9	20.8	22.5	21.3	20.1	21.9	20.7	19.5	21.2	20.1	18.9												
	gpm	9.9	7.3	5.6	9.6	7.0	5.3	9.1	6.7	5.0	8.7	6.3	4.7												
	wpd	21.2	11.6	6.8	19.7	10.7	6.1	17.9	9.6	5.5	16.2	8.5	4.8												
86	TC	39.3	36.3	33.3	37.7	34.6	31.7	36.0	33.0	30.2	34.4	31.4	28.6												
	SC	24.6	23.4	22.3	24.0	22.8	21.7	23.4	22.2	21.1	22.8	21.7	20.6												
	gpm	9.9	7.3	5.6	9.5	7.0	5.3	9.1	6.7	5.1	8.7	6.4	4.8												
	wpd	21.2	11.6	6.8	19.4	10.4	6.1	17.9	9.6	5.6	16.2	8.7	5.0												
88	TC	39.2	36.2	33.6	37.6	34.7	32.1	35.9	33.2	30.7	34.4	31.7	29.2												
	SC	26.1	25.0	23.9	25.5	24.4	23.4	24.9	23.8	22.8	24.3	23.3	22.3												
	gpm	9.9	7.3	5.6	9.5	7.0	5.4	9.1	6.8	5.2	8.7	6.4	4.9												
	wpd	21.2	11.6	6.8	19.4	10.4	6.3	17.9	9.8	5.8	16.2	8.7	5.1												
90	TC	39.1	36.4	34.0	37.6	35.0	32.6	36.0	33.6	31.4	34.6	32.2	30.0												
	SC	27.6	26.6	25.6	27.0	26.0	25.1	26.5	25.5	24.6	25.9	25.0	24.0												
	gpm	9.9	7.3	5.7	9.5	7.0	5.5	9.1	6.8	5.3	8.8	6.5	5.0												
	wpd	21.2	11.6	7.0	19.4	10.7	6.5	17.6	10.0	6.0	16.5	9.2	5.5												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	51.2	48.5	45.7	49.3	46.6	43.7	47.4	44.6	41.7	45.5	42.7	39.8												
	SC	20.4	19.2	18.1	19.6	18.4	17.3	18.8	17.6	16.5	18.0	16.9	15.7												
	gpm	13.0	9.8	7.7	12.5	9.5	7.3	12.0	9.1	7.0	11.5	8.6	6.7												
	wpd	30.1	17.2	10.7	27.9	16.1	9.7	25.8	14.8	8.9	23.8	13.3	8.1												
76	TC	51.2	48.5	45.7	49.3	46.6	43.8	47.5	44.7	41.8	45.6	42.8	39.8												
	SC	22.1	20.9	19.8	21.3	20.2	19.0	20.5	19.4	18.2	19.7	18.6	17.5												
	gpm	13.0	9.8	7.7	12.5	9.5	7.4	12.0	9.1	7.0	11.5	8.7	6.7												
	wpd	30.1	17.2	10.5	27.9	16.1	9.9	25.8	14.8	8.9	23.8	13.5	8.1												
78	TC	51.2	48.5	45.8	49.4	46.6	43.9	47.5	44.8	41.9	45.6	42.8	39.9												
	SC	23.8	22.7	21.5	23.0	21.9	20.8	22.2	21.1	20.0	21.4	20.3	19.2												
	gpm	13.0	9.8	7.7	12.6	9.4	7.4	12.1	9.1	7.1	11.5	8.7	6.7												
	wpd	30.1	17.2	10.7	28.3	15.8	9.9	26.2	14.8	9.1	23.8	13.5	8.1												
80	TC	51.3	48.6	45.8	49.4	46.7	43.9	47.6	44.8	41.9	45.7	42.9	39.9												
	SC	25.5	24.4	23.2	24.7	23.6	22.4	23.9	22.8	21.7	23.2	22.0	20.9												
	gpm	13.0	9.9	7.7	12.5	9.5	7.4	12.1	9.1	7.1	11.6	8.7	6.7												
	wpd	30.1	17.5	10.7	27.9	16.1	9.9	26.2	14.8	9.1	24.2	13.5	8.1												
82	TC	51.3	48.7	45.8	49.5	46.7	43.9	47.6	44.8	41.9	45.7	42.8	39.9												
	SC	27.2	26.1	24.9	26.4	25.3	24.1	25.6	24.5	23.3	24.8	23.7	22.6												
	gpm	13.0	9.9	7.7	12.5	9.5	7.4	12.0	9.1	7.0	11.6	8.7	6.7												
	wpd	30.1	17.5	10.7	27.9	16.1	9.9	25.8	14.8	8.9	24.2	13.5	8.1												
84	TC	51.4	48.6	45.8	49.5	46.7	43.9	47.6	44.8	42.0	45.6	42.8	40.1												
	SC	28.9	27.8	26.6	28.1	27.0	25.8	27.3	26.2	25.1	26.5	25.4	24.3												
	gpm	13.0	9.9	7.7	12.5	9.5	7.4	12.0	9.1	7.1	11.5	8.7	6.8												
	wpd	30.1	17.5	10.7	27.9	16.1	9.9	25.8	14.8	9.1	23.8	13.5	8.3												
86	TC	51.3	48.6	45.9	49.4	46.7	44.1	47.5	44.8	42.2	45.6	42.9	40.4												
	SC	30.5	29.4	28.3	29.7	28.6	27.6	28.9	27.9	26.8	28.2	27.1	26.1												
	gpm	13.0	9.9	7.7	12.5	9.5	7.4	12.0	9.1	7.1	11.5	8.7	6.8												
	wpd	30.1	17.5	10.7	27.9	16.1	9.9	25.8	14.8	9.1	23.8	13.5	8.3												
88	TC	51.2	48.6	46.1	49.4	46.8	44.3	47.5	45.0	42.5	45.6	43.2	40.8												
	SC	32.2	31.1	30.1	31.4	30.4	29.3	30.6	29.6	28.6	29.9	28.9	27.9												
	gpm	13.0	9.9	7.7	12.5	9.5	7.5	12.0	9.1	7.2	11.5	8.8	6.9												
	wpd	30.1	17.5	10.7	27.9	16.1	10.1	25.8	14.8	9.3	23.8	13.8	8.5												
90	TC	51.3	48.8	46.5	49.4	47.1	44.7	47.6	45.3	43.0	45.8	43.5	41.2												
	SC	33.9	32.8	31.9	33.1	32.1	31.2	32.4	31.4	30.5	31.6	30.7	29.8												
	gpm	13.0	9.9	7.8	12.5	9.6	7.6	12.1	9.2	7.3	11.6	8.8	7.0												
	wpd	30.1	17.5	11.0	27.9	16.4	10.3	26.2	15.0	9.5	24.2	14.0	8.7												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	54.1	51.9	49.2	52.3	50.1	47.2	50.4	48.1	45.2	48.5	46.2	43.0												
	SC	21.8	20.8	19.6	20.9	20.0	18.7	20.1	19.1	17.9	19.3	18.3	17.0												
	gpm	13.7	10.5	8.3	13.2	10.2	8.0	12.7	9.8	7.6	12.3	9.3	7.3												
	wpd	22.5	13.3	8.2	21.1	12.4	7.6	19.4	11.5	6.9	18.1	10.5	6.4												
76	TC	54.1	52.0	49.2	52.3	50.1	47.2	50.4	48.2	45.2	48.5	46.2	43.1												
	SC	23.4	22.4	21.3	22.6	21.6	20.4	21.7	20.8	19.6	20.9	20.0	18.7												
	gpm	13.7	10.5	8.3	13.2	10.2	8.0	12.7	9.8	7.7	12.3	9.3	7.3												
	wpd	22.5	13.3	8.2	21.1	12.4	7.6	19.4	11.5	7.1	18.1	10.5	6.4												
78	TC	54.1	52.0	49.2	52.3	50.1	47.2	50.5	48.2	45.2	48.6	46.2	43.1												
	SC	25.0	24.1	22.9	24.2	23.3	22.1	23.4	22.4	21.2	22.6	21.6	20.3												
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.6	12.3	9.3	7.3												
	wpd	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	6.9	18.1	10.5	6.4												
80	TC	54.2	52.0	49.3	52.3	50.1	47.2	50.5	48.2	45.2	48.6	46.2	43.1												
	SC	26.7	25.7	24.5	25.8	24.9	23.7	25.0	24.1	22.8	24.2	23.2	22.0												
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.6	12.3	9.3	7.3												
	wpd	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	6.9	18.1	10.5	6.4												
82	TC	54.2	52.0	49.2	52.3	50.1	47.3	50.5	48.2	45.2	48.5	46.2	43.2												
	SC	28.3	27.3	26.2	27.5	26.5	25.3	26.6	25.7	24.5	25.8	24.8	23.6												
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.7	12.3	9.3	7.3												
	wpd	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	7.1	18.1	10.5	6.4												
84	TC	54.1	51.9	49.3	52.3	50.1	47.3	50.4	48.1	45.4	48.5	46.2	43.4												
	SC	29.9	28.9	27.8	29.1	28.1	27.0	28.2	27.3	26.1	27.4	26.5	25.3												
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.7	12.3	9.4	7.3												
	wpd	22.5	13.3	8.4	21.1	12.4	7.6	19.7	11.5	7.1	18.1	10.6	6.4												
86	TC	54.1	51.9	49.4	52.2	50.1	47.5	50.4	48.2	45.6	48.5	46.3	43.6												
	SC	31.5	30.5	29.5	30.7	29.7	28.6	29.8	28.9	27.9	29.0	28.2	27.1												
	gpm	13.7	10.5	8.4	13.2	10.1	8.0	12.8	9.8	7.7	12.3	9.4	7.4												
	wpd	22.5	13.3	8.4	21.1	12.2	7.6	19.7	11.5	7.1	18.1	10.6	6.5												
88	TC	54.1	52.0	49.6	52.2	50.2	47.7	50.4	48.3	45.8	48.6	46.5	43.9												
	SC	33.1	32.2	31.2	32.3	31.4	30.4	31.5	30.6	29.6	30.7	29.8	28.8												
	gpm	13.7	10.5	8.4	13.2	10.2	8.0	12.8	9.8	7.7	12.3	9.4	7.4												
	wpd	22.5	13.3	8.4	21.1	12.4	7.8	19.7	11.5	7.2	18.3	10.6	6.7												
90	TC	54.1	52.2	49.9	52.3	50.4	48.1	50.5	48.6	46.2	48.7	46.8	44.4												
	SC	34.7	33.9	32.9	33.9	33.1	32.1	33.1	32.3	31.3	32.4	31.6	30.6												
	gpm	13.7	10.5	8.4	13.2	10.2	8.1	12.8	9.9	7.8	12.3	9.5	7.5												
	wpd	22.5	13.3	8.5	21.1	12.6	7.9	19.7	11.7	7.4	18.3	10.8	6.8												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	53.5	51.7	49.1	51.8	49.9	47.2	50.0	48.1	45.2	48.2	46.2	43.2												
	SC	22.5	21.6	20.4	21.6	20.8	19.5	20.8	19.9	18.6	19.9	19.0	17.7												
	gpm	13.5	10.5	8.3	13.1	10.1	7.9	12.7	9.7	7.7	12.2	9.3	7.2												
	wpd	23.1	13.9	8.6	21.7	13.0	7.9	20.3	11.9	7.4	18.8	10.9	6.6												
76	TC	53.5	51.8	49.2	51.8	50.0	47.3	50.1	48.2	45.3	48.3	46.3	43.3												
	SC	24.1	23.2	22.0	23.2	22.4	21.1	22.4	21.5	20.2	21.5	20.6	19.3												
	gpm	13.6	10.5	8.3	13.1	10.1	8.0	12.7	9.7	7.7	12.2	9.4	7.3												
	wpd	23.3	13.9	8.6	21.7	13.0	8.1	20.3	11.9	7.4	18.8	11.1	6.7												
78	TC	53.6	51.9	49.3	51.8	50.1	47.4	50.1	48.2	45.4	48.3	46.3	43.4												
	SC	25.6	24.8	23.6	24.8	24.0	22.7	24.0	23.1	21.8	23.1	22.2	20.9												
	gpm	13.6	10.5	8.3	13.1	10.1	8.0	12.7	9.8	7.7	12.2	9.4	7.3												
	wpd	23.3	13.9	8.8	21.7	13.0	8.1	20.3	12.1	7.4	18.8	11.1	6.7												
80	TC	53.6	51.9	49.3	51.8	50.1	47.4	50.1	48.2	45.4	48.3	46.3	43.4												
	SC	27.2	26.4	25.2	26.4	25.5	24.3	25.5	24.7	23.4	24.7	23.8	22.5												
	gpm	13.6	10.5	8.3	13.1	10.1	8.0	12.7	9.8	7.7	12.2	9.4	7.3												
	wpd	23.3	13.9	8.8	21.7	13.0	8.1	20.3	12.1	7.4	18.8	11.1	6.7												
82	TC	53.6	51.9	49.3	51.8	50.1	47.4	50.1	48.2	45.5	48.3	46.3	43.6												
	SC	28.8	28.0	26.7	27.9	27.1	25.8	27.1	26.2	25.0	26.3	25.4	24.1												
	gpm	13.6	10.5	8.3	13.2	10.1	8.0	12.7	9.8	7.7	12.2	9.4	7.4												
	wpd	23.3	13.9	8.6	21.9	13.0	8.1	20.3	12.1	7.4	18.8	11.1	6.9												
84	TC	53.5	51.8	49.4	51.8	50.1	47.5	50.1	48.3	45.6	48.3	46.4	43.7												
	SC	30.3	29.5	28.3	29.5	28.7	27.5	28.7	27.8	26.6	27.8	27.0	25.7												
	gpm	13.6	10.5	8.3	13.1	10.1	8.0	12.7	9.8	7.7	12.2	9.4	7.4												
	wpd	23.3	13.9	8.8	21.7	13.0	8.1	20.3	12.1	7.4	18.8	11.1	6.9												
86	TC	53.5	51.8	49.5	51.8	50.1	47.7	50.1	48.4	45.9	48.3	46.5	43.9												
	SC	31.9	31.1	30.0	31.1	30.3	29.1	30.2	29.4	28.3	29.4	28.6	27.4												
	gpm	13.6	10.5	8.3	13.1	10.1	8.1	12.7	9.8	7.7	12.2	9.5	7.5												
	wpd	23.3	13.9	8.8	21.7	13.0	8.2	20.3	12.1	7.5	18.8	11.3	7.0												
88	TC	53.5	51.9	49.7	51.8	50.2	47.9	50.1	48.5	46.1	48.4	46.7	44.3												
	SC	33.5	32.7	31.6	32.6	31.9	30.8	31.8	31.0	30.0	31.0	30.2	29.1												
	gpm	13.5	10.5	8.4	13.0	10.1	8.1	12.7	9.8	7.8	12.3	9.5	7.5												
	wpd	23.1	13.9	8.9	21.4	13.0	8.2	20.3	12.1	7.7	19.0	11.3	7.0												
90	TC	53.5	52.1	49.9	51.8	50.4	48.2	50.1	48.6	46.4	48.4	46.9	44.7												
	SC	35.0	34.3	33.3	34.2	33.5	32.5	33.4	32.7	31.7	32.6	31.9	30.9												
	gpm	13.5	10.6	8.4	13.1	10.2	8.1	12.7	9.9	7.9	12.2	9.5	7.5												
	wpd	23.1	14.1	8.9	21.7	13.1	8.4	20.3	12.3	7.8	18.8	11.4	7.1												

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	43.3	40.3	37.3	41.7	38.6	35.6	40.1	37.1	34.0	38.5	35.4	32.3												
	SC	14.7	13.5	12.4	14.1	12.9	11.8	13.5	12.4	11.2	12.9	11.8	10.7												
	gpm	10.9	8.2	6.3	10.5	7.8	6.0	10.2	7.5	5.7	9.8	7.2	5.5												
	wpd	25.5	14.3	8.5	23.8	13.0	7.8	22.2	12.1	7.0	20.6	11.1	6.5												
76	TC	43.2	40.2	37.2	41.6	38.6	35.6	40.0	37.0	33.9	38.5	35.4	32.3												
	SC	16.3	15.1	14.0	15.7	14.5	13.4	15.1	14.0	12.9	14.5	13.4	12.3												
	gpm	10.9	8.2	6.3	10.5	7.8	6.0	10.1	7.5	5.7	9.7	7.2	5.5												
	wpd	25.5	14.3	8.5	23.8	13.0	7.8	21.9	12.1	7.0	20.3	11.1	6.5												
78	TC	43.2	40.2	37.2	41.6	38.6	35.7	40.0	37.1	34.0	38.4	35.4	32.4												
	SC	17.8	16.7	15.6	17.2	16.1	15.0	16.6	15.5	14.4	16.0	14.9	13.9												
	gpm	10.9	8.2	6.3	10.5	7.8	6.0	10.1	7.5	5.7	9.7	7.2	5.5												
	wpd	25.5	14.3	8.5	23.8	13.0	7.8	21.9	12.1	7.0	20.3	11.1	6.5												
80	TC	43.4	40.4	37.4	41.8	38.8	35.8	40.2	37.2	34.2	38.6	35.6	32.6												
	SC	19.4	18.3	17.2	18.8	17.7	16.6	18.2	17.1	16.0	17.6	16.5	15.4												
	gpm	11.0	8.2	6.3	10.5	7.9	6.1	10.2	7.5	5.8	9.7	7.2	5.5												
	wpd	25.9	14.3	8.5	23.8	13.3	7.9	22.2	12.1	7.2	20.3	11.1	6.5												
82	TC	43.5	40.6	37.6	41.9	39.0	36.0	40.4	37.4	34.4	38.7	35.7	32.7												
	SC	21.0	19.9	18.8	20.4	19.3	18.2	19.8	18.7	17.6	19.2	18.1	17.0												
	gpm	11.0	8.2	6.3	10.6	7.9	6.1	10.2	7.6	5.8	9.8	7.2	5.5												
	wpd	25.9	14.6	8.5	24.2	13.3	7.9	22.5	12.3	7.2	20.6	11.1	6.5												
84	TC	43.7	40.7	37.7	42.1	39.1	36.1	40.5	37.5	34.5	38.9	35.8	32.8												
	SC	22.6	21.5	20.4	22.0	20.9	19.8	21.4	20.3	19.2	20.8	19.7	18.6												
	gpm	11.1	8.2	6.4	10.7	7.9	6.1	10.2	7.6	5.8	9.9	7.3	5.6												
	wpd	26.2	14.6	8.7	24.5	13.5	7.9	22.5	12.3	7.2	20.9	11.4	6.6												
86	TC	43.8	40.8	37.8	42.2	39.2	36.1	40.6	37.5	34.4	39.0	35.9	32.7												
	SC	24.2	23.1	21.9	23.6	22.4	21.3	23.0	21.8	20.7	22.4	21.2	20.1												
	gpm	11.1	8.3	6.4	10.7	7.9	6.1	10.3	7.6	5.8	9.9	7.3	5.5												
	wpd	26.6	14.8	8.7	24.5	13.5	7.9	22.8	12.3	7.2	20.9	11.4	6.5												
88	TC	43.9	40.8	37.7	42.3	39.2	36.0	40.6	37.5	34.4	39.0	35.8	32.8												
	SC	25.7	24.6	23.4	25.1	24.0	22.8	24.5	23.4	22.2	23.9	22.7	21.6												
	gpm	11.1	8.3	6.4	10.7	7.9	6.1	10.3	7.6	5.8	9.9	7.3	5.6												
	wpd	26.6	14.8	8.7	24.5	13.5	7.9	22.8	12.3	7.2	20.9	11.4	6.6												
90	TC	43.8	40.8	37.7	42.2	39.1	36.1	40.6	37.4	34.6	38.9	35.7	33.1												
	SC	27.3	26.1	24.9	26.6	25.5	24.3	26.0	24.9	23.8	25.4	24.2	23.3												
	gpm	11.1	8.2	6.4	10.7	7.9	6.1	10.2	7.6	5.9	9.9	7.2	5.6												
	wpd	26.6	14.6	8.7	24.5	13.5	7.9	22.5	12.3	7.4	20.9	11.1	6.6												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	56.8	54.1	51.3	55.0	52.2	49.3	53.1	50.3	47.4	51.2	48.3	45.4												
	SC	20.1	18.9	17.8	19.3	18.1	17.0	18.5	17.4	16.2	17.7	16.6	15.4												
	gpm	14.3	11.0	8.7	14.0	10.6	8.3	13.4	10.2	8.0	13.0	9.8	7.7												
	wpd	36.6	21.6	13.5	35.0	20.1	12.3	32.3	18.6	11.4	30.1	17.2	10.5												
76	TC	56.8	54.1	51.3	55.0	52.2	49.3	53.1	50.2	47.3	51.2	48.3	45.3												
	SC	21.8	20.6	19.5	21.0	19.9	18.7	20.2	19.1	17.9	19.4	18.3	17.2												
	gpm	14.3	11.0	8.7	13.9	10.6	8.3	13.4	10.1	8.0	13.0	9.8	7.7												
	wpd	36.6	21.6	13.5	34.6	20.1	12.3	32.3	18.3	11.4	30.1	17.2	10.5												
78	TC	56.7	54.1	51.3	54.9	52.1	49.3	53.1	50.2	47.3	51.1	48.3	45.4												
	SC	23.5	22.4	21.2	22.7	21.6	20.4	21.9	20.8	19.7	21.1	20.0	18.9												
	gpm	14.3	11.0	8.7	13.8	10.6	8.3	13.4	10.2	8.0	13.0	9.8	7.7												
	wpd	36.6	21.6	13.5	34.2	20.1	12.3	32.3	18.6	11.4	30.1	17.2	10.5												
80	TC	56.8	54.1	51.4	55.0	52.2	49.4	53.1	50.3	47.4	51.2	48.3	45.4												
	SC	25.2	24.1	23.0	24.4	23.3	22.2	23.6	22.5	21.4	22.9	21.7	20.6												
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.4	10.2	8.0	13.0	9.8	7.7												
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5												
82	TC	56.9	54.2	51.4	55.0	52.3	49.5	53.1	50.4	47.5	51.2	48.4	45.4												
	SC	26.9	25.8	24.7	26.1	25.0	23.9	25.3	24.2	23.1	24.6	23.4	22.3												
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.4	10.2	8.0	13.0	9.8	7.7												
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5												
84	TC	56.9	54.2	51.4	55.1	52.3	49.5	53.2	50.4	47.5	51.3	48.4	45.4												
	SC	28.6	27.5	26.4	27.8	26.7	25.6	27.1	25.9	24.8	26.3	25.2	24.0												
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.4	10.2	8.0	13.0	9.8	7.7												
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5												
86	TC	57.0	54.3	51.4	55.1	52.3	49.5	53.2	50.4	47.4	51.3	48.4	45.4												
	SC	30.3	29.2	28.1	29.5	28.4	27.3	28.8	27.6	26.5	28.0	26.8	25.7												
	gpm	14.5	11.0	8.7	13.9	10.6	8.4	13.4	10.2	8.0	13.0	9.8	7.7												
	wpd	37.5	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.4	30.1	17.2	10.5												
88	TC	57.0	54.2	51.4	55.1	52.3	49.5	53.2	50.3	47.5	51.2	48.4	45.6												
	SC	32.0	30.9	29.7	31.2	30.1	29.0	30.4	29.3	28.2	29.6	28.5	27.4												
	gpm	14.5	11.0	8.7	13.9	10.6	8.4	13.4	10.2	8.1	13.0	9.8	7.7												
	wpd	37.5	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.6	30.1	17.2	10.5												
90	TC	56.9	54.2	51.4	55.0	52.3	49.5	53.1	50.3	47.6	51.1	48.4	45.8												
	SC	33.7	32.5	31.4	32.9	31.8	30.7	32.1	31.0	29.9	31.3	30.2	29.2												
	gpm	14.4	11.0	8.7	13.9	10.6	8.4	13.4	10.2	8.1	13.0	9.8	7.7												
	wpd	37.0	21.6	13.5	34.6	20.1	12.6	32.3	18.6	11.6	30.1	17.2	10.7												

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	60.0	57.8	55.5	58.1	55.9	53.5	56.3	54.0	51.5	54.4	52.0	49.5
	SC	21.7	20.7	19.7	20.9	19.9	18.9	20.0	19.1	18.0	19.2	18.2	17.2
	gpm	15.2	11.7	9.4	14.7	11.4	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.6	10.6	26.1	15.5	9.8	24.3	14.3	9.2	22.8	13.3	8.4
76	TC	59.9	57.7	55.4	58.1	55.9	53.5	56.2	53.9	51.5	54.3	52.0	49.4
	SC	23.3	22.3	21.3	22.5	21.5	20.5	21.7	20.7	19.7	20.8	19.9	18.8
	gpm	15.2	11.7	9.4	14.7	11.4	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.6	10.6	25.9	15.5	9.8	24.3	14.3	9.0	22.8	13.3	8.4
78	TC	59.9	57.7	55.4	58.1	55.8	53.5	56.2	53.9	51.5	54.3	51.9	49.4
	SC	24.9	24.0	23.0	24.1	23.1	22.1	23.3	22.3	21.3	22.5	21.5	20.5
	gpm	15.2	11.7	9.4	14.7	11.4	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.6	10.6	25.9	15.5	9.8	24.3	14.3	9.2	22.8	13.3	8.4
80	TC	59.9	57.8	55.5	58.1	55.9	53.5	56.2	53.9	51.5	54.3	52.0	49.5
	SC	28.2	27.2	26.3	27.4	26.4	25.4	26.5	25.6	24.6	25.7	24.8	23.8
	gpm	15.2	11.7	9.4	14.7	11.4	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.6	10.6	26.1	15.5	9.8	24.3	14.3	9.2	22.8	13.3	8.4
82	TC	59.9	57.7	55.4	58.1	55.9	53.5	56.2	53.9	51.5	54.3	52.0	49.4
	SC	29.8	28.8	27.9	29.0	28.0	27.0	28.2	27.2	26.2	27.4	26.4	25.4
	gpm	15.2	11.7	9.3	14.7	11.4	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.4	10.5	26.1	15.5	9.8	24.3	14.3	9.2	22.8	13.3	8.4
84	TC	59.9	57.7	55.4	58.1	55.9	53.5	56.2	53.9	51.5	54.3	52.0	49.4
	SC	29.8	28.8	27.9	29.0	28.0	27.0	28.2	27.2	26.2	27.4	26.4	25.4
	gpm	15.2	11.7	9.3	14.7	11.4	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.4	10.5	26.1	15.5	9.8	24.3	14.3	9.2	22.8	13.3	8.4
86	TC	59.9	57.7	55.4	58.1	55.8	53.4	56.2	53.9	51.5	54.3	51.9	49.5
	SC	31.4	30.5	29.5	30.6	29.6	28.7	29.8	28.8	27.8	29.0	28.0	27.0
	gpm	15.2	11.7	9.3	14.7	11.3	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.4	10.5	26.1	15.3	9.8	24.3	14.3	9.2	22.8	13.3	8.4
88	TC	59.9	57.6	55.4	58.0	55.8	53.5	56.1	53.8	51.5	54.2	51.9	49.6
	SC	33.0	32.1	31.1	32.2	31.2	30.3	31.4	30.4	29.5	30.6	29.6	28.7
	gpm	15.2	11.7	9.3	14.7	11.3	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.4	10.5	26.1	15.3	9.8	24.3	14.3	9.2	22.8	13.2	8.4
90	TC	59.8	57.6	55.5	57.9	55.8	53.6	56.1	53.9	51.7	54.2	52.0	49.8
	SC	34.6	33.7	32.8	33.8	32.9	32.0	33.0	32.1	31.2	32.2	31.3	30.4
	gpm	15.2	11.7	9.4	14.7	11.3	9.0	14.2	10.9	8.7	13.8	10.5	8.4
	wpd	27.8	16.4	10.6	25.9	15.3	9.8	24.3	14.3	9.2	22.8	13.3	8.5

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	58.9	57.3	55.0	57.2	55.5	53.1	55.5	53.7	51.1	53.7	51.8	49.1
	SC	22.4	21.6	20.5	21.6	20.8	19.6	20.7	19.9	18.7	19.9	19.0	17.8
	gpm	15.0	11.7	9.3	14.5	11.2	9.0	14.1	10.9	8.6	13.6	10.5	8.3
	wpd	28.3	17.1	10.9	26.5	15.9	10.1	25.0	15.0	9.4	23.3	13.9	8.6
76	TC	59.0	57.4	55.1	57.3	55.6	53.2	55.5	53.8	51.3	53.7	51.9	49.3
	SC	24.0	23.2	22.1	23.2	22.4	21.2	22.3	21.5	20.4	21.5	20.7	19.5
	gpm	15.0	11.7	9.3	14.5	11.2	9.0	14.1	10.9	8.7	13.6	10.6	8.3
	wpd	28.3	17.1	10.9	26.5	15.9	10.1	25.0	15.0	9.5	23.3	14.1	8.8
78	TC	59.0	57.4	55.1	57.3	55.7	53.3	55.6	53.8	51.4	53.8	52.0	49.4
	SC	25.6	24.8	23.7	24.8	24.0	22.9	23.9	23.1	22.0	23.1	22.3	21.1
	gpm	15.0	11.6	9.3	14.6	11.3	9.0	14.1	10.9	8.7	13.6	10.6	8.3
	wpd	28.3	16.9	10.9	26.7	16.1	10.3	25.0	15.0	9.5	23.3	14.1	8.8
80	TC	59.0	57.4	55.2	57.3	55.7	53.3	55.6	53.9	51.5	53.8	52.0	49.5
	SC	27.2	26.4	25.3	26.3	25.5	24.4	25.5	24.7	23.6	24.7	23.8	22.7
	gpm	15.0	11.6	9.3	14.6	11.2	9.0	14.1	10.9	8.7	13.7	10.6	8.3
	wpd	28.3	16.9	10.9	26.7	15.9	10.1	25.0	15.0	9.5	23.5	14.1	8.8
82	TC	59.1	57.5	55.2	57.3	55.7	53.4	55.6	53.9	51.5	53.8	52.1	49.5
	SC	28.8	28.0	26.9	27.9	27.1	26.0	27.1	26.3	25.2	26.2	25.4	24.3
	gpm	15.0	11.7	9.3	14.6	11.2	9.0	14.1	11.0	8.7	13.7	10.6	8.3
	wpd	28.3	17.1	10.9	26.7	15.9	10.1	25.0	15.2	9.5	23.5	14.1	8.8
84	TC	59.1	57.5	55.3	57.3	55.7	53.4	55.6	53.9	51.5	53.8	52.1	49.5
	SC	30.3	29.6	28.5	29.5	28.7	27.6	28.6	27.8	26.7	27.8	27.0	25.8
	gpm	15.0	11.7	9.3	14.6	11.2	9.0	14.1	10.9	8.7	13.7	10.6	8.3
	wpd	28.3	17.1	10.9	26.7	15.9	10.3	25.0	15.0	9.5	23.5	14.1	8.8
86	TC	59.0	57.5	55.3	57.3	55.7	53.4	55.6	53.9	51.5	53.8	52.0	49.6
	SC	31.9	31.1	30.1	31.0	30.3	29.2	30.2	29.4	28.3	29.4	28.5	27.5
	gpm	14.9	11.7	9.3	14.6	11.2	9.0	14.1	10.9	8.7	13.7	10.5	8.3
	wpd	28.0	17.1	10.9	26.7	15.9	10.3	25.0	15.0	9.5	23.5	13.9	8.8
88	TC	59.0	57.5	55.3	57.3	55.7	53.5	55.5	53.9	51.7	53.8	52.0	49.7
	SC	33.4	32.7	31.7	32.6	31.8	30.8	31.8	31.0	30.0	30.9	30.1	29.1
	gpm	14.9	11.7	9.3	14.4	11.3	9.0	14.1	10.9	8.7	13.7	10.6	8.4
	wpd	28.0	17.1	10.9	26.2	16.1	10.3	25.0	15.0	9.5	23.5	14.1	8.9
90	TC	58.9	57.5	55.4	57.2	55.7	53.6	55.5	53.9	51.8	53.8	52.1	50.0
	SC	35.0	34.3	33.3	34.1	33.4	32.4	33.3	32.6	31.6	32.5	31.8	30.8
	gpm	14.9	11.7	9.4	14.5	11.3	9.0	14.0	10.9	8.8	13.7	10.6	8.4
	wpd	28.0	17.1	11.1	26.5	16.1	10.3	24.7	15.0	9.7	23.5	14.1	8.9

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	48.0	44.9	41.9	46.4	43.3	40.2	44.8	41.7	38.6	43.1	40.0	36.9
	SC	15.7	14.6	13.5	15.1	14.0	12.9	14.5	13.4	12.3	13.9	12.8	11.7
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.4	8.5	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	9.8	27.7	15.4	9.2	25.5	14.0	8.3
78	TC	48.0	44.9	41.8	46.4	43.3	40.2	44.8	41.6	38.5	43.1	40.0	36.9
	SC	17.3	16.2	15.1	16.7	15.6	14.5	16.1	15.0	13.9	15.5	14.4	13.3
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.3	8.4	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	9.8	27.3	15.1	9.2	25.5	14.0	8.3
80	TC	47.9	44.9	41.8	46.3	43.3	40.2	44.7	41.6	38.5	43.1	40.0	36.9
	SC	18.9	17.8	16.7	18.3	17.2	16.1	17.7	16.6	15.5	17.1	16.0	14.9
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.3	8.4	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	9.8	27.3	15.1	8.9	25.5	14.0	8.3
82	TC	48.0	45.0	41.9	46.4	43.4	40.3	44.8	41.7	38.7	43.2	40.1	37.0
	SC	20.5	19.4	18.2	19.9	18.8	17.7	19.3	18.2	17.1	18.7	17.6	16.5
	gpm	12.2	9.1	7.0	11.7	8.8	6.8	11.4	8.5	6.5	10.9	8.1	6.2
	wpd	31.8	17.9	10.7	29.5	16.5	10.0	27.7	15.4	9.2	25.5	14.0	8.3
84	TC	48.1	45.1	42.1	46.6	43.5	40.5	45.0	41.9	38.8	43.3	40.3	37.2
	SC	22.1	21.0	19.8	21.5	20.4	19.3	20.9	19.8	18.7	20.3	19.2	18.1
	gpm	12.2	9.1	7.1	11.8	8.8	6.8	11.4	8.5	6.5	11.0	8.2	6.2
	wpd	31.8	17.9	10.9	29.9	16.7	10.0	27.7	15.4	9.2	25.9	14.3	8.3
86	TC	48.3	45.3	42.3	46.7	43.7	40.6	45.1	42.0	39.0	43.5	40.4	37.3
	SC	23.7	22.5	21.4	23.1	21.9	20.8	22.5	21.4	20.2	21.9	20.8	19.7
	gpm	12.2	9.2	7.1	11.8	8.8	6.8	11.4	8.5	6.6	11.0	8.2	6.3
	wpd	32.2	18.2	10.9	29.9	16.7	10.0	28.0	15.6	9.4	25.9	14.3	8.5
88	TC	48.5	45.4	42.4	46.9	43.8	40.7	45.2	42.2	39.0	43.6	40.5	37.3
	SC	25.3	24.1	23.0	24.7	23.5	22.4	24.1	22.9	21.8	23.5	22.3	21.2
	gpm	12.2	9.2	7.2	11.9	8.9	6.9	11.4	8.5	6.6	11.1	8.2	6.3
	wpd	32.2	18.2	11.1	30.3	17.0	10.2	28.0	15.6	9.4	26.2	14.6	8.5
90	TC	48.6	45.5	42.4	47.0	43.9	40.7	45.3	42.2	39.0	43.7	40.5	37.3
	SC	26.8	25.7	24.5	26.2	25.1	23.9	25.6	24.5	23.3	25.0	23.9	22.7
	gpm	12.3	9.2	7.1	11.9	8.9	6.9	11.5	8.5	6.6	11.1	8.2	6.3
	wpd	32.6	18.2	10.9	30.3	17.0	10.2	28.4	15.6	9.4	26.2	14.6	8.5

3-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	62.8	60.0	57.2	60.9	58.1	55.2	59.0	56.1	53.2	57.1	54.1	51.1				
	SC	21.5	20.4	19.2	20.7	19.6	18.4	19.9	18.8	17.6	19.2	18.0	16.8				
	gpm	15.9	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.5	11.0	8.6				
	wpd	45.2	26.5	16.6	42.5	24.8	15.6	39.5	23.2	14.5	37.5	21.6	13.3				
78	TC	62.7	60.0	57.1	60.8	58.0	55.1	58.9	56.1	53.1	57.0	54.1	51.1				
	SC	23.2	22.1	20.9	22.4	21.3	20.1	21.6	20.5	19.3	20.9	19.7	18.6				
	gpm	15.9	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.5	10.9	8.6				
	wpd	45.2	26.5	16.6	42.5	24.8	15.6	39.5	23.2	14.5	37.5	21.3	13.3				
80	TC	62.7	59.9	57.1	60.8	58.0	55.1	58.9	56.0	53.1	56.9	54.1	51.1				
	SC	24.9	23.8	22.6	24.1	23.0	21.9	23.3	22.2	21.1	22.5	21.4	20.3				
	gpm	15.9	12.2	9.6	15.3	11.8	9.3	14.9	11.4	9.0	14.4	10.9	8.6				
	wpd	45.2	26.5	16.6	42.1	24.8	15.6	39.5	23.2	14.5	37.0	21.3	13.3				
82	TC	62.7	60.0	57.2	60.8	58.0	55.2	58.9	56.1	53.2	57.0	54.1	51.2				
	SC	26.6	25.5	24.4	25.8	24.7	23.6	25.0	23.9	22.8	24.3	23.1	22.0				
	gpm	15.9	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.4	11.0	8.6				
	wpd	45.2	26.5	16.6	42.5	24.8	15.6	39.5	23.2	14.5	37.0	21.6	13.3				
84	TC	62.7	60.0	57.2	60.9	58.1	55.3	59.0	56.2	53.3	57.0	54.2	51.2				
	SC	28.3	27.2	26.1	27.5	26.4	25.3	26.8	25.7	24.5	26.0	24.9	23.8				
	gpm	15.9	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.4	11.0	8.7				
	wpd	45.2	26.5	16.6	42.5	24.8	15.6	39.9	23.2	14.5	37.0	21.6	13.5				
86	TC	62.8	60.1	57.2	60.9	58.2	55.3	59.0	56.2	53.3	57.1	54.2	51.3				
	SC	30.0	28.9	27.8	29.2	28.1	27.0	28.5	27.4	26.2	27.7	26.6	25.5				
	gpm	15.9	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.5	11.0	8.7				
	wpd	45.2	26.5	16.6	42.5	24.8	15.6	39.9	23.2	14.5	37.5	21.6	13.5				
88	TC	62.8	60.1	57.2	60.9	58.2	55.3	59.0	56.2	53.3	57.1	54.2	51.2				
	SC	31.7	30.6	29.5	31.0	29.8	28.7	30.2	29.1	27.9	29.4	28.3	27.1				
	gpm	15.9	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.5	11.0	8.7				
	wpd	45.2	26.5	16.6	42.5	24.8	15.6	39.9	23.2	14.5	37.5	21.6	13.5				
90	TC	62.9	60.1	57.2	61.0	58.2	55.2	59.1	56.2	53.2	57.1	54.2	51.2				
	SC	33.4	32.3	31.2	32.7	31.5	30.4	31.9	30.7	29.6	31.1	30.0	28.8				
	gpm	16.0	12.2	9.6	15.4	11.8	9.3	14.9	11.4	9.0	14.5	11.0	8.7				
	wpd	45.6	26.5	16.6	42.5	24.8	15.6	39.9	23.2	14.5	37.5	21.6	13.5				

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	66.0	63.9	61.5	64.2	62.0	59.6	62.3	60.0	57.6	60.4	58.1	55.5
	SC	23.2	22.3	21.2	22.4	21.4	20.4	21.6	20.6	19.6	20.7	19.8	18.7
	gpm	16.7	12.9	10.4	16.2	12.6	10.1	15.8	12.2	9.7	15.3	11.8	9.4
	wpd	33.5	20.1	13.0	31.8	19.0	12.2	30.0	17.9	11.3	28.0	16.8	10.6
78	TC	66.0	63.8	61.4	64.1	61.9	59.5	62.3	60.0	57.5	60.4	58.0	55.5
	SC	24.8	23.9	22.9	24.0	23.0	22.0	23.2	22.2	21.2	22.4	21.4	20.4
	gpm	16.7	12.9	10.4	16.2	12.6	10.0	15.8	12.2	9.7	15.3	11.7	9.4
	wpd	33.5	20.1	13.0	31.8	19.0	12.0	30.0	17.9	11.3	28.0	16.6	10.6
80	TC	65.9	63.7	61.4	64.1	61.9	59.4	62.2	59.9	57.5	60.3	58.0	55.5
	SC	26.4	25.5	24.5	25.6	24.7	23.7	24.8	23.8	22.8	24.0	23.0	22.0
	gpm	16.7	12.9	10.4	16.2	12.6	10.0	15.8	12.2	9.7	15.3	11.7	9.4
	wpd	33.5	19.9	13.0	31.8	19.0	12.0	30.0	17.9	11.3	28.0	16.6	10.6
82	TC	65.9	63.7	61.4	64.1	61.9	59.5	62.2	59.9	57.5	60.3	58.0	55.5
	SC	28.1	27.1	26.1	27.2	26.3	25.3	26.4	25.5	24.5	25.6	24.7	23.7
	gpm	16.7	12.9	10.4	16.2	12.6	10.0	15.8	12.2	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	19.0	12.0	30.0	17.9	11.3	28.0	16.6	10.5
84	TC	65.9	63.7	61.4	64.1	61.8	59.5	62.2	60.0	57.5	60.3	58.0	55.5
	SC	29.7	28.7	27.8	28.9	27.9	26.9	28.1	27.1	26.1	27.2	26.3	25.3
	gpm	16.7	12.9	10.4	16.2	12.5	10.0	15.8	12.2	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.0	30.0	17.9	11.3	28.0	16.6	10.5
86	TC	65.9	63.7	61.4	64.1	61.8	59.5	62.2	59.9	57.5	60.3	58.0	55.4
	SC	31.3	30.4	29.4	30.5	29.5	28.6	29.7	28.7	27.7	28.9	27.9	26.9
	gpm	16.7	12.9	10.4	16.2	12.5	10.1	15.8	12.1	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.2	30.0	17.6	11.3	28.0	16.6	10.5
88	TC	65.9	63.7	61.4	64.1	61.8	59.4	62.2	59.9	57.4	60.3	57.9	55.4
	SC	32.9	32.0	31.0	32.1	31.2	30.2	31.3	30.3	29.4	30.5	29.5	28.5
	gpm	16.7	12.9	10.4	16.2	12.5	10.0	15.8	12.1	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.0	30.0	17.6	11.3	28.0	16.6	10.5
90	TC	65.9	63.7	61.4	64.1	61.8	59.4	62.2	59.8	57.4	60.2	57.8	55.4
	SC	34.5	33.6	32.6	33.7	32.8	31.8	32.9	31.9	31.0	32.1	31.1	30.2
	gpm	16.7	12.9	10.4	16.2	12.5	10.0	15.8	12.1	9.7	15.3	11.7	9.3
	wpd	33.5	19.9	13.0	31.8	18.8	12.0	30.0	17.6	11.3	28.0	16.6	10.5

5-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	64.7	63.0	61.1	63.0	61.2	59.3	61.2	59.5	57.4	59.4	57.6	55.5				
	SC	23.9	23.1	22.2	23.1	22.3	21.3	22.2	21.4	20.5	21.4	20.6	19.6				
	gpm	16.4	12.8	10.3	15.9	12.4	10.0	15.5	12.1	9.7	15.0	11.7	9.4				
	wpd	34.0	20.5	13.3	32.0	19.2	12.6	30.4	18.4	11.9	28.5	17.1	11.1				
78	TC	64.7	63.1	61.2	63.0	61.3	59.4	61.2	59.5	57.5	59.5	57.7	55.6				
	SC	25.5	24.7	23.8	24.7	23.9	23.0	23.8	23.0	22.1	23.0	22.2	21.2				
	gpm	16.4	12.8	10.4	16.0	12.4	10.0	15.5	12.0	9.7	15.0	11.7	9.4				
	wpd	34.0	20.5	13.5	32.3	19.5	12.6	30.4	18.2	11.9	28.5	17.3	11.1				
80	TC	64.8	63.2	61.3	63.0	61.4	59.5	61.3	59.6	57.6	59.5	57.7	55.7				
	SC	27.1	26.3	25.5	26.3	25.5	24.6	25.4	24.6	23.7	24.6	23.8	22.9				
	gpm	16.4	12.8	10.4	16.0	12.4	10.0	15.5	12.1	9.7	15.1	11.7	9.4				
	wpd	34.0	20.5	13.5	32.3	19.5	12.6	30.4	18.4	11.9	28.8	17.3	11.1				
82	TC	64.8	63.2	61.4	63.1	61.4	59.5	61.3	59.6	57.6	59.5	57.8	55.7				
	SC	28.7	27.9	27.1	27.9	27.1	26.2	27.0	26.2	25.3	26.2	25.4	24.4				
	gpm	16.4	12.8	10.4	16.0	12.4	10.1	15.5	12.1	9.7	15.1	11.7	9.4				
	wpd	34.0	20.8	13.5	32.3	19.5	12.8	30.4	18.4	11.9	28.8	17.1	11.1				
84	TC	64.8	63.2	61.4	63.1	61.5	59.6	61.3	59.6	57.7	59.6	57.8	55.7				
	SC	30.3	29.5	28.6	29.4	28.7	27.8	28.6	27.8	26.9	27.8	26.9	26.0				
	gpm	16.4	12.8	10.4	16.0	12.4	10.1	15.5	12.1	9.7	15.1	11.7	9.4				
	wpd	33.7	20.8	13.5	32.3	19.5	12.8	30.4	18.4	11.9	28.8	17.1	11.1				
86	TC	64.8	63.2	61.5	63.1	61.5	59.6	61.3	59.7	57.7	59.6	57.8	55.8				
	SC	31.8	31.1	30.2	31.0	30.2	29.4	30.2	29.4	28.5	29.3	28.5	27.6				
	gpm	16.4	12.8	10.4	16.0	12.5	10.1	15.6	12.1	9.7	15.1	11.7	9.4				
	wpd	33.7	20.8	13.5	32.3	19.7	12.8	30.7	18.4	11.9	28.8	17.3	11.1				
88	TC	64.8	63.2	61.4	63.0	61.5	59.6	61.3	59.6	57.7	59.5	57.8	55.8				
	SC	33.4	32.7	31.8	32.6	31.8	30.9	31.7	31.0	30.1	30.9	30.1	29.2				
	gpm	16.4	12.8	10.4	15.9	12.5	10.1	15.5	12.1	9.7	15.1	11.7	9.4				
	wpd	33.7	20.8	13.5	32.0	19.7	12.8	30.4	18.4	11.9	28.8	17.3	11.1				
90	TC	64.7	63.2	61.5	63.0	61.4	59.6	61.3	59.6	57.8	59.5	57.8	55.8				
	SC	35.0	34.2	33.4	34.1	33.4	32.5	33.3	32.5	31.6	32.5	31.7	30.8				
	gpm	16.4	12.8	10.4	15.9	12.5	10.1	15.5	12.1	9.7	15.1	11.7	9.5				
	wpd	33.7	20.8	13.7	32.0	19.7	12.8	30.1	18.4	11.9	28.8	17.3	11.3				

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	26.9	23.6	20.6	25.4	22.4	19.4	24.0	21.2	17.2	22.7	20.1	16.1
	SC	23.2	21.5	19.4	22.5	20.8	18.7	21.9	20.0	17.0	21.2	19.3	15.9
	gpm	6.8	4.8	3.5	6.5	4.5	3.2	6.1	4.3	2.9	5.8	4.0	2.7
	wpd	6.6	3.3	1.7	6.0	2.9	1.5	5.3	2.6	1.2	4.8	2.3	1.0
76	TC	28.1	25.4	22.8	26.8	24.3	20.9	25.6	23.3	19.8	24.5	21.7	18.7
	SC	25.6	24.0	22.1	25.0	23.2	20.6	24.3	22.6	19.5	23.6	21.4	18.5
	gpm	7.1	5.1	3.9	6.8	4.9	3.6	6.5	4.7	3.3	6.2	4.4	3.2
	wpd	7.2	3.8	2.1	6.6	3.4	1.8	6.0	3.2	1.6	5.6	2.8	1.4
78	TC	29.7	27.4	24.3	28.5	26.4	23.3	27.5	24.9	22.3	26.2	23.9	21.2
	SC	28.2	26.6	24.0	27.4	25.7	23.0	26.8	24.6	22.0	25.9	23.6	20.9
	gpm	7.5	5.5	4.1	7.3	5.4	3.9	6.9	5.0	3.8	6.6	4.8	3.6
	wpd	8.1	4.4	2.4	7.6	4.1	2.2	6.9	3.7	2.1	6.3	3.3	1.8
80	TC	31.3	29.0	26.6	30.4	28.1	25.6	29.2	27.1	24.6	28.3	26.2	23.6
	SC	30.6	28.7	26.3	29.8	27.8	25.3	28.9	26.8	24.3	27.9	25.8	23.3
	gpm	7.9	5.8	4.5	7.7	5.7	4.3	7.4	5.5	4.2	7.1	5.3	3.9
	wpd	8.9	4.9	2.9	8.4	4.6	2.7	7.9	4.4	2.5	7.2	4.0	2.2
82	TC	33.1	31.2	28.8	32.2	30.2	27.9	31.2	29.3	26.9	30.2	28.3	25.9
	SC	32.7	30.8	28.5	31.7	29.9	27.6	30.8	28.9	26.6	29.8	27.9	25.6
	gpm	8.4	6.3	4.9	8.1	6.2	4.7	7.9	5.9	4.6	7.7	5.7	4.4
	wpd	10.1	5.7	3.4	9.5	5.4	3.2	8.9	5.0	3.0	8.4	4.6	2.8
84	TC	35.1	33.3	31.1	34.1	32.4	30.1	33.1	31.4	29.1	32.2	30.5	28.2
	SC	34.6	32.9	30.7	33.7	32.0	29.7	32.7	31.0	28.8	31.8	30.1	27.8
	gpm	8.9	6.8	5.2	8.6	6.5	5.0	8.4	6.4	4.9	8.1	6.2	4.7
	wpd	11.4	6.6	3.9	10.6	6.2	3.7	10.1	5.9	3.4	9.5	5.4	3.2
86	TC	37.0	35.4	33.3	36.0	34.5	32.3	35.1	33.5	31.4	34.1	32.6	30.4
	SC	36.5	35.0	32.8	35.6	34.1	31.9	34.6	33.1	31.0	33.7	32.2	30.0
	gpm	9.4	7.2	5.6	9.2	7.0	5.4	8.9	6.8	5.3	8.7	6.6	5.1
	wpd	12.7	7.4	4.5	12.0	7.1	4.3	11.4	6.6	4.0	10.8	6.3	3.8
88	TC	38.9	37.4	35.4	38.0	36.5	34.5	37.0	35.6	33.5	36.1	34.6	32.6
	SC	38.5	37.0	34.9	37.5	36.0	34.0	36.6	35.1	33.1	35.6	34.2	32.2
	gpm	9.9	7.6	6.0	9.6	7.4	5.8	9.4	7.2	5.7	9.2	7.0	5.5
	wpd	14.0	8.2	5.2	13.3	7.9	4.9	12.7	7.4	4.6	12.0	7.1	4.4
90	TC	40.9	39.4	37.5	39.9	38.4	36.6	39.0	37.5	35.6	38.0	36.5	34.7
	SC	40.4	38.9	37.0	39.4	37.9	36.1	38.5	37.0	35.2	37.5	36.1	34.3
	gpm	10.3	8.0	6.3	10.1	7.8	6.2	9.9	7.6	6.0	9.6	7.4	5.8
	wpd	15.4	9.1	5.7	14.7	8.8	5.4	14.0	8.2	5.2	13.3	7.9	4.9

3-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	34.2	30.3	26.8	32.3	28.6	25.3	30.3	27.0	20.6	28.5	25.6	19.2				
	SC	27.8	25.9	24.0	26.9	25.1	23.3	26.0	24.4	20.3	25.2	23.6	18.9				
	gpm	8.6	6.1	4.6	8.1	5.8	4.2	7.6	5.5	3.5	7.2	5.1	3.2				
	wpd	5.9	3.0	1.7	5.3	2.7	1.4	4.6	2.4	1.0	4.1	2.1	0.8				
76	TC	35.4	32.1	29.2	33.6	30.7	25.1	31.9	29.3	23.8	30.4	26.1	22.4				
	SC	30.5	28.8	27.2	29.6	28.1	24.8	28.8	27.4	23.5	28.1	25.8	22.2				
	gpm	9.0	6.5	5.0	8.5	6.2	4.2	8.1	5.9	4.0	7.7	5.3	3.8				
	wpd	6.4	3.3	2.0	5.8	3.1	1.4	5.1	2.8	1.3	4.7	2.2	1.2				
78	TC	36.7	34.1	29.3	35.2	32.8	28.0	33.8	30.0	26.8	32.4	28.8	25.5				
	SC	33.2	31.7	28.9	32.4	31.1	27.7	31.7	29.7	26.5	31.0	28.5	25.2				
	gpm	9.3	6.9	5.0	8.9	6.6	4.7	8.5	6.1	4.5	8.2	5.8	4.3				
	wpd	6.9	3.8	2.0	6.3	3.5	1.8	5.8	2.9	1.6	5.4	2.7	1.5				
80	TC	38.4	36.3	32.0	37.0	33.8	30.8	35.8	32.6	29.7	33.9	31.4	28.4				
	SC	36.0	34.7	31.6	35.4	33.4	30.5	34.6	32.2	29.3	33.5	31.1	28.1				
	gpm	9.7	7.4	5.4	9.4	6.8	5.2	9.0	6.6	5.0	8.5	6.4	4.8				
	wpd	7.5	4.3	2.3	7.0	3.7	2.2	6.5	3.5	2.0	5.8	3.2	1.8				
82	TC	40.3	37.4	34.8	38.5	36.3	33.6	37.4	35.2	32.4	36.3	34.0	31.2				
	SC	38.9	37.0	34.3	38.0	35.9	33.2	37.0	34.8	32.0	35.8	33.6	30.8				
	gpm	10.2	7.6	5.9	9.7	7.4	5.6	9.5	7.1	5.5	9.2	6.9	5.2				
	wpd	8.3	4.5	2.8	7.5	4.3	2.5	7.1	4.0	2.4	6.7	3.8	2.2				
84	TC	42.0	39.9	37.4	40.9	38.8	36.3	39.8	37.7	35.1	38.7	36.6	33.9				
	SC	41.5	39.4	37.0	40.4	38.3	35.8	39.3	37.2	34.7	38.2	36.1	33.5				
	gpm	10.6	8.1	6.3	10.4	7.9	6.1	10.0	7.6	5.9	9.8	7.4	5.7				
	wpd	9.0	5.3	3.2	8.5	4.9	3.0	8.0	4.6	2.8	7.6	4.3	2.6				
86	TC	44.3	42.3	40.0	43.2	41.3	38.9	42.1	40.2	37.7	41.0	39.0	36.6				
	SC	43.8	41.8	39.5	42.7	40.8	38.4	41.6	39.7	37.3	40.5	38.6	36.2				
	gpm	11.2	8.5	6.7	11.0	8.4	6.6	10.7	8.1	6.4	10.4	7.9	6.1				
	wpd	10.0	5.8	3.6	9.5	5.6	3.4	9.1	5.3	3.2	8.5	4.9	3.0				
88	TC	46.6	44.7	42.5	45.6	43.6	41.4	44.5	42.5	40.3	43.4	41.4	39.1				
	SC	46.1	44.2	42.0	45.0	43.1	40.9	43.9	42.0	39.8	42.8	40.9	38.7				
	gpm	11.9	9.0	7.1	11.5	8.8	7.0	11.3	8.6	6.8	11.0	8.4	6.6				
	wpd	11.2	6.5	4.0	10.6	6.1	3.9	10.1	5.9	3.7	9.5	5.6	3.4				
90	TC	48.9	47.1	45.0	47.8	46.0	43.9	46.7	44.9	42.8	45.6	43.9	41.7				
	SC	48.3	46.6	44.5	47.2	45.5	43.4	46.1	44.4	42.3	45.0	43.3	41.2				
	gpm	12.4	9.5	7.6	12.0	9.3	7.4	11.8	9.1	7.2	11.5	8.9	7.1				
	wpd	12.1	7.2	4.6	11.5	6.9	4.3	11.0	6.6	4.1	10.6	6.3	4.0				

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	35.5	32.5	29.6	33.4	30.6	28.0	31.6	28.9	26.5	29.7	27.3	25.2
	SC	27.4	26.1	24.7	26.5	25.2	24.0	25.7	24.4	23.2	24.8	23.7	22.5
	gpm	9.0	6.6	5.0	8.4	6.2	4.7	8.0	5.8	4.5	7.5	5.5	4.2
	wpd	7.0	3.8	2.1	6.1	3.3	2.0	5.5	2.9	1.7	4.9	2.7	1.6
76	TC	36.2	33.6	31.4	34.4	32.0	29.9	32.6	30.6	28.6	30.9	29.1	27.3
	SC	29.8	28.6	27.4	28.9	27.8	26.7	28.1	27.1	26.0	27.3	26.4	25.3
	gpm	9.1	6.8	5.3	8.7	6.5	5.0	8.2	6.2	4.8	7.8	5.9	4.6
	wpd	7.2	4.0	2.5	6.6	3.6	2.2	5.8	3.3	2.0	5.3	3.0	1.8
78	TC	37.1	35.1	33.2	35.4	33.6	31.9	33.9	32.3	30.7	32.4	30.9	26.1
	SC	32.2	31.2	30.1	31.4	30.5	29.5	30.6	29.8	28.8	29.9	29.1	26.2
	gpm	9.4	7.1	5.6	9.0	6.8	5.4	8.6	6.5	5.2	8.2	6.3	4.4
	wpd	7.7	4.4	2.7	7.0	4.0	2.5	6.3	3.7	2.3	5.8	3.4	1.7
80	TC	38.2	36.6	35.1	36.7	35.3	33.9	35.3	34.1	29.8	34.0	30.7	28.7
	SC	34.6	33.8	32.9	33.9	33.1	32.3	33.2	32.5	29.9	32.6	30.8	28.8
	gpm	9.7	7.4	5.9	9.3	7.1	5.8	8.9	6.9	5.0	8.6	6.3	4.8
	wpd	8.2	4.8	3.0	7.6	4.4	2.9	6.9	4.1	2.2	6.5	3.4	2.0
82	TC	39.5	38.3	37.1	38.2	37.2	33.2	37.0	34.0	32.2	34.4	33.0	31.1
	SC	37.2	36.5	35.7	36.5	35.8	33.3	35.9	34.1	32.3	34.5	33.1	31.2
	gpm	10.0	7.8	6.3	9.6	7.5	5.6	9.4	6.9	5.5	8.7	6.7	5.2
	wpd	8.7	5.2	3.4	8.0	4.9	2.7	7.7	4.1	2.6	6.6	3.9	2.4
84	TC	41.1	38.2	36.6	38.5	37.2	35.6	37.5	36.2	34.5	36.5	35.2	33.5
	SC	39.8	38.4	36.7	38.6	37.3	35.7	37.6	36.3	34.6	36.6	35.3	33.6
	gpm	10.4	7.8	6.2	9.7	7.5	6.0	9.5	7.3	5.8	9.2	7.1	5.7
	wpd	9.3	5.2	3.3	8.2	4.9	3.2	7.8	4.7	2.9	7.3	4.4	2.8
86	TC	41.5	40.4	38.9	40.5	39.4	37.9	39.6	38.4	36.8	38.6	37.4	35.8
	SC	41.6	40.5	39.0	40.6	39.5	38.0	39.7	38.5	36.9	38.7	37.5	35.9
	gpm	10.5	8.2	6.5	10.3	8.0	6.4	10.0	7.8	6.3	9.8	7.5	6.0
	wpd	9.5	5.8	3.7	9.2	5.5	3.5	8.7	5.2	3.4	8.3	4.9	3.2
88	TC	43.6	42.5	41.1	42.6	41.5	40.1	41.6	40.5	39.0	40.6	39.5	38.1
	SC	43.7	42.6	41.2	42.7	41.6	40.2	41.7	40.6	39.2	40.7	39.6	38.2
	gpm	11.1	8.6	6.9	10.8	8.4	6.8	10.6	8.2	6.6	10.3	8.1	6.5
	wpd	10.6	6.5	4.1	10.1	6.1	4.0	9.7	5.8	3.8	9.2	5.6	3.6
90	TC	45.6	44.6	43.3	44.6	43.6	42.3	43.6	42.6	41.3	42.6	41.6	40.3
	SC	45.7	44.7	43.4	44.7	43.7	42.4	43.7	42.8	41.4	42.7	41.8	40.4
	gpm	11.6	9.0	7.3	11.3	8.8	7.1	11.1	8.6	7.0	10.8	8.5	6.8
	wpd	11.6	7.0	4.7	11.0	6.8	4.4	10.6	6.5	4.2	10.1	6.2	4.0

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	37.9	35.8	33.7	36.0	33.9	31.9	34.0	32.0	30.2	32.0	30.2	28.6
	SC	29.3	28.2	27.2	28.3	27.3	26.3	27.3	26.4	25.5	26.4	25.5	24.7
	gpm	9.4	7.1	5.6	8.9	6.7	5.3	8.5	6.3	5.0	8.0	6.0	4.8
	wpd	9.8	5.6	3.5	8.8	5.0	3.1	7.9	4.5	2.7	7.0	4.0	2.5
76	TC	38.4	36.7	34.9	36.5	34.8	33.3	34.6	33.1	31.7	32.8	31.5	30.3
	SC	31.5	30.6	29.7	30.5	29.7	28.9	29.6	28.9	28.2	28.7	28.1	27.5
	gpm	9.5	7.3	5.8	9.1	7.0	5.5	8.6	6.6	5.2	8.1	6.3	5.0
	wpd	10.1	5.9	3.7	9.1	5.4	3.4	8.2	4.8	3.1	7.3	4.4	2.8
78	TC	38.9	37.5	36.2	37.1	35.9	34.7	35.4	34.3	33.3	33.8	32.9	32.1
	SC	33.8	33.1	32.4	32.9	32.2	31.6	32.0	31.5	30.9	31.2	30.7	30.3
	gpm	9.7	7.5	6.0	9.2	7.2	5.8	8.8	6.8	5.5	8.4	6.5	5.3
	wpd	10.4	6.2	4.0	9.4	5.7	3.7	8.6	5.1	3.4	7.8	4.7	3.1
80	TC	39.6	38.6	37.6	38.0	37.1	36.3	36.4	35.7	35.1	35.0	34.5	34.0
	SC	36.1	35.6	35.1	35.3	34.8	34.4	34.5	34.1	33.7	33.8	33.5	33.1
	gpm	9.9	7.7	6.3	9.5	7.4	6.0	9.1	7.1	5.8	8.7	6.9	5.7
	wpd	10.8	6.6	4.4	9.9	6.0	4.0	9.1	5.6	3.7	8.4	5.3	3.5
82	TC	40.5	39.8	39.3	39.0	38.6	38.1	37.7	37.4	36.0	35.9	35.6	35.0
	SC	38.6	38.2	37.9	37.8	37.5	37.2	37.1	36.9	35.7	35.7	35.5	35.2
	gpm	10.1	7.9	6.5	9.7	7.7	6.3	9.3	7.4	5.9	8.9	7.1	5.8
	wpd	11.3	6.9	4.7	10.5	6.6	4.5	9.7	6.1	3.9	8.8	5.6	3.7
84	TC	41.7	41.4	40.0	39.8	39.5	39.0	38.9	38.6	38.0	37.9	37.6	37.1
	SC	41.1	41.0	39.7	39.6	39.4	39.2	39.1	39.0	38.7	38.6	38.5	38.1
	gpm	10.4	8.2	6.6	9.9	7.9	6.5	9.7	7.7	6.3	9.4	7.5	6.1
	wpd	11.9	7.5	4.8	10.8	6.9	4.6	10.4	6.6	4.5	9.8	6.2	4.2
86	TC	42.7	42.5	42.1	41.8	41.5	41.1	40.8	40.6	40.1	39.8	39.6	39.1
	SC	43.0	42.9	42.7	42.5	42.4	42.2	42.0	41.7	41.3	41.0	40.7	40.3
	gpm	10.6	8.5	7.0	10.4	8.2	6.8	10.2	8.1	6.7	9.9	7.9	6.5
	wpd	12.5	7.9	5.4	11.9	7.5	5.1	11.4	7.3	4.9	10.8	6.9	4.6
88	TC	44.6	44.5	44.1	43.7	43.5	43.1	42.7	42.5	42.1	41.8	41.6	41.2
	SC	46.0	45.8	45.4	45.0	44.8	44.4	44.0	43.8	43.4	43.0	42.8	42.4
	gpm	11.1	8.9	7.3	10.9	8.7	7.2	10.6	8.5	7.0	10.4	8.3	6.8
	wpd	13.7	8.7	5.9	13.2	8.3	5.7	12.5	7.9	5.5	12.1	7.7	5.1
90	TC	46.5	46.4	46.1	45.6	45.5	45.1	44.6	44.5	44.2	43.7	43.5	43.2
	SC	47.9	47.8	47.4	46.9	46.8	46.4	45.9	45.8	45.4	44.9	44.8	44.4
	gpm	11.6	9.2	7.6	11.4	9.0	7.5	11.1	8.9	7.4	10.9	8.7	7.2
	wpd	14.9	9.4	6.5	14.4	9.0	6.2	13.7	8.7	6.0	13.2	8.3	5.7

2-Row Chilled Water Cooling

EDB	EWT	43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12					
74	TC	30.5	26.2	21.8	28.6	24.4	20.2	26.8	22.7	18.9	25.1	21.2	17.5						
	SC	22.4	20.5	18.4	21.6	19.7	17.7	20.9	18.9	17.0	20.1	18.4	16.1						
	gpm	7.7	5.3	3.7	7.3	5.0	3.4	6.8	4.6	3.2	6.3	4.3	2.9						
	wpd	8.6	4.0	2.0	7.6	3.6	1.7	6.6	3.0	1.4	5.7	2.6	1.2						
76	TC	31.1	27.3	23.6	29.5	25.8	22.3	27.9	24.3	21.0	26.2	23.0	19.9						
	SC	24.6	22.9	21.0	23.9	22.1	20.4	23.2	21.6	19.6	22.5	20.8	18.8						
	gpm	7.9	5.5	4.0	7.5	5.2	3.8	7.0	4.9	3.6	6.6	4.7	3.4						
	wpd	8.9	4.4	2.3	8.1	3.9	2.1	7.1	3.4	1.8	6.3	3.1	1.7						
78	TC	32.0	28.7	25.5	30.4	27.2	24.4	28.9	26.0	23.3	27.5	24.8	22.1						
	SC	26.9	25.3	23.6	26.2	24.7	22.9	25.6	24.0	22.2	25.0	23.3	21.4						
	gpm	8.1	5.8	4.3	7.7	5.5	4.1	7.3	5.3	3.9	6.9	5.0	3.7						
	wpd	9.5	4.8	2.7	8.4	4.4	2.4	7.7	4.0	2.2	6.9	3.7	2.0						
80	TC	32.9	30.2	27.6	31.4	29.0	26.5	30.1	27.8	25.4	28.9	26.7	23.6						
	SC	29.3	27.8	26.1	28.5	27.2	25.5	28.0	26.5	24.6	27.4	25.8	23.3						
	gpm	8.4	6.2	4.7	8.0	5.8	4.5	7.7	5.7	4.3	7.3	5.4	4.0						
	wpd	10.1	5.4	3.1	9.1	4.9	2.9	8.4	4.6	2.6	7.7	4.3	2.3						
82	TC	33.9	31.8	29.5	32.7	30.8	28.6	31.6	29.7	27.0	30.5	28.8	26.0						
	SC	31.6	30.3	28.6	30.9	29.6	27.8	30.3	28.9	26.6	29.7	28.2	25.7						
	gpm	8.6	6.5	5.0	8.3	6.2	4.8	8.0	6.0	4.6	7.7	5.8	4.4						
	wpd	10.6	6.0	3.6	9.9	5.6	3.3	9.1	5.2	3.0	8.6	4.9	2.8						
84	TC	35.4	33.7	31.7	34.3	32.8	30.2	33.3	31.5	29.2	32.3	30.5	28.2						
	SC	34.0	32.8	31.0	33.3	32.0	29.8	32.6	31.1	28.8	31.8	30.1	27.9						
	gpm	9.0	6.9	5.4	8.7	6.6	5.1	8.4	6.4	4.9	8.1	6.2	4.7						
	wpd	11.6	6.8	4.1	10.8	6.3	3.8	10.2	5.9	3.4	9.5	5.4	3.2						
86	TC	37.1	35.5	33.3	36.1	34.6	32.4	35.2	33.6	31.4	34.2	32.7	30.5						
	SC	36.4	35.1	32.9	35.7	34.1	32.0	34.7	33.2	31.0	33.8	32.2	30.1						
	gpm	9.4	7.2	5.6	9.2	7.0	5.4	8.9	6.8	5.3	8.7	6.6	5.1						
	wpd	12.7	7.4	4.5	12.0	7.1	4.3	11.4	6.6	4.0	10.8	6.3	3.8						
88	TC	39.0	37.5	35.5	38.1	36.6	34.6	37.1	35.6	33.6	36.1	34.7	32.6						
	SC	38.5	37.0	35.0	37.6	36.1	34.1	36.6	35.2	33.2	35.7	34.2	32.2						
	gpm	9.9	7.6	6.0	9.6	7.4	5.8	9.4	7.3	5.7	9.2	7.0	5.5						
	wpd	14.0	8.2	5.2	13.3	7.9	4.9	12.7	7.6	4.6	12.0	7.1	4.4						
90	TC	41.0	39.5	37.6	40.0	38.5	36.7	39.0	37.5	35.7	38.1	36.6	34.8						
	SC	40.4	39.0	37.1	39.5	38.0	36.2	38.6	37.1	35.3	37.6	36.1	34.3						
	gpm	10.4	8.0	6.3	10.2	7.8	6.2	9.9	7.6	6.0	9.6	7.4	5.8						
	wpd	15.6	9.1	5.7	14.9	8.8	5.4	14.2	8.2	5.2	13.3	7.9	4.9						

3-Row Chilled Water Cooling

EDB	EWT	42				43			44				45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	39.1	34.2	29.1	36.9	32.0	27.1	34.6	29.8	25.2	32.3	27.8	23.4		
	SC	27.2	25.0	22.7	26.2	24.0	21.9	25.2	23.1	21.0	24.2	22.2	20.2		
	gpm	9.9	6.9	4.9	9.3	6.5	4.6	8.7	6.1	4.2	8.1	5.6	3.9		
	wpd	7.7	3.8	1.9	6.9	3.3	1.7	6.0	2.9	1.4	5.3	2.5	1.2		
76	TC	39.8	35.4	30.9	37.7	33.3	29.2	35.4	31.4	27.4	33.4	29.5	26.0		
	SC	29.6	27.7	25.6	28.7	26.8	24.8	27.7	25.9	24.0	26.9	25.1	23.2		
	gpm	10.0	7.1	5.2	9.5	6.7	4.9	9.0	6.4	4.6	8.5	6.0	4.4		
	wpd	8.0	4.0	2.2	7.2	3.6	1.9	6.4	3.2	1.7	5.7	2.8	1.5		
78	TC	40.6	36.7	32.9	38.6	34.8	31.3	36.6	33.0	29.9	34.7	31.3	28.5		
	SC	32.2	30.4	28.5	31.3	29.5	27.8	30.4	28.7	27.0	29.6	28.0	26.3		
	gpm	10.3	7.5	5.6	9.8	7.1	5.3	9.3	6.6	5.1	8.8	6.3	4.8		
	wpd	8.4	4.4	2.5	7.6	4.0	2.2	6.9	3.5	2.0	6.1	3.2	1.8		
80	TC	41.5	38.1	34.8	39.7	36.3	33.6	37.8	34.8	32.2	36.0	33.4	28.5		
	SC	34.8	33.1	31.5	33.9	32.3	30.8	33.1	31.6	30.1	32.2	30.9	28.2		
	gpm	10.5	7.7	5.9	10.0	7.3	5.6	9.5	7.1	5.4	9.1	6.7	4.8		
	wpd	8.8	4.7	2.8	8.0	4.2	2.5	7.2	4.0	2.3	6.6	3.6	1.8		
82	TC	42.6	39.6	37.1	40.9	38.2	35.8	39.1	36.8	32.5	37.6	35.5	31.3		
	SC	37.4	35.9	34.5	36.6	35.2	33.8	35.8	34.5	32.1	35.1	33.8	30.9		
	gpm	10.8	8.1	6.2	10.3	7.7	6.1	9.9	7.5	5.5	9.5	7.2	5.3		
	wpd	9.2	5.1	3.1	8.4	4.7	2.9	7.7	4.4	2.4	7.2	4.1	2.2		
84	TC	43.8	41.5	39.3	42.3	40.2	36.3	40.8	39.0	35.2	39.5	36.6	34.0		
	SC	40.1	38.8	37.4	39.3	38.2	35.9	38.6	37.4	34.8	37.9	36.2	33.6		
	gpm	11.1	8.4	6.6	10.7	8.1	6.1	10.4	7.9	6.0	10.0	7.4	5.7		
	wpd	9.8	5.6	3.5	9.1	5.3	3.0	8.5	4.9	2.8	8.0	4.3	2.6		
86	TC	45.4	43.5	40.0	44.0	41.3	39.0	42.8	40.2	37.8	41.1	39.1	36.7		
	SC	42.9	41.7	39.6	42.1	40.9	38.5	41.4	39.8	37.3	40.6	38.7	36.2		
	gpm	11.5	8.8	6.7	11.1	8.4	6.6	10.8	8.1	6.4	10.5	8.0	6.2		
	wpd	10.6	6.1	3.6	9.8	5.6	3.4	9.2	5.3	3.2	8.7	5.0	3.1		
88	TC	47.2	44.8	42.6	45.7	43.7	41.5	44.6	42.6	40.4	43.5	41.5	39.2		
	SC	45.7	44.3	42.1	45.1	43.2	41.0	44.0	42.1	39.9	42.9	41.0	38.8		
	gpm	12.0	9.0	7.2	11.5	8.9	7.0	11.3	8.6	6.8	11.0	8.4	6.6		
	wpd	11.3	6.5	4.1	10.6	6.3	3.9	10.1	5.9	3.7	9.7	5.6	3.5		
90	TC	49.0	47.2	45.1	47.9	46.1	44.0	46.8	45.1	42.9	45.7	44.0	41.8		
	SC	48.4	46.7	44.6	47.3	45.6	43.5	46.2	44.5	42.4	45.1	43.4	41.3		
	gpm	12.4	9.5	7.6	12.1	9.4	7.5	11.8	9.1	7.2	11.5	8.9	7.1		
	wpd	12.1	7.2	4.6	11.7	7.0	4.4	11.0	6.6	4.1	10.6	6.3	4.0		

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC		40.5	36.9	33.1	38.3	34.8	31.0	36.1	32.6	29.1	34.0	30.5	27.0											
	SC		27.1	25.5	23.8	26.1	24.5	22.9	25.1	23.6	22.1	24.2	22.7	21.1											
	gpm		10.3	7.5	5.6	9.7	7.0	5.2	9.1	6.6	4.9	8.6	6.2	4.5											
	wpd		9.2	4.8	2.7	8.2	4.3	2.4	7.2	3.8	2.1	6.5	3.3	1.8											
76	TC		40.9	37.6	34.3	38.9	35.6	32.4	36.8	33.6	30.5	34.7	31.7	28.8											
	SC		29.3	27.8	26.3	28.4	26.9	25.5	27.4	26.0	24.6	26.5	25.2	23.8											
	gpm		10.4	7.6	5.8	9.9	7.2	5.5	9.3	6.8	5.2	8.8	6.4	4.9											
	wpd		9.3	5.0	2.9	8.4	4.5	2.6	7.6	4.0	2.3	6.7	3.5	2.1											
78	TC		41.5	38.5	35.5	39.4	36.6	33.8	37.4	34.7	32.2	35.5	32.9	30.7											
	SC		31.5	30.2	28.8	30.6	29.3	28.0	29.7	28.5	27.3	28.8	27.7	26.6											
	gpm		10.5	7.8	6.0	10.0	7.4	5.7	9.5	7.0	5.5	9.0	6.7	5.2											
	wpd		9.5	5.2	3.2	8.7	4.8	2.8	7.8	4.3	2.6	7.0	3.9	2.3											
80	TC		42.1	39.5	36.9	40.1	37.7	35.4	38.3	35.9	33.9	36.5	34.4	32.4											
	SC		33.8	32.6	31.4	32.9	31.8	30.7	32.0	31.0	30.0	31.2	30.3	29.2											
	gpm		10.6	8.0	6.3	10.1	7.6	6.0	9.7	7.3	5.8	9.2	7.0	5.5											
	wpd		9.8	5.5	3.4	8.9	5.0	3.1	8.2	4.6	2.9	7.3	4.2	2.6											
82	TC		42.8	40.5	38.5	41.0	38.9	37.0	39.2	37.4	35.7	37.5	35.9	34.4											
	SC		36.1	35.0	34.1	35.2	34.3	33.3	34.4	33.6	32.6	33.7	32.9	32.0											
	gpm		10.9	8.2	6.5	10.4	7.8	6.3	9.9	7.5	6.0	9.5	7.3	5.8											
	wpd		10.2	5.8	3.7	9.3	5.3	3.4	8.5	4.9	3.2	7.8	4.6	2.9											
84	TC		43.6	41.8	40.1	41.9	40.3	38.8	40.3	38.9	37.5	38.8	37.6	36.4											
	SC		38.4	37.6	36.7	37.6	36.9	36.0	36.9	36.2	35.4	36.2	35.5	34.7											
	gpm		11.1	8.5	6.8	10.6	8.2	6.5	10.2	7.9	6.3	9.8	7.6	6.1											
	wpd		10.6	6.2	4.0	9.8	5.8	3.7	9.0	5.4	3.5	8.3	5.0	3.2											
86	TC		44.5	43.2	41.8	43.1	41.9	40.6	41.7	40.6	39.5	40.4	39.5	35.9											
	SC		40.8	40.2	39.4	40.1	39.5	38.7	39.5	38.8	38.1	38.8	38.2	36.0											
	gpm		11.3	8.8	7.0	10.9	8.5	6.8	10.6	8.3	6.7	10.2	8.0	6.0											
	wpd		11.0	6.7	4.3	10.4	6.2	4.0	9.7	5.9	3.9	9.0	5.5	3.2											
88	TC		45.8	44.7	43.7	44.5	43.6	40.2	43.3	40.6	39.1	40.7	39.6	38.1											
	SC		43.4	42.8	42.1	42.7	42.1	40.3	42.1	40.7	39.2	40.8	39.7	38.3											
	gpm		11.6	9.1	7.4	11.3	8.8	6.8	10.9	8.3	6.6	10.3	8.1	6.5											
	wpd		11.6	7.1	4.8	11.0	6.8	4.0	10.4	5.9	3.8	9.2	5.6	3.6											
90	TC		47.3	44.7	43.4	44.7	43.7	42.4	43.7	42.7	41.4	42.7	41.7	40.4											
	SC		46.0	44.8	43.5	44.8	43.8	42.5	43.8	42.9	41.5	42.8	41.9	40.5											
	gpm		12.0	9.1	7.3	11.4	8.8	7.1	11.1	8.7	7.0	10.9	8.5	6.8											
	wpd		12.5	7.1	4.7	11.2	6.8	4.4	10.6	6.6	4.2	10.2	6.2	4.0											

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	43.3	40.8	38.1	41.1	38.6	36.0	39.0	36.5	33.8	36.8	34.4	31.8
	SC	29.2	28.0	26.6	28.1	26.9	25.6	27.1	25.9	24.6	26.0	24.9	23.7
	gpm	10.8	8.1	6.3	10.2	7.7	6.0	9.7	7.3	5.6	9.1	6.8	5.2
	wpd	12.9	7.3	4.5	11.6	6.6	4.0	10.4	5.9	3.5	9.2	5.1	3.1
76	TC	43.5	41.3	38.8	41.4	39.2	36.8	39.3	37.2	34.8	37.2	35.1	32.9
	SC	31.3	30.2	29.0	30.2	29.1	28.0	29.2	28.2	27.1	28.2	27.2	26.1
	gpm	10.8	8.2	6.5	10.3	7.8	6.1	9.8	7.4	5.8	9.3	7.0	5.5
	wpd	13.0	7.4	4.6	11.7	6.7	4.2	10.7	6.1	3.7	9.5	5.5	3.3
78	TC	43.8	41.8	39.7	41.8	39.8	37.8	39.8	37.8	35.9	37.7	35.9	34.1
	SC	33.4	32.4	31.4	32.4	31.4	30.5	31.4	30.5	29.6	30.4	29.6	28.7
	gpm	10.9	8.3	6.6	10.4	7.9	6.3	9.9	7.5	5.9	9.4	7.2	5.7
	wpd	13.2	7.7	4.8	12.1	6.9	4.4	10.8	6.2	3.9	9.8	5.7	3.5
80	TC	44.1	42.4	40.6	42.1	40.5	38.8	40.2	38.7	37.1	38.3	36.9	35.5
	SC	35.6	34.7	33.8	34.6	33.8	32.9	33.6	32.9	32.1	32.7	32.0	31.3
	gpm	11.0	8.5	6.7	10.4	8.0	6.4	10.0	7.7	6.1	9.5	7.4	5.9
	wpd	13.3	7.9	5.0	12.1	7.2	4.5	11.1	6.6	4.2	10.1	6.0	3.8
82	TC	44.5	43.1	41.6	42.6	41.3	40.0	40.8	39.6	38.4	39.0	37.9	36.9
	SC	37.8	37.1	36.3	36.8	36.2	35.5	35.9	35.3	34.7	35.0	34.5	34.0
	gpm	11.0	8.6	6.9	10.6	8.2	6.6	10.2	7.8	6.4	9.7	7.6	6.1
	wpd	13.5	8.2	5.3	12.5	7.5	4.8	11.4	6.8	4.5	10.5	6.3	4.2
84	TC	45.0	43.8	42.7	43.2	42.2	41.2	41.5	40.7	39.8	39.9	39.2	38.5
	SC	40.0	39.4	38.9	39.1	38.6	38.1	38.3	37.8	37.4	37.4	37.1	36.7
	gpm	11.2	8.7	7.1	10.8	8.4	6.8	10.4	8.1	6.6	10.0	7.8	6.4
	wpd	13.8	8.4	5.6	12.9	7.8	5.1	11.9	7.3	4.8	11.0	6.7	4.5
86	TC	45.6	44.8	44.0	44.0	43.3	42.7	42.4	41.9	41.4	40.9	40.7	40.3
	SC	42.3	41.9	41.5	41.5	41.1	40.8	40.7	40.4	40.1	40.0	39.8	39.5
	gpm	11.4	8.9	7.3	11.0	8.7	7.1	10.6	8.4	6.9	10.2	8.1	6.7
	wpd	14.4	8.8	5.9	13.3	8.3	5.6	12.4	7.8	5.3	11.4	7.3	4.9
88	TC	46.4	45.9	45.5	44.9	44.7	44.4	43.6	43.5	42.2	41.9	41.7	41.3
	SC	44.7	44.5	44.2	43.9	43.8	43.6	43.3	43.2	42.0	41.8	41.7	41.5
	gpm	11.5	9.1	7.6	11.2	8.9	7.4	10.8	8.7	7.0	10.4	8.3	6.9
	wpd	14.7	9.2	6.3	13.8	8.8	6.0	13.0	8.3	5.5	12.1	7.7	5.3
90	TC	47.5	47.4	46.2	45.7	45.6	45.2	44.7	44.6	44.3	43.8	43.6	43.3
	SC	47.3	47.2	45.9	45.6	45.6	45.4	45.2	45.1	44.9	44.7	44.6	44.4
	gpm	11.9	9.5	7.7	11.4	9.1	7.5	11.2	8.9	7.4	10.9	8.7	7.2
	wpd	15.6	9.9	6.6	14.4	9.1	6.2	13.8	8.7	6.0	13.2	8.4	5.7

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	35.4	30.7	25.1	33.3	28.6	23.0	31.2	26.5	21.1	29.2	24.4	18.8												
	SC	21.9	20.0	17.7	21.1	19.1	16.8	20.2	18.3	16.0	19.4	17.4	15.1												
	gpm	8.9	6.2	4.3	8.4	5.8	3.9	7.9	5.4	3.6	7.4	5.0	3.2												
	wpd	11.4	5.6	2.6	10.2	4.8	2.1	8.9	4.1	1.8	7.9	3.6	1.4												
76	TC	35.3	31.1	26.3	33.3	29.2	24.3	31.4	27.3	22.6	29.5	25.4	21.1												
	SC	23.9	22.1	20.0	23.1	21.3	19.2	22.3	20.6	18.5	21.5	19.8	17.8												
	gpm	8.9	6.3	4.4	8.4	5.9	4.1	8.0	5.5	3.8	7.5	5.1	3.6												
	wpd	11.4	5.7	2.8	10.2	5.0	2.4	9.1	4.4	2.1	8.1	3.8	1.8												
78	TC	35.4	31.9	27.5	33.6	30.1	25.9	31.9	28.3	24.4	30.2	26.6	23.0												
	SC	26.0	24.4	22.4	25.2	23.6	21.7	24.5	22.9	21.2	23.8	22.2	20.4												
	gpm	8.9	6.5	4.7	8.5	6.1	4.3	8.0	5.8	4.1	7.7	5.4	3.9												
	wpd	11.4	6.0	3.1	10.4	5.3	2.7	9.3	4.8	2.4	8.4	4.1	2.1												
80	TC	36.0	32.8	29.0	34.3	31.2	27.6	32.7	29.5	26.2	31.1	28.0	25.0												
	SC	28.2	26.7	24.9	27.4	26.0	24.3	26.8	25.2	23.6	26.1	24.6	23.0												
	gpm	9.1	6.6	4.9	8.7	6.3	4.7	8.3	6.0	4.4	7.9	5.7	4.2												
	wpd	11.8	6.3	3.4	10.8	5.7	3.1	9.9	5.2	2.8	8.9	4.6	2.5												
82	TC	36.8	34.0	30.6	35.2	32.4	29.4	33.6	31.0	28.1	32.0	29.6	27.0												
	SC	30.5	29.1	27.5	29.7	28.4	26.8	29.1	27.8	26.2	28.4	27.1	25.4												
	gpm	9.3	6.9	5.2	8.9	6.5	5.0	8.5	6.3	4.7	8.1	6.0	4.6												
	wpd	12.5	6.8	3.9	11.4	6.2	3.6	10.4	5.7	3.2	9.5	5.2	3.0												
84	TC	37.6	35.1	32.3	36.1	33.7	31.1	34.6	32.5	30.0	33.2	31.2	28.9												
	SC	32.8	31.4	29.9	32.0	30.9	29.3	31.3	30.2	28.5	30.8	29.6	27.9												
	gpm	9.5	7.1	5.4	9.1	6.8	5.3	8.8	6.5	5.0	8.4	6.3	4.9												
	wpd	12.9	7.2	4.3	11.8	6.6	4.0	11.0	6.2	3.7	10.1	5.7	3.4												
86	TC	38.5	36.5	34.1	37.1	35.3	33.1	35.8	34.2	32.0	34.6	33.1	31.1												
	SC	35.0	33.9	32.4	34.3	33.2	31.7	33.7	32.6	31.1	33.1	32.1	30.3												
	gpm	9.8	7.4	5.8	9.4	7.2	5.6	9.1	6.9	5.4	8.8	6.7	5.2												
	wpd	13.8	7.9	4.8	12.7	7.4	4.5	11.8	6.9	4.3	11.0	6.5	3.9												
88	TC	39.7	38.0	36.0	38.4	36.9	35.1	37.3	35.9	33.7	36.3	35.0	32.7												
	SC	37.4	36.3	34.9	36.8	35.6	34.2	36.1	35.0	33.3	35.5	34.2	32.3												
	gpm	10.0	7.7	6.1	9.7	7.5	5.9	9.5	7.3	5.7	9.2	7.1	5.5												
	wpd	14.4	8.4	5.3	13.5	8.1	5.0	12.9	7.6	4.6	12.2	7.2	4.4												
90	TC	41.1	39.7	38.0	40.1	38.7	36.7	39.1	37.6	35.8	38.2	36.7	34.8												
	SC	39.8	38.7	37.2	39.2	37.9	36.3	38.4	37.1	35.3	37.7	36.2	34.4												
	gpm	10.4	8.0	6.5	10.2	7.8	6.2	9.9	7.6	6.1	9.7	7.4	5.8												
	wpd	15.6	9.3	6.0	14.9	8.8	5.6	14.2	8.2	5.3	13.5	7.9	4.9												

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	45.6	39.8	33.8	43.0	37.3	31.2	40.5	34.8	28.5	37.9	32.3	26.3
	SC	27.1	24.6	22.1	26.0	23.6	21.0	24.9	22.5	19.9	23.8	21.5	19.1
	gpm	11.5	8.1	5.7	10.9	7.6	5.2	10.2	7.1	4.8	9.5	6.6	4.4
	wpd	10.6	5.1	2.6	9.4	4.5	2.2	8.3	4.0	1.8	7.2	3.4	1.5
76	TC	45.7	40.4	34.8	43.2	38.1	32.7	40.8	35.7	30.5	38.4	33.3	28.4
	SC	29.3	27.0	24.6	28.3	26.1	23.8	27.2	25.1	22.9	26.2	24.1	22.0
	gpm	11.5	8.2	5.9	11.0	7.7	5.5	10.4	7.2	5.1	9.7	6.7	4.8
	wpd	10.6	5.4	2.8	9.5	4.7	2.4	8.5	4.1	2.1	7.5	3.6	1.8
78	TC	45.9	41.1	36.4	43.6	39.0	34.2	41.4	36.7	32.3	39.1	34.6	30.1
	SC	31.6	29.5	27.4	30.6	28.6	26.5	29.7	27.6	25.7	28.7	26.8	24.8
	gpm	11.6	8.3	6.1	11.0	7.9	5.8	10.5	7.4	5.5	9.9	7.1	5.1
	wpd	10.7	5.5	3.0	9.7	4.9	2.7	8.7	4.3	2.4	7.7	4.0	2.0
80	TC	46.5	42.2	37.8	44.3	40.1	35.9	42.2	38.0	33.9	39.9	36.1	32.2
	SC	34.1	32.1	30.2	33.1	31.2	29.4	32.2	30.4	28.5	31.2	29.5	27.7
	gpm	11.8	8.5	6.4	11.2	8.1	6.1	10.6	7.7	5.7	10.1	7.3	5.4
	wpd	11.0	5.8	3.2	10.0	5.3	2.9	9.0	4.7	2.6	8.1	4.2	2.3
82	TC	47.2	43.3	39.3	45.1	41.3	37.5	43.0	39.4	35.8	40.9	37.5	34.2
	SC	36.6	34.8	33.0	35.6	33.9	32.2	34.7	33.1	31.4	33.8	32.2	30.7
	gpm	12.0	8.8	6.6	11.5	8.4	6.3	10.9	8.0	6.1	10.4	7.6	5.7
	wpd	11.3	6.1	3.5	10.4	5.6	3.2	9.4	5.0	2.9	8.5	4.6	2.6
84	TC	47.9	44.4	40.9	46.0	42.5	39.3	43.9	40.8	37.8	42.0	39.0	36.5
	SC	39.0	37.4	35.7	38.1	36.6	35.0	37.3	35.8	34.3	36.4	35.0	33.6
	gpm	12.1	9.0	6.9	11.6	8.6	6.6	11.1	8.2	6.4	10.6	7.9	6.1
	wpd	11.7	6.4	3.8	10.7	5.9	3.5	9.8	5.4	3.2	9.0	4.9	3.0
86	TC	48.7	45.7	42.7	46.9	43.9	41.2	45.0	42.3	39.9	43.3	40.8	38.6
	SC	41.5	40.1	38.6	40.7	39.3	37.9	39.9	38.5	37.2	39.1	37.9	36.5
	gpm	12.4	9.3	7.2	11.9	8.9	7.0	11.4	8.5	6.7	11.0	8.3	6.6
	wpd	12.1	6.9	4.1	11.2	6.3	3.9	10.3	5.8	3.6	9.5	5.5	3.4
88	TC	49.6	47.0	44.6	47.9	45.6	43.4	46.2	44.1	42.1	44.7	42.8	39.3
	SC	44.1	42.8	41.5	43.3	42.1	40.9	42.5	41.4	40.1	41.8	40.7	38.8
	gpm	12.6	9.5	7.6	12.1	9.2	7.3	11.7	8.9	7.1	11.3	8.6	6.6
	wpd	12.6	7.1	4.5	11.7	6.7	4.2	10.9	6.3	4.0	10.1	5.9	3.5
90	TC	50.7	48.7	46.7	49.1	47.4	45.5	47.6	46.1	43.0	46.3	44.1	41.9
	SC	46.7	45.6	44.4	45.9	44.9	43.7	45.3	44.2	42.5	44.6	43.5	41.4
	gpm	12.9	9.9	7.9	12.4	9.5	7.7	12.0	9.3	7.2	11.7	8.9	7.1
	wpd	13.1	7.7	4.9	12.1	7.2	4.7	11.5	6.9	4.1	10.9	6.3	4.0

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	46.6	42.7	38.3	44.4	40.3	35.8	42.0	37.9	33.5	39.6	35.5	31.1												
	SC	27.2	25.4	23.5	26.2	24.3	22.4	25.1	23.3	21.4	24.0	22.2	20.4												
	gpm	11.8	8.6	6.5	11.2	8.2	6.0	10.6	7.7	5.7	10.0	7.2	5.2												
	wpd	12.0	6.5	3.6	10.9	5.8	3.2	9.8	5.1	2.8	8.7	4.5	2.4												
76	TC	46.7	43.0	39.0	44.5	40.7	36.7	42.2	38.4	34.5	39.9	36.1	32.3												
	SC	29.2	27.5	25.8	28.2	26.5	24.8	27.2	25.5	23.8	26.1	24.5	22.9												
	gpm	11.9	8.7	6.6	11.3	8.2	6.2	10.7	7.8	5.8	10.1	7.3	5.5												
	wpd	12.2	6.6	3.8	11.0	5.8	3.3	9.9	5.2	2.9	8.9	4.7	2.6												
78	TC	46.8	43.4	39.8	44.7	41.2	37.7	42.6	39.1	35.5	40.3	37.0	33.6												
	SC	31.2	29.7	28.1	30.3	28.7	27.2	29.3	27.8	26.2	28.3	26.9	25.4												
	gpm	11.9	8.8	6.7	11.4	8.3	6.3	10.8	7.9	6.0	10.2	7.5	5.7												
	wpd	12.2	6.7	3.9	11.2	6.0	3.5	10.1	5.4	3.1	9.0	4.8	2.8												
80	TC	47.1	44.1	40.7	45.0	42.0	38.8	43.0	39.9	36.8	40.9	37.8	34.9												
	SC	33.4	32.0	30.5	32.4	31.0	29.6	31.5	30.1	28.8	30.5	29.2	27.9												
	gpm	11.9	8.9	6.9	11.4	8.5	6.5	10.9	8.1	6.2	10.4	7.6	5.9												
	wpd	12.3	6.9	4.1	11.2	6.2	3.7	10.2	5.6	3.3	9.3	5.0	3.0												
82	TC	47.6	44.8	41.8	45.6	42.8	39.9	43.5	40.8	38.0	41.6	38.9	36.3												
	SC	35.5	34.2	32.9	34.6	33.3	32.1	33.7	32.5	31.3	32.8	31.6	30.5												
	gpm	12.1	9.1	7.0	11.6	8.7	6.8	11.0	8.3	6.4	10.5	7.9	6.1												
	wpd	12.6	7.1	4.3	11.6	6.6	4.0	10.5	5.9	3.5	9.5	5.4	3.2												
84	TC	48.0	45.5	42.9	46.1	43.7	41.1	44.1	41.8	39.4	42.2	40.0	37.9												
	SC	37.7	36.5	35.4	36.8	35.7	34.6	35.9	34.9	33.8	35.1	34.1	33.1												
	gpm	12.2	9.2	7.3	11.7	8.8	6.9	11.2	8.5	6.7	10.7	8.1	6.4												
	wpd	12.8	7.3	4.6	11.9	6.8	4.1	10.9	6.2	3.9	9.9	5.7	3.5												
86	TC	48.5	46.3	44.0	46.6	44.6	42.5	44.8	42.8	41.0	43.1	41.2	39.5												
	SC	39.9	38.9	37.9	39.0	38.1	37.1	38.2	37.3	36.5	37.4	36.6	35.7												
	gpm	12.2	9.3	7.5	11.8	9.0	7.2	11.4	8.7	6.9	10.9	8.3	6.7												
	wpd	12.9	7.6	4.8	12.0	7.0	4.5	11.2	6.6	4.1	10.4	6.0	3.9												
88	TC	49.1	47.3	45.4	47.4	45.6	44.0	45.6	44.1	42.5	44.0	42.6	41.2												
	SC	42.1	41.3	40.4	41.3	40.5	39.7	40.5	39.8	39.0	39.8	39.2	38.4												
	gpm	12.4	9.6	7.6	12.0	9.3	7.4	11.5	8.9	7.2	11.1	8.6	7.0												
	wpd	13.4	7.9	5.0	12.5	7.5	4.8	11.5	6.9	4.5	10.8	6.5	4.2												
90	TC	49.9	48.4	46.9	48.2	46.9	45.5	46.6	45.5	44.2	45.1	44.1	43.0												
	SC	44.4	43.8	43.0	43.7	43.1	42.3	42.9	42.4	41.7	42.3	41.7	41.0												
	gpm	12.7	9.9	7.9	12.2	9.5	7.7	11.8	9.2	7.5	11.4	8.9	7.3												
	wpd	13.9	8.4	5.4	12.9	7.8	5.1	12.0	7.3	4.8	11.3	6.9	4.6												

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	49.1	46.8	43.8	46.9	44.5	41.5	44.8	42.2	39.1	42.5	39.9	36.7
	SC	29.2	28.0	26.6	28.1	26.9	25.5	27.0	25.8	24.3	26.0	24.7	23.3
	gpm	12.2	9.3	7.3	11.7	8.9	6.9	11.1	8.4	6.5	10.6	7.9	6.1
	wpd	16.5	9.7	5.9	15.1	8.7	5.3	13.7	7.8	4.6	12.4	6.9	4.1
76	TC	49.1	47.0	44.1	47.0	44.8	41.9	44.8	42.5	39.6	42.7	40.2	37.3
	SC	31.2	30.1	28.7	30.1	29.0	27.7	29.1	27.9	26.6	28.0	26.9	25.5
	gpm	12.2	9.3	7.3	11.7	8.9	7.0	11.2	8.5	6.6	10.6	8.0	6.2
	wpd	16.5	9.7	5.9	15.2	8.8	5.4	13.8	7.9	4.8	12.5	7.0	4.3
78	TC	49.2	47.1	44.6	47.1	45.0	42.5	45.0	42.8	40.3	42.9	40.7	38.1
	SC	33.2	32.2	30.9	32.2	31.2	29.9	31.1	30.1	28.9	30.1	29.1	27.9
	gpm	12.3	9.3	7.4	11.7	9.0	7.0	11.2	8.5	6.7	10.7	8.1	6.3
	wpd	16.7	9.7	6.0	15.2	9.0	5.5	13.8	8.0	4.9	12.7	7.3	4.5
80	TC	49.3	47.5	45.2	47.3	45.4	43.1	45.2	43.3	41.0	43.2	41.2	39.1
	SC	35.3	34.3	33.2	34.2	33.3	32.2	33.2	32.3	31.2	32.2	31.3	30.3
	gpm	12.2	9.4	7.5	11.7	9.0	7.2	11.2	8.6	6.8	10.7	8.2	6.5
	wpd	16.5	9.8	6.2	15.2	9.0	5.7	13.8	8.2	5.1	12.7	7.4	4.6
82	TC	49.5	47.9	45.8	47.5	45.9	43.8	45.5	43.9	41.9	43.5	41.9	40.0
	SC	37.4	36.6	35.5	36.4	35.6	34.6	35.4	34.6	33.6	34.4	33.6	32.7
	gpm	12.3	9.5	7.6	11.8	9.1	7.3	11.3	8.7	7.0	10.8	8.3	6.6
	wpd	16.7	10.1	6.3	15.4	9.2	5.9	14.2	8.4	5.4	13.0	7.7	4.8
84	TC	49.8	48.4	46.5	47.9	46.4	44.6	45.9	44.5	42.8	44.0	42.6	41.0
	SC	39.5	38.8	37.9	38.5	37.8	36.9	37.6	36.9	36.1	36.6	36.0	35.2
	gpm	12.4	9.6	7.7	11.9	9.3	7.4	11.4	8.9	7.1	10.9	8.5	6.8
	wpd	17.1	10.2	6.6	15.8	9.5	6.1	14.5	8.7	5.6	13.2	8.0	5.1
86	TC	50.1	48.8	47.3	48.2	47.0	45.5	46.3	45.2	43.8	44.5	43.4	42.2
	SC	41.7	41.0	40.3	40.7	40.1	39.4	39.8	39.2	38.5	38.8	38.3	37.7
	gpm	12.5	9.7	7.8	12.0	9.3	7.6	11.5	9.0	7.3	11.0	8.6	7.0
	wpd	17.2	10.4	6.8	15.9	9.7	6.3	14.7	9.0	5.9	13.5	8.2	5.5
88	TC	50.5	49.5	48.2	48.6	47.7	46.5	46.8	46.0	44.9	45.1	44.3	43.4
	SC	43.8	43.3	42.7	42.9	42.4	41.8	42.0	41.6	41.1	41.1	40.8	40.3
	gpm	12.5	9.8	8.0	12.1	9.5	7.7	11.7	9.1	7.4	11.2	8.8	7.2
	wpd	17.4	10.7	7.0	16.3	9.9	6.6	15.1	9.2	6.1	14.0	8.6	5.8
90	TC	50.9	50.2	49.2	49.2	48.5	47.6	47.5	46.9	46.2	45.8	45.4	44.8
	SC	46.1	45.7	45.2	45.2	44.8	44.4	44.3	44.0	43.6	43.5	43.3	43.0
	gpm	12.6	10.0	8.2	12.2	9.7	7.9	11.8	9.3	7.6	11.4	9.1	7.4
	wpd	17.6	11.1	7.4	16.5	10.4	6.9	15.4	9.7	6.5	14.4	9.1	6.1

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	40.6	36.9	31.1	38.6	34.7	28.5	36.5	32.5	25.9	34.4	30.1	23.6												
	SC	21.4	19.9	17.6	20.6	19.0	16.6	19.8	18.2	15.6	19.0	17.3	14.7												
	gpm	10.3	7.5	5.2	9.8	7.0	4.8	9.2	6.5	4.3	8.7	6.1	3.9												
	wpd	15.1	8.1	3.9	13.8	7.1	3.3	12.2	6.2	2.7	10.8	5.3	2.2												
76	TC	40.7	37.0	31.1	38.7	34.7	28.8	36.6	32.4	26.6	34.5	30.1	24.5												
	SC	23.5	21.9	19.6	22.6	21.1	18.7	21.8	20.1	17.9	21.0	19.2	17.0												
	gpm	10.3	7.5	5.3	9.8	7.0	4.9	9.2	6.5	4.5	8.7	6.1	4.1												
	wpd	15.4	8.1	4.0	13.8	7.1	3.4	12.2	6.2	2.9	10.8	5.3	2.4												
78	TC	40.6	36.8	31.6	38.6	34.8	29.6	36.5	32.6	27.5	34.4	30.5	25.6												
	SC	25.4	23.9	21.8	24.6	23.1	21.0	23.8	22.2	20.2	23.0	21.4	19.4												
	gpm	10.3	7.4	5.4	9.8	7.0	5.0	9.2	6.6	4.7	8.7	6.2	4.3												
	wpd	15.1	7.9	4.1	13.8	7.1	3.6	12.2	6.3	3.1	10.8	5.4	2.7												
80	TC	40.9	37.4	32.6	38.8	35.4	30.8	36.8	33.5	29.0	34.8	31.5	27.0												
	SC	27.4	25.9	24.0	26.5	25.2	23.3	25.8	24.4	22.5	25.0	23.6	21.7												
	gpm	10.3	7.6	5.5	9.8	7.2	5.2	9.3	6.8	4.9	8.8	6.4	4.6												
	wpd	15.4	8.2	4.4	13.8	7.4	3.9	12.5	6.6	3.4	11.2	5.9	3.0												
82	TC	40.6	37.5	33.5	38.7	35.8	31.8	36.9	34.1	30.1	35.2	32.2	28.5												
	SC	29.4	28.1	26.4	28.7	27.4	25.7	28.0	26.7	24.9	27.3	26.0	24.2												
	gpm	10.3	7.6	5.7	9.8	7.3	5.4	9.3	6.9	5.0	8.9	6.5	4.8												
	wpd	15.1	8.2	4.6	13.8	7.6	4.1	12.5	6.9	3.7	11.4	6.2	3.3												
84	TC	41.0	38.3	34.7	39.3	36.6	33.0	37.6	35.0	31.5	36.0	33.4	30.1												
	SC	31.6	30.4	28.7	30.9	29.7	28.0	30.2	29.0	27.4	29.6	28.3	26.8												
	gpm	10.4	7.7	5.8	9.9	7.4	5.6	9.5	7.1	5.4	9.2	6.8	5.0												
	wpd	15.6	8.6	4.9	14.2	7.9	4.5	13.1	7.2	4.1	12.0	6.6	3.7												
86	TC	41.7	39.2	35.9	40.1	37.6	34.4	38.5	36.0	33.1	36.9	34.5	31.8												
	SC	33.8	32.7	31.2	33.2	32.0	30.5	32.5	31.3	29.9	31.9	30.7	29.2												
	gpm	10.6	7.9	6.1	10.1	7.6	5.8	9.7	7.3	5.6	9.3	7.0	5.4												
	wpd	16.1	8.9	5.3	14.7	8.2	4.9	13.5	7.6	4.5	12.5	7.1	4.1												
88	TC	42.6	40.1	37.3	41.0	38.5	36.0	39.4	37.2	34.8	37.8	35.8	33.6												
	SC	36.2	35.0	33.7	35.5	34.3	33.0	34.8	33.6	32.3	34.1	33.1	31.7												
	gpm	10.8	8.1	6.3	10.3	7.8	6.1	9.9	7.5	5.8	9.5	7.3	5.7												
	wpd	16.8	9.5	5.7	15.4	8.8	5.3	14.2	8.1	4.9	13.1	7.6	4.6												
90	TC	43.5	41.1	38.8	41.9	39.7	37.6	40.4	38.4	36.5	39.0	37.2	35.4												
	SC	38.5	37.2	36.0	37.7	36.7	35.5	37.0	36.0	34.8	36.5	35.4	34.0												
	gpm	11.0	8.4	6.5	10.6	8.0	6.3	10.3	7.8	6.2	9.9	7.5	6.0												
	wpd	17.3	10.1	6.2	16.1	9.3	5.7	15.1	8.8	5.4	14.0	8.1	5.2												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	52.2	47.2	40.6	49.9	44.6	37.9	47.4	41.9	34.9	44.9	39.0	32.0												
	SC	26.9	24.8	22.1	25.9	23.7	21.0	24.8	22.6	19.8	23.8	21.4	18.7												
	gpm	13.2	9.5	6.9	12.6	9.0	6.4	12.0	8.5	5.9	11.4	7.9	5.4												
	wpd	13.8	7.2	3.8	12.6	6.5	3.2	11.5	5.7	2.8	10.3	4.9	2.3												
76	TC	52.3	47.2	40.9	49.9	44.6	38.3	47.4	41.9	35.6	44.9	39.1	33.0												
	SC	29.1	27.0	24.4	28.1	25.9	23.3	27.1	24.8	22.3	26.0	23.7	21.2												
	gpm	13.2	9.5	6.9	12.6	9.0	6.5	12.0	8.5	6.0	11.4	7.9	5.6												
	wpd	13.8	7.2	3.8	12.6	6.5	3.3	11.5	5.7	2.8	10.3	4.9	2.5												
78	TC	52.3	47.4	41.5	49.8	44.9	39.2	47.4	42.4	36.6	44.9	39.8	34.0												
	SC	31.3	29.2	26.8	30.3	28.2	25.8	29.2	27.2	24.8	28.2	26.1	23.8												
	gpm	13.2	9.6	7.0	12.6	9.1	6.6	12.0	8.5	6.1	11.4	8.1	5.7												
	wpd	13.8	7.4	3.9	12.6	6.6	3.5	11.3	5.8	3.0	10.3	5.1	2.6												
80	TC	52.7	48.1	42.8	50.3	45.7	40.4	47.9	43.4	38.1	45.6	41.0	36.0												
	SC	33.5	31.6	29.3	32.5	30.5	28.3	31.5	29.6	27.4	30.5	28.6	26.5												
	gpm	13.4	9.7	7.2	12.7	9.2	6.8	12.1	8.8	6.5	11.5	8.3	6.1												
	wpd	14.2	7.5	4.1	12.8	6.7	3.7	11.7	6.1	3.3	10.6	5.5	2.9												
82	TC	52.5	48.4	43.5	50.3	46.0	41.4	48.0	43.9	39.2	45.8	41.6	37.2												
	SC	35.8	34.1	32.0	34.9	33.1	31.1	33.9	32.1	30.2	33.0	31.2	29.4												
	gpm	13.3	9.8	7.4	12.7	9.3	7.0	12.2	8.9	6.6	11.6	8.4	6.3												
	wpd	14.0	7.6	4.3	12.8	6.9	3.9	11.8	6.3	3.5	10.7	5.6	3.2												
84	TC	52.9	49.2	44.8	50.7	47.0	42.6	48.6	44.8	40.7	46.5	42.7	38.8												
	SC	38.2	36.6	34.6	37.2	35.6	33.8	36.3	34.7	32.9	35.5	33.8	32.1												
	gpm	13.4	10.0	7.6	12.8	9.5	7.2	12.3	9.0	6.9	11.8	8.6	6.6												
	wpd	14.2	7.9	4.5	13.0	7.2	4.1	12.0	6.5	3.8	11.0	5.9	3.4												
86	TC	53.5	49.9	46.0	51.4	47.9	44.2	49.3	45.9	42.2	47.2	43.9	40.4												
	SC	40.6	39.1	37.3	39.7	38.2	36.5	38.8	37.3	35.7	37.9	36.5	34.9												
	gpm	13.5	10.1	7.8	13.0	9.7	7.5	12.5	9.3	7.1	12.0	8.9	6.8												
	wpd	14.5	8.1	4.8	13.5	7.5	4.4	12.3	6.9	4.0	11.3	6.3	3.7												
88	TC	54.1	51.0	47.4	52.0	49.0	45.5	50.0	47.1	43.8	48.0	45.2	42.2												
	SC	43.1	41.6	40.0	42.2	40.8	39.2	41.3	40.0	38.4	40.4	39.2	37.7												
	gpm	13.7	10.3	8.0	13.2	10.0	7.7	12.7	9.5	7.4	12.1	9.1	7.1												
	wpd	14.9	8.4	5.0	13.8	7.9	4.7	12.8	7.2	4.3	11.7	6.6	4.0												
90	TC	54.8	52.0	48.8	52.8	50.2	47.0	50.9	48.4	45.5	49.0	46.6	44.0												
	SC	45.5	44.3	42.7	44.6	43.4	42.0	43.8	42.6	41.2	43.0	41.9	40.6												
	gpm	13.9	10.5	8.2	13.4	10.2	8.0	12.9	9.8	7.6	12.5	9.5	7.5												
	wpd	15.3	8.8	5.4	14.2	8.3	5.0	13.1	7.6	4.6	12.3	7.1	4.4												

4-Row Chilled Water Cooling

EDB	EWT	42						43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12		
74	TC	52.8	49.5	44.9	50.6	47.1	42.4	48.3	44.6	39.8	46.0	42.0	37.2			
	SC	27.2	25.7	23.6	26.2	24.6	22.5	25.1	23.5	21.5	24.1	22.4	20.4			
	gpm	13.4	10.0	7.5	12.8	9.6	7.1	12.2	9.0	6.8	11.6	8.5	6.3			
76	wpd	15.5	8.7	4.9	14.2	7.9	4.4	12.9	7.0	4.0	11.8	6.2	3.4			
	TC	52.8	49.5	45.2	50.6	47.1	42.7	48.3	44.7	40.2	45.9	42.2	37.6			
	SC	29.1	27.6	25.7	28.1	26.6	24.6	27.1	25.5	23.6	26.1	24.4	22.5			
78	gpm	13.3	10.1	7.6	12.8	9.6	7.2	12.2	9.1	6.8	11.6	8.6	6.3			
	wpd	15.3	8.8	5.0	14.2	7.9	4.5	12.9	7.1	4.0	11.8	6.3	3.5			
	TC	52.8	49.5	45.4	50.5	47.3	43.1	48.2	44.9	40.7	46.0	42.5	38.4			
80	SC	31.1	29.6	27.8	30.1	28.6	26.8	29.1	27.6	25.8	28.1	26.6	24.8			
	gpm	13.4	10.0	7.7	12.8	9.6	7.3	12.2	9.1	6.9	11.6	8.6	6.5			
	wpd	15.5	8.7	5.1	14.2	7.9	4.6	12.8	7.2	4.1	11.8	6.5	3.6			
82	TC	53.2	50.2	46.3	51.0	47.9	44.0	48.8	45.6	41.7	46.6	43.3	39.5			
	SC	33.1	31.7	30.0	32.1	30.7	29.0	31.1	29.7	28.0	30.1	28.7	27.1			
	gpm	13.4	10.1	7.8	12.9	9.7	7.4	12.4	9.2	7.0	11.8	8.8	6.7			
84	wpd	15.7	8.9	5.3	14.4	8.2	4.8	13.3	7.3	4.3	12.0	6.7	3.9			
	TC	53.0	50.2	46.6	50.8	48.0	44.5	48.7	45.7	42.4	46.5	43.6	40.2			
	SC	35.2	33.9	32.3	34.2	32.9	31.4	33.2	31.9	30.5	32.2	31.0	29.5			
86	gpm	13.4	10.1	7.9	12.9	9.7	7.5	12.3	9.3	7.2	11.8	8.8	6.8			
	wpd	15.7	8.9	5.4	14.4	8.2	4.8	13.1	7.5	4.5	12.0	6.8	4.0			
	TC	53.2	50.6	47.3	51.1	48.6	45.3	49.0	46.5	43.2	47.0	44.3	41.3			
88	SC	37.2	36.1	34.6	36.3	35.1	33.7	35.3	34.2	32.8	34.4	33.3	32.0			
	gpm	13.5	10.3	8.0	12.9	9.9	7.6	12.4	9.4	7.3	11.9	9.0	7.0			
	wpd	15.8	9.2	5.5	14.5	8.4	5.0	13.4	7.7	4.6	12.3	7.0	4.2			
90	TC	53.6	51.2	48.2	51.6	49.1	46.2	49.5	47.1	44.3	47.5	45.1	42.4			
	SC	39.4	38.3	36.9	38.4	37.3	36.1	37.5	36.4	35.2	36.6	35.5	34.4			
	gpm	13.6	10.4	8.1	13.1	9.9	7.8	12.6	9.5	7.5	12.0	9.1	7.1			
92	wpd	16.0	9.3	5.7	14.8	8.5	5.2	13.7	7.8	4.8	12.5	7.2	4.4			
	TC	54.0	51.8	49.1	52.0	49.8	47.2	50.0	47.9	45.4	48.0	46.0	43.6			
	SC	41.5	40.5	39.3	40.6	39.6	38.5	39.7	38.8	37.7	38.8	37.9	36.9			
94	gpm	13.6	10.5	8.3	13.1	10.1	8.0	12.6	9.7	7.7	12.1	9.3	7.3			
	wpd	16.0	9.5	5.9	14.8	8.8	5.5	13.7	8.2	5.1	12.6	7.5	4.7			
	TC	54.4	52.5	50.1	52.5	50.6	48.3	50.5	48.8	46.6	48.6	47.0	44.9			
96	SC	43.7	42.8	41.7	42.8	41.9	40.9	41.9	41.1	40.2	41.0	40.3	39.4			
	gpm	13.7	10.6	8.5	13.3	10.3	8.2	12.8	9.9	7.8	12.3	9.5	7.5			
	wpd	16.3	9.8	6.2	15.3	9.2	5.8	14.2	8.4	5.3	13.1	7.8	4.9			

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	55.2	53.3	50.4	53.1	51.1	48.0	50.9	48.7	45.5	48.6	46.3	43.0
	SC	29.2	28.3	26.8	28.1	27.1	25.7	27.0	26.0	24.5	26.0	24.9	23.3
	gpm	13.8	10.6	8.4	13.2	10.2	8.0	12.7	9.7	7.6	12.1	9.2	7.1
	wpd	21.0	12.5	7.8	19.4	11.4	7.0	17.8	10.4	6.3	16.1	9.4	5.6
76	TC	55.2	53.3	50.5	53.0	51.1	48.1	50.9	48.8	45.7	48.6	46.4	43.3
	SC	31.2	30.3	28.9	30.1	29.1	27.7	29.0	28.0	26.6	28.0	26.9	25.5
	gpm	13.8	10.6	8.4	13.2	10.2	8.0	12.7	9.7	7.6	12.1	9.2	7.2
	wpd	21.0	12.5	7.8	19.4	11.4	7.0	17.8	10.4	6.3	16.1	9.4	5.7
78	TC	55.2	53.4	50.6	53.0	51.2	48.3	50.9	48.9	46.0	48.7	46.6	43.6
	SC	33.2	32.3	30.9	32.1	31.2	29.8	31.0	30.1	28.7	30.0	29.0	27.6
	gpm	13.8	10.6	8.4	13.2	10.2	8.0	12.7	9.7	7.6	12.1	9.3	7.2
	wpd	21.0	12.5	7.8	19.4	11.6	7.0	17.8	10.5	6.5	16.3	9.5	5.8
80	TC	55.6	53.8	51.3	53.4	51.7	49.0	51.3	49.5	46.8	49.1	47.2	44.4
	SC	35.2	34.3	33.1	34.1	33.2	32.0	33.1	32.2	30.9	32.0	31.1	29.8
	gpm	13.8	10.7	8.5	13.3	10.3	8.1	12.8	9.9	7.8	12.3	9.4	7.4
	wpd	21.2	12.7	8.0	19.6	11.7	7.3	18.2	10.8	6.7	16.7	9.8	6.0
82	TC	55.2	53.6	51.3	53.1	51.5	49.0	51.0	49.3	46.9	48.9	47.1	44.7
	SC	37.2	36.4	35.2	36.1	35.3	34.2	35.1	34.3	33.1	34.1	33.2	32.1
	gpm	13.7	10.7	8.5	13.2	10.2	8.1	12.7	9.8	7.8	12.2	9.3	7.4
	wpd	20.8	12.7	8.0	19.2	11.6	7.3	17.8	10.7	6.7	16.5	9.7	6.1
84	TC	55.3	53.9	51.7	53.3	51.8	49.6	51.2	49.7	47.5	49.1	47.6	45.4
	SC	39.2	38.5	37.4	38.2	37.5	36.4	37.2	36.5	35.4	36.2	35.5	34.4
	gpm	13.8	10.7	8.5	13.2	10.3	8.2	12.7	9.9	7.9	12.2	9.5	7.6
	wpd	21.0	12.7	8.0	19.4	11.7	7.5	18.0	10.8	6.9	16.5	9.9	6.3
86	TC	55.5	54.2	52.2	53.5	52.2	50.2	51.5	50.1	48.1	49.4	48.1	46.1
	SC	41.3	40.7	39.7	40.3	39.7	38.7	39.3	38.7	37.7	38.3	37.7	36.8
	gpm	13.8	10.8	8.7	13.3	10.4	8.3	12.8	10.0	8.0	12.3	9.5	7.6
	wpd	21.0	12.9	8.3	19.6	11.9	7.7	18.2	11.0	7.0	16.7	10.1	6.5
88	TC	55.7	54.5	52.7	53.7	52.6	50.8	51.8	50.6	48.8	49.8	48.6	47.0
	SC	43.4	42.8	41.9	42.4	41.9	41.0	41.5	40.9	40.0	40.5	39.9	39.1
	gpm	13.8	10.8	8.7	13.4	10.5	8.5	12.9	10.1	8.1	12.4	9.7	7.8
	wpd	21.2	13.0	8.4	19.8	12.2	7.9	18.4	11.3	7.3	17.1	10.4	6.7
90	TC	56.0	54.9	53.3	54.0	53.0	51.5	52.1	51.1	49.6	50.2	49.2	47.8
	SC	45.6	45.0	44.2	44.6	44.1	43.3	43.6	43.1	42.4	42.7	42.2	41.5
	gpm	13.9	10.9	8.9	13.4	10.6	8.5	12.9	10.2	8.2	12.5	9.8	8.0
	wpd	21.4	13.2	8.7	20.0	12.4	8.0	18.6	11.4	7.5	17.2	10.7	7.0

2-Row Chilled Water Cooling

EDB	EWT	43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	45.7	41.9	37.3	43.7	39.9	35.0	41.6	37.9	32.7	39.5	35.8	30.2						
	SC	20.8	19.3	17.5	20.0	18.5	16.7	19.2	17.7	15.8	18.4	16.9	14.9						
	gpm	11.6	8.5	6.3	11.0	8.0	5.9	10.6	7.7	5.5	10.0	7.3	5.1						
	wpd	19.3	10.4	5.7	17.5	9.3	5.0	16.1	8.4	4.4	14.4	7.6	3.8						
76	TC	45.8	42.2	37.7	43.9	40.1	35.3	41.8	38.0	33.0	39.8	36.0	30.4						
	SC	22.9	21.4	19.6	22.1	20.6	18.7	21.3	19.8	17.9	20.5	19.0	16.9						
	gpm	11.6	8.5	6.4	11.1	8.1	6.0	10.6	7.7	5.6	10.1	7.3	5.1						
	wpd	19.3	10.4	5.9	17.8	9.5	5.2	16.1	8.6	4.5	14.7	7.6	3.8						
78	TC	46.1	42.4	37.7	44.0	40.3	35.4	42.0	38.2	33.0	40.0	36.0	30.6						
	SC	24.9	23.5	21.6	24.1	22.6	20.8	23.3	21.8	19.8	22.5	21.0	18.9						
	gpm	11.7	8.6	6.4	11.1	8.1	6.0	10.7	7.7	5.5	10.1	7.3	5.1						
	wpd	19.6	10.6	5.9	17.8	9.5	5.2	16.3	8.6	4.4	14.7	7.6	3.8						
80	TC	46.2	42.4	37.7	44.1	40.3	35.5	42.0	38.2	33.2	39.9	36.0	31.1						
	SC	27.0	25.5	23.6	26.2	24.6	22.8	25.3	23.8	21.9	24.5	23.0	21.1						
	gpm	11.7	8.6	6.4	11.1	8.2	6.0	10.6	7.7	5.6	10.1	7.3	5.2						
	wpd	19.6	10.6	5.9	17.8	9.7	5.2	16.1	8.6	4.5	14.7	7.6	3.9						
82	TC	46.1	42.3	38.0	44.0	40.2	35.9	41.9	38.2	33.9	39.8	36.1	31.9						
	SC	29.0	27.4	25.7	28.1	26.6	24.9	27.3	25.8	24.1	26.5	25.1	23.4						
	gpm	11.7	8.5	6.4	11.1	8.1	6.1	10.6	7.7	5.7	10.0	7.3	5.4						
	wpd	19.6	10.4	5.9	17.8	9.5	5.3	16.1	8.6	4.6	14.4	7.7	4.1						
84	TC	46.0	42.4	38.6	43.9	40.4	36.6	41.9	38.6	34.9	39.9	36.7	33.0						
	SC	30.9	29.4	27.9	30.1	28.7	27.2	29.3	28.0	26.5	28.5	27.2	25.7						
	gpm	11.7	8.6	6.5	11.1	8.2	6.2	10.6	7.8	5.9	10.1	7.4	5.6						
	wpd	19.6	10.6	6.0	17.8	9.7	5.4	16.1	8.8	5.0	14.7	7.9	4.5						
86	TC	46.0	42.7	39.4	44.1	40.9	37.7	42.2	39.2	35.8	40.3	37.6	34.2						
	SC	32.9	31.6	30.2	32.2	30.9	29.5	31.5	30.2	28.8	30.7	29.5	28.1						
	gpm	11.7	8.7	6.6	11.2	8.3	6.4	10.7	8.0	6.1	10.3	7.7	5.8						
	wpd	19.6	10.8	6.3	18.0	9.9	5.9	16.5	9.1	5.3	15.1	8.4	4.8						
88	TC	46.3	43.4	40.3	44.5	41.7	38.8	42.8	40.0	37.1	41.0	38.4	35.4						
	SC	35.1	33.8	32.5	34.3	33.1	31.8	33.7	32.5	31.1	32.9	31.8	30.5						
	gpm	11.7	8.8	6.8	11.2	8.4	6.5	10.8	8.1	6.3	10.3	7.8	6.0						
	wpd	19.6	11.0	6.6	18.0	10.2	6.2	16.8	9.5	5.7	15.4	8.8	5.2						
90	TC	46.9	44.2	41.5	45.2	42.6	39.9	43.6	41.0	38.3	42.0	39.4	36.9						
	SC	37.3	36.1	34.8	36.6	35.4	34.1	35.9	34.7	33.5	35.2	34.1	33.0						
	gpm	11.8	9.0	7.0	11.4	8.7	6.7	11.0	8.3	6.5	10.7	8.0	6.2						
	wpd	20.1	11.6	7.1	18.8	10.8	6.5	17.5	9.9	6.0	16.3	9.1	5.6						

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	58.8	54.7	48.7	56.4	52.1	45.9	53.9	49.5	43.0	51.5	46.8	40.0
	SC	26.5	24.8	22.3	25.5	23.7	21.2	24.4	22.6	20.1	23.5	21.6	19.0
	gpm	14.9	11.1	8.2	14.3	10.5	7.7	13.6	10.0	7.3	13.0	9.5	6.7
	wpd	17.5	9.8	5.4	16.2	8.8	4.7	14.7	8.0	4.2	13.5	7.1	3.6
76	TC	58.9	54.9	48.7	56.5	52.3	46.0	54.1	49.6	43.1	51.6	46.9	40.1
	SC	28.8	27.1	24.6	27.8	26.0	23.5	26.7	24.9	22.3	25.7	23.8	21.2
	gpm	14.9	11.1	8.2	14.3	10.6	7.8	13.7	10.0	7.3	13.0	9.5	6.8
	wpd	17.7	9.8	5.4	16.2	9.0	4.8	14.9	8.0	4.2	13.5	7.1	3.7
78	TC	59.1	55.0	48.8	56.6	52.3	46.0	54.2	49.7	43.3	51.6	46.9	40.4
	SC	31.0	29.3	26.8	30.0	28.2	25.7	29.0	27.2	24.6	27.9	26.0	23.5
	gpm	14.9	11.1	8.2	14.4	10.6	7.8	13.7	10.0	7.3	13.0	9.5	6.8
	wpd	17.7	9.8	5.4	16.4	9.0	4.8	14.9	8.0	4.2	13.5	7.1	3.7
80	TC	59.1	54.8	49.0	56.6	52.3	46.4	54.1	49.7	43.8	51.6	47.0	41.0
	SC	33.3	31.5	29.1	32.2	30.4	28.1	31.2	29.4	27.0	30.2	28.3	26.0
	gpm	14.9	11.1	8.3	14.4	10.6	7.8	13.7	10.0	7.4	13.0	9.5	6.9
	wpd	17.7	9.8	5.5	16.4	9.0	4.8	14.9	8.0	4.3	13.5	7.2	3.8
82	TC	59.0	54.9	49.4	56.6	52.4	46.9	54.1	49.9	44.5	51.6	47.4	42.1
	SC	35.5	33.7	31.5	34.4	32.7	30.4	33.4	31.7	29.5	32.4	30.7	28.5
	gpm	14.9	11.1	8.3	14.4	10.6	7.9	13.7	10.1	7.5	13.1	9.5	7.1
	wpd	17.7	9.8	5.5	16.4	9.0	4.9	14.9	8.1	4.4	13.7	7.2	4.0
84	TC	58.9	55.2	50.2	56.6	52.8	47.8	54.2	50.4	45.3	51.9	48.1	43.1
	SC	37.6	36.0	34.0	36.6	35.1	33.0	35.6	34.1	32.0	34.7	33.1	31.1
	gpm	14.9	11.2	8.5	14.4	10.7	8.1	13.8	10.2	7.6	13.1	9.7	7.3
	wpd	17.5	10.0	5.7	16.4	9.1	5.1	15.1	8.3	4.6	13.7	7.5	4.2
86	TC	59.1	55.6	50.9	56.8	53.4	48.7	54.5	51.1	46.5	52.3	48.8	44.3
	SC	39.9	38.4	36.4	38.9	37.5	35.5	38.0	36.5	34.6	37.0	35.6	33.8
	gpm	14.9	11.2	8.6	14.4	10.9	8.2	13.8	10.4	7.9	13.2	9.9	7.5
	wpd	17.7	10.0	5.9	16.4	9.4	5.4	15.1	8.5	4.9	13.8	7.7	4.4
88	TC	59.4	56.3	51.9	57.3	54.1	49.7	55.1	51.9	47.6	52.9	49.7	45.6
	SC	42.2	40.9	39.0	41.3	39.9	38.1	40.4	39.0	37.3	39.5	38.1	36.4
	gpm	15.0	11.4	8.7	14.5	11.0	8.4	13.9	10.5	8.1	13.4	10.0	7.7
	wpd	17.9	10.3	6.0	16.8	9.5	5.6	15.4	8.7	5.1	14.2	8.0	4.7
90	TC	60.0	57.1	53.0	57.9	54.9	50.9	55.8	52.7	49.0	53.6	50.7	47.1
	SC	44.6	43.4	41.6	43.7	42.5	40.8	42.8	41.5	39.9	41.9	40.7	39.1
	gpm	15.2	11.5	9.0	14.7	11.1	8.6	14.1	10.7	8.3	13.5	10.3	8.0
	wpd	18.3	10.6	6.4	17.1	9.8	5.9	15.8	9.1	5.5	14.5	8.4	5.0

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	59.2	56.5	52.3	56.9	54.2	49.8	54.7	51.7	47.2	52.4	49.3	44.6
	SC	27.1	25.9	24.0	26.0	24.8	22.9	25.0	23.7	21.8	24.0	22.7	20.7
	gpm	15.0	11.4	8.8	14.4	11.0	8.4	13.9	10.5	8.0	13.3	10.0	7.5
	wpd	19.4	11.3	6.8	17.9	10.5	6.1	16.7	9.5	5.5	15.3	8.7	4.9
76	TC	59.2	56.5	52.3	57.0	54.2	49.8	54.8	51.8	47.2	52.4	49.3	44.6
	SC	29.1	27.8	26.0	28.1	26.8	24.9	27.1	25.8	23.8	26.0	24.7	22.7
	gpm	15.0	11.4	8.8	14.4	11.0	8.4	13.9	10.5	8.0	13.3	10.0	7.5
	wpd	19.4	11.3	6.8	17.9	10.5	6.1	16.7	9.5	5.5	15.3	8.7	4.9
78	TC	59.3	56.5	52.3	57.0	54.2	50.0	54.7	51.7	47.5	52.3	49.4	45.1
	SC	31.1	29.8	28.0	30.1	28.8	26.9	29.0	27.7	25.8	28.0	26.7	24.8
	gpm	15.0	11.4	8.8	14.4	11.0	8.4	13.8	10.5	8.0	13.2	10.0	7.5
	wpd	19.6	11.3	6.8	17.9	10.5	6.1	16.5	9.5	5.5	15.2	8.7	4.9
80	TC	59.3	56.5	52.4	57.0	54.2	50.0	54.7	51.7	47.5	52.3	49.4	45.1
	SC	33.1	31.8	30.0	32.0	30.8	29.0	31.0	29.7	27.9	30.0	28.7	26.9
	gpm	15.0	11.4	8.8	14.5	10.9	8.4	13.8	10.4	8.0	13.2	10.0	7.6
	wpd	19.6	11.3	6.8	18.1	10.4	6.1	16.5	9.4	5.5	15.2	8.7	5.0
82	TC	59.2	56.5	52.7	57.0	54.3	50.4	54.7	51.9	47.9	52.4	49.6	45.6
	SC	35.0	33.8	32.1	34.0	32.8	31.1	33.0	31.8	30.1	32.0	30.7	29.1
	gpm	15.0	11.4	8.9	14.5	11.0	8.5	13.8	10.5	8.1	13.2	10.0	7.7
	wpd	19.6	11.3	6.9	18.1	10.5	6.2	16.5	9.5	5.7	15.2	8.7	5.1
84	TC	59.3	56.7	53.0	57.0	54.5	50.8	54.8	52.2	48.5	52.6	49.9	46.2
	SC	37.0	35.9	34.2	36.0	34.9	33.3	35.0	33.9	32.3	34.0	32.9	31.3
	gpm	15.0	11.5	9.0	14.5	11.1	8.6	13.9	10.6	8.2	13.3	10.1	7.8
	wpd	19.6	11.5	7.0	18.1	10.6	6.3	16.7	9.7	5.8	15.3	8.9	5.3
86	TC	59.4	56.9	53.5	57.2	54.8	51.3	55.0	52.6	49.2	52.8	50.4	47.0
	SC	39.0	37.9	36.4	38.0	37.0	35.5	37.1	36.0	34.6	36.1	35.0	33.6
	gpm	15.0	11.6	9.1	14.5	11.1	8.6	13.9	10.6	8.3	13.4	10.2	7.9
	wpd	19.6	11.6	7.1	18.3	10.8	6.5	16.9	9.8	5.9	15.5	9.0	5.4
88	TC	59.6	57.3	54.2	57.5	55.1	52.1	55.3	53.1	50.0	53.2	51.0	47.9
	SC	41.1	40.1	38.7	40.1	39.1	37.8	39.2	38.2	36.9	38.2	37.3	36.0
	gpm	15.1	11.6	9.1	14.6	11.1	8.8	14.0	10.7	8.4	13.5	10.4	8.1
	wpd	19.8	11.6	7.2	18.5	10.8	6.7	17.0	9.9	6.1	15.8	9.3	5.6
90	TC	59.9	57.7	54.8	57.7	55.7	52.8	55.7	53.6	50.8	53.6	51.6	48.8
	SC	43.2	42.2	40.9	42.2	41.3	40.1	41.3	40.4	39.2	40.4	39.5	38.3
	gpm	15.2	11.7	9.3	14.6	11.3	8.9	14.0	10.9	8.6	13.6	10.4	8.3
	wpd	19.9	11.9	7.5	18.5	11.0	6.9	17.0	10.2	6.3	16.0	9.4	5.9

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	61.5	59.8	57.3	59.4	57.5	55.0	57.2	55.3	52.5	55.0	52.9	50.0
	SC	29.2	28.3	27.1	28.1	27.2	25.9	27.0	26.1	24.8	25.9	25.0	23.6
	gpm	15.3	11.9	9.5	14.8	11.4	9.1	14.2	11.0	8.7	13.7	10.6	8.3
	wpd	26.1	15.8	10.1	24.2	14.5	9.2	22.5	13.5	8.4	20.8	12.4	7.7
76	TC	61.6	59.8	57.3	59.4	57.6	55.0	57.2	55.3	52.6	55.0	53.0	50.1
	SC	31.2	30.3	29.1	30.1	29.2	28.0	29.0	28.1	26.8	28.0	27.0	25.7
	gpm	15.3	11.9	9.5	14.8	11.4	9.1	14.2	11.0	8.7	13.7	10.6	8.3
	wpd	26.1	15.6	9.9	24.2	14.5	9.2	22.5	13.5	8.4	20.8	12.4	7.7
78	TC	61.6	59.8	57.4	59.4	57.5	55.0	57.2	55.3	52.7	55.0	53.0	50.2
	SC	33.2	32.3	31.1	32.1	31.2	30.0	31.0	30.1	28.9	30.0	29.0	27.7
	gpm	15.3	11.9	9.5	14.8	11.4	9.1	14.2	11.0	8.7	13.7	10.6	8.3
	wpd	26.1	15.6	9.9	24.2	14.5	9.2	22.5	13.5	8.4	20.8	12.4	7.7
80	TC	61.5	59.8	57.5	59.4	57.5	55.2	57.2	55.3	52.8	55.0	53.0	50.4
	SC	35.2	34.3	33.1	34.1	33.2	32.0	33.0	32.1	30.9	31.9	31.0	29.8
	gpm	15.3	11.9	9.5	14.8	11.4	9.1	14.2	11.0	8.7	13.7	10.5	8.3
	wpd	26.1	15.6	10.1	24.2	14.5	9.2	22.5	13.3	8.4	20.8	12.2	7.7
82	TC	61.5	59.8	57.6	59.3	57.6	55.3	57.2	55.4	53.0	55.0	53.1	50.7
	SC	37.1	36.3	35.2	36.1	35.2	34.1	35.0	34.2	33.0	33.9	33.1	31.9
	gpm	15.3	11.9	9.5	14.7	11.4	9.2	14.2	11.0	8.8	13.7	10.6	8.4
	wpd	25.8	15.8	10.1	24.0	14.5	9.4	22.5	13.5	8.6	20.8	12.4	7.8
84	TC	61.5	59.9	57.8	59.4	57.7	55.6	57.2	55.6	53.3	55.0	53.3	51.0
	SC	39.1	38.3	37.3	38.1	37.3	36.2	37.0	36.2	35.2	36.0	35.2	34.1
	gpm	15.3	11.9	9.6	14.7	11.5	9.2	14.2	11.0	8.9	13.6	10.6	8.5
	wpd	25.8	15.8	10.2	24.0	14.7	9.4	22.3	13.5	8.7	20.6	12.5	7.9
86	TC	61.5	60.0	58.0	59.4	57.9	55.9	57.3	55.7	53.7	55.2	53.6	51.5
	SC	41.1	40.4	39.4	40.1	39.3	38.4	39.1	38.3	37.3	38.0	37.3	36.3
	gpm	15.3	11.9	9.6	14.8	11.5	9.3	14.2	11.1	8.9	13.7	10.7	8.5
	wpd	25.8	15.8	10.2	24.2	14.7	9.5	22.5	13.7	8.8	20.8	12.7	8.0
88	TC	61.6	60.2	58.3	59.5	58.1	56.2	57.5	56.0	54.1	55.3	53.9	52.0
	SC	43.2	42.5	41.6	42.2	41.4	40.5	41.1	40.4	39.5	40.1	39.4	38.5
	gpm	15.3	12.0	9.7	14.8	11.6	9.3	14.3	11.2	9.0	13.8	10.8	8.6
	wpd	26.1	15.9	10.4	24.2	14.9	9.7	22.7	13.8	9.0	21.0	12.9	8.2
90	TC	61.7	60.4	58.8	59.7	58.3	56.7	57.7	56.3	54.7	55.6	54.2	52.6
	SC	45.3	44.6	43.8	44.2	43.6	42.8	43.2	42.6	41.8	42.2	41.6	40.8
	gpm	15.3	12.0	9.7	14.9	11.6	9.4	14.3	11.2	9.1	13.8	10.8	8.7
	wpd	26.1	15.9	10.5	24.5	14.9	9.8	22.7	13.8	9.1	21.2	12.9	8.4

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	51.1	47.4	43.5	49.2	45.3	41.4	47.1	43.2	39.1	45.0	41.0	36.7
	SC	20.2	18.7	17.2	19.4	17.9	16.4	18.6	17.1	15.6	17.8	16.3	14.7
	gpm	12.9	9.6	7.3	12.5	9.2	6.9	11.9	8.8	6.6	11.4	8.3	6.2
	wpd	24.1	13.3	7.7	22.3	12.0	6.9	20.4	11.0	6.3	18.6	9.9	5.4
76	TC	51.2	47.5	43.6	49.2	45.4	41.6	47.2	43.4	39.4	45.1	41.2	37.0
	SC	22.2	20.8	19.3	21.4	20.0	18.5	20.6	19.2	17.7	19.8	18.4	16.8
	gpm	12.9	9.6	7.3	12.4	9.2	7.0	12.0	8.8	6.6	11.4	8.4	6.2
	wpd	24.1	13.3	7.7	22.1	12.2	7.1	20.7	11.0	6.3	18.8	10.1	5.6
78	TC	51.4	47.7	43.9	49.4	45.6	41.8	47.3	43.6	39.6	45.3	41.4	37.3
	SC	24.3	22.8	21.4	23.5	22.1	20.6	22.7	21.3	19.8	21.9	20.5	18.9
	gpm	13.0	9.6	7.4	12.5	9.2	7.1	11.9	8.8	6.7	11.5	8.4	6.3
	wpd	24.4	13.3	7.9	22.3	12.2	7.2	20.4	11.2	6.5	19.1	10.1	5.7
80	TC	51.7	47.9	44.1	49.6	45.8	42.0	47.6	43.8	39.8	45.5	41.6	37.3
	SC	26.4	24.9	23.4	25.6	24.1	22.6	24.8	23.3	21.8	24.0	22.5	20.9
	gpm	13.1	9.7	7.4	12.5	9.2	7.1	12.0	8.8	6.7	11.4	8.4	6.3
	wpd	24.7	13.5	7.9	22.6	12.2	7.2	20.7	11.2	6.5	18.8	10.2	5.7
82	TC	51.9	48.1	44.2	49.8	45.9	42.0	47.7	43.8	39.8	45.6	41.7	37.4
	SC	28.5	27.0	25.5	27.7	26.1	24.6	26.8	25.3	23.8	26.0	24.5	22.9
	gpm	13.1	9.7	7.5	12.6	9.3	7.1	12.1	8.8	6.7	11.5	8.4	6.3
	wpd	24.7	13.5	8.1	22.9	12.5	7.2	20.9	11.2	6.5	19.1	10.2	5.7
84	TC	52.0	48.1	44.1	49.9	45.9	42.0	47.7	43.8	39.9	45.6	41.5	37.6
	SC	30.5	29.0	27.4	29.7	28.1	26.6	28.9	27.3	25.8	28.0	26.5	25.1
	gpm	13.2	9.7	7.4	12.6	9.3	7.1	12.1	8.8	6.7	11.5	8.4	6.3
	wpd	25.0	13.5	7.9	22.9	12.5	7.2	20.9	11.2	6.5	19.1	10.2	5.7
86	TC	51.9	48.0	44.2	49.8	45.8	42.1	47.6	43.7	40.2	45.5	41.7	38.3
	SC	32.5	30.9	29.4	31.7	30.1	28.7	30.8	29.3	28.0	30.0	28.5	27.2
	gpm	13.2	9.7	7.5	12.6	9.3	7.1	12.1	8.8	6.8	11.5	8.4	6.5
	wpd	25.0	13.5	8.1	22.9	12.5	7.2	20.9	11.2	6.6	19.1	10.2	6.0
88	TC	51.8	47.9	44.5	49.7	45.9	42.7	47.5	43.9	40.8	45.5	42.1	39.1
	SC	34.5	32.9	31.6	33.6	32.1	30.9	32.8	31.4	30.2	32.0	30.7	29.5
	gpm	13.1	9.7	7.5	12.5	9.3	7.3	12.1	8.9	6.9	11.5	8.5	6.6
	wpd	24.7	13.5	8.1	22.6	12.5	7.6	20.9	11.4	6.8	19.1	10.4	6.3
90	TC	51.6	48.2	45.1	49.7	46.3	43.4	47.7	44.4	41.7	45.7	42.7	39.9
	SC	36.4	35.0	33.8	35.6	34.3	33.1	34.9	33.6	32.4	34.1	32.9	31.8
	gpm	13.0	9.8	7.6	12.6	9.4	7.3	12.1	9.0	7.0	11.5	8.7	6.7
	wpd	24.4	13.8	8.2	22.9	12.7	7.7	20.9	11.6	7.1	19.1	10.8	6.5

3-Row Chilled Water Cooling

EDB	EWT	43						44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	65.8	61.9	56.6	63.4	59.4	53.9	60.9	56.9	51.2	58.4	54.4	48.3
	SC	26.2	24.5	22.4	25.1	23.5	21.3	24.1	22.5	20.2	23.1	21.5	19.1
	gpm	16.7	12.5	9.5	16.0	12.0	9.0	15.4	11.5	8.6	14.8	11.0	8.1
	wpd	22.1	12.5	7.2	20.4	11.5	6.5	18.7	10.6	5.9	17.3	9.7	5.3
76	TC	65.8	62.0	56.8	63.4	59.5	54.1	60.9	57.0	51.4	58.4	54.5	48.5
	SC	28.4	26.8	24.7	27.4	25.8	23.6	26.3	24.8	22.6	25.3	23.8	21.5
	gpm	16.7	12.5	9.5	16.0	12.0	9.1	15.4	11.5	8.7	14.8	11.0	8.2
	wpd	22.1	12.5	7.2	20.4	11.5	6.6	18.9	10.6	6.0	17.3	9.7	5.4
78	TC	65.9	62.1	56.9	63.5	59.6	54.2	61.0	57.1	51.4	58.5	54.6	48.6
	SC	30.7	29.1	27.0	29.6	28.1	25.9	28.6	27.0	24.8	27.6	26.0	23.7
	gpm	16.7	12.6	9.6	16.1	12.1	9.1	15.4	11.5	8.6	14.8	11.0	8.2
	wpd	22.1	12.6	7.4	20.6	11.7	6.6	18.9	10.6	5.9	17.3	9.7	5.4
80	TC	66.0	62.2	57.0	63.6	59.7	54.3	61.2	57.2	51.5	58.6	54.6	48.6
	SC	32.9	31.3	29.2	31.9	30.3	28.1	30.9	29.3	27.1	29.9	28.3	25.9
	gpm	16.8	12.6	9.6	16.1	12.1	9.1	15.5	11.5	8.7	14.9	11.0	8.2
	wpd	22.3	12.6	7.4	20.6	11.7	6.6	19.1	10.6	6.0	17.5	9.7	5.4
82	TC	66.1	62.3	57.0	63.7	59.8	54.2	61.2	57.2	51.6	58.7	54.6	48.8
	SC	35.2	33.6	31.4	34.2	32.5	30.3	33.1	31.5	29.3	32.1	30.5	28.2
	gpm	16.8	12.6	9.6	16.1	12.1	9.1	15.5	11.6	8.7	14.9	11.0	8.2
	wpd	22.3	12.6	7.4	20.6	11.7	6.6	19.1	10.7	6.0	17.5	9.7	5.4
84	TC	66.1	62.3	57.1	63.7	59.7	54.4	61.2	57.2	51.8	58.6	54.7	49.2
	SC	37.4	35.8	33.7	36.4	34.7	32.6	35.3	33.7	31.6	34.3	32.7	30.6
	gpm	16.8	12.6	9.6	16.1	12.1	9.2	15.5	11.6	8.7	14.9	11.0	8.3
	wpd	22.3	12.6	7.4	20.6	11.7	6.7	19.1	10.7	6.0	17.5	9.7	5.5
86	TC	66.0	62.2	57.4	63.6	59.7	54.9	61.0	57.2	52.3	58.6	54.9	49.9
	SC	39.5	38.0	36.0	38.5	36.9	35.0	37.5	35.9	34.0	36.5	35.0	33.1
	gpm	16.7	12.6	9.7	16.1	12.0	9.3	15.4	11.5	8.9	14.9	11.1	8.5
	wpd	22.1	12.6	7.5	20.6	11.5	6.9	18.7	10.6	6.3	17.5	9.8	5.7
88	TC	65.9	62.3	57.8	63.5	60.0	55.5	61.1	57.6	53.2	58.7	55.2	50.7
	SC	41.7	40.2	38.4	40.7	39.3	37.4	39.7	38.3	36.5	38.7	37.4	35.6
	gpm	16.7	12.6	9.7	16.0	12.1	9.4	15.4	11.7	9.0	14.9	11.2	8.5
	wpd	22.1	12.6	7.5	20.4	11.7	7.0	18.9	10.9	6.4	17.5	10.0	5.8
90	TC	66.0	62.7	58.6	63.7	60.4	56.2	61.4	58.2	54.0	59.0	55.9	51.7
	SC	44.0	42.6	40.9	43.0	41.6	39.9	42.0	40.7	39.0	41.1	39.8	38.1
	gpm	16.7	12.7	9.9	16.1	12.2	9.5	15.5	11.8	9.1	14.9	11.3	8.7
	wpd	22.1	12.8	7.7	20.6	11.8	7.1	19.1	11.0	6.6	17.7	10.1	6.0

4-Row Chilled Water Cooling

EDB	EWT	42						43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12		
74	TC	65.9	63.2	59.7	63.7	60.8	57.3	61.4	58.5	54.8	59.1	56.1	52.2			
	SC	27.0	26.7	24.2	26.0	24.7	23.2	24.9	23.7	22.1	23.9	22.7	21.0			
	gpm	16.7	12.8	10.1	16.1	12.3	9.7	15.5	11.8	9.3	15.0	11.4	8.8			
	wpd	24.1	14.2	8.8	22.5	13.1	8.2	20.7	12.0	7.5	19.4	11.2	6.7			
76	TC	65.9	63.2	59.8	63.7	60.9	57.4	61.4	58.5	54.9	59.1	56.1	52.3			
	SC	29.0	27.8	26.3	28.0	26.7	25.2	26.9	25.7	24.1	25.9	24.7	23.0			
	gpm	16.7	12.8	10.1	16.1	12.3	9.7	15.5	11.9	9.3	14.9	11.4	8.8			
	wpd	24.1	14.2	8.8	22.5	13.1	8.2	20.9	12.2	7.5	19.2	11.2	6.8			
78	TC	66.0	63.2	59.8	63.7	60.9	57.4	61.4	58.6	54.9	59.1	56.1	52.3			
	SC	31.0	29.8	28.3	30.0	28.7	27.2	29.0	27.7	26.1	27.9	26.7	25.0			
	gpm	16.7	12.8	10.1	16.1	12.4	9.6	15.5	11.9	9.3	15.0	11.4	8.8			
	wpd	24.1	14.2	8.8	22.5	13.3	8.0	20.9	12.2	7.5	19.4	11.2	6.8			
80	TC	66.0	63.3	59.8	63.8	60.9	57.4	61.5	58.6	54.8	59.1	56.2	52.3			
	SC	33.0	31.8	30.3	32.0	30.7	29.2	31.0	29.7	28.1	29.9	28.7	27.0			
	gpm	16.7	12.8	10.1	16.1	12.4	9.7	15.5	11.9	9.3	15.0	11.4	8.8			
	wpd	24.1	14.2	8.8	22.5	13.3	8.2	20.9	12.2	7.5	19.4	11.2	6.8			
82	TC	66.0	63.3	59.8	63.8	60.9	57.4	61.5	58.5	54.9	59.1	56.1	52.4			
	SC	35.0	33.8	32.3	34.0	32.7	31.2	32.9	31.7	30.1	31.9	30.6	29.1			
	gpm	16.8	12.8	10.1	16.2	12.4	9.7	15.5	11.9	9.3	15.0	11.4	8.8			
	wpd	24.3	14.2	8.9	22.7	13.3	8.2	20.9	12.2	7.5	19.4	11.2	6.8			
84	TC	66.0	63.2	59.9	63.7	60.9	57.5	61.4	58.6	55.1	59.0	56.2	52.7			
	SC	37.0	35.7	34.3	35.9	34.7	33.2	34.9	33.7	32.2	33.9	32.6	31.2			
	gpm	16.8	12.8	10.1	16.1	12.4	9.7	15.5	11.9	9.3	15.0	11.4	8.9			
	wpd	24.3	14.2	8.9	22.5	13.3	8.2	20.9	12.2	7.5	19.4	11.2	6.9			
86	TC	66.0	63.2	60.1	63.7	61.0	57.8	61.4	58.7	55.4	59.1	56.4	53.0			
	SC	38.9	37.7	36.3	37.9	36.7	35.3	36.9	35.7	34.3	35.8	34.7	33.3			
	gpm	16.7	12.8	10.1	16.1	12.4	9.8	15.5	11.9	9.3	15.0	11.4	8.9			
	wpd	24.1	14.2	8.9	22.5	13.3	8.3	20.9	12.3	7.6	19.4	11.3	6.9			
88	TC	65.9	63.3	60.3	63.7	61.1	58.0	61.5	58.8	55.8	59.2	56.5	53.5			
	SC	40.9	39.7	38.4	39.9	38.7	37.4	38.9	37.7	36.4	37.9	36.7	35.5			
	gpm	16.7	12.8	10.2	16.2	12.4	9.8	15.6	11.9	9.4	15.0	11.4	9.0			
	wpd	24.1	14.2	9.0	22.7	13.3	8.3	21.1	12.2	7.7	19.6	11.3	7.0			
90	TC	66.0	63.5	60.7	63.8	61.3	58.5	61.6	59.1	56.3	59.4	56.9	54.1			
	SC	42.9	41.8	40.5	41.9	40.8	39.6	40.9	39.8	38.6	39.9	38.9	37.7			
	gpm	16.8	12.9	10.3	16.2	12.4	9.9	15.6	12.0	9.5	15.0	11.5	9.1			
	wpd	24.3	14.4	9.2	22.7	13.4	8.4	21.1	12.5	7.8	19.6	11.5	7.2			

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	68.1	66.3	64.3	66.0	64.1	62.0	63.8	61.9	59.7	61.6	59.5	57.3												
	SC	29.1	28.2	27.2	28.0	27.1	26.1	27.0	26.0	25.0	25.9	24.9	23.9												
	gpm	17.0	13.2	10.6	16.4	12.7	10.3	15.9	12.3	9.9	15.3	11.9	9.5												
	wpd	31.9	19.2	12.5	29.9	18.0	11.7	27.9	16.9	10.8	26.1	15.6	9.9												
76	TC	68.2	66.4	64.4	66.0	64.2	62.1	63.8	61.9	59.8	61.6	59.6	57.4												
	SC	31.1	30.2	29.3	30.1	29.1	28.2	29.0	28.0	27.1	27.9	27.0	25.9												
	gpm	17.0	13.2	10.7	16.4	12.7	10.3	15.9	12.3	10.0	15.3	11.9	9.5												
	wpd	31.9	19.4	12.7	29.9	18.0	11.7	27.9	16.7	11.0	26.1	15.6	10.1												
78	TC	68.2	66.4	64.5	66.0	64.2	62.2	63.9	61.9	59.8	61.6	59.6	57.4												
	SC	33.1	32.3	31.3	32.1	31.2	30.2	31.0	30.1	29.1	29.9	29.0	28.0												
	gpm	17.0	13.2	10.7	16.4	12.7	10.3	15.9	12.3	9.9	15.3	11.9	9.5												
	wpd	31.9	19.4	12.7	29.9	18.0	11.7	27.9	16.9	10.8	26.1	15.6	10.1												
80	TC	68.1	66.4	64.5	66.0	64.2	62.2	63.9	62.0	59.8	61.6	59.6	57.5												
	SC	35.1	34.3	33.3	34.1	33.2	32.2	33.0	32.1	31.1	31.9	31.0	30.0												
	gpm	16.9	13.2	10.7	16.4	12.7	10.3	15.9	12.3	10.0	15.3	11.9	9.5												
	wpd	31.7	19.4	12.7	29.9	18.0	11.7	27.9	16.9	11.0	26.1	15.6	10.1												
82	TC	68.1	66.4	64.5	66.0	64.2	62.2	63.9	62.0	59.9	61.6	59.6	57.5												
	SC	37.1	36.3	35.3	36.1	35.2	34.2	35.0	34.1	33.1	33.9	33.0	32.0												
	gpm	16.9	13.2	10.7	16.4	12.7	10.3	15.9	12.3	10.0	15.3	11.9	9.5												
	wpd	31.7	19.4	12.7	29.7	18.0	11.7	27.9	16.9	11.0	26.1	15.6	10.1												
84	TC	68.1	66.4	64.5	66.0	64.2	62.3	63.8	62.0	60.0	61.6	59.7	57.7												
	SC	39.1	38.3	37.3	38.0	37.2	36.2	37.0	36.1	35.2	35.9	35.0	34.1												
	gpm	16.9	13.2	10.7	16.4	12.8	10.4	15.8	12.3	10.0	15.3	11.9	9.5												
	wpd	31.7	19.4	12.7	29.7	18.2	11.9	27.7	16.9	11.0	26.1	15.6	10.1												
86	TC	68.1	66.4	64.6	65.9	64.2	62.4	63.8	62.0	60.2	61.6	59.8	57.9												
	SC	41.1	40.3	39.4	40.0	39.2	38.3	39.0	38.1	37.2	37.9	37.1	36.2												
	gpm	16.9	13.2	10.7	16.4	12.8	10.4	15.8	12.3	10.0	15.3	11.9	9.6												
	wpd	31.7	19.4	12.7	29.7	18.2	11.9	27.7	16.9	11.1	25.8	15.8	10.2												
88	TC	68.1	66.5	64.7	65.9	64.3	62.6	63.8	62.1	60.3	61.6	59.9	58.1												
	SC	43.1	42.3	41.5	42.0	41.2	40.4	41.0	40.2	39.3	39.9	39.1	38.3												
	gpm	16.9	13.2	10.7	16.4	12.8	10.4	15.9	12.4	10.0	15.3	11.9	9.7												
	wpd	31.7	19.4	12.7	29.7	18.2	11.9	27.9	17.1	11.0	25.8	15.8	10.4												
90	TC	68.1	66.6	64.9	66.0	64.5	62.8	63.9	62.3	60.6	61.7	60.1	58.3												
	SC	45.1	44.4	43.5	44.1	43.3	42.5	43.0	42.3	41.4	42.0	41.2	40.4												
	gpm	16.9	13.3	10.8	16.4	12.8	10.4	15.9	12.4	10.0	15.3	12.0	9.7												
	wpd	31.7	19.6	12.9	29.9	18.2	12.1	27.9	17.1	11.1	26.1	15.9	10.4												

2-Row Chilled Water Cooling

EDB	EWT	42				43			44				45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC	57.2	53.3	49.4	55.1	51.2	47.3	53.0	49.1	45.1	50.9	46.9	42.9		
	SC	19.4	18.0	16.5	18.6	17.2	15.7	17.8	16.4	15.0	17.1	15.6	14.2		
	gpm	14.4	10.8	8.4	13.9	10.3	8.0	13.3	9.9	7.6	12.9	9.5	7.3		
	wpd	30.0	16.8	10.1	27.7	15.4	9.1	25.6	14.2	8.2	24.1	13.1	7.6		
76	TC	57.1	53.2	49.4	55.1	51.1	47.2	53.0	49.1	45.0	50.9	46.9	42.9		
	SC	21.6	20.1	18.7	20.8	19.3	17.9	20.0	18.6	17.1	19.2	17.8	16.3		
	gpm	14.4	10.8	8.4	13.9	10.3	8.0	13.3	9.9	7.6	12.9	9.5	7.3		
	wpd	30.0	16.8	10.1	27.7	15.4	9.1	25.6	14.2	8.2	24.1	12.9	7.6		
78	TC	57.1	53.2	49.4	55.0	51.1	47.3	52.9	49.0	45.1	50.8	47.0	43.0		
	SC	23.6	22.2	20.7	22.8	21.4	19.9	22.0	20.6	19.2	21.2	19.8	18.4		
	gpm	14.4	10.8	8.3	13.9	10.3	8.0	13.4	9.9	7.7	12.9	9.5	7.3		
	wpd	30.0	16.8	9.9	27.7	15.4	9.1	25.9	14.2	8.4	23.8	13.1	7.6		
80	TC	57.3	53.5	49.6	55.2	51.4	47.5	53.2	49.3	45.4	51.0	47.2	43.2		
	SC	25.7	24.3	22.8	24.9	23.5	22.0	24.1	22.7	21.3	23.3	21.9	20.5		
	gpm	14.5	10.8	8.4	14.0	10.4	8.0	13.4	9.9	7.7	12.9	9.5	7.3		
	wpd	30.3	16.8	10.1	28.0	15.6	9.3	25.9	14.2	8.4	23.8	13.1	7.6		
82	TC	57.5	53.7	49.8	55.4	51.6	47.7	53.3	49.4	45.6	51.2	47.3	43.4		
	SC	27.8	26.3	24.9	27.0	25.5	24.1	26.2	24.7	23.3	25.4	24.0	22.5		
	gpm	14.5	10.9	8.4	14.0	10.4	8.0	13.5	10.0	7.7	12.9	9.5	7.3		
	wpd	30.3	17.0	10.1	28.3	15.6	9.3	26.2	14.4	8.6	24.1	13.1	7.7		
84	TC	57.7	53.9	50.0	55.6	51.8	47.8	53.5	49.6	45.6	51.4	47.5	43.5		
	SC	29.9	28.4	26.9	29.1	27.6	26.1	28.3	26.8	25.3	27.5	26.0	24.5		
	gpm	14.6	10.9	8.4	14.1	10.5	8.0	13.6	10.0	7.7	13.0	9.6	7.3		
	wpd	30.6	17.0	10.2	28.7	15.8	9.3	26.5	14.4	8.4	24.4	13.3	7.7		
86	TC	57.9	54.0	50.0	55.8	51.9	47.9	53.7	49.7	45.6	51.5	47.5	43.4		
	SC	32.0	30.4	28.9	31.1	29.6	28.1	30.3	28.8	27.3	29.5	28.0	26.5		
	gpm	14.7	11.0	8.4	14.1	10.5	8.0	13.6	10.1	7.7	13.0	9.6	7.3		
	wpd	31.0	17.3	10.2	28.7	15.8	9.3	26.5	14.7	8.6	24.4	13.3	7.7		
88	TC	57.9	54.0	50.0	55.8	51.8	47.8	53.7	49.7	45.6	51.5	47.4	43.6		
	SC	34.0	32.4	30.9	33.2	31.6	30.1	32.3	30.8	29.3	31.5	30.0	28.6		
	gpm	14.7	11.0	8.4	14.1	10.5	8.0	13.6	10.1	7.7	13.0	9.6	7.3		
	wpd	31.0	17.3	10.2	28.7	15.8	9.3	26.5	14.7	8.6	24.4	13.3	7.7		
90	TC	57.9	53.8	49.9	55.7	51.7	47.9	53.6	49.4	45.8	51.4	47.4	43.9		
	SC	36.0	34.4	32.9	35.1	33.6	32.1	34.3	32.8	31.4	33.5	32.0	30.7		
	gpm	14.7	10.9	8.4	14.1	10.5	8.0	13.6	10.0	7.7	13.0	9.5	7.4		
	wpd	31.0	17.0	10.2	28.7	15.8	9.3	26.5	14.4	8.6	24.4	13.1	7.9		

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	73.3	69.4	65.0	70.8	66.9	62.4	68.3	64.3	59.7	65.8	61.7	56.9
	SC	25.8	24.2	22.4	24.8	23.1	21.4	23.7	22.1	20.3	22.7	21.1	19.2
	gpm	18.6	14.0	11.0	17.9	13.5	10.5	17.3	13.0	10.0	16.7	12.5	9.5
	wpd	27.4	15.6	9.5	25.5	14.5	8.8	23.7	13.5	8.0	22.1	12.3	7.2
76	TC	73.2	69.3	65.0	70.8	66.8	62.4	68.3	64.2	59.6	65.7	61.6	56.8
	SC	28.0	26.4	24.7	27.0	25.4	23.6	26.0	24.4	22.6	25.0	23.4	21.5
	gpm	18.6	14.0	11.0	17.9	13.5	10.5	17.3	13.0	10.0	16.6	12.5	9.5
	wpd	27.4	15.6	9.5	25.5	14.5	8.8	23.7	13.5	8.0	21.9	12.3	7.2
78	TC	73.2	69.3	65.0	70.7	66.8	62.3	68.2	64.3	59.7	65.7	61.7	56.9
	SC	30.3	28.7	27.0	29.2	27.7	25.9	28.2	26.6	24.9	27.2	25.6	23.8
	gpm	18.5	14.0	11.0	17.9	13.5	10.5	17.3	13.0	10.1	16.7	12.5	9.6
	wpd	27.2	15.6	9.5	25.5	14.5	8.8	23.7	13.5	8.1	22.1	12.5	7.4
80	TC	73.3	69.4	65.2	70.8	66.9	62.5	68.4	64.4	59.9	65.8	61.8	57.1
	SC	32.5	30.9	29.2	31.5	29.9	28.2	30.5	28.9	27.2	29.5	27.9	26.1
	gpm	18.6	14.1	11.0	17.9	13.5	10.5	17.3	13.0	10.1	16.7	12.5	9.6
	wpd	27.4	15.8	9.7	25.5	14.5	8.8	23.9	13.5	8.1	22.1	12.5	7.4
82	TC	73.3	69.4	65.3	70.9	67.0	62.6	68.4	64.5	59.9	65.9	61.9	57.2
	SC	34.8	33.2	31.5	33.8	32.2	30.5	32.7	31.2	29.4	31.7	30.2	28.3
	gpm	18.6	14.0	11.0	18.0	13.6	10.5	17.3	13.0	10.1	16.7	12.5	9.6
	wpd	27.4	15.6	9.7	25.8	14.7	8.8	23.9	13.5	8.1	22.1	12.5	7.4
84	TC	73.4	69.5	65.3	71.0	67.0	62.7	68.5	64.5	59.9	66.0	61.9	57.1
	SC	37.0	35.4	33.8	36.0	34.4	32.7	35.0	33.4	31.6	34.0	32.4	30.5
	gpm	18.5	14.0	11.0	18.0	13.5	10.5	17.3	13.1	10.1	16.7	12.5	9.6
	wpd	27.2	15.6	9.7	25.8	14.5	8.8	23.9	13.7	8.1	22.1	12.5	7.4
86	TC	73.4	69.6	65.3	71.0	67.0	62.6	68.5	64.4	60.0	66.0	61.9	57.2
	SC	39.3	37.7	36.0	38.2	36.6	34.9	37.2	35.6	33.9	36.2	34.6	32.8
	gpm	18.5	14.1	11.0	17.9	13.5	10.5	17.3	13.0	10.1	16.8	12.5	9.6
	wpd	27.2	15.8	9.7	25.5	14.5	8.8	23.9	13.5	8.1	22.3	12.5	7.4
88	TC	73.4	69.5	65.4	70.9	67.0	62.8	68.4	64.4	60.1	65.9	61.8	57.5
	SC	41.5	39.9	38.2	40.4	38.8	37.2	39.4	37.8	36.1	38.4	36.8	35.1
	gpm	18.6	14.1	11.0	17.9	13.5	10.6	17.3	13.0	10.1	16.7	12.5	9.7
	wpd	27.4	15.8	9.7	25.5	14.5	9.0	23.7	13.5	8.1	22.1	12.5	7.5
90	TC	73.4	69.4	65.4	70.9	67.0	63.0	68.3	64.5	60.5	65.7	62.0	57.9
	SC	43.6	42.0	40.4	42.6	41.0	39.4	41.6	40.0	38.5	40.5	39.1	37.5
	gpm	18.5	14.1	11.0	17.9	13.6	10.6	17.3	13.0	10.2	16.6	12.5	9.8
	wpd	27.2	15.8	9.7	25.5	14.7	9.0	23.7	13.5	8.3	21.9	12.5	7.6

4-Row Chilled Water Cooling

EDB	EWT	42						43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	73.1	70.3	67.4	70.8	68.0	65.0	68.5	65.6	62.5	66.2	63.2	60.1			
	SC	26.9	25.7	24.4	25.9	24.7	23.4	24.9	23.6	22.3	23.8	22.6	21.3			
	gpm	18.5	14.2	11.4	17.9	13.8	11.0	17.3	13.3	10.6	16.7	12.8	10.1			
	wpd	29.6	17.6	11.2	27.8	16.5	10.5	26.0	15.3	9.7	24.1	14.2	8.9			
76	TC	73.0	70.3	67.3	70.8	67.9	64.9	68.5	65.6	62.5	66.1	63.1	60.0			
	SC	28.9	27.7	26.4	27.9	26.6	25.4	26.9	25.6	24.3	25.8	24.6	23.3			
	gpm	18.5	14.2	11.4	17.9	13.7	10.9	17.3	13.3	10.6	16.7	12.8	10.1			
	wpd	29.6	17.6	11.2	27.8	16.3	10.4	26.0	15.3	9.7	24.1	14.2	8.9			
78	TC	73.0	70.2	67.3	70.7	67.9	64.9	68.4	65.5	62.5	66.1	63.1	60.0			
	SC	30.9	29.7	28.4	29.9	28.7	27.4	28.9	27.6	26.3	27.8	26.6	25.3			
	gpm	18.5	14.2	11.4	17.9	13.7	11.0	17.3	13.3	10.6	16.7	12.8	10.1			
	wpd	29.6	17.6	11.2	27.8	16.3	10.5	26.0	15.3	9.7	24.1	14.2	8.9			
80	TC	73.0	70.3	67.4	70.8	67.9	65.0	68.5	65.6	62.5	66.1	63.2	60.1			
	SC	32.9	31.7	30.4	31.9	30.7	29.4	30.9	29.6	28.3	29.9	28.6	27.3			
	gpm	18.5	14.2	11.4	17.9	13.8	11.0	17.3	13.3	10.6	16.8	12.8	10.1			
	wpd	29.6	17.6	11.2	27.8	16.5	10.5	26.0	15.3	9.7	24.3	14.2	8.9			
82	TC	73.0	70.3	67.4	70.8	68.0	65.0	68.5	65.6	62.5	66.2	63.2	60.0			
	SC	34.9	33.7	32.4	33.9	32.7	31.4	32.9	31.6	30.3	31.9	30.6	29.3			
	gpm	18.5	14.2	11.4	17.9	13.8	11.0	17.3	13.3	10.6	16.8	12.8	10.1			
	wpd	29.6	17.6	11.2	27.8	16.5	10.5	26.0	15.3	9.7	24.3	14.2	8.9			
84	TC	73.1	70.3	67.3	70.8	68.0	65.0	68.5	65.6	62.5	66.2	63.2	60.0			
	SC	36.9	35.7	34.4	35.9	34.7	33.4	34.9	33.6	32.3	33.8	32.6	31.3			
	gpm	18.6	14.2	11.4	17.9	13.8	11.0	17.3	13.3	10.6	16.8	12.8	10.1			
	wpd	29.8	17.6	11.2	27.8	16.5	10.5	26.0	15.3	9.7	24.3	14.2	8.9			
86	TC	73.1	70.2	67.3	70.8	67.9	64.9	68.5	65.6	62.6	66.1	63.1	60.1			
	SC	38.9	37.6	36.4	37.9	36.6	35.3	36.8	35.6	34.3	35.8	34.5	33.3			
	gpm	18.6	14.2	11.4	18.0	13.8	10.9	17.3	13.3	10.6	16.8	12.8	10.1			
	wpd	29.8	17.4	11.2	28.0	16.5	10.4	26.0	15.3	9.7	24.3	14.2	8.9			
88	TC	73.0	70.2	67.3	70.8	67.8	65.0	68.4	65.5	62.6	66.1	63.2	60.2			
	SC	40.9	39.6	38.4	39.8	38.6	37.3	38.8	37.5	36.3	37.8	36.5	35.3			
	gpm	18.6	14.2	11.4	17.9	13.7	11.0	17.3	13.2	10.6	16.8	12.8	10.1			
	wpd	29.8	17.4	11.2	27.8	16.3	10.5	26.0	15.2	9.7	24.3	14.2	8.9			
90	TC	73.0	70.2	67.5	70.7	67.9	65.1	68.4	65.6	62.8	66.0	63.2	60.5			
	SC	42.8	41.6	40.4	41.8	40.5	39.4	40.7	39.5	38.4	39.7	38.5	37.4			
	gpm	18.5	14.2	11.4	17.9	13.7	11.0	17.3	13.3	10.6	16.8	12.8	10.2			
	wpd	29.6	17.6	11.3	27.8	16.3	10.5	26.0	15.3	9.8	24.3	14.2	9.0			

5-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	75.0	73.2	71.2	72.8	71.0	68.9	70.6	68.7	66.5	68.4	66.4	64.1				
	SC	29.0	28.1	27.1	28.0	27.0	26.0	26.9	25.9	24.9	25.8	24.9	23.8				
	gpm	18.7	14.6	11.8	18.1	14.1	11.4	17.6	13.6	11.0	17.0	13.2	10.6				
	wpd	38.7	23.6	15.4	36.4	22.1	14.5	34.3	20.6	13.5	32.2	19.4	12.5				
76	TC	75.0	73.3	71.3	72.9	71.0	69.0	70.7	68.8	66.6	68.5	66.4	64.2				
	SC	31.0	30.2	29.2	30.0	29.1	28.1	28.9	28.0	27.0	27.8	26.9	25.9				
	gpm	18.7	14.6	11.9	18.1	14.1	11.4	17.6	13.6	11.0	17.0	13.2	10.6				
	wpd	38.7	23.6	15.6	36.4	22.1	14.5	34.3	20.6	13.5	32.2	19.4	12.5				
78	TC	75.0	73.3	71.4	72.9	71.1	69.1	70.7	68.8	66.7	68.5	66.5	64.3				
	SC	33.1	32.2	31.2	32.0	31.1	30.1	30.9	30.0	29.0	29.9	28.9	27.9				
	gpm	18.6	14.6	11.9	18.2	14.2	11.4	17.7	13.7	11.0	17.0	13.2	10.7				
	wpd	38.4	23.6	15.6	36.7	22.3	14.5	34.5	20.8	13.5	32.2	19.4	12.7				
80	TC	75.0	73.4	71.4	72.9	71.2	69.1	70.8	68.9	66.8	68.6	66.6	64.4				
	SC	35.1	34.2	33.3	34.0	33.1	32.2	33.0	32.1	31.1	31.9	31.0	29.9				
	gpm	18.6	14.6	11.9	18.1	14.2	11.4	17.7	13.7	11.1	17.1	13.2	10.7				
	wpd	38.4	23.6	15.6	36.2	22.3	14.5	34.5	20.8	13.7	32.4	19.4	12.7				
82	TC	75.1	73.4	71.5	72.9	71.2	69.2	70.7	68.9	66.8	68.6	66.6	64.4				
	SC	37.1	36.3	35.3	36.0	35.2	34.2	34.9	34.1	33.1	33.9	33.0	32.0				
	gpm	18.6	14.6	11.9	18.1	14.2	11.5	17.5	13.7	11.1	17.1	13.2	10.7				
	wpd	38.4	23.6	15.6	36.2	22.3	14.7	34.0	20.8	13.7	32.4	19.4	12.7				
84	TC	75.1	73.4	71.4	72.9	71.2	69.2	70.7	68.9	66.8	68.6	66.6	64.5				
	SC	39.1	38.3	37.3	38.0	37.2	36.2	37.0	36.1	35.1	35.9	35.0	34.0				
	gpm	18.6	14.6	11.8	18.1	14.2	11.5	17.5	13.7	11.1	17.1	13.2	10.7				
	wpd	38.4	23.6	15.4	36.4	22.3	14.7	34.0	20.8	13.7	32.4	19.4	12.7				
86	TC	75.0	73.4	71.4	72.9	71.2	69.1	70.7	68.9	66.9	68.5	66.6	64.5				
	SC	41.1	40.3	39.3	40.0	39.2	38.2	38.9	38.1	37.1	37.9	37.0	36.0				
	gpm	18.7	14.6	11.9	18.1	14.2	11.4	17.5	13.7	11.1	17.0	13.3	10.7				
	wpd	38.7	23.6	15.6	36.4	22.3	14.5	34.0	20.8	13.7	31.9	19.6	12.7				
88	TC	75.0	73.3	71.5	72.9	71.1	69.2	70.7	68.9	66.9	68.5	66.6	64.6				
	SC	43.1	42.2	41.3	42.0	41.2	40.2	40.9	40.1	39.1	39.9	39.0	38.0				
	gpm	18.6	14.6	11.9	18.1	14.2	11.4	17.5	13.7	11.1	17.0	13.3	10.7				
	wpd	38.4	23.6	15.6	36.4	22.3	14.5	34.0	20.8	13.7	31.9	19.6	12.7				
90	TC	74.9	73.3	71.5	72.8	71.2	69.3	70.6	68.9	67.0	68.4	66.7	64.7				
	SC	45.0	44.2	43.4	44.0	43.2	42.3	42.9	42.1	41.2	41.9	41.0	40.1				
	gpm	18.6	14.6	11.9	18.1	14.2	11.5	17.6	13.8	11.1	17.0	13.3	10.7				
	wpd	38.4	23.6	15.6	36.4	22.3	14.7	34.3	21.0	13.7	31.9	19.6	12.7				

2-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	63.4	59.5	55.5	61.3	57.3	53.3	59.2	55.2	51.2	57.1	53.0	48.9				
	SC	20.8	19.3	17.9	20.0	18.5	17.1	19.2	17.8	16.4	18.4	17.0	15.6				
	gpm	16.1	12.1	9.4	15.5	11.6	9.0	15.0	11.1	8.7	14.4	10.7	8.3				
	wpd	37.2	20.9	12.7	34.7	19.3	11.6	32.3	17.8	10.8	30.0	16.5	9.9				
78	TC	63.4	59.4	55.4	61.3	57.3	53.3	59.2	55.1	51.1	57.0	52.9	48.9				
	SC	22.9	21.5	20.0	22.2	20.7	19.3	21.4	19.9	18.5	20.6	19.1	17.7				
	gpm	16.0	12.1	9.4	15.5	11.6	9.0	15.0	11.1	8.6	14.4	10.7	8.3				
	wpd	36.9	20.9	12.7	34.7	19.3	11.6	32.3	17.8	10.6	30.0	16.5	9.9				
80	TC	63.3	59.4	55.4	61.2	57.3	53.2	59.1	55.1	51.1	57.0	52.9	48.9				
	SC	25.1	23.6	22.1	24.3	22.8	21.3	23.5	22.0	20.5	22.7	21.2	19.8				
	gpm	16.0	12.1	9.4	15.5	11.6	9.0	15.0	11.1	8.6	14.4	10.7	8.3				
	wpd	36.9	20.9	12.7	34.4	19.3	11.6	32.3	17.8	10.6	30.0	16.5	9.9				
82	TC	63.4	59.5	55.6	61.3	57.4	53.4	59.2	55.3	51.3	57.1	53.1	49.1				
	SC	27.1	25.6	24.2	26.3	24.9	23.4	25.5	24.1	22.6	24.7	23.3	21.9				
	gpm	16.1	12.1	9.4	15.5	11.6	9.0	15.0	11.2	8.7	14.4	10.7	8.3				
	wpd	37.2	20.9	12.7	34.7	19.3	11.6	32.3	18.0	10.8	30.0	16.5	9.9				
84	TC	63.6	59.7	55.8	61.5	57.6	53.7	59.4	55.5	51.5	57.3	53.3	49.3				
	SC	29.2	27.7	26.3	28.4	26.9	25.5	27.6	26.2	24.7	26.8	25.4	23.9				
	gpm	16.1	12.1	9.5	15.6	11.7	9.1	15.1	11.2	8.7	14.5	10.8	8.3				
	wpd	37.2	20.9	12.9	35.1	19.6	11.8	32.6	18.0	10.8	30.3	16.8	9.9				
86	TC	63.8	59.9	56.0	61.7	57.8	53.8	59.6	55.6	51.6	57.4	53.5	49.4				
	SC	31.3	29.8	28.3	30.5	29.0	27.6	29.7	28.2	26.8	28.9	27.4	26.0				
	gpm	16.2	12.1	9.5	15.6	11.7	9.1	15.1	11.3	8.8	14.5	10.8	8.4				
	wpd	37.6	21.2	12.9	35.1	19.6	11.8	32.6	18.3	11.0	30.3	16.8	10.1				
88	TC	64.0	60.1	56.0	61.9	57.9	53.9	59.8	55.8	51.7	57.6	53.6	49.5				
	SC	33.3	31.9	30.4	32.6	31.1	29.6	31.8	30.3	28.8	31.0	29.5	28.0				
	gpm	16.2	12.1	9.5	15.7	11.8	9.2	15.1	11.3	8.8	14.6	10.9	8.4				
	wpd	37.6	21.2	12.9	35.4	19.9	12.0	33.0	18.3	11.0	30.6	17.0	10.1				
90	TC	64.1	60.1	56.1	62.0	58.0	53.9	59.9	55.8	51.7	57.7	53.6	49.4				
	SC	35.4	33.9	32.4	34.6	33.1	31.6	33.8	32.3	30.8	33.0	31.5	30.0				
	gpm	16.3	12.1	9.5	15.7	11.8	9.1	15.1	11.4	8.8	14.6	10.9	8.4				
	wpd	38.0	21.2	12.9	35.4	19.9	11.8	33.0	18.6	11.0	30.6	17.0	10.1				

3-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	81.0	77.0	73.0	78.6	74.6	70.4	76.1	72.0	67.8	73.5	69.4	65.1				
	SC	27.7	26.0	24.4	26.6	25.0	23.4	25.6	24.0	22.4	24.6	23.0	21.3				
	gpm	20.6	15.6	12.4	19.9	15.1	11.9	19.3	14.6	11.5	18.6	14.0	11.0				
	wpd	33.6	19.3	12.1	31.5	18.1	11.2	29.4	16.9	10.4	27.4	15.6	9.5				
78	TC	81.0	77.0	72.9	78.5	74.5	70.4	76.0	71.9	67.7	73.4	69.3	65.0				
	SC	29.9	28.3	26.6	28.9	27.3	25.6	27.8	26.2	24.6	26.8	25.2	23.6				
	gpm	20.5	15.6	12.3	19.9	15.1	11.9	19.3	14.6	11.5	18.6	14.0	11.0				
	wpd	33.4	19.3	12.0	31.5	18.1	11.2	29.4	16.9	10.4	27.4	15.6	9.5				
80	TC	80.9	76.9	72.8	78.4	74.4	70.3	75.9	71.9	67.7	73.4	69.3	65.0				
	SC	32.1	30.5	28.9	31.1	29.5	27.9	30.1	28.5	26.9	29.1	27.5	25.9				
	gpm	20.5	15.5	12.3	19.9	15.0	11.9	19.3	14.6	11.5	18.6	14.0	11.0				
	wpd	33.4	19.1	12.0	31.5	17.9	11.2	29.4	16.9	10.4	27.4	15.6	9.5				
82	TC	80.8	77.0	73.0	78.5	74.4	70.4	76.0	72.0	67.8	73.4	69.4	65.2				
	SC	34.3	32.8	31.2	33.3	31.7	30.2	32.3	30.8	29.2	31.3	29.7	28.2				
	gpm	20.4	15.6	12.3	19.9	15.0	11.9	19.3	14.6	11.5	18.6	14.0	11.0				
	wpd	33.1	19.3	12.0	31.5	17.9	11.2	29.4	16.9	10.4	27.4	15.6	9.7				
84	TC	80.9	77.1	73.1	78.5	74.5	70.5	76.1	72.0	67.9	73.5	69.5	65.3				
	SC	36.6	35.0	33.4	35.6	34.0	32.4	34.6	33.0	31.4	33.6	32.0	30.4				
	gpm	20.4	15.6	12.4	19.8	15.1	11.9	19.3	14.5	11.5	18.7	14.1	11.0				
	wpd	33.1	19.3	12.1	31.2	18.1	11.2	29.4	16.8	10.4	27.7	15.8	9.7				
86	TC	81.0	77.1	73.1	78.5	74.6	70.5	76.0	72.1	67.9	73.6	69.4	65.3				
	SC	38.9	37.3	35.7	37.8	36.3	34.7	36.8	35.2	33.7	35.8	34.2	32.7				
	gpm	20.5	15.6	12.4	19.8	15.1	11.9	19.2	14.6	11.5	18.7	14.0	11.0				
	wpd	33.4	19.3	12.1	31.2	18.1	11.2	29.2	16.9	10.4	27.7	15.6	9.7				
88	TC	81.1	77.2	73.2	78.6	74.7	70.6	76.1	72.1	67.9	73.6	69.5	65.2				
	SC	41.1	39.5	37.9	40.1	38.5	36.9	39.1	37.5	35.9	38.0	36.5	34.9				
	gpm	20.5	15.6	12.4	19.8	15.1	11.9	19.3	14.6	11.5	18.6	14.0	11.0				
	wpd	33.4	19.3	12.1	31.2	18.1	11.2	29.4	16.9	10.4	27.4	15.6	9.5				
90	TC	81.1	77.2	73.2	78.7	74.7	70.5	76.1	72.1	67.9	73.5	69.4	65.2				
	SC	43.3	41.7	40.1	42.3	40.7	39.1	41.3	39.7	38.1	40.3	38.7	37.1				
	gpm	20.5	15.7	12.4	19.9	15.1	12.0	19.3	14.6	11.5	18.6	14.0	11.0				
	wpd	33.4	19.5	12.1	31.5	18.1	11.3	29.4	16.9	10.4	27.4	15.6	9.7				

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	80.5	77.7	74.7	78.3	75.4	72.4	76.0	73.0	69.9	73.6	70.6	67.4
	SC	28.9	27.6	26.3	27.8	26.6	25.3	26.8	25.5	24.2	25.7	24.5	23.2
	gpm	20.4	15.7	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.1	21.5	13.7	34.1	20.3	12.9	31.9	19.0	12.0	30.1	17.7	11.2
78	TC	80.5	77.7	74.7	78.2	75.3	72.3	75.9	73.0	69.9	73.5	70.5	67.4
	SC	30.8	29.6	28.3	29.8	28.6	27.3	28.8	27.5	26.2	27.7	26.5	25.2
	gpm	20.4	15.7	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.1	21.5	13.7	33.9	20.3	12.9	31.9	19.0	12.0	30.1	17.7	11.2
80	TC	80.4	77.6	74.6	78.1	75.3	72.2	75.8	72.9	69.8	73.5	70.5	67.3
	SC	32.8	31.6	30.3	31.8	30.6	29.3	30.8	29.5	28.2	29.7	28.5	27.2
	gpm	20.3	15.7	12.6	19.8	15.2	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	35.9	21.5	13.7	33.9	20.1	12.8	31.9	19.0	12.0	30.1	17.7	11.2
82	TC	80.4	77.6	74.6	78.1	75.3	72.2	75.8	72.9	69.9	73.5	70.5	67.4
	SC	34.8	33.6	32.3	33.8	32.6	31.3	32.8	31.5	30.3	31.8	30.5	29.2
	gpm	20.3	15.7	12.6	19.8	15.2	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	35.9	21.5	13.7	33.9	20.1	12.8	31.9	19.0	12.0	30.1	17.7	11.2
84	TC	80.4	77.6	74.7	78.1	75.3	72.3	75.8	73.0	69.8	73.5	70.5	67.4
	SC	36.8	35.6	34.3	35.8	34.6	33.3	34.8	33.6	32.2	33.8	32.5	31.2
	gpm	20.3	15.7	12.6	19.8	15.3	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	35.9	21.3	13.7	33.9	20.3	12.9	31.9	19.0	12.0	30.1	17.7	11.3
86	TC	80.4	77.6	74.7	78.1	75.3	72.3	75.8	73.0	69.8	73.5	70.5	67.3
	SC	38.8	37.6	36.3	37.8	36.6	35.3	36.8	35.5	34.2	35.8	34.5	33.2
	gpm	20.4	15.7	12.6	19.8	15.2	12.2	19.2	14.8	11.8	18.6	14.3	11.4
	wpd	36.1	21.3	13.7	34.1	20.1	12.9	31.9	19.0	12.0	30.1	17.7	11.2
88	TC	80.4	77.6	74.7	78.2	75.3	72.3	75.8	72.9	69.8	73.5	70.5	67.3
	SC	40.8	39.6	38.3	39.8	38.5	37.2	38.8	37.5	36.2	37.7	36.5	35.1
	gpm	20.4	15.7	12.6	19.8	15.2	12.2	19.2	14.7	11.8	18.6	14.3	11.4
	wpd	36.1	21.3	13.7	34.1	20.1	12.9	31.9	18.8	12.0	30.1	17.7	11.2
90	TC	80.4	77.6	74.6	78.1	75.2	72.2	75.8	72.8	69.8	73.4	70.4	67.3
	SC	42.8	41.5	40.3	41.8	40.5	39.2	40.7	39.4	38.2	39.7	38.4	37.1
	gpm	20.4	15.7	12.6	19.8	15.2	12.2	19.2	14.7	11.8	18.6	14.2	11.4
	wpd	36.1	21.3	13.7	34.1	20.1	12.9	31.9	18.8	12.0	30.1	17.6	11.2

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	82.2	80.4	78.5	80.1	78.2	76.2	77.9	75.9	73.8	75.6	73.6	71.4
	SC	30.9	30.1	29.1	29.9	29.0	28.0	28.8	27.9	26.9	27.7	26.8	25.8
	gpm	20.4	16.0	13.0	20.0	15.5	12.7	19.4	15.1	12.3	18.8	14.7	11.9
	wpd	46.0	28.4	18.8	44.2	26.8	17.8	41.8	25.4	16.7	39.2	23.8	15.6
78	TC	82.2	80.5	78.6	80.1	78.3	76.3	77.9	76.0	73.9	75.7	73.7	71.5
	SC	33.0	32.1	31.2	31.9	31.0	30.1	30.9	29.9	28.9	29.8	28.8	27.8
	gpm	20.4	16.0	13.0	19.8	15.6	12.7	19.4	15.1	12.3	18.9	14.7	11.9
	wpd	46.0	28.4	18.8	43.6	27.0	17.8	41.8	25.4	16.7	39.5	23.8	15.6
80	TC	82.2	80.6	78.6	80.1	78.4	76.4	78.0	76.1	74.0	75.7	73.8	71.6
	SC	35.0	34.2	33.2	33.9	33.1	32.1	32.9	32.0	31.0	31.8	30.9	29.9
	gpm	20.4	16.0	13.1	19.8	15.6	12.7	19.4	15.1	12.3	18.9	14.7	11.9
	wpd	46.0	28.4	19.0	43.6	27.0	17.8	41.8	25.4	16.7	39.5	23.8	15.6
82	TC	82.3	80.6	78.7	80.1	78.4	76.4	77.9	76.1	74.1	75.8	73.8	71.7
	SC	37.0	36.2	35.2	35.9	35.1	34.1	34.9	34.0	33.0	33.8	32.9	31.9
	gpm	20.4	16.1	13.0	19.9	15.6	12.7	19.4	15.1	12.3	18.9	14.7	11.9
	wpd	46.3	28.7	18.8	43.9	27.0	17.8	41.5	25.4	16.7	39.5	24.0	15.8
84	TC	82.3	80.6	78.7	80.1	78.4	76.4	78.0	76.2	74.1	75.7	73.9	71.7
	SC	39.0	38.2	37.3	38.0	37.1	36.1	36.9	36.0	35.1	35.8	34.9	33.9
	gpm	20.4	16.1	13.0	19.9	15.6	12.7	19.4	15.2	12.3	18.7	14.7	11.9
	wpd	46.3	28.7	18.8	43.9	27.0	17.8	41.5	25.6	16.9	38.9	24.0	15.8
86	TC	82.3	80.6	78.7	80.1	78.4	76.4	78.0	76.2	74.1	75.7	73.9	71.7
	SC	41.0	40.2	39.3	40.0	39.1	38.2	38.9	38.0	37.0	37.8	36.9	36.0
	gpm	20.4	16.1	13.0	19.9	15.6	12.7	19.4	15.2	12.3	18.8	14.7	11.9
	wpd	46.3	28.7	18.8	43.9	27.0	17.8	41.5	25.6	16.7	39.2	24.0	15.8
88	TC	82.3	80.6	78.7	80.1	78.4	76.4	77.9	76.2	74.1	75.7	73.9	71.7
	SC	43.0	42.2	41.3	42.0	41.1	40.2	40.9	40.0	39.1	39.8	38.9	37.9
	gpm	20.4	16.1	13.0	19.9	15.6	12.7	19.4	15.2	12.3	18.8	14.7	11.9
	wpd	46.3	28.7	18.8	43.9	27.0	17.8	41.5	25.6	16.7	39.2	24.0	15.6
90	TC	82.2	80.6	78.7	80.1	78.4	76.4	77.9	76.1	74.1	75.7	73.8	71.7
	SC	45.0	44.2	43.3	44.0	43.1	42.2	42.9	42.0	41.1	41.8	40.9	40.0
	gpm	20.4	16.1	13.1	19.9	15.6	12.7	19.4	15.2	12.3	18.8	14.7	11.9
	wpd	46.3	28.7	19.0	43.9	27.0	17.8	41.5	25.6	16.7	39.2	24.0	15.6

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	33.0	29.6	26.4	31.1	28.1	25.0	29.4	26.6	23.6	27.9	25.2	22.4
	SC	27.9	26.4	24.4	27.0	25.5	23.4	26.3	24.7	22.6	25.6	23.7	21.5
	gpm	8.4	6.0	4.5	7.9	5.7	4.3	7.4	5.3	4.0	7.0	5.1	3.8
	wpd	11.4	5.8	3.3	10.2	5.2	3.0	9.0	4.7	2.7	8.1	4.3	2.4
76	TC	34.1	31.6	28.8	32.5	30.1	27.5	31.0	28.9	26.3	29.7	27.6	24.1
	SC	30.7	29.2	27.2	29.9	28.4	26.5	29.1	27.5	25.5	28.4	26.7	23.7
	gpm	8.7	6.4	4.9	8.2	6.1	4.6	7.8	5.9	4.4	7.5	5.6	4.0
	wpd	12.3	6.8	3.9	11.0	6.1	3.5	10.0	5.7	3.2	9.2	5.1	2.7
78	TC	35.6	33.7	31.2	34.2	32.4	30.1	33.0	31.2	28.1	31.8	29.5	26.8
	SC	33.5	32.1	30.2	32.8	31.4	29.3	32.0	30.4	27.7	31.1	29.2	26.5
	gpm	9.0	6.8	5.3	8.7	6.6	5.1	8.4	6.3	4.7	8.1	6.0	4.5
	wpd	13.2	7.6	4.5	12.3	7.1	4.3	11.4	6.6	3.7	10.6	5.8	3.3
80	TC	37.5	35.9	33.1	36.3	34.4	31.9	35.0	33.2	30.7	33.8	32.1	29.6
	SC	36.3	35.0	32.6	35.5	33.9	31.5	34.5	32.8	30.3	33.4	31.6	29.2
	gpm	9.5	7.3	5.6	9.2	7.0	5.3	8.8	6.7	5.2	8.6	6.5	5.0
	wpd	14.8	8.7	5.1	13.9	7.9	4.7	12.7	7.4	4.4	12.1	6.9	4.1
82	TC	39.5	37.9	35.7	38.4	36.7	34.5	37.3	35.6	33.3	36.1	34.4	32.2
	SC	39.0	37.4	35.2	37.9	36.3	34.1	36.8	35.1	32.9	35.7	34.0	31.8
	gpm	10.0	7.7	6.0	9.8	7.4	5.8	9.4	7.2	5.7	9.1	7.0	5.4
	wpd	16.3	9.6	6.0	15.6	9.0	5.5	14.6	8.5	5.2	13.7	7.9	4.8
84	TC	41.8	40.1	38.2	40.7	39.0	37.1	39.6	37.9	35.9	38.4	36.8	34.8
	SC	41.3	39.6	37.7	40.2	38.5	36.6	39.0	37.4	35.5	37.9	36.3	34.3
	gpm	10.6	8.1	6.4	10.3	7.9	6.3	10.1	7.7	6.0	9.8	7.4	5.9
	wpd	18.4	10.8	6.8	17.4	10.2	6.4	16.6	9.6	6.0	15.6	9.0	5.7
86	TC	44.1	42.4	40.7	43.0	41.3	39.6	41.9	40.2	38.4	40.7	39.0	37.3
	SC	43.5	41.9	40.2	42.4	40.8	39.0	41.3	39.7	37.9	40.2	38.5	36.8
	gpm	11.1	8.6	6.9	10.9	8.4	6.7	10.6	8.1	6.5	10.3	7.9	6.3
	wpd	20.3	12.1	7.8	19.5	11.4	7.3	18.4	10.8	6.9	17.4	10.2	6.4
88	TC	46.4	44.7	43.1	45.3	43.6	41.9	44.1	42.5	40.8	43.0	41.3	39.7
	SC	45.8	44.2	42.5	44.7	43.1	41.4	43.6	41.9	40.3	42.4	40.8	39.2
	gpm	11.8	9.1	7.3	11.5	8.8	7.1	11.2	8.6	6.9	10.9	8.4	6.7
	wpd	22.7	13.4	8.7	21.5	12.7	8.3	20.6	12.1	7.8	19.5	11.4	7.4
90	TC	48.6	47.0	45.4	47.5	45.9	44.3	46.4	44.8	43.1	45.3	43.6	42.0
	SC	48.0	46.4	44.8	46.9	45.3	43.7	45.8	44.2	42.6	44.7	43.1	41.4
	gpm	12.3	9.5	7.7	12.0	9.3	7.5	11.8	9.1	7.3	11.5	8.8	7.1
	wpd	24.8	14.8	9.6	23.6	14.1	9.2	22.7	13.4	8.7	21.5	12.7	8.3

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	42.3	38.2	34.2	39.9	35.9	32.2	37.6	33.9	30.7	35.3	32.0	25.5
	SC	33.6	31.7	29.7	32.5	30.6	28.7	31.5	29.7	27.9	30.5	28.8	25.2
	gpm	10.7	7.7	5.8	10.1	7.2	5.5	9.5	6.8	5.2	9.0	6.5	4.3
	wpd	10.4	5.5	3.1	9.3	4.8	2.7	8.3	4.3	2.5	7.4	3.9	1.7
76	TC	43.5	39.9	36.6	41.3	38.0	35.1	39.1	36.2	30.5	37.1	34.6	29.0
	SC	36.7	34.9	33.2	35.7	34.0	32.3	34.7	33.1	30.2	33.7	32.3	28.7
	gpm	11.0	8.1	6.2	10.4	7.7	5.9	9.9	7.3	5.1	9.4	7.0	4.9
	wpd	11.1	6.0	3.5	10.0	5.5	3.2	9.0	4.9	2.4	8.2	4.5	2.2
78	TC	44.8	41.9	39.3	42.7	40.3	35.3	40.9	38.7	33.9	39.3	35.6	32.4
	SC	39.8	38.3	36.8	38.8	37.4	34.9	38.0	36.6	33.5	37.1	35.1	32.0
	gpm	11.3	8.5	6.6	10.8	8.1	5.9	10.3	7.8	5.7	9.9	7.2	5.5
	wpd	11.7	6.6	4.0	10.8	6.1	3.2	9.8	5.6	3.0	9.0	4.7	2.7
80	TC	46.4	44.2	39.9	44.7	42.7	38.5	43.1	40.0	37.1	40.9	38.6	35.7
	SC	43.0	41.8	39.4	42.2	40.9	38.0	41.4	39.5	36.6	40.4	38.1	35.2
	gpm	11.7	9.0	6.8	11.3	8.6	6.5	10.9	8.1	6.3	10.3	7.8	6.0
	wpd	12.6	7.4	4.2	11.7	6.8	3.9	10.9	6.0	3.6	9.8	5.6	3.3
82	TC	48.4	45.5	43.0	46.9	44.2	41.6	45.0	42.9	40.2	43.7	41.6	38.8
	SC	46.4	44.9	42.4	45.5	43.7	41.1	44.4	42.4	39.7	43.1	41.0	38.4
	gpm	12.3	9.2	7.2	11.9	9.0	7.0	11.4	8.7	6.8	11.1	8.4	6.6
	wpd	13.9	7.8	4.8	13.0	7.4	4.5	11.9	7.0	4.2	11.2	6.5	4.0
84	TC	50.2	48.4	45.9	48.9	47.0	44.6	47.6	45.7	43.2	46.3	44.4	41.9
	SC	49.6	47.8	45.4	48.3	46.5	44.1	47.0	45.2	42.7	45.7	43.9	41.4
	gpm	12.7	9.8	7.7	12.4	9.5	7.5	12.0	9.3	7.3	11.7	9.0	7.1
	wpd	14.8	8.8	5.5	14.0	8.3	5.1	13.1	7.9	4.9	12.6	7.4	4.6
86	TC	52.8	51.2	48.9	51.5	49.9	47.6	50.2	48.6	46.3	48.9	47.3	44.9
	SC	52.2	50.5	48.3	50.9	49.3	47.0	49.6	48.0	45.7	48.3	46.7	44.4
	gpm	13.4	10.3	8.2	13.0	10.1	8.1	12.7	9.9	7.8	12.4	9.5	7.6
	wpd	16.4	9.8	6.2	15.6	9.3	6.0	14.8	8.9	5.6	14.0	8.3	5.3
88	TC	55.4	54.0	51.8	54.1	52.7	50.5	52.8	51.4	49.2	51.5	50.1	47.9
	SC	54.8	53.3	51.2	53.5	52.0	49.9	52.2	50.7	48.6	50.9	49.5	47.3
	gpm	14.0	10.9	8.8	13.7	10.7	8.6	13.4	10.4	8.3	13.0	10.2	8.1
	wpd	18.0	10.9	7.1	17.2	10.4	6.7	16.4	10.0	6.3	15.6	9.5	6.0
90	TC	58.0	56.7	54.7	56.8	55.4	53.4	55.5	54.1	52.1	54.2	52.8	50.8
	SC	57.3	56.0	54.0	56.1	54.7	52.7	54.8	53.4	51.4	53.5	52.2	50.2
	gpm	14.7	11.5	9.3	14.3	11.2	9.0	14.0	11.0	8.8	13.7	10.7	8.6
	wpd	19.9	12.1	7.9	18.8	11.6	7.5	18.0	11.1	7.1	17.2	10.6	6.7

4-Row Chilled Water Cooling

EDB	EWT	43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	46.3	42.3	38.4	43.8	39.9	36.3	41.2	37.5	34.5	38.8	35.5	32.7						
	SC	35.4	33.6	31.7	34.2	32.5	30.8	33.1	31.4	29.9	32.0	30.5	29.0						
	gpm	11.7	8.6	6.5	11.1	8.0	6.2	10.4	7.6	5.9	9.8	7.2	5.5						
76	wpd	9.0	4.8	2.8	8.0	4.2	2.5	7.1	3.8	2.2	6.3	3.4	2.0						
	TC	47.2	43.9	40.8	44.8	41.8	39.0	42.5	39.7	37.3	40.4	37.9	31.1						
	SC	38.4	36.8	35.3	37.3	35.8	34.4	36.2	34.9	33.6	35.3	34.0	30.6						
78	gpm	11.9	8.9	6.9	11.3	8.5	6.6	10.7	8.0	6.3	10.2	7.7	5.2						
	wpd	9.4	5.2	3.1	8.4	4.7	2.8	7.6	4.2	2.6	6.8	3.9	1.8						
	TC	48.4	45.7	43.2	46.3	43.8	41.6	44.2	42.0	40.0	42.2	40.4	34.7						
80	SC	41.5	40.2	38.9	40.5	39.3	38.1	39.5	38.4	37.2	38.6	37.6	34.2						
	gpm	12.3	9.3	7.3	11.7	8.9	7.1	11.2	8.5	6.7	10.7	8.2	5.9						
	wpd	9.9	5.7	3.5	9.0	5.2	3.3	8.3	4.7	3.0	7.6	4.4	2.2						
82	TC	49.9	47.7	45.7	47.8	46.0	44.1	46.0	44.5	39.7	44.4	41.1	38.2						
	SC	44.7	43.6	42.5	43.7	42.8	40.5	42.9	42.0	39.1	42.1	40.5	37.6						
	gpm	12.7	9.6	7.7	12.0	9.3	7.0	11.6	9.1	6.7	11.3	8.3	6.4						
84	wpd	10.5	6.1	3.9	9.5	5.7	3.2	8.9	5.4	3.0	8.4	4.6	2.7						
	TC	51.5	50.0	45.7	49.8	48.5	44.3	48.3	45.5	42.9	46.0	44.1	41.4						
	SC	48.0	47.1	45.1	47.1	46.3	43.7	46.3	44.8	42.3	45.4	43.4	40.8						
86	gpm	13.0	10.1	7.7	12.6	9.8	7.5	12.3	9.2	7.2	11.6	8.9	7.0						
	wpd	11.1	6.7	3.9	10.4	6.3	3.6	9.9	5.6	3.4	8.9	5.2	3.2						
	TC	53.6	51.2	48.9	51.5	49.8	47.5	50.2	48.5	46.1	48.9	47.1	44.7						
88	SC	51.4	50.4	48.2	50.8	49.1	46.8	49.5	47.7	45.4	48.1	46.4	44.0						
	gpm	13.5	10.3	8.3	13.1	10.1	8.0	12.7	9.8	7.8	12.3	9.5	7.5						
	wpd	12.0	7.0	4.5	11.2	6.7	4.2	10.5	6.3	4.0	10.0	6.0	3.7						
90	TC	55.6	54.1	51.9	54.3	52.7	50.6	53.0	51.4	49.2	51.6	50.0	47.8						
	SC	54.8	53.3	51.2	53.5	51.9	49.8	52.2	50.6	48.5	50.9	49.3	47.1						
	gpm	14.1	11.0	8.8	13.7	10.7	8.6	13.4	10.4	8.3	13.1	10.1	8.1						
92	wpd	13.1	7.9	5.1	12.3	7.5	4.8	11.8	7.1	4.6	11.2	6.7	4.3						
	TC	58.3	56.9	54.9	57.0	55.6	53.6	55.7	54.3	52.3	54.4	52.9	50.9						
	SC	57.5	56.1	54.1	56.2	54.8	52.8	54.9	53.5	51.5	53.6	52.1	50.1						
94	gpm	14.8	11.5	9.2	14.4	11.3	9.1	14.1	11.0	8.8	13.8	10.7	8.6						
	wpd	14.3	8.7	5.6	13.7	8.4	5.4	13.1	7.9	5.1	12.5	7.6	4.8						
	TC	61.0	59.7	57.9	59.7	58.4	56.5	58.4	57.1	55.2	57.1	55.8	53.9						
96	SC	60.1	58.8	57.0	58.9	57.5	55.7	57.6	56.2	54.4	56.3	54.9	53.1						
	gpm	15.5	12.1	9.8	15.2	11.9	9.5	14.8	11.5	9.3	14.5	11.3	9.1						
	wpd	15.7	9.6	6.3	15.1	9.2	6.0	14.4	8.7	5.7	13.8	8.4	5.4						

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	46.6	44.6	42.4	44.3	42.3	40.1	41.9	39.9	38.0	39.6	37.7	35.8
	SC	34.8	33.9	32.8	33.7	32.7	31.7	32.6	31.6	30.7	31.4	30.5	29.7
	gpm	11.8	9.1	7.2	11.2	8.6	6.8	10.7	8.1	6.4	10.0	7.6	6.1
	wpd	12.7	7.5	4.7	11.6	6.8	4.2	10.4	6.0	3.8	9.3	5.3	3.4
76	TC	47.1	45.4	43.5	44.8	43.2	41.5	42.5	41.0	39.5	40.4	38.9	37.6
	SC	37.4	36.6	35.6	36.3	35.5	34.6	35.2	34.4	33.7	34.1	33.5	32.8
	gpm	11.9	9.2	7.3	11.4	8.8	7.0	10.8	8.3	6.7	10.2	7.9	6.3
	wpd	13.0	7.8	4.9	11.9	7.1	4.5	10.7	6.3	4.1	9.6	5.7	3.7
78	TC	47.6	46.3	44.9	45.5	44.2	43.0	43.4	42.3	43.8	41.3	40.4	39.6
	SC	40.0	39.3	38.6	39.0	38.3	37.7	37.9	37.4	38.1	36.9	36.5	36.0
	gpm	12.0	9.3	7.6	11.6	8.9	7.2	11.0	8.6	7.4	10.5	8.2	6.7
	wpd	13.4	8.0	5.3	12.3	7.3	4.8	11.1	6.8	5.0	10.2	6.2	4.1
80	TC	48.3	47.4	46.3	46.3	45.5	44.7	44.4	43.8	43.2	42.6	42.2	41.8
	SC	42.7	42.2	41.7	41.7	41.3	40.9	40.7	40.4	40.1	39.8	39.6	39.3
	gpm	12.3	9.6	7.8	11.8	9.3	7.5	11.3	8.9	7.3	10.7	8.6	7.0
	wpd	13.8	8.5	5.6	12.7	7.9	5.2	11.7	7.3	4.9	10.6	6.8	4.6
82	TC	49.2	48.7	48.1	47.4	47.1	46.7	45.7	45.6	45.3	44.3	43.3	42.8
	SC	45.5	45.2	44.9	44.6	44.4	44.1	43.7	43.6	43.4	43.0	41.9	41.7
	gpm	12.4	9.9	8.1	12.0	9.5	7.9	11.6	9.3	7.7	11.3	8.8	7.2
	wpd	14.1	9.0	6.1	13.2	8.4	5.7	12.4	7.9	5.4	11.7	7.1	4.8
84	TC	50.4	50.4	50.2	49.0	48.0	47.6	47.0	46.9	46.4	45.9	45.7	45.2
	SC	48.4	48.4	48.2	47.7	46.5	46.3	46.0	45.9	45.7	45.4	45.4	45.1
	gpm	12.8	10.2	8.5	12.5	9.8	8.1	11.9	9.5	7.9	11.6	9.3	7.7
	wpd	15.1	9.5	6.6	14.3	8.7	6.0	13.0	8.4	5.7	12.4	7.9	5.4
86	TC	51.6	51.6	51.2	50.5	50.4	50.1	49.3	49.3	48.9	48.2	48.1	47.7
	SC	50.6	50.6	50.4	50.0	50.0	49.8	49.5	49.4	49.0	48.3	48.2	47.8
	gpm	13.1	10.4	8.6	12.8	10.2	8.5	12.5	10.0	8.3	12.3	9.8	8.1
	wpd	15.8	10.0	6.9	15.1	9.5	6.6	14.5	9.3	6.3	13.8	8.7	6.0
88	TC	53.9	53.9	53.7	52.8	52.8	52.5	51.6	51.6	51.3	50.5	50.4	50.1
	SC	54.1	54.1	53.8	52.9	53.0	52.6	51.8	51.8	51.5	50.6	50.6	50.3
	gpm	13.7	10.9	9.1	13.4	10.7	8.8	13.1	10.4	8.7	12.8	10.2	8.5
	wpd	17.3	11.0	7.5	16.5	10.4	7.2	15.8	10.0	7.0	15.1	9.6	6.6
90	TC	56.2	56.3	56.0	55.1	55.1	54.9	53.9	53.9	53.7	52.7	52.8	52.5
	SC	56.4	56.5	56.2	55.2	55.3	55.1	54.1	54.1	53.9	52.9	52.9	52.7
	gpm	14.3	11.4	9.5	14.0	11.1	9.3	13.7	10.9	9.1	13.4	10.7	8.9
	wpd	18.8	12.0	8.3	18.0	11.4	7.9	17.3	11.0	7.5	16.5	10.6	7.3

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	36.9	33.3	28.3	34.8	31.1	26.6	32.7	28.9	24.8	30.8	26.9	23.2												
	SC	26.8	25.2	22.9	25.9	24.2	22.1	25.1	23.3	21.3	24.2	22.4	20.5												
	gpm	9.3	6.7	4.8	8.8	6.3	4.5	8.3	5.9	4.2	7.8	5.4	3.9												
	wpd	14.1	7.4	3.8	12.7	6.4	3.3	11.2	5.7	2.9	10.0	4.8	2.6												
76	TC	37.6	34.3	30.4	35.6	32.4	28.6	33.7	30.5	27.1	31.8	28.8	25.6												
	SC	29.4	27.9	25.9	28.6	27.0	25.2	27.8	26.1	24.3	26.9	25.5	23.5												
	gpm	9.5	7.0	5.1	9.0	6.6	4.8	8.5	6.2	4.6	8.1	5.8	4.3												
	wpd	14.8	7.9	4.3	13.2	7.1	3.8	11.9	6.3	3.4	10.6	5.5	3.1												
78	TC	38.5	35.7	32.3	36.7	33.9	30.8	34.8	32.3	29.3	33.1	30.8	28.0												
	SC	32.1	30.7	29.0	31.3	29.9	28.1	30.5	29.2	27.3	29.6	28.3	26.4												
	gpm	9.8	7.2	5.4	9.3	6.9	5.2	8.8	6.5	5.0	8.4	6.3	4.7												
	wpd	15.6	8.5	4.8	14.1	7.8	4.4	12.7	6.9	4.0	11.4	6.4	3.7												
80	TC	39.5	37.1	34.3	37.7	35.6	33.0	36.1	34.2	31.7	34.6	32.8	30.4												
	SC	34.8	33.6	32.0	34.0	32.8	31.1	33.3	32.1	30.4	32.4	31.2	29.4												
	gpm	10.0	7.5	5.8	9.5	7.2	5.6	9.1	6.9	5.3	8.7	6.7	5.1												
	wpd	16.3	9.2	5.5	14.8	8.5	5.1	13.7	7.8	4.7	12.5	7.3	4.3												
82	TC	40.7	38.8	36.5	39.2	37.4	35.3	37.8	36.1	34.1	36.5	34.9	32.3												
	SC	37.5	36.3	34.8	36.8	35.6	34.1	36.1	34.7	33.1	35.2	34.0	31.8												
	gpm	10.3	7.9	6.2	9.9	7.6	6.0	9.6	7.4	5.7	9.2	7.0	5.4												
	wpd	17.4	10.2	6.3	16.1	9.4	5.8	15.1	8.9	5.4	13.9	8.1	4.8												
84	TC	42.3	40.6	38.8	41.0	39.4	37.7	39.8	38.3	36.0	38.5	36.8	34.8												
	SC	40.5	39.1	37.7	39.6	38.4	36.8	38.8	37.5	35.5	38.0	36.4	34.4												
	gpm	10.7	8.2	6.6	10.4	8.0	6.3	10.1	7.7	6.1	9.8	7.5	5.9												
	wpd	18.7	11.0	7.1	17.6	10.4	6.6	16.6	9.8	6.1	15.6	9.2	5.7												
86	TC	44.2	42.8	40.8	43.1	41.4	39.6	41.9	40.3	38.5	40.8	39.1	37.4												
	SC	43.2	41.8	40.2	42.3	40.9	39.1	41.4	39.7	38.0	40.3	38.6	36.9												
	gpm	11.2	8.7	6.9	10.9	8.4	6.7	10.6	8.1	6.5	10.4	7.9	6.3												
	wpd	20.6	12.3	7.8	19.5	11.4	7.3	18.4	10.8	6.9	17.6	10.2	6.6												
88	TC	46.5	44.8	43.2	45.4	43.7	42.0	44.2	42.6	40.9	43.1	41.4	39.8												
	SC	45.9	44.3	42.6	44.8	43.1	41.5	43.7	42.0	40.4	42.5	40.9	39.2												
	gpm	11.8	9.1	7.3	11.5	8.8	7.1	11.2	8.6	6.9	10.9	8.4	6.7												
	wpd	22.7	13.4	8.7	21.8	12.7	8.3	20.6	12.1	7.8	19.5	11.4	7.4												
90	TC	48.7	47.1	45.5	47.6	46.0	44.3	46.5	44.9	43.2	45.4	43.7	42.1												
	SC	48.1	46.5	44.9	47.0	45.4	43.8	45.9	44.3	42.7	44.8	43.2	41.5												
	gpm	12.3	9.5	7.7	12.0	9.3	7.5	11.8	9.1	7.3	11.5	8.8	7.1												
	wpd	24.8	14.8	9.6	23.6	14.1	9.2	22.7	13.4	8.7	21.8	12.7	8.3												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	48.2	43.3	38.0	45.6	40.5	35.4	42.9	38.0	33.1	40.2	35.5	30.5												
	SC	32.9	30.7	28.4	31.8	29.5	27.3	30.6	28.4	26.2	29.5	27.4	25.1												
	gpm	12.2	8.8	6.4	11.5	8.2	5.9	10.8	7.7	5.5	10.2	7.2	5.1												
	wpd	13.7	7.1	3.8	12.1	6.2	3.2	10.8	5.5	2.8	9.5	4.7	2.4												
76	TC	48.8	44.3	39.8	46.3	41.9	37.4	43.8	39.4	35.1	41.3	37.2	33.2												
	SC	35.8	33.7	31.7	34.7	32.7	30.6	33.6	31.6	29.6	32.5	30.6	28.8												
	gpm	12.4	9.0	6.7	11.7	8.5	6.4	11.1	8.0	5.9	10.4	7.5	5.6												
	wpd	14.0	7.4	4.1	12.6	6.6	3.7	11.2	5.8	3.2	10.0	5.1	2.9												
78	TC	49.6	45.6	41.5	47.1	43.4	39.4	44.8	41.1	37.6	42.5	39.0	35.7												
	SC	38.7	36.9	34.9	37.6	35.9	33.9	36.6	34.9	33.2	35.6	33.8	32.2												
	gpm	12.5	9.3	7.0	12.0	8.8	6.7	11.3	8.3	6.4	10.7	7.9	6.0												
	wpd	14.4	7.9	4.5	13.1	7.1	4.1	11.7	6.3	3.7	10.6	5.7	3.3												
80	TC	50.4	47.1	43.6	48.1	44.9	41.7	46.0	42.9	40.0	43.8	41.0	38.4												
	SC	41.6	40.0	38.3	40.6	39.0	37.4	39.6	38.1	36.5	38.6	37.2	35.7												
	gpm	12.7	9.5	7.3	12.1	9.1	7.0	11.6	8.7	6.8	11.1	8.3	6.5												
	wpd	14.8	8.3	4.9	13.5	7.6	4.5	12.4	7.0	4.2	11.2	6.3	3.9												
82	TC	51.5	48.6	45.7	49.3	46.7	44.1	47.3	44.9	42.6	45.3	43.3	38.9												
	SC	44.6	43.2	41.7	43.6	42.3	40.8	42.7	41.5	40.0	41.8	40.6	38.5												
	gpm	13.0	9.9	7.7	12.5	9.4	7.4	12.0	9.1	7.2	11.5	8.8	6.6												
	wpd	15.6	8.9	5.5	14.2	8.2	5.0	13.1	7.6	4.7	12.1	7.1	4.0												
84	TC	52.7	50.4	48.1	50.6	48.7	46.6	48.9	47.2	45.3	47.3	45.7	42.0												
	SC	47.7	46.5	45.2	46.7	45.6	44.3	45.9	44.9	42.8	45.0	43.9	41.5												
	gpm	13.4	10.2	8.1	12.8	9.9	7.9	12.3	9.5	7.3	12.0	9.3	7.1												
	wpd	16.4	9.5	6.1	15.0	8.9	5.7	13.9	8.3	4.9	13.1	7.9	4.6												
86	TC	54.1	52.6	50.7	52.5	51.1	47.7	50.9	48.7	46.4	49.0	47.4	45.0												
	SC	50.8	49.9	48.5	50.0	49.0	47.1	49.2	48.1	45.8	48.4	46.8	44.5												
	gpm	13.7	10.7	8.6	13.3	10.3	8.1	12.9	9.9	7.8	12.4	9.6	7.6												
	wpd	17.2	10.4	6.7	16.2	9.8	6.0	15.2	8.9	5.6	14.0	8.5	5.3												
88	TC	56.1	54.1	51.9	54.3	52.8	50.6	53.0	51.5	49.3	51.6	50.2	48.0												
	SC	54.1	53.4	51.3	53.6	52.1	50.0	52.3	50.9	48.7	51.0	49.6	47.4												
	gpm	14.2	11.0	8.8	13.8	10.7	8.6	13.4	10.4	8.3	13.0	10.2	8.1												
	wpd	18.4	11.1	7.1	17.4	10.4	6.7	16.6	10.0	6.3	15.6	9.5	6.1												
90	TC	58.2	56.8	54.8	56.9	55.5	53.5	55.6	54.2	52.2	54.3	52.9	50.9												
	SC	57.5	56.1	54.1	56.2	54.9	52.8	54.9	53.6	51.6	53.6	52.3	50.3												
	gpm	14.7	11.6	9.3	14.4	11.2	9.0	14.1	11.0	8.8	13.8	10.7	8.6												
	wpd	19.9	12.3	7.9	19.0	11.6	7.5	18.2	11.1	7.1	17.4	10.6	6.8												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	53.0	48.0	42.9	50.2	45.4	40.3	47.2	42.5	37.5	44.4	39.8	35.2												
	SC	35.0	32.8	30.5	33.7	31.6	29.4	32.4	30.4	28.2	31.2	29.2	27.2												
	gpm	13.4	9.7	7.2	12.7	9.2	6.8	11.9	8.6	6.3	11.2	8.0	5.9												
	wpd	11.8	6.2	3.4	10.5	5.6	3.0	9.4	4.8	2.6	8.3	4.2	2.3												
76	TC	53.5	49.1	44.5	50.8	46.5	42.1	48.1	43.9	39.6	45.3	41.3	37.4												
	SC	37.8	35.8	33.8	36.6	34.7	32.7	35.4	33.5	31.7	34.2	32.4	30.7												
	gpm	13.5	9.9	7.5	12.9	9.4	7.1	12.2	8.9	6.7	11.5	8.3	6.3												
	wpd	12.0	6.5	3.7	10.9	5.8	3.3	9.7	5.2	2.9	8.6	4.6	2.6												
78	TC	54.2	50.3	46.3	51.5	47.7	44.0	49.0	45.3	41.9	46.4	42.9	39.8												
	SC	40.7	38.9	37.1	39.5	37.8	36.1	38.4	36.7	35.1	37.2	35.7	34.2												
	gpm	13.7	10.2	7.9	13.0	9.6	7.5	12.4	9.1	7.1	11.8	8.7	6.7												
	wpd	12.3	6.8	4.0	11.1	6.1	3.6	10.1	5.5	3.3	9.1	4.9	3.0												
80	TC	55.0	51.5	48.0	52.4	49.2	46.0	50.0	46.9	44.1	47.6	44.8	42.3												
	SC	43.6	42.0	40.4	42.5	41.0	39.5	41.3	39.9	38.6	40.3	39.0	37.8												
	gpm	14.0	10.4	8.1	13.2	9.9	7.8	12.7	9.5	7.5	12.0	9.1	7.1												
	wpd	12.8	7.1	4.3	11.5	6.5	4.0	10.5	6.0	3.6	9.5	5.4	3.3												
82	TC	55.9	52.8	50.1	53.5	50.8	48.2	51.2	48.7	46.5	49.0	46.8	44.9												
	SC	46.6	45.2	43.9	45.5	44.2	42.9	44.4	43.3	42.2	43.5	42.4	41.4												
	gpm	14.1	10.7	8.5	13.5	10.3	8.1	13.0	9.9	7.9	12.4	9.5	7.6												
	wpd	13.1	7.5	4.7	12.0	6.9	4.3	11.1	6.4	4.0	10.1	5.9	3.8												
84	TC	56.9	54.5	52.3	54.7	52.5	50.5	52.6	50.7	49.0	50.6	49.1	44.8												
	SC	49.6	48.5	47.4	48.6	47.5	46.5	47.6	46.7	45.7	46.7	45.8	44.1												
	gpm	14.4	11.1	8.8	13.8	10.7	8.6	13.3	10.3	8.3	12.8	9.9	7.5												
	wpd	13.7	8.0	5.1	12.5	7.5	4.8	11.6	6.9	4.5	10.8	6.5	3.7												
86	TC	58.2	56.3	54.5	56.1	54.5	53.1	54.3	53.0	49.3	52.6	50.1	47.9												
	SC	52.7	51.8	50.8	51.8	50.9	50.0	50.9	50.1	48.6	50.1	49.4	47.2												
	gpm	14.7	11.4	9.2	14.2	11.1	9.0	13.7	10.7	8.3	13.3	10.2	8.1												
	wpd	14.1	8.5	5.6	13.2	8.0	5.3	12.3	7.6	4.6	11.6	6.8	4.3												
88	TC	59.6	58.4	57.1	57.9	56.9	53.7	56.4	54.4	52.4	54.5	53.0	51.0												
	SC	55.9	55.2	54.4	55.1	54.4	52.9	54.3	53.6	51.6	53.7	52.3	50.3												
	gpm	15.2	11.9	9.6	14.7	11.5	9.1	14.3	11.1	8.8	13.8	10.7	8.7												
	wpd	15.1	9.2	6.1	14.1	8.7	5.4	13.4	8.0	5.1	12.5	7.6	4.9												
90	TC	61.6	59.8	58.0	59.9	58.5	56.7	58.5	57.2	55.3	57.2	55.9	54.0												
	SC	59.3	58.9	57.2	58.9	57.7	55.8	57.7	56.4	54.5	56.4	55.1	53.2												
	gpm	15.6	12.1	9.8	15.2	11.9	9.5	14.8	11.6	9.3	14.5	11.3	9.1												
	wpd	16.0	9.6	6.3	15.1	9.2	6.0	14.4	8.9	5.7	13.8	8.4	5.5												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	52.9	50.7	48.0	50.4	48.2	45.3	47.8	45.6	42.8	45.3	43.0	40.2												
	SC	34.6	33.6	32.3	33.4	32.4	31.0	32.2	31.1	29.8	31.0	29.9	28.6												
	gpm	13.4	10.2	8.1	12.7	9.8	7.7	12.1	9.3	7.2	11.5	8.7	6.8												
	wpd	16.5	9.6	6.0	14.9	8.7	5.4	13.5	7.9	4.8	12.1	7.0	4.2												
76	TC	53.0	51.1	48.7	50.6	48.7	46.2	48.1	46.2	43.8	45.7	43.7	41.4												
	SC	37.0	36.1	35.0	35.8	34.9	33.8	34.6	33.7	32.6	33.5	32.6	31.5												
	gpm	13.4	10.4	8.2	12.7	9.9	7.8	12.1	9.3	7.4	11.6	8.8	7.0												
	wpd	16.5	9.9	6.2	14.9	9.0	5.6	13.5	8.0	5.0	12.3	7.2	4.5												
78	TC	53.3	51.7	49.5	50.9	49.3	47.2	48.5	46.9	48.4	46.2	44.5	42.6												
	SC	39.5	38.7	37.6	38.3	37.6	36.5	37.2	36.4	37.1	36.1	35.3	34.4												
	gpm	13.5	10.5	8.4	12.9	10.0	7.9	12.3	9.5	8.1	11.7	9.1	7.2												
	wpd	16.8	10.2	6.4	15.3	9.3	5.8	13.8	8.4	6.1	12.6	7.5	4.7												
80	TC	53.6	52.3	50.4	51.4	50.0	48.2	49.0	47.7	46.1	46.7	45.5	44.0												
	SC	42.0	41.4	40.4	40.9	40.2	39.4	39.8	39.1	38.3	38.7	38.1	37.3												
	gpm	13.6	10.6	8.5	13.0	10.2	8.1	12.4	9.7	7.8	11.8	9.3	7.5												
	wpd	17.0	10.3	6.6	15.6	9.5	6.1	14.1	8.6	5.6	12.9	7.9	5.1												
82	TC	54.1	52.9	51.5	51.8	50.8	49.4	49.6	48.7	47.4	47.5	46.6	45.5												
	SC	44.6	44.0	43.3	43.5	43.0	42.3	42.4	41.9	41.3	41.4	40.9	40.4												
	gpm	13.7	10.7	8.7	13.2	10.3	8.4	12.6	9.8	8.0	12.0	9.5	7.7												
	wpd	17.3	10.6	7.0	15.9	9.8	6.4	14.6	8.9	5.9	13.4	8.3	5.5												
84	TC	54.6	53.8	52.6	52.5	51.7	50.7	50.4	49.8	48.9	48.4	47.9	47.2												
	SC	47.2	46.8	46.2	46.1	45.8	45.2	45.1	44.8	44.3	44.1	43.9	43.5												
	gpm	13.9	10.9	8.8	13.3	10.5	8.6	12.7	10.1	8.3	12.2	9.8	8.0												
	wpd	17.7	11.0	7.2	16.3	10.2	6.8	14.9	9.4	6.3	13.7	8.7	5.9												
86	TC	55.3	54.7	53.9	53.3	52.9	52.2	51.4	51.1	50.7	49.5	49.5	49.3												
	SC	49.9	49.6	49.2	48.9	48.6	48.3	47.9	47.8	47.5	47.0	47.0	46.8												
	gpm	14.0	11.1	9.1	13.5	10.7	8.8	13.0	10.4	8.6	12.6	10.0	8.4												
	wpd	18.0	11.3	7.7	16.8	10.6	7.2	15.6	9.9	6.8	14.6	9.3	6.4												
88	TC	56.1	55.9	55.5	54.3	54.3	54.1	52.7	52.8	52.7	50.6	50.6	50.2												
	SC	52.6	52.5	52.3	51.7	51.7	51.5	50.9	50.9	50.8	49.1	49.1	48.9												
	gpm	14.2	11.4	9.4	13.8	11.0	9.1	13.4	10.7	8.9	12.8	10.2	8.5												
	wpd	18.6	11.9	8.1	17.5	11.1	7.7	16.5	10.6	7.3	15.1	9.6	6.6												
90	TC	57.4	57.5	57.5	55.2	55.2	55.0	54.0	54.1	53.8	52.9	52.9	52.7												
	SC	55.6	55.6	55.6	53.7	53.7	53.6	53.1	53.1	53.0	52.5	52.5	52.4												
	gpm	14.6	11.7	9.8	14.0	11.2	9.3	13.7	10.9	9.1	13.4	10.7	8.9												
	wpd	19.5	12.6	8.7	18.0	11.6	8.0	17.3	11.0	7.7	16.6	10.6	7.3												

2-Row Chilled Water Cooling

EDB	EWT	43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12					
74	TC	42.9	38.7	33.2	40.5	36.3	30.9	38.0	34.0	28.4	35.6	31.5	26.0						
	SC	26.3	24.5	22.3	25.3	23.6	21.3	24.3	22.6	20.3	23.3	21.7	19.3						
	gpm	10.8	7.8	5.6	10.2	7.4	5.2	9.6	6.9	4.8	9.0	6.3	4.4						
	wpd	19.2	10.0	5.1	17.1	8.9	4.4	15.1	7.8	3.8	13.2	6.6	3.2						
76	TC	42.7	38.9	34.1	40.4	36.7	32.0	38.1	34.6	29.8	35.8	32.4	27.4						
	SC	28.6	26.9	25.0	27.6	26.1	24.0	26.7	25.2	23.1	25.8	24.3	22.1						
	gpm	10.8	7.9	5.7	10.2	7.4	5.4	9.6	7.0	5.0	9.1	6.6	4.6						
	wpd	19.0	10.2	5.4	17.1	9.0	4.8	15.1	7.9	4.1	13.4	7.1	3.5						
78	TC	42.8	39.5	35.4	40.7	37.4	33.2	38.6	35.4	31.2	36.5	33.4	29.6						
	SC	31.0	29.5	27.7	30.1	28.7	26.8	29.2	27.8	25.9	28.4	27.0	25.2						
	gpm	10.8	8.0	6.0	10.3	7.6	5.6	9.8	7.2	5.3	9.2	6.7	5.0						
	wpd	19.2	10.4	5.8	17.4	9.4	5.1	15.6	8.5	4.5	13.9	7.4	4.0						
80	TC	43.4	40.4	36.7	41.4	38.4	34.9	39.4	36.5	33.1	37.5	34.6	31.5						
	SC	33.5	32.2	30.5	32.7	31.4	29.6	31.9	30.5	29.1	31.1	29.6	28.2						
	gpm	11.0	8.2	6.2	10.5	7.8	5.9	10.0	7.4	5.6	9.5	7.0	5.3						
	wpd	19.8	11.0	6.3	18.1	10.0	5.7	16.3	9.0	5.1	14.8	7.9	4.7						
82	TC	44.2	41.4	38.3	42.3	39.5	36.6	40.4	37.8	35.1	38.5	36.1	33.6						
	SC	36.2	34.9	33.4	35.4	34.0	32.7	34.6	33.3	31.8	33.8	32.6	31.1						
	gpm	11.1	8.4	6.4	10.7	8.0	6.2	10.2	7.7	6.0	9.8	7.3	5.7						
	wpd	20.3	11.4	6.8	18.7	10.4	6.3	17.1	9.6	5.8	15.6	8.7	5.2						
84	TC	45.3	42.5	40.0	43.4	40.9	38.6	41.5	39.3	37.1	39.8	37.8	35.8						
	SC	38.9	37.6	36.3	38.1	36.8	35.5	37.3	36.1	34.8	36.4	35.3	33.9						
	gpm	11.5	8.6	6.7	11.0	8.3	6.5	10.5	8.0	6.3	10.1	7.7	6.0						
	wpd	21.5	12.1	7.4	19.8	11.2	6.9	18.1	10.4	6.4	16.6	9.6	6.0						
86	TC	46.2	43.8	41.9	44.5	42.4	40.5	42.8	40.9	39.3	41.4	39.7	38.0						
	SC	41.6	40.4	39.3	40.8	39.6	38.4	40.1	38.9	37.5	39.2	38.0	36.8						
	gpm	11.7	8.8	7.0	11.3	8.6	6.8	10.8	8.3	6.7	10.5	8.1	6.4						
	wpd	22.4	12.7	8.1	20.9	12.1	7.6	19.2	11.2	7.3	17.9	10.6	6.8						
88	TC	47.4	45.5	43.8	45.9	44.2	42.6	44.5	42.9	41.4	43.3	41.8	39.8						
	SC	44.4	43.3	41.9	43.6	42.4	41.3	42.9	41.7	40.3	42.2	40.8	39.3						
	gpm	12.0	9.2	7.4	11.6	9.0	7.2	11.3	8.7	7.0	11.0	8.4	6.7						
	wpd	23.6	13.9	9.0	22.1	13.2	8.5	20.9	12.3	7.9	19.8	11.7	7.4						
90	TC	49.0	47.4	45.9	47.7	46.2	44.8	46.5	45.0	43.3	45.5	43.8	42.2						
	SC	47.2	45.9	44.7	46.3	45.2	43.8	45.6	44.4	42.7	44.9	43.3	41.6						
	gpm	12.4	9.6	7.7	12.1	9.4	7.6	11.8	9.1	7.4	11.5	8.9	7.1						
	wpd	25.1	15.1	9.8	23.9	14.4	9.4	22.7	13.7	8.9	21.8	13.0	8.3						

3-Row Chilled Water Cooling

EDB	EWT	42				43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	55.3	50.5	44.2	52.4	47.4	41.1	49.5	44.4	38.2	46.7	41.5	35.1	
	SC	32.5	30.5	27.8	31.3	29.2	26.5	30.1	27.9	25.3	28.9	26.7	24.1	
	gpm	14.0	10.3	7.5	13.3	9.6	6.9	12.5	9.0	6.4	11.8	8.4	5.9	
	wpd	18.0	9.7	5.1	16.2	8.5	4.4	14.4	7.4	3.8	12.8	6.5	3.2	
76	TC	55.3	50.8	45.2	52.5	47.9	42.3	49.8	45.2	39.4	47.0	42.3	36.9	
	SC	35.1	33.2	30.8	33.9	32.0	29.6	32.8	30.8	28.4	31.6	29.6	27.4	
	gpm	14.0	10.3	7.7	13.3	9.7	7.2	12.6	9.2	6.7	11.9	8.6	6.3	
	wpd	18.0	9.7	5.4	16.2	8.6	4.7	14.6	7.8	4.1	13.0	6.7	3.6	
78	TC	55.5	51.5	46.2	52.8	48.8	43.8	50.3	46.0	41.2	47.7	43.4	38.8	
	SC	37.8	36.1	33.8	36.7	34.9	32.7	35.6	33.7	31.7	34.5	32.6	30.6	
	gpm	14.1	10.4	7.8	13.4	9.9	7.4	12.7	9.3	6.9	12.1	8.8	6.5	
	wpd	18.2	10.0	5.6	16.4	8.9	5.0	14.8	7.9	4.4	13.3	7.1	3.9	
80	TC	56.0	52.3	47.8	53.4	49.8	45.2	50.9	47.3	43.1	48.5	44.8	40.7	
	SC	40.6	39.0	37.0	39.5	37.9	35.9	38.4	36.8	34.9	37.4	35.8	33.9	
	gpm	14.2	10.6	8.1	13.5	10.1	7.7	12.9	9.6	7.2	12.3	9.1	6.8	
	wpd	18.4	10.3	6.0	16.8	9.3	5.4	15.2	8.5	4.8	13.9	7.6	4.3	
82	TC	56.7	53.3	49.3	54.2	50.9	47.0	51.7	48.6	44.7	49.4	46.3	42.8	
	SC	43.5	42.0	40.1	42.4	40.9	39.2	41.3	39.9	38.1	40.3	38.9	37.2	
	gpm	14.3	10.8	8.3	13.7	10.3	7.9	13.1	9.9	7.6	12.5	9.4	7.2	
	wpd	18.8	10.8	6.3	17.2	9.7	5.7	15.8	8.9	5.3	14.2	8.0	4.8	
84	TC	57.4	54.5	50.9	55.0	52.3	48.7	52.7	50.0	46.8	50.5	47.9	44.9	
	SC	46.4	45.1	43.3	45.3	44.0	42.3	44.3	43.1	41.5	43.3	42.1	40.6	
	gpm	14.5	11.1	8.6	13.9	10.6	8.2	13.4	10.2	7.9	12.8	9.7	7.6	
	wpd	19.3	11.2	6.8	17.8	10.3	6.2	16.4	9.5	5.7	15.0	8.6	5.3	
86	TC	58.3	55.9	52.5	56.1	53.7	50.7	53.9	51.5	48.9	51.8	49.6	47.4	
	SC	49.3	48.1	46.5	48.3	47.2	45.6	47.3	46.2	44.8	46.4	45.3	44.0	
	gpm	14.7	11.3	8.9	14.2	10.9	8.6	13.7	10.4	8.2	13.1	10.0	8.0	
	wpd	19.9	11.7	7.2	18.4	10.9	6.7	17.2	10.0	6.2	15.8	9.2	5.8	
88	TC	59.3	57.2	54.5	57.2	55.2	52.9	55.1	53.4	51.3	53.2	51.7	49.8	
	SC	52.3	51.2	49.9	51.3	50.3	49.0	50.4	49.5	48.3	49.5	48.7	47.4	
	gpm	15.1	11.6	9.2	14.5	11.2	9.0	13.9	10.8	8.6	13.4	10.5	8.4	
	wpd	20.8	12.3	7.8	19.3	11.4	7.4	17.8	10.8	6.8	16.6	10.1	6.5	
90	TC	60.5	58.7	56.7	58.5	57.0	55.2	56.7	55.4	53.8	55.1	53.9	51.0	
	SC	55.3	54.4	53.3	54.4	53.6	52.5	53.6	52.8	51.6	52.7	51.9	50.4	
	gpm	15.3	11.9	9.6	14.8	11.6	9.4	14.3	11.2	9.1	13.9	10.9	8.6	
	wpd	21.5	13.0	8.5	20.1	12.3	8.0	18.8	11.6	7.6	17.8	10.9	6.8	

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	61.0	55.7	49.8	58.0	52.7	46.7	55.0	49.5	43.5	51.8	46.4	40.3												
	SC	35.1	32.7	30.1	33.7	31.4	28.8	32.4	30.0	27.5	31.0	28.7	26.2												
	gpm	15.5	11.3	8.4	14.7	10.7	7.9	13.9	10.0	7.3	13.1	9.4	6.8												
	wpd	15.7	8.4	4.6	14.1	7.5	4.0	12.6	6.6	3.5	11.2	5.8	3.0												
76	TC	61.1	56.1	50.6	58.2	53.3	47.6	55.2	50.2	44.9	52.3	47.1	42.0												
	SC	37.7	35.5	33.1	36.4	34.2	31.8	35.1	32.9	30.7	33.8	31.6	29.5												
	gpm	15.5	11.4	8.6	14.8	10.8	8.0	14.0	10.2	7.6	13.2	9.5	7.1												
	wpd	15.7	8.5	4.8	14.3	7.7	4.2	12.8	6.8	3.8	11.5	6.0	3.3												
78	TC	61.3	56.7	51.9	58.6	53.9	49.0	55.7	51.2	46.4	52.8	48.3	43.6												
	SC	40.3	38.3	36.2	39.1	37.1	35.0	37.8	35.9	33.8	36.6	34.7	32.7												
	gpm	15.5	11.5	8.7	14.8	10.9	8.3	14.1	10.3	7.9	13.4	9.8	7.4												
	wpd	15.7	8.6	5.0	14.4	7.8	4.5	13.1	7.0	4.0	11.8	6.3	3.6												
80	TC	61.7	57.6	53.2	59.0	54.8	50.5	56.2	52.1	47.8	53.5	49.5	45.5												
	SC	43.1	41.3	39.3	41.9	40.0	38.1	40.7	38.8	37.0	39.5	37.7	36.0												
	gpm	15.6	11.6	9.0	14.9	11.1	8.5	14.2	10.6	8.1	13.5	10.0	7.7												
	wpd	16.0	8.9	5.3	14.6	8.0	4.7	13.2	7.3	4.3	11.9	6.6	3.9												
82	TC	62.3	58.4	54.4	59.6	55.9	52.0	56.9	53.3	49.6	54.3	50.8	47.2												
	SC	45.9	44.2	42.4	44.7	43.1	41.3	43.5	41.9	40.3	42.4	40.8	39.3												
	gpm	15.8	11.9	9.2	15.1	11.3	8.8	14.4	10.8	8.3	13.8	10.3	7.9												
	wpd	16.4	9.2	5.6	14.9	8.4	5.1	13.7	7.7	4.6	12.5	6.9	4.1												
84	TC	62.8	59.5	55.9	60.3	57.0	53.6	57.8	54.5	51.4	55.2	52.2	49.4												
	SC	48.7	47.2	45.6	47.6	46.1	44.6	46.5	45.0	43.6	45.3	44.0	42.7												
	gpm	16.0	12.0	9.5	15.3	11.5	9.1	14.7	11.0	8.7	14.0	10.6	8.3												
	wpd	16.7	9.5	5.9	15.4	8.7	5.4	14.1	7.9	4.9	12.8	7.3	4.6												
86	TC	63.5	60.5	57.4	61.0	58.2	55.4	58.7	55.9	53.3	56.2	53.8	51.5												
	SC	51.6	50.2	48.8	50.5	49.2	47.9	49.4	48.1	47.0	48.3	47.2	46.2												
	gpm	16.0	12.3	9.7	15.5	11.8	9.4	14.9	11.3	9.0	14.3	10.9	8.7												
	wpd	16.9	9.9	6.2	15.7	9.1	5.8	14.6	8.4	5.3	13.4	7.8	5.0												
88	TC	64.2	61.7	59.2	61.9	59.6	57.2	59.6	57.5	55.5	57.5	55.5	53.8												
	SC	54.5	53.3	52.1	53.4	52.3	51.2	52.4	51.4	50.4	51.4	50.5	49.6												
	gpm	16.2	12.5	9.9	15.6	12.1	9.6	15.1	11.7	9.4	14.5	11.2	9.1												
	wpd	17.2	10.3	6.5	16.0	9.6	6.1	14.9	9.0	5.8	13.8	8.3	5.4												
90	TC	65.1	63.2	61.1	63.0	61.2	59.3	60.9	59.3	57.7	58.8	57.5	56.2												
	SC	57.4	56.5	55.5	56.4	55.6	54.7	55.5	54.7	53.8	54.5	53.9	53.1												
	gpm	16.5	12.8	10.3	16.0	12.4	10.0	15.4	12.0	9.7	14.9	11.7	9.5												
	wpd	17.9	10.8	7.0	16.7	10.1	6.6	15.5	9.5	6.2	14.6	9.0	6.0												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	59.8	57.8	55.0	57.2	55.2	52.3	54.6	52.5	49.4	52.0	49.8	46.5												
	SC	34.6	33.6	32.3	33.3	32.4	31.0	32.1	31.1	29.7	30.8	29.8	28.3												
	gpm	15.2	11.7	9.3	14.5	11.2	8.8	13.9	10.7	8.4	13.2	10.1	7.9												
	wpd	21.2	12.6	7.9	19.3	11.6	7.2	17.7	10.4	6.4	15.9	9.4	5.7												
76	TC	59.8	57.9	55.3	57.3	55.3	52.6	54.7	52.7	49.9	52.1	50.1	47.1												
	SC	36.9	36.0	34.8	35.7	34.8	33.5	34.5	33.5	32.2	33.2	32.3	30.9												
	gpm	15.2	11.7	9.3	14.6	11.2	8.8	13.9	10.7	8.4	13.2	10.2	7.9												
	wpd	21.2	12.6	8.0	19.5	11.6	7.2	17.7	10.4	6.5	16.1	9.5	5.8												
78	TC	59.8	58.1	55.7	57.4	55.6	53.1	54.8	53.0	54.4	52.3	50.4	47.9												
	SC	39.3	38.4	37.3	38.1	37.2	36.0	36.8	36.0	36.6	35.7	34.8	33.6												
	gpm	15.1	11.8	9.4	14.5	11.3	9.0	13.9	10.7	9.2	13.2	10.2	8.1												
	wpd	21.0	12.7	8.1	19.3	11.7	7.4	17.7	10.6	7.8	16.1	9.6	6.0												
80	TC	60.0	58.4	56.2	57.6	55.9	53.7	55.0	53.5	51.3	52.6	51.0	48.8												
	SC	41.7	40.9	39.9	40.5	39.7	38.7	39.3	38.6	37.5	38.1	37.4	36.4												
	gpm	15.2	11.8	9.5	14.6	11.4	9.1	13.9	10.9	8.6	13.3	10.4	8.2												
	wpd	21.2	12.9	8.3	19.5	11.9	7.5	17.9	10.9	6.9	16.3	9.9	6.2												
82	TC	60.2	58.8	56.9	57.8	56.4	54.5	55.4	54.0	52.1	53.0	51.6	49.7												
	SC	44.2	43.5	42.5	43.0	42.3	41.4	41.8	41.1	40.2	40.7	40.0	39.1												
	gpm	15.3	11.9	9.6	14.6	11.4	9.2	14.1	10.9	8.8	13.4	10.4	8.4												
	wpd	21.4	13.0	8.5	19.7	12.0	7.8	18.2	11.0	7.1	16.6	10.0	6.5												
84	TC	60.5	59.2	57.6	58.2	56.9	55.3	55.8	54.6	53.0	53.5	52.3	50.8												
	SC	46.6	46.0	45.2	45.5	44.9	44.1	44.4	43.8	43.0	43.2	42.7	42.0												
	gpm	15.3	12.0	9.8	14.8	11.5	9.3	14.1	11.1	9.0	13.6	10.6	8.6												
	wpd	21.6	13.2	8.7	20.1	12.1	8.0	18.4	11.3	7.4	17.0	10.3	6.8												
86	TC	60.9	59.7	58.4	58.6	57.5	56.2	56.3	55.3	54.0	54.0	53.1	52.0												
	SC	49.2	48.6	47.9	48.0	47.5	46.9	46.9	46.4	45.8	45.8	45.4	44.8												
	gpm	15.5	12.1	9.9	14.8	11.6	9.5	14.3	11.2	9.1	13.7	10.8	8.8												
	wpd	22.0	13.5	9.0	20.2	12.4	8.3	18.8	11.6	7.7	17.3	10.7	7.1												
88	TC	61.2	60.3	59.2	59.0	58.2	57.1	56.8	56.1	55.2	54.7	54.0	53.3												
	SC	51.7	51.2	50.7	50.6	50.2	49.7	49.5	49.1	48.7	48.5	48.2	47.8												
	gpm	15.5	12.3	10.0	15.0	11.8	9.7	14.4	11.4	9.3	13.8	10.9	9.0												
	wpd	22.2	13.8	9.3	20.6	12.7	8.6	19.1	11.9	8.0	17.5	11.0	7.4												
90	TC	61.7	61.0	60.3	59.6	59.0	58.4	57.5	57.0	56.5	55.5	55.2	54.8												
	SC	54.3	53.9	53.5	53.2	52.9	52.6	52.2	52.0	51.7	51.2	51.0	50.8												
	gpm	15.6	12.4	10.2	15.0	12.0	9.9	14.6	11.6	9.5	14.1	11.2	9.3												
	wpd	22.4	14.1	9.5	20.8	13.2	9.0	19.5	12.3	8.4	18.2	11.6	7.9												

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	49.0	44.9	40.5	46.7	42.5	37.7	44.3	40.0	34.8	41.8	37.6	31.9
	SC	25.7	24.0	22.2	24.8	23.1	21.2	23.8	22.1	20.1	22.8	21.1	18.9
	gpm	12.4	9.1	6.8	11.8	8.6	6.3	11.2	8.1	5.9	10.6	7.6	5.3
	wpd	25.1	13.7	7.6	23.0	12.1	6.6	20.6	10.8	5.7	18.4	9.4	4.7
76	TC	49.1	45.0	40.5	46.7	42.6	37.8	44.4	40.1	35.2	41.9	37.5	32.4
	SC	28.1	26.4	24.6	27.1	25.4	23.5	26.2	24.5	22.5	25.2	23.5	21.5
	gpm	12.4	9.1	6.8	11.8	8.6	6.3	11.2	8.1	6.0	10.6	7.6	5.4
	wpd	25.1	13.7	7.6	22.7	12.1	6.6	20.6	10.8	5.8	18.4	9.4	4.8
78	TC	49.1	44.9	40.7	46.7	42.4	38.2	44.2	40.1	35.9	41.7	37.7	33.4
	SC	30.5	28.7	27.0	29.5	27.7	26.0	28.5	26.8	25.1	27.5	25.9	24.2
	gpm	12.4	9.1	6.9	11.8	8.6	6.4	11.1	8.1	6.0	10.5	7.6	5.7
	wpd	25.1	13.4	7.8	22.7	12.1	6.8	20.3	10.8	6.0	18.1	9.4	5.2
80	TC	49.4	45.4	41.8	47.0	43.0	39.5	44.6	40.9	37.2	42.2	38.7	35.0
	SC	32.8	31.1	29.6	31.8	30.2	28.6	30.8	29.3	27.7	29.9	28.4	26.8
	gpm	12.5	9.2	7.0	11.8	8.7	6.7	11.3	8.3	6.3	10.7	7.8	5.9
	wpd	25.7	13.9	8.1	23.0	12.5	7.3	20.9	11.2	6.4	18.7	10.0	5.7
82	TC	49.1	45.5	42.3	46.7	43.3	40.2	44.6	41.3	38.0	42.4	39.3	36.0
	SC	35.2	33.6	32.3	34.3	32.8	31.4	33.4	32.0	30.5	32.5	31.1	29.6
	gpm	12.5	9.2	7.1	11.8	8.7	6.8	11.3	8.4	6.4	10.8	8.0	6.0
	wpd	25.4	13.9	8.3	23.0	12.5	7.6	20.9	11.4	6.8	19.0	10.4	6.0
84	TC	49.4	46.2	43.1	47.3	44.3	41.3	45.3	42.3	39.4	43.3	40.4	37.7
	SC	37.7	36.3	34.9	36.8	35.4	34.1	36.0	34.6	33.2	35.1	33.8	32.4
	gpm	12.5	9.4	7.3	11.9	9.0	7.0	11.5	8.6	6.7	10.9	8.2	6.3
	wpd	25.4	14.4	8.7	23.3	13.2	7.9	21.5	12.1	7.3	19.5	11.0	6.6
86	TC	50.1	47.2	44.4	48.2	45.3	42.6	46.3	43.5	40.9	44.4	41.6	39.2
	SC	40.3	39.0	37.6	39.4	38.1	36.7	38.7	37.3	36.1	37.8	36.6	35.4
	gpm	12.7	9.6	7.5	12.2	9.2	7.2	11.7	8.8	6.9	11.2	8.4	6.6
	wpd	26.4	15.1	9.2	24.2	13.9	8.5	22.4	12.7	7.8	20.6	11.7	7.1
88	TC	51.1	48.3	45.6	49.2	46.4	44.0	47.3	44.7	42.5	45.4	43.0	41.0
	SC	43.0	41.6	40.3	42.2	40.9	39.7	41.4	40.0	38.9	40.5	39.4	38.3
	gpm	12.9	9.8	7.7	12.5	9.4	7.4	12.0	9.1	7.2	11.5	8.7	7.0
	wpd	27.4	15.8	9.6	25.4	14.6	9.0	23.6	13.4	8.5	21.5	12.3	7.9
90	TC	52.1	49.3	47.1	50.2	47.7	45.7	48.3	46.1	44.2	46.6	44.6	42.9
	SC	45.7	44.3	43.2	44.9	43.5	42.4	44.0	42.9	41.7	43.2	42.0	40.9
	gpm	13.2	10.0	8.0	12.7	9.7	7.7	12.2	9.4	7.5	11.8	9.1	7.3
	wpd	28.4	16.3	10.4	26.4	15.3	9.8	24.5	14.4	9.2	23.0	13.4	8.7

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	62.9	58.7	52.6	60.1	55.9	49.4	57.2	52.8	46.0	54.2	49.6	42.6												
	SC	32.2	30.5	27.9	31.0	29.3	26.6	29.8	28.0	25.2	28.6	26.7	23.9												
	gpm	16.0	11.9	8.9	15.2	11.3	8.3	14.4	10.7	7.7	13.7	10.0	7.2												
	wpd	23.4	13.0	7.2	21.3	11.7	6.3	19.0	10.4	5.5	17.2	9.2	4.7												
76	TC	63.0	58.8	52.8	60.1	55.8	49.6	57.2	52.9	46.5	54.2	49.7	43.4												
	SC	34.9	33.1	30.6	33.6	31.8	29.3	32.4	30.6	28.0	31.2	29.3	26.8												
	gpm	16.0	11.9	8.9	15.2	11.3	8.4	14.5	10.7	7.8	13.7	10.1	7.3												
	wpd	23.4	13.0	7.2	21.3	11.7	6.5	19.3	10.4	5.6	17.2	9.3	4.9												
78	TC	62.9	58.8	53.2	60.1	56.0	50.3	57.1	53.0	47.1	54.3	50.1	44.3												
	SC	37.5	35.7	33.3	36.2	34.5	32.1	35.0	33.3	30.8	33.8	32.1	29.7												
	gpm	16.0	11.9	9.0	15.2	11.3	8.5	14.5	10.7	8.0	13.8	10.1	7.5												
	wpd	23.4	13.0	7.4	21.3	11.7	6.6	19.3	10.6	5.8	17.4	9.3	5.1												
80	TC	63.3	59.4	54.3	60.6	56.8	51.6	57.7	54.0	48.7	55.0	51.2	45.7												
	SC	40.0	38.3	36.1	38.8	37.2	35.0	37.6	36.0	33.8	36.5	34.9	32.6												
	gpm	16.0	12.0	9.2	15.4	11.5	8.7	14.7	10.9	8.2	13.9	10.3	7.7												
	wpd	23.4	13.1	7.8	21.7	12.1	7.0	19.7	10.9	6.2	17.8	9.8	5.5												
82	TC	63.0	59.5	54.8	60.4	56.9	52.0	57.7	54.3	49.6	55.1	51.6	47.0												
	SC	42.7	41.2	39.1	41.5	40.0	37.9	40.4	39.0	36.9	39.3	37.8	35.9												
	gpm	16.0	12.1	9.3	15.2	11.5	8.8	14.6	11.0	8.4	13.9	10.4	8.0												
	wpd	23.4	13.3	7.9	21.3	12.1	7.1	19.5	11.1	6.5	17.8	10.0	5.8												
84	TC	63.5	60.2	55.9	60.9	57.6	53.5	58.3	55.1	50.9	55.8	52.6	48.6												
	SC	45.5	44.0	42.1	44.3	42.9	41.1	43.2	41.8	40.1	42.2	40.8	39.1												
	gpm	16.0	12.2	9.4	15.4	11.6	9.0	14.7	11.2	8.6	14.1	10.7	8.2												
	wpd	23.6	13.7	8.2	21.7	12.4	7.5	19.9	11.4	6.8	18.2	10.4	6.2												
86	TC	64.0	61.0	57.2	61.6	58.5	54.8	59.1	56.1	52.6	56.6	53.7	50.3												
	SC	48.3	46.9	45.2	47.2	45.8	44.2	46.1	44.8	43.2	45.1	43.8	42.3												
	gpm	16.2	12.4	9.7	15.6	11.9	9.3	15.0	11.4	8.9	14.3	10.9	8.5												
	wpd	24.1	14.0	8.6	22.4	13.0	7.9	20.6	11.9	7.2	18.8	10.9	6.6												
88	TC	64.8	61.8	58.5	62.3	59.4	56.3	59.9	57.2	54.0	57.5	55.0	51.9												
	SC	51.2	49.8	48.3	50.1	48.8	47.3	49.0	47.8	46.4	48.0	46.8	45.4												
	gpm	16.5	12.5	9.9	15.8	12.1	9.5	15.1	11.6	9.1	14.6	11.1	8.8												
	wpd	24.8	14.2	8.9	22.9	13.3	8.3	21.0	12.3	7.6	19.5	11.2	7.1												
90	TC	65.5	62.8	59.9	63.1	60.6	57.8	60.8	58.4	55.7	58.6	56.3	53.8												
	SC	54.0	52.8	51.5	53.0	51.8	50.5	52.0	50.9	49.5	51.0	49.9	48.7												
	gpm	16.6	12.7	10.1	16.0	12.3	9.8	15.4	11.8	9.4	14.8	11.4	9.1												
	wpd	25.3	14.8	9.3	23.6	13.9	8.8	21.7	12.8	8.2	20.1	11.9	7.6												

4-Row Chilled Water Cooling

EDB	EWT	43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	69.2	64.7	58.6	66.3	61.6	55.4	63.3	58.3	51.9	60.3	55.0	48.4						
	SC	35.0	33.0	30.4	33.7	31.6	29.0	32.4	30.2	27.6	31.1	28.8	26.1						
	gpm	17.6	13.1	9.9	16.8	12.4	9.4	16.0	11.8	8.7	15.2	11.1	8.2						
	wpd	20.2	11.3	6.4	18.6	10.1	5.8	16.9	9.1	5.0	15.2	8.1	4.4						
76	TC	69.2	64.7	58.8	66.3	61.6	55.7	63.3	58.4	52.4	60.2	55.2	48.9						
	SC	37.6	35.6	33.1	36.3	34.3	31.7	35.0	32.9	30.4	33.6	31.5	29.0						
	gpm	17.5	13.1	9.9	16.8	12.5	9.4	16.0	11.8	8.8	15.2	11.1	8.3						
	wpd	20.0	11.3	6.5	18.6	10.3	5.8	16.9	9.1	5.1	15.2	8.1	4.5						
78	TC	69.1	64.8	59.3	66.2	61.8	56.3	63.3	58.8	53.1	60.3	55.6	49.9						
	SC	40.1	38.2	35.9	38.8	36.9	34.6	37.6	35.6	33.3	36.3	34.3	31.9						
	gpm	17.5	13.1	10.0	16.8	12.5	9.5	16.0	11.9	9.0	15.3	11.2	8.4						
	wpd	20.0	11.3	6.6	18.4	10.3	6.0	16.9	9.2	5.3	15.4	8.3	4.6						
80	TC	69.7	65.6	60.5	66.8	62.6	57.4	63.9	59.7	54.3	61.0	56.7	51.6						
	SC	42.7	40.9	38.7	41.4	39.6	37.4	40.2	38.4	36.1	38.9	37.1	35.0						
	gpm	17.6	13.3	10.2	16.9	12.7	9.7	16.2	12.0	9.1	15.4	11.5	8.7						
	wpd	20.4	11.6	6.8	18.8	10.5	6.2	17.2	9.5	5.5	15.5	8.6	4.9						
82	TC	69.4	65.6	60.8	66.6	62.7	58.1	63.8	59.9	55.2	60.9	57.0	52.5						
	SC	45.4	43.7	41.6	44.2	42.5	40.5	42.9	41.2	39.3	41.7	40.0	38.1						
	gpm	17.6	13.3	10.3	16.8	12.7	9.8	16.2	12.1	9.3	15.4	11.5	8.9						
	wpd	20.2	11.6	6.9	18.6	10.5	6.3	17.2	9.6	5.7	15.5	8.7	5.2						
84	TC	69.7	66.2	61.8	67.0	63.4	59.1	64.3	60.8	56.6	61.5	57.9	53.9						
	SC	48.1	46.6	44.6	46.9	45.3	43.5	45.7	44.2	42.4	44.5	43.0	41.2						
	gpm	17.6	13.4	10.4	17.0	12.8	10.0	16.3	12.3	9.5	15.6	11.7	9.1						
	wpd	20.4	11.8	7.1	18.9	10.8	6.6	17.4	10.0	6.0	15.9	9.0	5.4						
86	TC	70.2	66.9	63.0	67.5	64.2	60.4	64.8	61.6	57.7	62.1	59.1	55.4						
	SC	50.9	49.4	47.7	49.7	48.2	46.6	48.5	47.1	45.4	47.3	46.0	44.4						
	gpm	17.8	13.5	10.6	17.1	13.0	10.2	16.4	12.4	9.7	15.8	11.9	9.4						
	wpd	20.8	12.0	7.3	19.1	11.1	6.8	17.7	10.1	6.2	16.4	9.4	5.8						
88	TC	70.6	67.7	64.1	68.0	65.2	61.6	65.4	62.6	59.3	62.8	60.1	56.9						
	SC	53.6	52.3	50.7	52.5	51.2	49.6	51.3	50.1	48.6	50.2	49.0	47.6						
	gpm	17.8	13.7	10.8	17.2	13.2	10.4	16.5	12.7	10.0	15.9	12.1	9.6						
	wpd	20.8	12.3	7.7	19.3	11.5	7.1	17.9	10.5	6.6	16.5	9.6	6.1						
90	TC	71.2	68.6	65.3	68.6	66.1	63.0	66.1	63.7	60.8	63.6	61.3	58.7						
	SC	56.4	55.3	53.8	55.3	54.2	52.8	54.2	53.1	51.8	53.1	52.1	50.9						
	gpm	18.0	13.9	11.1	17.3	13.4	10.7	16.8	12.9	10.3	16.0	12.4	9.9						
	wpd	21.2	12.6	8.0	19.7	11.8	7.5	18.4	10.9	6.9	16.9	10.1	6.5						

5-Row Chilled Water Cooling

EDB	EWT	43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12					
74	TC	66.8	64.8	62.6	64.3	62.2	59.8	61.7	59.5	56.9	59.0	56.7	54.0						
	SC	34.4	33.5	32.3	33.2	32.2	31.0	31.9	30.9	29.7	30.7	29.6	28.4						
	gpm	17.1	13.2	10.6	16.4	12.6	10.2	15.7	12.1	9.7	15.0	11.6	9.1						
	wpd	26.8	15.9	10.3	24.6	14.6	9.5	22.8	13.5	8.6	20.8	12.3	7.7						
76	TC	66.8	64.9	62.7	64.3	62.2	59.9	61.7	59.5	57.0	59.0	56.8	54.2						
	SC	36.7	35.8	34.7	35.5	34.5	33.4	34.2	33.2	32.1	33.0	32.0	30.8						
	gpm	17.1	13.2	10.7	16.4	12.7	10.2	15.7	12.1	9.7	15.0	11.6	9.2						
	wpd	26.8	16.1	10.4	24.6	14.8	9.5	22.8	13.5	8.6	20.8	12.3	7.8						
78	TC	66.8	64.9	62.8	64.2	62.3	60.1	61.7	59.6	61.1	59.0	56.9	54.5						
	SC	39.1	38.1	37.1	37.8	36.9	35.8	36.6	35.6	36.3	35.3	34.4	33.3						
	gpm	16.9	13.2	10.7	16.3	12.7	10.2	15.7	12.1	10.4	15.0	11.6	9.3						
	wpd	26.4	16.1	10.4	24.4	14.8	9.5	22.8	13.5	9.9	20.8	12.3	7.9						
80	TC	67.2	65.4	63.5	64.7	62.9	60.8	62.1	60.3	58.1	59.5	57.6	55.3						
	SC	41.4	40.5	39.6	40.1	39.3	38.3	38.9	38.0	37.0	37.7	36.8	35.8						
	gpm	17.1	13.4	10.8	16.4	12.8	10.3	15.7	12.3	9.9	15.1	11.7	9.4						
	wpd	26.8	16.5	10.7	24.9	15.1	9.8	22.8	13.8	9.0	21.0	12.6	8.1						
82	TC	66.8	65.2	63.3	64.3	62.6	60.7	61.8	60.1	58.1	59.3	57.5	55.4						
	SC	43.7	42.9	42.0	42.5	41.7	40.8	41.3	40.5	39.6	40.1	39.3	38.3						
	gpm	17.0	13.3	10.7	16.4	12.7	10.3	15.7	12.3	9.9	15.0	11.7	9.4						
	wpd	26.6	16.3	10.6	24.6	14.9	9.8	22.8	13.8	9.0	20.8	12.6	8.1						
84	TC	66.9	65.4	63.6	64.5	62.9	61.2	62.0	60.4	58.7	59.5	57.9	56.2						
	SC	46.1	45.4	44.5	44.9	44.2	43.4	43.7	43.0	42.2	42.5	41.8	41.0						
	gpm	17.1	13.3	10.8	16.4	12.8	10.4	15.7	12.3	10.0	15.1	11.8	9.5						
	wpd	26.8	16.3	10.7	24.9	15.1	9.9	22.8	14.0	9.1	21.0	12.9	8.4						
86	TC	67.1	65.6	64.1	64.7	63.2	61.7	62.3	60.8	59.3	59.8	58.4	56.9						
	SC	48.6	47.8	47.1	47.4	46.7	45.9	46.2	45.5	44.8	45.0	44.4	43.7						
	gpm	17.1	13.4	10.9	16.4	12.9	10.5	15.9	12.3	10.1	15.3	11.8	9.7						
	wpd	26.8	16.5	10.9	24.9	15.3	10.2	23.2	14.0	9.4	21.4	12.9	8.6						
88	TC	67.3	66.0	64.7	64.9	63.6	62.3	62.6	61.3	60.0	60.2	58.9	57.7						
	SC	51.0	50.3	49.7	49.8	49.2	48.5	48.7	48.1	47.5	47.5	46.9	46.4						
	gpm	17.1	13.4	11.0	16.6	13.0	10.6	15.9	12.5	10.2	15.3	12.0	9.8						
	wpd	27.0	16.6	11.1	25.3	15.4	10.3	23.4	14.3	9.5	21.6	13.2	8.9						
90	TC	67.6	66.4	65.2	65.3	64.1	62.9	62.9	61.8	60.7	60.6	59.5	58.5						
	SC	53.5	52.9	52.3	52.3	51.8	51.2	51.2	50.7	50.1	50.1	49.6	49.1						
	gpm	17.2	13.5	11.1	16.6	13.1	10.7	16.0	12.6	10.3	15.5	12.1	9.9						
	wpd	27.2	16.8	11.3	25.5	15.8	10.4	23.6	14.6	9.8	22.0	13.5	9.0						

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	55.0	50.9	46.7	52.6	48.5	44.2	50.3	46.1	41.8	47.9	43.6	39.3												
	SC	25.0	23.3	21.7	24.0	22.4	20.8	23.1	21.5	19.8	22.1	20.5	18.9												
	gpm	13.9	10.3	7.9	13.3	9.8	7.4	12.8	9.4	7.0	12.2	8.8	6.7												
	wpd	31.8	17.4	10.2	29.0	15.8	9.0	26.7	14.4	8.1	24.2	12.7	7.3												
76	TC	55.3	51.2	47.0	52.9	48.7	44.5	50.5	46.4	42.1	48.1	43.9	39.5												
	SC	27.5	25.8	24.1	26.5	24.8	23.2	25.5	23.9	22.2	24.6	22.9	21.3												
	gpm	14.0	10.4	8.0	13.4	9.8	7.5	12.8	9.4	7.1	12.2	8.9	6.7												
	wpd	32.1	17.6	10.4	29.4	15.8	9.2	26.7	14.4	8.3	24.5	13.0	7.3												
78	TC	55.6	51.4	47.2	53.2	49.0	44.7	50.7	46.5	42.1	48.3	44.0	39.5												
	SC	29.9	28.2	26.5	28.9	27.2	25.6	28.0	26.3	24.6	27.0	25.3	23.6												
	gpm	14.1	10.4	8.0	13.5	9.9	7.5	12.9	9.4	7.1	12.2	8.9	6.7												
	wpd	32.5	17.6	10.4	29.7	16.1	9.2	27.0	14.4	8.3	24.2	13.0	7.3												
80	TC	55.7	51.5	47.1	53.3	49.0	44.6	50.8	46.5	42.2	48.3	43.9	39.7												
	SC	32.3	30.6	28.9	31.3	29.6	27.9	30.3	28.6	27.0	29.4	27.6	26.1												
	gpm	14.1	10.5	8.0	13.5	9.9	7.5	12.9	9.4	7.1	12.2	8.9	6.7												
	wpd	32.5	17.9	10.4	29.7	16.1	9.2	27.0	14.4	8.3	24.5	13.0	7.4												
82	TC	55.7	51.4	47.3	53.2	48.9	44.8	50.7	46.5	42.6	48.2	44.1	40.4												
	SC	34.6	32.9	31.2	33.7	31.9	30.4	32.7	31.0	29.5	31.7	30.0	28.6												
	gpm	14.1	10.5	8.0	13.5	9.9	7.6	12.9	9.4	7.2	12.2	8.9	6.8												
	wpd	32.5	17.9	10.4	29.7	16.1	9.4	27.0	14.6	8.5	24.2	13.0	7.6												
84	TC	55.6	51.4	47.6	53.1	49.0	45.5	50.6	46.7	43.2	48.2	44.5	41.3												
	SC	37.0	35.2	33.7	36.0	34.3	32.9	35.0	33.5	32.0	34.1	32.6	31.2												
	gpm	14.1	10.4	8.1	13.5	9.9	7.7	12.9	9.4	7.3	12.2	9.0	7.0												
	wpd	32.5	17.6	10.6	29.7	16.1	9.6	27.0	14.6	8.7	24.5	13.2	7.9												
86	TC	55.5	51.7	48.3	53.2	49.6	46.3	50.8	47.4	44.3	48.6	45.4	42.2												
	SC	39.3	37.8	36.4	38.4	36.9	35.5	37.5	36.1	34.6	36.6	35.2	33.9												
	gpm	14.1	10.5	8.1	13.5	10.1	7.8	12.8	9.6	7.5	12.2	9.2	7.1												
	wpd	32.5	17.9	10.8	29.7	16.6	10.0	26.7	15.1	9.2	24.5	13.9	8.3												
88	TC	55.6	52.3	49.3	53.4	50.3	47.2	51.4	48.3	45.3	49.4	46.3	43.4												
	SC	41.8	40.4	38.9	40.8	39.5	38.2	40.1	38.7	37.4	39.2	37.9	36.5												
	gpm	14.1	10.6	8.4	13.5	10.2	8.0	13.0	9.8	7.7	12.5	9.4	7.4												
	wpd	32.5	18.4	11.4	29.7	17.1	10.4	27.7	15.8	9.6	25.4	14.4	8.9												
90	TC	56.2	53.2	50.3	54.2	51.3	48.4	52.3	49.4	46.5	50.4	47.5	44.8												
	SC	44.4	42.9	41.6	43.5	42.2	40.8	42.7	41.4	40.0	41.9	40.5	39.3												
	gpm	14.2	10.8	8.5	13.7	10.4	8.1	13.2	10.0	7.8	12.8	9.6	7.6												
	wpd	33.2	19.0	11.9	30.7	17.6	10.8	28.7	16.3	10.0	26.7	15.1	9.4												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	70.6	66.5	61.7	67.8	63.6	58.5	64.9	60.6	55.2	62.0	57.6	51.9												
	SC	31.8	30.1	28.1	30.6	28.8	26.8	29.4	27.6	25.5	28.2	26.4	24.2												
	gpm	17.9	13.4	10.4	17.2	12.9	9.9	16.5	12.2	9.3	15.7	11.6	8.8												
	wpd	29.4	16.6	10.0	27.1	15.2	8.9	24.8	13.7	7.9	22.6	12.4	7.1												
76	TC	70.8	66.7	61.8	68.0	63.7	58.7	65.1	60.8	55.4	62.1	57.8	52.1												
	SC	34.5	32.7	30.7	33.3	31.5	29.4	32.0	30.3	28.1	30.8	29.1	26.8												
	gpm	17.9	13.5	10.4	17.2	12.9	9.9	16.5	12.3	9.4	15.7	11.6	8.8												
	wpd	29.4	16.8	10.0	27.1	15.4	9.0	24.8	13.9	8.0	22.6	12.4	7.1												
78	TC	70.9	66.8	61.8	68.1	63.8	58.7	65.2	60.8	55.4	62.2	57.8	52.2												
	SC	37.1	35.4	33.3	35.9	34.2	32.1	34.7	32.9	30.8	33.5	31.7	29.5												
	gpm	18.0	13.5	10.4	17.3	12.9	9.9	16.5	12.3	9.4	15.7	11.7	8.8												
	wpd	29.7	16.8	10.0	27.3	15.4	9.0	25.1	13.9	8.0	22.6	12.6	7.1												
80	TC	71.0	66.7	61.9	68.1	63.8	58.9	65.2	60.8	55.6	62.2	57.9	52.7												
	SC	39.8	37.9	36.0	38.5	36.7	34.7	37.3	35.5	33.4	36.1	34.3	32.3												
	gpm	18.0	13.4	10.4	17.3	12.9	9.9	16.5	12.3	9.4	15.7	11.7	8.9												
	wpd	29.7	16.6	10.0	27.3	15.4	9.0	25.1	13.9	8.0	22.6	12.6	7.2												
82	TC	70.8	66.7	62.2	67.9	63.8	59.3	65.1	60.9	56.3	62.2	58.1	53.3												
	SC	42.3	40.5	38.7	41.1	39.3	37.5	39.9	38.2	36.3	38.7	37.0	35.1												
	gpm	17.9	13.5	10.5	17.1	12.9	10.0	16.5	12.3	9.5	15.8	11.7	9.0												
	wpd	29.4	16.8	10.1	26.8	15.4	9.2	25.1	13.9	8.3	22.9	12.6	7.5												
84	TC	70.8	66.9	62.7	68.0	64.1	59.9	65.1	61.4	57.1	62.3	58.6	54.3												
	SC	44.9	43.2	41.5	43.7	42.1	40.3	42.5	40.9	39.2	41.3	39.8	38.0												
	gpm	17.9	13.5	10.6	17.2	13.0	10.1	16.5	12.5	9.6	15.7	11.9	9.2												
	wpd	29.4	16.8	10.3	27.1	15.6	9.3	24.8	14.2	8.5	22.6	13.0	7.8												
86	TC	70.9	67.3	63.5	68.2	64.6	60.8	65.5	62.0	57.9	62.8	59.3	55.3												
	SC	47.5	46.0	44.4	46.4	44.9	43.2	45.2	43.8	42.1	44.1	42.7	41.0												
	gpm	17.9	13.6	10.7	17.3	13.1	10.3	16.5	12.5	9.8	15.9	12.1	9.4												
	wpd	29.4	17.0	10.6	27.3	15.8	9.7	25.1	14.4	8.8	23.1	13.3	8.0												
88	TC	71.2	67.9	64.3	68.6	65.2	61.8	66.0	62.7	59.2	63.4	60.2	56.7												
	SC	50.2	48.8	47.3	49.1	47.7	46.2	48.0	46.6	45.1	46.9	45.6	44.1												
	gpm	18.1	13.8	10.8	17.3	13.3	10.4	16.7	12.7	10.0	16.0	12.2	9.6												
	wpd	30.0	17.4	10.8	27.6	16.2	10.0	25.6	14.8	9.2	23.6	13.7	8.5												
90	TC	71.8	68.5	65.3	69.2	66.0	62.8	66.7	63.6	60.4	64.2	61.0	58.0												
	SC	53.0	51.6	50.2	52.0	50.6	49.2	50.9	49.5	48.2	49.8	48.5	47.2												
	gpm	18.2	13.8	11.0	17.5	13.4	10.6	16.9	12.9	10.2	16.3	12.3	9.8												
	wpd	30.2	17.6	11.1	28.1	16.4	10.3	26.3	15.2	9.5	24.3	13.9	8.8												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	77.5	74.0	68.3	74.6	70.9	65.0	71.7	67.7	61.7	68.7	64.5	58.2												
	SC	34.8	33.2	30.8	33.5	31.9	29.4	32.2	30.5	28.0	30.9	29.2	26.6												
	gpm	19.6	15.0	11.5	18.8	14.4	11.0	18.2	13.7	10.4	17.4	13.1	9.9												
	wpd	25.1	14.7	8.7	23.3	13.5	7.9	21.7	12.3	7.1	19.9	11.2	6.4												
76	TC	77.6	74.1	68.4	74.7	71.0	65.1	71.7	67.8	61.7	68.7	64.5	58.2												
	SC	37.4	35.9	33.5	36.1	34.5	32.1	34.8	33.2	30.6	33.5	31.8	29.2												
	gpm	19.6	15.0	11.5	18.8	14.4	11.0	18.1	13.7	10.4	17.4	13.1	9.8												
	wpd	25.3	14.7	8.7	23.3	13.5	7.9	21.5	12.3	7.1	19.9	11.2	6.3												
78	TC	77.6	74.0	68.4	74.7	71.0	65.2	71.7	67.8	61.9	68.6	64.5	58.4												
	SC	40.0	38.4	36.1	38.7	37.1	34.7	37.4	35.8	33.3	36.1	34.4	31.9												
	gpm	19.6	15.0	11.5	18.8	14.4	11.0	18.1	13.7	10.4	17.3	13.1	9.9												
	wpd	25.3	14.7	8.7	23.3	13.7	7.9	21.5	12.3	7.1	19.7	11.2	6.4												
80	TC	77.6	74.0	68.5	74.7	70.9	65.4	71.7	67.9	62.3	68.6	64.6	58.9												
	SC	42.6	41.0	38.7	41.3	39.7	37.4	40.0	38.4	36.1	38.7	37.0	34.7												
	gpm	19.6	15.0	11.5	18.9	14.4	11.1	18.1	13.8	10.5	17.3	13.1	9.9												
	wpd	25.3	14.7	8.7	23.5	13.5	8.0	21.5	12.5	7.2	19.7	11.2	6.5												
82	TC	77.5	74.0	68.9	74.6	71.0	65.8	71.7	68.0	62.8	68.6	64.9	59.6												
	SC	45.2	43.6	41.4	43.9	42.3	40.1	42.6	41.0	38.8	41.3	39.7	37.5												
	gpm	19.6	15.0	11.6	18.9	14.4	11.1	18.1	13.8	10.6	17.4	13.1	10.0												
	wpd	25.3	14.7	8.9	23.5	13.5	8.0	21.5	12.5	7.3	19.9	11.3	6.6												
84	TC	77.6	74.3	69.5	74.7	71.3	66.5	71.8	68.4	63.4	68.9	65.4	60.4												
	SC	47.8	46.3	44.2	46.5	45.0	43.0	45.2	43.8	41.7	44.0	42.5	40.4												
	gpm	19.6	15.1	11.7	18.9	14.4	11.2	18.2	13.9	10.7	17.4	13.2	10.2												
	wpd	25.3	14.9	9.0	23.5	13.7	8.3	21.7	12.6	7.5	19.9	11.5	6.8												
86	TC	77.7	74.7	69.9	74.9	71.8	67.1	72.1	68.8	64.3	69.2	66.0	61.5												
	SC	50.4	49.1	47.0	49.1	47.8	45.8	47.9	46.5	44.6	46.7	45.3	43.5												
	gpm	19.7	15.2	11.8	19.0	14.6	11.3	18.3	14.0	10.8	17.6	13.4	10.4												
	wpd	25.5	15.1	9.1	23.7	14.0	8.4	21.9	12.8	7.7	20.2	11.8	7.1												
88	TC	78.0	75.0	70.8	75.3	72.3	68.1	72.4	69.5	65.3	69.7	66.8	62.6												
	SC	53.1	51.8	50.0	51.9	50.6	48.8	50.6	49.4	47.6	49.5	48.2	46.5												
	gpm	19.8	15.2	11.9	19.1	14.6	11.5	18.4	14.1	11.0	17.6	13.5	10.6												
	wpd	25.7	15.1	9.4	23.9	14.0	8.6	22.1	13.1	7.9	20.4	12.0	7.3												
90	TC	78.3	75.6	71.7	75.6	72.9	69.0	73.0	70.2	66.5	70.2	67.5	63.8												
	SC	55.8	54.6	52.9	54.6	53.4	51.7	53.4	52.2	50.6	52.2	51.1	49.5												
	gpm	19.7	15.3	12.1	19.1	14.8	11.6	18.5	14.2	11.2	17.8	13.6	10.7												
	wpd	25.5	15.4	9.6	23.9	14.3	8.9	22.5	13.2	8.3	20.8	12.2	7.6												

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	74.8	72.8	70.7	72.2	70.2	67.9	69.6	67.5	65.1	67.0	64.7	62.2
	SC	34.6	33.6	32.6	33.3	32.3	31.2	32.1	31.0	29.9	30.8	29.8	28.6
	gpm	18.9	14.8	11.9	18.3	14.2	11.5	17.7	13.7	11.0	17.0	13.2	10.5
	wpd	33.0	20.1	13.0	30.9	18.6	12.1	28.8	17.1	11.1	26.6	15.9	10.2
76	TC	74.8	72.9	70.7	72.3	70.2	67.9	69.6	67.5	65.1	67.0	64.7	62.2
	SC	36.9	36.0	34.9	35.7	34.7	33.6	34.4	33.4	32.3	33.2	32.1	31.0
	gpm	18.9	14.8	12.0	18.3	14.2	11.5	17.7	13.7	11.0	17.0	13.1	10.5
	wpd	32.8	20.1	13.2	30.9	18.6	12.1	28.8	17.1	11.1	26.6	15.8	10.2
78	TC	74.8	72.9	70.7	72.2	70.2	68.1	69.6	67.5	65.3	66.9	64.8	62.5
	SC	39.3	38.3	37.3	38.0	37.0	36.0	36.8	35.8	34.5	35.5	34.5	33.4
	gpm	18.9	14.8	12.0	18.2	14.2	11.5	17.7	13.7	11.6	17.0	13.1	10.5
	wpd	32.8	20.1	13.2	30.6	18.6	12.1	28.8	17.1	12.4	26.6	15.8	10.2
80	TC	74.8	72.9	70.8	72.2	70.2	68.1	69.6	67.5	65.3	66.9	64.8	62.5
	SC	41.6	40.7	39.7	40.3	39.4	38.4	39.1	38.1	37.1	37.8	36.8	35.8
	gpm	18.9	14.8	12.0	18.2	14.2	11.5	17.6	13.7	11.1	17.0	13.1	10.6
	wpd	32.8	20.1	13.2	30.6	18.6	12.1	28.3	17.3	11.3	26.6	15.8	10.3
82	TC	74.7	72.9	70.9	72.1	70.3	68.2	69.6	67.6	65.5	66.9	64.9	62.8
	SC	43.9	43.0	42.1	42.7	41.8	40.8	41.4	40.5	39.5	40.2	39.2	38.3
	gpm	18.9	14.8	12.0	18.2	14.3	11.5	17.6	13.7	11.1	16.9	13.2	10.6
	wpd	32.8	20.1	13.2	30.6	18.8	12.1	28.3	17.3	11.3	26.4	15.9	10.3
84	TC	74.7	73.0	71.0	72.2	70.4	68.4	69.6	67.8	65.7	67.0	65.1	63.0
	SC	46.3	45.4	44.5	45.0	44.2	43.2	43.8	42.9	42.0	42.5	41.7	40.7
	gpm	18.9	14.8	12.0	18.2	14.3	11.6	17.6	13.7	11.1	16.9	13.2	10.7
	wpd	33.0	20.2	13.2	30.6	18.8	12.3	28.6	17.3	11.3	26.4	16.1	10.4
86	TC	74.7	73.1	71.2	72.2	70.6	68.7	69.7	68.0	66.1	67.1	65.3	63.4
	SC	48.6	47.8	46.9	47.4	46.6	45.7	46.2	45.4	44.5	45.0	44.1	43.2
	gpm	18.9	14.8	12.0	18.3	14.3	11.6	17.6	13.8	11.1	17.0	13.2	10.7
	wpd	33.0	20.2	13.4	30.9	18.9	12.4	28.6	17.5	11.4	26.6	16.1	10.6
88	TC	74.8	73.2	71.6	72.3	70.7	69.0	69.8	68.2	66.5	67.3	65.6	64.0
	SC	51.0	50.2	49.4	49.8	49.0	48.2	48.6	47.8	47.0	47.4	46.6	45.8
	gpm	18.9	14.8	12.1	18.3	14.3	11.6	17.7	13.8	11.2	17.1	13.3	10.8
	wpd	33.0	20.2	13.5	30.9	18.8	12.4	28.8	17.5	11.6	26.8	16.3	10.7
90	TC	74.9	73.4	71.9	72.5	71.0	69.5	70.0	68.5	67.0	67.5	66.0	64.5
	SC	53.4	52.7	51.9	52.2	51.5	50.8	51.0	50.3	49.6	49.8	49.1	48.5
	gpm	19.0	14.9	12.2	18.4	14.3	11.8	17.8	13.9	11.4	17.1	13.4	10.9
	wpd	33.3	20.4	13.7	31.1	18.9	12.7	29.0	17.7	11.9	27.0	16.5	11.0

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	61.6	57.4	53.1	59.2	54.9	50.6	56.7	52.5	48.1	54.3	49.9	45.5
	SC	24.3	22.6	21.0	23.3	21.7	20.1	22.4	20.8	19.1	21.4	19.8	18.2
	gpm	15.6	11.6	9.0	14.9	11.1	8.5	14.3	10.6	8.1	13.8	10.1	7.7
	wpd	39.6	22.1	13.2	36.5	20.1	11.9	33.6	18.4	10.8	31.1	16.8	9.6
76	TC	61.7	57.5	53.2	59.3	55.1	50.8	56.9	52.6	48.3	54.4	50.1	45.7
	SC	26.7	25.1	23.4	25.7	24.1	22.5	24.8	23.2	21.6	23.8	22.2	20.6
	gpm	15.6	11.6	9.0	15.0	11.1	8.6	14.4	10.6	8.1	13.7	10.1	7.7
	wpd	40.0	22.1	13.2	36.9	20.3	12.1	33.9	18.4	10.8	30.7	16.8	9.8
78	TC	61.9	57.7	53.5	59.5	55.3	51.0	57.1	52.8	48.5	54.6	50.3	46.0
	SC	29.2	27.5	25.9	28.2	26.6	24.9	27.3	25.6	24.0	26.3	24.7	23.0
	gpm	15.6	11.7	9.1	15.1	11.2	8.6	14.4	10.7	8.2	13.8	10.1	7.7
	wpd	40.0	22.4	13.4	37.3	20.6	12.1	33.9	18.7	11.0	31.1	16.8	9.8
80	TC	62.2	58.0	53.8	59.8	55.6	51.2	57.3	53.1	48.7	54.9	50.5	46.1
	SC	31.6	30.0	28.3	30.7	29.0	27.3	29.7	28.1	26.4	28.7	27.1	25.4
	gpm	15.7	11.8	9.1	15.1	11.2	8.7	14.5	10.8	8.2	13.9	10.2	7.8
	wpd	40.4	22.7	13.4	37.3	20.6	12.3	34.3	19.0	11.0	31.4	17.1	10.0
82	TC	62.4	58.2	53.9	60.0	55.7	51.3	57.6	53.2	48.7	55.0	50.6	46.1
	SC	34.0	32.4	30.7	33.1	31.4	29.7	32.1	30.4	28.7	31.2	29.5	27.8
	gpm	15.8	11.8	9.1	15.2	11.3	8.7	14.6	10.8	8.2	13.9	10.2	7.7
	wpd	40.8	22.7	13.7	37.7	20.9	12.3	34.7	19.0	11.0	31.8	17.1	9.8
84	TC	62.5	58.3	53.9	60.1	55.7	51.3	57.6	53.2	48.8	55.0	50.6	46.3
	SC	36.4	34.7	33.0	35.5	33.8	32.0	34.5	32.8	31.1	33.5	31.8	30.2
	gpm	15.9	11.8	9.1	15.3	11.3	8.7	14.6	10.8	8.2	13.9	10.2	7.8
	wpd	41.2	23.0	13.7	38.1	20.9	12.3	34.7	19.0	11.0	31.8	17.1	10.0
86	TC	62.5	58.1	53.8	60.0	55.6	51.4	57.5	53.0	49.0	54.9	50.6	46.7
	SC	38.8	37.0	35.3	37.8	36.1	34.4	36.8	35.1	33.6	35.8	34.2	32.7
	gpm	15.9	11.8	9.1	15.2	11.3	8.7	14.6	10.7	8.3	13.9	10.3	7.9
	wpd	41.2	22.7	13.4	37.7	20.9	12.3	34.7	18.7	11.2	31.8	17.4	10.2
88	TC	62.4	58.0	54.0	59.9	55.6	51.9	57.3	53.2	49.7	54.8	50.9	47.4
	SC	41.1	39.4	37.8	40.1	38.4	37.0	39.1	37.5	36.1	38.2	36.7	35.3
	gpm	15.8	11.8	9.1	15.2	11.2	8.7	14.5	10.8	8.4	13.9	10.3	8.0
	wpd	40.8	22.7	13.7	37.7	20.6	12.5	34.3	19.0	11.4	31.4	17.4	10.4
90	TC	62.1	58.2	54.7	59.7	56.0	52.5	57.3	53.8	50.5	55.0	51.6	48.5
	SC	43.4	41.8	40.4	42.4	41.0	39.5	41.5	40.1	38.7	40.7	39.3	37.9
	gpm	15.7	11.8	9.2	15.1	11.3	8.8	14.5	10.9	8.5	13.9	10.5	8.2
	wpd	40.4	22.7	13.9	37.3	20.9	12.7	34.3	19.5	11.9	31.8	17.9	11.0

3-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	78.9	74.7	70.3	76.1	71.8	67.3	73.2	68.8	64.2	70.2	65.8	61.2				
	SC	31.4	29.6	27.8	30.2	28.4	26.6	29.0	27.2	25.4	27.7	26.0	24.2				
	gpm	20.0	15.1	11.9	19.3	14.6	11.4	18.6	13.9	10.8	17.8	13.4	10.3				
	wpd	36.8	21.0	13.0	34.2	19.5	11.9	31.6	17.8	10.8	28.9	16.4	9.8				
76	TC	78.9	74.8	70.4	76.1	71.8	67.4	73.2	68.9	64.4	70.3	65.9	61.4				
	SC	34.0	32.3	30.5	32.8	31.1	29.3	31.6	29.9	28.1	30.4	28.7	26.9				
	gpm	20.0	15.1	11.9	19.3	14.6	11.4	18.6	13.9	10.8	17.8	13.4	10.3				
	wpd	36.8	21.0	13.0	34.2	19.5	11.9	31.6	17.8	10.8	29.2	16.4	9.8				
78	TC	79.0	74.8	70.6	76.2	72.0	67.6	73.3	69.0	64.5	70.4	66.0	61.5				
	SC	36.7	34.9	33.2	35.5	33.7	32.0	34.3	32.5	30.8	33.1	31.3	29.6				
	gpm	20.0	15.1	11.9	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.4				
	wpd	36.8	21.0	13.0	34.2	19.5	11.9	31.6	18.0	10.9	29.2	16.4	10.0				
80	TC	79.1	75.0	70.6	76.3	72.0	67.7	73.4	69.1	64.6	70.5	66.1	61.5				
	SC	39.3	37.6	35.8	38.2	36.4	34.6	36.9	35.2	33.4	35.7	34.0	32.2				
	gpm	20.0	15.1	11.9	19.4	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.3				
	wpd	36.5	21.0	13.0	34.4	19.5	11.9	31.9	18.0	10.9	29.2	16.6	9.8				
82	TC	79.2	75.0	70.7	76.3	72.1	67.6	73.5	69.1	64.6	70.5	66.1	61.6				
	SC	42.0	40.2	38.4	40.8	39.0	37.2	39.6	37.8	36.0	38.4	36.6	34.8				
	gpm	20.0	15.2	11.9	19.3	14.6	11.4	18.6	13.9	10.9	17.9	13.4	10.4				
	wpd	36.8	21.3	13.0	34.2	19.5	11.9	31.9	17.8	10.9	29.4	16.6	10.0				
84	TC	79.2	75.0	70.7	76.3	72.0	67.7	73.4	69.0	64.7	70.4	66.0	61.8				
	SC	44.6	42.8	41.0	43.4	41.6	39.9	42.1	40.4	38.7	40.9	39.2	37.5				
	gpm	20.0	15.2	12.0	19.3	14.6	11.4	18.6	14.0	10.9	17.8	13.4	10.4				
	wpd	36.8	21.3	13.1	34.2	19.5	11.9	31.6	18.0	10.9	28.9	16.4	10.0				
86	TC	79.2	74.9	70.8	76.3	72.1	68.0	73.3	69.1	65.2	70.3	66.2	62.2				
	SC	47.2	45.4	43.7	45.9	44.2	42.6	44.7	43.0	41.4	43.5	41.8	40.3				
	gpm	20.0	15.2	12.0	19.3	14.6	11.5	18.5	14.0	11.0	17.8	13.4	10.5				
	wpd	36.8	21.3	13.1	34.2	19.5	12.1	31.3	18.0	11.1	28.9	16.6	10.1				
88	TC	79.1	75.1	71.2	76.2	72.2	68.3	73.4	69.5	65.7	70.4	66.6	63.0				
	SC	49.7	48.0	46.4	48.5	46.9	45.3	47.3	45.7	44.2	46.1	44.6	43.1				
	gpm	20.0	15.2	12.0	19.3	14.7	11.5	18.6	14.1	11.1	17.8	13.5	10.7				
	wpd	36.8	21.3	13.1	34.2	19.7	12.1	31.6	18.2	11.2	29.2	16.8	10.4				
90	TC	79.1	75.4	71.7	76.3	72.6	69.1	73.6	69.9	66.4	70.8	67.3	63.6				
	SC	52.3	50.8	49.2	51.2	49.6	48.1	50.0	48.5	47.0	48.9	47.4	45.9				
	gpm	20.0	15.3	12.1	19.3	14.7	11.6	18.6	14.2	11.2	17.9	13.7	10.7				
	wpd	36.8	21.5	13.5	34.2	19.9	12.4	31.9	18.4	11.6	29.4	17.2	10.6				

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	86.4	82.8	78.2	83.4	79.8	75.0	80.4	76.7	71.7	77.5	73.6	68.3												
	SC	34.7	33.1	31.1	33.3	31.8	29.8	32.0	30.5	28.4	30.7	29.2	27.0												
	gpm	21.8	16.8	13.2	21.1	16.1	12.7	20.3	15.5	12.1	19.6	14.9	11.5												
	wpd	31.2	18.4	11.5	29.2	17.0	10.5	27.0	15.7	9.6	25.3	14.6	8.7												
76	TC	86.3	82.8	78.2	83.4	79.8	75.1	80.4	76.7	71.8	77.4	73.7	68.4												
	SC	37.3	35.7	33.7	35.9	34.4	32.4	34.6	33.1	31.0	33.3	31.8	29.6												
	gpm	21.8	16.8	13.1	21.1	16.2	12.7	20.3	15.6	12.1	19.6	14.9	11.5												
	wpd	31.2	18.4	11.3	29.2	17.2	10.5	27.0	15.9	9.6	25.1	14.6	8.7												
78	TC	86.4	82.9	78.3	83.5	79.9	75.1	80.5	76.8	71.9	77.5	73.7	68.4												
	SC	39.9	38.3	36.4	38.6	37.0	35.0	37.3	35.7	33.7	36.0	34.4	32.3												
	gpm	21.9	16.8	13.2	21.1	16.2	12.7	20.4	15.6	12.1	19.6	14.9	11.5												
	wpd	31.4	18.6	11.5	29.2	17.2	10.5	27.2	15.9	9.6	25.1	14.6	8.7												
80	TC	86.4	82.9	78.3	83.5	79.9	75.1	80.5	76.8	71.9	77.5	73.7	68.4												
	SC	42.5	41.0	39.0	41.2	39.6	37.6	39.9	38.3	36.3	38.6	37.0	34.9												
	gpm	21.9	16.8	13.2	21.2	16.2	12.7	20.4	15.6	12.1	19.6	14.9	11.5												
	wpd	31.4	18.6	11.5	29.4	17.2	10.5	27.2	15.9	9.6	25.1	14.6	8.7												
82	TC	86.5	82.9	78.3	83.5	79.9	75.1	80.5	76.8	71.9	77.5	73.6	68.5												
	SC	45.1	43.5	41.6	43.8	42.2	40.2	42.5	40.9	38.9	41.2	39.6	37.5												
	gpm	21.9	16.8	13.2	21.2	16.2	12.7	20.4	15.6	12.1	19.6	14.9	11.5												
	wpd	31.4	18.6	11.5	29.4	17.2	10.5	27.2	15.9	9.6	25.1	14.6	8.7												
84	TC	86.4	82.9	78.4	83.5	79.9	75.2	80.4	76.8	72.2	77.4	73.7	68.9												
	SC	47.7	46.1	44.2	46.3	44.8	42.9	45.0	43.5	41.6	43.7	42.2	40.3												
	gpm	21.9	16.8	13.2	21.2	16.2	12.7	20.4	15.6	12.2	19.6	14.9	11.6												
	wpd	31.4	18.6	11.5	29.4	17.2	10.7	27.2	15.9	9.7	25.1	14.6	8.9												
86	TC	86.3	82.9	78.7	83.4	79.9	75.6	80.4	76.9	72.5	77.4	73.9	69.5												
	SC	50.2	48.7	46.9	48.9	47.4	45.6	47.6	46.1	44.3	46.3	44.9	43.1												
	gpm	21.9	16.8	13.3	21.2	16.2	12.7	20.4	15.6	12.3	19.6	15.0	11.7												
	wpd	31.4	18.6	11.6	29.4	17.2	10.7	27.2	16.0	9.9	25.3	14.7	9.0												
88	TC	86.3	83.0	79.0	83.4	80.1	76.0	80.5	77.1	73.1	77.5	74.2	70.0												
	SC	52.8	51.3	49.6	51.5	50.1	48.4	50.2	48.8	47.1	48.9	47.6	45.8												
	gpm	21.9	16.8	13.3	21.2	16.2	12.8	20.4	15.6	12.3	19.6	15.0	11.9												
	wpd	31.4	18.4	11.6	29.4	17.2	10.8	27.2	16.0	10.0	25.3	14.7	9.2												
90	TC	86.4	83.2	79.5	83.6	80.4	76.5	80.6	77.6	73.7	77.8	74.6	70.7												
	SC	55.4	54.0	52.4	54.1	52.8	51.1	52.8	51.6	49.9	51.6	50.3	48.7												
	gpm	21.9	16.8	13.4	21.2	16.3	12.9	20.4	15.7	12.4	19.7	15.1	11.9												
	wpd	31.4	18.6	11.8	29.4	17.4	10.9	27.4	16.2	10.1	25.5	14.9	9.4												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	82.7	80.8	78.6	80.2	78.1	75.9	77.6	75.4	73.1	74.9	72.6	70.2												
	SC	34.5	33.6	32.5	33.2	32.3	31.2	32.0	31.0	29.9	30.7	29.7	28.6												
	gpm	20.9	16.4	13.3	20.3	15.8	12.8	19.6	15.3	12.3	19.0	14.7	11.8												
	wpd	40.2	24.6	16.3	38.0	23.0	15.1	35.5	21.4	14.0	33.3	19.9	12.9												
76	TC	82.7	80.9	78.7	80.2	78.2	76.0	77.6	75.5	73.2	74.9	72.7	70.3												
	SC	36.9	35.9	34.9	35.6	34.7	33.6	34.4	33.4	32.3	33.1	32.1	31.0												
	gpm	20.9	16.4	13.3	20.3	15.9	12.8	19.7	15.3	12.3	19.0	14.7	11.8												
	wpd	40.2	24.6	16.3	38.0	23.2	15.1	35.7	21.6	14.0	33.3	19.9	12.9												
78	TC	82.8	80.9	78.8	80.2	78.3	76.0	77.6	75.6	73.2	75.0	72.8	70.4												
	SC	39.2	38.3	37.3	38.0	37.0	36.0	36.7	35.8	34.5	35.5	34.5	33.4												
	gpm	20.9	16.4	13.3	20.3	15.9	12.9	19.7	15.3	13.0	19.0	14.8	11.9												
	wpd	40.2	24.9	16.3	37.8	23.2	15.3	35.7	21.6	15.6	33.3	20.1	13.0												
80	TC	82.8	80.9	78.7	80.2	78.3	76.0	77.6	75.6	73.2	75.0	72.8	70.4												
	SC	41.6	40.7	39.6	40.3	39.4	38.3	39.1	38.1	37.0	37.8	36.8	35.7												
	gpm	20.9	16.4	13.3	20.3	15.9	12.9	19.6	15.3	12.4	19.0	14.8	11.9												
	wpd	40.2	24.9	16.3	37.8	23.2	15.3	35.2	21.6	14.1	33.3	20.1	13.0												
82	TC	82.7	80.9	78.8	80.2	78.3	76.0	77.6	75.6	73.3	74.9	72.8	70.5												
	SC	43.9	43.0	42.0	42.7	41.7	40.7	41.4	40.5	39.4	40.1	39.2	38.1												
	gpm	21.0	16.4	13.3	20.3	15.9	12.8	19.6	15.3	12.4	18.9	14.8	11.9												
	wpd	40.4	24.9	16.3	37.8	23.2	15.1	35.2	21.6	14.1	32.8	20.1	13.0												
84	TC	82.7	80.9	78.8	80.2	78.2	76.1	77.5	75.6	73.3	74.9	72.8	70.6												
	SC	46.2	45.4	44.4	45.0	44.1	43.1	43.7	42.8	41.8	42.5	41.5	40.5												
	gpm	21.0	16.4	13.3	20.3	15.9	12.8	19.6	15.3	12.4	18.9	14.8	11.9												
	wpd	40.4	24.9	16.3	37.8	23.2	15.1	35.2	21.6	14.1	33.0	20.1	13.0												
86	TC	82.7	80.9	78.9	80.1	78.3	76.2	77.5	75.6	73.5	74.9	72.9	70.8												
	SC	48.6	47.7	46.8	47.3	46.4	45.5	46.1	45.2	44.2	44.8	43.9	42.9												
	gpm	21.0	16.4	13.3	20.3	15.9	12.9	19.6	15.3	12.4	18.9	14.8	11.9												
	wpd	40.4	24.9	16.3	37.8	23.2	15.3	35.5	21.6	14.1	33.0	20.1	13.0												
88	TC	82.6	80.9	79.0	80.1	78.4	76.4	77.5	75.7	73.7	74.9	73.1	71.0												
	SC	50.9	50.1	49.2	49.7	48.8	47.9	48.4	47.6	46.7	47.2	46.3	45.4												
	gpm	21.0	16.4	13.4	20.3	15.9	12.9	19.6	15.4	12.5	18.9	14.8	12.0												
	wpd	40.4	24.6	16.5	37.8	23.2	15.3	35.5	21.8	14.3	33.0	20.2	13.2												
90	TC	82.6	81.0	79.2	80.1	78.4	76.6	77.6	75.8	74.0	75.0	73.2	71.3												
	SC	53.3	52.5	51.6	52.0	51.2	50.4	50.8	50.0	49.1	49.6	48.8	47.9												
	gpm	21.0	16.4	13.4	20.3	15.9	13.0	19.6	15.3	12.5	19.0	14.8	12.0												
	wpd	40.4	24.6	16.5	38.0	23.2	15.4	35.5	21.6	14.5	33.3	20.1	13.4												

2-Row Chilled Water Cooling

EDB	EWT	43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	68.8	64.5	60.1	66.3	62.0	57.5	63.8	59.4	55.0	61.3	56.9	52.4						
	SC	23.4	21.8	20.2	22.5	20.8	19.2	21.5	19.9	18.3	20.6	19.0	17.4						
	gpm	17.4	13.1	10.1	16.8	12.5	9.7	16.1	12.0	9.3	15.5	11.5	8.8						
	wpd	49.7	28.0	16.8	46.2	25.7	15.3	42.4	23.6	14.1	39.2	21.5	12.7						
76	TC	68.7	64.4	60.0	66.3	61.9	57.5	63.8	59.4	55.0	61.3	56.8	52.4						
	SC	26.0	24.3	22.7	25.0	23.4	21.8	24.1	22.4	20.8	23.1	21.5	19.9						
	gpm	17.4	13.1	10.1	16.8	12.5	9.7	16.1	12.0	9.3	15.5	11.5	8.8						
	wpd	49.7	28.0	16.8	46.2	25.7	15.3	42.4	23.6	14.1	39.2	21.5	12.7						
78	TC	68.7	64.4	60.1	66.2	61.9	57.6	63.8	59.4	55.0	61.3	56.9	52.5						
	SC	28.4	26.7	25.1	27.4	25.8	24.2	26.5	24.9	23.2	25.5	23.9	22.3						
	gpm	17.4	13.1	10.1	16.8	12.5	9.7	16.1	12.0	9.3	15.5	11.5	8.9						
	wpd	49.7	28.0	16.8	46.2	25.7	15.3	42.4	23.6	14.1	39.2	21.8	13.0						
80	TC	68.9	64.6	60.3	66.4	62.2	57.8	64.0	59.7	55.3	61.5	57.1	52.7						
	SC	30.8	29.2	27.6	29.9	28.3	26.6	28.9	27.3	25.7	28.0	26.4	24.8						
	gpm	17.4	13.1	10.2	16.8	12.6	9.8	16.2	12.1	9.4	15.6	11.5	8.9						
	wpd	49.7	28.0	17.1	46.2	26.1	15.6	42.9	23.9	14.4	39.6	21.8	13.0						
82	TC	69.1	64.8	60.6	66.7	62.4	58.0	64.2	59.9	55.5	61.7	57.3	52.9						
	SC	33.3	31.6	30.0	32.3	30.7	29.1	31.4	29.8	28.1	30.4	28.8	27.2						
	gpm	17.5	13.2	10.2	16.9	12.6	9.8	16.3	12.2	9.4	15.6	11.6	8.9						
	wpd	50.1	28.4	17.1	46.6	26.1	15.8	43.3	24.2	14.4	40.0	22.1	13.0						
84	TC	69.3	65.1	60.7	66.9	62.6	58.2	64.4	60.1	55.7	61.9	57.5	53.0						
	SC	35.7	34.1	32.4	34.8	33.1	31.5	33.8	32.2	30.5	32.9	31.2	29.6						
	gpm	17.6	13.2	10.2	17.0	12.7	9.8	16.3	12.2	9.4	15.7	11.7	9.0						
	wpd	50.6	28.7	17.1	47.1	26.4	15.8	43.7	24.2	14.4	40.4	22.4	13.2						
86	TC	69.6	65.2	60.8	67.1	62.8	58.2	64.6	60.2	55.7	62.1	57.6	53.0						
	SC	38.2	36.5	34.8	37.2	35.5	33.8	36.2	34.6	32.9	35.3	33.6	31.9						
	gpm	17.7	13.2	10.3	17.0	12.7	9.8	16.3	12.2	9.4	15.7	11.7	9.0						
	wpd	51.0	28.4	17.4	47.5	26.4	15.8	43.7	24.5	14.6	40.4	22.4	13.2						
88	TC	69.6	65.2	60.8	67.2	62.7	58.2	64.6	60.1	55.6	62.1	57.5	53.1						
	SC	40.5	38.8	37.1	39.6	37.8	36.1	38.6	36.9	35.2	37.6	35.9	34.3						
	gpm	17.7	13.2	10.3	17.0	12.7	9.8	16.4	12.2	9.4	15.7	11.7	9.0						
	wpd	51.0	28.4	17.4	47.5	26.4	15.8	44.1	24.2	14.4	40.4	22.4	13.2						
90	TC	69.5	65.1	60.7	67.1	62.6	58.3	64.5	60.0	55.8	61.9	57.4	53.3						
	SC	42.9	41.1	39.4	41.9	40.2	38.5	40.9	39.2	37.6	40.0	38.2	36.8						
	gpm	17.6	13.2	10.2	17.0	12.7	9.8	16.3	12.2	9.4	15.7	11.6	9.0						
	wpd	50.6	28.4	17.1	47.5	26.4	15.8	43.7	24.2	14.6	40.4	22.1	13.2						

3-Row Chilled Water Cooling

EDB	EWT	42				43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	87.8	83.4	79.0	84.9	80.6	76.1	82.0	77.6	73.0	79.0	74.5	69.9	
	SC	31.0	29.2	27.4	29.8	28.0	26.2	28.6	26.8	25.0	27.3	25.6	23.8	
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.3	20.0	15.1	11.8	
	wpd	45.3	26.1	16.4	42.4	24.6	15.2	39.5	22.6	13.9	36.8	20.8	12.8	
76	TC	87.6	83.4	79.0	84.8	80.4	76.0	81.9	77.5	72.9	78.9	74.4	69.8	
	SC	33.6	31.8	30.0	32.4	30.6	28.8	31.2	29.4	27.6	30.0	28.2	26.4	
	gpm	22.1	16.9	13.4	21.5	16.3	12.9	20.8	15.7	12.3	20.0	15.1	11.8	
	wpd	44.7	26.1	16.4	42.4	24.3	15.2	39.5	22.6	13.9	36.8	20.8	12.8	
78	TC	87.5	83.3	78.9	84.8	80.4	76.0	81.8	77.4	73.0	78.9	74.4	69.9	
	SC	36.2	34.5	32.7	35.0	33.3	31.5	33.8	32.0	30.3	32.6	30.9	29.1	
	gpm	22.1	16.9	13.3	21.5	16.3	12.8	20.8	15.6	12.3	20.0	15.1	11.8	
	wpd	44.7	26.1	16.2	42.4	24.3	15.0	39.5	22.4	13.9	36.5	20.8	12.8	
80	TC	87.6	83.5	79.1	84.8	80.5	76.1	81.9	77.5	73.0	79.0	74.6	70.0	
	SC	38.9	37.1	35.4	37.7	35.9	34.2	36.5	34.7	33.0	35.3	33.5	31.8	
	gpm	22.2	16.9	13.4	21.4	16.3	12.9	20.8	15.7	12.3	20.0	15.1	11.8	
	wpd	45.0	26.3	16.4	42.1	24.3	15.2	39.5	22.6	13.9	36.8	21.0	12.8	
82	TC	87.7	83.6	79.2	84.9	80.6	76.2	81.9	77.6	73.1	79.1	74.6	70.1	
	SC	41.5	39.8	38.0	40.3	38.6	36.8	39.1	37.4	35.6	37.9	36.2	34.4	
	gpm	22.2	16.9	13.4	21.4	16.3	12.9	20.7	15.7	12.3	20.0	15.1	11.8	
	wpd	45.0	26.3	16.4	42.1	24.3	15.2	39.2	22.6	13.9	36.8	20.8	12.8	
84	TC	87.9	83.7	79.3	85.0	80.7	76.3	82.1	77.7	73.2	79.1	74.7	70.0	
	SC	44.2	42.5	40.7	43.0	41.2	39.5	41.8	40.0	38.2	40.6	38.8	37.0	
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.4	20.0	15.1	11.8	
	wpd	45.3	26.3	16.6	42.4	24.6	15.2	39.5	22.6	14.0	36.5	20.8	12.8	
86	TC	87.9	83.7	79.3	85.1	80.7	76.3	82.1	77.7	73.2	79.1	74.6	70.1	
	SC	46.8	45.1	43.3	45.6	43.9	42.1	44.4	42.6	40.8	43.2	41.4	39.7	
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.4	20.0	15.1	11.8	
	wpd	45.3	26.3	16.6	42.4	24.6	15.2	39.5	22.6	14.0	36.5	21.0	12.8	
88	TC	87.9	83.7	79.3	85.0	80.7	76.3	82.1	77.6	73.3	79.0	74.6	70.2	
	SC	49.4	47.7	45.9	48.2	46.4	44.7	47.0	45.2	43.5	45.8	44.0	42.3	
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.4	20.0	15.1	11.9	
	wpd	45.3	26.3	16.6	42.4	24.6	15.2	39.5	22.6	14.0	36.5	21.0	13.0	
90	TC	87.9	83.6	79.3	84.9	80.6	76.3	82.0	77.7	73.5	78.9	74.7	70.7	
	SC	52.0	50.2	48.5	50.8	49.0	47.3	49.5	47.8	46.2	48.3	46.6	45.1	
	gpm	22.2	16.9	13.4	21.5	16.4	12.9	20.8	15.7	12.4	20.0	15.1	12.0	
	wpd	45.3	26.3	16.4	42.4	24.6	15.2	39.5	22.6	14.0	36.5	21.0	13.1	

4-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	96.7	92.2	88.4	92.8	89.2	85.3	89.8	86.1	82.1	86.7	82.9	78.8				
	SC	34.5	33.0	31.4	33.2	31.7	30.0	31.9	30.3	28.7	30.6	29.0	27.3				
	gpm	24.2	18.7	14.9	23.5	18.0	14.4	22.7	17.4	13.9	21.9	16.8	13.3				
	wpd	38.4	22.9	14.6	36.2	21.3	13.5	33.8	19.9	12.6	31.4	18.4	11.6				
76	TC	95.6	92.1	88.3	92.7	89.1	85.2	89.7	86.0	82.0	86.6	82.8	78.7				
	SC	37.1	35.6	33.9	36.8	34.2	32.6	34.5	32.9	31.3	33.2	31.6	29.9				
	gpm	24.2	18.7	14.9	23.5	18.0	14.4	22.7	17.5	13.8	21.9	16.8	13.3				
	wpd	38.4	22.9	14.6	36.2	21.3	13.5	33.8	20.0	12.5	31.4	18.4	11.6				
78	TC	95.6	92.1	88.4	92.7	89.1	85.3	89.7	86.0	82.1	86.6	82.9	78.8				
	SC	39.7	38.2	36.6	38.4	36.8	35.2	37.1	35.5	33.9	35.8	34.2	32.6				
	gpm	24.2	18.7	14.9	23.4	18.0	14.4	22.7	17.4	13.9	21.9	16.8	13.3				
	wpd	38.4	22.9	14.6	35.9	21.3	13.5	33.8	19.9	12.6	31.4	18.4	11.6				
80	TC	95.6	92.1	88.4	92.7	89.1	85.3	89.7	86.0	82.1	86.6	82.9	78.8				
	SC	42.3	40.8	39.2	41.0	39.5	37.9	39.7	38.2	36.5	38.4	36.8	35.2				
	gpm	24.2	18.7	14.9	23.5	18.0	14.4	22.7	17.4	13.9	21.9	16.8	13.3				
	wpd	38.4	22.9	14.6	36.2	21.3	13.7	33.8	19.9	12.6	31.4	18.4	11.6				
82	TC	95.6	92.1	88.4	92.7	89.1	85.3	89.7	86.0	82.1	86.7	82.9	78.8				
	SC	44.9	43.4	41.8	43.6	42.1	40.5	42.3	40.8	39.2	41.0	39.5	37.8				
	gpm	24.2	18.7	14.9	23.5	18.0	14.4	22.7	17.5	13.9	22.0	16.8	13.3				
	wpd	38.4	22.9	14.6	36.2	21.3	13.7	33.8	20.0	12.6	31.6	18.6	11.6				
84	TC	95.6	92.1	88.4	92.7	89.1	85.3	89.7	86.0	82.1	86.7	82.9	78.7				
	SC	47.5	46.0	44.4	46.2	44.7	43.1	44.9	43.4	41.7	43.6	42.0	40.4				
	gpm	24.2	18.7	14.9	23.5	18.0	14.4	22.7	17.5	13.9	22.0	16.8	13.3				
	wpd	38.4	22.9	14.6	36.2	21.3	13.7	33.8	20.0	12.6	31.6	18.6	11.6				
86	TC	95.6	92.0	88.3	92.7	89.1	85.3	89.7	86.0	82.1	86.6	82.8	78.9				
	SC	50.1	48.5	46.9	48.8	47.3	45.7	47.5	45.9	44.4	46.2	44.6	43.0				
	gpm	24.2	18.6	14.9	23.5	18.0	14.4	22.7	17.5	13.9	22.0	16.8	13.3				
	wpd	38.4	22.7	14.6	36.2	21.3	13.7	33.8	20.0	12.6	31.6	18.4	11.6				
88	TC	95.6	92.0	88.4	92.6	88.9	85.2	89.6	85.9	82.2	86.5	82.9	79.1				
	SC	52.7	51.1	49.6	51.3	49.8	48.2	50.0	48.5	47.0	48.7	47.2	45.7				
	gpm	24.2	18.6	14.9	23.5	18.0	14.4	22.7	17.4	13.9	21.9	16.8	13.4				
	wpd	38.4	22.7	14.6	36.2	21.2	13.5	33.8	19.9	12.6	31.4	18.6	11.8				
90	TC	95.5	92.0	88.5	92.5	89.0	85.5	89.5	86.0	82.4	86.5	82.9	79.3				
	SC	55.2	53.7	52.2	53.9	52.4	50.9	52.6	51.1	49.7	51.3	49.8	48.4				
	gpm	24.2	18.6	14.9	23.5	18.0	14.4	22.7	17.4	13.9	22.0	16.8	13.4				
	wpd	38.4	22.7	14.6	36.2	21.3	13.7	33.8	19.9	12.6	31.6	18.4	11.8				

5-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	91.0	89.1	86.9	88.4	86.4	84.2	85.8	83.7	81.3	83.1	80.9	78.5				
	SC	34.4	33.5	32.4	33.2	32.2	31.1	31.9	30.9	29.8	30.7	29.6	28.5				
	gpm	23.0	18.0	14.7	22.4	17.5	14.2	21.8	16.9	13.7	21.1	16.4	13.2				
	wpd	48.6	29.9	19.9	46.3	28.1	18.6	43.7	26.4	17.3	41.0	24.6	16.1				
76	TC	91.0	89.2	87.0	88.5	86.5	84.3	85.9	83.8	81.5	83.2	81.0	78.6				
	SC	36.8	35.9	34.8	35.5	34.6	33.5	34.3	33.3	32.2	33.0	32.0	30.9				
	gpm	23.0	18.1	14.7	22.4	17.6	14.3	21.8	17.0	13.8	21.1	16.4	13.3				
	wpd	48.6	30.2	19.9	46.0	28.3	18.8	43.7	26.6	17.5	41.0	24.9	16.3				
78	TC	91.1	89.2	87.1	88.5	86.6	84.4	85.9	83.9	81.5	83.3	81.1	78.7				
	SC	39.1	38.3	37.2	37.9	37.0	35.9	36.6	35.7	34.5	35.4	34.4	33.3				
	gpm	23.1	18.1	14.7	22.4	17.6	14.3	21.7	17.0	14.4	21.1	16.4	13.3				
	wpd	48.9	30.2	19.9	46.0	28.3	18.8	43.2	26.6	19.1	41.0	24.9	16.3				
80	TC	91.1	89.3	87.1	88.5	86.6	84.4	85.9	83.9	81.6	83.2	81.2	78.8				
	SC	41.5	40.6	39.6	40.3	39.4	38.3	39.0	38.1	37.0	37.8	36.8	35.7				
	gpm	23.1	18.1	14.7	22.4	17.6	14.2	21.7	17.0	13.8	21.0	16.4	13.3				
	wpd	48.9	30.2	19.9	46.0	28.3	18.6	43.4	26.6	17.5	40.7	24.9	16.3				
82	TC	91.1	89.3	87.2	88.5	86.6	84.4	85.9	83.9	81.7	83.3	81.2	78.8				
	SC	43.9	43.0	42.0	42.6	41.7	40.7	41.4	40.4	39.4	40.1	39.2	38.1				
	gpm	23.1	18.1	14.7	22.4	17.6	14.2	21.7	17.0	13.8	21.0	16.4	13.3				
	wpd	48.9	30.2	19.9	46.0	28.3	18.6	43.4	26.6	17.5	40.7	24.9	16.3				
84	TC	91.1	89.3	87.2	88.5	86.6	84.4	85.9	83.9	81.6	83.3	81.2	78.8				
	SC	46.2	45.3	44.3	45.0	44.1	43.0	43.7	42.8	41.7	42.5	41.5	40.4				
	gpm	23.1	18.1	14.7	22.4	17.6	14.3	21.7	17.0	13.8	21.0	16.4	13.3				
	wpd	48.9	30.2	19.9	46.3	28.3	18.8	43.4	26.6	17.5	40.7	24.9	16.3				
86	TC	91.0	89.3	87.2	88.5	86.6	84.4	85.9	83.9	81.7	83.2	81.2	78.8				
	SC	48.6	47.7	46.7	47.3	46.4	45.4	46.1	45.1	44.1	44.8	43.8	42.8				
	gpm	23.1	18.1	14.7	22.4	17.6	14.3	21.7	17.0	13.8	21.0	16.4	13.3				
	wpd	48.9	30.2	19.9	46.3	28.3	18.8	43.4	26.6	17.5	40.7	24.9	16.3				
88	TC	91.0	89.2	87.2	88.4	86.6	84.5	85.8	83.9	81.7	83.2	81.2	78.9				
	SC	50.9	50.0	49.0	49.6	48.8	47.8	48.4	47.5	46.5	47.1	46.2	45.2				
	gpm	23.1	18.1	14.8	22.4	17.6	14.3	21.7	17.0	13.8	21.0	16.4	13.3				
	wpd	48.9	30.2	20.1	46.3	28.3	18.8	43.4	26.6	17.5	40.7	24.9	16.3				
90	TC	90.9	89.2	87.2	88.4	86.6	84.6	85.8	83.9	81.8	83.1	81.2	79.1				
	SC	53.2	52.3	51.4	52.0	51.1	50.2	50.7	49.8	48.9	49.5	48.6	47.6				
	gpm	23.1	18.0	14.8	22.4	17.6	14.3	21.7	17.1	13.9	21.0	16.5	13.4				
	wpd	48.9	29.9	20.1	46.3	28.3	18.8	43.4	26.8	17.7	40.7	25.1	16.5				

2-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	76.2	71.8	67.4	73.7	69.3	64.8	71.2	66.7	62.2	68.7	64.2	59.6				
	SC	25.1	23.4	21.8	24.1	22.5	20.9	23.2	21.6	19.9	22.2	20.6	19.0				
	gpm	19.3	14.6	11.4	18.7	14.0	10.9	18.0	13.5	10.5	17.3	13.0	10.1				
	wpd	60.8	34.7	21.2	57.0	32.1	19.5	53.3	30.0	18.1	49.2	27.7	16.6				
78	TC	76.1	71.7	67.3	73.7	69.2	64.7	71.1	66.6	62.1	68.5	64.1	59.5				
	SC	27.6	25.9	24.3	26.6	25.0	23.4	25.7	24.1	22.5	24.8	23.2	21.6				
	gpm	19.3	14.6	11.4	18.7	14.0	10.9	18.0	13.5	10.5	17.3	13.0	10.1				
	wpd	60.8	34.7	21.2	57.0	32.1	19.5	53.3	30.0	18.1	49.2	27.7	16.6				
80	TC	76.1	71.7	67.3	73.6	69.2	64.7	71.1	66.6	62.1	68.5	64.1	59.5				
	SC	30.1	28.4	26.8	29.1	27.5	25.8	28.2	26.5	24.9	27.2	25.6	24.0				
	gpm	19.3	14.6	11.4	18.7	14.0	10.9	18.0	13.5	10.5	17.3	13.0	10.1				
	wpd	60.8	34.7	21.2	57.0	32.1	19.5	53.3	29.7	18.1	49.2	27.7	16.6				
82	TC	76.1	71.7	67.4	73.7	69.3	64.9	71.2	66.8	62.4	68.7	64.2	59.8				
	SC	32.5	30.8	29.2	31.5	29.9	28.3	30.6	29.0	27.4	29.6	28.0	26.4				
	gpm	19.3	14.5	11.4	18.7	14.1	11.0	18.0	13.5	10.5	17.4	13.0	10.1				
	wpd	60.8	34.3	21.2	57.0	32.5	19.8	53.3	30.0	18.1	49.7	27.7	16.6				
84	TC	76.3	72.0	67.6	73.9	69.5	65.1	71.4	67.0	62.6	68.9	64.5	60.0				
	SC	34.9	33.3	31.6	34.0	32.3	30.7	33.0	31.4	29.8	32.1	30.5	28.9				
	gpm	19.4	14.6	11.4	18.7	14.0	11.0	18.1	13.6	10.6	17.4	13.1	10.1				
	wpd	61.3	34.7	21.2	57.5	32.1	19.8	53.7	30.4	18.4	49.7	28.0	16.8				
86	TC	76.5	72.2	67.8	74.1	69.7	65.3	71.6	67.1	62.7	69.1	64.6	60.1				
	SC	37.4	35.7	34.1	36.4	34.8	33.1	35.5	33.8	32.2	34.5	32.9	31.3				
	gpm	19.4	14.6	11.5	18.7	14.1	11.0	18.1	13.5	10.6	17.5	13.1	10.1				
	wpd	61.8	35.0	21.5	57.5	32.5	19.8	53.7	30.0	18.4	50.1	28.0	16.8				
88	TC	76.7	72.4	68.0	74.3	69.9	65.4	71.8	67.3	62.8	69.3	64.8	60.2				
	SC	39.8	38.1	36.5	38.9	37.2	35.5	37.9	36.2	34.6	37.0	35.3	33.6				
	gpm	19.4	14.6	11.5	18.8	14.2	11.1	18.2	13.6	10.6	17.6	13.2	10.1				
	wpd	61.3	35.0	21.5	57.9	32.9	20.1	54.2	30.4	18.4	50.6	28.4	16.8				
90	TC	76.9	72.6	68.1	74.5	70.0	65.5	72.0	67.4	62.9	69.4	64.8	60.2				
	SC	42.2	40.5	38.9	41.3	39.6	37.9	40.3	38.6	37.0	39.4	37.7	36.0				
	gpm	19.4	14.7	11.5	18.9	14.2	11.1	18.3	13.6	10.6	17.6	13.1	10.1				
	wpd	61.8	35.4	21.8	58.4	32.9	20.1	54.6	30.4	18.4	50.6	28.0	16.8				

3-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	96.8	92.6	88.1	93.9	89.6	85.1	91.1	86.6	82.0	88.1	83.6	78.9				
	SC	33.2	31.4	29.6	31.9	30.2	28.4	30.8	28.9	27.2	29.5	27.8	26.0				
	gpm	24.4	18.7	14.9	23.7	18.2	14.3	23.1	17.5	13.8	22.3	16.9	13.4				
	wpd	54.7	32.2	20.4	51.5	30.2	18.8	49.0	28.1	17.6	45.6	26.3	16.4				
78	TC	96.8	92.5	88.0	93.9	89.5	85.0	90.9	86.5	81.9	88.0	83.4	78.7				
	SC	35.8	34.0	32.2	34.6	32.8	31.0	33.4	31.6	29.8	32.2	30.4	28.6				
	gpm	24.4	18.7	14.9	23.7	18.2	14.3	23.0	17.5	13.8	22.3	16.9	13.3				
	wpd	54.7	32.2	20.4	51.5	30.2	18.8	48.4	28.1	17.6	45.6	26.1	16.2				
80	TC	96.7	92.4	88.0	93.8	89.4	85.0	90.8	86.4	81.9	87.9	83.4	78.7				
	SC	38.4	36.7	34.9	37.2	35.5	33.7	36.0	34.2	32.5	34.8	33.0	31.3				
	gpm	24.4	18.7	14.9	23.7	18.1	14.3	23.0	17.5	13.8	22.3	16.9	13.3				
	wpd	54.7	32.2	20.4	51.5	30.0	18.8	48.4	28.1	17.6	45.6	26.1	16.2				
82	TC	96.7	92.5	88.1	93.8	89.5	85.1	90.9	86.5	82.0	87.9	83.5	78.9				
	SC	41.1	39.3	37.6	39.8	38.1	36.4	38.6	36.9	35.2	37.4	35.7	34.0				
	gpm	24.4	18.7	14.9	23.7	18.2	14.3	23.0	17.5	13.8	22.2	16.9	13.3				
	wpd	54.7	32.2	20.4	51.5	30.2	18.8	48.4	28.1	17.6	45.3	26.1	16.2				
84	TC	96.8	92.6	88.2	93.9	89.6	85.2	91.0	86.6	82.1	88.0	83.6	79.0				
	SC	43.7	42.0	40.2	42.5	40.8	39.0	41.3	39.6	37.8	40.1	38.4	36.6				
	gpm	24.5	18.7	14.9	23.8	18.2	14.4	23.0	17.5	13.8	22.2	16.9	13.4				
	wpd	55.1	32.2	20.4	51.8	30.2	19.0	48.4	28.1	17.6	45.3	26.3	16.4				
86	TC	96.9	92.7	88.3	94.0	89.7	85.2	91.0	86.7	82.2	88.1	83.6	79.0				
	SC	46.4	44.6	42.9	45.2	43.4	41.7	43.9	42.2	40.5	42.7	41.0	39.3				
	gpm	24.5	18.8	14.9	23.8	18.2	14.4	23.0	17.6	13.8	22.2	16.9	13.4				
	wpd	55.1	32.4	20.4	51.8	30.2	19.0	48.7	28.4	17.6	45.3	26.3	16.4				
88	TC	97.0	92.7	88.3	94.1	89.8	85.3	91.1	86.7	82.2	88.1	83.7	79.0				
	SC	49.0	47.3	45.5	47.8	46.1	44.3	46.6	44.9	43.1	45.4	43.6	41.9				
	gpm	24.5	18.8	14.9	23.8	18.2	14.4	23.0	17.6	13.9	22.3	16.9	13.4				
	wpd	55.1	32.4	20.4	51.8	30.2	19.0	48.7	28.4	17.8	45.6	26.3	16.4				
90	TC	97.0	92.8	88.3	94.1	89.8	85.2	91.2	86.7	82.1	88.1	83.6	79.0				
	SC	51.6	49.9	48.1	50.4	48.7	46.9	49.2	47.5	45.7	48.0	46.2	44.5				
	gpm	24.6	18.8	14.9	23.9	18.2	14.3	23.0	17.6	13.8	22.3	16.9	13.4				
	wpd	55.5	32.4	20.4	52.2	30.5	18.8	48.7	28.4	17.6	45.6	26.3	16.4				

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC													
	SC													
	gpm													
76	TC	105.4	101.9	98.0	102.5	98.8	95.0	99.5	95.7	91.8	96.4	92.6	88.5	
	SC	37.0	35.4	33.8	35.7	34.1	32.5	34.4	32.8	31.1	33.0	31.5	29.8	
	gpm	26.7	20.7	16.5	26.0	20.0	16.0	25.2	19.4	15.5	24.4	18.8	15.0	
78	TC	105.3	101.8	97.9	102.4	98.8	94.9	99.4	95.7	91.7	96.3	92.5	88.4	
	SC	39.5	38.0	36.4	38.2	36.7	35.1	36.9	35.4	33.7	35.6	34.1	32.4	
	gpm	26.7	20.7	16.5	25.9	20.0	16.0	25.2	19.4	15.5	24.4	18.8	14.9	
80	TC	105.2	101.7	97.9	102.3	98.7	94.8	99.3	95.6	91.7	96.2	92.4	88.4	
	SC	42.1	40.6	39.0	40.8	39.3	37.6	39.5	38.0	36.3	38.2	36.6	35.0	
	gpm	26.7	20.6	16.5	25.9	20.0	16.0	25.2	19.4	15.5	24.4	18.8	14.9	
82	TC	105.2	101.7	97.9	102.3	98.7	94.8	99.3	95.6	91.7	96.2	92.5	88.5	
	SC	44.7	43.2	41.6	43.4	41.9	40.3	42.1	40.6	39.0	40.8	39.3	37.7	
	gpm	26.7	20.6	16.5	25.9	20.0	16.0	25.2	19.4	15.5	24.4	18.8	15.0	
84	TC	105.2	101.7	98.0	102.3	98.7	94.8	99.3	95.6	91.7	96.3	92.5	88.5	
	SC	47.3	45.8	44.2	46.0	44.5	42.9	44.7	43.2	41.6	43.4	41.9	40.3	
	gpm	26.7	20.5	16.5	25.9	20.0	16.0	25.2	19.4	15.5	24.4	18.8	15.0	
86	TC	105.2	101.7	98.0	102.3	98.6	94.8	99.3	95.6	91.6	96.3	92.5	88.4	
	SC	49.9	48.4	46.8	48.6	47.1	45.5	47.3	45.8	44.2	46.0	44.5	42.8	
	gpm	26.7	20.6	16.5	25.9	20.0	16.0	25.2	19.4	15.5	24.4	18.8	14.9	
88	TC	105.2	101.7	97.9	102.3	98.6	94.8	99.3	95.5	91.6	96.2	92.3	88.4	
	SC	52.5	51.0	49.4	51.2	49.7	48.1	49.9	48.3	46.8	48.6	47.1	45.4	
	gpm	26.7	20.6	16.5	25.9	20.0	16.0	25.2	19.3	15.5	24.4	18.8	14.9	
90	TC	105.2	101.6	97.9	102.3	98.6	94.8	99.2	95.5	91.6	96.2	92.3	88.4	
	SC	55.1	53.6	52.0	53.8	52.2	50.6	52.5	50.9	49.4	51.2	49.6	48.1	
	gpm	26.7	20.6	16.5	25.9	20.0	16.0	25.2	19.3	15.5	24.4	18.7	14.9	
	wpd	46.7	27.8	17.9	44.0	26.1	16.9	41.6	24.7	15.7	39.0	23.1	14.6	

5-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
76	TC	99.7	97.8	95.6	97.1	95.2	92.9	94.5	92.5	90.1	91.8	89.7	87.2
	SC	36.7	35.8	34.7	35.4	34.5	33.4	34.2	33.2	32.1	32.9	31.9	30.8
	gpm	25.2	19.8	16.2	24.5	19.3	15.7	23.8	18.7	15.3	23.3	18.2	14.8
78	TC	99.7	97.9	95.8	97.2	95.2	93.0	94.5	92.5	94.2	91.9	89.8	87.4
	SC	39.1	38.2	37.1	37.8	36.9	35.8	36.5	35.6	36.4	35.3	34.3	33.2
	gpm	25.2	19.8	16.2	24.6	19.3	15.7	23.9	18.7	15.9	23.3	18.2	14.8
80	TC	99.7	98.0	95.8	97.2	95.3	93.1	94.6	92.6	90.3	91.9	89.8	87.5
	SC	41.4	40.5	39.5	40.2	39.3	38.2	38.9	38.0	36.9	37.7	36.7	35.6
	gpm	25.2	19.8	16.2	24.6	19.4	15.7	23.9	18.8	15.3	23.2	18.2	14.8
82	TC	99.8	98.0	95.9	97.2	95.4	93.2	94.6	92.7	90.4	91.9	89.9	87.5
	SC	43.8	42.9	41.9	42.5	41.6	40.6	41.3	40.4	39.3	40.0	39.1	38.0
	gpm	25.3	19.9	16.2	24.6	19.4	15.7	23.9	18.8	15.3	23.3	18.2	14.8
84	TC	99.8	98.0	95.9	97.2	95.4	93.2	94.6	92.7	90.4	92.0	89.9	87.5
	SC	46.2	45.3	44.3	44.9	44.0	43.0	43.7	42.7	41.7	42.4	41.5	40.4
	gpm	25.3	19.9	16.2	24.6	19.4	15.7	24.0	18.8	15.3	23.3	18.2	14.8
86	TC	99.8	98.0	96.0	97.2	95.4	93.2	94.6	92.7	90.4	91.9	89.9	87.5
	SC	48.5	47.6	46.7	47.3	46.4	45.3	46.0	45.1	44.0	44.8	43.8	42.7
	gpm	25.3	19.9	16.2	24.6	19.4	15.7	24.0	18.8	15.3	23.3	18.2	14.8
88	TC	99.7	98.0	95.9	97.2	95.4	93.2	94.6	92.7	90.4	91.9	89.9	87.6
	SC	50.8	50.0	49.0	49.6	48.7	47.7	48.3	47.4	46.4	47.1	46.2	45.1
	gpm	25.3	19.9	16.2	24.6	19.4	15.7	24.0	18.8	15.3	23.3	18.2	14.8
90	TC	99.7	97.9	95.9	97.2	95.3	93.2	94.5	92.6	90.4	91.9	89.9	87.6
	SC	53.2	52.3	51.3	51.9	51.1	50.1	50.7	49.8	48.7	49.4	48.5	47.5
	gpm	25.3	19.8	16.2	24.6	19.4	15.7	24.0	18.8	15.3	23.3	18.2	14.8
	wpd	58.8	36.0	24.2	55.6	34.5	22.8	52.8	32.5	21.4	49.8	30.6	20.1

2-Row Chilled Water Cooling

EDB	EWT	43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	39.3	36.3	32.6	37.3	34.5	31.0	35.4	32.8	29.3	33.6	31.2	27.8						
	SC	34.4	32.9	30.4	33.5	31.8	29.2	32.6	30.8	28.2	31.7	29.9	26.9						
	gpm	9.9	7.4	5.5	9.5	7.0	5.2	9.0	6.7	5.0	8.5	6.3	4.7						
	wpd	16.1	8.9	5.0	14.6	8.0	4.4	13.2	7.3	4.0	11.9	6.5	3.5						
76	TC	41.0	38.5	35.6	39.3	37.0	34.1	37.6	35.5	31.5	36.1	34.1	30.1						
	SC	38.1	36.4	34.2	37.2	35.3	33.0	36.1	34.4	31.1	35.1	33.2	29.7						
	gpm	10.4	7.8	6.0	9.9	7.4	5.7	9.5	7.2	5.4	9.1	6.9	5.0						
	wpd	17.7	10.0	6.0	16.1	9.1	5.4	14.9	8.5	4.7	13.5	7.8	4.2						
78	TC	43.3	41.1	38.7	41.7	39.7	36.4	40.3	37.7	34.9	38.6	36.3	33.5						
	SC	41.6	39.9	37.7	40.6	38.7	36.0	39.5	37.3	34.5	38.1	35.9	33.0						
	gpm	10.9	8.3	6.5	10.5	8.1	6.1	10.2	7.7	5.9	9.8	7.4	5.7						
	wpd	19.6	11.3	6.9	18.2	10.6	6.1	16.9	9.6	5.7	15.6	8.9	5.2						
80	TC	45.9	43.5	41.1	44.3	42.1	39.7	42.9	40.6	38.2	41.5	39.2	36.8						
	SC	45.0	42.9	40.6	43.7	41.5	39.2	42.3	40.1	37.7	40.9	38.7	36.3						
	gpm	11.6	8.8	7.0	11.2	8.5	6.7	10.9	8.2	6.4	10.5	8.0	6.2						
	wpd	22.1	12.8	8.0	20.7	11.9	7.3	19.3	11.1	6.8	17.9	10.4	6.3						
82	TC	48.6	46.3	44.0	47.1	44.9	42.7	45.7	43.5	41.3	44.3	42.1	39.8						
	SC	47.9	45.7	43.5	46.5	44.4	42.1	45.1	43.0	40.7	43.8	41.6	39.3						
	gpm	12.3	9.4	7.4	11.9	9.1	7.2	11.6	8.8	7.0	11.2	8.5	6.7						
	wpd	24.9	14.4	9.1	23.3	13.7	8.5	21.8	12.8	8.0	20.7	11.9	7.4						
84	TC	51.4	49.2	46.9	50.0	47.8	45.5	48.6	46.4	44.1	47.2	45.0	42.7						
	SC	50.8	48.5	46.3	49.4	47.1	44.9	48.0	45.8	43.6	46.6	44.4	42.2						
	gpm	13.0	9.9	7.9	12.6	9.7	7.7	12.3	9.4	7.4	11.9	9.1	7.2						
	wpd	27.8	16.1	10.2	26.1	15.4	9.6	24.9	14.4	9.1	23.3	13.7	8.5						
86	TC	54.3	52.0	49.8	52.9	50.6	48.4	51.5	49.2	47.0	50.0	47.8	45.6						
	SC	53.6	51.4	49.2	52.2	50.0	47.8	50.8	48.6	46.4	49.4	47.2	45.0						
	gpm	13.7	10.5	8.5	13.4	10.2	8.1	13.0	9.9	7.9	12.7	9.7	7.7						
	wpd	30.8	18.2	11.7	29.4	17.1	10.8	27.8	16.1	10.2	26.5	15.4	9.6						
88	TC	57.1	54.9	52.7	55.7	53.5	51.3	54.3	52.1	49.9	52.9	50.7	48.5						
	SC	56.4	54.2	52.0	55.0	52.8	50.6	53.6	51.4	49.2	52.2	50.0	47.9						
	gpm	14.5	11.1	8.9	14.1	10.9	8.7	13.8	10.5	8.5	13.4	10.2	8.2						
	wpd	34.4	20.1	13.0	32.6	19.3	12.3	31.2	18.2	11.7	29.4	17.1	11.1						
90	TC	60.0	57.8	55.6	58.6	56.4	54.2	57.1	55.0	52.8	55.7	53.5	51.4						
	SC	59.2	57.0	54.8	57.8	55.6	53.5	56.4	54.2	52.1	55.0	52.9	50.7						
	gpm	15.2	11.7	9.4	14.9	11.4	9.1	14.5	11.2	8.9	14.1	10.9	8.7						
	wpd	37.8	22.4	14.4	36.3	21.3	13.7	34.4	20.4	13.0	32.6	19.3	12.3						

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	52.3	47.9	43.2	49.6	45.2	40.9	46.8	42.8	38.9	44.2	40.5	32.9
	SC	42.6	40.5	38.1	41.4	39.2	36.8	40.2	38.1	35.7	38.9	36.8	32.5
	gpm	13.3	9.7	7.3	12.5	9.1	6.9	11.9	8.6	6.6	11.2	8.2	5.5
	wpd	16.2	8.6	4.9	14.4	7.6	4.4	13.0	6.8	4.0	11.6	6.2	2.8
76	TC	53.8	50.3	46.5	51.2	47.8	44.4	48.7	45.8	39.1	46.5	43.8	37.2
	SC	46.6	44.7	42.5	45.4	43.6	41.4	44.2	42.4	38.6	43.1	41.3	36.8
	gpm	13.6	10.2	7.8	12.9	9.7	7.5	12.3	9.3	6.6	11.7	8.9	6.3
	wpd	17.0	9.5	5.6	15.4	8.6	5.1	13.9	7.9	4.0	12.6	7.2	3.6
78	TC	55.6	53.0	49.8	53.4	51.0	45.0	51.3	49.1	43.3	49.3	45.3	41.5
	SC	50.7	49.1	47.1	49.6	48.1	44.5	48.5	46.9	42.8	47.4	44.7	40.9
	gpm	14.1	10.7	8.4	13.5	10.3	7.6	13.0	9.9	7.3	12.5	9.1	7.0
	wpd	18.2	10.6	6.5	16.8	9.8	5.3	15.6	9.0	4.9	14.2	7.6	4.5
80	TC	58.0	56.0	50.8	56.0	52.5	49.0	53.2	50.8	47.3	51.5	49.1	45.5
	SC	55.0	53.5	50.2	53.9	51.9	48.4	52.6	50.2	46.7	50.9	48.5	44.9
	gpm	14.7	11.3	8.6	14.2	10.7	8.3	13.5	10.3	8.0	13.0	9.9	7.7
	wpd	19.9	11.7	6.7	18.4	10.4	6.3	16.8	9.7	5.8	15.6	9.0	5.4
82	TC	60.0	57.8	54.7	58.3	56.1	52.9	56.6	54.5	51.2	54.9	52.8	49.5
	SC	59.2	57.1	54.0	57.6	55.4	52.3	55.9	53.8	50.6	54.3	52.1	48.9
	gpm	15.2	11.7	9.2	14.8	11.3	9.0	14.3	11.1	8.6	13.9	10.7	8.4
	wpd	21.3	12.6	7.8	20.1	11.7	7.4	18.8	11.2	6.8	17.8	10.4	6.5
84	TC	63.3	61.2	58.4	61.6	59.6	56.7	60.0	57.9	55.0	58.3	56.2	53.4
	SC	62.5	60.5	57.7	60.9	58.8	56.0	59.3	57.2	54.3	57.6	55.5	52.7
	gpm	16.0	12.4	9.9	15.6	12.1	9.6	15.2	11.7	9.3	14.8	11.4	9.0
	wpd	23.4	14.0	8.9	22.2	13.3	8.5	21.3	12.6	7.9	20.1	11.9	7.5
86	TC	66.7	64.6	62.2	65.0	63.0	60.5	63.3	61.3	58.8	61.7	59.6	57.1
	SC	65.9	63.9	61.4	64.2	62.2	59.8	62.6	60.5	58.1	60.9	58.9	56.4
	gpm	16.9	13.1	10.5	16.5	12.8	10.2	16.0	12.5	9.9	15.6	12.1	9.6
	wpd	26.1	15.8	10.1	24.8	15.0	9.5	23.4	14.2	9.0	22.2	13.3	8.5
88	TC	70.1	68.0	65.9	68.4	66.4	64.2	66.7	64.7	62.5	65.0	63.0	60.8
	SC	69.2	67.2	65.1	67.6	65.6	63.4	65.9	63.9	61.8	64.2	62.2	60.1
	gpm	17.8	13.8	11.2	17.3	13.4	10.8	16.9	13.1	10.6	16.5	12.8	10.3
	wpd	28.9	17.4	11.4	27.3	16.6	10.8	26.1	15.8	10.3	24.8	15.0	9.7
90	TC	73.4	71.4	69.3	71.8	69.8	67.6	70.1	68.1	65.9	68.4	66.4	64.3
	SC	72.5	70.6	68.4	70.9	68.9	66.8	69.2	67.3	65.1	67.6	65.6	63.5
	gpm	18.6	14.5	11.6	18.2	14.2	11.4	17.8	13.8	11.1	17.3	13.4	10.8
	wpd	31.6	19.3	12.4	30.2	18.4	11.9	28.9	17.6	11.2	27.3	16.6	10.8

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	46.3	42.3	38.4	43.8	39.9	36.3	41.2	37.5	34.5	38.8	35.5	32.7												
	SC	35.5	33.6	31.8	34.3	32.5	30.9	33.1	31.5	30.0	32.1	30.6	29.1												
	gpm	11.7	8.6	6.5	11.1	8.0	6.2	10.4	7.6	5.9	9.8	7.2	5.5												
	wpd	9.0	4.8	2.8	8.0	4.2	2.5	7.1	3.8	2.2	6.3	3.4	2.0												
76	TC	47.2	43.9	40.8	44.8	41.8	39.0	42.5	39.7	37.3	40.4	37.9	31.1												
	SC	38.5	36.9	35.4	37.4	35.9	34.5	36.3	35.0	33.7	35.3	34.1	30.7												
	gpm	11.9	8.9	6.9	11.3	8.5	6.6	10.7	8.0	6.3	10.2	7.7	5.2												
	wpd	9.4	5.2	3.1	8.4	4.7	2.8	7.6	4.2	2.6	6.8	3.9	1.8												
78	TC	48.4	45.7	43.2	46.3	43.8	41.6	44.2	42.0	40.0	42.2	40.4	34.7												
	SC	41.6	40.3	39.0	40.6	39.3	38.2	39.6	38.5	37.3	38.7	37.7	34.3												
	gpm	12.3	9.3	7.3	11.7	8.9	7.1	11.2	8.5	6.7	10.7	8.2	5.9												
	wpd	9.9	5.7	3.5	9.0	5.2	3.3	8.3	4.7	3.0	7.6	4.4	2.2												
80	TC	49.9	47.7	45.7	47.8	46.0	41.1	46.0	44.5	39.7	44.4	41.1	38.2												
	SC	44.8	43.7	42.6	43.8	42.8	40.6	43.0	42.0	39.2	42.2	40.6	37.7												
	gpm	12.7	9.6	7.7	12.0	9.3	7.0	11.6	9.1	6.7	11.3	8.3	6.4												
	wpd	10.5	6.1	3.9	9.5	5.7	3.2	8.9	5.4	3.0	8.4	4.6	2.7												
82	TC	51.5	50.0	45.7	49.8	48.5	44.3	48.3	45.5	42.9	46.0	44.1	41.4												
	SC	48.1	47.2	45.2	47.2	46.4	43.8	46.4	44.9	42.4	45.5	43.5	40.9												
	gpm	13.0	10.1	7.7	12.6	9.8	7.5	12.3	9.2	7.2	11.6	8.9	7.0												
	wpd	11.1	6.7	3.9	10.4	6.3	3.6	9.9	5.6	3.4	8.9	5.2	3.2												
84	TC	53.6	51.2	48.9	51.5	49.8	47.5	50.2	48.5	46.1	48.9	47.1	44.7												
	SC	51.5	50.5	48.3	50.9	49.2	46.9	49.6	47.9	45.5	48.2	46.5	44.1												
	gpm	13.5	10.3	8.3	13.1	10.1	8.0	12.7	9.8	7.8	12.3	9.5	7.5												
	wpd	12.0	7.0	4.5	11.2	6.7	4.2	10.5	6.3	4.0	10.0	6.0	3.7												
86	TC	55.6	54.1	51.9	54.3	52.7	50.6	53.0	51.4	49.2	51.6	50.0	47.8												
	SC	54.9	53.4	51.3	53.6	52.1	50.0	52.3	50.7	48.6	51.0	49.4	47.2												
	gpm	14.1	11.0	8.8	13.7	10.7	8.6	13.4	10.4	8.3	13.1	10.1	8.1												
	wpd	13.1	7.9	5.1	12.3	7.5	4.8	11.8	7.1	4.6	11.2	6.7	4.3												
88	TC	58.3	56.9	54.9	57.0	55.6	53.6	56.7	54.3	52.3	54.4	52.9	50.9												
	SC	57.6	56.2	54.2	56.3	54.9	52.9	55.0	53.6	51.6	53.7	52.3	50.3												
	gpm	14.8	11.5	9.2	14.4	11.3	9.1	14.1	11.0	8.8	13.8	10.7	8.6												
	wpd	14.3	8.7	5.6	13.7	8.4	5.4	13.1	7.9	5.1	12.5	7.6	4.8												
90	TC	61.0	59.7	57.9	59.7	58.4	56.5	58.4	57.1	55.2	57.1	55.8	53.9												
	SC	60.3	59.0	57.2	59.0	57.7	55.8	57.7	56.4	54.5	56.4	55.1	53.2												
	gpm	15.5	12.1	9.8	15.2	11.9	9.5	14.8	11.5	9.3	14.5	11.3	9.1												
	wpd	15.7	9.6	6.3	15.1	9.2	6.0	14.4	8.7	5.7	13.8	8.4	5.4												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	71.0	68.6	65.5	67.4	65.1	62.0	63.8	61.6	58.8	60.3	58.2	55.6												
	SC	56.9	55.6	54.0	55.0	53.8	52.2	53.2	52.1	50.6	51.4	50.4	49.0												
	gpm	18.0	13.9	11.1	17.1	13.2	10.5	16.1	12.5	9.9	15.2	11.8	9.4												
	wpd	29.6	17.7	11.2	26.6	16.0	10.1	23.8	14.3	9.0	21.2	12.8	8.1												
76	TC	71.9	69.8	67.4	68.4	66.5	64.2	65.1	63.3	61.2	61.7	60.3	58.4												
	SC	61.2	60.2	58.8	59.4	58.5	57.2	57.7	56.8	55.7	56.1	55.3	54.3												
	gpm	18.2	14.1	11.4	17.3	13.5	10.8	16.5	12.8	10.3	15.6	12.2	9.9												
	wpd	30.4	18.3	11.9	27.4	16.6	10.7	24.8	15.0	9.7	22.4	13.7	9.0												
78	TC	73.0	71.3	69.6	69.7	68.3	66.7	66.6	65.4	67.2	63.6	62.7	61.6												
	SC	65.7	64.8	63.9	64.0	63.2	62.3	62.4	61.7	62.6	60.9	60.3	59.7												
	gpm	18.5	14.4	11.7	17.6	13.8	11.2	16.9	13.2	11.4	16.1	12.7	10.4												
	wpd	31.2	19.0	12.6	28.5	17.5	11.5	26.1	16.0	11.9	23.8	14.8	9.9												
80	TC	74.3	73.2	72.0	71.3	70.4	69.5	68.5	67.8	67.2	65.9	65.5	65.0												
	SC	70.3	69.7	69.0	68.7	68.2	67.6	67.3	66.8	66.4	65.9	65.6	65.2												
	gpm	18.8	14.8	12.1	18.1	14.3	11.7	17.4	13.8	11.3	16.6	13.3	11.0												
	wpd	32.4	20.1	13.5	29.8	18.7	12.6	27.7	17.5	11.7	25.3	16.2	11.0												
82	TC	76.0	75.4	74.9	73.4	73.1	72.7	71.1	70.9	68.7	67.8	67.5	66.8												
	SC	75.1	74.7	74.4	73.7	73.4	73.1	72.4	72.2	70.3	69.9	69.7	69.4												
	gpm	19.2	15.3	12.6	18.6	14.8	12.3	18.1	14.4	11.6	17.1	13.7	11.2												
	wpd	33.8	21.4	14.6	31.5	20.1	13.9	29.8	19.0	12.2	26.9	17.2	11.5												
84	TC	78.5	78.4	76.3	75.2	74.9	74.4	73.4	73.0	72.5	71.5	71.2	70.6												
	SC	80.3	80.1	78.1	77.5	77.4	77.1	76.6	76.4	76.2	75.6	75.4	74.8												
	gpm	19.9	15.9	12.9	19.0	15.2	12.6	18.6	14.8	12.2	18.1	14.5	12.0												
	wpd	36.2	23.1	15.2	33.2	21.2	14.4	31.5	20.1	13.7	30.1	19.2	13.1												
86	TC	80.7	80.4	80.0	78.8	78.6	78.1	77.0	76.7	76.3	75.2	74.9	74.4												
	SC	84.3	84.1	83.9	83.3	83.2	82.8	81.5	81.3	80.8	79.6	79.3	78.8												
	gpm	20.5	16.2	13.6	20.0	15.9	13.2	19.5	15.6	12.9	19.0	15.2	12.6												
	wpd	38.3	24.1	16.8	36.5	23.1	16.0	35.0	22.2	15.2	33.2	21.2	14.4												
88	TC	84.3	84.1	83.7	82.4	82.2	81.8	80.6	80.4	80.0	78.8	78.5	78.1												
	SC	89.3	89.1	88.7	87.3	87.1	86.7	85.4	85.1	84.7	83.4	83.2	82.7												
	gpm	21.4	17.1	14.1	20.9	16.6	13.8	20.5	16.2	13.6	20.0	15.9	13.2												
	wpd	41.8	26.6	18.3	39.9	25.3	17.5	38.3	24.1	16.8	36.5	23.1	16.0												
90	TC	87.9	87.7	87.4	86.1	85.9	85.5	84.2	84.1	83.7	82.4	82.2	81.8												
	SC	93.1	92.9	92.6	91.1	91.0	90.6	89.2	89.0	88.6	87.3	87.1	86.7												
	gpm	22.3	17.8	14.8	21.9	17.4	14.5	21.4	17.1	14.1	20.9	16.6	13.8												
	wpd	45.5	29.0	20.1	43.8	27.7	19.2	41.8	26.6	18.3	39.9	25.3	17.5												

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	43.9	39.8	34.7	41.3	37.5	32.7	38.9	35.0	30.5	36.5	33.0	28.6												
	SC	32.9	31.1	28.7	31.8	30.0	27.8	30.8	29.0	26.6	29.8	28.0	25.8												
	gpm	11.1	8.1	5.9	10.5	7.6	5.5	9.8	7.1	5.1	9.2	6.7	4.8												
	wpd	20.1	10.6	5.7	17.9	9.5	5.0	15.9	8.3	4.3	13.9	7.3	3.8												
76	TC	44.8	41.1	37.1	42.4	38.9	35.2	40.2	36.9	33.4	37.9	35.0	31.6												
	SC	36.3	34.5	32.5	35.3	33.4	31.5	34.3	32.7	30.6	33.2	31.7	29.4												
	gpm	11.3	8.3	6.3	10.8	7.9	6.0	10.2	7.4	5.7	9.6	7.1	5.4												
	wpd	21.0	11.3	6.5	19.0	10.2	5.8	16.9	9.1	5.2	15.1	8.3	4.7												
78	TC	46.0	42.7	39.7	43.7	40.8	37.9	41.7	39.0	36.3	39.8	37.3	34.6												
	SC	39.7	38.0	36.2	38.7	37.1	35.3	37.7	36.1	34.1	36.8	35.1	33.2												
	gpm	11.6	8.6	6.7	11.0	8.2	6.4	10.5	7.9	6.1	10.0	7.5	5.8												
	wpd	22.1	12.1	7.4	19.8	11.1	6.8	18.2	10.2	6.1	16.4	9.3	5.5												
80	TC	47.4	44.7	42.3	45.5	43.0	40.7	43.7	41.4	39.1	42.0	39.8	37.7												
	SC	43.1	41.5	39.9	42.3	40.6	38.8	41.2	39.5	37.8	40.3	38.6	36.7												
	gpm	12.0	9.1	7.1	11.5	8.7	6.9	11.1	8.4	6.6	10.6	8.1	6.4												
	wpd	23.6	13.5	8.3	21.6	12.3	7.8	20.1	11.5	7.1	18.5	10.6	6.6												
82	TC	49.3	47.0	44.8	47.6	45.5	43.4	46.1	44.0	41.3	44.6	42.2	39.9												
	SC	46.7	45.0	43.4	45.8	44.1	42.2	44.9	43.0	40.8	43.7	41.6	39.4												
	gpm	12.5	9.5	7.5	12.1	9.2	7.4	11.6	8.9	7.0	11.3	8.5	6.7												
	wpd	25.5	14.9	9.3	23.9	13.9	8.9	22.1	13.0	8.0	21.0	11.9	7.4												
84	TC	51.6	49.6	47.6	50.2	47.8	45.6	48.7	46.5	44.2	47.3	45.1	42.8												
	SC	50.2	48.4	46.5	49.2	47.2	45.0	48.1	45.9	43.6	46.7	44.5	42.2												
	gpm	13.1	10.0	8.1	12.7	9.7	7.7	12.3	9.5	7.4	11.9	9.1	7.2												
	wpd	28.1	16.4	10.6	26.5	15.4	9.6	24.9	14.6	9.1	23.3	13.7	8.5												
86	TC	54.4	52.1	49.9	53.0	50.7	48.5	51.5	49.3	47.1	50.1	47.9	45.7												
	SC	53.7	51.5	49.3	52.3	50.1	47.9	50.9	48.7	46.5	49.5	47.3	45.1												
	gpm	13.8	10.5	8.5	13.4	10.2	8.2	13.1	10.0	8.0	12.7	9.7	7.7												
	wpd	31.2	18.2	11.7	29.4	17.1	11.1	28.1	16.4	10.4	26.5	15.4	9.6												
88	TC	57.2	55.0	52.8	55.8	53.6	51.4	54.4	52.2	50.0	53.0	50.8	48.6												
	SC	56.5	54.3	52.1	55.1	52.9	50.7	53.7	51.5	49.3	52.3	50.1	48.0												
	gpm	14.5	11.2	8.9	14.2	10.9	8.7	13.8	10.5	8.5	13.4	10.3	8.2												
	wpd	34.4	20.4	13.0	33.0	19.3	12.3	31.2	18.2	11.7	29.4	17.4	11.1												
90	TC	60.1	57.9	55.7	58.7	56.5	54.3	57.3	55.1	52.9	55.8	53.6	51.5												
	SC	59.3	57.1	54.9	57.9	55.7	53.6	56.5	54.3	52.2	55.1	53.0	50.8												
	gpm	15.2	11.7	9.4	14.9	11.5	9.1	14.5	11.2	8.9	14.2	10.9	8.7												
	wpd	37.8	22.4	14.4	36.3	21.6	13.7	34.4	20.4	13.0	33.0	19.3	12.3												

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	58.9	54.1	47.7	55.7	50.6	44.7	52.5	47.6	41.6	49.3	44.4	38.7
	SC	41.3	39.1	36.3	39.9	37.6	34.9	38.5	36.3	33.6	37.1	34.9	32.2
	gpm	14.9	11.0	8.1	14.1	10.3	7.5	13.3	9.6	7.0	12.5	9.0	6.5
	wpd	20.4	11.1	6.0	18.2	9.7	5.1	16.2	8.5	4.5	14.2	7.4	3.9
76	TC	59.7	55.5	50.0	56.7	52.4	47.0	53.6	49.5	44.4	50.7	46.6	42.0
	SC	45.0	43.0	40.4	43.7	41.7	39.1	42.3	40.4	37.9	41.1	39.1	36.8
	gpm	15.1	11.2	8.5	14.3	10.6	7.9	13.6	10.0	7.5	12.9	9.4	7.1
	wpd	21.0	11.6	6.6	18.8	10.3	5.7	17.0	9.2	5.1	15.2	8.2	4.6
78	TC	60.7	57.1	52.1	57.8	54.4	49.8	55.0	51.5	47.3	52.3	49.0	45.3
	SC	48.8	47.1	44.6	47.5	45.8	43.5	46.3	44.5	42.4	45.1	43.3	41.2
	gpm	15.3	11.6	8.8	14.6	11.0	8.4	13.9	10.4	8.0	13.2	9.9	7.7
	wpd	21.5	12.3	7.1	19.5	11.1	6.5	17.8	10.0	5.8	16.0	9.0	5.4
80	TC	62.1	58.8	54.9	59.4	56.3	52.5	56.7	53.9	50.7	54.1	51.8	48.7
	SC	52.7	51.1	49.1	51.5	49.9	47.8	50.3	48.9	46.9	49.1	47.7	45.7
	gpm	15.7	11.9	9.3	15.0	11.4	8.9	14.3	10.9	8.6	13.7	10.5	8.2
	wpd	22.6	13.0	7.9	20.6	11.9	7.2	18.8	10.9	6.7	17.2	10.1	6.2
82	TC	63.7	60.8	57.8	61.1	58.6	55.9	58.7	56.5	54.0	56.6	54.6	49.6
	SC	56.7	55.2	53.4	55.5	54.2	52.5	54.4	53.0	51.2	53.4	52.0	49.0
	gpm	16.1	12.3	9.8	15.5	11.9	9.4	14.9	11.4	9.1	14.3	11.1	8.4
	wpd	23.8	13.9	8.8	21.9	13.0	8.2	20.4	11.9	7.6	18.8	11.2	6.5
84	TC	65.5	63.3	60.9	63.2	61.3	58.9	61.3	59.5	55.1	59.4	56.3	53.5
	SC	60.8	59.4	57.9	59.7	58.4	56.2	58.7	57.3	54.5	57.5	55.6	52.8
	gpm	16.6	12.8	10.3	16.0	12.5	9.6	15.6	12.1	9.3	15.1	11.4	9.0
	wpd	25.3	15.0	9.7	23.4	14.2	8.5	22.2	13.3	7.9	20.8	11.9	7.5
86	TC	67.9	66.1	62.3	66.0	63.1	60.6	63.5	61.4	59.0	61.8	59.7	57.2
	SC	65.0	63.7	61.6	63.9	62.3	59.9	62.7	60.7	58.2	61.0	59.0	56.5
	gpm	17.2	13.4	10.5	16.7	12.8	10.3	16.0	12.5	9.9	15.6	12.1	9.7
	wpd	27.1	16.6	10.1	25.6	15.0	9.7	23.6	14.2	9.0	22.4	13.5	8.6
88	TC	70.2	68.2	66.0	68.5	66.5	64.4	66.9	64.8	62.7	65.2	63.1	61.0
	SC	69.3	67.3	65.2	67.7	65.7	63.6	66.0	64.0	61.9	64.4	62.4	60.2
	gpm	17.8	13.8	11.2	17.3	13.5	10.9	16.9	13.1	10.6	16.5	12.8	10.3
	wpd	28.9	17.6	11.4	27.6	16.8	10.9	26.3	15.8	10.3	24.8	15.0	9.7
90	TC	73.6	71.6	69.4	71.9	69.9	67.7	70.2	68.2	66.1	68.6	66.6	64.4
	SC	72.7	70.7	68.6	71.0	69.0	66.9	69.4	67.4	65.2	67.7	65.7	63.6
	gpm	18.6	14.5	11.7	18.2	14.2	11.4	17.8	13.8	11.2	17.3	13.5	10.9
	wpd	31.9	19.3	12.6	30.2	18.4	11.9	28.9	17.6	11.4	27.6	16.8	10.9

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	67.0	61.3	55.4	63.5	57.9	51.8	59.9	54.3	48.5	56.5	50.9	45.3
	SC	45.0	42.5	39.8	43.5	41.0	38.3	41.9	39.4	36.8	40.4	38.0	35.5
	gpm	17.0	12.4	9.4	16.1	11.7	8.7	15.2	11.0	8.2	14.3	10.3	7.6
	wpd	18.9	10.1	5.8	17.0	9.0	5.0	15.1	7.9	4.4	13.4	6.9	3.8
76	TC	67.6	49.1	44.5	64.2	59.5	54.1	60.9	56.1	51.0	57.7	52.9	48.1
	SC	48.7	35.9	33.9	47.2	45.1	42.6	45.7	43.6	41.3	44.3	42.2	40.0
	gpm	17.1	9.9	7.5	16.2	12.0	9.1	15.4	11.4	8.6	14.6	10.7	8.1
	wpd	19.1	6.5	3.7	17.2	9.5	5.5	15.5	8.5	4.8	14.0	7.6	4.3
78	TC	68.4	64.2	59.5	65.3	61.0	56.5	62.1	58.0	53.8	58.9	55.0	51.3
	SC	52.5	50.6	48.4	51.1	49.1	47.0	49.6	47.8	45.8	48.3	46.5	44.7
	gpm	17.3	13.0	10.0	16.5	12.3	9.5	15.7	11.7	9.1	14.9	11.1	8.7
	wpd	19.7	11.1	6.6	17.9	10.0	6.0	16.2	9.0	5.4	14.6	8.1	4.9
80	TC	69.6	51.5	48.0	66.5	63.0	59.2	63.4	60.2	56.8	60.6	57.5	54.5
	SC	56.4	42.1	40.5	55.0	53.4	51.5	53.6	52.1	50.4	52.4	50.9	49.3
	gpm	17.6	10.4	8.1	16.8	12.7	10.0	16.0	12.2	9.6	15.3	11.6	9.2
	wpd	20.4	7.1	4.3	18.6	10.7	6.6	16.9	9.7	6.1	15.4	8.9	5.6
82	TC	70.8	67.8	64.4	67.9	65.1	62.1	65.2	62.6	60.0	62.5	60.3	57.9
	SC	60.3	58.9	57.2	59.0	57.6	56.1	57.8	56.5	55.0	56.6	55.4	54.0
	gpm	18.0	13.7	10.9	17.2	13.1	10.5	16.5	12.7	10.1	15.9	12.2	9.8
	wpd	21.2	12.3	7.8	19.5	11.3	7.2	17.9	10.5	6.7	16.5	9.7	6.3
84	TC	72.3	70.0	67.3	69.7	67.6	65.2	67.1	65.4	63.2	64.8	63.3	61.1
	SC	64.4	63.2	61.8	63.1	62.1	60.7	61.9	61.0	59.6	60.9	59.9	58.2
	gpm	18.3	14.2	11.4	17.6	13.7	11.0	17.0	13.2	10.7	16.4	12.8	9.5
	wpd	21.9	13.2	8.5	20.4	12.3	7.9	18.9	11.5	7.5	17.5	10.8	7.5
86	TC	74.1	72.5	70.4	71.7	70.4	68.6	69.6	68.5	67.7	67.7	66.7	64.7
	SC	68.6	67.7	66.4	67.4	66.6	65.4	66.3	65.5	62.9	65.3	63.9	61.1
	gpm	18.8	14.7	11.9	18.2	14.3	11.6	17.6	13.9	10.7	17.2	13.1	10.4
	wpd	23.1	14.1	9.2	21.7	13.4	8.9	20.4	12.6	7.6	19.3	11.3	7.1
88	TC	76.4	75.4	74.0	74.4	71.9	69.3	71.7	70.2	67.6	70.0	68.5	65.8
	SC	72.9	72.2	70.1	71.9	71.0	68.5	70.8	69.3	66.7	69.1	67.6	65.0
	gpm	19.4	15.3	11.9	18.8	14.6	11.7	18.2	14.3	11.5	17.7	13.9	11.1
	wpd	24.7	15.4	9.4	23.3	14.0	9.0	21.7	13.4	8.6	20.6	12.6	8.1
90	TC	78.6	77.2	74.9	76.9	75.5	73.1	75.2	73.7	71.4	73.5	72.0	69.6
	SC	77.7	76.2	73.9	76.0	74.5	72.2	74.3	72.8	70.5	72.5	71.1	68.8
	gpm	20.0	15.6	12.7	19.5	15.3	12.3	19.1	15.0	12.0	18.6	14.6	11.7
	wpd	26.1	16.0	10.5	24.9	15.4	10.0	23.9	14.7	9.5	22.7	14.0	9.0

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	80.5	77.3	74.0	76.6	73.4	70.0	72.6	69.5	66.0	68.7	65.6	62.1												
	SC	56.2	54.6	53.0	54.3	52.7	51.0	52.3	50.7	49.0	50.3	48.9	47.1												
	gpm	20.4	15.6	12.5	19.4	14.9	11.8	18.4	14.1	11.1	17.4	13.2	10.5												
	wpd	38.0	22.4	14.3	34.4	20.3	12.8	30.9	18.1	11.4	27.7	16.0	10.1												
76	TC	80.7	78.0	75.2	76.9	74.2	71.3	73.2	70.5	67.6	69.5	66.8	63.9												
	SC	60.3	58.9	57.5	58.4	57.0	55.5	56.5	55.2	53.7	54.6	53.3	51.9												
	gpm	20.4	15.8	12.7	19.4	15.1	12.1	18.5	14.3	11.4	17.6	13.6	10.8												
	wpd	38.0	22.9	14.8	34.4	20.8	13.3	31.2	18.7	11.9	28.5	16.8	10.7												
78	TC	81.3	78.9	76.4	77.7	75.2	72.8	74.0	71.7	73.7	70.3	68.2	65.9												
	SC	64.5	63.3	62.0	62.7	61.4	60.2	60.8	59.6	60.6	59.0	57.9	56.8												
	gpm	20.5	16.0	12.9	19.6	15.2	12.3	18.7	14.6	12.5	17.8	13.8	11.1												
	wpd	38.6	23.4	15.2	35.3	21.2	13.9	32.1	19.4	14.3	29.0	17.5	11.4												
80	TC	82.1	79.9	77.8	78.5	76.4	74.5	75.0	73.0	71.3	71.5	69.7	68.2												
	SC	68.8	67.7	66.6	67.0	65.9	64.9	65.2	64.2	63.3	63.5	62.6	61.8												
	gpm	20.8	16.1	13.1	19.9	15.5	12.6	19.0	14.8	12.1	18.1	14.1	11.6												
	wpd	39.6	23.8	15.8	36.2	21.9	14.4	32.9	20.1	13.3	30.1	18.1	12.2												
82	TC	82.9	81.1	79.4	79.5	77.8	76.3	76.1	74.7	73.4	72.9	71.7	70.6												
	SC	73.2	72.2	71.3	71.4	70.6	69.8	69.7	68.9	68.3	68.1	67.4	66.8												
	gpm	21.0	16.5	13.4	20.1	15.8	12.9	19.3	15.1	12.4	18.5	14.6	11.9												
	wpd	40.5	24.8	16.4	37.1	22.9	15.2	34.1	21.0	14.1	31.2	19.4	13.0												
84	TC	83.9	82.5	81.3	80.7	79.5	78.4	77.6	76.6	75.8	74.7	73.9	73.4												
	SC	77.7	76.9	76.2	76.0	75.3	74.7	74.4	73.8	73.4	72.9	72.4	72.1												
	gpm	21.3	16.7	13.7	20.5	16.1	13.2	19.7	15.6	12.8	19.0	15.0	12.4												
	wpd	41.5	25.6	17.2	38.3	23.8	16.0	35.6	22.2	15.0	32.9	20.5	14.1												
86	TC	85.2	84.3	83.5	82.3	81.6	81.0	79.5	79.0	78.7	76.9	76.8	76.5												
	SC	82.3	81.7	81.3	80.7	80.3	79.9	79.2	78.9	78.6	77.9	77.7	77.4												
	gpm	21.5	17.1	14.1	20.8	16.6	13.7	20.1	16.0	13.3	19.5	15.6	13.0												
	wpd	42.5	26.9	18.3	39.6	25.1	17.2	37.1	23.4	16.2	34.7	22.2	15.4												
88	TC	87.0	86.5	86.2	84.4	84.2	84.1	82.1	80.6	80.2	79.0	78.7	78.3												
	SC	87.1	86.8	86.5	85.7	85.5	85.3	84.4	82.6	82.4	81.8	81.6	81.4												
	gpm	22.0	17.6	14.6	21.4	17.1	14.2	20.9	16.3	13.6	20.0	15.9	13.2												
	wpd	44.5	28.2	19.4	41.8	26.6	18.5	39.9	24.3	16.8	36.8	23.1	16.0												
90	TC	89.5	87.9	87.6	86.3	86.1	85.8	84.4	84.3	83.9	82.6	82.4	82.0												
	SC	92.3	90.2	90.1	89.4	89.3	89.1	88.4	88.3	88.1	87.5	87.3	86.9												
	gpm	22.7	17.8	14.8	21.9	17.5	14.5	21.5	17.1	14.2	21.0	16.7	13.9												
	wpd	47.2	29.0	20.1	43.8	27.9	19.2	42.2	26.6	18.5	40.2	25.6	17.7												

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	50.8	45.6	40.5	47.9	42.8	37.7	44.9	40.0	34.7	42.0	37.4	31.8												
	SC	32.0	29.8	27.7	30.8	28.7	26.5	29.6	27.6	25.4	28.5	26.5	24.1												
	gpm	12.9	9.2	6.8	12.1	8.7	6.4	11.4	8.1	5.9	10.6	7.5	5.4												
	wpd	27.1	13.9	7.6	23.9	12.3	6.6	21.3	10.6	5.7	18.5	9.3	4.7												
76	TC	50.6	45.9	41.6	47.8	43.4	38.9	45.0	40.8	36.3	42.5	38.3	33.6												
	SC	34.9	33.0	31.1	33.8	31.9	29.9	32.8	30.9	28.8	31.7	29.8	27.7												
	gpm	12.8	9.3	7.0	12.1	8.8	6.6	11.4	8.2	6.1	10.7	7.8	5.7												
	wpd	26.8	14.2	8.0	23.9	12.6	7.1	21.3	11.1	6.1	18.7	9.8	5.2												
78	TC	51.0	46.8	42.9	48.4	44.4	40.4	45.9	41.9	38.3	43.5	39.6	36.1												
	SC	38.2	36.3	34.4	37.1	35.3	33.4	36.1	34.3	32.4	35.0	33.2	31.5												
	gpm	12.9	9.5	7.2	12.3	9.0	6.8	11.6	8.5	6.4	11.0	8.1	6.1												
	wpd	27.1	14.6	8.5	24.6	13.2	7.6	22.1	11.9	6.8	19.8	10.6	6.1												
80	TC	51.8	47.9	44.4	49.4	45.6	42.4	47.1	43.4	40.4	44.8	41.4	38.7												
	SC	41.5	39.7	37.8	40.4	38.6	37.1	39.5	37.6	36.1	38.4	36.9	35.1												
	gpm	13.1	9.7	7.5	12.5	9.2	7.1	11.9	8.8	6.8	11.3	8.4	6.5												
	wpd	28.1	15.4	9.3	25.5	13.9	8.3	23.3	12.6	7.6	21.0	11.5	6.9												
82	TC	52.9	49.3	46.3	50.6	47.3	44.5	48.3	45.3	42.7	46.2	43.5	41.0												
	SC	44.9	43.0	41.6	43.8	42.2	40.6	42.9	41.3	39.7	41.9	40.3	38.6												
	gpm	13.3	10.0	7.8	12.8	9.6	7.5	12.2	9.1	7.2	11.7	8.8	6.9												
	wpd	29.1	16.4	10.0	26.8	15.1	9.3	24.3	13.7	8.5	22.4	12.8	7.8												
84	TC	54.2	51.0	48.4	52.0	49.2	46.7	49.9	47.4	45.1	48.1	45.8	43.6												
	SC	48.3	46.7	44.9	47.3	45.7	44.1	46.4	44.8	43.0	45.4	43.7	42.1												
	gpm	13.7	10.3	8.1	13.2	10.0	7.9	12.6	9.6	7.6	12.2	9.3	7.4												
	wpd	30.8	17.4	10.8	28.4	16.4	10.2	26.1	15.1	9.5	24.3	14.2	8.9												
86	TC	55.6	53.0	50.8	53.8	51.4	49.2	52.0	49.8	47.7	50.5	48.3	46.4												
	SC	51.7	50.3	48.4	50.8	49.2	47.6	49.9	48.3	46.4	48.8	47.2	45.3												
	gpm	14.1	10.7	8.6	13.6	10.4	8.3	13.2	10.1	8.1	12.8	9.8	7.8												
	wpd	32.6	18.7	12.1	30.5	17.7	11.3	28.4	16.6	10.6	26.8	15.6	10.0												
88	TC	57.6	55.4	53.3	56.1	53.9	51.9	54.5	52.5	50.1	53.1	50.9	48.7												
	SC	55.4	53.5	51.9	54.3	52.6	50.8	53.4	51.5	49.4	52.4	50.2	48.0												
	gpm	14.6	11.2	9.0	14.2	10.9	8.8	13.8	10.6	8.5	13.5	10.3	8.2												
	wpd	34.8	20.7	13.2	33.0	19.6	12.6	31.2	18.5	11.7	29.8	17.4	11.1												
90	TC	60.1	58.1	55.8	58.7	56.6	54.4	57.4	55.2	53.0	56.0	53.8	51.6												
	SC	58.8	57.0	55.1	57.7	55.8	53.7	56.6	54.5	52.3	55.2	53.1	50.9												
	gpm	15.1	11.8	9.5	14.9	11.5	9.2	14.6	11.2	8.9	14.2	10.9	8.7												
	wpd	37.4	22.7	14.6	36.3	21.6	13.9	34.8	20.4	13.0	33.0	19.3	12.3												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	67.4	62.1	55.4	63.8	56.5	51.6	60.3	55.2	48.0	56.7	51.7	44.1												
	SC	40.5	38.2	35.3	39.0	36.7	33.8	37.5	35.3	32.3	36.0	33.9	30.7												
	gpm	17.0	12.5	9.4	16.1	11.8	8.7	15.2	11.2	8.1	14.3	10.4	7.4												
	wpd	26.6	14.4	8.0	23.8	12.8	7.0	21.3	11.4	6.0	18.8	10.0	5.0												
76	TC	67.5	62.6	56.5	64.0	59.2	53.0	60.7	55.9	49.5	57.3	52.7	46.4												
	SC	43.9	41.8	39.2	42.5	40.4	37.7	41.0	39.0	36.2	39.6	37.6	34.9												
	gpm	17.1	12.7	9.5	16.2	12.0	9.0	15.4	11.3	8.4	14.5	10.7	7.8												
	wpd	26.8	14.8	8.3	24.1	13.1	7.4	21.7	11.7	6.5	19.3	10.4	5.6												
78	TC	67.9	63.4	57.8	64.7	60.2	54.8	61.4	57.0	51.7	58.2	54.0	48.8												
	SC	47.5	45.5	43.0	46.1	44.1	41.7	44.7	42.8	40.4	43.4	41.5	39.2												
	gpm	17.2	12.9	9.8	16.4	12.2	9.3	15.6	11.6	8.7	14.7	11.0	8.2												
	wpd	27.1	15.2	8.8	24.6	13.7	7.9	22.2	12.3	7.0	19.9	11.1	6.2												
80	TC	68.6	64.4	59.7	65.5	61.4	56.8	62.4	58.4	54.0	59.2	55.6	51.0												
	SC	51.2	49.3	47.1	49.8	48.0	45.9	48.5	46.8	44.7	47.2	45.5	43.3												
	gpm	17.3	13.0	10.1	16.5	12.5	9.6	15.7	11.8	9.1	15.0	11.2	8.6												
	wpd	27.6	15.6	9.3	25.1	14.2	8.5	22.6	12.8	7.6	20.6	11.6	6.8												
82	TC	69.6	65.7	61.8	66.5	62.9	58.9	63.6	60.2	56.2	60.7	57.4	53.9												
	SC	55.0	53.2	51.3	53.6	52.0	50.0	52.4	50.7	48.8	51.1	49.5	47.8												
	gpm	17.6	13.4	10.4	16.9	12.8	9.9	16.1	12.2	9.5	15.4	11.6	9.1												
	wpd	28.4	16.4	10.0	26.1	15.0	9.0	23.8	13.7	8.3	21.7	12.4	7.6												
84	TC	70.7	67.3	63.7	67.8	64.5	61.3	65.1	61.9	58.9	62.3	59.4	56.7												
	SC	58.8	57.2	55.4	57.5	55.9	54.2	56.3	54.7	53.2	55.1	53.6	52.0												
	gpm	17.9	13.7	10.7	17.2	13.0	10.3	16.5	12.5	9.9	15.8	12.1	9.5												
	wpd	29.4	17.2	10.6	27.1	15.6	9.8	24.8	14.4	9.0	22.9	13.3	8.3												
86	TC	72.1	68.9	66.1	69.3	66.3	63.9	66.7	64.1	61.9	64.2	61.9	59.9												
	SC	62.7	61.1	59.6	61.5	60.0	58.6	60.3	58.9	57.5	59.1	57.8	56.5												
	gpm	18.2	13.9	11.2	17.6	13.4	10.7	16.9	12.9	10.4	16.3	12.5	10.1												
	wpd	30.5	17.8	11.4	28.4	16.6	10.6	26.3	15.4	10.0	24.3	14.4	9.3												
88	TC	73.6	70.9	68.7	71.0	68.7	66.7	68.7	66.7	64.8	66.6	64.7	61.1												
	SC	66.7	65.2	63.9	65.5	64.2	63.0	64.3	63.1	61.8	63.3	62.0	60.3												
	gpm	18.6	14.4	11.6	17.9	13.9	11.3	17.3	13.5	10.9	16.9	13.1	10.3												
	wpd	31.9	19.0	12.4	29.4	17.8	11.7	27.6	16.8	10.9	26.1	15.8	9.8												
90	TC	75.5	73.4	71.4	73.3	71.4	69.6	71.2	69.5	66.2	69.4	66.7	64.6												
	SC	70.7	69.5	68.2	69.7	68.4	67.0	68.6	67.2	65.4	67.5	65.9	63.8												
	gpm	19.1	14.9	12.1	18.6	14.5	11.8	18.0	14.1	11.2	17.6	13.5	10.9												
	wpd	33.3	20.4	13.3	31.6	19.3	12.8	29.7	18.2	11.4	28.4	16.8	10.9												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	76.2	71.0	63.8	72.4	67.1	59.9	68.7	63.3	55.9	64.9	59.2	51.9												
	SC	44.4	42.2	39.1	42.8	40.5	37.4	41.2	38.8	35.8	39.6	37.2	34.1												
	gpm	19.3	14.4	10.7	18.4	13.5	10.1	17.4	12.8	9.5	16.4	12.0	8.7												
	wpd	24.5	13.5	7.6	22.1	12.0	6.7	19.9	10.8	5.9	17.7	9.5	5.0												
76	TC	76.2	56.1	50.6	72.6	67.8	61.1	68.9	64.0	57.6	65.4	60.1	54.0												
	SC	47.9	35.6	33.2	46.3	44.2	41.3	44.7	42.6	39.8	43.2	40.9	38.4												
	gpm	19.2	11.4	8.6	18.4	13.7	10.3	17.4	13.0	9.7	16.6	12.2	9.1												
	wpd	24.3	8.5	4.8	22.1	12.3	7.0	19.9	11.1	6.2	18.1	9.7	5.5												
78	TC	76.7	72.2	66.3	73.2	68.6	62.8	69.6	65.1	59.5	66.1	61.6	56.0												
	SC	51.5	49.5	47.0	50.0	48.0	45.4	48.4	46.5	44.0	46.9	45.0	42.5												
	gpm	19.4	14.6	11.2	18.5	13.9	10.6	17.6	13.1	10.0	16.7	12.5	9.5												
	wpd	24.7	14.0	8.3	22.5	12.6	7.3	20.2	11.3	6.6	18.2	10.3	5.9												
80	TC	77.3	57.6	53.2	73.9	69.9	64.6	70.5	66.5	61.4	67.0	63.1	58.4												
	SC	55.2	41.3	39.4	53.7	51.9	49.6	52.2	50.5	48.2	50.7	49.0	46.9												
	gpm	19.6	11.6	9.0	18.7	14.2	10.9	17.9	13.5	10.3	17.0	12.7	9.9												
	wpd	25.1	8.9	5.3	22.9	13.2	7.8	21.0	11.9	7.0	18.9	10.7	6.4												
82	TC	78.0	74.6	69.6	74.7	71.3	66.7	71.5	68.0	63.6	68.2	64.9	60.7												
	SC	58.9	57.4	55.1	57.5	55.9	53.8	56.0	54.5	52.5	54.6	53.1	51.2												
	gpm	19.8	15.1	11.8	18.9	14.4	11.3	18.1	13.8	10.7	17.2	13.1	10.3												
	wpd	25.7	14.9	9.1	23.5	13.7	8.4	21.5	12.5	7.6	19.5	11.3	6.9												
84	TC	78.9	75.8	71.6	75.8	72.7	68.7	72.6	69.8	66.0	69.5	66.7	49.4												
	SC	62.8	61.3	59.3	61.3	59.9	58.1	59.9	58.6	56.8	58.6	57.3	42.8												
	gpm	20.0	15.4	12.1	19.2	14.8	11.6	18.4	14.2	11.1	17.6	13.5	8.3												
	wpd	26.3	15.5	9.6	24.3	14.3	8.9	22.3	13.2	8.1	20.4	11.9	4.6												
86	TC	80.0	77.2	73.7	76.9	74.3	71.1	73.9	71.6	68.6	71.1	69.0	66.3												
	SC	66.6	65.3	63.6	65.2	64.0	62.4	63.8	62.8	61.3	62.6	61.6	60.2												
	gpm	20.3	15.6	12.4	19.5	15.1	12.0	18.7	14.5	11.6	18.0	14.0	11.2												
	wpd	27.0	16.0	10.1	24.9	14.9	9.5	22.9	13.8	8.9	21.2	12.8	8.3												
88	TC	81.1	78.9	76.0	78.3	76.2	73.7	75.6	73.6	71.4	72.9	71.3	69.3												
	SC	70.5	69.4	68.0	69.2	68.2	66.9	68.0	67.0	65.8	66.8	65.9	64.8												
	gpm	20.5	16.0	12.8	19.8	15.5	12.4	19.2	14.9	12.1	18.4	14.5	11.7												
	wpd	27.6	16.9	10.8	25.7	15.7	10.1	24.1	14.6	9.6	22.3	13.8	9.0												
90	TC	82.7	80.8	78.6	80.1	78.3	76.4	77.5	76.0	74.5	75.1	74.0	72.6												
	SC	74.6	73.6	72.5	73.4	72.4	71.4	72.1	71.3	70.4	71.1	70.3	69.3												
	gpm	20.9	16.4	13.2	20.3	15.9	12.9	19.6	15.4	12.6	19.1	15.0	12.3												
	wpd	28.7	17.5	11.5	27.0	16.5	10.9	25.3	15.5	10.4	23.9	14.7	9.9												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	91.1	87.6	84.0	87.0	83.5	79.8	83.0	79.4	75.7	78.8	75.2	71.5												
	SC	56.0	54.2	52.4	53.9	52.2	50.4	51.9	50.2	48.3	49.9	48.1	46.4												
	gpm	23.1	17.7	14.2	22.0	16.9	13.5	21.0	16.1	12.7	20.0	15.2	12.1												
	wpd	49.0	28.7	18.5	44.5	26.1	16.6	40.5	23.8	14.8	36.5	21.2	13.3												
76	TC	91.1	87.8	84.5	87.2	83.8	80.4	83.1	79.8	76.4	79.1	75.6	72.3												
	SC	59.9	58.3	56.6	57.9	56.3	54.6	55.9	54.3	52.6	53.9	52.3	50.7												
	gpm	23.1	17.8	14.3	22.1	17.0	13.6	21.0	16.1	12.9	20.0	15.3	12.2												
	wpd	49.0	29.0	18.7	44.8	26.4	16.8	40.5	23.8	15.2	36.8	21.4	13.7												
78	TC	91.3	88.2	85.1	87.4	84.3	81.2	83.5	80.3	82.6	79.5	76.4	73.5												
	SC	63.9	62.4	60.8	62.0	60.4	58.9	60.0	58.5	59.6	58.0	56.6	55.1												
	gpm	23.0	17.9	14.4	22.2	17.1	13.7	21.1	16.3	14.0	20.1	15.5	12.4												
	wpd	48.6	29.3	19.0	45.2	26.6	17.2	40.9	24.3	17.9	37.1	21.9	14.1												
80	TC	91.6	88.7	85.9	87.7	85.0	82.2	83.9	81.2	78.4	80.1	77.4	74.7												
	SC	68.0	66.6	65.1	66.1	64.7	63.3	64.1	62.8	61.4	62.3	60.9	59.6												
	gpm	23.1	18.0	14.5	22.1	17.2	13.9	21.2	16.5	13.2	20.2	15.7	12.6												
	wpd	49.0	29.6	19.2	44.8	27.1	17.7	41.2	24.8	16.0	37.4	22.6	14.6												
82	TC	92.0	89.5	86.9	88.3	85.8	83.3	84.6	82.1	79.8	80.9	78.5	76.2												
	SC	72.2	70.9	69.6	70.3	69.0	67.8	68.4	67.2	66.0	66.6	65.4	64.3												
	gpm	23.3	18.1	14.7	22.4	17.4	14.1	21.4	16.6	13.5	20.5	16.0	12.9												
	wpd	49.7	30.1	19.8	45.8	27.7	18.1	41.8	25.3	16.6	38.3	23.4	15.2												
84	TC	92.6	90.3	88.1	89.0	86.8	84.7	85.4	83.2	81.3	81.7	79.8	78.0												
	SC	76.4	75.2	74.1	74.6	73.4	72.3	72.7	71.6	70.6	70.9	69.9	69.0												
	gpm	23.5	18.3	14.9	22.5	17.6	14.3	21.6	16.9	13.7	20.7	16.1	13.1												
	wpd	50.4	30.7	20.3	46.5	28.2	18.7	42.8	26.1	17.2	39.3	23.8	15.8												
86	TC	93.3	91.3	89.4	89.8	87.9	86.2	86.3	84.5	82.9	82.8	81.3	79.9												
	SC	80.7	79.7	78.7	78.9	77.9	77.0	77.1	76.2	75.4	75.4	74.6	73.9												
	gpm	23.6	18.5	15.1	22.8	17.8	14.6	21.9	17.1	14.0	21.0	16.5	13.5												
	wpd	51.1	31.2	20.8	47.6	29.0	19.4	43.8	26.9	17.9	40.5	24.8	16.6												
88	TC	94.1	92.5	90.9	90.7	89.3	87.9	87.4	86.1	85.0	84.1	83.1	82.1												
	SC	85.1	84.2	83.4	83.3	82.5	81.8	81.6	80.9	80.3	80.0	79.4	78.8												
	gpm	23.9	18.8	15.4	23.0	18.1	14.8	22.2	17.5	14.4	21.2	16.9	13.9												
	wpd	52.2	32.4	21.7	48.6	30.1	20.1	45.2	27.9	19.0	41.2	26.1	17.7												
90	TC	95.1	93.9	92.8	91.9	90.9	89.9	88.8	88.0	87.2	85.8	85.2	84.7												
	SC	89.5	88.8	88.2	87.8	87.3	86.7	86.2	85.8	85.3	84.7	84.3	84.0												
	gpm	24.0	19.0	15.7	23.2	18.5	15.2	22.5	17.9	14.7	21.7	17.2	14.3												
	wpd	52.9	33.2	22.6	49.3	31.2	21.2	46.2	29.3	19.8	43.2	27.1	18.7												

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	58.1	53.0	47.7	55.3	50.1	44.8	52.4	47.1	41.7	49.4	44.0	38.6												
	SC	31.0	29.0	26.9	29.9	27.8	25.7	28.8	26.7	24.6	27.6	25.5	23.4												
	gpm	14.7	10.8	8.1	14.0	10.2	7.6	13.3	9.5	7.1	12.5	8.9	6.5												
	wpd	35.1	19.0	10.6	32.2	16.9	9.5	28.8	14.9	8.1	25.5	13.0	6.9												
76	TC	58.3	53.1	47.8	55.4	50.1	44.9	52.5	47.1	42.0	49.4	44.1	39.3												
	SC	34.1	32.0	29.9	33.0	30.9	28.8	31.8	29.7	27.6	30.7	28.5	26.6												
	gpm	14.7	10.7	8.1	14.0	10.2	7.6	13.3	9.5	7.1	12.5	8.9	6.7												
	wpd	35.5	18.7	10.6	31.9	16.9	9.5	28.8	14.9	8.1	25.5	13.0	7.3												
78	TC	58.3	53.0	48.1	55.3	50.1	45.4	52.3	47.3	42.9	49.2	44.5	40.2												
	SC	37.2	35.0	33.0	36.0	33.9	32.0	34.8	32.7	30.9	33.6	31.7	29.9												
	gpm	14.7	10.7	8.1	14.0	10.2	7.7	13.2	9.5	7.2	12.4	9.0	6.8												
	wpd	35.5	18.7	10.8	31.9	16.9	9.6	28.4	14.9	8.5	25.2	13.2	7.6												
80	TC	58.6	53.7	49.3	55.6	51.0	46.7	52.8	48.4	44.2	50.0	45.8	41.8												
	SC	40.1	38.0	36.2	38.9	37.0	35.2	37.8	36.0	34.1	36.8	35.0	33.1												
	gpm	14.8	10.9	8.3	14.1	10.3	7.9	13.3	9.8	7.4	12.6	9.3	7.1												
	wpd	35.9	19.3	11.3	32.6	17.4	10.2	29.1	15.6	9.1	26.1	14.2	8.1												
82	TC	58.3	53.9	50.0	55.7	51.5	47.5	53.1	49.0	45.2	50.6	46.6	43.1												
	SC	43.2	41.5	39.6	42.2	40.4	38.7	41.2	39.4	37.6	40.2	38.4	36.6												
	gpm	14.7	10.9	8.5	14.1	10.4	8.0	13.4	9.9	7.6	12.8	9.4	7.3												
	wpd	35.5	19.6	11.7	32.6	17.7	10.4	29.4	16.1	9.5	26.8	14.4	8.7												
84	TC	58.9	55.1	51.3	56.5	52.7	49.1	54.0	50.4	47.0	51.7	48.1	45.0												
	SC	46.6	44.8	43.0	45.6	43.8	42.0	44.6	42.8	41.0	43.6	41.8	40.3												
	gpm	14.9	11.2	8.7	14.3	10.7	8.3	13.6	10.2	8.0	13.0	9.8	7.6												
	wpd	36.3	20.4	12.3	33.3	18.7	11.3	30.5	17.1	10.4	27.8	15.6	9.5												
86	TC	60.0	56.4	52.9	57.7	54.0	50.9	55.4	51.9	49.0	53.0	49.9	47.2												
	SC	50.0	48.2	46.5	49.0	47.3	45.7	47.9	46.3	44.7	47.0	45.5	43.9												
	gpm	15.2	11.4	8.9	14.6	10.9	8.6	14.0	10.5	8.3	13.4	10.1	8.0												
	wpd	37.8	21.3	13.0	34.8	19.6	12.1	32.2	18.2	11.3	29.4	16.6	10.4												
88	TC	61.3	57.7	54.7	59.0	55.7	53.0	56.7	53.7	51.2	54.6	51.9	49.6												
	SC	53.5	51.6	50.1	52.4	50.6	49.1	51.4	49.8	48.2	50.3	49.0	47.2												
	gpm	15.5	11.6	9.2	14.9	11.2	8.9	14.3	10.9	8.7	13.8	10.5	8.4												
	wpd	39.4	22.1	13.9	36.3	20.7	13.0	33.7	19.3	12.3	31.2	17.9	11.5												
90	TC	62.4	59.4	56.9	60.4	57.6	55.2	58.4	55.8	53.7	56.5	54.3	52.1												
	SC	56.8	55.2	53.7	55.7	54.1	52.6	54.9	53.3	51.5	53.8	52.2	50.6												
	gpm	15.8	12.0	9.6	15.3	11.6	9.3	14.8	11.3	9.1	14.3	11.0	8.8												
	wpd	40.9	23.6	15.1	38.2	22.1	14.2	35.9	21.0	13.5	33.7	19.8	12.8												

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	76.8	71.3	66.6	73.2	67.7	61.6	69.6	64.0	57.4	65.9	60.3	53.3
	SC	39.8	37.5	35.2	38.3	36.0	33.6	36.8	34.6	31.9	35.3	33.1	30.3
	gpm	19.5	14.4	11.1	18.5	13.7	10.4	17.6	12.9	9.7	16.6	12.2	9.0
	wpd	34.7	19.0	11.2	31.3	17.2	10.0	28.4	15.4	8.6	25.3	13.7	7.4
76	TC	76.9	71.4	66.9	73.3	67.7	61.9	69.7	64.1	58.0	65.9	60.4	54.3
	SC	43.3	41.0	38.7	41.8	39.5	37.1	40.3	38.0	35.5	38.8	36.5	34.0
	gpm	19.5	14.5	11.2	18.6	13.7	10.4	17.6	12.9	9.8	16.7	12.2	9.2
	wpd	34.7	19.3	11.4	31.6	17.2	10.0	28.4	15.4	8.8	25.6	13.7	7.8
78	TC	76.9	71.5	66.4	73.3	67.9	62.8	69.7	64.5	59.0	66.1	61.0	55.4
	SC	46.7	44.4	42.3	45.2	43.0	40.8	43.7	41.5	39.3	42.2	40.1	37.8
	gpm	19.5	14.5	11.2	18.6	13.8	10.6	17.7	13.0	9.9	16.7	12.4	9.4
	wpd	34.7	19.3	11.4	31.6	17.4	10.3	28.6	15.6	9.0	25.6	14.0	8.0
80	TC	77.5	72.4	67.5	74.0	69.0	64.3	70.5	65.6	60.8	67.1	62.3	57.1
	SC	50.1	47.9	45.8	48.6	46.5	44.5	47.2	45.1	43.0	45.8	43.8	41.6
	gpm	19.6	14.7	11.4	18.7	13.9	10.8	17.8	13.3	10.3	17.0	12.6	9.6
	wpd	35.3	19.7	11.9	32.2	17.8	10.8	29.2	16.2	9.7	26.6	14.6	8.5
82	TC	77.2	72.6	68.0	73.9	69.4	64.9	70.6	66.1	61.9	67.3	62.9	58.8
	SC	53.7	51.7	49.7	52.3	50.3	48.3	50.9	48.9	47.1	49.5	47.6	45.8
	gpm	19.5	14.7	11.5	18.6	14.0	10.9	17.8	13.4	10.5	17.0	12.7	9.9
	wpd	35.0	19.9	12.1	31.9	18.0	10.9	29.2	16.4	10.1	26.6	14.8	9.0
84	TC	77.9	73.5	69.4	74.7	70.4	66.5	71.5	67.4	63.5	68.4	64.3	60.8
	SC	57.3	55.4	53.6	56.0	54.1	52.3	54.6	52.8	51.1	53.3	51.6	49.9
	gpm	19.7	14.9	11.7	18.9	14.3	11.2	18.1	13.7	10.7	17.3	13.0	10.3
	wpd	35.6	20.4	12.6	32.7	18.6	11.6	30.0	17.2	10.6	27.3	15.6	9.7
86	TC	78.8	74.7	70.9	75.7	71.7	68.2	72.5	68.8	65.4	69.5	66.0	62.6
	SC	61.1	59.2	57.5	59.8	58.0	56.3	58.4	56.7	55.1	57.1	55.5	53.9
	gpm	20.0	15.1	12.0	19.1	14.6	11.5	18.3	13.9	11.0	17.6	13.4	10.6
	wpd	36.5	21.0	13.1	33.6	19.5	12.1	30.8	17.8	11.1	28.4	16.4	10.3
88	TC	79.7	75.9	72.6	76.7	73.2	69.9	73.8	70.4	67.3	71.0	67.7	64.9
	SC	64.9	63.1	61.5	63.5	61.9	60.3	62.3	60.7	59.1	61.0	59.5	58.0
	gpm	20.2	15.4	12.3	19.5	14.8	11.8	18.7	14.3	11.4	18.0	13.7	11.0
	wpd	37.4	21.7	13.9	34.7	20.1	12.8	32.2	18.6	11.9	29.7	17.2	11.1
90	TC	80.9	77.5	74.4	78.0	74.8	71.8	75.2	72.2	69.5	72.6	69.6	67.3
	SC	68.6	67.0	65.5	67.4	65.8	64.3	66.2	64.6	63.4	65.0	63.5	62.2
	gpm	20.5	15.7	12.5	19.8	15.1	12.1	19.1	14.7	11.7	18.4	14.1	11.4
	wpd	38.6	22.6	14.4	35.9	21.0	13.5	33.3	19.7	12.6	31.1	18.2	11.9

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	86.4	81.5	74.8	82.6	77.6	70.7	78.8	73.7	66.4	74.9	69.7	62.0												
	SC	44.1	42.0	39.1	42.4	40.3	37.4	40.8	38.6	35.6	39.1	37.0	33.8												
	gpm	21.9	16.5	12.6	20.9	15.7	11.9	20.0	14.9	11.2	18.9	14.1	10.4												
	wpd	31.4	17.9	10.4	28.7	16.2	9.4	26.1	14.6	8.3	23.5	13.1	7.1												
76	TC	86.3	64.7	58.8	82.6	77.7	71.1	78.8	73.8	67.0	74.9	69.9	62.8												
	SC	47.5	35.7	33.1	45.9	43.8	41.0	44.2	42.1	39.3	42.6	40.5	37.6												
	gpm	21.8	13.1	9.9	20.9	15.8	12.0	20.0	15.0	11.3	19.0	14.2	10.6												
	wpd	31.2	11.3	6.5	28.7	16.4	9.5	26.1	14.7	8.4	23.7	13.2	7.3												
78	TC	86.3	81.6	75.7	82.6	77.9	71.7	78.8	74.1	67.8	75.0	70.4	63.8												
	SC	50.9	48.9	46.3	49.3	47.3	44.7	47.7	45.7	43.1	46.0	44.1	41.4												
	gpm	21.8	16.5	12.7	20.8	15.8	12.1	19.9	15.0	11.5	18.9	14.3	10.7												
	wpd	31.2	17.9	10.7	28.5	16.4	9.6	25.9	14.7	8.6	23.5	13.4	7.6												
80	TC	87.0	65.6	60.5	83.4	79.0	73.2	79.7	75.3	69.4	76.0	71.6	65.8												
	SC	54.4	41.0	38.8	52.8	50.9	48.4	51.2	49.3	46.8	49.6	47.8	45.4												
	gpm	22.0	13.3	10.2	21.1	16.0	12.3	20.1	15.2	11.7	19.2	14.5	11.1												
	wpd	31.9	11.6	6.8	29.2	16.9	10.0	26.6	15.2	9.0	24.3	13.8	8.0												
82	TC	86.8	82.7	77.6	83.3	79.0	74.0	79.7	75.5	70.5	76.1	72.2	67.1												
	SC	58.0	56.2	54.0	56.4	54.6	52.5	54.9	53.1	51.0	53.4	51.7	49.5												
	gpm	22.0	16.8	13.1	21.1	16.0	12.5	20.2	15.3	11.9	19.2	14.6	11.3												
	wpd	31.6	18.4	11.2	29.2	16.9	10.3	26.8	15.4	9.2	24.3	14.0	8.4												
84	TC	87.3	83.3	78.8	83.9	80.0	75.5	80.4	76.5	72.2	76.9	73.3	53.9												
	SC	61.6	59.9	57.9	60.1	58.4	56.5	58.6	57.0	55.1	57.1	55.6	41.3												
	gpm	22.1	16.8	13.3	21.2	16.2	12.7	20.4	15.5	12.2	19.5	14.8	9.1												
	wpd	32.1	18.6	11.6	29.6	17.2	10.7	27.2	15.7	9.7	24.9	14.4	5.4												
86	TC	88.0	84.3	80.3	84.6	81.1	77.0	81.3	77.8	73.8	77.9	74.5	70.8												
	SC	65.4	63.7	61.9	63.8	62.3	60.5	62.4	60.9	59.1	60.9	59.5	57.8												
	gpm	22.3	17.1	13.5	21.5	16.4	13.0	20.6	15.7	12.4	19.7	15.1	11.9												
	wpd	32.6	19.1	12.0	30.3	17.7	11.1	27.8	16.2	10.1	25.5	14.9	9.4												
88	TC	88.7	85.5	81.8	85.4	82.2	78.8	82.2	79.1	75.8	79.0	76.0	72.8												
	SC	69.1	67.6	65.9	67.6	66.2	64.6	66.2	64.8	63.3	64.8	63.5	62.0												
	gpm	22.4	17.3	13.8	21.6	16.7	13.3	20.8	16.0	12.8	20.0	15.4	12.3												
	wpd	32.8	19.7	12.5	30.5	18.2	11.6	28.3	16.9	10.8	26.3	15.5	10.0												
90	TC	89.6	86.6	83.5	86.4	83.6	80.7	83.3	80.6	77.9	80.2	77.7	75.2												
	SC	72.9	71.5	70.1	71.4	70.1	68.8	70.0	68.8	67.6	68.7	67.6	66.4												
	gpm	22.7	17.6	14.1	21.9	16.9	13.6	21.0	16.4	13.1	20.3	15.8	12.7												
	wpd	33.8	20.2	13.1	31.4	18.8	12.2	28.9	17.5	11.3	27.0	16.4	10.5												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	102.4	98.9	95.1	98.4	94.8	90.8	94.3	90.5	86.4	90.1	86.2	82.1												
	SC	55.8	54.0	52.1	53.8	52.0	50.0	51.7	49.9	47.9	49.7	47.8	45.9												
	gpm	26.0	20.0	16.1	25.0	19.2	15.3	23.9	18.4	14.6	22.8	17.5	13.9												
	wpd	61.7	36.5	23.6	57.0	33.8	21.4	52.2	30.9	19.4	47.6	27.9	17.7												
76	TC	102.5	98.9	95.2	98.4	94.7	91.0	94.3	90.5	86.7	90.1	86.3	82.4												
	SC	59.8	58.0	56.2	57.7	55.9	54.1	55.7	53.8	52.0	53.6	51.8	50.0												
	gpm	26.0	20.0	16.1	25.0	19.1	15.4	23.9	18.3	14.6	22.8	17.5	13.9												
	wpd	61.7	36.8	23.6	57.0	33.5	21.7	52.2	30.7	19.6	47.6	27.9	17.7												
78	TC	102.4	99.0	95.5	98.4	94.9	91.3	94.3	90.8	86.3	90.1	86.5	82.9												
	SC	63.7	62.0	60.2	61.6	59.9	58.2	59.6	57.9	59.0	57.6	55.8	54.1												
	gpm	26.0	20.0	16.1	25.0	19.2	15.5	23.9	18.4	15.7	22.9	17.6	14.0												
	wpd	61.7	36.8	23.8	57.0	33.8	21.9	52.2	30.9	22.6	47.9	28.2	17.9												
80	TC	103.1	99.9	96.6	99.1	95.9	92.5	95.2	91.8	88.3	91.0	87.6	84.2												
	SC	67.6	66.0	64.3	65.6	64.0	62.3	63.6	62.0	60.3	61.6	59.9	58.3												
	gpm	26.0	20.3	16.3	25.0	19.5	15.6	24.1	18.6	15.0	23.1	17.7	14.2												
	wpd	62.1	37.7	24.3	57.4	34.7	22.4	53.3	31.8	20.5	49.0	28.7	18.5												
82	TC	102.5	99.6	96.4	98.6	95.6	92.4	94.6	91.6	88.4	90.7	87.5	84.5												
	SC	71.6	70.1	68.5	69.6	68.1	66.5	67.6	66.1	64.6	65.7	64.2	62.7												
	gpm	26.0	20.2	16.2	25.0	19.4	15.6	23.9	18.6	14.9	22.9	17.7	14.2												
	wpd	61.7	37.4	24.1	57.0	34.4	22.2	52.2	31.5	20.3	47.9	28.7	18.5												
84	TC	102.8	100.0	97.1	99.0	96.1	93.2	95.0	92.3	89.5	91.1	88.4	85.6												
	SC	75.7	74.2	72.8	73.7	72.3	70.9	71.8	70.4	69.0	69.9	68.5	67.2												
	gpm	26.0	20.3	16.4	25.0	19.5	15.7	24.0	18.7	15.1	23.0	18.0	14.5												
	wpd	62.1	37.7	24.6	57.4	34.7	22.6	52.9	32.1	21.0	48.6	29.6	19.2												
86	TC	103.1	100.5	97.9	99.4	96.8	94.2	95.6	93.0	90.5	91.8	89.3	86.9												
	SC	79.8	78.5	77.1	77.9	76.6	75.3	76.0	74.7	73.4	74.1	72.9	71.7												
	gpm	26.1	20.3	16.6	25.2	19.5	15.9	24.2	18.8	15.3	23.2	18.1	14.7												
	wpd	62.5	37.7	25.1	58.2	35.0	23.1	53.6	32.4	21.4	49.3	29.8	19.8												
88	TC	103.6	101.3	98.9	100.0	97.6	95.3	96.3	94.0	91.8	92.5	90.3	88.3												
	SC	84.0	82.8	81.5	82.1	80.9	79.8	80.2	79.1	78.0	78.4	77.3	76.3												
	gpm	26.3	20.5	16.7	25.3	19.8	16.1	24.4	19.0	15.6	23.5	18.3	14.9												
	wpd	63.3	38.3	25.6	58.5	35.9	23.8	54.4	33.2	22.2	50.4	30.7	20.3												
90	TC	104.2	102.1	100.0	100.6	98.5	96.6	97.0	95.0	93.1	93.4	91.6	89.8												
	SC	88.2	87.1	86.0	86.4	85.3	84.3	84.5	83.5	82.6	82.7	81.8	80.9												
	gpm	26.5	20.7	16.9	25.5	20.0	16.3	24.6	19.3	15.7	23.7	18.6	15.1												
	wpd	64.1	39.3	26.1	59.7	36.5	24.3	55.5	34.1	22.6	51.5	31.5	21.0												

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10
74	TC	65.2	60.0	54.8	62.3	57.1	51.8	59.4	54.2	48.9	56.5	51.2	45.9
	SC	29.9	27.9	25.9	28.8	26.8	24.8	27.7	25.7	23.7	26.5	24.5	22.5
	gpm	16.4	12.1	9.2	15.7	11.6	8.8	15.0	11.0	8.3	14.3	10.4	7.8
	wpd	44.2	23.9	13.9	40.5	21.8	12.6	37.0	19.8	11.3	33.7	17.7	9.8
76	TC	65.6	60.5	55.3	62.7	57.5	52.3	59.8	54.6	49.2	56.9	51.6	46.2
	SC	33.1	31.0	29.0	31.9	29.9	27.9	30.8	28.8	26.7	29.7	27.7	25.6
	gpm	16.6	12.3	9.3	15.8	11.6	8.8	15.1	11.1	8.3	14.4	10.5	7.8
	wpd	45.1	24.6	14.2	40.9	22.1	12.8	37.4	20.1	11.3	34.0	17.9	10.0
78	TC	66.0	60.8	55.4	63.1	57.8	52.4	60.1	54.7	49.3	57.1	51.7	46.2
	SC	36.2	34.1	32.0	35.1	33.0	30.9	33.9	31.8	29.8	32.8	30.7	28.6
	gpm	16.7	12.3	9.3	16.0	11.7	8.8	15.2	11.1	8.3	14.4	10.5	7.8
	wpd	45.5	24.9	14.2	41.8	22.4	12.8	37.8	20.1	11.3	34.0	17.9	10.0
80	TC	66.1	60.8	55.4	63.2	57.8	52.4	60.1	54.7	49.6	57.1	51.6	46.6
	SC	39.3	37.2	35.0	38.1	36.0	33.9	37.0	34.8	32.8	35.8	33.7	31.8
	gpm	16.7	12.3	9.4	16.0	11.7	8.8	15.2	11.1	8.4	14.4	10.5	7.9
	wpd	45.9	24.9	14.4	41.8	22.4	12.8	37.8	20.1	11.5	34.0	17.9	10.2
82	TC	66.0	60.7	55.7	63.0	57.7	52.9	60.0	54.8	50.3	56.8	52.0	47.6
	SC	42.3	40.2	38.1	41.1	39.0	37.1	40.0	37.9	36.1	38.8	36.9	35.1
	gpm	16.7	12.3	9.4	16.0	11.7	8.9	15.2	11.1	8.5	14.4	10.5	8.1
	wpd	45.9	24.9	14.4	41.8	22.4	13.0	37.8	20.1	11.9	34.0	18.2	10.6
84	TC	65.9	60.8	56.3	62.9	58.0	53.7	60.0	55.4	51.2	57.1	52.7	48.7
	SC	45.3	43.2	41.4	44.1	42.2	40.4	43.0	41.1	39.4	42.0	40.2	38.3
	gpm	16.7	12.3	9.5	15.9	11.7	9.1	15.2	11.2	8.6	14.5	10.6	8.2
	wpd	45.5	24.6	14.9	41.4	22.4	13.5	37.8	20.4	12.1	34.4	18.5	11.1
86	TC	65.7	61.4	57.3	63.1	58.8	54.9	60.5	56.4	52.4	57.8	53.9	50.0
	SC	48.3	46.5	44.7	47.3	45.5	43.7	46.3	44.5	42.8	45.3	43.5	41.8
	gpm	16.6	12.4	9.7	15.9	11.9	9.3	15.4	11.4	8.8	14.6	10.9	8.5
	wpd	45.1	25.2	15.4	41.4	23.3	14.2	38.6	21.3	12.8	34.8	19.6	11.7
88	TC	66.3	62.4	58.4	63.9	59.9	56.1	61.3	57.6	53.8	58.9	55.2	51.7
	SC	51.6	49.9	48.1	50.7	48.8	47.1	49.6	47.9	46.1	48.7	46.9	45.3
	gpm	16.7	12.6	9.8	16.1	12.2	9.5	15.5	11.6	9.1	14.9	11.2	8.8
	wpd	45.9	26.1	15.9	42.6	24.3	14.6	39.4	22.1	13.5	36.3	20.4	12.6
90	TC	67.3	63.6	59.9	65.0	61.3	57.7	62.7	58.9	55.6	60.3	56.6	53.6
	SC	55.0	53.3	51.4	54.1	52.3	50.6	53.0	51.4	49.6	52.0	50.3	48.8
	gpm	17.1	12.9	10.1	16.4	12.4	9.8	15.8	11.9	9.4	15.3	11.4	9.1
	wpd	47.6	27.1	16.6	44.2	25.2	15.6	40.9	23.3	14.4	38.2	21.3	13.5

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	86.2	80.7	75.1	82.7	77.1	71.5	79.0	73.4	67.7	75.4	69.6	63.9												
	SC	39.0	36.7	34.4	37.5	35.2	33.0	36.0	33.8	31.5	34.5	32.3	30.0												
	gpm	21.8	16.4	12.7	20.9	15.6	12.1	20.0	14.8	11.4	19.1	14.1	10.7												
	wpd	43.7	24.6	14.8	40.2	22.4	13.3	36.8	20.1	11.9	33.3	18.2	10.6												
76	TC	86.5	81.0	75.4	82.9	77.4	71.6	79.3	73.7	67.9	75.6	69.9	64.0												
	SC	42.5	40.3	38.0	41.0	38.8	36.5	39.6	37.3	35.0	38.1	35.8	33.5												
	gpm	21.9	16.5	12.7	21.0	15.7	12.1	20.1	14.9	11.5	19.1	14.2	10.8												
	wpd	44.0	24.8	14.8	40.5	22.6	13.3	37.1	20.4	12.1	33.6	18.4	10.8												
78	TC	86.7	81.2	75.5	83.1	77.5	71.7	79.5	73.8	68.0	75.7	69.9	64.2												
	SC	46.0	43.7	41.4	44.5	42.2	39.9	43.0	40.7	38.4	41.5	39.2	37.0												
	gpm	22.0	16.5	12.8	21.1	15.7	12.1	20.1	15.0	11.5	19.1	14.2	10.8												
	wpd	44.3	24.8	15.0	40.8	22.6	13.5	37.1	20.6	12.1	33.6	18.4	10.8												
80	TC	86.8	81.1	75.6	83.2	77.5	72.0	79.5	73.8	68.3	75.7	70.1	64.8												
	SC	49.5	47.1	44.8	48.0	45.6	43.4	46.5	44.2	42.0	45.0	42.7	40.6												
	gpm	22.0	16.4	12.7	21.1	15.7	12.1	20.1	15.0	11.6	19.1	14.3	10.9												
	wpd	44.3	24.6	14.8	40.8	22.6	13.5	37.1	20.6	12.3	33.6	18.6	10.9												
82	TC	86.6	81.2	76.0	83.1	77.6	72.5	79.4	74.0	69.0	75.8	70.5	65.6												
	SC	52.8	50.6	48.4	51.4	49.1	47.0	49.9	47.7	45.6	48.4	46.3	44.3												
	gpm	21.8	16.5	12.9	21.1	15.7	12.2	20.1	15.0	11.6	19.2	14.3	11.1												
	wpd	43.7	24.8	15.2	40.8	22.6	13.7	37.1	20.6	12.4	33.9	18.6	11.2												
84	TC	86.6	81.5	76.6	83.1	78.1	73.4	79.6	74.7	70.0	76.1	71.3	66.6												
	SC	56.3	54.1	52.1	54.8	52.7	50.7	53.4	51.3	49.4	51.9	50.0	48.0												
	gpm	21.9	16.5	12.9	21.0	15.8	12.4	20.1	15.1	11.8	19.2	14.4	11.2												
	wpd	44.0	25.1	15.4	40.5	22.9	14.0	37.1	21.0	12.8	33.9	19.0	11.6												
86	TC	86.9	82.2	77.6	83.5	78.9	74.3	80.2	75.6	71.1	76.9	72.3	68.1												
	SC	59.8	57.8	55.8	58.4	56.4	54.5	57.0	55.0	53.1	55.6	53.7	51.9												
	gpm	22.0	16.7	13.1	21.1	16.0	12.5	20.3	15.3	12.1	19.5	14.7	11.5												
	wpd	44.3	25.6	15.8	40.8	23.4	14.4	37.7	21.5	13.3	34.7	19.7	12.1												
88	TC	87.5	82.9	78.6	84.3	79.8	75.6	81.0	76.7	72.6	77.8	73.5	69.6												
	SC	63.4	61.4	59.6	62.1	60.2	58.3	60.7	58.8	57.1	59.4	57.5	55.9												
	gpm	22.2	16.8	13.3	21.3	16.2	12.8	20.5	15.6	12.2	19.7	14.9	11.7												
	wpd	45.0	25.8	16.2	41.7	24.1	15.0	38.6	22.2	13.7	35.6	20.4	12.6												
90	TC	88.3	84.0	80.0	85.2	80.8	77.0	82.0	77.8	74.2	78.8	74.8	71.4												
	SC	67.1	65.2	63.5	65.8	63.9	62.3	64.5	62.7	61.0	63.2	61.4	59.8												
	gpm	22.4	17.0	13.5	21.6	16.4	13.0	20.8	15.7	12.5	20.0	15.1	12.1												
	wpd	46.0	26.6	16.8	42.7	24.6	15.6	39.5	22.6	14.4	36.5	21.0	13.3												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	96.8	91.9	86.8	93.1	88.1	82.7	89.3	84.2	78.5	85.4	80.2	74.1												
	SC	43.6	41.5	39.3	41.9	39.8	37.6	40.3	38.2	35.9	38.7	36.5	34.1												
	gpm	24.5	18.6	14.7	23.6	17.9	14.0	22.6	17.1	13.2	21.6	16.3	12.5												
	wpd	39.2	22.7	14.1	36.4	21.0	12.8	33.5	19.1	11.5	30.7	17.4	10.3												
76	TC	96.9	74.1	68.4	93.1	88.1	82.8	89.4	84.3	78.5	85.5	80.3	74.2												
	SC	47.1	36.0	33.5	45.4	43.3	41.1	43.8	41.7	39.3	42.2	40.1	37.6												
	gpm	24.5	15.0	11.5	23.5	17.8	14.0	22.7	17.1	13.2	21.6	16.3	12.5												
	wpd	39.2	14.7	8.7	36.2	20.8	12.8	33.8	19.1	11.5	30.7	17.4	10.3												
78	TC	97.0	92.1	87.0	93.2	88.2	82.9	89.3	84.2	78.7	85.5	80.2	74.4												
	SC	50.6	48.5	46.3	48.9	46.8	44.6	47.2	45.1	42.9	45.6	43.5	41.1												
	gpm	24.5	18.7	14.7	23.6	17.9	14.0	22.5	17.0	13.3	21.6	16.2	12.6												
	wpd	39.5	22.9	14.1	36.4	21.0	12.9	33.3	18.9	11.6	30.7	17.2	10.4												
80	TC	97.0	74.0	68.5	93.2	88.2	83.1	89.3	84.4	79.2	85.4	80.4	75.0												
	SC	54.0	41.1	38.8	52.3	50.3	48.1	50.7	48.6	46.5	49.0	47.0	44.8												
	gpm	24.5	15.0	11.5	23.6	17.9	14.0	22.5	17.1	13.4	21.6	16.3	12.7												
	wpd	39.5	14.7	8.7	36.4	21.0	12.9	33.3	19.1	11.8	30.5	17.4	10.5												
82	TC	96.9	92.2	87.6	93.2	88.5	83.7	89.4	84.7	79.8	85.5	80.8	75.8												
	SC	57.4	55.4	53.4	55.8	53.8	51.8	54.1	52.2	50.2	52.5	50.6	48.5												
	gpm	24.5	18.7	14.8	23.6	18.0	14.1	22.6	17.2	13.5	21.6	16.4	12.7												
	wpd	39.5	22.9	14.4	36.4	21.2	13.1	33.5	19.3	11.9	30.7	17.5	10.7												
84	TC	97.0	92.6	88.2	93.4	88.9	84.5	89.7	85.2	80.6	85.9	81.5	60.4												
	SC	60.9	59.0	57.1	59.3	57.4	55.5	57.7	55.8	53.9	56.1	54.3	40.5												
	gpm	24.5	18.8	14.9	23.7	18.0	14.3	22.7	17.3	13.6	21.7	16.5	10.2												
	wpd	39.5	23.1	14.6	36.7	21.3	13.4	33.8	19.7	12.2	31.0	17.9	6.8												
86	TC	97.3	93.1	88.8	93.7	89.4	85.3	90.1	85.8	81.8	86.4	82.2	78.3												
	SC	64.4	62.6	60.7	62.9	61.0	59.3	61.3	59.5	57.8	59.8	58.0	56.4												
	gpm	24.7	18.8	15.0	23.7	18.0	14.4	22.8	17.3	13.8	21.9	16.6	13.2												
	wpd	40.0	23.3	14.7	36.9	21.3	13.5	34.2	19.7	12.5	31.4	18.1	11.5												
88	TC	97.8	93.7	89.9	94.3	90.2	86.5	90.8	86.8	83.0	87.2	83.3	79.8												
	SC	68.1	66.3	64.6	66.5	64.8	63.2	65.0	63.3	61.7	63.5	61.9	60.4												
	gpm	24.8	19.0	15.2	23.9	18.3	14.6	23.0	17.6	14.0	22.1	16.8	13.5												
	wpd	40.3	23.7	15.1	37.4	21.9	14.0	34.7	20.2	12.9	32.1	18.6	11.9												
90	TC	98.4	94.6	90.9	95.0	91.2	87.7	91.4	87.8	84.4	88.0	84.5	81.1												
	SC	71.7	70.0	68.4	70.2	68.6	67.1	68.7	67.1	65.7	67.2	65.7	64.3												
	gpm	24.9	19.2	15.4	24.1	18.4	14.8	23.2	17.8	14.3	22.3	17.2	13.7												
	wpd	40.8	24.1	15.5	37.9	22.3	14.4	35.2	20.8	13.4	32.6	19.3	12.3												

5-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
		TR	8	10	12	8	10	12	8	10	12	8	10	12			
74	TC	114.2	110.6	106.8	110.1	106.4	102.5	106.0	102.2	98.1	101.8	97.9	93.6				
	SC	55.6	53.8	51.9	53.5	51.7	49.8	51.5	49.6	47.7	49.4	47.6	45.6				
	gpm	28.9	22.4	18.1	28.0	21.5	17.3	26.9	20.7	16.6	25.8	19.9	15.8				
	wpd	76.7	45.8	29.8	71.5	42.5	27.4	66.1	39.3	25.1	60.9	36.2	22.9				
76	TC	114.3	110.7	107.0	110.2	106.6	102.6	106.1	102.3	98.2	101.9	98.0	93.8				
	SC	59.5	57.8	55.9	57.5	55.7	53.8	55.5	53.6	51.7	53.4	51.6	49.6				
	gpm	28.9	22.5	18.1	28.0	21.5	17.3	26.9	20.7	16.6	25.8	19.9	15.8				
	wpd	76.7	46.2	29.8	71.5	42.5	27.4	66.1	39.3	25.1	60.9	36.2	22.9				
78	TC	114.3	110.8	107.0	110.2	106.6	102.7	106.1	102.3	104.8	101.9	98.0	94.0				
	SC	63.5	61.8	59.9	61.5	59.7	57.8	59.4	57.6	58.8	57.4	55.5	53.6				
	gpm	29.0	22.5	18.1	28.0	21.5	17.4	26.9	20.7	17.7	25.9	19.8	15.9				
	wpd	77.2	46.2	29.8	71.5	42.5	27.7	66.1	39.3	28.7	61.3	35.9	23.1				
80	TC	114.3	110.8	107.2	110.2	106.6	102.9	106.1	102.4	98.6	101.9	98.1	94.3				
	SC	67.4	65.7	63.9	65.4	63.6	61.8	63.3	61.6	59.7	61.3	59.5	57.7				
	gpm	29.0	22.5	18.1	28.0	21.6	17.4	26.9	20.7	16.6	25.9	19.9	16.0				
	wpd	77.2	46.2	30.1	71.5	42.8	27.7	66.1	39.3	25.3	61.3	36.2	23.4				
82	TC	114.2	110.9	107.3	110.1	106.7	103.1	106.1	102.6	99.0	101.9	98.4	94.7				
	SC	71.3	69.7	67.9	69.3	67.6	65.8	67.3	65.6	63.8	65.2	63.5	61.8				
	gpm	28.9	22.5	18.1	27.8	21.6	17.4	27.0	20.8	16.7	25.9	20.0	16.1				
	wpd	76.3	46.2	30.1	70.7	42.8	27.7	66.5	39.6	25.6	61.3	36.5	23.6				
84	TC	114.2	111.0	107.7	110.2	107.0	103.6	106.2	102.9	99.4	102.0	98.7	95.3				
	SC	75.3	73.7	72.0	73.2	71.7	70.0	71.2	69.7	68.0	69.2	67.6	66.0				
	gpm	28.9	22.5	18.1	27.9	21.7	17.5	26.8	20.9	16.8	25.8	20.0	16.1				
	wpd	76.3	46.5	30.1	71.1	43.2	27.9	65.7	39.9	25.8	60.9	36.8	23.6				
86	TC	114.3	111.3	108.1	110.3	107.3	104.1	106.4	103.3	100.0	102.3	99.2	96.0				
	SC	79.3	77.8	76.1	77.3	75.7	74.2	75.3	73.8	72.2	73.3	71.8	70.3				
	gpm	28.9	22.6	18.2	28.0	21.8	17.6	26.9	21.0	16.9	25.9	20.1	16.2				
	wpd	76.7	46.9	30.4	71.5	43.5	28.2	66.1	40.2	26.1	61.3	37.1	24.1				
88	TC	114.5	111.6	108.6	110.6	107.7	104.8	106.7	103.8	100.9	102.7	99.9	97.0				
	SC	83.3	81.9	80.3	81.3	79.9	78.4	79.4	77.9	76.5	77.4	76.0	74.7				
	gpm	28.9	22.6	18.4	28.0	21.9	17.7	27.0	21.0	17.1	26.0	20.3	16.4				
	wpd	76.7	46.9	30.9	71.9	43.8	28.7	66.9	40.5	26.6	61.7	37.7	24.6				
90	TC	114.7	112.1	109.4	110.9	108.2	105.6	107.1	104.4	101.8	103.2	100.6	98.0				
	SC	87.4	86.0	84.7	85.4	84.1	82.8	83.5	82.2	80.9	81.6	80.3	79.1				
	gpm	29.0	22.7	18.5	28.1	21.9	17.9	27.1	21.1	17.2	26.1	20.4	16.6				
	wpd	77.2	47.2	31.2	72.4	43.8	29.3	67.3	40.9	27.1	62.5	38.0	25.1				

2-Row Chilled Water Cooling

EDB	EWT	42				43			44			45		
		TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC	72.9	67.6	62.3	70.0	64.6	59.3	67.0	61.7	56.2	64.1	58.6	53.1	
	SC	28.8	26.7	24.8	27.6	25.6	23.6	26.5	24.5	22.5	25.4	23.4	21.4	
	gpm	18.5	13.6	10.5	17.7	13.0	10.0	16.9	12.5	9.5	16.2	11.9	8.9	
	wpd	55.7	30.5	18.2	51.2	27.8	16.4	46.8	25.5	14.6	43.0	23.0	13.0	
76	TC	73.1	67.8	62.5	70.2	64.8	59.6	67.2	61.9	56.6	64.2	58.9	53.5	
	SC	31.9	29.9	27.9	30.8	28.7	26.8	29.6	27.6	25.7	28.5	26.5	24.6	
	gpm	18.5	13.7	10.5	17.8	13.1	10.1	17.0	12.5	9.5	16.2	11.9	9.0	
	wpd	55.7	30.8	18.2	51.6	28.1	16.6	47.2	25.5	14.9	43.0	23.3	13.2	
78	TC	73.4	68.2	62.9	70.5	65.2	59.9	67.5	62.2	56.9	64.5	59.2	53.9	
	SC	35.1	33.0	31.0	33.9	31.9	29.9	32.8	30.8	28.8	31.7	29.7	27.7	
	gpm	18.6	13.8	10.6	17.8	13.2	10.1	17.1	12.6	9.6	16.3	11.9	9.1	
	wpd	56.7	31.2	18.5	52.1	28.4	16.6	47.6	25.8	15.1	43.4	23.3	13.5	
80	TC	73.8	68.6	63.3	70.9	65.6	60.2	67.9	62.6	57.1	64.9	59.5	54.1	
	SC	38.2	36.2	34.1	37.1	35.0	33.0	36.0	33.9	31.9	34.8	32.8	30.7	
	gpm	18.7	13.9	10.7	17.9	13.3	10.2	17.2	12.6	9.6	16.4	12.0	9.1	
	wpd	57.2	31.5	18.7	52.5	28.8	16.9	48.5	26.1	15.1	44.2	23.6	13.7	
82	TC	74.2	68.8	63.4	71.2	65.8	60.3	68.2	62.7	57.2	65.1	59.6	54.0	
	SC	41.3	39.3	37.2	40.2	38.1	36.0	39.1	37.0	34.9	37.9	35.8	33.7	
	gpm	18.8	14.0	10.7	18.0	13.3	10.2	17.2	12.7	9.6	16.4	12.1	9.1	
	wpd	57.6	31.9	18.7	53.0	29.1	16.9	48.5	26.5	15.1	44.2	23.9	13.7	
84	TC	74.3	68.8	63.4	71.2	65.8	60.2	68.2	62.7	57.4	65.1	59.5	54.4	
	SC	44.4	42.3	40.2	43.3	41.1	39.0	42.1	40.0	37.9	40.9	38.8	36.9	
	gpm	18.8	14.0	10.7	18.1	13.3	10.2	17.3	12.7	9.7	16.4	12.0	9.1	
	wpd	58.1	31.9	18.7	53.4	29.1	16.9	48.9	26.5	15.4	44.2	23.6	13.7	
86	TC	74.2	68.6	63.5	71.1	65.5	60.5	68.0	62.6	57.8	64.9	59.8	55.1	
	SC	47.4	45.3	43.2	46.3	44.1	42.2	45.1	43.0	41.2	43.9	41.9	40.1	
	gpm	18.8	13.9	10.7	18.0	13.3	10.2	17.2	12.6	9.8	16.4	12.1	9.3	
	wpd	57.6	31.5	18.7	53.0	28.8	17.1	48.5	26.1	15.6	44.2	23.9	14.2	
88	TC	74.0	68.7	64.0	70.8	65.7	61.4	67.9	63.1	58.7	64.8	60.4	56.2	
	SC	50.4	48.3	46.5	49.2	47.2	45.4	48.1	46.2	44.5	46.9	45.2	43.5	
	gpm	18.8	13.9	10.8	17.9	13.3	10.4	17.2	12.8	9.9	16.4	12.3	9.5	
	wpd	57.6	31.5	19.0	52.5	29.1	17.7	48.5	26.8	16.1	43.8	24.6	14.6	
90	TC	73.8	69.1	64.8	70.9	66.5	62.3	68.2	63.9	59.9	65.4	61.4	57.3	
	SC	53.4	51.6	49.8	52.3	50.5	48.7	51.3	49.6	47.7	50.2	48.5	46.8	
	gpm	18.6	14.0	10.9	17.9	13.5	10.5	17.2	12.9	10.2	16.5	12.4	9.7	
	wpd	56.7	32.2	19.6	52.5	29.8	17.9	48.5	27.4	16.9	44.6	25.2	15.4	

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	96.4	90.7	85.0	92.8	87.0	81.2	89.1	83.3	77.4	85.4	79.5	73.6												
	SC	38.1	35.8	33.6	36.7	34.4	32.1	35.2	32.9	30.7	33.7	31.4	29.2												
	gpm	24.4	18.4	14.3	23.5	17.7	13.7	22.6	16.9	13.1	21.6	16.1	12.5												
	wpd	54.7	31.1	18.8	50.8	28.6	17.2	46.7	26.1	15.8	42.7	23.8	14.2												
76	TC	96.5	90.9	85.2	92.9	87.2	81.4	89.2	83.5	77.6	85.5	79.7	73.8												
	SC	41.7	39.4	37.1	40.2	37.9	35.7	38.7	36.4	34.2	37.2	35.0	32.7												
	gpm	24.4	18.4	14.4	23.5	17.7	13.8	22.6	16.9	13.1	21.7	16.1	12.5												
	wpd	54.7	31.1	19.0	50.8	28.6	17.4	46.7	26.3	15.8	43.0	23.8	14.2												
78	TC	96.6	91.0	85.4	93.0	87.4	81.7	89.4	83.7	77.9	85.7	79.9	74.0												
	SC	45.2	42.9	40.6	43.7	41.4	39.2	42.2	40.0	37.7	40.7	38.5	36.2												
	gpm	24.5	18.4	14.4	23.6	17.8	13.8	22.6	16.9	13.1	21.7	16.2	12.5												
	wpd	55.1	31.1	19.0	51.1	28.9	17.4	47.0	26.3	15.8	43.0	24.1	14.2												
80	TC	96.9	91.2	85.5	93.3	87.5	81.8	89.6	83.9	78.0	85.9	80.1	74.1												
	SC	48.7	46.4	44.1	47.2	44.9	42.7	45.7	43.5	41.2	44.3	42.0	39.7												
	gpm	24.6	18.5	14.4	23.6	17.7	13.8	22.7	17.0	13.2	21.7	16.2	12.5												
	wpd	55.5	31.3	19.0	51.1	28.6	17.6	47.3	26.6	16.0	43.3	24.1	14.4												
82	TC	97.0	91.3	85.6	93.4	87.6	81.8	89.7	83.8	78.0	86.0	80.1	74.2												
	SC	52.2	49.9	47.5	50.7	48.4	46.0	49.2	46.9	44.6	47.7	45.4	43.1												
	gpm	24.4	18.5	14.4	23.7	17.8	13.8	22.7	16.9	13.1	21.7	16.2	12.5												
	wpd	54.7	31.3	19.0	51.5	28.9	17.4	47.3	26.3	15.8	43.3	24.1	14.4												
84	TC	97.0	91.3	85.7	93.3	87.6	82.0	89.7	83.8	78.2	85.9	80.1	74.7												
	SC	55.6	53.3	51.0	54.1	51.8	49.5	52.6	50.3	48.1	51.1	48.8	46.7												
	gpm	24.5	18.5	14.5	23.5	17.8	13.8	22.7	16.9	13.2	21.7	16.2	12.6												
	wpd	55.1	31.3	19.3	50.8	28.9	17.6	47.3	26.3	16.0	43.3	24.1	14.6												
86	TC	96.9	91.3	86.0	93.2	87.7	82.5	89.4	84.0	79.0	85.8	80.5	75.4												
	SC	59.0	56.7	54.5	57.5	55.2	53.1	55.9	53.8	51.7	54.5	52.4	50.4												
	gpm	24.5	18.5	14.5	23.5	17.8	13.9	22.6	17.0	13.4	21.7	16.3	12.7												
	wpd	55.1	31.3	19.3	50.8	28.9	17.8	46.7	26.6	16.4	43.0	24.3	14.8												
88	TC	96.8	91.6	86.5	93.3	88.1	83.1	89.6	84.6	79.8	86.1	81.2	76.4												
	SC	62.4	60.2	58.1	60.9	58.8	56.8	59.4	57.4	55.4	58.0	56.0	54.1												
	gpm	24.5	18.6	14.6	23.6	17.8	14.0	22.6	17.2	13.4	21.7	16.5	12.9												
	wpd	55.1	31.6	19.5	51.1	29.2	18.0	47.0	27.1	16.6	43.3	24.8	15.4												
90	TC	97.0	92.0	87.4	93.6	88.8	84.1	90.1	85.5	80.7	86.7	82.0	77.4												
	SC	65.9	63.8	61.8	64.4	62.5	60.5	63.0	61.1	59.2	61.7	59.8	57.9												
	gpm	24.6	18.6	14.7	23.7	18.0	14.2	22.8	17.3	13.6	22.0	16.6	13.0												
	wpd	55.5	31.6	19.9	51.5	29.7	18.4	47.7	27.6	17.0	44.3	25.3	15.6												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	107.9	102.9	97.7	104.1	99.0	93.7	100.3	95.0	89.8	96.4	91.1	85.7												
	SC	43.1	41.0	38.8	41.4	39.3	37.1	39.8	37.6	35.5	38.2	36.0	33.9												
	gpm	27.3	20.8	16.5	26.3	20.0	15.8	25.4	19.2	15.2	24.5	18.4	14.5												
	wpd	48.7	28.5	17.9	45.4	26.3	16.4	42.4	24.3	15.1	39.2	22.3	13.8												
76	TC	107.9	82.8	78.2	104.1	99.1	93.8	100.2	95.1	89.8	96.4	91.1	85.8												
	SC	46.6	35.8	33.8	44.9	42.8	40.7	43.3	41.2	39.0	41.7	39.5	37.4												
	gpm	27.3	16.8	13.1	26.3	20.0	15.8	25.3	19.2	15.2	24.5	18.4	14.5												
	wpd	48.7	18.4	11.3	45.4	26.3	16.4	42.1	24.3	15.1	39.2	22.3	13.8												
78	TC	108.0	103.1	98.0	104.2	99.2	94.0	100.3	95.2	89.9	96.4	91.2	85.9												
	SC	50.1	48.0	45.9	48.4	46.3	44.2	46.8	44.7	42.5	45.1	43.0	40.9												
	gpm	27.3	20.9	16.5	26.4	20.1	15.9	25.3	19.2	15.2	24.3	18.4	14.5												
	wpd	49.0	28.7	17.9	45.6	26.6	16.5	42.1	24.3	15.1	38.7	22.3	13.8												
80	TC	108.1	82.9	78.3	104.3	99.3	94.1	100.4	95.3	90.0	96.5	91.3	85.8												
	SC	53.6	41.0	39.1	51.9	49.8	47.7	50.3	48.2	46.0	48.6	46.5	44.4												
	gpm	27.3	16.8	13.2	26.4	20.1	15.9	25.4	19.3	15.2	24.4	18.4	14.5												
	wpd	49.0	18.6	11.5	45.6	26.6	16.5	42.4	24.5	15.1	39.0	22.3	13.8												
82	TC	108.2	103.2	98.0	104.3	99.3	94.1	100.5	95.3	90.1	96.5	91.3	86.1												
	SC	57.0	54.9	52.8	55.4	53.3	51.1	53.7	51.6	49.5	52.1	50.0	47.9												
	gpm	27.4	20.9	16.6	26.4	20.1	15.9	25.4	19.3	15.2	24.4	18.5	14.5												
	wpd	49.3	28.7	18.1	45.6	26.6	16.5	42.4	24.5	15.2	39.0	22.5	13.8												
84	TC	108.1	103.1	98.1	104.3	99.3	94.2	100.4	95.4	90.4	96.4	91.4	86.9												
	SC	60.5	58.3	56.2	58.8	56.7	54.6	57.2	55.1	53.1	55.5	53.4	40.3												
	gpm	27.4	20.9	16.5	26.4	20.1	15.9	25.4	19.3	15.3	24.4	18.5	11.6												
	wpd	49.3	28.7	17.9	45.6	26.6	16.5	42.4	24.5	15.4	39.0	22.5	8.9												
86	TC	108.0	103.3	98.5	104.2	99.4	94.6	100.4	95.6	90.8	96.5	91.8	87.1												
	SC	63.9	61.8	59.8	62.2	60.2	58.2	60.6	58.6	56.7	59.0	57.0	55.1												
	gpm	27.3	20.9	16.6	26.4	20.2	16.0	25.4	19.4	15.3	24.5	18.6	14.7												
	wpd	49.0	28.7	18.1	45.6	26.8	16.7	42.4	24.7	15.4	39.2	22.7	14.1												
88	TC	108.1	103.5	99.0	104.3	99.7	95.3	100.6	96.0	91.6	96.8	92.3	87.7												
	SC	67.3	65.3	63.5	65.7	63.7	61.9	64.1	62.2	60.4	62.5	60.7	58.8												
	gpm	27.4	20.9	16.8	26.5	20.2	16.1	25.5	19.4	15.5	24.5	18.7	14.8												
	wpd	49.3	28.7	18.4	45.9	26.8	17.0	42.6	24.7	15.7	39.5	22.9	14.4												
90	TC	108.3	103.9	99.7	104.6	100.3	95.9	101.0	96.6	92.4	97.3	92.9	88.9												
	SC	70.8	69.0	67.1	69.2	67.4	65.6	67.7	65.9	64.1	66.2	64.4	62.7												
	gpm	27.5	21.1	16.8	26.5	20.3	16.2	25.6	19.6	15.6	24.7	18.8	15.0												
	wpd	49.6	29.2	18.6	46.2	27.0	17.2	42.9	25.1	16.0	40.0	23.3	14.7												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	126.3	122.8	118.9	122.3	118.6	114.6	118.1	114.3	110.2	113.9	110.0	105.7												
	SC	55.2	53.4	51.5	53.2	51.3	49.4	51.1	49.3	47.3	49.1	47.2	45.2												
	gpm	32.0	24.9	20.1	31.0	24.0	19.4	29.9	23.1	18.6	28.9	22.3	17.8												
	wpd	93.9	56.6	37.1	88.1	52.5	34.4	82.1	49.0	31.8	76.3	45.5	29.0												
76	TC	126.5	123.0	119.2	122.4	118.8	114.8	118.3	114.5	110.4	114.1	110.1	105.9												
	SC	59.2	57.5	55.6	57.2	55.4	53.5	55.1	53.3	51.4	53.1	51.2	49.3												
	gpm	32.1	24.9	20.1	31.0	24.0	19.4	30.0	23.1	18.6	28.9	22.3	17.9												
	wpd	94.4	56.6	37.1	88.1	52.9	34.4	82.6	49.0	31.8	76.7	45.5	29.3												
78	TC	126.6	123.1	119.3	122.5	118.9	115.0	118.4	114.6	117.2	114.2	110.3	106.1												
	SC	63.2	61.5	59.6	61.2	59.4	57.5	59.2	57.3	58.6	57.1	55.2	53.3												
	gpm	32.1	25.0	20.1	31.1	24.1	19.5	30.0	23.2	19.8	28.9	22.3	17.9												
	wpd	94.4	57.0	37.1	88.6	53.3	34.7	82.6	49.3	35.9	76.7	45.5	29.3												
80	TC	126.5	123.2	119.4	122.6	119.0	115.1	118.4	114.7	110.7	114.2	110.3	106.2												
	SC	67.2	65.5	63.6	65.2	63.4	61.5	63.1	61.3	59.4	61.1	59.2	57.3												
	gpm	31.9	25.0	20.2	31.1	24.1	19.5	30.0	23.2	18.7	28.9	22.4	18.0												
	wpd	93.4	57.0	37.4	88.6	53.3	34.7	82.6	49.3	32.1	76.7	45.8	29.6												
82	TC	126.6	123.2	119.4	122.5	119.0	115.1	118.4	114.7	110.8	114.2	110.4	106.4												
	SC	71.1	69.4	67.5	69.1	67.3	65.5	67.1	65.3	63.4	65.0	63.2	61.3												
	gpm	31.9	25.0	20.1	30.9	24.1	19.5	30.0	23.2	18.7	28.9	22.4	18.0												
	wpd	93.4	57.0	37.1	87.7	53.3	34.7	82.6	49.3	32.1	76.7	45.8	29.6												
84	TC	126.5	123.2	119.5	122.5	119.0	115.2	118.3	114.7	110.9	114.2	110.5	106.7												
	SC	75.1	73.4	71.5	73.0	71.3	69.5	70.9	69.2	67.4	68.9	67.2	65.4												
	gpm	31.9	25.0	20.1	30.9	24.1	19.5	29.9	23.3	18.7	28.9	22.4	18.1												
	wpd	93.4	57.0	37.1	87.7	53.3	34.7	81.6	49.7	32.1	76.7	45.8	29.8												
86	TC	126.5	123.2	119.7	122.4	119.0	115.5	118.3	114.9	111.2	114.1	110.7	107.0												
	SC	79.0	77.3	75.6	76.9	75.3	73.5	74.9	73.2	71.5	72.9	71.2	69.5												
	gpm	31.9	25.0	20.2	30.9	24.1	19.5	29.9	23.3	18.8	28.8	22.5	18.1												
	wpd	93.4	57.0	37.4	87.7	53.3	34.7	81.6	49.7	32.4	75.8	46.2	29.8												
88	TC	126.4	123.3	119.9	122.4	119.3	115.8	118.4	115.1	111.6	114.3	111.0	107.4												
	SC	82.9	81.3	79.7	80.9	79.3	77.6	78.9	77.3	75.6	76.9	75.3	73.6												
	gpm	32.0	25.0	20.3	30.9	24.2	19.5	29.9	23.4	18.9	28.9	22.5	18.1												
	wpd	93.9	57.4	37.7	87.7	53.6	35.0	82.1	50.0	32.6	76.3	46.5	30.1												
90	TC	126.5	123.5	120.3	122.5	119.5	116.2	118.5	115.4	112.2	114.5	111.3	108.0												
	SC	86.9	85.4	83.7	84.9	83.4	81.8	82.9	81.4	79.8	80.9	79.4	77.8												
	gpm	32.0	25.0	20.3	31.0	24.3	19.6	30.0	23.5	19.0	28.9	22.6	18.2												
	wpd	93.9	57.4	37.7	88.1	54.0	35.3	82.6	50.4	32.9	76.7	46.9	30.4												

2-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	81.4	76.0	70.5	78.4	73.0	67.4	75.4	69.9	64.4	72.3	66.9	61.3												
	SC	27.3	25.3	23.4	26.2	24.3	22.3	25.1	23.2	21.3	24.0	22.1	20.2												
	gpm	20.6	15.4	11.9	19.9	14.7	11.4	19.1	14.1	10.9	18.3	13.6	10.3												
	wpd	69.6	38.6	23.0	64.5	35.5	21.3	59.5	32.6	19.3	54.8	30.1	17.4												
76	TC	81.4	75.9	70.5	78.4	72.9	67.4	75.3	69.8	64.3	72.3	66.7	61.2												
	SC	30.7	28.7	26.7	29.6	27.6	25.6	28.5	26.5	24.5	27.3	25.4	23.4												
	gpm	20.6	15.4	11.9	19.9	14.7	11.4	19.1	14.1	10.9	18.3	13.5	10.3												
	wpd	69.6	38.6	23.0	64.5	35.5	21.3	59.5	32.6	19.3	54.8	29.8	17.4												
78	TC	81.3	75.9	70.6	78.4	72.9	67.5	75.4	69.9	64.5	72.3	66.9	61.3												
	SC	33.8	31.8	29.8	32.7	30.7	28.7	31.6	29.6	27.6	30.4	28.5	26.5												
	gpm	20.6	15.4	11.9	19.9	14.8	11.4	19.1	14.2	10.9	18.3	13.5	10.3												
	wpd	69.6	38.6	23.3	64.5	35.9	21.3	59.5	33.0	19.3	54.8	29.8	17.4												
80	TC	81.6	76.3	70.9	78.7	73.3	67.9	75.7	70.3	64.8	72.7	67.2	61.7												
	SC	37.0	35.0	33.0	35.9	33.8	31.9	34.7	32.7	30.8	33.6	31.6	29.7												
	gpm	20.7	15.4	12.0	19.9	14.9	11.5	19.2	14.3	10.9	18.4	13.6	10.4												
	wpd	70.1	39.0	23.6	65.0	36.3	21.6	60.0	33.3	19.6	55.3	30.1	17.7												
82	TC	82.0	76.6	71.3	79.0	73.6	68.3	76.0	70.6	65.2	73.0	67.6	62.1												
	SC	40.1	38.1	36.1	39.0	37.0	35.0	37.9	35.9	33.9	36.8	34.8	32.8												
	gpm	20.8	15.5	12.0	20.0	15.0	11.6	19.2	14.3	11.0	18.5	13.6	10.5												
	wpd	70.7	39.4	23.6	65.5	36.7	21.8	60.5	33.7	19.8	55.7	30.5	17.9												
84	TC	82.4	77.0	71.5	79.4	74.0	68.5	76.4	70.9	65.4	73.3	67.8	62.2												
	SC	43.3	41.2	39.2	42.2	40.1	38.1	41.0	39.0	37.0	39.9	37.9	35.8												
	gpm	20.9	15.6	12.0	20.1	15.0	11.6	19.3	14.3	11.0	18.5	13.7	10.5												
	wpd	71.2	39.8	23.6	66.0	37.0	21.8	61.0	33.7	19.8	56.2	30.8	17.9												
86	TC	82.6	77.1	71.6	79.6	74.1	68.5	76.6	71.0	65.4	73.5	67.9	62.2												
	SC	46.4	44.3	42.2	45.3	43.2	41.1	44.1	42.1	40.0	43.0	40.9	38.8												
	gpm	20.9	15.6	12.1	20.2	15.0	11.6	19.4	14.4	11.1	18.6	13.7	10.5												
	wpd	71.7	39.8	23.9	66.5	37.0	21.8	61.5	34.0	20.1	56.7	30.8	18.2												
88	TC	82.7	77.1	71.6	79.6	74.0	68.4	76.5	70.8	65.3	73.4	67.7	62.4												
	SC	49.5	47.3	45.2	48.3	46.2	44.1	47.2	45.0	43.0	46.0	43.9	41.9												
	gpm	20.9	15.6	12.1	20.2	15.0	11.6	19.4	14.3	11.0	18.6	13.7	10.5												
	wpd	71.7	39.8	23.9	66.5	36.7	21.8	61.5	33.7	19.8	56.7	30.8	18.2												
90	TC	82.6	77.0	71.6	79.5	73.8	68.7	76.4	70.7	65.7	73.2	67.8	63.0												
	SC	52.5	50.3	48.3	51.3	49.2	47.2	50.2	48.0	46.2	49.0	47.0	45.2												
	gpm	20.9	15.6	12.1	20.2	15.0	11.6	19.4	14.3	11.1	18.5	13.7	10.6												
	wpd	71.7	39.8	23.9	66.5	36.7	22.1	61.5	33.7	20.1	56.2	30.8	18.5												

3-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12						
74	TC	107.3	101.5	95.7	103.6	97.8	91.9	99.9	94.0	88.0	96.1	90.2	84.1												
	SC	37.2	34.9	32.6	36.7	33.5	31.2	34.3	32.0	29.7	32.8	30.5	28.3												
	gpm	27.2	20.6	16.2	26.2	19.9	15.6	25.3	19.1	14.9	24.3	18.2	14.2												
	wpd	67.8	38.9	24.1	63.0	36.2	22.2	58.8	33.3	20.4	54.4	30.5	18.4												
76	TC	107.2	101.3	95.5	103.5	97.7	91.8	99.8	93.9	87.9	96.0	90.1	84.0												
	SC	40.8	38.4	36.1	39.3	37.0	34.7	37.8	35.5	33.3	36.3	34.1	31.8												
	gpm	27.2	20.5	16.1	26.2	19.8	15.5	25.3	19.1	14.8	24.3	18.2	14.2												
	wpd	67.8	38.6	23.8	63.0	35.9	21.9	58.8	33.3	20.1	54.4	30.5	18.4												
78	TC	107.1	101.3	95.6	103.5	97.6	91.8	99.8	94.0	88.1	96.0	90.2	84.2												
	SC	44.3	42.0	39.7	42.8	40.5	38.2	41.3	39.1	36.8	39.8	37.6	35.4												
	gpm	27.2	20.5	16.1	26.2	19.7	15.5	25.3	19.1	14.9	24.3	18.2	14.3												
	wpd	67.8	38.6	23.8	63.0	35.6	21.9	58.8	33.3	20.4	54.4	30.5	18.6												
80	TC	107.2	101.5	95.8	103.6	97.8	92.0	100.0	94.1	88.2	96.2	90.4	84.4												
	SC	47.8	45.5	43.2	46.3	44.0	41.8	44.8	42.5	40.3	43.4	41.1	38.9												
	gpm	27.0	20.5	16.2	26.3	19.8	15.6	25.3	19.0	14.9	24.3	18.3	14.3												
	wpd	67.0	38.6	24.1	63.4	35.9	22.2	58.8	33.0	20.4	54.4	30.8	18.6												
82	TC	107.3	101.7	96.0	103.7	98.0	92.2	100.1	94.3	88.4	96.4	90.4	84.5												
	SC	51.3	49.0	46.8	49.8	47.5	45.3	48.4	46.1	43.8	46.9	44.6	42.3												
	gpm	27.1	20.6	16.2	26.1	19.9	15.6	25.4	19.1	14.9	24.4	18.2	14.3												
	wpd	67.4	38.9	24.1	62.7	36.2	22.2	59.2	33.3	20.4	54.7	30.5	18.6												
84	TC	107.6	101.9	96.2	103.9	98.2	92.3	100.2	94.4	88.5	96.6	90.6	84.5												
	SC	54.8	52.5	50.2	53.3	51.0	48.7	51.8	49.5	47.3	50.4	48.1	45.8												
	gpm	27.2	20.7	16.2	26.2	19.9	15.6	25.3	19.1	14.9	24.5	18.3	14.3												
	wpd	67.8	39.2	24.1	63.0	36.2	22.2	58.8	33.6	20.4	55.1	30.8	18.6												
86	TC	107.7	102.0	96.2	104.0	98.2	92.3	100.3	94.4	88.4	96.5	90.5	84.6												
	SC	58.3	56.0	53.7	56.8	54.5	52.2	55.3	53.0	50.7	53.8	51.5	49.2												
	gpm	27.2	20.7	16.3	26.3	19.9	15.6	25.3	19.1	14.9	24.3	18.3	14.3												
	wpd	67.8	39.2	24.3	63.4	36.2	22.4	58.8	33.6	20.4	54.4	30.8	18.8												
88	TC	107.7	102.0	96.1	104.0	98.2	92.4	100.2	94.3	88.6	96.4	90.5	85.0												
	SC	61.7	59.4	57.1	60.2	57.9	55.6	58.7	56.4	54.2	57.2	54.9	52.8												
	gpm	27.3	20.7	16.3	26.3	19.9	15.6	25.3	19.1	15.0	24.3	18.3	14.3												
	wpd	68.2	39.2	24.3	63.4	36.2	22.4	58.8	33.6	20.6	54.4	30.8	18.8												
90	TC	107.6	101.9	96.3	103.9	98.2	92.7	100.1	94.5	89.2	96.3	90.8	85.5												
	SC	65.1	62.7	60.5	63.6	61.3	59.1	62.1	59.8	57.8	60.6	58.4	56.4												
	gpm	27.2	20.7	16.2	26.3	20.0	15.6	25.3	19.1	15.1	24.3	18.4	14.4												
	wpd	67.8	39.2	24.1	63.4	36.5	22.4	58.8	33.6	20.8	54.4	31.1	19.0												

4-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	119.7	114.7	109.5	115.9	110.7	105.4	112.0	106.7	101.3	108.1	102.7	97.2												
	SC	42.6	40.5	38.3	41.0	38.8	36.7	39.3	37.2	35.0	37.7	35.5	33.3												
	gpm	30.3	23.3	18.5	29.3	22.4	17.8	28.3	21.6	17.1	27.4	20.8	16.4												
	wpd	60.2	35.5	22.5	56.2	33.1	20.8	52.5	30.5	19.1	49.3	28.3	17.5												
76	TC	119.6	92.1	88.3	115.8	110.6	105.3	111.9	106.6	101.2	107.9	102.6	97.1												
	SC	46.1	35.6	34.0	44.4	42.3	40.1	42.8	40.6	38.5	41.1	39.0	36.8												
	gpm	30.2	18.7	14.9	29.3	22.4	17.8	28.3	21.6	17.1	27.3	20.8	16.4												
	wpd	59.9	22.9	14.6	56.2	33.1	20.8	52.5	30.5	19.1	48.7	28.3	17.5												
78	TC	119.5	114.5	109.4	115.7	110.6	105.4	111.8	106.7	101.3	107.9	102.6	97.2												
	SC	49.6	47.4	45.3	47.9	45.8	43.7	46.3	44.2	42.0	44.6	42.5	40.4												
	gpm	30.2	23.3	18.5	29.3	22.4	17.8	28.3	21.6	17.1	27.3	20.8	16.4												
	wpd	59.9	35.5	22.5	56.2	33.1	20.8	52.5	30.5	19.1	48.7	28.3	17.7												
80	TC	119.6	92.1	88.4	115.8	110.7	105.5	111.9	106.8	101.4	108.0	102.7	97.3												
	SC	53.1	40.9	39.3	51.4	49.3	47.2	49.8	47.7	45.5	48.1	46.0	43.9												
	gpm	30.3	18.7	14.9	29.3	22.4	17.8	28.3	21.6	17.2	27.3	20.8	16.4												
	wpd	60.2	22.9	14.6	56.5	33.1	20.8	52.5	30.7	19.3	48.7	28.5	17.7												
82	TC	119.7	114.7	109.6	115.9	110.8	105.6	112.0	106.8	101.5	108.1	102.8	97.3												
	SC	56.5	54.5	52.3	54.9	52.8	50.7	53.3	51.2	49.0	51.6	49.5	47.4												
	gpm	30.3	23.3	18.5	29.3	22.4	17.9	28.3	21.6	17.2	27.3	20.8	16.4												
	wpd	60.2	35.5	22.5	56.5	33.1	21.0	52.5	30.7	19.3	49.0	28.5	17.7												
84	TC	119.8	114.8	109.5	115.9	110.9	105.5	112.1	106.9	101.5	108.1	102.8	97.7												
	SC	60.0	57.9	55.8	58.4	56.3	54.1	56.7	54.6	52.5	55.1	53.0	40.5												
	gpm	30.3	23.3	18.4	29.3	22.4	17.8	28.4	21.6	17.2	27.3	20.8	13.3												
	wpd	60.2	35.5	22.3	56.5	33.1	20.8	52.8	30.7	19.3	49.0	28.5	11.6												
86	TC	119.8	114.8	109.5	115.9	110.8	105.5	112.0	106.8	101.5	108.0	102.7	97.4												
	SC	63.5	61.4	59.2	61.8	59.7	57.5	60.2	58.1	55.9	58.5	56.4	54.3												
	gpm	30.4	23.3	18.4	29.3	22.4	17.8	28.4	21.6	17.2	27.3	20.8	16.4												
	wpd	60.6	35.5	22.3	56.5	33.1	20.8	52.8	30.7	19.3	49.0	28.5	17.7												
88	TC	119.7	114.6	109.6	115.9	110.7	105.6	111.9	106.8	101.7	107.9	102.8	97.8												
	SC	66.9	64.7	62.7	65.2	63.1	61.0	63.6	61.5	59.5	61.9	59.9	57.9												
	gpm	30.3	23.2	18.5	29.3	22.4	17.8	28.4	21.6	17.2	27.3	20.8	16.5												
	wpd	60.2	35.2	22.5	56.5	32.8	20.8	52.8	30.7	19.3	49.0	28.5	17.9												
90	TC	119.6	114.7	109.9	115.7	110.7	106.1	111.9	106.9	102.1	108.0	103.1	98.3												
	SC	70.3	68.2	66.2	68.6	66.6	64.6	67.0	65.0	63.0	65.4	63.4	61.5												
	gpm	30.3	23.2	18.6	29.3	22.4	18.0	28.4	21.6	17.2	27.3	20.8	16.6												
	wpd	60.2	35.2	22.7	56.5	33.1	21.2	52.8	30.7	19.5	49.0	28.5	18.1												

5-Row Chilled Water Cooling

EDB	EWT	42						43						44						45					
		TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12								
74	TC	139.0	135.4	131.5	134.9	131.2	127.2	130.8	126.9	122.7	126.5	122.5	118.2												
	SC	54.8	53.0	51.1	52.8	50.9	49.0	50.7	48.8	46.9	48.7	46.8	44.8												
	gpm	35.3	27.5	22.2	34.2	26.5	21.5	33.2	25.7	20.7	32.1	24.8	20.0												
	wpd	113.9	69.0	45.2	107.0	64.5	42.2	100.8	60.5	39.3	94.4	56.3	36.5												
76	TC	139.2	135.6	131.8	135.1	131.4	127.5	130.9	127.1	123.0	126.7	122.7	118.5												
	SC	58.9	57.1	55.2	56.8	55.0	53.1	54.8	52.9	51.0	52.7	50.8	48.9												
	gpm	35.3	27.5	22.3	34.3	26.6	21.5	33.2	25.7	20.8	32.1	24.8	20.0												
	wpd	113.9	69.0	45.5	107.5	64.9	42.5	100.8	60.5	39.6	94.4	56.3	36.8												
78	TC	139.3	135.8	132.0	135.2	131.6	127.7	131.1	127.3	130.0	126.9	123.0	118.8												
	SC	62.9	61.1	59.2	60.8	59.0	57.1	58.8	57.0	58.3	56.7	54.9	52.9												
	gpm	35.4	27.5	22.3	34.3	26.7	21.6	33.3	25.8	22.0	32.2	24.9	20.0												
	wpd	114.4	69.4	45.5	107.5	65.3	42.8	101.4	60.9	44.1	94.9	56.6	36.8												
80	TC	139.3	135.9	132.2	135.3	131.7	127.9	131.2	127.5	123.5	127.0	123.1	119.0												
	SC	66.8	65.1	63.3	64.8	63.1	61.2	62.8	61.0	59.1	60.8	58.9	57.0												
	gpm	35.2	27.5	22.4	34.4	26.7	21.6	33.3	25.8	20.9	32.2	25.0	20.1												
	wpd	113.3	69.4	45.8	108.0	65.3	42.8	101.4	60.9	39.9	94.9	57.0	37.1												
82	TC	139.4	136.0	132.2	135.3	131.8	128.0	131.3	127.6	123.6	127.0	123.2	119.1												
	SC	70.8	69.1	67.3	68.8	67.1	65.2	66.8	65.0	63.1	64.7	62.9	61.0												
	gpm	35.2	27.6	22.3	34.2	26.7	21.6	33.3	25.9	20.9	32.2	25.0	20.1												
	wpd	113.3	69.8	45.5	107.0	65.3	42.8	101.4	61.3	39.9	94.9	57.0	37.1												
84	TC	139.4	136.1	132.3	135.4	131.9	127.9	131.2	127.6	123.6	127.1	123.2	119.1												
	SC	74.8	73.1	71.2	72.8	71.0	69.1	70.7	69.0	67.0	68.7	66.9	64.9												
	gpm	35.3	27.6	22.3	34.2	26.7	21.5	33.1	25.9	20.9	32.3	25.0	20.1												
	wpd	113.9	69.8	45.5	107.0	65.3	42.5	100.3	61.3	39.9	95.4	57.0	37.1												
86	TC	139.4	136.1	132.3	135.4	131.9	128.0	131.2	127.6	123.6	127.0	123.2	119.2												
	SC	78.8	77.1	75.2	76.7	75.0	73.1	74.7	72.9	71.0	72.6	70.8	68.9												
	gpm	35.3	27.6	22.3	34.2	26.7	21.6	33.1	25.9	20.9	32.0	25.0	20.1												
	wpd	113.9	69.8	45.5	107.0	65.3	42.8	100.3	61.3	39.9	93.9	57.0	37.1												
88	TC	139.4	136.0	132.3	135.3	131.8	128.1	131.2	127.6	123.7	126.9	123.3	119.4												
	SC	82.7	81.0	79.2	80.6	78.9	77.1	78.6	76.8	75.0	76.5	74.8	73.0												
	gpm	35.3	27.6	22.4	34.2	26.8	21.6	33.1	25.9	20.9	32.0	25.0	20.1												
	wpd	113.9	69.8	45.8	107.0	65.7	42.8	100.3	61.3	39.9	93.9	57.4	37.1												
90	TC	139.3	136.0	132.5	135.2	131.9	128.3	131.1	127.7	124.0	126.9	123.4	119.7												
	SC	86.6	84.9	83.2	84.6	82.9	81.2	82.5	80.8	79.1	80.5	78.8	77.1												
	gpm	35.3	27.6	22.4	34.2	26.8	21.7	33.2	25.9	21.0	32.1	25.0	20.2												
	wpd	113.9	69.8	45.8	107.0	65.7	43.2	100.8	61.3	40.2	94.4	57.4	37.4												

2-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	90.2	84.7	79.1	87.2	81.6	76.0	84.1	78.5	72.8	81.0	75.3	69.7
	SC	29.1	27.2	25.2	28.0	26.1	24.2	27.0	25.0	23.1	25.9	23.9	22.0
	gpm	22.9	17.1	13.3	22.1	16.5	12.9	21.2	15.9	12.3	20.5	15.3	11.8
	wpd	85.6	48.1	29.1	79.9	44.6	27.1	73.9	41.4	24.9	68.6	38.2	22.7
78	TC	90.1	84.6	79.0	87.1	81.5	75.9	84.0	78.4	72.8	80.9	75.3	69.6
	SC	32.5	30.5	28.6	31.4	29.5	27.5	30.3	28.4	26.4	29.3	27.3	25.4
	gpm	22.8	17.1	13.3	22.0	16.5	12.8	21.2	15.9	12.3	20.5	15.3	11.7
	wpd	85.1	48.1	29.1	79.4	44.6	26.8	73.9	41.4	24.6	68.6	38.2	22.4
80	TC	90.0	84.5	79.0	87.0	81.5	75.9	84.0	78.4	72.8	80.9	75.3	69.7
	SC	35.7	33.7	31.7	34.6	32.6	30.6	33.5	31.5	29.5	32.4	30.4	28.4
	gpm	22.8	17.1	13.3	22.0	16.5	12.8	21.2	15.9	12.3	20.5	15.3	11.8
	wpd	85.1	48.1	29.1	79.4	44.6	26.8	73.9	41.4	24.9	68.6	38.2	22.7
82	TC	90.2	84.7	79.2	87.2	81.7	76.2	84.2	78.7	73.1	81.1	75.6	70.0
	SC	38.8	36.8	34.8	37.7	35.7	33.8	36.6	34.6	32.7	35.5	33.5	31.6
	gpm	22.9	17.2	13.3	22.1	16.6	12.9	21.3	16.0	12.3	20.5	15.4	11.8
	wpd	85.6	48.5	29.1	79.9	45.1	27.1	74.4	41.8	24.9	69.1	38.6	22.7
84	TC	90.5	85.0	79.5	87.5	82.0	76.5	84.5	79.0	73.4	81.4	75.9	70.3
	SC	42.0	40.0	38.0	40.9	38.9	36.9	39.8	37.8	35.8	38.7	36.7	34.7
	gpm	23.0	17.2	13.4	22.2	16.7	12.9	21.4	16.1	12.4	20.6	15.4	11.9
	wpd	86.2	48.5	29.4	80.5	45.5	27.1	75.0	42.2	25.2	69.6	38.6	23.0
86	TC	90.8	85.3	79.9	87.8	82.3	76.8	84.8	79.3	73.7	81.7	76.2	70.6
	SC	45.2	43.1	41.1	44.0	42.0	40.0	42.9	40.9	38.9	41.8	39.8	37.8
	gpm	23.0	17.3	13.5	22.3	16.6	12.9	21.5	16.1	12.4	20.7	15.4	11.9
	wpd	86.8	48.9	29.8	81.0	45.1	27.4	75.5	42.2	25.2	70.1	39.0	23.3
88	TC	91.2	85.7	80.2	88.2	82.6	77.0	85.1	79.5	73.8	82.0	76.4	70.6
	SC	48.3	46.2	44.2	47.2	45.1	43.1	46.1	44.0	42.0	45.0	42.9	40.9
	gpm	23.1	17.4	13.6	22.3	16.7	13.0	21.6	16.1	12.5	20.8	15.5	11.9
	wpd	87.4	49.4	30.1	81.6	45.5	27.8	76.0	42.2	25.5	70.7	39.4	23.3
90	TC	91.4	85.8	80.2	88.4	82.7	77.1	85.3	79.5	73.9	82.1	76.3	70.6
	SC	51.4	49.3	47.3	50.3	48.2	46.1	49.2	47.1	45.0	48.0	45.9	43.9
	gpm	23.2	17.4	13.6	22.4	16.7	13.0	21.6	16.1	12.5	20.8	15.4	11.9
	wpd	88.0	49.4	30.1	82.2	45.9	27.8	76.6	42.2	25.5	70.7	39.0	23.3

3-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	118.4	112.6	106.7	114.8	108.8	102.8	111.1	105.1	98.9	107.3	101.2	95.1
	SC	39.8	37.5	35.2	38.3	36.0	33.7	36.9	34.6	32.3	35.4	33.1	30.8
	gpm	29.9	22.8	18.0	29.2	22.0	17.3	28.2	21.3	16.7	27.2	20.5	16.0
	wpd	81.9	47.7	29.7	77.9	44.3	27.6	72.8	41.7	25.6	67.8	38.6	23.6
78	TC	118.3	112.5	106.6	114.7	108.7	102.8	111.0	104.9	98.8	107.2	101.1	95.0
	SC	43.3	41.0	38.7	41.9	39.5	37.3	40.4	38.1	35.8	38.9	36.6	34.4
	gpm	29.9	22.8	18.0	29.1	22.0	17.3	28.2	21.2	16.7	27.2	20.5	16.0
	wpd	81.9	47.7	29.7	77.5	44.3	27.6	72.8	41.1	25.6	67.8	38.6	23.6
80	TC	118.2	112.4	106.6	114.5	108.7	102.7	110.9	104.9	98.9	107.1	101.0	94.9
	SC	46.8	44.5	42.3	45.3	43.1	40.8	43.9	41.6	39.4	42.4	40.1	37.9
	gpm	29.9	22.8	18.0	28.9	22.0	17.3	28.1	21.2	16.7	27.1	20.4	16.0
	wpd	81.9	47.7	29.7	76.6	44.3	27.6	72.4	41.1	25.6	67.4	38.3	23.6
82	TC	118.3	112.6	106.7	114.6	108.8	102.9	110.9	105.0	99.1	107.2	101.2	95.2
	SC	50.3	48.1	45.8	48.9	46.6	44.4	47.4	45.1	42.9	46.0	43.7	41.4
	gpm	29.9	22.8	18.0	28.9	22.1	17.3	28.0	21.3	16.7	27.2	20.4	16.0
	wpd	81.9	47.7	29.7	76.6	44.7	27.6	72.0	41.4	25.6	67.8	38.3	23.6
84	TC	118.5	112.7	106.9	114.8	109.0	103.1	111.1	105.2	99.2	107.3	101.4	95.3
	SC	53.8	51.6	49.3	52.4	50.1	47.9	50.9	48.6	46.4	49.4	47.2	44.9
	gpm	30.0	22.9	18.1	29.0	22.1	17.4	28.0	21.3	16.8	27.0	20.5	16.1
	wpd	82.3	48.0	30.0	77.1	44.7	27.8	72.0	41.7	25.8	67.0	38.6	23.8
86	TC	118.6	112.9	107.1	114.9	109.2	103.3	111.2	105.4	99.4	107.4	101.5	95.4
	SC	57.4	55.1	52.8	55.9	53.6	51.4	54.4	52.2	49.9	52.9	50.7	48.4
	gpm	30.0	22.9	18.1	29.1	22.2	17.4	28.1	21.3	16.8	27.1	20.5	16.1
	wpd	82.3	48.0	30.0	77.5	45.0	27.8	72.4	41.7	25.8	67.4	38.6	23.8
88	TC	118.8	113.1	107.2	115.1	109.3	103.3	111.4	105.5	99.4	107.6	101.6	95.5
	SC	60.9	58.6	56.3	59.4	57.1	54.8	57.9	55.6	53.3	56.4	54.1	51.9
	gpm	30.1	23.0	18.2	29.1	22.2	17.4	28.2	21.3	16.8	27.2	20.6	16.1
	wpd	82.8	48.4	30.2	77.5	45.0	27.8	72.8	41.7	25.8	67.8	38.9	23.8
90	TC	118.9	113.1	107.1	115.2	109.3	103.3	111.4	105.5	99.4	107.6	101.5	95.5
	SC	64.3	62.0	59.7	62.8	60.5	58.2	61.3	59.0	56.7	59.9	57.6	55.3
	gpm	30.1	23.0	18.1	29.2	22.2	17.4	28.2	21.3	16.8	27.2	20.6	16.1
	wpd	83.2	48.4	30.0	77.9	45.0	27.8	72.8	41.7	25.8	67.8	38.9	23.8

4-Row Chilled Water Cooling

EDB	EWT	42			43			44			45		
	TR	8	10	12	8	10	12	8	10	12	8	10	12
74	TC												
	SC												
	gpm												
	wpd												
76	TC	132.0	101.9	98.0	128.1	122.9	117.5	124.2	118.9	113.4	120.2	114.8	109.2
	SC	45.6	35.5	33.9	44.0	41.8	39.6	42.3	40.1	38.0	40.7	38.5	36.3
	gpm	33.4	20.7	16.5	32.4	24.9	19.9	31.4	24.1	19.2	30.4	23.3	18.4
	wpd	73.3	28.1	17.9	68.8	40.8	25.9	64.8	37.9	24.1	60.6	35.5	22.3
78	TC	131.9	126.8	121.5	128.0	122.8	117.4	124.1	118.8	113.3	120.1	114.7	109.1
	SC	49.1	46.9	44.7	47.4	45.3	43.1	45.8	43.6	41.4	44.1	42.0	39.8
	gpm	33.4	25.7	20.5	32.4	24.9	19.9	31.3	24.1	19.2	30.4	23.3	18.4
	wpd	73.0	43.4	27.6	68.8	40.8	25.9	64.4	37.9	24.1	60.6	35.5	22.3
80	TC	131.7	101.7	97.9	127.9	122.7	117.4	124.0	118.7	113.3	120.0	114.6	109.1
	SC	52.5	40.7	39.1	50.9	48.7	46.6	49.2	47.1	44.9	47.6	45.5	43.3
	gpm	33.4	20.6	16.5	32.4	24.9	19.9	31.3	24.1	19.2	30.4	23.3	18.4
	wpd	73.0	27.8	17.9	68.8	40.5	25.9	64.4	37.9	24.1	60.6	35.5	22.3
82	TC	131.8	126.7	121.4	127.9	122.8	117.4	124.0	118.8	113.4	120.0	114.7	109.2
	SC	56.0	53.9	51.7	54.4	52.3	50.1	52.7	50.6	48.5	51.1	49.0	46.8
	gpm	33.4	25.7	20.4	32.4	24.9	19.8	31.4	24.1	19.2	30.4	23.3	18.4
	wpd	73.0	43.4	27.4	68.8	40.8	25.7	64.8	37.9	24.1	60.6	35.5	22.3
84	TC	131.8	126.8	121.5	128.0	122.9	117.5	124.1	118.9	113.4	120.1	114.8	109.2
	SC	59.5	57.4	55.2	57.8	55.8	53.6	56.2	54.1	51.9	54.6	52.5	50.4
	gpm	33.4	25.7	20.5	32.4	24.9	19.8	31.4	24.1	19.1	30.4	23.3	15.0
	wpd	73.3	43.4	27.6	68.8	40.8	25.7	64.8	38.2	23.9	60.6	35.5	14.7
86	TC	131.9	126.8	121.6	128.0	122.9	117.5	124.1	118.9	113.4	120.2	114.8	109.2
	SC	63.0	60.8	58.7	61.3	59.2	57.1	59.7	57.6	55.4	58.1	55.9	53.8
	gpm	33.4	25.7	20.5	32.5	24.9	19.8	31.4	24.1	19.2	30.4	23.3	18.4
	wpd	73.3	43.2	27.6	69.1	40.8	25.7	64.8	38.2	24.1	60.6	35.7	22.3
88	TC	131.9	126.8	121.6	128.1	122.8	117.5	124.2	118.9	113.4	120.2	114.8	109.2
	SC	66.4	64.3	62.2	64.8	62.6	60.5	63.2	61.0	58.9	61.5	59.4	57.2
	gpm	33.4	25.7	20.5	32.5	24.9	19.8	31.4	24.1	19.2	30.5	23.3	18.4
	wpd	73.3	43.2	27.6	69.1	40.5	25.7	64.8	38.2	24.1	60.9	35.7	22.3
90	TC	131.9	126.8	121.5	128.0	122.8	117.5	124.1	118.7	113.5	120.1	114.6	109.3
	SC	69.9	67.7	65.6	68.2	66.1	63.9	66.6	64.4	62.3	64.9	62.8	60.7
	gpm	33.4	25.7	20.5	32.5	24.9	19.9	31.4	24.0	19.2	30.4	23.2	18.4
	wpd	73.3	43.2	27.6	69.1	40.5	25.9	64.8	37.7	24.1	60.6	35.2	22.3

5-Row Chilled Water Cooling

EDB	EWT	42				43				44				45			
	TR	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	
74	TC																
	SC																
	gpm																
	wpd																
76	TC	152.4	148.8	144.9	148.3	144.6	140.6	144.1	140.3	136.1	139.9	135.9	131.6				
	SC	58.4	56.6	54.7	56.4	54.5	52.6	54.3	52.5	50.5	52.3	50.4	48.4				
	gpm	38.7	30.2	24.5	37.6	29.3	23.8	36.6	28.4	23.0	35.4	27.5	22.2				
	wpd	137.0	83.5	55.1	129.4	78.5	51.8	122.6	74.1	48.6	115.0	69.4	45.2				
78	TC	152.5	149.0	145.2	148.5	144.8	140.9	144.3	140.5	143.4	140.1	136.1	131.9				
	SC	62.4	60.7	58.8	60.4	58.6	56.7	58.4	56.5	57.9	56.3	54.4	52.5				
	gpm	38.5	30.2	24.5	37.7	29.4	23.8	36.6	28.4	24.2	35.5	27.5	22.3				
	wpd	135.8	83.5	55.1	130.0	78.9	51.8	122.6	74.1	53.6	115.5	69.4	45.5				
80	TC	152.6	149.2	145.3	148.5	145.0	141.1	144.5	140.7	136.7	140.2	136.3	132.2				
	SC	66.5	64.7	62.8	64.4	62.7	60.8	62.4	60.6	58.7	60.3	58.5	56.6				
	gpm	38.5	30.3	24.5	37.5	29.4	23.9	36.7	28.5	23.1	35.6	27.6	22.4				
	wpd	135.8	83.9	55.1	128.8	78.9	52.2	123.2	74.5	49.0	116.0	69.8	45.8				
82	TC	152.7	149.3	145.5	148.6	145.1	141.2	144.5	140.9	136.8	140.3	136.5	132.3				
	SC	70.5	68.8	66.9	68.4	66.7	64.8	66.4	64.6	62.7	64.4	62.5	60.6				
	gpm	38.6	30.3	24.5	37.5	29.4	23.8	36.4	28.5	23.1	35.6	27.6	22.4				
	wpd	136.4	83.9	55.1	128.8	79.4	51.8	121.5	74.5	49.0	116.0	69.8	45.8				
84	TC	152.8	149.4	145.6	148.7	145.2	141.3	144.6	141.0	136.9	140.4	136.6	132.5				
	SC	74.5	72.8	70.9	72.4	70.7	68.8	70.4	68.6	66.7	68.4	66.5	64.6				
	gpm	38.6	30.3	24.5	37.6	29.4	23.9	36.5	28.6	23.0	35.6	27.7	22.4				
	wpd	136.4	83.9	55.1	129.4	79.4	52.2	122.1	75.0	48.6	116.0	70.2	45.8				
86	TC	152.8	149.5	145.7	148.8	145.3	141.4	144.6	141.0	137.0	140.4	136.7	132.4				
	SC	78.4	76.8	74.9	76.4	74.7	72.8	74.3	72.6	70.7	72.3	70.5	68.5				
	gpm	38.7	30.4	24.6	37.6	29.4	23.9	36.5	28.6	23.1	35.4	27.7	22.3				
	wpd	137.0	84.4	55.5	129.4	79.4	52.2	122.1	75.0	49.0	115.0	70.2	45.5				
88	TC	152.9	149.5	145.7	148.8	145.3	141.4	144.6	141.0	137.0	140.4	136.7	132.5				
	SC	82.4	80.7	78.9	80.4	78.6	76.7	78.3	76.6	74.6	76.3	74.5	72.5				
	gpm	38.7	30.4	24.6	37.6	29.4	23.9	36.5	28.6	23.1	35.4	27.7	22.4				
	wpd	137.0	84.4	55.5	129.4	79.4	52.2	122.1	75.0	49.0	115.0	70.2	45.8				
90	TC	152.8	149.5	145.7	148.8	145.3	141.4	144.6	141.0	137.0	140.4	136.6	132.6				
	SC	86.4	84.7	82.8	84.3	82.6	80.7	82.3	80.5	78.6	80.2	78.4	76.5				
	gpm	38.7	30.4	24.6	37.6	29.4	23.9	36.6	28.6	23.1	35.4	27.7	22.4				
	wpd	137.0	84.4	55.5	129.4	79.4	52.2	122.6	75.0	49.0	115.0	70.2	45.8				



Daikin Applied Training and Development

Now that you have made an investment in modern, efficient Daikin equipment, its care should be a high priority. For training information on all Daikin HVAC products, please visit us at www.DaikinApplied.com and click on Training, or call 540-248-9646 and ask for the Training Department.

Warranty

All Daikin equipment is sold pursuant to its standard terms and conditions of sale, including Limited Product Warranty. Consult your local Daikin Applied representative for warranty details. Refer to Form 933-430285Y. To find your local Daikin Applied representative, go to www.DaikinApplied.com.

Aftermarket Services

To find your local parts office, visit www.DaikinApplied.com or call 800-37PARTS (800-377-2787).
To find your local service office, visit www.DaikinApplied.com or call 800-432-1342.

This document contains the most current product information as of this printing. For the most up-to-date product information, please go to www.DaikinApplied.com.

Products manufactured in an ISO Certified Facility.