

## TEC Custom Solutions Application 2403 VAV with Modified Parallel Fan and Reheat

---

This document contains the following topics:

- Overview
- Hardware inputs
  - Analog
  - Digital
- Hardware outputs
  - Analog
  - Digital
- Ordering Notes
- Sequence of Operation
  - Control temperature set points
  - Day and night modes
  - Night mode override switch
  - Heating/cooling switchover
  - Control loops
  - Hot water reheat
  - Sequencing logic
  - Calibration
  - Fan Operation
  - Fail-safe operation
- Application notes
- Wiring diagram
- Point database

## Overview

In Application 2403, the controller modulates the supply air damper of the terminal box to provide cooling. A hot water valve is modulated for heating. During heating operation, the supply air damper is set to a minimum position, or it can be modulated as a source of heating. The terminal box also has a parallel fan that recirculates the room air. In order for the terminal box to work properly, the central air handling unit must provide supply air. Refer to Figures 2403-1 through 2403-3.






Figure 2403-1. Application 2403 Control Drawing.



**Figure 2403-2. Application 2403 Control Schedule with Minimum Supply Air in Heating Mode.**



**Figure 2403-3. Application 2403 Control Schedule with Modulating Damper in Heating Mode.**

## Hardware Inputs

### Analog

- Air velocity sensor
- Room temperature sensor
- Room temperature set point dial (optional)

### Digital

- Night mode override (optional)
- Wall switch (optional)

## Hardware Outputs

### Analog

- None

### Digital

- Damper actuator
- Fan
- Valve actuator

## Ordering Notes

TEC Custom Solution number 250.

## Point Database

The point database information is in Table 2403-1 at the end of this document.

## Sequence of Operation

The following paragraphs present the sequence of operation for Application 2403, “VAV Parallel Fan with Hot Water Reheat.”

### Control Temperature Set Points

Depending on the controller’s current operational mode (day or night), the control temperature set point, CTL STPT (Point 92) holds the value of one of the following set points:

**Day Mode** – In day mode, CTL STPT holds the value of DAY CLG STPT (Point 06) or DAY HTG STPT (Point 07). If the room temperature sensor has a set point dial and STPT DIAL (Point 14) is set to YES, then CTL STPT holds the value of RM STPT DIAL (Point 13).

If the set point dial is used and the value of RM STPT DIAL is less than the value of RM STPT MIN (Point 11), then CTL STPT holds the value of RM STPT MIN. If the value of RM STPT DIAL is greater than the value of RM STPT MAX (Point 12), then CTL STPT holds the value of RM STPT MAX.

**Night Mode** – In night mode, CTL STPT holds the value of NGT CLG STPT (Point 08) or NGT HTG STPT (Point 09).

**NOTE:** The value of CTL TEMP (Point 78) is the same as the value of the point ROOM TEMP (Point 04), unless CTL TEMP is overridden.

### Day and Night Modes

The day/night status of the space is determined by the status of DAY.NGT (Point 29). The control of this point differs depending on whether the controller is monitoring the status of a wall switch or if the controller is connected to a field panel.

When a wall switch is physically connected to the termination strip on the controller at DI 2 (Figures 2403-1 and 2403-5), and WALL SWITCH (Point 18) equals YES, the controller monitors the status of DI 2. When the status of DI 2 (Point 24) is ON (the switch is closed), DAY.NGT is set to DAY indicating that the controller is in day mode. When the status of DI 2 is OFF (the switch is open), DAY.NGT is set to NIGHT, indicating the controller is in night mode.

When WALL SWITCH equals NO, the controller does not monitor the status of the wall switch, even if one is connected to it. In this case, and if the controller is operating stand-alone (not connected to a field panel), then the controller stays in day mode all the time. If the controller is operating with centralized control (connected to a field panel), then the field panel can send an operator or PPCL command to override the status of DAY.NGT. Refer to *Powers Process Control Language (PPCL) User’s Manual* (125-1896) and *Field Panel User’s Manual* (125-1895) for more information.

## Night Mode Override Switch

If an override switch is present on the room temperature sensor and a value (in hours) other than zero has been entered into OVRD TIME (Point 20), then by pressing the override switch a room occupant can reset the controller to day operational mode for the amount of time set in OVRD TIME. The status of NGT OVRD (Point 21) changes to DAY and remains there until override time elapses, at which time the controller returns to night mode and the status of NGT OVRD changes back to NIGHT.

It is only when the controller is in night mode that the override switch on the room sensor has any effect on the controller.

## Heating/Cooling Switchover

By monitoring room temperature and the demand for heating and cooling (as determined by the temperature control loops), the heating/cooling switchover determines whether the controller operates in heating or cooling mode.

If all of the following conditions are met for the length of time set in SWITCH TIME (Point 86), then the controller switches from heating to cooling mode by setting HEAT.COOL (Point 05) to COOL:

- HTG LOOPOUT (Point 80) is less than SWITCH LIMIT (Point 85).
- CTL TEMP (Point 78) is above CTL STPT (Point 92) by at least the value set in SWITCH DBAND (Point 90).
- CTL TEMP is greater than the appropriate cooling set point minus SWITCH DBAND.

If all of the following conditions are met for the length of time set in SWITCH TIME, then the controller switches from cooling to heating mode by setting HEAT.COOL to HEAT:

- CLG LOOPOUT (Point 79) is less than SWITCH LIMIT.
- CTL TEMP is below CTL STPT by at least the value set in SWITCH DBAND.
- CTL TEMP is less than the appropriate heating set point plus SWITCH DBAND.



### CAUTION:

This heating/cooling switchover mechanism is not affected by the air temperature in the supply duct.

To change the value of HEAT.COOL (Point 05) based on the supply air temperature, HEAT.COOL must be commanded through PPCL. This is required when the flow loop is used to control cooling in cooling mode and heat in heating mode. Refer to Examples 1 through 3 in the *Sequencing Logic* section that follows. If the flow loop is used in heating mode just to meet minimum air requirements, then the heating/cooling switchover mechanism operates as described in this section to control HEAT.COOL. Refer to Example 4 in the *Sequencing Logic* section.

## Control Loops

The terminal box is controlled by three Proportional, Integral, and Derivative (PID) control loops: two temperature loops and a flow loop.

**Temperature Loops** – The two temperature loops are a cooling loop and a heating loop. The active temperature loop maintains room temperature at the value in CTL STPT (Point 92). Refer to the *Control Temperature Set Points* section for more information.

The cooling temperature loop generates a cooling loopout which is then used to generate FLOW STPT (Point 93). FLOW STPT is the result of scaling the cooling loopout to the appropriate range of values determined by CLG FLOW MIN (Point 31) and CLG FLOW MAX (Point 32). In order to scale it, the loopout is multiplied by the range (MAX – MIN) and then added to the minimum set point.

When CLG FLOW MIN does not equal 0 CFM, FLOW STPT does not equal CLG LOOPOUT (Point 79). The minimum flow set point is  $(\text{CLG FLOW MIN} \div \text{CLG FLOW MAX}) \times 100\%$  flow. FLOW STPT is  $[\text{CLG LOOPOUT} \times (100\% - \text{minimum set point})] + \text{minimum set point}$ .

For example:

If CLG FLOW MIN = 200 CFM, and CLG FLOW MAX = 1000 CFM,

then,

the minimum flow set point is  
 $(200 \text{ CFM} \div 1000 \text{ CFM}) \times 100\% \text{ flow} = 20\%$

When CLG LOOPOUT is 0%, FLOW STPT equals 20% flow.

$$[0\% \times (100\% - 20\%)] + 20\% = 20\%$$

This ensures that the airflow out of the terminal box is no less than CLG FLOW MIN.

When CLG LOOPOUT is 50%, FLOW STPT equals 60% flow.

$$[50\% \times (100\% - 20\%)] + 20\% = 60\%$$

When CLG LOOPOUT is 100%, FLOW STPT equals 100% flow.

$$[100\% \times (100\% - 20\%)] + 20\% = 100\%$$

If the controller is in heating mode, then the operation of the flow loop is flexible. It can be set up to do **one** of the following:

- Constantly maintain an airflow out of the terminal box equal to HTG FLOW MIN (Point 33).
- Operate in sequence with the hot water valve.
- Operate parallel with the hot water valve.
- Operate overlapping with the hot water valve.

If the first option is chosen, then HTG LOOPOUT (Point 80) controls the hot water valve in order to maintain the room temperature. If any of the remaining three options is chosen, then HTG LOOPOUT controls both the flow loop set point (FLOW STPT) and the hot water valve in order to maintain the room temperature. Refer to the *Sequencing Logic* section(s) for more information.

HTG LOOPOUT adjusts the value of FLOW STPT differently depending on which flow loop setup is chosen. However, the following rule applies no matter what setup is chosen:

- In heating mode, FLOW STPT is never set below  
 $(\text{HTG FLOW MIN} \div \text{HTG FLOW MAX}) \times 100\% \text{ flow}$ , or above 100% flow.

**Flow Loop** – The flow loop maintains minimum airflow and maximum airflow through CTL FLOW MIN (Point 76) and CTL FLOW MAX (Point 77).

When the controller is in cooling mode, CTL FLOW MIN equals CLG FLOW MIN and CTL FLOW MAX equals CLG FLOW MAX.

When the controller is in heating mode, CTL FLOW MIN equals HTG FLOW MIN and CTL FLOW MAX equals HTG FLOW MAX.

CLG FLOW MIN can be set equal to but not greater than CLG FLOW MAX, and HTG FLOW MIN can be set equal to but not greater than HTG FLOW MAX. If the minimum and maximum values are set equal, then the flow loop becomes a constant volume loop and its ability to control temperature is lost.

The flow loop maintains FLOW STPT by modulating the supply air damper point, DMPR COMD (Point 48). The flow loop maintains the airflow between CTL FLOW MIN and CTL FLOW MAX.

FLOW (Point 75) is the input value for the flow loop. It is calculated as a percentage based on where AIR VOLUME (Point 35) is between 0 CFM and CTL FLOW MAX. In the following text, this percentage is referred to as *% flow*.

- If AIR VOLUME equals 0 CFM, then FLOW is 0% flow.
- If AIR VOLUME equals CTL FLOW MAX, then FLOW is 100% flow.

The low limit of FLOW STPT will be the percentage that corresponds to the volume given in CTL FLOW MIN. This percentage can be calculated as:  
 $(\text{CTL FLOW MIN} \div \text{CTL FLOW MAX}) \times 100\% \text{ flow}$ . The flow loop ensures that the supply air is not less than CTL FLOW MIN.

For example:

If CTL FLOW MIN equals 250 CFM, and if CTL FLOW MAX equals 1000 CFM,

then,

$$\begin{aligned} \text{the low limit of FLOW STPT} &= (250 \text{ CFM} \div 1000 \text{ CFM}) \times 100\% \text{ flow} \\ &= 0.25 \times 100\% \text{ flow} \\ &= 25\% \text{ flow} \end{aligned}$$



Since 25% of 1000 CFM equals 250 CFM, the minimum airflow out of the terminal box is 250 CFM.

## Hot Water Reheat

The heating loop modulates the heating valve to warm up the room. In cooling mode, the heating valve is closed.

## Sequencing Logic

In heating mode, this application includes logic that allows the flow loop to operate in sequence, parallel, or overlapping with the hot water valve. This algorithm is very similar to the spring range sequencing of valves and dampers. Portions of the output of the heating loop, HTG LOOPOUT (Point 80) will drive both the flow loop and the hot water valve from 0 to 100%.

This concept is illustrated in the following three examples. (For simplicity, assume that in these examples HTG FLOW MIN (Point 33) equals 0 CFM. When this is done, FLOW STPT (Point 93) equals 0 when HTG LOOPOUT equals 0. The ladder diagrams in Figure 2403-4 show sequenced, parallel, and overlapping flow loop operations with reheat. The vertical bars show the output of heating loopout from 0 to 100%. The horizontal bars (reheat start, flow start, etc.) show the action that occurs when the loop output rises above the horizontal bar. The relative positions shown on the graphs are for illustration purposes only and may differ from the examples.)

**NOTE:** The default setups for FLOW START (Point 16) and FLOW END (Point 17) are 0. This provides minimum airflow during heating mode.




Figure 2403-4. Sequenced, Parallel, and Overlapping Flow Loop Operations with Hot Water Reheat.

**Example 1:** Assume that your system has a hot water valve operating *in sequence* with the flow loop.

If:

- FLOW START (Point 16) equals 0%
- FLOW END (Point 17) equals 50%
- REHEAT START (Point 22) equals 50%
- REHEAT END (Point 23) equals 100%

then,

- When HTG LOOPOUT (Point 80) equals 0%, FLOW STPT will equal 0% flow.
- When HTG LOOPOUT equals 25%, FLOW STPT will equal 50% flow.
- When HTG LOOPOUT is greater than or equal to 50%, FLOW STPT will equal 100% flow.
- When HTG LOOPOUT is less than or equal to 50%, VLV COMD (Point 52) will equal 0% open.
- When HTG LOOPOUT equals 75%, VLV COMD will equal 50% open.
- When HTG LOOPOUT equals 100%, VLV COMD will equal 100% open.

**Example 2:** Assume that your system has a hot water valve operating *parallel* with the flow loop.

If,

- FLOW START (Point 16) equals 0%
- FLOW END (Point 17) equals 100%
- REHEAT START (Point 22) equals 0%
- REHEAT END (Point 23) equals 100%

then,

- When HTG LOOPOUT equals 0%, FLOW STPT will equal 0% flow.
- When HTG LOOPOUT equals 50%, FLOW STPT will equal 50% flow.
- When HTG LOOPOUT equals 100%, FLOW STPT will equal 100% flow.
- When HTG LOOPOUT equals 0%, VLV COMD will equal 0% open.
- When HTG LOOPOUT equals 50%, VLV COMD will equal 50% open.
- When HTG LOOPOUT equals 100%, VLV COMD will equal 100% open.

**Example 3:** Assume that your system has a hot water valve that is to operate *overlapping* with the flow loop. If,

- FLOW START (Point 16) equals 0%
- FLOW END (Point 17) equals 75%
- REHEAT START (Point 22) equals 25%
- REHEAT END (Point 23) equals 100%

then,

- When HTG LOOPOUT equals 0%, FLOW STPT will equal 0% flow.
- When HTG LOOPOUT equals 37.5%, FLOW STPT will equal 50% flow.
- When HTG LOOPOUT is greater than or equal to 75%, FLOW STPT will equal 100% flow.
- When HTG LOOPOUT is less than or equal to 25%, VLV COMD will equal 0% open.
- When HTG LOOPOUT equals 62.5%, VLV COMD will equal 50% open.
- When HTG LOOPOUT equals 100%, VLV COMD will equal 100% open.

Another option the sequencing logic provides is to have the flow loop provide an airflow equal to HTG FLOW MIN throughout the heating mode, with all temperature control being done by the hot water valve. This is accomplished by setting FLOW START and FLOW END to zero. Example 4 clarifies this:

**Example 4:** Assume that in your system a hot water valve provides temperature control in heating mode, while the flow loop controls the minimum air requirements. Also, assume that HTG FLOW MIN equals 170 CFM and that HTG FLOW MAX equals 1000 CFM. If,

- FLOW START (Point 16) equals 0%
- FLOW END (Point 17) equals 0%
- REHEAT START (Point 22) equals 0%
- REHEAT END (Point 23) equals 100%

then,

- When HTG LOOPOUT equals 0%, FLOW STPT will equal  $(170 \text{ CFM} \div 1000 \text{ CFM}) \times 100\% \text{ flow} = 17\% \text{ flow}$ .  
This will cause the flow loop to maintain an airflow of 170 CFM out of the terminal box.
- When HTG LOOPOUT equals 50%, FLOW STPT will equal 17% flow.
- When HTG LOOPOUT equals 100%, FLOW STPT will equal 17% flow.
- When HTG LOOPOUT equals 0%, VLV COMD will equal 0% open.
- When HTG LOOPOUT equals 50%, VLV COMD will equal 50% open.
- When HTG LOOPOUT equals 100%, VLV COMD will equal 100% open.

## Calibration

**Air Velocity Transducer** – Calibration of the controller's internal air velocity transducers is periodically required to maintain accurate air velocity readings. CAL SETUP (Point 95) is set with the desired calibration option during controller startup. Depending upon the value of CAL SETUP, calibration can be set to take place automatically or manually. If the status of CAL AIR (Point 94) is YES, then calibration is in progress.

The damper is commanded closed to get a zero airflow reading during calibration.

**Hot Water Valve** – Calibration of a hot water valve is done by commanding the valve to fully closed.

At the end of a calibration sequence, CAL AIR returns to NO automatically. A status of NO indicates that the controller is not in a calibration sequence.

## Fan Operation

During normal operation, AIR VOLUME (Point 35) is Normal, and the fan is controlled as follows:

- The fan will turn ON only when the airflow out of the supply duct, FLOW (Point 75), is less than the value stored in PARALLEL ON (Point 28). (This means that there is not enough airflow out of the supply duct to transfer heat supplied by the hot water valve into the room.)
- The fan will turn OFF when the airflow out of the supply duct, FLOW (Point 75), is greater than the value stored in PARALLEL OFF (Point 30). (This means that there is enough airflow out of the supply duct to transfer heat supplied by the hot water valve into the room.)

If the conditions have not been satisfied to turn the fan either ON or OFF, then the state of the fan remains unchanged. (If it is ON, it remains ON; if OFF, it remains OFF.)

During fail-safe operation, AIR VOLUME (Point 35) is Failed, and the fan is controlled as follows:

- The fan will turn ON only when FLOW STPT (Point 93) is less than the value stored in PARALLEL ON (Point 28).
- The fan will turn OFF only when FLOW STPT is greater than the value stored in PARALLEL OFF (Point 30).

If the conditions have not been satisfied to turn the fan either ON or OFF, then the state of the fan remains unchanged. If it is ON, it remains ON; if OFF, it remains OFF.

## Fail-safe Operation

If the air velocity sensor fails, then the controller uses pressure dependent control. The temperature loop controls the operation of the damper.

If the room temperature sensor fails, then the controller operates using the last known temperature value.

## Application Notes

1. If the temperature swings in the room are excessive or if there is trouble in maintaining the set point, then either the cooling loop, the heating loop or both need to be tuned. If FLOW (Point 75) is oscillating while FLOW STPT (Point 93) is constant, then the flow loop requires tuning. Refer to the *APOGEE Automation Service Procedures* on InfoLink for more information.
2. The Terminal Box Controller – Electronic Output, as shipped from the factory, keeps all associated equipment OFF. Refer to the Equipment Controllers tab in the *APOGEE Automation Start-up Procedures* on InfoLink for information on how to release the controller and its equipment to application control.
3. Spare DOs can be used as auxiliary points that are controlled by the field panel after being defined in the field panel's database. DO 3 and DO 4 or DO 5 and DO 6 may be used as auxiliary motor points. If using a pair of spare DOs to control a motor, you must unbundle the corresponding motor command point.


## Wiring Diagram

The point wiring for Application 2403 is shown in Figure 2403-5.

**CAUTION:**

The Controller's DOs control 24 Vac loads only. The maximum rating is 12 VA for each DO. Use an interposing 220 V 4-relay module for any of the following:

- VA requirements higher than the maximum
- 110 or 220 Vac requirements
- DC power requirements



TEC2403WDR1

\* REFER TO ACTUATOR INSTALLATION INSTRUCTIONS FOR SPECIFIC WIRING TERMINATIONS

**Figure 2403-5. Application 2403 Wiring Diagram.**

Table 2403-1. Point Database for Application 2403.

| Point Number | Descriptor   | Factory Default (SI Units) | Engr Units (SI Units) | Slope (SI Units) | Intercept (SI Units) | On Text | Off Text |
|--------------|--------------|----------------------------|-----------------------|------------------|----------------------|---------|----------|
| 01           | CTLR ADDRESS | 99                         | --                    | 1                | 0                    | --      | --       |
| 02           | APPLICATION  | 2091                       | --                    | 1                | 0                    | --      | --       |
| {04}         | ROOM TEMP    | 74.0 (23.44888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| {05}         | HEAT.COOL    | COOL                       | --                    | --               | --                   | HEAT    | COOL     |
| 06           | DAY CLG STPT | 74.0 (23.44888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| 07           | DAY HTG STPT | 70.0 (21.20888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| 08           | NGT CLG STPT | 82.0 (27.92888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| 09           | NGT HTG STPT | 65.0 (18.40888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| 11           | RM STPT MIN  | 55.0 (12.80888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| 12           | RM STPT MAX  | 90.0 (32.40888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| {13}         | RM STPT DIAL | 74.0 (23.44888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| 14           | STPT DIAL    | NO                         | --                    | --               | --                   | YES     | NO       |
| {15}         | AUX TEMP     | 74.0 (23.495556)           | DEG F (DEG C)         | 0.5 (0.28)       | 37.5(3.055556)       | --      | --       |
| 16           | FLOW START   | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 17           | FLOW END     | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 18           | WALL SWITCH  | NO                         | --                    | --               | --                   | YES     | NO       |
| {19}         | DI OVRD SW   | OFF                        | --                    | --               | --                   | ON      | OFF      |
| 20           | OVRD TIME    | 0                          | HRS                   | 1                | 0                    | --      | --       |
| {21}         | NGT OVRD     | NIGHT                      | --                    | --               | --                   | NIGHT   | DAY      |
| 22           | REHEAT START | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 23           | REHEAT END   | 100.0                      | PCT                   | 0.4              | 0.0                  | --      | --       |
| {24}         | DI 2         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {25}         | DI 3         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| 28           | PARALLEL ON  | 50.0                       | PCT                   | 0.4              | 0.0                  | --      | --       |
| {29}         | DAY.NGT      | DAY                        | --                    | --               | --                   | NIGHT   | DAY      |
| 30           | PARALLEL OFF | 60.0                       | PCT                   | 0.4              | 0.0                  | --      | --       |
| 31           | CLG FLOW MIN | 220 (103.818)              | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |
| 32           | CLG FLOW MAX | 2200 (1038.18)             | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |
| 33           | HTG FLOW MIN | 220 (103.818)              | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |

1. Points not listed are not used in this application.
2. A single value in a column means that the value is the same in English units and in SI units.
3. Point numbers that appear in brackets { } may be unbundled at the field panel.

continued on next page...

Table 2403-1. Point Database for Application 2403.

| Point Number | Descriptor   | Factory Default (SI Units) | Engr Units (SI Units) | Slope (SI Units) | Intercept (SI Units) | On Text | Off Text |
|--------------|--------------|----------------------------|-----------------------|------------------|----------------------|---------|----------|
| 34           | HTG FLOW MAX | 2200 (1038.18)             | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |
| {35}         | AIR VOLUME   | 0 (0.0)                    | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |
| 36           | FLOW COEFF   | 1.0                        | --                    | 0.01             | 0.0                  | --      | --       |
| {41}         | DO 1         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {42}         | DO 2         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {43}         | DO 3         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {44}         | DO 4         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {45}         | DO 5         | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {46}         | FAN          | OFF                        | --                    | --               | --                   | ON      | OFF      |
| {48}         | DMPR COMD    | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| {49}         | DMPR POS     | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 51           | MTR1 TIMING  | 95                         | SEC                   | 1                | 0                    | --      | --       |
| {52}         | VLV COMD     | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| {53}         | VLV POS      | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 55           | MTR2 TIMING  | 130                        | SEC                   | 1                | 0                    | --      | --       |
| 56           | DMPR ROT ANG | 90                         | --                    | 1                | 0                    | --      | --       |
| 58           | MTR SETUP    | 0                          | --                    | 1                | 0                    | --      | --       |
| 59           | DO DIR. REV  | 0                          | --                    | 1                | 0                    | --      | --       |
| 63           | CLG P GAIN   | 20.0 (36.0)                | --                    | 0.25 (0.45)      | 0.0                  | --      | --       |
| 64           | CLG I GAIN   | 0.01 (0.018)               | --                    | 0.001 (0.0018)   | 0.0                  | --      | --       |
| 65           | CLG D GAIN   | 0 (0.0)                    | --                    | 2 (3.6)          | 0                    | --      | --       |
| 66           | CLG BIAS     | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 67           | HTG P GAIN   | 10.0 (18.0)                | --                    | 0.25 (0.45)      | 0.0                  | --      | --       |
| 68           | HTG I GAIN   | 0.01 (0.018)               | --                    | 0.001 (0.0018)   | 0.0                  | --      | --       |
| 69           | HTG D GAIN   | 0 (0.0)                    | --                    | 2 (3.6)          | 0                    | --      | --       |
| 70           | HTG BIAS     | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 71           | FLOW P GAIN  | 0.0                        | --                    | 0.05             | 0.0                  | --      | --       |
| 72           | FLOW I GAIN  | 0.01                       | --                    | 0.001            | 0.0                  | --      | --       |
| 73           | FLOW D GAIN  | 0                          | --                    | 2                | 0                    | --      | --       |
| 74           | FLOW BIAS    | 50.0                       | PCT                   | 0.4              | 0.0                  | --      | --       |

1. Points not listed are not used in this application.

2. A single value in a column means that the value is the same in English units and in SI units.

3. Point numbers that appear in brackets { } may be unbundled at the field panel.

*continued on next page...*



Table 2403-1. Point Database for Application 2403.

| Point Number | Descriptor   | Factory Default (SI Units) | Engr Units (SI Units) | Slope (SI Units) | Intercept (SI Units) | On Text | Off Text |
|--------------|--------------|----------------------------|-----------------------|------------------|----------------------|---------|----------|
| {75}         | FLOW         | 0.0                        | PCT                   | 0.25             | 0.0                  | --      | --       |
| {76}         | CTL FLOW MIN | 220 (103.818)              | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |
| {77}         | CTL FLOW MAX | 2200 (1038.18)             | CFM ( LPS)            | 4 (1.8876)       | 0                    | --      | --       |
| {78}         | CTL TEMP     | 74.0 (23.44888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| {79}         | CLG LOOPOUT  | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| {80}         | HTG LOOPOUT  | 0.0                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 85           | SWITCH LIMIT | 5.2                        | PCT                   | 0.4              | 0.0                  | --      | --       |
| 86           | SWITCH TIME  | 10                         | MIN                   | 1                | 0                    | --      | --       |
| 90           | SWITCH DBAND | 1.0 (0.56)                 | DEG F (DEG C)         | 0.25 (0.14)      | 0.0                  | --      | --       |
| {91}         | TOTAL VOLUME | 0 (0)                      | CF ( L)               | 4 (113)          | 0                    | --      | --       |
| {92}         | CTL STPT     | 74.0 (23.44888)            | DEG F (DEG C)         | 0.25 (0.14)      | 48.0(8.88888)        | --      | --       |
| {93}         | FLOW STPT    | 0.0                        | PCT                   | 0.25             | 0.0                  | --      | --       |
| {94}         | CAL AIR      | NO                         | --                    | --               | --                   | YES     | NO       |
| 95           | CAL SETUP    | 4                          | --                    | 1                | 0                    | --      | --       |
| 96           | CAL TIMER    | 12                         | HRS                   | 1                | 0                    | --      | --       |
| 97           | DUCT AREA    | 1.0 (0.09292)              | SQ. FT (SQ M)         | 0.025 (0.002323) | 0.0                  | --      | --       |
| 98           | LOOP TIME    | 5                          | SEC                   | 1                | 0                    | --      | --       |
| {99}         | ERROR STATUS | 0                          | --                    | 1                | 0                    | --      | --       |

1. Points not listed are not used in this application.
2. A single value in a column means that the value is the same in English units and in SI units.
3. Point numbers that appear in brackets { } may be unbundled at the field panel.